

Filename: PMP9806-BOM.xls
 Variant: 001
 Generated: 2/4/2017 1:58:40 PM
 SVN path: \$URL::
 SVN rev: \$Rev: \$

\$

precise current limit circuit for the TPS61088 Boost converter

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
!PCB	1		Printed Circuit Board		PMP9806	Any	-	-
C1, C2, C4, C5, C6, C7	6	22uF	CAP, CERM, 22 µF, 16 V, +/- 10%, X5R, 1206	1206	GRM31CR61C226KE15L	MuRata		
C3	1	1uF	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603	GRM188R71E105KA12D	MuRata		
C8	1	4700pF	CAP, CERM, 4700 pF, 50 V, +/- 10%, X5R, 0402	0402	GRM155R61H472KA01D	MuRata		
C9, C16, C17	3	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X5R, 0402	0402	GRM155R61C104KA88D	MuRata		
C11	1	100pF	CAP, CERM, 100 pF, 50 V, +/- 1%, C0G/NP0, 0402	0402	GRM155C1H101FA01D	MuRata		
C13, C20	2	47pF	CAP, CERM, 47 pF, 50 V, +/- 1%, C0G, 0402	0402	GRM155C1H470FA01D	MuRata		
C14	1	4.7uF	CAP, CERM, 4.7uF, 10V, +/-10%, X5R, 0603	0603	0603ZD475KAT2A	AVX		
C15	1	0.047uF	CAP, CERM, 0.047 µF, 16 V, +/- 10%, X7R, 0402	0402	GRM155R71C473KA01D	MuRata		
C18	1	10uF	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0603	0603	C1608X5R1E106M080AC	TDK		
C19	1	100pF	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402	GRM155C1H101JA01D	MuRata		
D1	1	75V	Diode, Switching, 75 V, 0.3 A, SMD, 2-Leads, Body 1.2x0.8mm	SMD, 2-Leads, Body 1.2x0.8mm	1N4148WT	Fairchild Semiconductor		
JP1	1		Header, 100mil, 3x1, Tin, TH	Header, 3 PIN, 100mil, Tin	PEC03SAAN	Sullins Connector Solutions		
L1	1	1.8uH	Inductor, Shielded Drum Core, Metal Composite, 1.2 µH, 12.9 A, 0.007 ohm, SMD	9.5x8.7mm	CDMC8D28NP-1R2MC	Sumida		
R1	1	768k	RES, 768 k, 1%, 0.063 W, 0402	0402	CRCW0402768KFKED	Vishay-Dale		
R2, R3, R4	3	120k	RES, 120 k, 1%, 0.063 W, 0402	0402	CRCW0402120KFKED	Vishay-Dale		
R5, R8	2	100k	RES, 100k ohm, 1%, 0.063W, 0402	0402	CRCW0402100KFKED	Vishay-Dale		
R6	1	17.4k	RES, 17.4k ohm, 1%, 0.063W, 0402	0402	CRCW040217K4FKED	Vishay-Dale		
R7	1	330k	RES, 330 k, 5%, 0.063 W, 0402	0402	CRCW0402330KJNED	Vishay-Dale		
R10	1	0.025	RES, 0.025, 1%, 1 W, 2010	2010	CSRN2010FK25L0	Stackpole Electronics Inc		
R11	1	10.0	RES, 10.0, 1%, 0.063 W, 0402	0402	CRCW040210R0FKED	Vishay-Dale		
R12	1	12.1	RES, 12.1, 1%, 0.063 W, 0402	0402	CRCW040212R1FKED	Vishay-Dale		
R15, R16	2	10.5k	RES, 10.5 k, 1%, 0.063 W, 0402	0402	CRCW040210K5FKED	Vishay-Dale		
R17	1	232k	RES, 232 k, 1%, 0.063 W, 0402	0402	CRCW0402232KFKED	Vishay-Dale		
R18	1	169k	RES, 169 k, 1%, 0.063 W, 0402	0402	CRCW0402169KFKED	Vishay-Dale		
R20	1	0	RES, 0, 5%, 0.063 W, 0402	0402	RC0402JR-070RL	Yageo America		
U1	1		13.2-V Output, Synchronous Boost Converter with 10-A Switch, RHL0020A	RHL0020A	TPS61088RHLR	Texas Instruments	TPS61088RHLT	Texas Instruments
U2	1		3-MHz, Low-Power, Internal EMI Filter, RRIO, Operational Amplifier, DGK0008A (VSSOP-8)	DGK0008A	TLV2314IDGKR	Texas Instruments	TLV2314IDGKT	Texas Instruments
C12	0	2200pF	CAP, CERM, 2200 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603	GRM1885C1H222JA01D	MuRata		
R9	0	1.00	RES, 1.00, 1%, 0.125 W, 0805	0805	CRCW08051R00FKEA	Vishay-Dale		
R161	0	16.2k	RES, 16.2 k, 1%, 0.063 W, 0402	0402	CRCW040216K2FKED	Vishay-Dale		
R162	0	7.87k	RES, 7.87 k, 1%, 0.063 W, 0402	0402	CRCW04027K87FKED	Vishay-Dale		

Notes:

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
-------------------	-----------------	--------------	--------------------	-------------------------	-------------------	---------------------	-----------------------------	-------------------------------

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated