

PMP10523 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPCB1	1		PMP10505	Any	PMP10505 REV A	N/A
C1, C2, C3, C4	4	4.7uF	C3225X7S2A475K200AB	TDK	CAP, CERM, 4.7uF, 100V, +/-10%, X7S, 1210	1210
C5	1	0.22uF	GRM188R71C224KA01D	MuRata	CAP, CERM, 0.22uF, 16V, +/-10%, X7R, 0603	0603
C6	1	0.1uF	GRM188R72A104KA35D	MuRata	CAP, CERM, 0.1uF, 100V, +/-10%, X7R, 0603	0603
C7	1	330pF	GRM188R71H331KA01D	MuRata	CAP, CERM, 330pF, 50V, +/-10%, X7R, 0603	0603
C8	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100pF, 50V, +/-5%, C0G/NP0, 0603	0603
C9	1	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	0603
C101, C102	2	1uF	GRM21BR71E105KA99L	MuRata	CAP, CERM, 1uF, 25V, +/-10%, X7R, 0805	0805
D2	1	200V	DFLS1200-7	Diodes Inc.	Diode, Schottky, 200V, 1A, PowerDI123	PowerDI123
D101, D102	2	43V	BZX84C43LT1G	ON Semiconductor	Diode, Zener, 43V, 225mW, SOT-23	SOT-23
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
L1	1	220uH	MSS1038-224KLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 220uH, 0.97A, 0.76 ohm, SMD	MSS1038
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q1	1	200V	IRF5801TRPBF	International Rectifier	MOSFET, N-CH, 200V, 0.6A, TSOP-6	TSOP-6
Q101	1	0.2V	MMBT3904-7-F	Diodes Inc.	Transistor, NPN, 40V, 0.2A, SOT-23	SOT-23
R1, R18, R101, R102, R103	5	10k	CRCW060310K0JNEA	Vishay-Dale	RES, 10k ohm, 5%, 0.1W, 0603	0603
R2	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100k ohm, 1%, 0.1W, 0603	0603
R3	1	300	CRCW0603300RJNEA	Vishay-Dale	RES, 300 ohm, 5%, 0.1W, 0603	0603
R4	1	1.00	CRCW08051R00FKEA	Vishay-Dale	RES, 1.00 ohm, 1%, 0.125W, 0805	0805
R5, R6	2	19.1	CRCW120619R1FKEA	Vishay-Dale	RES, 19.1 ohm, 1%, 0.25W, 1206	1206
R9, R107	2	2.49k	CRCW06032K49FKEA	Vishay-Dale	RES, 2.49k ohm, 1%, 0.1W, 0603	0603
R12	1	31.6k	CRCW060331K6FKEA	Vishay-Dale	RES, 31.6k ohm, 1%, 0.1W, 0603	0603
R15	1	51k	CRCW060351K0JNEA	Vishay-Dale	RES, 51k ohm, 5%, 0.1W, 0603	0603
R104	1	5.1k	CRCW06035K10JNEA	Vishay-Dale	RES, 5.1k ohm, 5%, 0.1W, 0603	0603
R105	1	51	CRCW060351R0JNEA	Vishay-Dale	RES, 51 ohm, 5%, 0.1W, 0603	0603
R106	1	191k	CRCW0603191KFKEA	Vishay-Dale	RES, 191k ohm, 1%, 0.1W, 0603	0603
TP1, TP2, TP9, TP10, TP11, TP12, TP13, TP14, TP101, TP102, TP103, TP104	12	Triple	1598-2	Keystone	Terminal, Turret, TH, Triple	Keystone1598-2
TP3, TP5, TP7	3	Red	5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP4, TP6, TP8	3	Black	5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1	1		LM5020MM-2/NOPB	Texas Instruments	100V Current Mode PWM Controller, 10-pin MSOP, Pb-Free	MUB10A
U101	1		LMV431AIMFX/NOPB	Texas Instruments	Low-Voltage (1.24V) Adjustable Precision Shunt Regulators, 3-pin SOT-23, Pb-Free	MF03A
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated