

## PMP30197 REV A Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1	1	DNP	DNP	MuRata	CAP, CERM, 3300 pF, 300 V, +/- 20%, E, D10xT7mm	D10xT7mm
C2	1	2.2uF	C3216X7R1H225K160AB	TDK	CAP, CERM, 2.2 μF, 50 V, +/- 10%, X7R, 1206	1206
C3, C6, C8, C13, C25, D4, R1, R2, R12, R15, R27		DNP	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], Diode, Zener, xxV, xxxmW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference]]	Used in PnP output and some BOM reports
C4	1	22uF	GCM31CR71A226KE02	MuRata	CAP, CERM, 22 µF, 10 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C5	1	220uF	APXE100ARA221MH70G	Chemi-Con	CAP, AL, 220 µF, 10 V, +/- 20%, 0.021 ohm, SMD	H70
C7, C16, C22, C24, R11, R24	6	TBD	Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference], RES, xxx ohm, x%, xW, [PackageReference]	Used in PnP output and some BOM reports
C9, C18	2	0.1uF	GRM21BR71H104KA01L	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0805	0805
C10	1	0.01uF	C0603C103J5RACTU	Kemet	CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0603	0603
C11	1	1uF	GRM21BR71H105KA12L	MuRata	CAP, CERM, 1 μF, 50 V, +/- 10%, X7R, 0805	0805
C12	1	22uF	GRM31CR71A226KE15L	MuRata	CAP, CERM, 22 µF, 10 V, +/- 10%, X7R, 1206	1206
C14, C26	2	2.2uF	GRM219R71C225KE15	MuRata	CAP, CERM, 2.2 µF, 16 V, +/- 10%, X7R, 0805	0805
C15, C21	2	10uF	GRM31CR71C106KAC7L	MuRata	CAP, CERM, 10 μF, 16 V, +/- 10%, X7R, 1206	1206
C17	1	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	0603
C19	1	1uF	GRM21BR71C105KA01L	MuRata	CAP, CERM, 1 μF, 16 V, +/- 10%, X7R, 0805	0805
C20	1	DNP	GRM31CR71C106KAC7L	MuRata	CAP, CERM, 10 µF, 16 V, +/- 10%, X7R, 1206	1206
C23	1	0.022uF	C0603X223K5RACTU	Kemet	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	0603
D1, D5	2	MBRA120	MBRA120T3G	ON Semiconductor	Diode, Schottky, 20 V, 1 A, SMA	SMA
D2	1	DNP	BZX84C6V8LT1G	ON Semiconductor	Diode, Zener, 6.8 V, 225 mW, SOT-23	SOT-23
D3	1	6.8V	BZX84C6V8LT1G	ON Semiconductor	Diode, Zener, 6.8 V, 225 mW, SOT-23	SOT-23
D6	1	SHORT	MBRA120T3G	ON Semiconductor	Diode, Schottky, 20 V, 1 A, SMA	SMA
D7	1	20V	MBR0520LT1G	ON Semiconductor	Diode, Schottky, 20 V, 0.5 A, SOD-123	SOD-123
D8	1		DNP	Used in BOM report	Diode, Schottky, xxV, xxA, [PackageReference]	Used in PnP output and some BOM reports
D9	1	30V	BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
Q1, Q2, Q3	3	25V	CSD16340Q3	Texas Instruments	MOSFET, N-CH, 25 V, 60 A, DQG0008A (VSON-CLIP-8)	DQG0008A
R3, R5, R6, R7, R9, R16	6	0	CRCW08050000Z0EA	Vishay-Dale	RES, 0, 5%, 0.125 W, 0805	0805
R4, R18	2	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, 0603	0603
R8, R21		10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R10	1	10.0	CRCW080510R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.125 W, 0805	0805
R13	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R14	1	866	CRCW0603866RFKEA	Vishay-Dale	RES, 866, 1%, 0.1 W, 0603	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R17, R20, R26,	4	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
R28						
R19	1	2.32k	CRCW06032K32FKEA	Vishay-Dale	RES, 2.32 k, 1%, 0.1 W, 0603	0603
R22	1	154k	CRCW0603154KFKEA	Vishay-Dale	RES, 154 k, 1%, 0.1 W, 0603	0603
R23	1	DNP	CRCW06032K49FKEA	Vishay-Dale	DNP	0603
R25	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R29	1	4.64k	CRCW06034K64FKEA	Vishay-Dale	RES, 4.64 k, 1%, 0.1 W, 0603	0603
R30	1	100k	CRCW0805100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.125 W, 0805	0805
T1	1	15uH	750316697	Wurth Elektronik	Transformer, 15 uH, TH	33x26.3mm
TP1, TP2, TP4	3		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature
						Testpoint
TP3, TP5, TP6	3		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature
						Testpoint
U1	1		LP2985AIM5-5.0	Texas Instruments	Micropower 150 mA Low-Noise Ultra Low-Dropout Regulator, 5-pin SOT-	MF05A
					23	
U2	1		LM2743MTC	Texas Instruments	Low Voltage N-Channel MOSFET Synchronous Buck Regulator Controller,	MTC14
					14-pin TSSOP	
U3	1		FOD817A	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, TH	DIP, 4-Leads, Body
						6.86x4.83mm, Pitch
						2.54mm
U4	1		LMV431AIMFX/NOPB	Texas Instruments	Low-Voltage (1.24V) Adjustable Precision Shunt Regulators, 3-pin SOT-	MF03A
					23, Pb-Free	

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ('TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products <a href="http://www.ti.com/sc/docs/stdterms.htm">http://www.ti.com/sc/docs/stdterms.htm</a>), evaluation modules, and samples (<a href="http://www.ti.com/sc/docs/sampterms.htm">http://www.ti.com/sc/docs/sampterms.htm</a>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2017, Texas Instruments Incorporated