

Filename: Pro5080.tmp
 Variant: UCC28700
 Generated: 7/13/2017 11:51:52 AM
 TID #: N/A



PMP20869 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C2	2	1000uF	16ZLJ560M8X16	Rubycon	1000µF 16V Aluminum Capacitors Radial, Can 5000 Hrs @ 105°C	6.3x5.5mm
2	C3, C11	2	22uF	GRT31CR61E226KE01L	MuRata	22µF ±20% 25V Ceramic Capacitor X5R 1206 (3216 Metric)	1206
3	C4, C9	2	18uF	UVR2E100MPD	Rubycon	18µF 250V Aluminum Capacitors Radial, Can 5000 Hrs @ 125°C	10x17.5
4	C8	1	2200pF	DE1E3KX222MA5BA01	MuRata	CAP, CERM, 2200 pF, 250 V, +/- 20%, E, Disc 10x8mm	Disc 10x8mm
5	C10	1	4.7uF	GRM319R61H475KA12	MuRata	4.7µF 50V Aluminum Capacitors Radial, Can 2000 Hrs @ 85°C	1206
6	D1	1	100V	SS110-TP	Micro Commercial Components	Diode, Schottky, 100 V, 1 A, SMA	SMA
7	D2	1	7.5V	1SMA5922BT3G	ON Semiconductor	Diode, Zener, 7.5 V, 1.5 W, AEC-Q101, SMA	SMA
8	D3, D7	2	600V	1N4006-T	Diodes Inc.	Diode, Standard Recovery Rectifier, 600 V, 1 A, TH	DO-41
9	D4	1	160V	SMCJ160A-TP	Micro Commercial Components	Diode, TVS, Uni, 160 V, 259 Vc, SMC	SMC
10	D6	1	1.7V	US1M-13-F	Diodes Inc.	Diode, Ultrafast, 1000V, 1A, SMA	SMA
11	D8	1		BAS20HT1G		DIODE SWITCH 200V 200MA SOD323	SOD-323
12	F1	1		37202500001	Littelfuse	Fuse, 0.25 A, 250 V, TH	TR5 fuse 8.5mm DIA
13	J1	1		923345-03-C	3M	Jumper Wire, 300mil spacing, Orange, pkg of 200	300 mil Jumper Wire
14	J2, J3	2		923345-04-C	3M	Jumper Wire, 400 mil Spacing, Yellow, Pkg of 200	Jumper Wire, 400 mil Spacing, Yellow, Pkg of 200
15	L1	1	10mH	744862100	Würth Elektronik	COMMON MODE CHOKE 450MA 2 LN T/H	17x12.32x15.32 mm
16	Q1	1	800V	STP10NK80Z	STMicroelectronics	N-Channel 800V 9A (Tc) 190W (Tc) Through Hole TO-220AB	TO-220AB
17	R1	1	2.05k	CRCW08052K05FKEA	Vishay-Dale	RES, 2.05 k, 1%, 0.125 W, 0805	0805
18	R2, R3, R5, R7	4	4.7Meg	CRCW12064M70JNEA	Vishay-Dale	RES, 4.7Meg ohm, 5%, 0.25W, 1206	1206
19	R6	1	150	CRCW1206150RFKEA	Vishay-Dale	RES, 150, 1%, 0.25 W, 1206	1206
20	R8	1	1.50Meg	1-1614959-1	Tyco Electronics	RES, 1.50 M, 0.1%, 0.1 W, 0805	0805
21	R9	1	20.0	CRCW080520R0FKEA	Vishay-Dale	RES, 20.0, 1%, 0.125 W, 0805	0805
22	R10, R12	2	1.5Meg	CRCW12061M50JNEA	Vishay-Dale	RES, 1.5 M, 5%, 0.25 W, 1206	1206
23	R11	1	137k	CRCW0603137KFKEA	Vishay-Dale	RES, 137 k, 1%, 0.1 W, 0603	0603
24	R13	1	3.0k	CRCW06033K00JNEA	Vishay-Dale	RES, 3.0 k, 5%, 0.1 W, 0603	0603
25	R14	1	42.2k	CRCW060342K2FKEA	Vishay-Dale	RES, 42.2 k, 1%, 0.1 W, 0603	0603
26	R15	1	0.82	ERJ-6RQFR82V	Panasonic	RES, 0.82, 1%, 0.125 W, 0805	0805
27	T1	1		RLTI-1195	Renco	Flyback Transformer, 700uH	
28	TP1, TP3	2	Red	5000	Keystone	Test Point, TH, Miniature, Red	Keystone5000
29	TP2, TP5	2	Black	5001	Keystone	Test Point, TH, Miniature, Black	Keystone5001
30	TP4	1		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
31	TP6	1		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
32	UCC28700	1		UCC28700DBVR	Texas Instruments	Constant-Voltage, Constant-Current PWM With Primary-Side Regulation, DBV0006A (SOT-6)	DBV0006A
33	C5	0	470uF	RS80J471MDNASQJT	Nichicon	CAP ALUM POLY 470UF 20% 6.3V T/H	5x7 mm
34	C6	0	4.7uF	CGB3B1X5R1A475K055AC	TDK	CAP, CERM, 4.7 µF, 10 V, +/- 10%, X5R, 0603	0603
35	C7	0	22uF	CL10A226MP8NUNE	Samsung	CAP, CERM, 22 µF, 10 V, +/- 20%, X5R, 0603	0603
36	D5	0	100V	SS1H10-E3/61T	Vishay-Semiconductor	Diode, Schottky, 100V, 1A, SMA	SMA
37	R4	0	511	CRCW0603511RFKEA	Vishay-Dale	RES, 511, 1%, 0.1 W, 0603	0603

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated