

Designator	Quantity	Value	Description	PackageReference	PartNumber	Manufacturer	Alternate PartNumber	Alternate Manufacturer
IPCB1	1		Printed Circuit Board		PMP21384	Any	-	-
C1	1	10uF	CAP ALUM 10UF 16V 20% RADIAL	5x7mm	EAA-GA1C100B	Panasonic		
C2	1	22pF	CAP_CERM, 22pF, 50V, +/-5%, C0G/NP0, 0603	0603	06035A220JAT2A	AVX		
C3	1	150uF	CAP ALUM 150UF 25V 20% RADIAL		EEU-FR1E151B	Panasonic Electronic Compon		
C4	1	10uF	CAP ALUM 10UF 400V 20% RADIAL	10x12.5mm	EKMG401ELL100MJ20S	United Chemi-Con		
C5	1	2.2uF	CAP ALUM 2.2UF 400V 20% RADIAL	8x11	400LLE2R2MEFC8X9	Rubycon		
C6	1	0.1uF	CAP_CERM, 0.1uF, 16V, +/-5%, X7R, 0603	0603	0603YC104JAT2A	AVX		
D1	1	100V	Diode, Ultrafast, 100V, 0.15A, SOD-123	SOD-123	1N4148W-7-F	Diodes Inc.		
D2	1	600V	DIODE FAST REC 600V 1A DO214AC	SMA	ES1J-TP	Diodes Inc.		
D3	1	1000V	Diode, P-N, 1000V, 1A, TH	DO-41	1N4007	Fairchild Semiconductor		
D4	1	600V	Diode, Ultrafast, 600V, 1A, SMB	SMB	MURS160-13-F	Diodes Inc.		
L1	1	1mH	Inductor, Unshielded Drum Core, Ferrite, 1mH, 0.25A, 4.38 ohm, TH	D6 x 8.5mm	7447462102	Würth Elektronik eiSos		
L2	1	470uH	Inductor, Unshielded Drum Core, Ferrite, 470uH, , TH	D6 x 8.5mm	744772471	Würth Elektronik eiSos		
L4	1	10000uH	Coupled inductor, 10000uH, 0.25A, 3.5 ohm, TH	Coupled inductor, 17.5x17x11mm	UU9.8V-103LF	GCI Technologies		
L, TP1	2	Red	Test Point, Miniature, Red, TH	Red Miniature Testpoint	5000	Keystone		
N, TP2	2	Black	Test Point, TH, Miniature, Black	Keystone5001	5001	Keystone	Equivalent	Any
R1	1	24.3k	RES, 24.3 k, 1%, 0.1 W, 0603	0603	CRCW060324K3FKEA	Vishay-Dale		
R2	1	100k	RES, 100k ohm, 5%, 0.25W, 1206	1206	CRCW1206100KJNEA	Vishay-Dale		
R4	1	12.4k	RES, 12.4 k, 1%, 0.1 W, 0603	0603	CRCW060312K4FKEA	Vishay-Dale		
R5	1	5.1k	RES, 5.1k ohm, 5%, 0.25W, 1206	1206	CRCW12065K10JNEA	Vishay-Dale		
RF1	1	4.7	RES, 4.7 ohm, 5%, 1W, Fusible, TH	Axial resistor	FKN1WSJR-52-4R7	Yageo America		
RT1	1	10 ohm	Thermistor NTC, 10 ohm, 20%, Disc 11.5mmx6mm	Disc 11.5mmx6mm	B57236S0100M000	EPCOS Inc		
RV1	1		Varistor 275V RMS 10MM Radial, TH	10mm Radial	S10K275E2	EPCOS Inc		
U1	1		LOW STAND-BY POWER, CV / CC PWM HV SWITCHER WITH PRIMARY SIDE REGULATION, D0007A	D0007A	UCC28910D	Texas Instruments		None
R3	0	2.00k	RES, 2.00k ohm, 1%, 0.1W, 0603	0603	CRCW06032K00FKEA	Vishay-Dale		

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated