

Filename: #VALUE!
 Variant: 001
 Generated 4/8/2024 15:46 PM
 TID #: TIDA-010042



**TEXAS
 INSTRUMENTS**
 TIDA-010042 REV E3 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	Package Referen
1	C12	1	0.1uF		MuRata	CAP, CERM, 0.1	0402
2	C13, C64	2	100µF	ESY476M100AH1A	Kemet	100 µF 100 V Alu	RADIAL
3	C18, C19	2	2.2uF	GRM188C71C225K	Murata	2.2µF ±10% 16V	0603
4	C20	1	100pF	GRT1555C1E101JA	Murata	Multi-Layer Cera	0402
5	C21, C22, C38	8	0.1uF		Taiyo Yuden	CAP CER 0.1UF 2	0603
6	C23, C24	2	2.2µF	12061C225KAT2A	AVX	2.2uF @ ±10% 1	1206
7	C25, C29	2		GRM188R72A104	Murata	0.1µF ±10% 100	0603
8	C26, C31	2	1uF		Yageo	CAP CER 1UF 16	0603
9	C27, C32, C35	3	10uF		MuRata	CAP, CERM, 10 u	1206
10	C28	1		CL21B106KOQNN	Samsung El	Cap Ceramic 10u	0805
11	C30	1	1uF		Samsung El	CAP, CERM, 1 µF	0603
12	C33, C34, C36	3	0.1uF		MuRata	CAP, CERM, 0.1	0603
13	C37	1	1uF		AVX	CAP, CERM, 1 uF	0603
14	C39, C44, C48	3	0.1uF		MuRata	CAP, CERM, 0.1	0402
15	C40	1	4.7nF	GRM188R71H472	Murata	Multilayer Cera	0603
16	C49, C50	2	1nF	CC0603KRX7R7BB	YAGEO	1000 pF ±10% 16	0603
17	C52	1	1µF	GRT155R61E105K	Murata	Multi-Layer Cera	0402
18	C53, C54	2	1000pF		Kemet	CAP, CERM, 100	0402
19	D1	1	15V		Diodes Inc.	Diode, Zener, 15	SOD-123
20	D2	1	3.6V		ON Semico	Diode, Zener, 3.6	SOD-123
21	D3, D4	2	Green		Lite-On	LED, Green, SMD	1.6x0.8x0
22	D5, D6	2	Red		Lite-On	LED, Red, SMD	Red LED, :
23	H1, H2, H3, H4	4			B&F Fasten	Machine Screw,	Screw
24	J1, J2, J3	3			On-Shore T	Terminal Block, C	On-Shore
25	J4	1			Samtec	Header(Shroude	Header(St
26	J5	1			Würth Elek	Header(Shroude	Header, 2
27	L1	1	10uH		Würth Elek	Inductor, Shielde	28.5x19.5
28	LBL1	1			Brady	Thermal Transfe	PCB Label
29	Q1, Q2, Q3	3	60V		Texas Instru	MOSFET, N-CH, C	DNK0008,
30	Q4	1	40 V		Micro Com	TRANS NPN 40V	SOT-23
31	R1, R4, R5	3	1m	ULRG32512R001F	TT Electron	Res Metal Strip	2512
32	R2	1	2.2		Vishay-Dale	RES, 2.2, 5%, 0.0	0402
33	R3	1	10.0k		Susumu Co	RES, 10.0 k, 0.1%	0603
34	R6	1	0	RCG04020000Z0E	Vishay Dale	Res Thick Film 04	0402
35	R8, R11	2	5.11		Vishay-Dale	RES, 5.11, 1%, 0.	1206
36	R9, R10	2	20.0		Yageo	RES, 20.0, 1%, 0.	0603
37	R12	1	768k		Yageo	RES, 768 k, 1%, 0	0603
38	R13	1	100k		Yageo	RES, 100 k, 1%, 0	0603
39	R14	1	100k		Yageo Ame	RES, 100 k, 1%, 0	0402
40	R15	1	5.1		Vishay-Dale	RES, 5.1, 5%, 0.1	0603
41	R16	1	47k		Yageo	RES, 47 k, 5%, 0.	0603
42	R17, R19, R20	4	3.3k		Vishay-Dale	RES, 3.3 k, 5%, 0	0603
43	R18	1	100k		Yageo Ame	RES, 100 k, 0.1%	0603

Variant: 001



44	R25, R35, R40	3	100		Yageo	RES, 100, 1%, 0.1	0603
45	R26, R27	2	1.00k		Yageo	RES, 1.00 k, 1%,	0603
46	R28, R33	2	1.0k		Yageo	RES, 1.0 k, 5%, 0	0603
47	R32	1	0		Yageo	RES, 0, 5%, 0.1 V	0603
48	R34, R36	2	22.0		Yageo	RES, 22.0, 1%, 0.	0603
49	R37	1	10.0k		Panasonic	RES, 10.0 k, 1%,	0603
50	R38	1	2.05k		Yageo	RES, 2.05 k, 1%,	0603
51	R39	1	1.0		Vishay-Dale	RES, 1.0, 5%, 0.1	0603
52	R41, R42	2	10.0k		Stackpole E	RES, 10.0 k, 1%,	0603
53	R43, R44, R49	4	3.30k		Vishay-Dale	RES, 3.30 k, 1%,	0603
54	R45, R46, R47	4	80.6k		Yageo	RES, 80.6 k, 1%,	0603
55	R100, R101	2	10.5k		Yageo Ame	RES, 10.5 k, 1%,	0402
56	U1, U2	2			Texas Instru	33-V Precision S	DRV0006/
57	U3	1		LMG2100R026	Texas Instru	100-V, 53-A GaN	VQFN-FCF
58	U4, U5	2			Texas Instru	4A/4A Single Cha	DBV0005/
59	U6	1		TPSM365R6V5RDM	Texas Instru	3-V to 65-V Inpu	VQFN-HR9
60	U7	1		TPS7A2033PDBVR	Texas Instru	300-mA, Ultra-Lc	SOT23-5
61	U8	1		MSPM0G1507SRG	Texas Instru	Mixed-Signal Mi	VQFN48
62	U9, U11, U13	3		INA241A4IDDF	Texas Instru	-4-V to 110-V, Bi	SOT-23-8
63	U12	1			Texas Instru	Factory Program	DRL0006/

rounded), 1.27mm, 5x2, SMT

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated