


1 Board Photo

The image below shows PMP20815 Rev B. This is a low line input (90VAC to 130VAC) Opto/DCM Flyback that produces a 72W output (24V@3A)






Page 1 of 9 Power Design Services



2 Efficiency

2.1 115VAC/60Hz (24V)



115VAC/60Hz


lout	Vout	Vin	lin	PF	Pin	Pout	Efficiency
0.000	24.09	115.2			0.30	0.00	0%
0.100	24.08	115.2	0.087	0.305	3.05	2.41	79%
0.300	24.08	115.2	0.209	0.340	8.20	7.22	88%
0.600	24.08	115.2	0.358	0.390	16.09	14.45	90%
0.900	24.08	115.2	0.487	0.427	23.98	21.67	90%
1.200	24.08	115.2	0.609	0.454	31.87	28.90	91%
1.500	24.08	115.2	0.725	0.476	39.77	36.12	91%
1.800	24.08	115.2	0.842	0.491	47.58	43.34	91%
2.100	24.08	115.2	0.951	0.507	55.53	50.57	91%
2.400	24.08	115.2	1.060	0.521	63.51	57.79	91%
2.700	24.08	115.2	1.167	0.533	71.49	65.02	91%
3.000	24.08	115.2	1.273	0.543	79.53	72.24	91%

Page 2 of 9 Power Design Services

PMP20815B Test Results



3 Startup



Page 3 of 9 Power Design Services


PMP20815B Test Results



4 Output Ripple Voltage

The following image shows the output ripple at full load.

4.1 Output Ripple (3A Load)




Page 4 of 9 Power Design Services

PMP20815B Test Results



5 Load Transients

5.1 0-3A Step




Page 5 of 9 Power Design Services



6 Switch Node Waveforms


6.1 Drain of FET Q1



Page 6 of 9 Power Design Services



6.2 Anode of Diode D4




Page 7 of 9 Power Design Services




7 Thermal Images

These thermal images were taken after a 5 minute soak when fully loaded to 3A, and then when pulsed between 0 and 3A at a 50% duty cycle

7.1 120VAC/60Hz - Continuous Full Load







Page 8 of 9 Power Design Services



7.2 120VAC/60Hz - Pulsed Load





Page 9 of 9 Power Design Services

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated