

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LP2992AILD-1.5/NO.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L011A
LP2992AILD-1.5/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L011A
LP2992AILD-1.8/NO.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L012A
LP2992AILD-1.8/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L012A
LP2992AILD-3.3/NO.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L014A
LP2992AILD-3.3/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L014A
LP2992AILD-5.0/NO.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A
LP2992AILD-5.0/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L015A
LP2992AILDX-3.3/NO.A	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L014A
LP2992AILDX-3.3/NOPB	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L014A
LP2992AILDX-5.0/NO.A	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A
LP2992AILDX-5.0/NOPB	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L015A
LP2992AIM5-1.5/NO.A	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBA
LP2992AIM5-1.5/NOPB	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBA
LP2992AIM5-1.8/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCA
LP2992AIM5-1.8/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCA
LP2992AIM5-2.5/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDA
LP2992AIM5-2.5/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDA
LP2992AIM5-3.3/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LFEA
LP2992AIM5-3.3/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	LFEA
LP2992AIM5-5.0/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFFA
LP2992AIM5-5.0/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFFA
LP2992AIM5X-1.5/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBA
LP2992AIM5X-1.5/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBA
LP2992AIM5X-1.8/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCA
LP2992AIM5X-1.8/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCA
LP2992AIM5X-2.5/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDA
LP2992AIM5X-2.5/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDA
LP2992AIM5X-3.3/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LFEA

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LP2992AIM5X-3.3/NO.B	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	
LP2992AIM5X-3.3/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	LFEA
LP2992AIM5X-5.0/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFFA
LP2992AIM5X-5.0/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFFA
LP2992ILD-1.8/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L012A B
LP2992ILD-1.8/NOPB.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L012A B
LP2992ILD-1.8/NOPB.B	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L012A B
LP2992ILD-2.5/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L013A B
LP2992ILD-2.5/NOPB.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L013A B
LP2992ILD-2.5/NOPB.B	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L013A B
LP2992ILD-3.3/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L014A B
LP2992ILD-3.3/NOPB.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L014A B
LP2992ILD-3.3/NOPB.B	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L014A B
LP2992ILD-5.0/NOPB	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L015A B
LP2992ILD-5.0/NOPB.A	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A B
LP2992ILD-5.0/NOPB.B	Active	Production	WSON (NGD) 6	1000 SMALL T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A B
LP2992ILD-1.5/NO.A	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L011A B
LP2992ILD-1.5/NOPB	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L011A B
LP2992ILD-3.3/NO.A	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L014A B

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LP2992ILDY-3.3/NOPB	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	NIPDAU SN	Level-3-260C-168 HR	-40 to 125	L014A B
LP2992ILDY-5.0/NO.A	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A B
LP2992ILDY-5.0/NOPB	Active	Production	WSON (NGD) 6	4500 LARGE T&R	Yes	SN	Level-3-260C-168 HR	-40 to 125	L015A B
LP2992IM5-1.5/NOPB	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBB
LP2992IM5-1.5/NOPB.A	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBB
LP2992IM5-1.5/NOPB.B	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBB
LP2992IM5-1.8/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCE
LP2992IM5-1.8/NOPB.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCE
LP2992IM5-2.5/NOPB	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDB
LP2992IM5-2.5/NOPB.A	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDB
LP2992IM5-2.5/NOPB.B	Active	Production	SOT-23 (DBV) 5	1000 SMALL T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDB
LP2992IM5-3.0/NOPB	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LF8B
LP2992IM5-3.0/NOPB.A	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LF8B
LP2992IM5-3.0/NOPB.B	Active	Production	SOT-23 (DBV) 5	1000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LF8B
LP2992IM5-3.3/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5-3.3/NOPB.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5-5.0/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5-5.0/NOPB.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5X-1.5/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBB
LP2992IM5X-1.5/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFBB
LP2992IM5X-1.8/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCE
LP2992IM5X-1.8/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFCE
LP2992IM5X-2.5/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDB
LP2992IM5X-2.5/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFDB
LP2992IM5X-3.3/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5X-3.3/NO.B	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	-	Call TI	Call TI	-40 to 125	
LP2992IM5X-3.3/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	NIPDAU SN	Level-1-260C-UNLIM	-40 to 125	LFEB
LP2992IM5X-5.0/NO.A	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFEB

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
LP2992IM5X-5.0/NOPB	Active	Production	SOT-23 (DBV) 5	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	LFFB

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.