

TAPE AND REEL INFORMATION




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMCS1127A1AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127A2AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127A3AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127A4AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127A5AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127A6AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B1AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B2AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B3AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B4AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B5AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127B7AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127C1AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127C2AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127C3AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
TMCS1127C4AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TMCS1127C5AQDVGR	SOIC	DVG	10	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TMCS1127A1AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127A2AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127A3AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127A4AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127A5AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127A6AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B1AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B2AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B3AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B4AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B5AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127B7AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127C1AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127C2AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127C3AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127C4AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0
TMCS1127C5AQDVGR	SOIC	DVG	10	2000	350.0	350.0	43.0