

Test Report for 100Base-TX

Time: 11:49:17

Device ID : Not Available



Device Description : DK-TM4C129X

Port ID : Chan-A



Test	Spec. Range	Measured Value	Result
AOI Template	Fit the template		Pass
Output Voltage (+Vout)	950mV to 1050mV	999.7mV	Pass
Output Voltage (-Vout)	-950mV to -1050mV	-996.4mV	Pass
Amplitude Symmetry	0.98 to 1.02	1.003	Pass
Rise Time(+ve)	3ns to 5ns	4.39ns	Pass
Rise Time(-ve)	3ns to 5ns	4.37ns	Pass
Fall Time(+ve)	3ns to 5ns	4.21ns	Pass
Fall Time(-ve)	3ns to 5ns	4.28ns	Pass
Rise/Fall Symmetry(+ve)	<500ps	174ps	Pass
Rise/Fall Symmetry(-ve)	<500ps	85.7ps	Pass
Overshoot(+ve)	<5%	2.25%	Pass
Overshoot(-ve)	<5%	2.04%	Pass
Transmit Jitter(+ve)	<1.4ns	360ps	Pass
Transmit Jitter(-ve)	<1.4ns	430ps	Pass
Distortion (Duty Cycle)	<500ps(±250ps)	340ps	Pass
Transmitter Return Loss			Not Available
Receiver Return Loss			Not Available

Application Version : 3.2.6 Build 7

ANSI X3.263-1995: Annex J AOI Template



ANSI X.3.263-1995 : 9.1.2.2 Differential Output Voltage




Positive Amplitude(+Vout) : 999.7mV	Negative Amplitude(-Vout) : -996.4mV
Baseline(+ve) : -43.0mV	Baseline(-ve) : -49.8mV
Spec Range : 950mV to 1050mV	Spec Range : -950mV to -1050mV
Output Voltage(+Vout) Result : Pass	Output Voltage(-Vout) Result : Pass

Differential Output Voltage Result : Pass


NOTE: Amplitude values are corrected for Baseline

ANSI X3.263-1995: 9.1.4 Signal Amplitude Symmetry



Amplitude Symmetry :	1.003
Spec Range: 0.98 to 1.02	
Amplitude Symmetry Result :	Pass



ANSI X3.263-1995: 9.1.6 Rise Time



Rise Time(+ve) :	4.39ns	Rise Time(-ve) :	4.37ns
Spec Range: 3ns to 5ns		Spec Range: 3ns to 5ns	
Rise Time(+ve) Result :	Pass	Rise Time(-ve) Result :	Pass

Rise Time Test Result : Pass



ANSI X3.263-1995: 9.1.6 Fall Time



Fall Time(+ve) :	4.21ns	Fall Time(-ve) :	4.28ns
Spec Range: 3ns to 5ns		Spec Range: 3ns to 5ns	
Fall Time(+ve) Result :	Pass	Fall Time(-ve) Result :	Pass

Fall Time Test Result : Pass

ANSI X3.263-1995: 9.1.6 Rise Fall Symmetry





Rise/Fall Symmetry(+ve) :	174ps	Rise/Fall Symmetry(-ve) :	85.7ps
Spec Range: <500ps		Spec Range: <500ps	
Rise/Fall Symmetry(+ve) Result :	Pass	Rise/Fall Symmetry(-ve) Result :	Pass

Rise/Fall Symmetry(Max-Min) : 174ps

Rise/Fall Symmetry Result : Pass



ANSI X3.263-1995: 9.1.3 Waveform Overshoot



Overshoot(+ve) :	2.25%	Overshoot(-ve) :	2.04%
Spec Range: <5%		Spec Range: <5%	
Overshoot(+ve) Result :	Pass	Overshoot(-ve) Result :	Pass


Waveform Overshoot Test Results : Pass

ANSI X3.263-1995: 9.1.9 Transmit Jitter



Transmit Jitter(+ve) :	360ps	Transmit Jitter(-ve) :	430ps
Spec Range: <1.4ns		Spec Range: <1.4ns	
Transmit Jitter(+ve) Result :	Pass	Transmit Jitter(-ve) Result :	Pass

ANSI X3.263-1995: 9.1.8 Distortion(Duty Cycle)



Distortion(Duty Cycle) :	340ps
Spec Range: <500ps(+/-250ps)	
Distortion(Duty Cycle) Result :	
Pass	
T1 = 250ps	T2 = 100ps
T3 = 240ps	T4 = 150ps
T5 = 340ps	T6 = 90.0ps

Test Report for 100Base-TX

Time: 12:00:22

Device ID : Not Available



Device Description : DK-TM4C129X

Port ID : Chan-B

Test	Spec. Range	Measured Value	Result
AOI Template	Fit the template		Pass
Output Voltage (+Vout)	950mV to 1050mV	997.6mV	Pass
Output Voltage (-Vout)	-950mV to -1050mV	-996.0mV	Pass
Amplitude Symmetry	0.98 to 1.02	1.002	Pass
Rise Time(+ve)	3ns to 5ns	3.52ns	Pass
Rise Time(-ve)	3ns to 5ns	3.46ns	Pass
Fall Time(+ve)	3ns to 5ns	3.37ns	Pass
Fall Time(-ve)	3ns to 5ns	3.3ns	Pass
Rise/Fall Symmetry(+ve)	<500ps	157ps	Pass
Rise/Fall Symmetry(-ve)	<500ps	157ps	Pass
Overshoot(+ve)	<5%	2.27%	Pass
Overshoot(-ve)	<5%	2.72%	Pass
Transmit Jitter(+ve)	<1.4ns	1.01ns	Pass
Transmit Jitter(-ve)	<1.4ns	910ps	Pass
Distortion (Duty Cycle)	<500ps(\pm 250ps)	467ps	Pass
Transmitter Return Loss			Not Available
Receiver Return Loss			Not Available



Application Version : 3.2.6 Build 7

ANSI X3.263-1995: Annex J AOI Template



AOI Template Result :			
Pass			
Hits per Segment			
Seg1	0	Seg2	0
Seg3	0	Seg4	10
Seg5	0	Seg6	0
Seg7	0	Seg8	0
Seg9	0	Seg10	0

ANSI X.3.263-1995 : 9.1.2.2 Differential Output Voltage




Positive Amplitude(+Vout) : 997.6mV	Negative Amplitude(-Vout) : -996.0mV
Baseline(+ve) : -43.8mV	Baseline(-ve) : -49.1mV
Spec Range : 950mV to 1050mV	Spec Range : -950mV to -1050mV
Output Voltage(+Vout) Result : Pass	Output Voltage(-Vout) Result : Pass

Differential Output Voltage Result : Pass


NOTE: Amplitude values are corrected for Baseline

ANSI X3.263-1995: 9.1.4 Signal Amplitude Symmetry



Amplitude Symmetry :	1.002
Spec Range:	0.98 to 1.02
Amplitude Symmetry Result :	Pass



ANSI X3.263-1995: 9.1.6 Rise Time



Rise Time(+ve) :	3.52ns	Rise Time(-ve) :	3.46ns
Spec Range:	3ns to 5ns	Spec Range:	3ns to 5ns
Rise Time(+ve) Result :	Pass	Rise Time(-ve) Result :	Pass

Rise Time Test Result : Pass



ANSI X3.263-1995: 9.1.6 Fall Time



Fall Time(+ve) :	3.37ns	Fall Time(-ve) :	3.3ns
Spec Range: 3ns to 5ns		Spec Range: 3ns to 5ns	
Fall Time(+ve) Result :	Pass	Fall Time(-ve) Result :	Pass

Fall Time Test Result : Pass

ANSI X3.263-1995: 9.1.6 Rise Fall Symmetry





Rise/Fall Symmetry(+ve) :	157ps	Rise/Fall Symmetry(-ve) :	157ps
Spec Range: <500ps		Spec Range: <500ps	
Rise/Fall Symmetry(+ve) Result :	Pass	Rise/Fall Symmetry(-ve) Result :	Pass

Rise/Fall Symmetry(Max-Min) : 223ps

Rise/Fall Symmetry Result : Pass



ANSI X3.263-1995: 9.1.3 Waveform Overshoot



Overshoot(+ve) :	2.27%	Overshoot(-ve) :	2.72%
Spec Range: <5%		Spec Range: <5%	
Overshoot(+ve) Result :	Pass	Overshoot(-ve) Result :	Pass


Waveform Overshoot Test Results : Pass

ANSI X3.263-1995: 9.1.9 Transmit Jitter



Transmit Jitter(+ve) :	1.01 ns	Transmit Jitter(-ve) :	910 ps
Spec Range: <1.4ns		Spec Range: <1.4ns	
Transmit Jitter(+ve) Result :	Pass	Transmit Jitter(-ve) Result :	Pass

ANSI X3.263-1995: 9.1.8 Distortion(Duty Cycle)



Distortion(Duty Cycle) :	467ps
Spec Range: <500ps(+/-250ps)	
Distortion(Duty Cycle) Result :	
Pass	
T1 = 367ps	T2 = 7.98zs
T3 = 467ps	T4 = 367ps
T5 = 467ps	T6 = 100ps

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.