

TPS65313-Q1 Technical Reference Manual

This document provides the factory programmed EEPROM configuration settings and device ID register values (DEV_ID) for the orderable part number, 031310QRWGRQ1.

1 Introduction

This technical reference manual can be used as a reference for the TPS65313-Q1 default factory programmed EEPROM configuration settings for the given orderable part number. This technical reference manual does not provide information about the electrical characteristics, external components, package, or the functionality of the device. For this information and the full register map, refer to the [TPS65313-Q1 Wide-VIN Power-Management IC for Automotive Applications Data Sheet](#).

Table 1 lists the register bits loaded from the EEPROM during device start-up.

Table 1. Main EEPROM Settings for TPS65313-Q1

Orderable Part Number	DEV_ID Register Value	BUCK1 Output Voltage Setting (BUCK1_CFG)	BUCK2 Output Voltage Setting (BUCK2_CFG)	Switching Regulator Clock and Modulation Source (SMPS_CLK_SRC)	External VMON1 Configuration at Power-Up (EXT_VMON1_CFG)	External VMON2 Configuration at Power-Up (EXT_VMON2_CFG)	NRES Extension Delay Configuration (NRES_EXT_DELAY)
031310QRWGRQ1	0x10	3.3 V	1.2 V	Internal	No	No	Short

Figure 1 shows the typical power supply connections used with 031310QRWGRQ1 device for TI's single chip mmWave radar application.




Figure 1. TPS65313-Q1 Power Supply Block Diagram for AWR16xx and AWR18xx Application

⁽¹⁾ All trademarks are the property of their respective owners.

2 Register Bits Loaded From EEPROM

The register bit values loaded from the EEPROM during device start-up.

Table 2. Summary of Register Bits

SPI COMMAND	REGISTER NAME	BIT	VALUE
RD_DEV_ID	DEV_ID	BIT [7] : SMPS_CLK_SRC	0b
RD_DEV_ID	DEV_ID	BIT[6] : EXT_VMON1_CFG	0b
RD_DEV_ID	DEV_ID	BIT [5] : EXT_VMON2_CFG	0b
RD_DEV_ID	DEV_ID	BIT [4] : NRES_EXT_DELAY	1b
RD_DEV_ID	DEV_ID	BIT [2:1] : BUCK2_CFG	00b
RD_DEV_ID	DEV_ID	BIT [0] : BUCK1_CFG	0b

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025