Variant: 001

Generated: 9/8/2022 3:10 PM TID #: TIDA-060042



## TIDA-060042 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	!PCB	1		TIDA-060042	Any	Printed Circuit Board	
2	1, 1V21, 2, 3, 4, 5, 5V, 6, 7, 8	10		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
3	5V_in	1		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
4	ADCin1, ADCin1_woBuff, ADCin2, ADCin2_woBuff	4		SSQ-103-01-T-S	Samtec	3 Position Receptacle Connector 0.100" (2.54mm) Through Hole Tin	HDR3
5	byPassRTD1, byPassRTD2, byPassRTD3, byPassRTD5, byPassRTD6, byPassRTD7, byPassRTD7, byPassRTD9, byPassRTD9, byPassRTD10, J1, J7, J11, J16, J17, Vref, Vref buff	17		SL 11 112 02G	Fischer Elektronik	Header, 2.54mm, 2x1, Gold, TH	TH, 2-Leads, Body 2.5x5.08mm, Pitch 2.54mm
6	C1	1	0.1uF	C3216NP01H104J160AA	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 5%, C0G/NP0, 1206_190	1206_190
7	C2	1	10uF	TMK316AB7106KLHT	Taiyo Yuden	CAP, CERM, 10 µF, 25 V,+/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
8	C3	1	22uF	GRM21BZ71A226ME15L	MuRata	CAP, CERM, 22 uF, 10 V, +/- 20%, X7R, 0805	0805
9	C4, C6	2	0.1uF	08053C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0805	0805
10	C5	1	47uF	EMVY160ADA470MF55G	Chemi-Con	CAP, AL, 47 uF, 16 V, +/- 20%, 1 ohm, SMD	F55
11	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
12	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
13	J2, J3, J4, J5, J6, J8, J9, J10, J12, J13, J14, J15, Rref, Rset	14		SSQ-102-03-G-S	Samtec	Receptacle, 2.54mm, 2x1, Gold, TH	Receptacle, 2.54mm, 2x1, TH
14	J18, J19, J24	3		D3082-05	Harwin	1mm Uninsulated Shorting Plug, 10.16mm spacing, TH	Shorting Plug, 10.16mm spacing, TH
15	R1, R5, R6, R7, R8	5	0	RC0805JR-070RL	Yageo America	RES, 0, 5%, 0.125 W, 0805	0805
16	R3	1	20.0k	RT0805BRD0720KL	Yageo America	RES, 20.0 k, 0.1%, 0.125 W, 0805	0805
17	R4	1	32.0k	RT0805BRD0732KL	Yageo America	RES, 32.0 k, 0.1%, 0.125 W, 0805	0805
18	U1	1		TPS7A4533DCQT	Texas Instruments	Single Output Fast Transient Response LDO, 1.5 A, Fixed 3.3 V Output 2.1 to 20 V Input, 6-pin SOT-223 (DCQ), -40 to 125 degC, Green (RoHS & no Sb/Br)	, DCQ0006A
19	U2, U3	2			Texas Instruments	Precision, CMOS Input, RRIO, Wide Supply Range Amplifiers, 14-pin Narrow SOIC, Pb-Free	
20	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
21	R2	0	0	RC0805JR-070RL	Yageo America	RES, 0, 5%, 0.125 W, 0805	0805

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated