

## TIDA-01371 REV E2 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB	1		TIDA-01371	Any	Printed Circuit Board	
C1, C31, C32	3	10uF	GRM21BR61E106MA73	MuRata	CAP, CERM, 10 µF, 25 V, +/- 20%, X5R, 0805	0805
C2, C11, C12, C13, C22	5	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
C3	1	1000pF	GRM21AR72E102KW01D	MuRata	CAP, CERM, 1000 pF, 250 V, +/- 10%, X7R, 0805	0805
C4, C5, C6, C19, C20, C21	6	330uF	EEUED2D331	Panasonic	CAP, AL, 330 µF, 200 V, +/- 20%, 0.07385 ohm, TH	18x40
C7	1	1uF	GRM55DR72E105KW01L	MuRata	CAP, CERM, 1 µF, 250 V, +/- 10%, X7R, 2220	2220
C8, C14, C15	3	10uF	C3216X5R1H106K160AB	TDK	CAP, CERM, 10 µF, 50 V, +/- 10%, X5R, 1206	1206
C9, C17	2	0.01uF	GRM188R71H103KA01D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0603	0603
C10	1	1uF	C2012X7S2A105K125AB	TDK	CAP, CERM, 1 µF, 100 V, +/- 10%, X7S, 0805	0805
C18	1	330pF	GRM188R72E331KW07D	MuRata	CAP, CERM, 330 pF, 250 V, +/- 10%, X7R, 0603	0603
C24	1	4.7uF	400AX4.7MTA8X9	Rubycon	CAP, AL, 4.7 µF, 400 V, +/- 20%, TH	D8xL9mm
C25, C27	2	0.01uF	06031C103JAT2A	AVX	CAP, CERM, 0.01 µF, 100 V, +/- 5%, X7R, 0603	0603
C29	1	2.2uF	GRM188R61H225KE11D	MuRata	CAP, CERM, 2.2 µF, 50 V, +/- 10%, X5R, 0603	0603
C30	1	10uF	ULV2G100MNL1GS	Nichicon	CAP, AL, 10 µF, 400 V, +/- 20%, SMD	D10xL13.5mm
D1, D3, D4	3	12V	MMSZ5242B-7-F	Diodes Inc.	Diode, Zener, 12 V, 500 mW, SOD-123	SOD-123
D2	1	100V	B1100-13-F	Diodes Inc.	Diode, Schottky, 100 V, 1 A, SMA	SMA
D5	1	150V	BAV20WS-TP	Micro Commercial Component	Diode, P-N, 150 V, 0.2 A, SOD-323	SOD-323
D6, D7	2	20V	3SMAJ5932B-TP	Micro Commercial Component	Diode, Zener, 20 V, 3 W, SMA	SMA
D8, D9	2	36V	CDSOD323-T36S	Bourns	Diode, TVS, Uni, 36 V, 75 Vc, SOD-323	SOD-323
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
H13, H14	2		ATS-T110P-521-C1-R1	Advanced Thermal Solutions	HEAT SINK FOR TI MOD, 50x13.9mm	HEAT SINK, 50x13.9mm
J1, J2, J5	3		282834-2	TE Connectivity	Terminal Block, 2x1, 2.54mm, TH	Terminal Block, 2x1, 2.54mm, TH
J3, J4, J6, J7	4		393800102	Molex	Terminal Block, 6.35mm, 2 Pos, Tin, R/A, TH	Terminal Block, 6.35mm, 2 Pos, R/A, TH
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q1, Q2, Q10, Q11, Q13, Q14	6	100V	CSD19533KCS	Texas Instruments	MOSFET, N-CH, 100 V, 86 A, KCS0003B (TO-220-3)	KCS0003B
Q3, Q4, Q7, Q8, Q12, Q15	6	150 V	MMBT5401LT1G	ON Semiconductor	Transistor, PNP, 150 V, 0.5 A, SOT-23	SOT-23
Q5, Q6, Q9	3	300 V	FMMT497	Zetex	Transistor, NPN, 300 V, 0.5 A, SOT-23	SOT-23
R1, R2, R28, R29, R31, R32	6	0.47	CSRN2512FKR470	Stackpole Electronics Inc	RES, 0.47, 1%, 2 W, 2512	2512
R3, R4, R24, R25, R30, R33	6	47	CRCW080547R0JNEA	Vishay-Dale	RES, 47, 5%, 0.125 W, 0805	0805
R5	1	390k	RR1220P-394-D	Susumu Co Ltd	RES, 390 k, 0.5%, 0.1 W, 0805	0805
R6, R15, R17, R22, R45	5	1.00k	CRCW08051K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.125 W, 0805	0805
R7	1	22k	CRCW080522K0JNEA	Vishay-Dale	RES, 22 k, 5%, 0.125 W, 0805	0805
R8	1	2.2k	CRCW08052K20JNEA	Vishay-Dale	RES, 2.2 k, 5%, 0.125 W, 0805	0805
R10, R37, R46	3	47	CRCW120647R0JNEA	Vishay-Dale	RES, 47, 5%, 0.25 W, 1206	1206
R11	1	1.37k	CRCW08051K37FKEA	Vishay-Dale	RES, 1.37 k, 1%, 0.125 W, 0805	0805
R12	1	20.5k	CRCW080520K5FKEA	Vishay-Dale	RES, 20.5 k, 1%, 0.125 W, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R13, R14, R23, R27	4	10.0k	CRCW120610K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.25 W, 1206	1206
R16	1	90.9k	CRCW080590K9FKEA	Vishay-Dale	RES, 90.9 k, 1%, 0.125 W, 0805	0805
R18	1	47.0k	RT0805BRD0747KL	Yageo America	RES, 47.0 k, 0.1%, 0.125 W, 0805	0805
R19	1	1.00Meg	RG2012P-105-B-T5	Susumu Co Ltd	RES, 1.00 M, 0.1%, 0.125 W, 0805	0805
R20	1	390k	ERJ-6GEYJ394V	Panasonic	RES, 390 k, 5%, 0.125 W, 0805	0805
R21	1	1.80k	RR1220P-182-D	Susumu Co Ltd	RES, 1.80 k, 0.5%, 0.1 W, 0805	0805
R26	1	24.9k	CRCW080524K9FKEA	Vishay-Dale	RES, 24.9 k, 1%, 0.125 W, 0805	0805
R35	1	22	CRCW201022R0JNEF	Vishay-Dale	RES, 22, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R39, R41, R42, R43, R44	5	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R47	1	4.7k	CRCW06034K70JNEA	Vishay-Dale	RES, 4.7 k, 5%, 0.1 W, 0603	0603
U1	1		TLV171IDBVR	Texas Instruments	36-V, Single-Supply, Low-Power Operational Amplifiers for Cost-Sensitive Systems, DBV0005A (SOT-5)	DBV0005A
U2	1		TPS7A4701RGWR	Texas Instruments	36-V, 1-A, 4-uVRMS, RF LDO Voltage Regulator, RGW0020A (VQFN-20)	RGW0020A
U3	1		TLV2171IDR	Texas Instruments	36-V, Single-Supply, Low-Power Operational Amplifier for Cost-Sensitive Systems, D0008A (SOIC-8)	D0008A
U4	1		TPS7A3301RGWR	Texas Instruments	Single Output High PSRR LDO, 1 A, Adjustable -1.18 to -33 V Output, -3 to -36 V Input, with Ultra-Low Noise, 20-pin VQFN (RGW), -40 to 125 degC, Green (RoHS & no Sb/Br)	RGW0020A
C16	0	1uF	GRM55DR72E105KW01L	MuRata	CAP, CERM, 1 µF, 250 V, +/- 10%, X7R, 2220	2220
C23	0	4.7uF	400AX4.7MTA8X9	Rubycon	CAP, AL, 4.7 µF, 400 V, +/- 20%, TH	D8xL9mm
C26, C28	0	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0603	0603
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
R9, R36	0	0	CRCW08050000Z0EAHP	Vishay-Dale	RES, 0, 5%, 0.333 W, 0805	0805
R34	0	22	CRCW201022R0JNEF	Vishay-Dale	RES, 22, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R38	0	1.00Meg	RG2012P-105-B-T5	Susumu Co Ltd	RES, 1.00 M, 0.1%, 0.125 W, 0805	0805
R40	0	1.00Meg	CRCW12061M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.25 W, 1206	1206

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated