

TID#:TIDA-060009

TIDA-060009 Bill of Materials

Designator	Description	Footprint	Quantity	Manufacturer	PartNumber
C1, C15	CAP, CERM, 10 μ F, 50 V, +/- 10%, X7R, 1206	1210_280	2	Taiyo Yuden	UMK325AB7106KM-T
C2, C12, C14, C16	CAP, CERM, 0.1 μ F, 25 V, +/- 5%, X7R, 0603	0603	4	AVX	06033C104JAT2A
C3	CAP, CERM, 4.7 μ F, 10 V, +/- 10%, X5R, 0603	0603	1	AVX	0603ZD475KAT2A
C4, C7, C13	CAP, CERM, 1 μ F, 25 V, +/- 10%, X7R, 0603	0603	3	AVX	06033C105KAT2A
C5	CAP, AL, 680 μ F, 25 V, +/- 20%, SMD	CL_1000x1350	1	Nichicon	UCL1E681MNL1GS
C6, C8, C20	CAP, CERM, 1 μ F, 6.3 V, +/- 20%, X7R, 0402	0402	3	MuRata	GRM155R70J105MA12D
C9, C10, C17, C18	CAP, CERM, 0.01 μ F, 50 V, +/- 5%, X7R, 0402	0402	4	Kemet	C0402C103J5RACTU
C11	CAP, CERM, 10 μ F, 50 V, +/- 10%, X5R, 1206	1206_180	1	TDK	C3216X5R1H106K160AB
C19	CAP, CERM, 1000 pF, 16 V, +/- 10%, X7R, 0402	0402	1	MuRata	GRM155R71C102KA01D
CS, GND, GND	Test Point, Compact, Black, TH	Keystone5006	3	Keystone	5006
D1	LED, Green, SMD	LTST-C191_Green	1	Lite-On	LTST-C191TGKT
D2	Diode, Schottky, 40 V, 5 A, SMC	SMC	1	Diodes Inc.	B540C-13-F
D3	LED, Orange, SMD	LTST-C170KFKT_Orange	1	Lite-On	LTST-C170KFKT
DOWN, MANUAL, UP	Switch, Push Button, SMD	SW_SKRKAEE010	3	Alps	SKRKAEE010
J1, J4, J5	Terminal Block, 6.35mm, 2x1, TH	On-Shore_OSTT70201	3	On-Shore Technology	OSTT7020150
J2, J3	Receptacle, 2.54mm, 10x2, Gold, TH	HDR2X10	2	Samtec	SSQ-110-03-G-D
J6	Receptacle, 2.54mm, 4x1, Tin, TH	Sullins_xPxC041LFBN	1	Sullins Connector Solutions	PPTC041LFBN-RC
LS1	BUZZER MAGNETIC, 12V, 12.8MM, SMD	WST-1310S	1	Sobertron	WST-1310S-3
Motor1, Motor2	Test Point, Compact, White, TH	Keystone5007	2	Keystone	5007
PVDD, VBAT	Test Point, Compact, Red, TH	Keystone5005	2	Keystone	5005
Q1	MOSFET, N-CH, 40 V, 75 A, PowerPAK_SO-8L	PowerPAK_SO-8L	1	Vishay-Siliconix	SQJ422EP-T1-GE3
Q2, Q3, Q4, Q5	MOSFET, N-CH, 40 V, 32 A, AEC-Q101, PowerPAK_SO-8L	PowerPAK_SO-8L	4	Vishay-Siliconix	SQJA412EP-T1_GE3
Q6, Q7	Transistor, NPN, 45 V, 0.5 A, SOT-23	SOT-23	2	ON Semiconductor	BC817-16LT1G
R1, R3, R6	RES, 100, 5%, 0.063 W, 0402	0402	3	Vishay-Dale	CRCW0402100RJNED
R2, R4, R7	RES, 1.5 k, 5%, 0.063 W, 0402	0402	3	Vishay-Dale	CRCW04021K50JNED
R5	RES, 4.99 k, 1%, 0.063 W, 0402	0402	1	Vishay-Dale	CRCW04024K99FKED
R8, R9, R16, R17, R25	RES, 0, 5%, 0.063 W, 0402	0402	5	Panasonic	ERJ-2GE0R00X
R10, R11, R20, R21, R24, R26	RES, 100, 1%, 0.063 W, 0402	0402	6	Vishay-Dale	CRCW0402100RFKED
R12, R13, R14, R15, R19, R22	RES, 10.0 k, 0.5%, 0.063 W, 0402	0402	7	Vishay-Dale	CRCW040210K0DHEDP
R18	RES, 499, 1%, 0.063 W, 0402	0402	1	Vishay-Dale	CRCW0402499RFKED

R22, R29, R30	RES, 1.0 k, 5%, 0.063 W, 0402	0402	3	Vishay-Dale	CRCW04021K00JNED
R23	RES, 0.002, 1%, 2 W, 2512	2512	1	Stackpole Electronics	CSNL2512FT2L00
U1	300mA High-Voltage Ultra-Low-Iq Low-D	DGN0008D_N	1	Texas Instruments	TPS7B8233QDGNRQ1
U2	Smart Diode Controller, DGK0008A	DGK0008A_N	1	Texas Instruments	LM74610QDGKRQ1
U3	Automotive Brushed DC Gate Driver, RHB	RHB0032E	1	Texas Instruments	DRV8703QRHBRQ1
U4	40V/100mOhm Single Channel Smart Hid	PWP0014C_N	1	Texas Instruments	TPS1H100AQPWPRQ1
U5	Automotive Catalog Dual Schmitt-Trigge	DCK0006A_N	1	Texas Instruments	SN74LVC2G17QDCKRQ1

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated