




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal Layer 1	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal Layer 2	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 9/9/2025	8:21:31 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 9/9/2025	8:21:31 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Overlay	TID #: N/A		
PLOT NAME = Bottom Overlay	GENERATED : 9/9/2025 8:21:31 PM	TEXAS INSTRUMENTS	



Symbol	Count	Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
⚙	55	0.200mm (7.87mil)	PTH	Round	Top Layer - Bottom Layer	
⌘	52	0.203mm (8.00mil)	PTH	Round	Top Layer - Bottom Layer	
H	4	0.300mm (11.81mil)	PTH	Round	Top Layer - Bottom Layer	
⚙	9	0.305mm (12.00mil)	PTH	Round	Top Layer - Bottom Layer	
⚙	26	0.356mm (14.00mil)	PTH	Round	Top Layer - Bottom Layer	
C	10	0.381mm (15.00mil)	PTH	Round	Top Layer - Bottom Layer	
B	2	0.400mm (15.75mil)	PTH	Round	Top Layer - Bottom Layer	
O	65	0.406mm (16.00mil)	PTH	Round	Top Layer - Bottom Layer	
⬛	2	0.465mm (18.29mil)	PTH	Round	Top Layer - Bottom Layer	
⌘	2	0.650mm (25.59mil)	NPTH	Round	Top Layer - Bottom Layer	
G	12	0.650mm (25.59mil)	PTH	Round	Top Layer - Bottom Layer	
▼	4	0.900mm (35.43mil)	PTH	Round	Top Layer - Bottom Layer	
□	1	1.016mm (40.00mil)	PTH	Round	Top Layer - Bottom Layer	
F	42	1.100mm (43.31mil)	PTH	Round	Top Layer - Bottom Layer	
⌘	22	1.150mm (45.28mil)	PTH	Round	Top Layer - Bottom Layer	
⬤	4	1.300mm (51.18mil)	PTH	Round	Top Layer - Bottom Layer	
D	2	1.400mm (55.12mil)	PTH	Slot	Top Layer - Bottom Layer	
⚙	10	1.500mm (59.06mil)	PTH	Round	Top Layer - Bottom Layer	
⌘	17	1.600mm (63.00mil)	PTH	Round	Top Layer - Bottom Layer	
E	2	1.700mm (66.93mil)	PTH	Slot	Top Layer - Bottom Layer	
	343 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 9/9/2025	8:21:31 PM	TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD107-001	REV: A	SUN REV: Not in version control
LAYER NAME = M2 Board Dimensions	TID #: N/A		
PLOT NAME = Board Dimensions	GENERATED : 9/9/2025 8:21:32 PM	TEXAS INSTRUMENTS	