




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 5/21/2024 9:30:40 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 5/21/2024 9:30:40 AM		TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 5/21/2024 9:30:40 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal 1	GENERATED : 5/21/2024 9:30:40 AM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME =	TID #: N/A		
PLOT NAME = Signal 2	GENERATED : 5/21/2024 9:30:41 AM		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 5/21/2024 9:30:41 AM		TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 5/21/2024 9:30:41 AM		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Bottom Overlay	TID #: N/A		
PLOT NAME = Bottom Overlay	GENERATED : 5/21/2024 9:30:41 AM		TEXAS INSTRUMENTS






Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
■	5	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	
⊠	372	10.00mil (0.254mm)	PTH	Round	Top Layer - Bottom Layer	
▽	14	33.47mil (0.850mm)	PTH	Round	Top Layer - Bottom Layer	
☆	66	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	
⊠	8	47.24mil (1.200mm)	PTH	Round	Top Layer - Bottom Layer	
⊙	6	49.21mil (1.250mm)	PTH	Round	Top Layer - Bottom Layer	
○	6	51.18mil (1.300mm)	PTH	Round	Top Layer - Bottom Layer	
□	2	63.00mil (1.600mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	4	125.98mil (3.200mm)	PTH	Round	Top Layer - Bottom Layer	
◆	2	23.62mil (0.600mm)	PTH	Slot	Top Layer - Bottom Layer	
	485 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.  
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 5/21/2024 9:30:42 AM		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: MD078	REV: A	SUN REV: Not in version control
LAYER NAME = M2 Board Dimensions	TID #: N/A		
PLOT NAME = Board Dimensions	GENERATED : 5/21/2024 9:30:43 AM		TEXAS INSTRUMENTS