




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME = Top Overlay	TID #: TIDA-010025CB		
PLOT NAME = Top Overlay	GENERATED : 10/10/2018 5:32:04 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	010025CB	REV:	E1	SUN REV:	Not In VersionControl
LAYER NAME = Top Solder	TID #:	TIDA-010025CB				
PLOT NAME = Top Solder Mask	GENERATED	: 10/10/2018	5:32:05 PM	TEXAS INSTRUMENTS		




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	010025CB	REV:	E1	SUN REV:	Not In VersionControl
LAYER NAME = Top Layer	TID #:	TIDA-010025CB				
PLOT NAME = Top Layer	GENERATED	: 10/10/2018	5:32:06 PM	TEXAS INSTRUMENTS		




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	010025CB	REV:	E1	SUN REV:	Not In VersionControl
LAYER NAME =	GND	TID #:	TIDA-010025CB			
PLOT NAME =	Signal Layer 1	GENERATED	:	10/10/2018	5:32:06 PM	TEXAS INSTRUMENTS




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME = PWR	TID #: TIDA-010025CB		
PLOT NAME = Signal Layer 2	GENERATED : 10/10/2018 5:32:07 PM	TEXAS INSTRUMENTS	




ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:	010025CB	REV:	E1	SUN REV:	Not In VersionControl
LAYER NAME = Bottom Layer	TID #:	TIDA-010025CB				
PLOT NAME = Bottom Layer	GENERATED	: 10/10/2018	5:32:08 PM	TEXAS INSTRUMENTS		



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME = Bottom Solder	TID #: TIDA-010025CB		
PLOT NAME = Bottom Solder Mask	GENERATED : 10/10/2018 5:32:09 PM	TEXAS INSTRUMENTS	





ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME = Bottom Overlay	TID #: TIDA-010025CB		
PLOT NAME = Bottom Overlay	GENERATED : 10/10/2018 5:32:09 PM		TEXAS INSTRUMENTS



Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
⊗	8	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	+/-3,00mil
⊗	166	16.00mil (0.406mm)	PTH	Round	Top Layer - Bottom Layer	
○	80	39.37mil (1.000mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	15	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	
⊗	50	41.00mil (1.041mm)	PTH	Round	Top Layer - Bottom Layer	
□	2	43.31mil (1.100mm)	PTH	Round	Top Layer - Bottom Layer	
▽	4	125.00mil (3.175mm)	PTH	Round	Top Layer - Bottom Layer	+/-3,00mil
◇	4	125.98mil (3.200mm)	PTH	Round	Top Layer - Bottom Layer	
329 Total						

Drill tolerances:
For 7.874mil mil drill via +0/-7.874mil
For 16 mil drill via +0/-16 mil
For PTH +/- 3 mil
For NPTH +/- 2 mil
2. This not an impedance controlled board

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME = Drill Drawing	TID #: TIDA-010025CB		
PLOT NAME = Drill Drawing	GENERATED : 10/10/2018 5:32:10 PM	TEXAS INSTRUMENTS	



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: 010025CB	REV: E1	SUN REV: Not In VersionControl
LAYER NAME =	TID #: TIDA-010025CB		
PLOT NAME = Board Dimensions	GENERATED : 10/10/2018 5:32:12 PM	TEXAS INSTRUMENTS	