

Variant: 001
 Generated: 2/12/2026 4:43 PM
 TID #:



TIDA-050082 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C7, C13, C20	4	0.01uF	GRM155R71E103KA01D	MuRata	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0402	0402
2	C2, C3	2	0.1uF	CGA3E2X7R1H104K080AA	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
3	C4	1	0.01uF	GCM188R71H103KA37D	MuRata	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
4	C5	1	10uF	GRT188R61E106ME13D	MuRata	CAP, CERM, 10 uF, 25 V, +/- 20%, X5R, 0603	0603
5	C6	1	10uF	GRM31CR71E106KA12L	MuRata	CAP, CERM, 10 uF, 25 V, +/- 10%, X7R, 1206	1206
6	C8	1	1uF	C4AQSBU4100A1WJ	KEMET	1 uF Film Capacitor 1500V (1.5kV) Polypropylene (PP), Metallized Radial	RADIAL
7	C9, C11, C15	3	10uF	GRM21BZ71E106KE15L	MuRata	CAP, CERM, 10 uF, 25 V, +/- 10%, X7R, 0805	0805
8	C10, C17, C18, C22	4	0.1uF	C1210C104KBRAC7800	Kemet	CAP, CERM, 0.1 uF, 630 V, +/- 10%, X7R, 1210	1210
9	C12, C14, C24	3	2200pF	8.85012E+11	Würth Elektronik	CAP, CERM, 2200 pF, 16 V, +/- 10%, X7R, 0402	0402
10	C16	1	22uF	GRM21BR61E226ME44L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 20%, X5R, 0805	0805
11	C19	1	1uF	CGA3E1X7R1C105K080AC	TDK	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
12	C21, C23	2	10pF	C0402C100K5RAC7867	KEMET	10 pF ±10% 50V Ceramic Capacitor X7R 0402 (1005 Metric)	0402
13	C25	1	2.2nF	C1206X222KGRACAUTO	KEMET	2200 pF ±10% 2000V (2kV) Ceramic Capacitor X7R 1206 (3216 Metric)	1206
14	D1	1		VS-8EWF12SLHM3	Vishay	Diode 1200 V 8A Surface Mount TO-252AA (DPAK)	DPAK
15	D2	1		STTH1512GY-TR	STMicroelectronics	Rectifier Diode Switching 1.2KV 15A 75ns Automotive 3-Pin(2+Tab) D2PAK T/R	D2PAK
16	D3	1		SMF18CA	Littelfuse	Diode TVS Single Bi-Dir 18V 200W 2-Pin SOD-123FL T/R	SOD-123FL
17	FB1, FB2	2		BLM21HE802SH1L	Murata	8 kOhms @ 100 MHz 1 Signal Line Ferrite Bead 0805 (2012 Metric) 650mA 700mOhm	0805
18	FID1, FID2, FID3	3		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
19	J2, J3, J4	3		6.91251E+11	Würth Electronics	2 Position Wire to Board Terminal Block Horizontal with Board 0.250" (6.35mm) Through Hole	CONN_TERM_BLOC K2
20	L1, L2	2	1000 ohm	BLM21AG102SN1D	MuRata	Ferrite Bead, 1000 ohm @ 100 MHz, 0.5 A, 0805	0805
21	L3	1	100uH	ZG3718	Coilcraft	Power inductor, 100uH-9.6A, Flat wire, TH, PQ26	PTH6
22	Q1	1		UF3C120150B7S	UnitedSiC	N-Channel 1200 V 17A (Tc) 136W (Tc) Surface Mount D2PAK-7	D2PAK7
23	R1	1	294k	ERJ-2RKF2943X	Panasonic	RES, 294 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
24	R2	1	90.9k	ERJ-2RKF9092X	Panasonic	RES, 90.9 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
25	R3, R4, R5, R7, R14, R15	6	180k	CRCW1206180KJNEA	Vishay-Dale	RES, 180 k, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
26	R6	1	1.1k	CRCW04021K10JNED	Vishay-Dale	RES, 1.1 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
27	R8	1	10k	ERJ-2GEJ103X	Panasonic	RES, 10 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
28	R9	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
29	R10	1	100k	ERJ-3GEYJ104V	Panasonic	RES, 100 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
30	R11	1	0.06	WSL2512R0600FEA	Vishay-Dale	RES, 0.06, 1%, 1 W, 2512	2512
31	R12	1	80m	TLRP3A20CR080FTE	TE Connectivity	80 mOhms ±1% 2W Chip Resistor 2512 (6432 Metric) Anti-Sulfur, Automotive AEC-Q200, Current Sense Metal Element	2512
32	R13	1	56	CRCW120656R0JNEA	Vishay-Dale	RES, 56, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
33	TP1, TP6, TP7	3		5011	Keystone Electronics	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
34	TP2	1		5010	Keystone Electronics	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
35	TP4	1		5014	Keystone Electronics	Test Point, Multipurpose, Yellow, TH	Yellow Multipurpose Testpoint
36	U1	1		TPS7A4901DRBR	Texas Instruments	Vin 3V to 36V, 150mA, Ultra-Low-Noise, High-PSRR Low-Dropout (LDO) Linear Regulator, DRB0008A (VSON-8)	DRB0008A
37	U2	1		TPSI31P1QDVXRQ1	Texas Instruments	Isolated Automotive Active Pre-charge Controller with Integrated Gate Driver and Bias Supply	SSOP16

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025