

B



TIDA-00891 USB Type-C TM Plug to USB Type-A
Receptacle SS MUX with UFP Controller Reference Design

Item	Quantity	Reference	Part	Manufacturer	Manufacturer Part Number	Digi-Key Part Number	PCB Footprint	Description
1	1	C1	0.01uF	Murata Electronics North America	GRM155R71H102KA01D	490-1303-1-ND		402 CAP CER 1000PF 50V X7R 0402
2	4	C2,C3,C4,C15	0.1uF	Samsung Electro-Mechanics America, Inc.	CL05A104MP5NNNC	1276-1443-1-ND		402 CAP CER 0.1UF 10V X5R 0402
3	1	C5	NC, 10uF	Samsung Electro-Mechanics America, Inc.	CL10A106MP8NNNC	1276-1871-1-ND		603 CAP CER 10UF 10V X5R 0603
4	1	C7	10uF	Yageo	CC0805ZKY5V6BB106	311-1355-1-ND		805 CAP CER 10UF 10V Y5V 0805
5	2	C12,C13	10uF	Murata Electronics North America	GRM2219R6Q106KE19D	490-3340-1-ND		805 CAP CER 10UF 6.3V X5R 0805
6	1	C14	22uF	Samsung Electro-Mechanics America, Inc.	CL21A226MQLQNC	1276-2412-1-ND		805 CAP CER 22UF 6.3V X5R 0805
7	1	C16	47uF	TDK Corporation	C2012X5R1A476M125AC	445-8239-1-ND		805 CAP CER 47UF 10V X5R 0805
8	6	C17,C18,C19,C20,C21,C22	0.47uF	TDK Corporation	C0603X5R1A474M030BC	445-13666-1-ND		201 CAP CER 0.47UF 10V X5R 0201
9	1	D2	LED Green 0402	Lumex	SML-LX0402SUGC-TR	67-1881-1-ND	LED_0402	Green LED
10	1	D6	ESD5Z6.0T1G	ON Semi	ESD5Z6.0T1G	ESD5Z6.0T1GOSCT-ND	SOD_523	TVS Diode
11	1	D7	LED Orange 0402	Lumex	SML-LX0402S0CC-TR	67-1879-1-ND	LED_0402	Orange LED
12	1	D8	LED YLW 0402	Lumex	SML-LX0402SYC-TR	67-1880-1-ND	LED_0402	Orange LED
13	1	D9	LED RED 0402	Lumex	SML-LX0402SIC-TR	67-1878-1-ND	LED_0402	Orange LED
14	1	FB1	220 @ 100MHZ	MuRata	BLM18EG221SN1D	490-3992-1-ND		603 FB EAD 1000@100MHz
15	1	J3	USB3_TypeA_Connector	Amphenol	GSB311131HR	GSB311131HR-ND	USB3_TYPEA	Connector Receptacle USB TypeA 3.0, Super Speed 9 Position Through Hole, Right Angle, Horizontal
16	1	J4	TypeC_Receptacle_DualSMT_TOP	Foxconn	UT12113-11601-7H		USB_TYPEC_UT1211	
17	1	L1	1uH	Taiyo Yuden	NR3015T1R0N	587-1647-1-ND	IND_NR3015	FIXED IND 1UH 2.1A 36 MOHM SMD
18	1	R4	1.6K	Panasonic Electronic Components	ERJ-2GEJ162X	P1.6KJCT-ND		402 RES SMD 1.6K OHM 5% 1/10W 0402
19	4	R5,R6,R38,R43	0	Yageo	RC0402JR-070RL	311-0.0URCT-ND		402 RES SMD 0.00OHM JUMPER 1/16W 0402
20	1	R27	178K	Yageo	RC0402FR-07178KL	YAG3010CT-ND		402 RES SMD 178K OHM 1% 1/16W 0402
21	2	R28,R29	NC, 0	Yageo	RC0402JR-070RL	311-0.0URCT-ND		402 RES SMD 0.00OHM JUMPER 1/16W 0402
22	1	R35	900K	Panasonic Electronic Components	ERJ-2RKF9093X	P909KJCT-ND		402 RES SMD 909K OHM 1% 1/10W 0402
23	1	R36	4.7K	Yageo	RC0402JR-074K7L	311-4.7KJCT-ND		402 RES SMD 4.7K OHM 5% 1/16W 0402
24	1	R37	NC, 10K	Yageo	RC0402JR-0710KL	311-10KJCT-ND		402 RES SMD 10K OHM 5% 1/16W 0402
25	4	R39,R40,R41,R42	100K	Yageo	RC0201JR-07100KL	311-100KNCT-ND		201 RES SMD 100K OHM 5% 1/20W 0201
26	5	R45,R46,R47,R48,R54	200K	Panasonic Electronic Components	ERJ-1GEF2003C	P200KABCT-ND		201 RES SMD 200K OHM 1% 1/20W 0201
27	2	R49,R50	NC, 10K	Yageo	RC0201JR-0710KL	311-10KNCT-ND		201 RES SMD 10K OHM 5% 1/20W 0201
28	3	R51,R53,R55		499 Panasonic Electronic Components	ERJ-2RKF4990X	P499KJCT-ND		402 RES SMD 499 OHM 1% 1/10W 0402
29	1	R52		330 Panasonic	ERJ-XGNJ331Y	Mouser667-ERJ-XGNJ331Y		402 Distributed by Mouser
30	6	TP1,TP2,TP5,TP6,TP7,TP8	15-mil TEST PAD				15_mil_Round_Probe_Point	15 mil Round Pad
31	1	U1	TUSB211RWB	Texas Instruments	TUSB211RWB		RWB	USB 2.0 480Mbps High Speed Signal Conditioner
32	1	U2	HD3SS3220	Texas Instruments	HD3SS3220RNHR		RNH_QFN-30	USB Type-C DRP Port Controller with SuperSpeed 2.1 MUX DISTRIBUTED BY TI
33	2	U3,U4	TPD4E05U06	Texas Instruments	TPD4E05U06DQAR	296-35765-1-ND	DQA	4 Channel Ultra Low Capacitance IEC ESD Protection Diodes
34	1	U5	TPD6E05U06	Texas Instruments	TPD6E05U06RVZR	TPD6E05U06RVZR-ND	RVZ	6-Channel Ultra low capacitance IEC ESD protection diodes
35	1	U8	TP562082DSGT	Texas Instruments	TP562082DSGT	296-29647-1-ND	dsg	1.2A High Efficient Step Down Converter in 2x2mm SON Package. 3.3 Vout (Min)
36	1	PCB		ANY	INT027			PCB Board

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.