

TIDA-01236 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB1	1		TIDA-01236	Any	Printed Circuit Board	
2	BT1	1		3039	Keystone	Battery Holder, TH	25.4x22.61mm
3	C1, C2, C4, C5	4	4.7uF	C2012X7R1V475K125AC	TDK	CAP, CERM, 4.7 uF, 35 V, +/- 10%, X7R, 0805	0805
4	C3, C6, C8	3	1uF	C1005X5R1A105K050BB	TDK	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0402	0402
5	C7, C9	2	0.1uF	885012105016	Wurth Elektronik	CAP, CERM, 0.1 uF, 16 V, +/- 20%, X5R, 0402	0402
6	C10	1	33pF	C1005C0G1H330J050BA	TDK	CAP, CERM, 33 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
7	C11, C23	2	22uF	GRM188R60J226MEA0J	MuRata	CAP, CERM, 22 uF, 6.3 V, +/- 20%, X5R, 0603	0603
8	C12, C13, C14, C15, C16, C17, C18, C19, C22, C38	10	0.1uF	GRM155R70J104KA01D	MuRata	CAP, CERM, 0.1 uF, 6.3 V, +/- 10%, X7R, 0402	0402
9	C20, C21, C34	3	1uF	GRM155R70J105MA12D	MuRata	CAP, CERM, 1 uF, 6.3 V, +/- 20%, X7R, 0402	0402
10	C24, C33	2	3.6pF	GRM1555C1H3R6CA01D	MuRata	CAP, CERM, 3.6 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
11	C25, C36, C37	3	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
12	C28, C29	2	18pF	GRM1555C1H180JA01D	MuRata	CAP, CERM, 18 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
13	C30	1	2.7pF	GRM1555C1H2R7CA01D	MuRata	CAP, CERM, 2.7 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
14	C31	1	6.2pF	GRM1555C1H6R2CA01D	MuRata	CAP, CERM, 6.2 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
15	C32	1	3pF	GRM1555C1H3R0CA01D	MuRata	CAP, CERM, 3 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
16	C35	1	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0402	0402
17	E1	1		ANTENNA_HELICAL	N/A	PCB Antenna. There is nothing to buy or mount.	Antenna
18	H1, H2, H3, H4	4		SJ-5303 (CLEAR)	3M	Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon
19	J1	1		TMM-107-01-G-D	Samtec	Header, 2mm, 7x2, Gold, TH	Header, 7x2, 2mm, TH
20	J2	1		GRPB052VWVN-RC	Sullins Connector Solutions	Header, 50mil, 5x2, Gold, TH	Header, 5x2, 50mil
21	L1	1	4.7uH	EPL3015-472MLB	Coilcraft	Inductor, Shielded, Ferrite, 4.7 uH, 1.2 A, 0.14 ohm, SMD	Inductor, 3x1.55x3mm
22	L2	1	1500 ohm	BLM18HE152SN1D	MuRata	Ferrite Bead, 1500 ohm @ 100 MHz, 0.5 A, 0603	0603
23	L3, L4, L5, L6, L7, L8	6	1000 ohm	BLM15HG102SN1D	MuRata	Ferrite Bead, 1000 ohm @ 100 MHz, 0.25 A, 0402	0402
24	L10	1	6.8uH	VLF252015MT-6R8M	TDK	Inductor, Shielded, Ferrite, 6.8 uH, 0.57 A, 0.16 ohm, SMD	2.5x1.5x2.0
25	L11, L16	2	7.5nH	LQG15HS7N5J02D	MuRata	Inductor, Multilayer, Air Core, 7.5 nH, 0.3 A, 0.24 ohm, SMD	0402 polarized
26	L12, L13	2	6.8nH	LQG15HS6N8J02D	MuRata	Inductor, Multilayer, Air Core, 6.8 nH, 0.3 A, 0.24 ohm, SMD	0402 polarized
27	L14	1	27nH	LQG15HS27NJ02D	MuRata	Inductor, Multilayer, Air Core, 27 nH, 0.3 A, 0.46 ohm, SMD	0402 polarized
28	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
29	LS1	1		CPE-253	CUI Inc.	PIEZO BUZZER INDICATOR, TH	D28xL25.9mm
30	MK1	1		SPH0641LU4H-1	Knowles Acoustics	Microphone, ULTRASONIC, MIC MEMS DIGITAL, SMT	3.5x2.65mm
31	Q1	1	12V	CSD13201W10	Texas Instruments	MOSFET, N-CH, 12 V, 1.6 A, 1x0.62x1mm	1x0.62x1mm
32	R1	1	1.96Meg	CRCW04021M96FKED	Vishay-Dale	RES, 1.96 M, 1%, 0.063 W, 0402	0402
33	R2, R6, R7	3	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
34	R3	1	249k	CRCW0402249KFKED	Vishay-Dale	RES, 249 k, 1%, 0.063 W, 0402	0402
35	R4	1	1.00	CRCW04021R00FKED	Vishay-Dale	RES, 1.00, 1%, 0.063 W, 0402	0402
36	R5, R9	2	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
37	R8	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
38	U1	1		TPS61070DDCR	Texas Instruments	90% Efficient Synchronous Boost Converter with 600-mA Switch, DDC0006A	DDC0006A
39	U2	1		BQ35100PWR	Texas Instruments	Single Lithium Primary State-of-Health and End-of-Service Monitor, PW0014A	PW0014A
40	U3	1		CC1310F128RGZR	Texas Instruments	Sub-1 GHz and 2.4 GHz Multi-standard RF IC Family, RGZ0048A	RGZ0048A
41	U4	1		TLV320AIC3256IRSB	Texas Instruments	Ultra Low Power Stereo Audio Codec With Embedded miniDSP, RSB0040B	RSB0040B
42	U5	1		TPS73118DBVR	Texas Instruments	Single Output Fast Transient Response LDO, 150 mA, Fixed 1.8 V Output, 1.7 to 5.5 V Input, 5-pin SOT-23 (DBV), -40 to 85 degC, Green (RoHS & no Sb/Br)	DBV0005A
43	Y1	1		FC-135 32.7680KA-A3	Epson	Crystal, 32.768 KHz, 12.5 pF, SMD	SMD, 2-Leads, Body 3.2x1.5mm
44	Y2	1		TSX-3225 24.0000MF20G-AC3	Epson	Crystal, 24 MHz, 9 pF, SMD	SMD, 4-Leads, Body 2.65x3.35mm, Height 0.6mm
45	C26, C27	0	12pF	GRM1555C1H120JA01D	MuRata	CAP, CERM, 12 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
46	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
47	L15	0	3.3nH	ELJPF3N3DFB	Panasonic	Inductor, Ceramic, 3.3 nH, 1500 A, 0.07 ohm, SMD	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated