

TIDA-00816 Bill of Materials



Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
A1	0	DNM	DNM	DNM	DNM	
C3 C4 C5 C7 C9 C16 C20 C30 C32 C38 C39 C43 C46 C52 C53 C54 C55 C56 C57	19	100nF	GRM155R70J104KA01D	MURATA	CAPACITOR, CERAMIC X7R, 100nF, 6.3V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD	0402
C6 C8	2	22uF	GRM188R60J226MEA0D	MURATA	CAPACITOR, CERAMIC, X5R, 22uF, 6.3V, -20%/+20%, -55DEGC/+85DEGC, 0603, SMD	0603
C11 C22	2	3.6pF	GRM1555C1H3R6CA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 3.6pF, 50V, -0.25pF/+0.25pF, -55DEGC/+125DEGC, 0402, SMD	0402
C12	1	2.7pF	GRM1555C1H2R7CA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 2.7pF, 50V, -0.25pF/+0.25pF, -55DEGC/+125DEGC, 0402, SMD	0402
C13	1	6.2pF	GRM1555C1H6R2CA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 6.2pF, 50V, -0.25pF/+0.25pF, -55DEGC/+125DEGC, 0402, SMD	0402
C14	1	3pF	GRM1555C1H3R0CA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 3pF, 50V, -0.25pF/+0.25pF, -55DEGC/+125DEGC, 0402, SMD	0402
C15 C21	2	100pF	GRM1555C1H101JA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 100pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	0402
C17 C18 C33 C34	4	12pF	GRM1555C1H120JA01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 12pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	0402
C19 C40 C42 C44	4	1uF	GRM155R61A105KE15D	MURATA	CAPACITOR, CERAMIC X5R, 1uF, 10V, -10%/+10%, -55DEGC/+85DEGC, 0402, SMD	0402
C24 C58	0	DNM	DNM	DNM	DNM	DNM
C35 C36 C37 C41 C50	5	10nF	CAPACITOR_0402_10nF_X7R_M_+/-10%_25V	MANUFACTURER SELECTION	CAPACITOR, CERAMIC X7R, 10nF, 25V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD	0402
C45 C48 C49	3	2.2uF	GRM155R60J225KE95D	MURATA	CAPACITOR, CERAMIC X5R, 2.2uF, 6.3V, -10%/+10%, -55DEGC/+85DEGC, 0402, SMD	0402
C47	1	15pF	CAPACITOR_0402_15pF_C0G/NP0_M_+/-5%_50V	MANUFACTURER SELECTION	CAPACITOR, CERAMIC C0G/NP0, 15pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD	0402
C59	1	100nF	CAPACITOR_0402_100nF_X7R_M_+/-10%_10V	MANUFACTURER SELECTION	CAPACITOR, CERAMIC X7R, 100nF, 10V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD	0402
CR1 CR5	2	LPL296-J2L2-25	LP L296-J2L2-25	OSRAM	OPTO, LED, GREEN COLOR, 562nm, 0.02A, 0.08W, 0603, SMD	0603

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
CR2 CR4	2	LS L296-P2Q2-1	LS L296-P2Q2-1	OSRAM	OPTO, LED, SUPER RED COLOR, 630nm, 1.8V TO 2.3V, 0.06A, 0603, SMD	0603
CR6	1	TPD4E004DRY	TPD4E004DRYR	TEXAS INSTRUMENTS	DIODE, PROTECTION, ESD ARRAY, 4 CHANNEL, 6V TO 8V, -40DEGC/+85DEGC, SON6, SMD	SON6
CR7 CR8	2	TPD6E004RSER	TPD6E004RSER	TEXAS INSTRUMENTS	DIODE, PROTECTION, ESD, 7V, -40DEGC/+85DEGC, QFN8, SMD	QFN8
FIDU1 FIDU2 FIDU3 FIDU4 FIDU5 FIDU6	0	DNM			DNM	
FL1	1	BLM18HE152SN1	BLM18HE152SN1D	MURATA	FILTER, EMI, 1500@100MHz, -55DEGC/+125DEGC, 0603, SMD	0603
J1 J2	2	SSQ-110-23-LD	SSQ-110-23-L-D	SAMTEC	CONNECTOR, HEADER, FEMALE, STRAIGHT, 2 ROWS, 20 ROWS, 2.54mm, PTH	
J6	1	105164-0001	105164-0001	MOLEX	CONNECTOR, USB, FEMALE, RIGHT ANGLE, 1 ROW, 5 PINS, PITCH 0.65mm, SMD	
L1	1	6.8uH	MLZ2012N6R8LT000	TDK	INDUCTOR, STANDARD, CHIP, FERRITE CORE, SHIELDED, 6.8uH, -20%/+20%, 1.1A, -55DEGC/+125DEGC, 0805, SMD	0805
L12 L23	2	7.5nH	LQG15HS7N5J02D	MURATA	INDUCTOR, RF, CHIP, NON-MAGNETIC CORE, 7.5nH, -5%/+5%, 0.3A, -55DEGC/+125DEGC, 0402, SMD	0402
L13 L14	2	6.8nH	LQG15HS6N8J02D	MURATA	INDUCTOR, RF, CHIP, NON-MAGNETIC CORE, 6.8nH, -5%/+5%, 0.3A, -55DEGC/+125DEGC, 0402, SMD	0402
L22	1	27nH	LQG15HS27NJ02D	MURATA	INDUCTOR, RF, CHIP, NON-MAGNETIC CORE, 27nH, -5%/+5%, 0.3A, -55DEGC/+125DEGC, 0402, SMD	0402
M1 M2 M3 M4 M5 M6 M7 M8 M9 M10 M11 M12 M13 M14	14	SNT-100BK-G	SNT-100-BK-G	SAMTEC	MECHANIC, SHUNT, CURRENT RATING 4.3A PER PIN, 2.54 X 5.08 X 6.1mm, BLACK	
MH1 MH2	0	DNM			DNM	
MH3 MH4	0	DNM			DNM	
MH5	0	DNM			DNM	
P1 P2 P10	3	BB02-HC031-KB1-603000	BB02-HC031-KB1-603000	GRADCONN	CONNECTOR, HEADER, MALE, STRAIGHT, 1 ROW, 3 PINS, PITCH 2.54mm, PTH	
P4	1	BB02-HJ221-KB1-603000	BB02-HJ221-KB1-603000	GRADCONN	CONNECTOR, HEADER, MALE, STRAIGHT, 2 ROWS, 22 PINS, PITCH 2.54mm, PTH	

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
P5 P7	2	FTSH-105-01-F-DV-K	FTSH-105-01-F-DV-K	SAMTEC	CONNECTOR, HEADER, MALE, STRAIGHT, 10 PINS, 2 ROWS, PITCH 1.27mm, SMD	
P6	1	BB02-HJ041-KB1-603000	BB02-HJ041-KB1-603000	GRADCONN	CONNECTOR, HEADER, MALE, STRAIGHT, 2 ROWS, 4 PINS, PITCH 2.54mm, PTH	
P8	0	DNM			DNM	
P11	1	MM5829-2700	MM5829-2700RJ4	MURATA	CONNECTOR, COAX, MALE, UP TO 12GHz, 30V, SMD	
R1 R61 R62 R63 R65	5	100k	RESISTOR_0402_100k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 100k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R2 R3 R58	3	3.3k	RESISTOR_0402_3.3k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 3.3k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R11	1	2.2k	RESISTOR_0402_2.2k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 2.2k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R12	1	1.8pF	GJM1555C1H1R8BB01D	MURATA	CAPACITOR, CERAMIC C0G/NP0, 1.8pF, 50V, -0.1pF/+0.1pF, -55DEGC/+125DEGC, 0402, SMD	0402
R13	0	DNM	DNM	DNM	DNM	DNM
R14 R25	2	220	RESISTOR_0402_220_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 220, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R15 R23	2	180	RESISTOR_0402_180_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 180, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R17	1	10k	RESISTOR_0402_10k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 10k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R18	1	4.7k	RESISTOR_0402_4.7k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 4.7k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R19 R21 R59 R60	0	DNM	DNM	DNM	DNM	DNM
R20	1	100	RESISTOR_0402_100_+/-1%_50V_0.063W_M_+/-100ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 100, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R22	1	330k	RESISTOR_0402_330k_+/-1%_50V_0.063W_M_+/-100ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 330k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R24	1	220k	RESISTOR_0402_220k_+/-1%_50V_0.063W_M_+/-100ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 220k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R27 R29 R30 R39	4	1k	RESISTOR_0402_1k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 1k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R28	1	4.87k	RESISTOR_0402_4.87k_+/-1%_50V_0.063W_M_+/-100ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 4.87k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R31	1	51	RESISTOR_0402_51_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 51, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R32	1	33k	RESISTOR_0402_33k_+/-1%_50V_0.063W_M_+/-100ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 33k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R33	1	51k	RESISTOR_0402_51k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 51k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R34	1	30k	RESISTOR_0402_30k_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 30k, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
R46 R47 R48 R49 R51	0	DNM	DNM	DNM	DNM	DNM
R52	1	0	RESISTOR_0603_0_+/-5%_75V_0.1W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 0, 0.1W, 75V, -55DEGC/+155DEGC, 0603, SMD	0603
R55 R56 R57 R66	4	100	RESISTOR_0402_100_+/-5%_50V_0.063W_M_+/-200ppm	MANUFACTURER SELECTION	RESISTOR, THICK FILM, 100, -5%/+5%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD	0402
SW1 SW2 SW3	3	1188E-1K2-V	1188E-1K2-V-TR	DIPTRONICS	SWITCH, TACT, 0.05A@250VAC, 0.05A@12VDC, 0.05A, 250V, SMD	
U1	1	CC1310 F128RGZT	CC1310F128RGZT	TEXAS INSTRUMENTS	IC, MICROCONTROLLER, 128kB, 1.8V TO 3.8V, VQFN48-EP, SMD	VQFN48-EP
U4	1	MX25R8 035FZUI L0	MX25R8035FZUI L0	MACRONIX	IC, MEMORY, FLASH, SERIAL, 8Mbit, 1.65V TO 3.6V, USON8, SMD	USON8
U5	1	TM4C12 94NCPD TT3R	TM4C1294NCPD TT3R	TEXAS INSTRUMENTS	IC, MICROPROCESSOR, TIVA C SERIES MICROCONTROLLER, ARM CRTEX-M4, 2.97V TO 3.63V, TQFP128, SMD	TQFP128
U6	1	LM4040 B25IDC K	LM4040B25IDCKR	TEXAS INSTRUMENTS	IC, ANALOG, PRECISION MICROPOWER SHUNT VOLTAGE REFERENCE, 2.5V, SC70-5, SMD	SC70-5

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U7	1	TPS79601DR	TPS79601DRBR	TEXAS INSTRUMENTS	IC, ANALOG, ULTRALOW-NOISE, HIGH PSRR, FAST, RF, 1A LOW-DROPOUT LINEAR REGULATORS, VIN:2.7V TO 5.5V, VOUT:1.2V TO 5.5V, SON8, SMD	SON8
U8 U9 U10	3	SN74AVC4T245RSV	SN74AVC4T245RSVR	TEXAS INSTRUMENTS	IC, DIGITAL, LOGIC, 4bit DUAL-SUPPLY BUS TRANSCEIVER 3 STATE OUTPUT, 1.2V TO 3.6V, UQFN16, SMD	UQFN16
Y1	1	32.768kHz	FC-135 32.7680KA-AG0	EPSON	CRYSTAL, RESONATOR, 32.768kHz, -20PPM/+20PPM, -40DEGC/+85DEGC, SMD	
Y2	1	24MHz	TSX-3225 24.0000MF15X-AC3	EPSON	CRYSTAL, CRYSTAL OSCILLATOR, 24MHz, -15PPM/DEGC/+15PPM/DEGC, -40DEGC/+85DEGC, SMD	
Y3	1	16MHz	NX3225GA-16.000M-STD-CRG-1	NIHON DEMPAKOGYO	CRYSTAL, OSCILLATOR, 16MHz, -30PPM/DEGC/+30PPM/DEGC, -40DEGC/+85DEGC, SMD	

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated