





NOTES: UNLESS OTHERWISE SPECIFIED:

© COPYRIGHT 2018 TEXAS INSTRUMENTS
UNPUBLISHED, ALL RIGHTS RESERVED

REVISIONS			
REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	04/23/2018	SS
B	UPDATED BOM	5/3/2018	SS




ITEMS 19 AND 20 NOT SHOWN IN THESE VIEWS



ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	MCH019	LIGHTCRAFTERDEVM MOUNTING PLATE	1
2	MCH020	ENGINE MOUNTING PLATE BLOCK	1
3	MCH021	LIGHT ENGINE MOUNTING PLATE	1
4	PHOTB0161	OPTICAL ENGINE - 0.2 WVGA	1
5	DLP2010EVM-LC MainBoard DLP016-001	MAIN BOARD	1
6	DLP2010EVM-LC DisplayBoard DLP017-001	DISPLAY BOARD	1
7	92005A116	M3 X 6MM LONG PAN HEAD (McMaster- Carr)	2
8	92005A112	M3 X 4MM LONG PAN HEAD (McMaster-Carr)	8
9	92005A111	M3 X 3MM LONG PAN HEAD (McMaster-Carr)	2
10	92005A002	M1.6 X 3MM LONG PAN HEAD (McMaster-Carr)	2
11	92005A056	M2.5 X 4MM LONG PAN HEAD (McMaster-Carr)	2
12	R30-1000402	M3 X 4MM LONG F/F STANDOFF (HARWIN)	2
13	R30-3000402	M3 X 4 M/F STANDOFF (HARWIN)	3
14	SFE-M1.2-10-A2	M1.2 X 10mm Cheese Head Screws (DIN 84) - A2 Stainless Steel (Accugroup)	2
15	R30-1000802	M3 X 8MM F/F STANDOFF (HARWIN)	3
16	SJ-5003 (BLACK)	BUMPER CYLINDRICAL0.44" DIA BLK (3M)	4
17	5519	OPTICAL ENGINE THERMAL PAD (3M)	1
18	DLP024	LED ADAPTOR BOARD	1
19	2514111_revB	OPTICAL ENGINE FLEX	1
20	050R6-76B	CABLE FLAT FLEX 6POS 0.5MM 3" FOR LED CONNECTIONS (PARLEX)	2



UNLESS OTHERWISE SPECIFIED		DWN STEVE SMITH Engr	DATE 4/23/2018	 TEXAS INSTRUMENTS
<ul style="list-style-type: none"> DIMENSIONS ARE IN MILLIMETERS TOLERANCES: ANGLES ±1° 2 PLACE DECIMALS ±0.25 1 PLACE DECIMALS ±0.50 DIMENSIONAL LIMITS APPLY BEFORE PROCESSES INTERPRET DIMENSIONS IN ACCORDANCE WITH ASME Y14.5M-1994 REMOVE ALL BURRS AND SHARP EDGES PARENTHETICAL INFO FOR REF ONLY 		CQE/QA	CM	
NEXT ASSY	USED ON	Apprvd	SCALE 1:5	DLP LIGHTCRAFTER DISPLAY 2010 EVM SIZE B DWG NO DLP2010EVM-LC Top Assembly RevA REV B
APPLICATION			SHEET 1 OF 2	



8

7

6

5

4

3

1

D

D

C

C

B

B

A

A

8

7

6

5

4

3

2

1

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated