

LM140L/LM340L Series 3-Terminal Positive Regulators

Check for Samples: LM140L, LM340L

FEATURES

- Line Regulation of 0.04%/V
- Load Regulation of 0.01%/mA
- **Output Voltage Tolerances of**
 - $\pm 2\%$ at $T_i = 25$ °C and $\pm 4\%$ Over the **Temperature Range (LM140LA)**
 - ±3% Over the Temperature Range (LM340LA)
- **Output Current of 100 mA**
- **Internal Thermal Overload Protection**
- **Output Transistor Safe Area Protection**
- **Internal Short Circuit Current Limit**
- Available in
 - Metal TO Low Profile Package (LM140LA/LM340LA)
 - Plastic TO-92 (LM340LA)

DESCRIPTION

The LM140L series of three terminal positive regulators is available with several fixed output voltages making them useful in a wide range of applications. The LM140LA is an improved version of the LM78LXX series with a tighter output voltage tolerance (specified over the full military temperature range), higher ripple rejection, better regulation and lower quiescent current. The LM140LA regulators have ±2% V_{OUT} specification, 0.04%/V line regulation, and 0.01%/mA load regulation. When used as a zener diode/resistor combination replacement, the LM140LA usually results in an effective output impedance improvement of two orders of magnitude. and lower quiescent current. These regulators can provide local on card regulation, eliminating the distribution problems associated with single point regulation. The voltages available allow the LM140LA to be used in logic systems, instrumentation, Hi-Fi, and other solid state electronic equipment. Although designed primarily as fixed voltage regulators, these devices can be used with external components to obtain adjustable voltages and currents.

The LM140LA/LM340LA are available in the low profile metal three lead TO (NDT) and the LM340LA are also available in the plastic TO-92 (LP). With adequate heat sinking the regulator can deliver 100 mA output current. Current limiting is included to limit the peak output current to a safe value. Safe area protection for the output transistor is provided to limit power dissipation. If internal power dissipation becomes too high for the heat sinking provided, the thermal shut-down circuit takes over, preventing the IC from overheating.

For applications requiring other voltages, see LM117L Data Sheet.

Output Voltage Options

LM140LA-5.0	5V	LM340LA-5.0	5V
LM140LA-12	12V	LM340LA-12	12V
LM140LA-15	15V	LM340LA-15	15V

Connection Diagrams




Figure 1. TO Metal Can Package (NDT) (Bottom View)




Figure 2. TO-92 Plastic Package (LP) (Bottom View)

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.





These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

Absolute Maximum Ratings (1)(2)(3)

Input Voltage		35V
Internal Power Dissipation ⁽⁴⁾		Internally Limited
Operating Temperature Bongs	LM140LA	−55°C to +125°C
Operating Temperature Range	LM340LA	0°C to +70°C
Maximum Junction Temperature		+150°C
Storage Temperature Bange	Metal Can (NDT package)	−65°C to +150°C
Storage Temperature Range	Molded TO-92	−55°C to +150°C
Load Tamperature (Coldering 10 acc)	Metal Can	+300°C
Lead Temperature (Soldering, 10 sec.)	Plastic TO-92	+230°C

- (1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not ensure specific performance limits.
- (2) A military RETS specification is available upon request. At the time of printing, the LM140LA-5.0, -12, and -15 RETS specifications complied with the Min and Max limits in this table. The LM140LAH-5.0, LM140LAH-12, and LM140LAH-15 may also be procured as Standard Military Drawings.
- (3) If Military/Aerospace specified devices are required, please contact the Texas Instruments Sales Office/ Distributors for availability and specifications.
- (4) Thermal resistance of NDT-package is typically 26°C/W θ_{jC}, 250°C/W θ_{jA} still air, and 94°C/W θ_{jA} 400 lf/min of air. For the LP-package is 60°C/W θ_{jC}, 232°C/W θ_{jA} still air, and 88°C/W θ_{jA} at 400 lf/min of air. The maximum junction temperature shall not exceed 125°C on electrical parameters.

Electrical Characteristics

Test conditions unless otherwise specified. $T_A = -55^{\circ}\text{C}$ to +125°C (LM140LA), $T_A = 0^{\circ}\text{C}$ to +70°C (LM340LA), $I_O = 40$ mA, $C_{IN} = 0.33 \ \mu\text{F}$, $C_O = 0.01 \ \mu\text{F}$.

Output Voltage Option					5.0V			12V						
Input Voltage (unless otherwise noted)					10V			19V			23V			
Symbol	Parameter	(Conditions	Min	Тур	Max	Min	Тур	Max	Min	Min Typ Max			
Vo	Output Voltage	T _j = 25°C		4.9	5	5.1	11.75	12	12.25	14.7	15	15.3		
		LM140LA	$I_0 = 1 - 100 \text{ mA}$	4.8		5.2	11.5		12.5	14.4		15.6		
	Output				(7.2–20))	(14.5–27	·)	((17.6–30	0)	V	
	Voltage Over	LM340LA	$I_0 = 1 - 100 \text{ mA or}$	4.85		5.15	11.65		12.35	14.55		15.45		
	Temp. (1)		$I_O = 1 - 40 \text{ mA}$ and		(7–20)		(14.3–27	·)	((17.5–30	0)		
			$V_{IN} = ()V$											
ΔV_{O}	Line Regulation	$T_j = 25^{\circ}C$	I _O = 40 mA		18	30		30	65		37	70		
			V _{IN} = ()V	(7–25)			(14.2–30)	(17.3–30)	0)			
			I _O = 100 mA		18	30		30	65		37	70	mV	
	V _{IN} = ()V				(7.5–25	5)	(14.5–30)	((17.5–30	0)	IIIV	
	Load $T_j = 25^{\circ}C$ Regulation		$I_0 = 1 - 40 \text{ mA}$		5	20		10	40		12	50		
			$I_0 = 1 - 100 \text{ mA}$		20	40		30	80		35	100		
	Long Term Stability				12			24			30		mV 1000 hrs	
Io	Quiescent	T _i = 25°C			3	4.5		3	4.5		3.1	4.5	A	
	Current	T _j = 125°C				4.2			4.2			4.2	mA	
ΔI_Q	Quiescent	T _j = 25°C	ΔLoad I _O = 1 - 40 mA			0.1			0.1			0.1		
	Current Change		Δ Line $V_{IN} = ()V$			0.5			0.5			0.5	mA	
	- lango				(7.5–25	j)	(14.3–30)		(17.5–30	0)		

(1) The temperature coefficient of V_{OUT} is typically within 0.01% V_O /°C.



Electrical Characteristics (continued)


Test conditions unless otherwise specified. $T_A = -55^{\circ}C$ to +125°C (LM140LA), $T_A = 0^{\circ}C$ to +70°C (LM340LA), $I_O = 40$ mA, $C_{IN} = 0.33 \ \mu F$, $C_O = 0.01 \ \mu F$.

	Output	Voltage Option	5.0V			12V						
ıl	nput Voltage (ı		10V		19V			23V			Units	
Symbol	Symbol Parameter Conditions				Max	Min	Тур	Max	Min	Тур	Max	
V _N	Output Noise Voltage	$T_j = 25^{\circ}C^{(2)}$, f = 10 Hz–10 kHz		40			80			90		μV
ΔV _{IN}	Ripple	f = 120 Hz, V _{IN} = ()V	55	62		47	54		45	52		-ID
ΔVout	Rejection		(7.5–18)			(14.5–25)			(17.5–28.5)			dB
	Input Voltage Required to Maintain Line Regulation	T _j = 25°C, I _O = 40 mA	7			14.2			17.3			V


⁽²⁾ It is recommended that a minimum load capacitor of 0.01 µF be used to limit the high frequency noise bandwidth.



Typical Performance Characteristics







Dropout Voltage





Figure 7.

Maximum Average Power Dissipation (Metal Can Package)








Figure 6.





Submit Documentation Feedback



Typical Performance Characteristics (continued) Ripple Rejection Quiesc











TYPICAL APPLICATIONS



^{*}Required if the regulator is located far from the power supply filter.

Figure 12. Fixed Output Regulator




$$\begin{split} &V_{OUT}=5V+(5V/R1+I_O)~R2\\ &5V/R1=3~I_O~load~regulation~(L,)~[(R1+R2)/R1]~(L,~of~LM140LA-5.0) \end{split}$$

Figure 13. Adjustable Output Regulator

^{**}It is recommended that a minimum load capacitor of 0.01 µF be used to limit the high frequency noise bandwidth.



Equivalent Circuit



SNVS758B -APRIL 1998-REVISED MARCH 2013



REVISION HISTORY

Cł	Changes from Revision A (March 2013) to Revision B							
•	Changed layout of National Data Sheet to TI format							

www.ti.com 7-Oct-2021

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
LM140LAH-12	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-12, LM1 40LAH-12)	Samples
LM140LAH-12/NOPB	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-12, LM1 40LAH-12)	Samples
LM140LAH-15	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-15, LM1 40LAH-15)	Samples
LM140LAH-15/NOPB	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-15, LM1 40LAH-15)	Samples
LM140LAH-5.0	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-5.0, LM 140LAH-5.0)	Samples
LM140LAH-5.0/NOPB	ACTIVE	ТО	NDT	3	500	RoHS & Green	AU	Level-1-NA-UNLIM	-55 to 125	(LM140LAH-5.0, LM 140LAH-5.0)	Samples
LM340LAZ-5.0/LFT4	ACTIVE	TO-92	LP	3	2000	RoHS & Green	Call TI	N / A for Pkg Type		340LA Z-5.0	Samples
LM340LAZ-5.0/NOPB	ACTIVE	TO-92	LP	3	1800	RoHS & Green	Call TI	N / A for Pkg Type	0 to 70	340LA Z-5.0	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.



PACKAGE OPTION ADDENDUM


www.ti.com 7-Oct-2021

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040001-2/F



TO-92 - 5.34 mm max height

TO-92



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.
- 3. Lead dimensions are not controlled within this area.4. Reference JEDEC TO-226, variation AA.
- 5. Shipping method:

 - a. Straight lead option available in bulk pack only.
 b. Formed lead option available in tape and reel or ammo pack.
 - c. Specific products can be offered in limited combinations of shipping medium and lead options.
 - d. Consult product folder for more information on available options.



TO-92





TO-92





IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated