





TAS5825M

ZHCSIC2H - OCTOBER 2019 - REVISED JANUARY 2023

TAS5825M 具有 192kHz 扩展音频处理能力的 4.5V 至 26.4V、38W 立体声、无电 感器、数字输入、闭环 D 类音频放大器

1 特性

// Texas

INSTRUMENTS

- 灵活的音频 I/O:
 - 支持 32kHz、44.1kHz、48kHz、88.2kHz、 96kHz 和 192kHz 采样速率
 - I²S、LJ、RJ 或 TDM
 - 用于音频监控、子通道或回声消除的 SDOUT
 - 支持三线制数字音频接口 (无需 MCLK)
- 高效 D 类运行模式
 - 电源效率高于 90%, R_{DS(on)} 为 90m Ω
 - 低静态电流, PVDD=12V 时小于 20mA
- 支持多路输出配置
 - 1×53W, 1.0 模式 (4Ω, 22V, THD+N=1%)
 - 1×65W, 1.0 模式 (4Ω, 22V, THD+N=10%)
 - 2×30W, 2.0 模式(8Ω, 24V, THD+N=1%)
 - 2×38W, 2.0 模式(8Ω, 24V,
 - THD+N=10%)
- 优异的音频性能:
 - 1W、1kHz、PVDD = 12V 的条件下, THD + N ≤ 0.03%
 - SNR \geq 110dB(A 加权),ICN \leq 35 μ VRMS
- 灵活处理特性
 - 3 频带高级 DRC + AGL, 2 × 15 BQ,
 - 声场定位器 (SFS)、电平计
 - 96kHz、192kHz 处理器采样
 - 动态 EQ、低音增强和扬声器过热/偏移保护
- 灵活的电源配置
 - PVDD: 4.5V 至 26.4V
 - DVDD 和 I/O: 1.8V 或 3.3V
- 出色的集成式自保护功能:
 - 过流错误 (OCE)
 - 逐周期电流限制
 - 过热警告 (OTW)
 - 过热错误 (OTE)
 - 欠压和过压锁定 (UVLO/OVLO)
- 可轻松进行系统集成
 - I²C 软件控制
 - 减小了解决方案尺寸
 - 小型 5 x 5mm 封装
 - 与开环器件相比,所需的无源器件更少
 - 大多数应用都不需要体积较大的电解电容器 或大型电感器

2 应用

- 智能扬声器 (带语音助理)
- 无线、蓝牙扬声器
- DTV、HDTV、UHD 和多功能监控器
- 条形音箱和低音炮、笔记本电脑、PC 扬声器

3 说明

TAS5825M 是一款立体声、高性能闭环 D 类放大器, 具有集成的音频处理器,支持高达 192kHz 的频率。

强大的音频 DSP 内核支持多种先进的音频处理流程, 例如 2×15 BQ、3 频带 DRC、全频带 AGL (自动增益 限制器)、智能放大器算法(过热和偏移保护)、低音 增强、定位器、THD 管理器、PVDD 跟踪和热折返。 TAS5825M 具有 48kHz 或 96kHz 架构,集成的 SRC (采样率转换器)可检测到输入采样率并自动将输入采 样转换为 DSP 目标采样率,从而避免音频伪影。

	器件信息	
器件型号	封装 ⁽¹⁾	封装尺寸(标称值)
TAS5825M	VQFN (32) RHB	5.00mm × 5.00mm

如需了解所有可用封装,请参阅数据表末尾的可订购产品附 (1)录。








Table of Contents

1	特性	. 1
2	应用	. 1
	说明	
4	Revision History	2
	Device Comparison Table	
	Pin Configuration and Functions	
7	Specifications	
	7.1 Absolute Maximum Ratings	
	7.2 ESD Ratings	
	7.3 Recommended Operating Conditions	
	7.4 Thermal Information	6
	7.5 Electrical Characteristics	
	7.6 Timing Requirements	10
	7.7 Typical Characteristics	11
8	Parameter Measurement Information	26
9	Detailed Description	27
	9.1 Overview	27
	9.2 Functional Block Diagram	27

9.3 Feature Description	.28
9.4 Device Functional Modes	.34
9.5 Programming and Control	
9.6 Register Maps	.44
10 Application and Implementation	
10.1 Application Information	
10.2 Typical Applications	. 86
10.3 Power Supply Recommendations	.92
10.4 Layout	. 93
11 Device and Documentation Support	.98
11.1 Device Support	.98
11.2 Receiving Notification of Documentation Updates.	. 98
11.3 支持资源	.98
11.4 Trademarks	. 99
11.5 静电放电警告	.99
11.6 术语表	99
12 Mechanical, Packaging, and Orderable	
Information	. 99

4 Revision History 注:以前版本的页码可能与当前版本的页码不同

Changes from Revision G (July 2020) to Revision H (January 2023)	Page
• 将提到 SPI 的旧术语的所有实例更改为控制器和外设	1
• 将提到 SPI 的旧术语的所有实例更改为 POCI 和 PICO	
Changed figures in <i>Typical Characteristics</i> section	
Changes from Revision F (October 2019) to Revision G (July 2020)	Page
- Changed capacitor values from 0.22 μ F to 0.47 μ F in the <i>Bootstrap Capacitors</i> section	85
Changes from Revision E (October 2019) to Revision F (November 2019)	Page
• 设置了首页格式,从而将特性和应用编排为一列	
Changes from Revision D (December 2018) to Revision E (October 2019)	Page
Added section: Class D Loop Bandwidth and Switching Frequency Setting	
Added NOTE to the Overcurrent Limit (Cycle-By-Cycle) section	
• Added register: SAP_CTRL3 Register (Offset = 35h) [reset = 0x11]	
- Changed capacitor values of C6, C9, C10, and C13 from 0.22 μF to 0.47 μF in \boxtimes 10-1	
Changes from Revision C (September 2018) to Revision D (December 2018)	Page
Added the Thermal Foldback section	
• Added 图 9-14	42
• Added 图 9-15	43
Changed the Inductor Selections section	
Changes from Revision B (August 2018) to Revision C (September 2018)	Page
• Deleted 001: 260K from 表 9-9	



Page

Changes from Revision A (June 2018) to Revision B (August 2018)

• 将器件状态从*预告信息*更改为量产数据......1



5 Device Comparison Table

	DEVICE NAME R _{DS(on)} DSP Audio Process Flows			
TAS5825M 90 m Ω Flexible Audio Process Flows		Flexible Audio Process Flows		
	TAS5805M	180 m Ω	ROM Fixed Process Flows	

6 Pin Configuration and Functions




图 6-1. RHB Package 32-Pin VQFN

表 6-1. Pin Functions Table

PIN TYPE ⁽¹⁾ NAME NO.			DESCRIPTION	
			DESCRIPTION	
DGND	5	Р	Digital ground	
DVDD	6	Р	3.3-V or 1.8-V digital power supply	
VR_DIG	7	Р	Internally regulated 1.5-V digital supply voltage. This pin must not be used to drive external devices	
ADR	8	AI	A table of resistor value (Pull down to GND) decides device I2C address. See $ eq$ 9-5.	
GPIO0	9	DI/O	General-purpose input/output, function of this pin can be programmed by register (Register Address 0x60h and 0x61h). Can be configured to be CMOS output or Open drain output (WARNZ or FAULTZ)	
GPIO1	10	DI/O	General-purpose input/output, function of this pin can be programmed by register (Register Address 0x60h ar x62h). Can be configured to be CMOS output or Open drain output (WARNZ or FAULTZ)	
GPIO2	11	DI/O	General-purpose input/output, function of this pin can be programmed by register (Register Address 0x60h an 0x63h). Can be configured to be CMOS output or Open drain output (WARNZ or FAULTZ)	
LRCLK	12	DI	Word select clock for the digital signal that is active on the serial port's input data line. In I ² S, LJ and RJ, this corresponds to the left channel and right channel boundary. In TDM mode, this corresponds to the frame sync boundary.	
SCLK ⁽²⁾	13	DI	Bit clock for the digital signal that is active on the input data line of the serial data port. Sometimes, this pin also be written as "bit clock (BCLK)"	
SDIN	14	DI	Data line to the serial data port	
SDA	15	DI/O	I2C serial control data interface input/output	
SCL	16	DI	2C serial control clock input	
PDN	17	DI	Power down, active-low. PDN place the amplifier in Shutdown, turn off all internal regulators.	



表 6-1. Pin Functions Table (continued)

PIN		TYPE ⁽¹⁾	DESCRIPTION	
NAME	NO.		DESCRIPTION	
GVDD	18	Р	Gate drive internal regulator output. This pin must not be used to drive external devices	
AVDD	19	Р	Internally regulated 5-V analog supply voltage. This pin must not be used to drive external devices	
AGND	20	Р	Analog ground	
	3	Р		
PVDD	4	Р	- PVDD voltage input	
PVDD	21	Р		
	22	Р		
	25	Р		
PGND	26	Р	Ground reference for power device circuitry. Connect this pin to system ground.	
	31	Р		
	32	Р		
OUT_B+	23	0	Positive pin for differential speaker amplifier output B	
BST_B+	24	Р	Connection point for the OUT_B+ bootstrap capacitor which is used to create a power supply for the high-side gate drive for OUT_B+	
OUT_B-	27	0	Negative pin for differential speaker amplifier output B	
BST_B-	28	Р	Connection point for the OUT_B- bootstrap capacitor which is used to create a power supply for the high-side gate drive for OUT_B-	
BST_A-	29	Р	Connection point for the OUT_A- bootstrap capacitor which is used to create a power supply for the high-side gate drive for OUT_A-	
OUT_A-	30	0	Negative pin for differential speaker amplifier output A	
BST_A+	1	Р	Connection point for the OUT_A+ bootstrap capacitor which is used to create a power supply for the high-side gate drive for OUT_A+	
OUT_A+	2	0	Positive pin for differential speaker amplifier output A	
PowerPAD™		Р	Connect to the system Ground	

(1) AI = Analog input, AO = Analog output, DI = Digital Input, DO = Digital Output, DI/O = Digital Bi-directional (input and output), P = Power, G = Ground (0 V)
(2) Typically written "bit clock (BCLK)" in some audio codecs.

7 Specifications

7.1 Absolute Maximum Ratings

Free-air room temperature 25°C (unless otherwise noted) (1)

		MIN	MAX	UNIT
DVDD	Low-voltage digital supply	- 0.3	3.9	V
PVDD	PVDD supply	- 0.3	30	V
V _{I(DigIn)}	DVDD referenced digital inputs ⁽²⁾	- 0.5	V _{DVDD} + 0.5	V
VI(SPK_OUTxx)	Voltage at speaker output pins	- 0.3	32	V
T _A	Ambient operating temperature,	- 25	85	°C
T _{stg}	Storage temperature	- 40	125	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) DVDD referenced digital pins include: ADR, GPIO0, GPIO1, GPIO2, LRCLK, SCLK, SDIN,, SCL, SDA, PDN

7.2 ESD Ratings

			VALUE	UNIT
V	Electrostatic discharge	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	V
V _(ESD)		Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±500	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

			MIN	NOM	МАХ	UNIT
V _(POWER) Power supply inputs	Power supply inputs	DVDD	1.62		3.63	V
	Power suppry inputs	PVDD	4.5		26.4	
R _{SPK}	Minimum speaker load BTL Mode PBTL Mode	BTL Mode	3.2	4		Ω
		1.6	2		Ω	
L _{OUT}	Minimum inductor value in LC filter under short-circuit condition		1	4.7		μH

7.4 Thermal Information

THERMAL METRIC ⁽¹⁾			TAS5825M VQFN (RHB) 32 PINS		
		JEDEC STANDARD 2-LAYER PCB	JEDEC STANDARD 4-LAYER PCB	TAS5825MEVM-4 4-LAYER PCB	UNIT
R _{0JA}	Junction-to-ambient thermal resistance	N/A	30.0	24.1	°C/W
R ₀ JC(top)	Junction-to-case (top) thermal resistance	N/A	19.1	19.1	°C/W
R _{0 JB}	Junction-to-board thermal resistance	N/A	9.9	9.9	°C/W
ΨJT	Junction-to-top characterization parameter	N/A	0.2	0.9	°C/W
ψ _{JB}	Junction-to-board characterization parameter	N/A	10.5	8.8	°C/W
R ₀ JC(bot)	Junction-to-case (bottom) thermal resistance	N/A	N/A	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.



7.5 Electrical Characteristics

Free-air room temperature 25°C (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP MAX	UNIT
DIGITAL I/O					
ШН	Input logic high current level for DVDD referenced digital input pins	V _{IN(DigIn)} = V _{DVDD}		10	μA
_	Input logic low current level for DVDD referenced digital input pins	V _{IN(DigIn)} = 0 V		- 10	μA
V _{IH(Digin)}	Input logic high threshold for DVDD referenced digital inputs		70%		V _{DVDD}
V _{IL(Digin)}	Input logic low threshold for DVDD referenced digital inputs			30%	V _{DVDD}
V _{OH(Digin)}	Output logic high voltage level	I _{OH} = 4 mA	80%		V _{DVDD}
V _{OL(Digin)}	Output logic low voltage level	$I_{OH} = -4 \text{ mA}$		20%	V _{DVDD}
² C CONTROL	PORT	· · · · · · · · · · · · · · · · · · ·			
C _{L(I2C)}	Allowable load capacitance for each I ² C Line			400	pF
f _{SCL(fast)}	Support SCL frequency	No wait states, fast mode		400	kHz
f _{SCL(slow)}	Support SCL frequency	No wait states, slow mode		100	kHz
SERIAL AUDI	O PORT				
t _{DLY}	Required LRCK/FS to SCLK rising edge delay		5		ns
D _{SCLK}	Allowable SCLK duty cycle		40%	60%	
f _S	Supported input sample rates		32	192	kHz
f _{SCLK}	Supported SCLK frequencies		32	64	f _S
f _{SCLK}	SCLK frequency			24.576	MHz
SPEAKER AM	IPLIFIER (ALL OUTPUT CONFIGUR	ATIONS)			
t _{off}	Turn-off Time	Excluding volume ramp		10	ms
I _{cc}	Quiescent supply current of DVDD	PDN=2V,DVDD=3.3V, Play mode, General Audio Process flow with full DSP running		25.5	mA
I _{CC}	Quiescent supply current of DVDD	PDN = 2 V,DVDD = 3.3 V, Play mode, Smart Amp Process Flows based on 48 kHz or 96 kHz		17.5	mA
I _{cc}	Quiescent supply current of DVDD	PDN = 2 V, DVDD = 3.3 V, Play mode, Audio Process flow with Housekeeping mode, 192 kHz sample rate		24.8	mA
I _{cc}	Quiescent supply current of DVDD	PDN = 2 V, DVDD = 3.3 V, Play mode, Audio Process flow with Housekeeping mode, 96 kHz sample rate		19.3	mA
Icc	Quiescent supply current of DVDD	PDN=2V,DVDD=3.3V, Play mode, Audio Process flow with Housekeeping mode, 48 kHz sample rate		14.8	mA
Icc	Quiescent supply current of DVDD	PDN = 2 V, DVDD = 3.3 V, Sleep mode		0.87	mA
I _{cc}	Quiescent supply current of DVDD	PDN = 2 V, DVDD = 3.3 V, Deep Sleep mode		0.82	mA
lcc	Quiescent supply current of DVDD	PDN = 0.8 V, DVDD = 3.3 V, Shutdown mode		7.4	μΑ
lcc	Quiescent supply current of PVDD	PDN = 2 V, PVDD = 13.5 V, No Load, LC filter = 10 uH + 0.68 uF, Fsw = 384 kHz, Hybrid Modulation, Play Mode		29.5	mA
lcc	Quiescent supply current of PVDD	PDN = 2 V, PVDD = 13.5 V, No Load, LC filter = 22 uH + 0.68 uF, Fsw = 384 kHz, Hybrid Modulation, Play Mode		20.5	mA
I _{cc}	Quiescent supply current of PVDD	PDN = 2 V, PVDD = 13.5 V, No Load, LC filter = 10uH + 0.68 uF, Fsw = 384 kHz, Output Hiz Mode		10.7	mA
I _{cc}	Quiescent supply current of PVDD	PDN = 2 V, PVDD = 13.5 V, No Load, LC filter = 10 uH + 0.68 uF, Fsw = 384 kHz, Sleep Mode		7.26	mA



7.5 Electrical Characteristics (continued)

Free-air room temperature 25°C (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN TYP	MAX	UNIT
I _{CC}	Quiescent supply current of PVDD	PDN = 2 V, PVDD = 13.5 V, No Load, LC filter = 10 uH + 0.68 uF, Fsw = 384 kHz, Deep Sleep Mode	12.01		μΑ
сс	Quiescent supply current of PVDD	PDN = 0.8 V, PVDD = 13.5 V, No Load, LC filter = 10 uH + 0.68 uF,Fsw = 384 kHz, Shutdown Mode	7.8		μΑ
A _{V(SPK_AMP)}	Programmable Gain	Value represents the <i>peak voltage</i> disregarding clipping due to lower PVDD). Measured at 0 dB input (1FS)	4.87	29.5	V
$\Delta A_{V(SPK_AMP)}$	Amplifier gain error	Gain = 29.5 Vp	0.5		dB
f _{SPK_AMP}	Switching frequency of the speaker amplifier		384 768		kHz kHz
R _{DS(on)}	Drain-to-source on resistance of the individual output MOSFETs	FET + Metallization.	90		mΩ
	Over-Current Error Threshold	Any short to supply, ground, or other channels	7.5		А
OCE _{THRES}	Over-Current cycle-by-cycle limit		6.5		А
OVE _{THRES(PVDD}	PVDD over voltage error threshold		28		V
UVE _{THRES(PVDD}	PVDD under voltage error threshold		4.2		V
OTE _{THRES}	Over temperature error threshold		160		°C
OTE _{Hystersis}	Over temperature error hysteresis		10		°C
OTW _{THRES}	Over temperature warning level 1	Read by register 0x73 bit0	112		°C
OTW _{THRES}	Over temperature warning level 2	Read by register 0x73 bit1	122		°C
OTW _{THRES}	Over temperature warning level 3	Read by register 0x73 bit2	134		°C
OTW _{THRES}	Over temperature warning level 4	Read by register 0x73 bit3	146		°C
SPEAKER AMPL	IFIER (STEREO BTL)				
IV _{os} l	Amplifier offset voltage	Measured differentially with zero input data, programmable gain configured with 29.5 Vp gain, V_{PVDD} = 16 V	- 7.5	7.5	mV
	Output Power (Per Channel)	V _{PVDD} = 14.4 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 6 Ω, f = 1 kHz THD+N = 10%	17.8		W
		V_{PVDD} = 14.4 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 6 Ω , f = 1 kHz THD+N = 1%	14.5		W
P _{O(SPK)}		V_{PVDD} = 24 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 8 Ω , f = 1 kHz THD+N = 10% (Instantaneous Output Power)	38		W
		V_{PVDD} = 24 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 8 Ω , f = 1 kHz THD+N = 1% (Continuous Output Power)	30		W
	Total harmonic distortion and	V _{PVDD} = 12 V, SPK_GAIN = 20.9 Vp, LC-filter	0.03%		
THD+N _{SPK}	noise (P _O = 1 W, f = 1 kHz, R _{SPK} = 6 Ω)	V _{PVDD} = 24 V, SPK_GAIN = 29.5 Vp, LC-filter	0.03%		
I _{CN(SPK)}		V_{PVDD} = 12 V, LC-filter, Load = 6 Ω , Hybrid Modulation	32		
CN(SPK)		V_{PVDD} = 12 V, LC-filter, Load = 6 Ω , BD Modulation	40		
I _{CN(SPK)}	 Idle channel noise (A- weighted, AES17) 	V_{PVDD} = 24 V, LC-filter ,Load = 6 Ω , Hybrid Modulation	35		µVrms
I _{CN(SPK)}		V_{PVDD} = 24 V, LC-filter ,Load = 6 Ω , BD Modulation	45		1
DR	Dynamic range	A-Weighted, -60 dBFS method. P _{VDD} = 24 V, SPK_GAIN = 29.5 Vp	111		dB



7.5 Electrical Characteristics (continued)

Free-air room temperature 25°C (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN TY	P MAX	UNIT	
SNR	Signal-to-noise ratio	A-Weighted, referenced to 1% THD+N Output Level, PVDD = 24 V	1'	11	dB	
SINK		A-Weighted, referenced to 1% THD+N Output Level, PVDD = 14.4 V	10	08	dB	
K _{SVR}	Power supply rejection ratio	Injected Noise = 1 kHz, 1 V _{rms} , P _{VDD} = 14.4 V, input audio signal = digital zero	7	72		
Crosstalk _{SPK}	Crosstalk (worst case between left-to-right and right-to-left coupling)	f = 1 kHz	-100		dB	
SPEAKER AMP	LIFIER (MONO PBTL)					
_		V_{PVDD} = 19 V, SPK_GAIN = 29.5 Vp, R_{SPK} = 3 Ω , f = 1 kHz, THD+N = 1%	5	50	W	
	Output Davies	V_{PVDD} = 19 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 3 Ω , f = 1 kHz, THD+N = 10%	6	60	W	
P _{O(SPK)}	Output Power	V_{PVDD} = 22 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 4 Ω , f = 1 kHz, THD+N = 1%	ξ	53	W	
		V_{PVDD} = 22 V, SPK_GAIN = 29.5 Vp, R _{SPK} = 4 Ω , f = 1 kHz, THD+N = 10%	6	5	W	
	Total harmonic distortion and	V_{PVDD} = 19 V, SPK_GAIN = 20.9 Vp, LC-filter R _{SPK} = 3 Ω)	0.03	%		
THD+N _{SPK}	$(P_0 = 1 \text{ W}, \text{ f} = 1 \text{ kHz})$	V_{PVDD} = 24 V, SPK_GAIN = 29.5 Vp, LC-filter R _{SPK} = 4 Ω)	0.03	%		
DR	Dynamic range	A-Weighted, -60 dBFS method, PVDD=19V	10	9	dB	
SNR	Signal-to-noise ratio	A-Weighted, referenced to 1% THD+N Output Level, PVDD = 19 V	10	9	dB	
SNK		A-Weighted, referenced to 1% THD+N Output Level, PVDD = 24 V	1'	11	dB	




7.6 Timing Requirements

		MIN	NOM	MAX	UNIT
Serial Aud	io Port Timing - Target Mode			·	
f _{SCLK}	SCLK frequency	1.024			MHz
t _{SCLK}	SCLK period	40			ns
t _{SCLKL}	SCLK pulse width, low	16			ns
t _{SCLKH}	SCLK pulse width, high	16			ns
t _{SL}	SCLK rising to LRCK/FS edge	8			ns
t _{LS}	LRCK/FS Edge to SCLK rising edge	8			ns
t _{SU}	Data setup time, before SCLK rising edge	8			ns
t _{DH}	Data hold time, after SCLK rising edge	8			ns
t _{DFS}	Data delay time from SCLK falling edge			15	ns
I ² C Bus Ti	ning - Standard				ns
f _{SCL}	SCL clock frequency			100	kHz
t _{BUF}	Bus free time between a STOP and START condition	4.7			μs
t _{LOW}	Low period of the SCL clock	4.7			μs
t _{HI}	High period of the SCL clock	4			μs
t _{RS-SU}	Setup time for (repeated) START condition	4.7			μs
t _{s-HD}	Hold time for (repeated) START condition	4			μs
t _{D-SU}	Data setup time	250			ns
t _{D-HD}	Data hold time	0		900	ns
t _{SCL-R}	Rise time of SCL signal	20 + 0.1C _B		1000	ns
t _{SCL-R1}	Rise time of SCL signal after a repeated START condition and after an acknowledge bit	20 + 0.1C _B		1000	ns
t _{SCL-F}	Fall time of SCL signal	20 + 0.1C _B		1000	ns
t _{SDA-R}	Rise time of SDA signal	20 + 0.1C _B		1000	ns
t _{SDA-F}	Fall time of SDA signal	20 + 0.1C _B		1000	ns
t _{P-SU}	Setup time for STOP condition	4			μs
I ² C Bus Ti	ning - Fast				
f _{SCL}	SCL clock frequency			400	kHz
t _{BUF}	Bus free time between a STOP and START condition	1.3			μs
t _{LOW}	Low period of the SCL clock	1.3			μs
t _{HI}	High period of the SCL clock	600			ns
t _{RS-SU}	Setup time for (repeated)START condition	600			ns
t _{RS-HD}	Hold time for (repeated)START condition	600			ns
t _{D-SU}	Data setup time	100			ns
t _{D-HD}	Data hold time	0		900	ns
t _{SCL-R}	Rise time of SCL signal	20 + 0.1C _B		300	ns
t _{SCL-R1}	Rise time of SCL signal after a repeated START condition and after an acknowledge bit	20 + 0.1C _B		300	ns
t _{SCL-F}	Fall time of SCL signal	20 + 0.1C _B		300	ns
t _{SDA-R}	Rise time of SDA signal	20 + 0.1C _B		300	ns
t _{SDA-F}	Fall time of SDA signal	20 + 0.1C _B		300	ns
t _{P-SU}	Setup time for STOP condition	600			ns
t _{SP}	Pulse width of spike suppressed			50	ns




7.7 Typical Characteristics


7.7.1 Bridge Tied Load (BTL) Configuration Curves with Hybrid Modulation



















7.7.2 Parallel Bridge Tied Load (PBTL) Configuration With Hybrid Modulation


Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 384 kHz, the LC filter used was 10 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see connect method in \ddagger 10.2.5), unless otherwise noted.





7.7.2 Parallel Bridge Tied Load (PBTL) Configuration With Hybrid Modulation (continued)


Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 384 kHz, the LC filter used was 10 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see connect method in \ddagger 10.2.5), unless otherwise noted.







7.7.2 Parallel Bridge Tied Load (PBTL) Configuration With Hybrid Modulation (continued)

Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 384 kHz, the LC filter used was 10 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see connect method in \ddagger 10.2.5), unless otherwise noted.

























7.7.4 Parallel Bridge Tied Load (PBTL) Configuration With BD Modulation


Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 768 kHz, the LC filter used was 4.7 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see details in \ddagger 10.2.5), unless otherwise noted.





7.7.4 Parallel Bridge Tied Load (PBTL) Configuration With BD Modulation (continued)


Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 768 kHz, the LC filter used was 4.7 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see details in \ddagger 10.2.5), unless otherwise noted.





7.7.4 Parallel Bridge Tied Load (PBTL) Configuration With BD Modulation (continued)

Free-air room temperature 25°C (unless otherwise noted) Measurements were made using TAS5825MEVM board and Audio Precision System 2722 with Analog Analyzer filter set to 20-kHz brickwall filter. All measurements taken with audio frequency set to 1 kHz and device PWM frequency set to 768 kHz, the LC filter used was 4.7 μ H / 0.68 μ F (Pre-Filter PBTL, the merging of the two output channels in this device can be done before the inductor portion of the output filter, see details in \ddagger 10.2.5), unless otherwise noted.



8 Parameter Measurement Information




图 8-1. Serial Audio Port Timing in Target Mode




图 8-2. I²C Communication Port Timing Diagram



9 Detailed Description


9.1 Overview

The TAS5825M device combines 4 main building blocks into a single cohesive device that maximizes sound quality, flexibility, and ease of use. The 4 main building blocks are listed as follows:

- A stereo digital to PWM modulator.
- An Audio DSP subsystem.
- A flexible close-loop amplifier capable of operating in stereo or mono, at several different switching frequencies, and with a variety of output voltages and loads.
- An I²C control port for communication with the device

The device requires only two power supplies for proper operation. A DVDD supply is required to power the low voltage digital circuitry. Another supply, called PVDD, is required to provide power to the output stage of the audio amplifier. Two internal LDOs convert PVDD to 5 V for GVDD and AVDD and to 1.5V for DVDD respectively.

9.2 Functional Block Diagram





9.3 Feature Description

9.3.1 Power Supplies

For system design, TAS5825M needs a 3.3-V or 1.8-V supply in addition to the (typical) 12 V or 24 V powerstage supply. Two internal voltage regulators provide good voltage levels for the gate drive circuitry and internal circuitry. The external pins are provided only as a connection point for off-chip bypass capacitors to filter the supply. Connecting external circuitry to these regulator outputs can result in reduced performance and damage to the device. Additionally, all circuitry requiring a floating voltage supply, that is, the high-side gate drive, is accommodated by built-in bootstrap circuitry requiring only a few external capacitors. To provide good electrical and acoustical characteristics, the PWM signal path for the output stage is designed as identical, independent half-bridges. For this reason, each half-bridge has separate bootstrap pins (BST_x). The gate drive voltages (GVDD) are derived from the PVDD voltage. Special attention needs to be paid to placing all decoupling capacitors as close to their associated pins as possible. In general, inductance between the power-supply pins and decoupling capacitors must be avoided. For a properly functioning bootstrap circuit, a small ceramic capacitor must be connected from each bootstrap pin (BST x) to the power-stage output pin (OUT x). When the power-stage output is low, the bootstrap capacitor is charged through an internal diode connected between the gate-drive regulator output pin (GVDD) and the bootstrap pin. When the power-stage output is high, the bootstrap capacitor potential is shifted above the output potential and thus provides a good voltage supply for the high-side gate driver.

9.3.2 Device Clocking

The TAS5825M devices have flexible systems for clocking. Internally, the device requires a number of clocks, mostly at related clock rates to function correctly. All of these clocks can be derived from the Serial Audio Interface.




图 9-1. Audio Flow with Respective Clocks

图 9-1 shows the basic data flow and clock Distribution.

The Serial Audio Interface typically has 3 connection pins which are listed as follows:

- SCLK (Bit Clock)
- LRCLK/FS (Left/Right Word Clock or Frame Sync)
- SDIN (Input Data)

The device has an internal PLL that is used to take SCLK and create the higher rate clocks required by the DSP and the DAC clock.

The TAS5825M device has an audio sampling rate detection circuit that automatically senses which frequency the sampling rate is operating. Common audio sampling frequencies of 32 kHz, 44.1kHz - 48 kHz, 88.2 kHz - 96 kHz, 176.4 kHz - 192 kHz are supported. The sampling frequency detector sets the clock for DAC and DSP automatically.

If the input LRCLK/SCLK stopped during music playing, the TAS5825M DSP switches to sleep state and waiting for the clock recovery (Class D output switches to Hiz automatically), once LRCLK/SCLK recovered, TAS5825M auto recovers to the play mode. There is no need to reload the DSP code.



9.3.3 Serial Audio Port - Clock Rates

The serial audio interface port is a 3-wire serial port with the signals LRCLK/FS, SCLK, and SDIN. SCLK is the serial audio bit clock, used to clock the serial data present on SDIN into the serial shift register of the audio interface. Serial data is clocked into the TAS5825M device with SCLK. The LRCLK/FS pin is the serial audio left/ right word clock or frame sync when the device is operated in TDM Mode.

······································							
FORMAT	FORMAT DATA BITS		SCLK RATE (f _S)				
I ² S/LJ/RJ	32, 24, 20, 16	32 to 192	64, 32				
	32, 24, 20, 16	32	128				
TDM		44.1,48	128,256,512				
TDM		96	128,256				
		192	128				

表 9-1. Audio Data Formats, Bit Depths and Clock Rates

When Clock halt, non-supported SCLK to LRCLK(FS) ratio is detected, the device reports Clock Error in Register 113 (Register Address 0x71).

9.3.4 Clock Halt Auto-Recovery


Some of host processor halts the I²S clock when there is no audio playing. When Clock halt, the device puts all channels into the Hi-Z state and reports Clock Error in Register 113 (Register Address 0x71). After the audio clock recovery, the device automatically returns to the previous state.

9.3.5 Sample Rate on the Fly Change

TAS5825M supports LRCLK(FS) rate on the fly change. For example, change LCRLK from 32kHz to 48kHz or 96kHz or 192kHz, Host processor needs to put the LRCLK(FS)/SCLK to Halt state at least 100us before changing to the new sample rate.

9.3.6 Serial Audio Port - Data Formats and Bit Depths


The device supports industry-standard audio data formats, including standard I2S, left-justified, right-justified and TDM/DSP data. Data formats are selected via Register (Register Address 0x33h -D[5:4]). If the high width of LRCLK/FS in TDM/DSP mode is less than 8 cycles of SCK, then the register (Register Address 0x33h -D[3:2]) sets to 01. All formats require binary two's complement, MSB-first audio data; up to 32-bit audio data is accepted. All the data formats, word length and clock rate supported by this device are shown in Table 1. The data formats are detailed in [8] 9-2 through [8] 9-6. The word length are selected via Register (Register Address 0x33h -D[7]) and Register (Register Address 0x34h -D[7:0]). Default setting is I2S and 24 bit word length.



I²S Data Format; L-channel = LOW, R-channel = HIGH


图 9-3. I²S Audio Data Format






Right-Justified Data Format; L-channel = HIGH, R-channel = LOW


Right Justified Data Format; L-channel = HIGH, R-channel = LOW





In TDM Modes, Duty Cycle of LRCK/FS must be 1x SCLK at minimum. Rising edge is considered frame start.

图 9-5. TDM 1 Audio Data Format



TDM Data Format with OFFSET = 1

In TDM Modes, Duty Cycle of LRCK/FS must be 1x SCLK at minimum. Rising edge is considered frame start.

图 9-6. TDM 2 Audio Data Format

9.3.7 Digital Audio Processing

TAS5825M DSP has flexible process flows which support Multi-Band DRC, Post AGL,FIR filter, 2*15 BQs, Spatializer (stereo widening),Dynamic Biquad, Smart Speaker Excursion control, Smart Thermal and Smart Bass Control for different applications, refer to application note: TAS5825M Process Flows for details.

Based on integrated PVDD sense ADC and 4 level temperature sensor, TAS5825M DSP also support PVDD tracking(Dynamic Headroom tracking),advanced thermal foldback and Hybrid modulation(Low power dissipation to extend battery life time), refer to application note:TAS5825M Advanced Features.

9.3.8 Class D Audio Amplifier

Following the digital clipper, the interpolated audio data is next sent to the Closed Loop Class-D amplifier, and the first stage is Digital to PWM Conversion (DPC) block. In this block, the stereo audio data is translated into two pairs of complimentary pulse width modulated (PWM) signals which are used to drive the outputs of the speaker amplifier. Feedback loops around the DPC provide for constant gain across supply voltages, reduce distortion, and increase immunity to power supply injected noise and distortion. The analog gain is also applied in the Class-D amplifier section of the device. The gain structures are discussed in detail below for both [8] 9-7 and $\frac{1}{5}$ 9-2. The switching rate of the amplifier is configurable by register (Register Address 0x02h -D[6:4])

9.3.8.1 Speaker Amplifier Gain Select

A combination of digital gain and analog gain is used to provide the overall gain of the speaker amplifier. As seen in 🕅 9-7, the audio path of the TAS5825M consists of a digital audio input port, a digital audio path, a digital to PWM converter (DPC), a gate driver stage, a Class D power stage, and a feedback loop which feeds the output information back into the DPC block to correct for distortion sensed on the output pins. The total amplifier gain is comprised of digital gain, shown in the digital audio path and the analog gain from the input of the analog modulator to the output of the speaker amplifier power stage.






图 9-7. Speaker Amplifier Gain

As shown in [8] 9-7, the first gain stage for the speaker amplifier is present in the digital audio path. The first gain stage consists of the volume control and the digital boost block. The volume control is set to 0 dB by default and does not change. For all settings of the register 0x54, AGAIN[4:0], the digital boost block remains at 0 dB. These gain settings make sure that the output signal is not clipping at different PVDD levels. 0dBFS output is 29.5-V peak output voltage

表 9-2.	Analog	Gain	Setting
--------	--------	------	---------

AGAIN <4:0>	GAIN (dBFS)	AMPLIFIER OUTPUT PEAK VOLTAGE (V)	
00000	0	29.5	
00001	-0.5	27.85	
·····.	······	·····.	
11111	-15.5	4.95	

9.3.8.2 Class D Loop Bandwidth and Switching Frequency Setting

TAS5825M closed loop structure provides Loop bandwidth setting option (Setting by register 83 -Register address 0x53h-D[6-5]) to co-work with different switching frequency (Setting by register 2 -Register address 0x02h-D[6-4]). $\gtrsim 9-3$ shows recommended settings for the Loop Bandwidth and Switching Frequency selection. Same Fsw, Better THD+N performance with higher BW.

Modulation Scheme	Fsw	BW (Loop Band Width)	Notes			
	384 kHz	80 kHz				
Hybrid, 1SPW	480 kHz	80 kHz, 100 kHz	Principle: Fsw (Switching Frequency) \ge 4.2 × Loop			
Hybrid, 13FVV	576 kHz	80 kHz, 100 kHz, 120 kHz	Bandwidth			
	768 kHz	80 kHz, 100 kHz, 120 kHz, 175 kHz				
	384 kHz	80 kHz, 100 kHz, 120 kHz				
BD	480 kHz	80 kHz, 100 kHz, 120 kHz	Principle: Fsw (Switching Frequency) \geq 3 × Loop			
עם	576 kHz	80 kHz, 100 kHz, 120 kHz, 175 kHz	Bandwidth			
	768 kHz	80 kHz, 100 kHz, 120 kHz, 175 kHz				

表 9-3. Loop Bandwidth and Switching Frequency Setting



9.4 Device Functional Modes

9.4.1 Software Control

The TAS5825M device is configured via an I² C communication port.

The I2C Communication Protocol is detailed in the I²C Communication Port section. The I²C timing requirements are described in the I²C Bus Timing – Standard and I²C Bus Timing – Fast sections.

There are two methods to program TAS5825M DSP memory.

- Loading with I²C Communication Port by host processor. This method is recommend for most of applications.
- Fast loading from external EEPROM with SPI communication Port. This method can be used in some applications which need fast loading to save initialization time or release the Host Controller's loading. TAS5825M supports to load the DSP memory data from external EEPROM via SPI. The GPIOs can be configured as SI,SO and SCK for EEPROM via Register (0x60,0x61,0x62,0x63,0x64). The chip selection CS of EEPROM is controlled by the Host Processor. See AppNote: Load TAS5825M Configurations from EEPROM via SPI.

9.4.2 Speaker Amplifier Operating Modes

The TAS5825M device can be used with two different amplifier configurations, can be configured by Register 0x02h -D[2]:

- BTL Mode
- PBTL Mode

9.4.2.1 BTL Mode

In BTL mode, the TAS5825M amplifies two independent signals, which represent the left and right portions of a stereo signal. The amplified left signal is presented on differential output pair shown as OUT_A+ and OUT_A-, the amplified right signal is presented on differential output pair shown as OUT_B+ and OUT_B-.

9.4.2.2 PBTL Mode

The PBTL mode of operation is used to describe operation in which the two outputs of the device are placed in parallel with one another to increase the power sourcing capabilities of the device. On the output side of the TAS5825M device, the summation of the devices can be done before the filter in a configuration called Pre-Filter Parallel Bridge Tied Load (PBTL). However, the two outputs can be required to merge together after the inductor portion of the output filter. Doing so does require two additional inductors, but allows smaller, less expensive inductors to be used because the current is divided between the two inductors. The process is called Post-Filter PBTL. On the input side of the TAS5825M device, the input signal to the PBTL amplifier is left frame of I2S or TDM data.

9.4.3 Low EMI Modes

TAS5825M employs several modes to minimize EMI during playing audio, and can be used based on different applications.

9.4.3.1 Spread Spectrum

Spread spectrum is used in some inductor free cases to minimize EMI noise. The TAS5825M supports Spread Spectrum with triangle mode.

User needs to configure register SS_CTRL0 (0x6B) to enable triangle mode and enable spread spectrum, select spread spectrum frequency and range with SS_CTRL1 (0x6C). For 384 kHz F_{SW} , which is configured by DEVICE_CTRL1 (0x02), the spread spectrum frequency and range are described in $\gtrsim 9-4$.

SS_TRI_CTRL[3:0]	0	1	2	3	4	5	6	7
Triangle Freq	24k				48k			
Spread Spectrum Range	5%	10%	20%	25%	5%	10%	20%	25%

表 9-4. Triangle Mode Spread Spectrum Frequency and Range Selection

User Application example: Central Switching Frequency is 384 kHz, Triangle Frequency is 24 kHz.

Register 0x6b = 0x03 // Enable Spread Spectrum

Register 0x6c = 0x03 // SS_CTRL[3:0]=0011, Triangle Frequency = 24 kHz, Spread Spectrum Range must be 25% (336 kHz through 432 kHz)

9.4.3.2 Channel to Channel Phase Shift

This device supports channel to channel 180-degree PWM phase shift to minimize the EMI. Bit 0 of Register 0x53 can be used to disable or enable the phase shift.

9.4.3.3 Multi-Devices PWM Phase Synchronization

TAS5825M support up to 4 phases selection for the multi devices application system. For example, when a system integrated 4 TAS5825MM devices, user can select phase0/1/2/3 for each device by register PHASE_CTRL(0x6A), which means there is a 45 degree phase shift between each device to minimize the EMI.

There are two methods for Multi-Device PWM phase synchronization. Phase Synchronization With I²S Clock In Startup Phase or Phase Synchronization With GPIO.

9.4.3.3.1 Phase Synchronization With I²S Clock In Startup Phase

- 1. Step 1: Halt I²S clock.
- Step 2: Configure each device phase selection and enable the phase synchronization. For example: Register 0x6A=0x03 for device 0; Register 0x6A=0x07 for device 1; Register 0x6A=0x0B for device 2; Register 0x6A=0x0F for device 3.
- 3. Step 3: Configure each device into HIZ mode.
- 4. Step 4: Provide I²S to each device. Phase synchronization for all 4 devices is automatically done by internal sequence.
- 5. Step 5: Initialize the DSP code (This step can be skipped if only need to do the Phase Synchronization).
- 6. Step 6: Device to Device PWM phase shift must be fixed with 45 degree.

9.4.3.3.2 Phase Synchronization With GPIO

- 1. Step 1: Connect GPIOx pin of each device to SOC's GPIO pin on PCB.
- 2. Step 2: Configure each device GPIOx as phase sync input usage by registers GPIO_CTRL (0X60) and GPIO_INPUT_SEL (0x64).
- 3. Step 3: Select different phase for each device and enable phase synchronization by register PHASE_CTRL (0x6A).
- 4. Step 4: Configure each device into PLAY mode by register DEVICE_CTRL2 (0x03) and monitor the POWER_STATE register (0x68) until device changed to HIZ state.
- 5. Step 5: Give a 0 to 1 toggle on SOC GPIO. Then all 4 devices enter into PLAY mode and device to Device PWM phase shift must be fixed with 45 degrees.
- 6. Step 6: Phase Synchronization has been finished. Configure the GPIOx pin to other function based on the application.

9.4.4 Thermal Foldback

The Thermal Foldback (TFB), is designed to protect TAS5825M from excessive die temperature increases, in case the device operates beyond the recommended temperature/power limit, or with a weaker thermal system design than recommended. The TFB allows the TAS5825M to play as loud as possible without triggering unexpected thermal shutdown. When the die temperature triggers the over-temperature warning (OTW) level, (TAS5825M has four different temperature threshold, each threshold is indicated in I²C register 0x73 bits 0,1,2 and 3), an internal AGL (Automatic Gain Limiter) reduces the digital gain gradually, lower value of OTW, smaller



attenuation added, with the OTW warning goes higher, more attenuation added. Once the die temperature drops below the OTW, the device's digital gain gradually returns to the former setting. Both the attenuation gain and adjustable rate are programmable. The TFB gain regulation speed (attack rate and release rate) settings are the same as a regular AGL, which is also configurable with TAS5825M App in PurePathTM Console3.

9.4.5 Device State Control

Except Shutdown Mode, TAS5825M has other 4 states for different power dissipation which listed in # 7.5.

- Deep Sleep Mode. Register 0x03h -D[1:0]=00, Device stays in Deep Sleep Mode. In this mode, I² C block keep works. This mode can be used to extend the battery life time in some portable speaker application case, once the host processor stopped playing audio for a long time, TAS5825M can be set to Deep Sleep Mode to minimize power dissipation until host processor start playing audio again. Device returns back to Play Mode by setting Register 0x03h -D[1:0] to 11. Compare with Shutdown Mode (Pull PDN Low), enter or exit Deep Sleep Mode, DSP keeps active.
- Sleep Mode. Register 0x03h -D[1:0]=01, Device stays in Sleep Mode. In this mode, I² C block, Digital core, DSP Memory, 5 V Analog LDO keep works. Compare with Shutdown Mode (Pull PDN Low), enter or exit Sleep Mode, DSP keeps active.
- Output Hiz Mode. Register 0x03h -D[1:0]=10, Device stays in Hiz Mode. In this mode, Only output driver set to be Hiz state, all other block work normally.
- Play Mode. Register 0x03h -D[1:0]=11, Device stays in Play Mode.


9.4.6 Device Modulation

TAS5825M has 3 modulation schemes: BD modulation, 1SPW modulation and Hybrid modulation. Select modulation schemes for TAS5825M with Register 0x02 [1:0]-DAMP_MOD.

9.4.6.1 BD Modulation

This is a modulation scheme that allows operation without the classic LC reconstruction filter when the amp is driving an inductive load with short speaker wires. Each output is switching from 0 volts to the supply voltage. The OUTPx and OUTNx are in phase with each other with no input so that there is little or no current in the speaker. The duty cycle of OUTPx is greater than 50% and OUTNx is less than 50% for positive output voltages. The duty cycle of OUTPx is less than 50% and OUTNx is greater than 50% for negative output voltages. The voltage across the load sits at 0 V throughout most of the switching period, reducing the switching current, which reduces any I^2R losses in the load.





9.4.6.2 1SPW Modulation

The 1SPW mode alters the normal modulation scheme to achieve higher efficiency with a slight penalty in THD degradation and more attention required in the output filter selection. In Low Idle Current mode, the outputs operate at approximately 17% modulation during idle conditions. When an audio signal is applied, one output decreases and one increases. The decreasing output signal rails to GND. At this point all the audio modulation takes place through the rising output. The result is that only one output is switching during a majority of the audio cycle. Efficiency is improved in this mode due to the reduction of switching losses.






图 9-9. 1SPW Mode Modulation

9.4.6.3 Hybrid Modulation

Hybrid Modulation is designed for minimized power loss without compromising the THD+N performance, and is optimized for battery-powered applications. With Hybrid modulation, TAS5825M detects the input signal level and adjust PWM duty cycle dynamically based on PVDD. Hybrid modulation achieves ultra low idle current and maintains the same audio performance level as the BD Modulation.

备注

As Hybrid Modulation need the internal DSP to detect the input signal level and adjust PWM duty cycle dynamically. To use the Hybrid Modulation, users need to select the corresponding process flows which support Hybrid Modulation in TAS5825M PPC3 App. Look intoTAS5825M PPC3 App for more information about TAS5825M flexible audio process flows.



9.5 Programming and Control

9.5.1 I² C Serial Communication Bus

The device has a bidirectional serial control interface that is compatible with I²C bus protocol and supports 100 and 400-kHz data transfer rates for random and sequential write and read operations as a target device. Because the TAS5825M register map and DSP memory spans multi pages, the user must change from page to page before writing individual register or DSP memory. Changing from page to page is accomplished via register 0 on each page. This register value selects the page address, from 0 to 255. All registers are listed in the TAS5825M data sheet and is in Page 0.

9.5.2 I² C Target Address

The TAS5825M device has 7 bits for the target address. The first five bits (MSBs) of the target address are factory preset to 10011(0x9x). The next two bits of address byte are the device select bits which can be user-defined by ADR pin in $\frac{1}{2}$ 9-5.

ADR PIN Configuration			MSBs	User Define	LSB			
0 Ω to GND	1	0	0	1	1	0	0	R/ W
1 kΩ to GND	1	0	0	1	1	0	1	R/ W
4.7 k Ω to GND	1	0	0	1	1	1	0	R/ W
15 kΩ to GND	1	0	0	1	1	1	1	R/ W

表 9-5. I² C Target Address Configuration

9.5.2.1 Random Write

As shown in [8] 9-10, a single-byte data-write transfer begins with the controller device transmitting a start condition followed by the I²C device address and the read/write bit. The read/write bit determines the direction of the data transfer. For a write data transfer, the read/write bit is a 0. After receiving the correct I²C device address and the read/write bit. Next, the controller transmits the address byte corresponding to the internal memory address being accessed. After receiving the data byte, the device again responds with an acknowledge bit. Next, the controller data byte to be written to the memory address being accessed. After receiving the data byte to be written to the memory address being accessed. After receiving the data byte, the device again responds with an acknowledge bit. Finally, the controller device transmits a stop condition to complete the single-byte data-write transfer.





图 9-10. Random Write Transfer

9.5.2.2 Sequential Write

A sequential data-write transfer is identical to a single-byte data-write transfer except that multiple data bytes are transmitted by the controller to the device as shown in [a] 9-11. After receiving each data byte, the device responds with an acknowledge bit and the l² subaddress is automatically incremented by one.







9.5.2.3 Random Read

As shown in \mathbb{R} 9-12, a single-byte data-read transfer begins with the controller device transmitting a start condition followed by the I²C device address and the read/write bit. For the data-read transfer, both a write followed by a read are actually done. Initially, a write is done to transfer the address byte of the internal memory address to be read. As a result, the read/write bit is a 0. After receiving the address and the read/write bit, the device responds with an acknowledge bit. In addition, after sending the internal memory address byte, the controller device transmits another start condition followed by the address and the read/write bit again. This time the read/write bit is a 1, indicating a read transfer. After receiving the address and the read/write bit, the device again responds with an acknowledge bit. Next, the device transmits the data byte from the memory address being read. After receiving the data byte, the controller device transmits a not-acknowledge followed by a stop condition to complete the single-byte data-read transfer.




图 9-12. Random Read Transfer

9.5.2.4 Sequential Read

A sequential data-read transfer is identical to a single-byte data-read transfer except that multiple data bytes are transmitted by the device to the controller device as shown in [a] 9-13. Except for the last data byte, the controller device responds with an acknowledge bit after receiving each data byte and automatically increments the I²C sub address by one. After receiving the last data byte, the controller device transmits a not-acknowledge followed by a stop condition to complete the transfer.




图 9-13. Sequential Read Transfer



9.5.2.5 DSP Memory Book, Page and BQ update

On Page 0x00 of each book, Register 0x7f is used to change the book. Register 0x00 of each page is used to change the page. To change a Page first write 0x00 to Register 0x00 to switch to Page 0 then write the book number to Register 0x7f on Page 0. To switch between pages in a book, simply write the page number to register 0x00.

All the Biquad Filters coefficients are addressed in book 0xAA. The five coefficients of every Biquad Filter must be written entirely and sequentially from the lowest address to the highest address. The address of all Biquad Filters can be found in \ddagger 9.6.

All DSP/Audio Process Flow Related Register are listed in Application Note, TAS5825M Process Flows.

9.5.2.6 Checksum

This device supports two different check sum schemes, a cyclic redundancy check (CRC) checksum, and an Exclusive (XOR) checksum. Register reads do not change checksum, but writes so that even nonexistent registers change the checksum. Both checksums are 8-bit checksums and both are available together simultaneously. The checksums can be reset by writing a starting value (eg. 0x 00 00 00 00) to their respective 4-byte register locations.

9.5.2.6.1 Cyclic Redundancy Check (CRC) Checksum

The 8-bit CRC checksum used is the 0x7 polynomial (CRC-8-CCITT I.432.1; ATM HEC, ISDN HEC and cell delineation, (1 + x1 + x2 + x8)). A major advantage of the CRC checksum is that the input order is sensitive. The CRC supports all I²C transactions, excluding book and page switching. The CRC checksum is read from register 0x7E on page0 of any book (B_x, Page_0, Reg_126). The CRC checksum can be reset by writing 0x00 to the same register locations where the CRC checksum is valid.

9.5.2.6.2 Exclusive or (XOR) Checksum

The XOR Checksum is a simpler checksum scheme. The scheme performs sequential XOR of each register byte write with the previous 8-bit checksum register value. XOR supports only Book 0x8C, and excludes page switching and all registers in Page 0x00 of Book 0x8C. XOR checksum is read from location register 0x7D on page 0x00 of book 0x8C (B_140, Page_0, Reg_125). The XOR Checksum can be reset by writing 0x00 to the same register location where the XOR Checksum is read.



9.5.3 Control via Software

- Startup Procedures
- Shutdown Procedures

9.5.3.1 Startup Procedures

- 1. Configure ADR pin with proper setting for I²C device address.
- 2. Bring up power supplies (it does not matter if PVDD or DVDD comes up first).
- 3. Once power supplies are stable, bring up PDN to High and wait 5 ms at least, then start SCLK, LRCLK.
- 4. Once I²S clock are stable, set the device into HiZ state and enable DSP via the I²C control port.
- 5. Wait 5 ms at least. Then initialize the DSP Coefficient, then set the device to Play state.
- 6. The device is now in normal operation.





图 9-14. Start-Up Sequence



9.5.3.2 Shutdown Procedures

- 1. The device is in normal operation.
- 2. Configure the Register 0x03h -D[1:0]=10 (Hiz) via the I²C control port or Pull PDN low.
- 3. Wait at least 6 ms (this time depends on the LRCLK rate ,digital volume and digital volume ramp down rate).
- 4. Bring down power supplies.
- 5. The device is now fully shutdown and powered off.



- Before PVDD/DVDD power down, Class D Output driver needs to be disabled by \overline{PDN} or by l^2C .
- At least 6ms delay needed based on LRCLK (Fs) = 48kHz, Digital volume ramp down update every sample period, decreased by 0.5dB for each update, digital volume =24dB. Change the value of register 0x4C and 0x4E or change the LRCLK rate, the delay changes.

图 9-15. Power-Down Sequence

9.5.3.3 Protection and Monitoring

9.5.3.3.1 Overcurrent Limit (Cycle-By-Cycle)

The CBC current-limiting circuit terminates each PWM pulse limit the output current flow to the average current limit (I_{LIM}) threshold. The overall effect on the audio in the case of a current overload is quite similar a voltage-clipping event, temporarily limiting power at the peaks of the music signal and normal operation continues without disruption on removal of the overload.

备注

CBC (Cycle-By-Cycle) current-limiting only allows in BTL mode, not allowed under PBTL.

9.5.3.3.2 Overcurrent Shutdown (OCSD)

Under severe short-circuit event, such as a short to PVDD or ground, the device uses a peak-current detector, and the affected channel shuts down in < 100 ns if the peak current are enough. The shutdown speed depends on a number of factors, such as the impedance of the short circuit, supply voltage, and switching frequency. The user can restart the affected channel via l^2C . An OCSD event activates the fault pin, and the l^2 fault register saves a record. If the supply or ground short is strong enough to exceed the peak current threshold but not severe enough to trigger the OCSD, the peak current limiter prevents excess current from damaging the output FETs, and operation returns to normal after the short is removed.

9.5.3.3.3 DC Detect

If the TAS5825M device measures a DC offset in the output voltage, the FAULTZ line is pulled low and the OUTxx outputs transition to high impedance, signifying a fault.



9.6 Register Maps

9.6.1 CONTROL PORT Registers

Offset	Acronym	Register Name	Section
1h	RESET_CTRL	Register 1	节 9.6.1.2
2h	DEVICE CTRL 1	Register 2	节 9.6.1.3
3h	DEVICE CTRL2	Register 3	节 9.6.1.4
Fh	 I2C_PAGE_AUTO_INC	Register 15	节 9.6.1.5
28h	SIG_CH_CTRL	Register 40	节 9.6.1.6
29h	CLOCK_DET_CTRL	Register 41	节 9.6.1.7
30h	SDOUT_SEL	Register 48	节 9.6.1.8
31h	I2S_CTRL	Register 49	节 9.6.1.9
33h	SAP_CTRL1	Register 51	节 9.6.1.10
34h	SAP_CTRL2	Register 52	节 9.6.1.11
35h	SAP_CTRL3	Register 53	节 9.6.1.12
37h	FS_MON	Register 55	节 9.6.1.13
38h	BCK (SCLK)_MON	Register 56	节 9.6.1.14
39h	CLKDET_STATUS	Register 57	节 9.6.1.15
40h	DSP_PGM_MODE	Register 64	节 9.6.1.16
46h	DSP_CTRL	Register 70	节 9.6.1.17
4Ch	DIG_VOL	Register 76	节 9.6.1.18
4Eh	DIG_VOL_CTRL1	Register 78	节 9.6.1.19
4Fh	DIG_VOL_CTRL2	Register 79	节 9.6.1.20
50h	AUTO_MUTE_CTRL	Register 80	节 9.6.1.21
51h	AUTO_MUTE_TIME	Register 81	节 9.6.1.22
53h	ANA_CTRL	Register 83	节 9.6.1.23
54h	AGAIN	Register 84	节 9.6.1.24
55h	SPI_CLK	Register 85	节 9.6.1.25
56h	EEPROM_CTRL0	Register 86	节 9.6.1.26
57h	EEPROM_RD_CMD	Register 87	节 9.6.1.27
58h	EEPROM_ADDR_START0	Register 88	节 9.6.1.28
59h	EEPROM_ADDR_START1	Register 89	节 9.6.1.29
5Ah	EEPROM_ADDR_START2	Register 90	节 9.6.1.30
5Bh	EEPROM_BOOT_STATUS	Register 91	节 9.6.1.31
5Ch	BQ_WR_CTRL1	Register 92	节 9.6.1.32
5Eh	PVDD_ADC	Register 94	节 9.6.1.33
60h	GPIO_CTRL	Register 96	节 9.6.1.34
61h	GPIO0_SEL	Register 97	节 9.6.1.35
62h	GPIO1_SEL	Register 98	节 9.6.1.36
63h	GPIO2_SEL	Register 99	节 9.6.1.37
64h	GPIO_INPUT_SEL	Register 100	节 9.6.1.38
65h	GPIO_OUT	Register 101	节 9.6.1.39



Offset	Acronym	Register Name	Section
66h	GPIO_OUT_INV	Register 102	节 9.6.1.40
67h	DIE_ID	Register 103	节 9.6.1.41
68h	POWER_STATE	Register 104	节 9.6.1.42
69h	AUTOMUTE_STATE	Register 105	节 9.6.1.43
6Ah	PHASE_CTRL	Register 106	节 9.6.1.44
6Bh	SS_CTRL0	Register 107	节 9.6.1.45
6Ch	SS_CTRL1	Register 108	节 9.6.1.46
6Dh	SS_CTRL2	Register 109	节 9.6.1.47
6Eh	SS_CTRL3	Register 110	节 9.6.1.48
6Fh	SS_CTRL4	Register 111	节 9.6.1.49
70h	CHAN_FAULT	Register 112	节 9.6.1.50
71h	GLOBAL_FAULT1	Register 113	节 9.6.1.51
72h	GLOBAL_FAULT2	Register 114	节 9.6.1.52
73h	WARNING	Register 115	节 9.6.1.53
74h	PIN_CONTROL1	Register 116	节 9.6.1.54
75h	PIN_CONTROL2	Register 117	节 9.6.1.55
76h	MISC_CONTROL	Register 118	节 9.6.1.56
77h	CBC_CONTROL	Register 119	节 9.6.1.57
78h	FAULT_CLEAR	Register 120	节 9.6.1.58

Complex bit access types are encoded to fit into small table cells. 表 9-7 shows the codes that are used for access types in this section.

Access Type	Code	Description						
Read Type								
R	R Read							
Write Type								
W	W	Write						
Reset or Default	Value	-						
-n		Value after reset or the default value						

表 9-7. CONTROL PORT Access Type Codes



9.6.1.1 RESET_CTRL Register (Offset = 1h) [reset = 0x00]

RESET_CTRL is shown in $\underline{\mathbb{8}}$ 9-12 and described in $\underline{\mathbb{7}}$ 9-8.

Return to 表 9-6.

7	6	5	4	3	2	1	0
	RESERVED		RST_MOD		RESERVED		RST_REG
	R/W		W		R		W

Bit	Field	Туре	Reset	Description				
7-5	RESERVED	R/W	000	This bit is reserved				
4	RST_DIG_CORE	W	0	WRITE CLEAR BIT Reset DIG_CORE WRITE CLEAR BIT Reset Full Digital Core. This bit resets the Full Digital Signal Path (Include DSP coefficient RAM and I2C Control Port Registers), Since the DSP is also reset, the coefficient RAM content is also cleared by the DSP. 0: Normal 1: Reset Full Digital Signal Path				
3-1	RESERVED	R	000	This bit is reserved				
0	RST_REG	W	0	WRITE CLEAR BIT Reset Registers This bit resets the mode registers back to their initial values. Only reset Control Port Registers, The RAM content is not cleared. 0: Normal 1: Reset I ² C Control Port Registers				

表 9-8. RESET_CTRL Register Field Descriptions



9.6.1.2 DEVICE_CTRL_1 Register (Offset = 2h) [reset = 0x00]

DEVICE_CTRL_1 is shown in 图 9-13 and described in 表 9-9.

Return to 表 9-6.

图 9-17. DEVICE_CTRL_1 Register

7	6	5	4	3	2	1	0
RESERVED	FSW_SEL			RESERVED	DAMP_PBTL	DAMP_MOD	
R/W	R/W		R/W	R/W	R/M	V	

	表 9-9. DEVICE_CTRL_1 Register Field Descriptions								
Bit	Field	Туре	Reset	Description					
7	RESERVED	R/W	0	This bit is reserved					
6-4	FSW_SEL	R/W	000	SELECT FSW 000:384K 010:480K 011:576K 100:768K 001:Reserved 101:Reserved 110:Reserved 111:Reserved 111:Reserved					
3	RESERVED	R/W	0	This bit is reserved					
2	DAMP_PBTL	R/W	0	0: SET DAMP TO BTL MODE 1:SET DAMP TO PBTL MODE					
1-0	DAMP_MOD	R/W	00	00:BD MODE 01:1SPW MODE 10:HYBRID MODE					

表 9-9. DEVICE_CTRL_1 Register Field Descriptions

9.6.1.3 DEVICE_CTRL2 Register (Offset = 3h) [reset = 00x10]

DEVICE_CTRL2 is shown in 图 9-14 and described in 表 9-10.

Return to 表 9-6.

图 9-18. DEVICE_CTRL2 Register

7	6	5	4	3	2	1	0
RESERVED			DIS_DSP	MUTE_LEFT	RESERVED	CTRL_STATE	
R/W		R/W	R/W	R/W	R/V	V	

Bit	Field	Туре	Reset	Description				
7-5	RESERVED	R/W	000	This bit is reserved				
4	DIS_DSP	R/W	1	DSP reset When the bit is made 0, DSP starts powering up and send out data. This needs to be made 0 only after all the input clocks are settled so that DMA channels do not go out of sync. 0: Normal operation 1: Reset the DSP				
3	MUTE	R/W	0	Mute both Left and Right Channel This bit issues soft mute request for both left and right channel. The volume is smoothly ramped down/up to avoid pop/click noise. 0: Normal volume 1: Mute				
2	RESERVED	R/W	0	This bit is reserved				
1-0	CTRL_STATE	R/W	00	device state control register 00: Deep Sleep 01: Sleep 10: Hiz, 11: PLAY				

表 9-10. DEVICE_CTRL2 Register Field Descriptions



9.6.1.4 I2C_PAGE_AUTO_INC Register (Offset = Fh) [reset = 0x00]

I2C_PAGE_AUTO_INC is shown in 图 9-15 and described in 表 9-11.

Return to 表 9-6.

图 9-19. I2C_PAGE_AUTO_INC Register									
7	6	5	4	3	2	1	0		
RESERVED				PAGE_AUTOIN C_REG	RESERVED				
R/W			R/W		R/W				

表 9-11. I2C_PAGE_AUTO_INC Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	RESERVED	R/W	0000	This bit is reserved
3	PAGE_AUTOINC_REG	R/W	0	Page auto increment disable Disable page auto increment mode for non -zero books. When end of page is reached, the page goes back to 8th address location of next page when this bit is 0. When this bit is 1 the page goes to the 0th location of current page itself. 0: Enable Page auto increment 1: Disable Page auto increment
2-0	RESERVED	R/W	000	This bit is reserved

9.6.1.5 SIG_CH_CTRL Register (Offset = 28h) [reset = 0x00]

SIG_CH_CTRL is shown in 图 9-16 and described in 表 9-12.

Return to 表 9-6.

图 9-20. SIG_CH_CTRL Register

_					_ 3			
	7	6	5	4	3	2	1	0
	SCLK_RATIO_CONFIGURE				FSMODE		RESERVED	
	R/W				R/W		R/W	

表 9-12. SIG_CH_CTRL Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	SCLK_RATIO_CONFIGU RE	R/W	0000	These bits indicate the configured SCLK ratio, the number of SCLK clocks in one audio frame. Device sets this ratio automatically. 4'b0011:32FS 4'b0101:64FS 4'b0101:256FS 4'b1001:256FS 4'b1011:512FS
3	FSMODE	R/W	0	FS Speed Mode: These bits select the FS operation mode, which must be set according to the current audio sampling rate and is set manually. If the input Fs is 44.1 kHz/88.2 kHz/176.4 kHz. 4 'b0000 Auto detection 4 'b0100 Reserved 4 'b0110 32 KHz 4 'b1000 44.1 KHz 4 'b1001 48 KHz 4 'b1001 88.2 KHz 4 'b1011 96 KHz 4 'b1100 176.4 KHz 4 'b1101 192 KHz Others Reserved

TAS5825M ZHCSIC2H - OCTOBER 2019 - REVISED JANUARY 2023



表 9-12. SIG_CH_CTRL Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
2-0	RESERVED	R/W	000	This bit is reserved



9.6.1.6 CLOCK_DET_CTRL Register (Offset = 29h) [reset = 0x00]

CLOCK_DET_CTRL is shown in 图 9-17 and described in 表 9-13.

Return to 表 9-6.

图 9-21. CLOCK_DET_CTRL Register

7	6	5	4	3	2	1	0
RESERVED	DIS_DET_PLL	DIS_DET_SCL K_RANGE	DIS_DET_FS	DIS_DET_SCL K	DIS_DET_MISS	RESERVED	RESERVED
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W

Bit	Field	Туре	Reset	Description
7	RESERVED	R/W	0	This bit is reserved
6	DIS_DET_PLL	R/W	0	Ignore PLL overate Detection This bit controls whether to ignore the PLL overrate detection. The PLL must be slow than 150 MHz or an error is reported. When ignored, a PLL overrate error does not cause a clock error. 0: Regard PLL overrate detection 1: Ignore PLL overrate detection
5	DIS_DET_SCLK_RANGE	R/W	0	Ignore BCK Range Detection This bit controls whether to ignore the SCLK range detection. The SCLK must be stable between 256 KHz and 50 MHz or an error is reported. When ignored, a SCLK range error does not cause a clock error. 0: Regard BCK Range detection 1: Ignore BCK Range detection
4	DIS_DET_FS	R/W	0	Ignore FS Error Detection This bit controls whether to ignore the FS Error detection. When ignored, FS error does not cause a clock error. But CLKDET_STATUS reports fs error. 0: Regard FS detection 1: Ignore FS detection
3	DIS_DET_SCLK	R/W	0	Ignore SCLK Detection This bit controls whether to ignore the SCLK detection against LRCK. The SCLK must be stable between 32 FS and 512 FS inclusive or an error is reported. When ignored, a SCLK error does not cause a clock error. 0: Regard SCLK detection 1: Ignore SCLK detection
2	DIS_DET_MISS	R/W	0	Ignore SCLK Missing Detection This bit controls whether to ignore the SCLK missing detection. When ignored an SCLK missing does not cause a clock error. 0: Regard SCLK missing detection 1: Ignore SCLK missing detection
1	RESERVED	R/W	0	This bit is reserved
0	RESERVED	R/W	0	This bit is reserved

表 9-13. CLOCK_DET_CTRL Register Field Descriptions



9.6.1.7 SDOUT_SEL Register (Offset = 30h) [reset = 0x00]

SDOUT_SEL is shown in [8] 9-19 and described in $\overline{$ $$\pm$$ 9-14.

Return to 表 9-6.

图 9-22. SDOUT_SEL Register

7	6	5	4	3	2	1	0
	RESERVED						SDOUT_SEL
		R/W	R/	W	R/W		

r.					
	Bit	Field	Туре	Reset	Description
	7-1	RESERVED	R/W	0000000	These bits are reserved
	0	SDOUT_SEL	R/W	0	SDOUT Select. This bit selects what is being output as SDOUT pin.0: SDOUT is the DSP output (post-processing)1: SDOUT is the DSP input (pre-processing)

表 9-14. SDOUT_SEL Register Field Descriptions



9.6.1.8 I2S_CTRL Register (Offset = 31h) [reset = 0x00]

I2S_CTRL is shown in $\[Begin{subarray}{c} 9-19 \]$ and described in $\[Embed{subarray} 9-15. \]$

Return to 表 9-6.

			图 9-23. I2S_C	CTRL Register			
7	6	5	4	3	2	1	0
RESE	ERVED	SCLK_INV	RESERVED	RESERVED	RESER	RVED	RESERVED
R	2/W	R/W	R/W	R	R		R/W

	~ 衣	: 9-15. IZS_	CIKL Reg	ister Field Descriptions
Bit	Field	Туре	Reset	Description
7-6	RESERVED	R/W	00	This bit is reserved
5	SCLK_INV	R/W	0	SCLK Polarity This bit sets the inverted SCLK mode. In inverted SCLK mode, the DAC assumes that the LRCK and DIN edges are aligned to the rising edge of the SCLK. Normally the edges are assumed to be aligned to the falling edge of the SCLK 0: Normal SCLK mode 1: Inverted SCLK mode
4	RESERVED	R/W	0	This bit is reserved
3	RESERVED	R	0	This bit is reserved
2-1	RESERVED	R	00	These bits are reserved
0	RESERVED	R/W	0	This bit is reserved

表 9-15 12S CTRI Register Field Descriptions



9.6.1.9 SAP_CTRL1 Register (Offset = 33h) [reset = 0x02]

SAP_CTRL1 is shown in 图 9-20 and described in 表 9-16.

Return to 表 9-6.

图 9-24. SAP_CTRL1 Register							
7	6	5	4	3	2	1	0
I2S_SHIFT_MS B	RESERVED	DATA_FORMAT		I2S_LRCL	K_PULSE	WORD_I	LENGTH
R/W	R/W	R/W		R/W		R/	W

表 9-16. SAP_CTRL1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7	I2S_SHIFT_MSB	R/W	0	I2S Shift MSB
6	RESERVED	R/W	0	This bit is reserved
5-4	DATA_FORMAT	R/W	00	I2S Data Format These bits control both input and output audio interface formats for DAC operation. 00: I2S 01: TDM/DSP 10: RTJ 11: LTJ
3-2	I2S_LRCLK_PULSE	R/W	00	01: LRCLK pulse < 8 SCLK
1-0	WORD_LENGTH	R/W	10	I2S Word Length These bits control both input and output audio interface sample word lengths for DAC operation. 00: 16 bits 01: 20 bits 10: 24 bits 11: 32 bits

9.6.1.10 SAP_CTRL2 Register (Offset = 34h) [reset = 0x00]

SAP_CTRL2 is shown in 图 9-21 and described in 表 9-17.

Return to 表 9-6.

图 9-25. SAP_CTRL2 Register

7	6	5	4	3	2	1	0	
	I2S_SHIFT							
			R	/W				

表 9-17. SAP_CTRL2 Register Field Descriptions

Bit	Field	Туре	Reset	Description					
7-0	I2S_SHIFT	R/W	0000000	I2S Shift LSB These bits control the offset of audio data in the audio frame for both input and output. The offset is defined as the number of SCLK from the starting (MSB) of audio frame to the starting of the desired audio sample. MSB [8] locates in 节 9.6.1.10 000000000: offset = 0 SCLK (no offset) 000000001: offset = 1 SCLK 000000010: offset = 2 SCLKs and 11111111: offset = 512 SCLKs					



9.6.1.11 SAP_CTRL3 Register (Offset = 35h) [reset = 0x11]

SAP_CTRL3 is shown in 图 9-22 and described in 表 9-18.

Return to 表 9-6.

图 9-26. SAP_CTRL3 Register										
7 6 5 4 3 2 1 0										
RESE	RESERVED LEFT_DAC_DPATH RESERVED RIGHT_DAC_DPATH									
R	R/W R/W R/W									

	表 9-18. SAP_CTRL3 Register Field Descriptions									
Bit	Field	Туре	Reset	Description						
7-6	RESERVED	R/W	00	These bits are reserved						
5-4	LEFT_DAC_DPATH	R/W	01	Left DAC Data Path. These bits control the left channel audio data path connection. 00: Zero data (mute) 01: Left channel data 10: Right channel data 11: Reserved (do not set)						
3-2	RESERVED	R/W	00	These bits are reserved						
1-0	RIGHT_DAC_DPATH	R/W	01	Right DAC Data Path. These bits control the right channel audio data path connection. 00: Zero data (mute) 01: Right channel data 10: Left channel data 11: Reserved (do not set)						

表 9-18. SAP_CTRL3 Register Field Descriptions



9.6.1.12 FS_MON Register (Offset = 37h) [reset = 0x00]

FS_MON is shown in 图 9-23 and described in 表 9-19.

Return to 表 9-6.

	图 9-27. FS_MON Register										
7	6	5	4	3	2	1	0				
RESE	RESERVED SCLK_RATIO_HIGH FS										
R	/W	F	R		F	र					

Bit	Field	Туре	Reset	Description					
7-6	RESERVED	R/W	00	This bit is reserved					
5-4	SCLK_RATIO_HIGH	R	00	2 msbs of detected SCLK ratio					
3-0	FS	R	0000	These bits indicate the currently detected audio sampling rate. 4 'b0000 FS Error 4 'b0100 16 KHz 4 'b0110 32 KHz 4 'b1000 Reserved 4 'b1001 48 KHz 4 'b1011 96 KHz 4 'b1101 192 KHz Others Reserved					

表 9-19. FS_MON Register Field Descriptions

9.6.1.13 BCK (SCLK)_MON Register (Offset = 38h) [reset = 0x00]

BCK_MON is shown in 图 9-24 and described in 表 9-20.

Return to 表 9-6.

图 9-28. BCK (SCLK)_MON Register

7	6	5	4	3	2	1	0		
	BCLK (SCLK)_RATIO_LOW								
			F	2					

表 9-20. BCK_MON Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	BCLK (SCLK)_RATIO_LOW	R		These bits indicate the currently detected BCK (SCLK) ratio, the number of BCK (SCLK) clocks in one audio frame. BCK (SCLK) = 32 FS - 512 FS



9.6.1.14 CLKDET_STATUS Register (Offset = 39h) [reset = 0x00]

CLKDET_STATUS is shown in 图 9-25 and described in 表 9-21.

Return to 表 9-6.

图 9-29. CLKDET_STATUS Register

7	6	5	4	3	2	1	0
RESE	RVED			DET_S	TATUS		
R	/W	R					

Bit	Field	Туре	Reset	Description
7-6	RESERVED	R/W	00	This bit is reserved
5-0	DET_STATUS	R	000000	bit0: In auto detection mode(reg_fsmode=0),this bit indicated whether the audio sampling rate is valid or not. In non auto detection mode(reg_fsmode!=0), Fs error indicates that configured fs is different with detected fs. Even FS Error Detection Ignore is set, this flag is also asserted. bit1: This bit indicates whether the SCLK is valid or not. The SCLK ratio must be stable and in the range of 32-512FS to be valid. bit2: This bit indicates whether the SCLK is missing or not. bit3:This bit indicates whether the PLL is locked or not. The PLL is reported as unlocked when the PLL is disabled. bits4:This bit indicates whether the PLL is overrate bits5:This bit indicates whether the SCLK is overrate

表 9-21. CLKDET_STATUS Register Field Descriptions

9.6.1.15 DSP_PGM_MODE Register (Offset = 40h) [reset = 0x01]

DSP_PGM_MODE is shown in 图 9-26 and described in 表 9-22.

Return to 表 9-6.

图 9-30	. DSP	PGM	MODE	Register

7	6	5	4	3	2	1	0
	RESERVED				MODE_SEL		
	R/W				R/W		

	表 9-22. DSP_PGM_MODE Register Field Descriptions							
Bit	Field	Туре	Reset	Description				
7-5	RESERVED	R/W	000	This bit is reserved				
2-0	MODE_SEL	R/W	00001	DSP Program Selection These bits select the DSP program to use for audio processing. 00000 => ram mode 00001 => rom mode 1 00010 => rom mode 2 00011 => rom mode 3				

9.6.1.16 DSP_CTRL Register (Offset = 46h) [reset = 0x01]

DSP_CTRL is shown in 图 9-27 and described in 表 9-23.

Return to 表 9-6.

图 9-31	DSP	CTRI	Register
BI J-JI.			INCHISICI

		-			-		
7	6	5	4	3	2	1	0
	RESERVED		USER_DEFINED _RA		RESERVED	BOOT_FROM_I RAM	USE_DEFAULT _COEFFS
	R/W		R/	N	R	R/W	R/W

表 9-23. DSP_CTRL Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-5	RESERVED	R/W	000	This bit is reserved
4-3	USER_DEFINED_PROCE SSING_RATE	R/W	00	00:input 01:48k 10:96k 11:192k
2	RESERVED	R	0	This bit is reserved
1	RESERVED	R	0	This bit is reserved
0	USE_DEFAULT_COEFFS	R/W	1	Use default coefficients from ZROM this bit controls whether to use default coefficients from ZROM or use the non-default coefficients downloaded to device by the Host 0 : don't use default coefficients from ZROM 1 : use default coefficients from ZROM

9.6.1.17 DIG_VOL Register (Offset = 4Ch) [reset = 30h]

DIG_VOL is shown in 图 9-28 and described in 表 9-24.

Return to 表 9-6.

图 9-32. DIG_VOL Register





图 9-32. DIG_VOL Register (continued)

PGA_LEFT

R/W

	表 9-24. DIG_VOL Register Field Descriptions								
Bit	Field	Туре	Reset	Description					
7-0	PGA	R/W	00110000	Digital Volume These bits control both left and right channel digital volume. The digital volume is 24 dB to -103 dB in -0.5 dB step. 00000000: +24.0 dB 00000001: +23.5 dB and 00101111: +0.5 dB 00110000: 0.0 dB 00110001: -0.5 dB 1111110: -103 dB 11111111: Mute					

9.6.1.18 DIG_VOL_CTRL1 Register (Offset = 4Eh) [reset = 0x33]

DIG_VOL_CTRL1 is shown in $\underline{\mathbb{8}}$ 9-29 and described in $\underline{\pi}$ 9-25.

Return to 表 9-6.

图 9-33. DIG_VOL_CTR	L1 Register
---------------------	-------------

7	6	5	4	3	2	1	0	
	SPEED	PGA_RAMP_D			PGA_RAMP_UP_SPEED		PGA_RAMP_UP_STEP	
R/W		R/V	V	R/	W	R/W	Ι	

Bit	Field	Туре	Reset	Description
7-6	PGA_RAMP_DOWN_SPE ED	R/W	00	Digital Volume Normal Ramp Down Frequency These bits control the frequency of the digital volume updates when the volume is ramping down. 00: Update every 1 FS period 01: Update every 2 FS periods 10: Update every 4 FS periods 11: Directly set the volume to zero (Instant mute)
5-4	PGA_RAMP_DOWN_STE P	R/W	11	Digital Volume Normal Ramp Down Step These bits control the step of the digital volume updates when the volume is ramping down. 00: Decrement by 4 dB for each update 01: Decrement by 2 dB for each update 10: Decrement by 1 dB for each update 11: Decrement by 0.5 dB for each update
3-2	PGA_RAMP_UP_SPEED	R/W	00	Digital Volume Normal Ramp Up Frequency These bits control the frequency of the digital volume updates when the volume is ramping up. 00: Update every 1 FS period 01: Update every 2 FS periods 10: Update every 4 FS periods 11: Directly restore the volume (Instant unmute)
1-0	PGA_RAMP_UP_STEP	R/W	11	Digital Volume Normal Ramp Up Step These bits control the step of the digital volume updates when the volume is ramping up. 00: Increment by 4 dB for each update 01: Increment by 2 dB for each update 10: Increment by 1 dB for each update 11: Increment by 0.5 dB for each update

表 9-25. DIG_VOL_CTRL1 Register Field Descriptions



9.6.1.19 DIG_VOL_CTRL2 Register (Offset = 4Fh) [reset = 0x30]

DIG_VOL_CTRL2 is shown in 图 9-30 and described in 表 9-26.

Return to 表 9-6.

图 9-34. DIG_VOL_CTRL2 Register								
7	6	5	4	3	2	1	0	
FAST_RAMP_DOWN_SPEED FAST_RAMP_DOV		DOWN_STEP		RESEF	RVED			
R/W		R	/W		R/\	N		

₹ 9-26. DIG_VOL_CTRL2 Register Field Descriptions							
Bit	Field	Туре	Reset	Description			
7-6	FAST_RAMP_DOWN_SP EED	R/W	00	Digital Volume Emergency Ramp Down Frequency These bits control the frequency of the digital volume updates when the volume is ramping down due to clock error or power outage, which usually needs faster ramp down compared to normal soft mute. 00: Update every 1 FS period 01: Update every 2 FS periods 10: Update every 4 FS periods 11: Directly set the volume to zero (Instant mute)			
5-4	FAST_RAMP_DOWN_ST EP	R/W	11	Digital Volume Emergency Ramp Down Step These bits control the step of the digital volume updates when the volume is ramping down due to clock error or power outage, which usually needs faster ramp down compared to normal soft mute. 00: Decrement by 4 dB for each update 01: Decrement by 2 dB for each update 10: Decrement by 1 dB for each update 11: Decrement by 0.5 dB for each update			
3-0	RESERVED	R/W	0000	This bit is reserved			

表 9-26. DIG_VOL_CTRL2 Register Field Descriptions

9.6.1.20 AUTO_MUTE_CTRL Register (Offset = 50h) [reset = 0x07]

AUTO_MUTE_CTRL is shown in 图 9-31 and described in 表 9-27.

Return to 表 9-6.

图 9-35. AUTO_MUTE_CTRL Register

7	6	5	4	3	2	1	0
		RESERVED	REG_AUTO_MUTE_CTRL				
		R/W		R/W			

表 9-27. AUTO_MUTE_CTRL Register Field Descriptions

		_		· · ·
Bit	Field	Туре	Reset	Description
7-3	RESERVED	R/W	00000	This bit is reserved
2-0	REG_AUTO_MUTE_CTR L	R/W	111	bit0: 0: Disable left channel auto mute 1: Enable left channel auto mute bit1: 0: Disable right channel auto mute 1: Enable right channel auto mute bit2: 0: Auto mute left channel and right channel independently. 1: Auto mute left and right channels only when both channels are about to be auto muted.

9.6.1.21 AUTO_MUTE_TIME Register (Offset = 51h) [reset = 0x00]

AUTO_MUTE_TIME is shown in $\underline{\mathbb{8}}$ 9-32 and described in $\underline{\mathbb{7}}$ 9-28.

Return to 表 9-6.

图 9-36.	AUTO	MUTE	TIME	Register
д 0 00.	/.0.0			i togiotoi

7	6	5	4	3	2	1	0
RESERVED	AU	FOMUTE_TIME_LE	EFT	RESERVED	AUTO	OMUTE_TIME_R	RIGHT
R/W		R/W		R/W		R/W	

	-			
Bit	Field	Туре	Reset	Description
7	RESERVED	R/W	0	This bit is reserved
6-4	AUTOMUTE_TIME_LEFT	R/W	000	Auto Mute Time for Left Channel These bits specify the length of consecutive zero samples at left channel before the channel can be auto muted. The times shown are for 96 kHz sampling rate and scale with other rates. 000: 11.5 ms 001: 53 ms 010: 106.5 ms 011: 266.5 ms 100: 0.535 sec 101: 1.065 sec 110: 2.665 sec 111: 5.33 sec
3	RESERVED	R/W	0	This bit is reserved
2-0	AUTOMUTE_TIME_RIGH T	R/W	000	Auto Mute Time for Right Channel These bits specify the length of consecutive zero samples at right channel before the channel can be auto muted. The times shown are for 96 kHz sampling rate and scale with other rates. 000: 11.5 ms 001: 53 ms 010: 106.5 ms 010: 0.535 sec 101: 1.065 sec 110: 2.665 sec 111: 5.33 sec

表 9-28. AUTO_MUTE_TIME Register Field Descriptions



9.6.1.22 ANA_CTRL Register (Offset = 53h) [reset = 0h]

ANA_CTRL is shown in 图 9-33 and described in 表 9-29

Return to 表 9-6

	图 9-37. ANA_CTRL Register									
7 6 5 4 3 2 1 0										
	AMUTE_DLY									
			R/	W						

Bit	Field	Туре	Reset	Description
7	RESERVED	R/W	0	This bit is reserved
6-5	Class D bandwidth control	R/W	00	00: 100 kHz 01: 80 kHz 10: 120 kHz 11:175 kHz With Fsw = 384 kHz, 100 kHz bandwidth is selected for high audio performance. With Fsw = 768 kHz, 175 kHz bandwidth is selected for high audio performance.
4-1	RESERVED	R/W	0000	These bits are reserved
0	L and R PWM output phase control	R/W	0	0: out of phase 1: in phase

表 9-29. ANA_CTRL Register Field Descriptions



9.6.1.23 AGAIN Register (Offset = 54h) [reset = 0x00]

AGAIN is shown in [8] 9-34 and described in [7, 9-30].

Return to 表 9-6.

图 9-38. AGAIN Register									
7	6	5	4	3	2	1	0		
	RESERVED ANA_GAIN								
R/W R/W									

Bit	Field	Туре	Reset	Description					
7-5	RESERVED	R/W	000	This bit is reserved					
4-0	ANA_GAIN	R/W	00000	Analog Gain Control This bit controls the analog gain. 00000: 0 dB (29.5V peak voltage) 00001:-0.5db 11111: -15.5 dB					

表 9-30. AGAIN Register Field Descriptions

9.6.1.24 SPI_CLK Register (Offset = 55h) [reset = 0x00]

SPI_CLK is shown in 图 9-35 and described in 表 9-31.

Return to 表 9-6.

图 9-39. SPI_CLK Register

7	6	5	4	3	2	1	0
	RESE	RVED			SPI_CI	K_SEL	
	R/	W			R	W	

表 9-31. SPI_CLK Register Field Descriptions								
Bit	Field	Туре	Reset	Description				
7-4	RESERVED	R/W	0000	This bit is reserved				
3-0	SPI_CLK_SEL	R/W	0000	00:1.25M 01:2.5M 10:5M 11:10M				

本 0.31 SPI CLK Pagistor Field Descriptions



9.6.1.25 EEPROM_CTRL0 Register (Offset = 56h) [reset = 0x00]

EEPROM_CTRL0 is shown in 图 9-36 and described in 表 9-32.

Return to 表 9-6.

	图 9-40. EEPROM_CTRL0 Register										
7	6	5	4	3	2	1	0				
RESE	RVED	EEPROM_ADD R_24BITS_ENA BLE	SPI_CLK	(_RATE	SPI_INV_POLA R	SPI_MST_LSB	LOAD_EEPRO M_START				
R/	W	R/W	R/\	N	R/W	R/W	R/W				

表 9-32. EEPROM_CTRL0 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-6	RESERVED	R/W	00	This bit is reserved
5	EEPROM_ADDR_24BITS _ENABLE	R/W	0	enable 24 bits mode for EEPROM address
4-3	SPI_CLK_RATE	R/W	00	0: spi clock rate = 1.25 MHz 1: spi clock rate = 2.5 MHz 2: spi clock rate = 5 MHz 3: spi clock rate = 10 MHz
2	SPI_INV_POLAR	R/W	0	0: spi serial data change at post edge SCK 1: spi serial data change at neg edge SCK
1	SPI_MST_LSB	R/W	0	0: msb first 1: lsb first
0	LOAD_EEPROM_START	R/W	0	0: dsp coefficients read from host 1: dsp coefficients read from EEPROM

9.6.1.26 EEPROM_RD_CMD Register (Offset = 57h) [reset = 0x03]

EEPROM_RD_CMD is shown in 图 9-37 and described in 表 9-33.

Return to 表 9-6.

图 9-41. EEPROM_RD_CMD Register

7	6	5	4	3	2	1	0		
	EEPROM_RD_CMD								
			R/W-00	000011					

表 9-33. EEPROM_RD_CMD Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	EEPROM_RD_CMD	R/W	00000011	EEPROM read command

9.6.1.27 EEPROM_ADDR_START0 Register (Offset = 58h) [reset = 0x00]

EEPROM_ADDR_START0 is shown in 图 9-38 and described in 表 9-34.

Return to 表 9-6.

图 9-42. EEPROM_ADDR_START0 Register

7	6	5	4	3	2	1	0		
	EEPROM_ADDR_START_HIGH								
			R	/W					

Bit	Field	Туре	Reset	Description
7-0	EEPROM_ADDR_START _HIGH	R/W	0000000	8 msb of EEPROM read starting address for coefficient

9.6.1.28 EEPROM_ADDR_START1 Register (Offset = 59h) [reset = 0x00]

EEPROM_ADDR_START1 is shown in [8] 9-39 and described in $\frac{1}{2}$ 9-35.

Return to 表 9-6.

图 9-43. EEPROM_ADDR_START1 Register

7	6	5	4	3	2	1	0	
		EEPROM_ADDR_START_MIDDLE						
			R/	W				
	7	7 6	7 6 5		7 6 5 4 3 EEPROM_ADDR_START_MIDDLE R/W			

表 9-35. EEPROM_ADDR_START1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	EEPROM_ADDR_START _MIDDLE	R/W	0000000	8 middle of EEPROM read starting address for coefficients

9.6.1.29 EEPROM_ADDR_START2 Register (Offset = 5Ah) [reset = 0h]

EEPROM_ADDR_START2 is shown in 图 9-40 and described in 表 9-36.

Return to 表 9-6.

图 9-44. EEPROM_ADDR_START2 Register

				—	<u> </u>		
7	6	5	4	3	2	1	0
	EEPROM_ADDR_START_LOW						
			R	2/W			

表 9-36. EEPROM_ADDR_START2 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-0	EEPROM_ADDR_START _LOW	R/W	0000000	8 lsb of EEPROM read starting address for coefficients



9.6.1.30 EEPROM_BOOT_STATUS Register (Offset = 5Bh) [reset = 0x00]

EEPROM_BOOT_STATUS is shown in 图 9-41 and described in 表 9-37.

Return to 表 9-6.

图 9-45. EEPROM_BOOT_STATUS Register

7	6	5	4	3	2	1	0
		RESE	RVED			LOAD_EEPRO M_CRC_ERRO R	LOAD_EEPRO M_DONE
		F	3			R	R

表 9-37. EEPROM_BOOT_STATUS Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-2	RESERVED	R	000000	This bit is reserved
1	LOAD_EEPROM_CRC_E RROR	R	0	0: CRC pass for EEPROM boot load 1: CRC don't pass for EEPROM boot load.
0	LOAD_EEPROM_DONE	R	0	Indicate that the EEPROM boot load has been finished.

9.6.1.31 BQ_WR_CTRL1 Register (Offset = 5Ch) [reset = 0x000]

BQ_WR_CTRL1 is shown in 图 9-42 and described in 表 9-38.

Return to 表 9-6.

图 9-46. BQ_WR_CTRL1 Register

7	6	5	4	3	2	1	0	
	RESERVED							
			R/W				R/W	

表 9-38. BQ_WR_CTRL1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-1	RESERVED	R/W	0000000	This bit is reserved
0	BQ_WR_FIRST_COEF	R/W	0	Indicate the first coefficient of a BQ is starting to write.

9.6.1.32 PVDD_ADC Register (Offset = 5Eh) [reset = 0h]

PVDD_ADC is shown in 图 9-43 and described in 表 9-39.

Return to 表 9-6.

	图 9-47. PVDD_ADC Register											
7	6	5	4	3	2	1	0					
			ADC_DA	TA_OUT								
			F	२								



	₹ 9-39. PVDD_ADC Register Field Descriptions						
Bit	Field	Туре	Reset	Description			
7-0	PVDD_ADC[7:0]	R	0000000	PVDD Voltage = PVDD_ADC[7:0] / 8.428 (V)			
				223: 26.45V			
				222: 26.34V			
				221:26.22V			
				39: 4.63V			
				38: 4.51V			
				37: 4.39V			

表 9-39. PVDD_ADC Register Field Descriptions

9.6.1.33 GPIO_CTRL Register (Offset = 60h) [reset = 0x00]

GPIO_CTRL is shown in $\underline{8}$ 9-44 and described in $\underline{8}$ 9-40.

Return to 表 9-6.

	图 9-48. GPIO_CTRL Register											
7	6	5	4	3	2	1	0					
		RESERVED			GPIO2_OE	GPIO1_OE	GPIO0_OE					
		R/W			R/W	R/W	R/W					

表 9-40. GPIO_CTRL Register Field Descriptions							
Bit	Field	Туре	Reset	Description			
7-3	RESERVED	R/W	0000	This bit is reserved			
2	GPIO2_OE	R/W	0	GPIO2 Output Enable. This bit sets the direction of the GPIO2 pin 0: GPIO2 is input 1: GPIO2 is output			
1	GPIO1_OE	R/W	0	GPIO1 Output Enable This bit sets the direction of the GPIO1 pin 0: GPIO1 is input 1: GPIO1 is output			
0	GPIO0_OE	R/W	0	GPIO0 Output Enable This bit sets the direction of the GPIO0 pin 0: GPIO0 is input 1: GPIO0 is output			

表 9-40. GPIO_CTRL Register Field Descriptions



9.6.1.34 GPIO0_SEL Register (Offset = 61h) [reset = 0x00]

GPIO0_SEL is shown in 图 9-45 and described in 表 9-41.

Return to 表 9-6.

	图 9-49. GPIO0_SEL Register										
7	6	5	4	3	2	1	0				
	RESE	RVED			GPIOC	_SEL					
	R/W				R/	W					

Bit	Field	Туре	Reset	Description
7-4	RESERVED	R/W	0000	This bit is reserved
3-0	GPIO0_SEL	R/W	0000	0000: off (low) 0001: Reserved 0010: GPIO output value programmed by User in 节 9.6.1.39 0011: Auto mute flag (asserted when both L and R channels are auto muted) 0100: Auto mute flag for left channel 0101: Auto mute flag for right channel 0110: Clock invalid flag (clock error or clock missing) 0111: Reserved 1000: GPIO0 as WARNZ output 1001: Serial audio interface data output (SDOUT) 1011: GPIO0 as FAULTZ output 1100: GPIO0 as SPI CLK 1101: GPIO0 as SPI_PICO 1110: Reserved 1111: Reserved

表 9-41. GPIO0_SEL Register Field Descriptions

9.6.1.35 GPIO1_SEL Register (Offset = 62h) [reset = 0x00]

GPIO1_SEL is shown in 图 9-46 and described in 表 9-42.

Return to 表 9-6.

图 9-50.	GPIO1	SEL	Register
д 0 00.	0.101		regiotor

7	6	5	4	3	2	1	0
	RESE	RVED			GPIO ²	1_SEL	
	R/W				R/	W	

表 9-42. GPIO1_SEL Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	RESERVED	R/W	0000	This bit is reserved

TAS5825M ZHCSIC2H - OCTOBER 2019 - REVISED JANUARY 2023



表 9-42. GPIO1_SEL Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
3-0	GPIO1_SEL	R/W	0000	0000: off (low) 0001: Reserved 0010: GPIO output value programmed by User in # 9.6.1.39 0011: Auto mute flag (asserted when both L and R channels are auto muted) 0100: Auto mute flag for left channel 0101: Auto mute flag for right channel 011: Auto mute flag (clock error or clock missing) 0111: Reserved 1000: GPIO1 as WARNZ output 1001: Serial audio interface data output (SDOUT) 1011: GPIO1 as FAULTZ output 1100: GPIO1 as SPI CLK 1101: GPIO1 as SPI_PICO 1111: Reserved 1111: Reserved



9.6.1.36 GPIO2_SEL Register (Offset = 63h) [reset = 0x00]

GPIO2_SEL is shown in 图 9-47 and described in 表 9-43.

Return to 表 9-6.

	图 9-51. GPIO2_SEL Register										
7	6	5	4	3	2	1	0				
	RESE	RVED			GPIO2	_SEL					
	R/W				R/	W					

Bit	Field	Туре	Reset	Description
7-4	RESERVED	R/W	0000	This bit is reserved
3-0	GPIO2_SEL	R/W	0000	0000: off (low) 0001: Reserved 0010: GPIO output value programmed by User in ♯ 9.6.1.39 0011: Auto mute flag (asserted when both L and R channels are auto muted) 0100: Auto mute flag for left channel 0101: Auto mute flag for right channel 0110: Clock invalid flag (clock error or clock missing) 0111: Reserved 1000: GPIO2 as WARNZ output 1001: Serial audio interface data output (SDOUT) 1011: GPIO2 as FAULTZ output 1100: GPIO2 as SPI CLK 1101: GPIO2 as SPI_PICO 1111: Reserved

表 9-43. GPIO2_SEL Register Field Descriptions

9.6.1.37 GPIO_INPUT_SEL Register (Offset = 64h) [reset = 0x00]

GPIO_INPUT_SEL is shown in 图 9-48 and described in 表 9-44.

Return to 表 9-6.

图 9-52. GPIO_INPUT_SEL Register

7 6	5	4	3	2	1	0
GPIO_SPI_POCI_SEL	GPIO_PHASE_SYNC_SEL		GPIO_RESETZ_SEL		GPIO_MUTEZ_SEL	
R/W	R/W		R/W		R/W	

表 9-44. GPIO_INPUT_SEL Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-6	GPIO_SPI_POCI_SEL	R/W	00	00: N/A 01: GPIO0 10: GPIO1 11: GPIO2
5-4	GPIO_PHASE_SYNC_SE L	R/W	00	00: N/A 01: GPIO0 10: GPIO1 11: GPIO2
3-2	GPIO_RESETZ_SEL	R/W	00	00: N/A 01: GPIO0 10: GPIO1 11: GPIO2 cannot be reset by GPIO reset

Copyright © 2023 Texas Instruments Incorporated

TAS5825M ZHCSIC2H - OCTOBER 2019 - REVISED JANUARY 2023



表 9-44. GPIO_INPUT_SEL Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
1-0	GPIO_MUTEZ_SEL	R/W	00	00: N/A 01: GPIO0 10: GPIO1 11: GPIO2 MUTEZ pin active-low, output driver sets to HiZ state, the output stop switching of the Class D amplifier.



9.6.1.38 GPIO_OUT Register (Offset = 65h) [reset = 0x00]

GPIO_OUT is shown in 图 9-49 and described in 表 9-45.

Return to 表 9-6.

图 9-53. GPIO_OUT Register								
7	6	5	4	3	2	1	0	
		RESERVED			GPIO_OUT			
		R/W				R/W		

	表 9-45. GPIO_OUT Register Field Descriptions						
Bit	Field	Туре	Reset	Description			
7-3	RESERVED	R/W	00000	This bit is reserved			
2-0	GPIO_OUT	R/W	000	bit0: GPIO0 output bit1: GPIO1 output bit2: GPIO2 output			

9.6.1.39 GPIO_OUT_INV Register (Offset = 66h) [reset = 0x00]

GPIO_OUT_INV is shown in 图 9-50 and described in 表 9-46.

Return to 表 9-6.

图 9-54. GPIO_OUT_INV Register

7	6	5	4	3	2	1	0
		RESERVED		GPIO_OUT			
		R/W			R/W		

表 9-46. GPIO_OUT_INV Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-3	RESERVED	R/W	00000	This bit is reserved
2-0	GPIO_OUT	R/W		bit0: GPIO0 output invert bit1: GPIO1 output invert bit2: GPIO2 output invert

9.6.1.40 DIE_ID Register (Offset = 67h) [reset = 95h]

DIE_ID is shown in 图 9-51 and described in 表 9-47.

Return to 表 9-6.

图 9-55. DIE_ID Register

7	6	5	4	3	2	1	0
			DIE	E_ID			
			F	२			

表 9-47. DIE_ID Register Field Descriptions							
Bit	Field	Туре	Reset	Description			
7-0	DIE_ID	R	10010101	DIE ID			

Copyright © 2023 Texas Instruments Incorporated

9.6.1.41 POWER_STATE Register (Offset = 68h) [reset = 0x00]

POWER_STATE is shown in 图 9-52 and described in 表 9-48.

Return to 表 9-6.

图 9-56. POWER_STATE Register

7	6	5	4	3	2	1	0
			STATE	E_RPT			
			F	R			

Bit	Field	Туре	Reset	Description
7-0	STATE_RPT	R	0000000	0: Deep sleep
				1: Seep
				2: HIZ
				3: Play
				Others: reserved

表 9-48. POWER_STATE Register Field Descriptions



9.6.1.42 AUTOMUTE_STATE Register (Offset = 69h) [reset = 0x00]

AUTOMUTE_STATE is shown in 图 9-53 and described in 表 9-49.

Return to 表 9-6.

图 9-57. AUTOMUTE_STATE Register

7	6	5	4	3	2	1	0
	RESERVED						ZERO_LEFT_M ON
		F		R	R		

表 9-49. AUTOMUTE_STATE Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-2	RESERVED	R	000000	This bit is reserved
1	ZERO_RIGHT_MON	R	0	This bit indicates the auto mute status for right channel. 0: Not auto muted 1: Auto muted
0	ZERO_LEFT_MON	R	0	This bit indicates the auto mute status for left channel. 0: Not auto muted 1: Auto muted

9.6.1.43 PHASE_CTRL Register (Offset = 6Ah) [reset = 0]

PHASE_CTRL is shown in 图 9-54 and described in 表 9-50.

Return to 表 9-6.

图 9-58. PHASE_CTRL Register

				- J -			
7	6	5	4	3	2	1	0
RESERVED				RAMP_PH	HASE_SEL	PHASE_SYNC _SEL	PHASE_SYNC _EN
	R/W				W	R/W	R/W

表 9-50. PHASE_CTRL Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	RESERVED	R/W	0000	This bit is reserved
3-2	RAMP_PHASE_SEL	R/W	00	Select ramp clock phase when multi devices integrated in one system to reduce EMI and peak supply peak current. TI recommends set all devices the same RAMP frequency and same spread spectrum and must be set before driving device into PLAY mode if this feature is needed. 2'b00: phase 0 2'b01: phase 1 2'b10: phase 2 2'b11: phase 3 all of above have a 45 degree of phase shift
1	PHASE_SYNC_SEL	R/W	0	ramp phase sync sel, 0: is GPIO sync; 1: internal sync
0	PHASE_SYNC_EN	R/W	0	ramp phase sync enable

Copyright © 2023 Texas Instruments Incorporated

9.6.1.44 RAMP_SS_CTRL0 Register (Offset = 6Bh) [reset = 0x00]

RAMP_SS_CTRL0 is shown in 图 9-55 and described in 表 9-51.

Return to 表 9-6.

图 9-59. SS_CTRL0 Register

7	6	5	4	3	2	1	0
RESERVED	RESERVED	SS_PRE_DIV_ SEL	SS_MANUAL_ MODE	RESE	RVED	SS_RDM_EN	SS_TRI_EN
R/W	R/W	R/W	R/W	R/\	N	R/W	R/W

表 9-51. RAMP_SS_CTRL0 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7	RESERVED	R/W	0	This bit is reserved
6	RESERVED	R/W	0	This bit is reserved
5	SS_PRE_DIV_SEL	R/W	0	Select pll clock divide 2 as source clock in manual mode
4	SS_MANUAL_MODE	R/W	0	Set ramp ss controller to manual mode
3-2	RESERVED	R/W	00	This bit is reserved
1	SS_RDM_EN	R/W	0	Random SS enable
0	SS_TRI_EN	R/W	0	Triangle SS enable

9.6.1.45 SS_CTRL1 Register (Offset = 6Ch) [reset = 0x00]

SS_CTRL1 is shown in 图 9-56 and described in 表 9-52.

Return to 表 9-6.

图 9-60. SS_CTRL1 Register

7	6	5	4	3	2	1	0		
RESERVED		SS_RDM_CTRL			SS_TRI_CTRL				
R/W	R/W				R/	W			

	**		- J	
Bit	Field	Туре	Reset	Description
7 RESERVED R/W 0 This b		This bit is reserved		
6-4	SS_RDM_CTRL	R/W	000	Add Dither
3-0	SS_TRI_CTRL	S_TRI_CTRL R/W 0000 Triangle SS frequency and range control		Triangle SS frequency and range control

表 9-52. SS_CTRL1 Register Field Descriptions



9.6.1.46 SS_CTRL2 Register (Offset = 6Dh) [reset = 0xA0]

SS_CTRL2 is shown in 图 9-57 and described in 表 9-53.

Return to 表 9-6.

	图 9-61. SS_CTRL2 Register										
7	6	5	4	3	2	1	0				
			TM_FRE	Q_CTRL							
			R/	W							

Bit	Bit Field Ty		Reset	Description
7-0	TM_FREQ_CTRL	R/W	10100000	Control ramp frequency in manual mode, F=61440000/N

9.6.1.47 SS_CTRL3 Register (Offset = 6Eh) [reset = 0x11]

SS_CTRL3 is shown in $\boxed{8}$ 9-58 and described in $\boxed{8}$ 9-54.

Return to 表 9-6.

图 9-62. SS_CTRL3 Register

7	6	5	4	3	2	1	0
	TM_DST	EP_CTRL			TM_UST	EP_CTRL	
	R	W			R	W	

表 9-54. SS_CTRL3 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-4	SS_TM_DSTEP_CTRL	R/W	0001	Control triangle mode spread spectrum fall step in ramp ss manual mode
3-0	SS_TM_USTEP_CTRL	R/W	0001	Control triangle mode spread spectrum rise step in ramp ss manual mode

9.6.1.48 SS_CTRL4 Register (Offset = 6Fh) [reset = 0x24]

SS_CTRL4 is shown in 图 9-59 and described in 表 9-55.

Return to 表 9-6.

图 9-63. SS_CTRL4 Register

			· · · -	•			
7	6	5	4	3	2	1	0
RESERVED	TM_AM	P_CTRL		SS_TM	M_PERIOD_BOU	NDRY	
R/W	R/	W			R/W		

				•
Bit	Field	Туре	Reset	Description
7	RESERVED	R/W	0	This bit is reserved
6-5	TM_AMP_CTRL	R/W	01	Control ramp amp ctrl in ramp ss manual model
4-0	SS_TM_PERIOD_BOUND RY	R/W	00100	Control triangle mode spread spectrum boundary in ramp ss manual mode

表 9-55. SS_CTRL4 Register Field Descriptions

9.6.1.49 CHAN_FAULT Register (Offset = 70h) [reset = 0x00]

CHAN_FAULT is shown in $\underline{8}$ 9-60 and described in $\underline{8}$ 9-56.

Return to 表 9-6.

	图 9-64. CHAN_FAULT Register										
7	6	2	1	0							
	RESE	RVED		CH1_DC_1	CH2_DC_1	CH1_OC_I	CH2_OC_I				
	F	र		R	R	R	R				

	•••					
Bit	Field	Туре	Reset	Description		
7-4	RESERVED	R	0000	This bit is reserved		
3	CH1_DC_1	R	0	Left channel DC fault. Once there is a DC fault, this bit sets to be Class D output sets to Hi-Z. Report by FAULT pin (GPIO). Clear fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.		
2	CH2_DC_1	R	0	Right channel DC fault. Once there is a DC fault, this bit sets to be 1. Class D output sets to Hi-Z. Report by FAULT pin (GPIO). Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.		
1	CH1_OC_I	R	0	Left channel over current fault. Once there is an OC fault, this bit sets to be 1. Class D output sets to Hi-Z. Report by FAULT pin (GPIO). Clear this fault by setting bit 7 of 节 9.6.1.58 to 1 or this bit keeps 1.		
0	CH2_OC_I	R	0	Right channel over current fault. Once there is an OC fault, this bit sets to be 1. Class D output sets to Hi-Z. Report by FAULT pin (GPIO). Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.		

表 9-56. CHAN_FAULT Register Field Descriptions

9.6.1.50 GLOBAL_FAULT1 Register (Offset = 71h) [reset = 0h]

GLOBAL_FAULT1 is shown in 图 9-61 and described in 表 9-57.

Return to 表 9-6.

图 9-65. GLOBAL_FAULT1 Register	图 9-65.	GLOBAL	FAULT1	Register
--------------------------------	---------	--------	--------	----------

7	6	5	4	3	2	1	0
OTP_CRC_ER ROR	BQ_WR_ERRO R	LOAD_EEPRO M_ERROR	RESERVED	RESERVED	CLK_FAULT_I	PVDD_OV_I	PVDD_UV_I
R	R	R	R	R	R	R	R

Bit	Field	Туре	Reset	Description					
7	OTP_CRC_ERROR	R	0	Indicate OTP CRC check error.					
6	BQ_WR_ERROR	R	0 The recent BQ is written failed						
5	LOAD_EEPROM_ERROR	R		0: EEPROM boot load was done successfully 1: EEPROM boot load was done unsuccessfully					
4	RESERVED	R	0	This bit is reserved					
3	RESERVED	R	0	This bit is reserved					

表 9-57. GLOBAL_FAULT1 Register Field Descriptions



表 9-57. GLOBAL_FAULT1 Register Field Descriptions (continued)

Bit	Field	Туре	Reset	Description
2	CLK_FAULT_I	R	0	Clock fault. Once there is a Clock fault, this bit sets to be 1. Class D output sets to Hi-Z. Report by FAULT pin (GPIO). Clock fault works with an auto-recovery mode, once the clock error removes, device automatically returns to the previous state. Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.
1	PVDD_OV_I	R	0	PVDD OV fault. Once there is an OV fault, this bit sets to be 1. ClassD output sets to Hi-Z. Report by FAULT pin (GPIO). OV fault workswith an auto-recovery mode, once the OV error removes, deviceautomatically returns to the previous state.Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.
0	PVDD_UV_I	R	0	PVDD UV fault. Once there is an UV fault, this bit sets to be 1. ClassD output sets to Hi-Z. Report by FAULT pin (GPIO). OV fault workswith an auto-recovery mode, once the OV error removes, deviceautomatically returns to the previous state.Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.

9.6.1.51 GLOBAL_FAULT2 Register (Offset = 72h) [reset = 0h]

GLOBAL_FAULT2 is shown in 图 9-62 and described in 表 9-58.

Return to 表 9-6.

	图 9-66. GLOBAL_FAULT2 Register										
7	6	5	4	3	2	1	0				
		RESERVED	CBC_FAULT_C H2_I	CBC_FAULT_C H1_I	OTSD_I						
		R			R	R	R				

表 9-58. GLOBAL_FAULT2 Register Field Descriptions

Bit	Field	Туре	Reset	Description	
7-3	RESERVED	R	0000	This bit is reserved	
2	CBC_FAULT_CH2_I	R	0	Right channel cycle by cycle over current fault	
1	CBC_FAULT_CH1_I	R	0	Left channel cycle by cycle over current fault	
0	OTSD_I	R	0	Over temperature shut down fault. Once there is a OT fault, this bit sets to be 1. Class D output sets to Hi-Z. Report by FAULT pin (GPIO). OV fault works with an auto- recovery mode, once the OV error removes, device automatically returns to the previous state. Clear this fault by setting bit 7 of \ddagger 9.6.1.58 to 1 or this bit keeps 1.	

9.6.1.52 WARNING Register (Offset = 73h) [reset = 0x00]

WARNING is shown in [8] 9-63 and described in \mathbb{R} 9-59.

Return to 表 9-6.

图 9-67. WARNING Register

				•			
7	6	5	4	3	2	1	0
RESE	RVED	CBCW_CH1_I	CBCW_CH2_I	OTW_LEVEL4_	OTW_LEVEL3_	OTW_LEVEL2_	OTW_LEVEL1_
F	2	R	R	R	R	R	R

表 9-59. WARNING Register Field Descriptions

Bit	Field	Туре	Reset	Description
7-6	RESERVED	R	0	This bit is reserved
5	CBCW_CH1_I	R	0 Left channel cycle by cycle over current warning	
4	CBCW_CH2_I	R	0	Right channel cycle by cycle over current warning
3	OTW_LEVEL4_I	R	0	Over temperature warning leve4, 146C
2	OTW_LEVEL3_I	R	0	Over temperature warning leve3, 134C
1	OTW_LEVEL2_I	R	0	Over temperature warning leve2, 122C
0	OTW_LEVEL1_I	R	0	Over temperature warning leve1, 112C



9.6.1.53 PIN_CONTROL1 Register (Offset = 74h) [reset = 0x00]

PIN_CONTROL1 is shown in 图 9-64 and described in 表 9-60.

Return to 表 9-6.

图 9-68. PIN_CONTROL1 Register

7	6	5	4	3	2	1	0
MASK_OTSD	MASK_DVDD_ UV	MASK_DVDD_ OV	MASK_CLK_FA ULT	RESERVED	MASK_PVDD_ UV	MASK_DC	MASK_OC
R/W	R/W	R/W	R/W	R	R/W	R/W	R/W

表 9-60. PIN_CONTROL1 Register Field Descriptions

Bit	Field	Туре	Reset	Description
7	MASK_OTSD	R/W	0	Mask OTSD fault report
6	MASK_DVDD_UV	R/W	0	Mask DVDD UV fault report
5	MASK_DVDD_OV	R/W	0	Mask DVDD OV fault report
4	MASK_CLK_FAULT	R/W	0	Mask clock fault report
3	RESERVED	R	0	This bit is reserved
2	MASK_PVDD_UV	R/W	0	Mask PVDD UV fault report mask PVDD OV fault report
1	MASK_DC	R/W	0	Mask DC fault report
0	MASK_OC	R/W	0	Mask OC fault report

9.6.1.54 PIN_CONTROL2 Register (Offset = 75h) [reset = 0xF8]

PIN_CONTROL2 is shown in 图 9-65 and described in 表 9-61.

Return to 表 9-6.

图 9-69. PIN_CONTROL2 Register

				•			
7	6	5	4	3	2	1	0
CBC_FAULT_L ATCH_EN	CBC_WARN_L ATCH_EN	CLKFLT_LATC H_EN	OTSD_LATCH_ EN	OTW_LATCH_ EN	MASK_OTW	MASK_CBCW	MASK_CBC_F AULT
R/W	R/W	R/W	R/W	R/W	R/W	R/W	R/W

表 9-61. PIN_CONTROL2 Register Field Descriptions

Bit	Field	Туре	Reset	Description				
7	CBC_FAULT_LATCH_EN	R/W	1	Enable CBC fault latch by setting this bit to 1				
6	CBC_WARN_LATCH_EN	R/W	1	Enable CBC warning latch by setting this bit to 1				
5	CLKFLT_LATCH_EN	R/W	1	Enable clock fault latch by setting this bit to 1				
4	OTSD_LATCH_EN	R/W	1	Enable OTSD fault latch by setting this bit to 1				
3	OTW_LATCH_EN	R/W	1	Enable OT warning latch by setting this bit to 1				
2	MASK_OTW	R/W	0	Mask OT warning report by setting this bit to 1				
1	MASK_CBCW	R/W	0	Mask CBC warning report by setting this bit to 1				
0	MASK_CBC_FAULT	R/W	0	Mask CBC fault report by setting this bit to 1				

Copyright © 2023 Texas Instruments Incorporated

9.6.1.55 MISC_CONTROL Register (Offset = 76h) [reset = 0x00]

MISC_CONTROL is shown in 图 9-66 and described in 表 9-62.

Return to 表 9-6.

图 9-70. MISC_CONTROL Register

7	6	5	4	3	2	1	0
DET_STATUS_ LATCH	RESERVED		OTSD_AUTO_ REC_EN		RVED		
R/W	R/W		R/W	R/W			

表 9-62. MISC_CONTROL Register Field Descriptions

Bit	Field Type		Reset	Description				
7	DET_STATUS_LATCH	R/W	0	1:Latch clock detection status				
				0:Don't latch clock detection status				
6-5	RESERVED	R/W	00	These bits are reserved				
4	OTSD_AUTO_REC_EN	N R/W 0		OTSD auto recovery enable				
3-0	RESERVED	R/W	0000	This bit is reserved				

9.6.1.56 CBC_CONTROL Register (Offset = 77h) [reset = 0x00]

CBC_CONTROL is shown in 图 9-67 and described in 表 9-63.

Return to 表 9-6.

图 9-71. CBC_CONTROL Register

7	6	5	5 4 3 2				0
		RESERVED			CBC_EN	CBC_WARN_E N	CBC_FAULT_E N
		R/W	R/W	R/W	R/W		

表 9-63. CBC_CONTROL Register Field Descriptions

Bit	Field Type F		Reset	Description				
7-3	3 RESERVED R/W 0000		00000	These bits are reserved				
2	CBC_EN	R/W 0		Enable CBC function				
1	CBC_WARN_EN	R/W	0	Enable CBC warning				
0	CBC_FAULT_EN	R/W	0	Enable CBC fault				



9.6.1.57 FAULT_CLEAR Register (Offset = 78h) [reset = 0x00]

FAULT_CLEAR is shown in 图 9-68 and described in 表 9-64.

Return to 表 9-6.

图 9-72. FAULT_CLEAR Register

7	6	5	4	3	2	1	0
ANALOG_FAUL T_CLEAR				RESERVED			
W				R/W			

表 9-64. FAULT_CLEAR Register Field Descriptions

Bit	Field	Туре	Reset	Description
7	ANALOG_FAULT_CLEAR	W	0	WRITE CLEAR BIT once write this bit to 1, device clears analog fault
6-0	RESERVED	R/W	0000000	This bit is reserved



(2)

10 Application and Implementation

备注

以下应用部分中的信息不属于 TI 器件规格的范围, TI 不担保其准确性和完整性。TI 的客 户应负责确定器件是否适用于其应用。客户应验证并测试其设计,以确保系统功能。

10.1 Application Information

This section details the information required to configure the device for several popular configurations and provides guidance on integrating the TAS5825M device into the larger system.

10.1.1 Inductor Selections

TI requires that the peak current is smaller than the OCP (Over Current Protection) value which is 7.5 A, there are 3 cases which cause high peak current flow through inductor.

1. During power up (idle state, no audio input), the duty cycle increases from 0 to θ .

$$I_{peak_power_up} \approx PVDD \times \sqrt{C/L} \times \sin(1/\sqrt{L \times C} \times \theta/F_{sw})$$
⁽¹⁾

备注

θ =0.5 (BD Modulation), 0.14 (1SPW Modulation), 0.14 (Hybrid Modulation)

2. During music playing, some audio burst signal (high frequency) with very hard PVDD clipping causes PWM duty cycle increase dramatically. This is the worst case and rarely happens.

$$I_{peak_clipping} \approx PVDD \times (1 - \theta) / (F_{sw} \times L)$$

3. Peak current due to Max output power. Ignore the ripple current flow through capacitor here.

$$I_{peak_output_power} \approx \sqrt{2 \times Max_Output_Power / R_{speaker_Load}}$$
(3)

TI suggests that inductor saturation current I_{sat}, is larger than the amplifier peak current during power-up and play audio.

$$I_{SAT} \ge \max(I_{peak_power_up}, I_{peak_clipping}, I_{peak_output_power})$$
(4)

表 10-1. Inductor Requirements

PVDD (V)	Switching Frequency (kHz)	Minimum Inductance (L) (µH)
≤ 12	384	4.7
> 12	384	10

For higher switching frequencies (Fsw), select the inductors with minimum inductance to be 384 kHz / Fsw × L. Same PVDD and switching frequency, larger inductance means smaller idle current for lower power dissipation.



10.1.2 Bootstrap Capacitors

The output stage of the TAS5825M uses a high-side NMOS driver, rather than a PMOS driver. To generate the gate driver voltage for the high-side NMOS, a bootstrap capacitor for each output terminal acts as a floating power supply for the switching cycle. Use 0.47- μ F capacitors to connect the appropriate output pin (OUT_X) to the bootstrap pin (BST_X). For example, connect a 0.47- μ F capacitor between OUT_A and BST_A for bootstrapping the A channel. Similarly, connect another 0.47- μ F capacitor between the OUT_B and BST_B pins for the B channel inverting output.

10.1.3 Power Supply Decoupling

To make sure of high efficiency, low THD, and high PSRR, proper power supply decoupling is necessary. Noise transients on the power supply lines are short duration voltage spikes. These spikes can contain frequency components that extend into the hundreds of megahertz. The power supply input must be decoupled with some good quality, low ESL, Low ESR capacitors larger than 22 μ F. These capacitors bypasses low frequency noise to the ground plane. For high frequency decoupling, place 1- μ F or 0.1- μ F capacitors as close as possible to the PVDD pins of the device.

10.1.4 Output EMI Filtering

The TAS5825M device is often used with a low-pass filter, which is used to filter out the carrier frequency of the PWM modulated output. This filter is frequently referred to as the L-C Filter, due to the presence of an inductive element L and a capacitive element C to make up the 2-pole filter.

The L-C filter removes the carrier frequency, reducing electromagnetic emissions and smoothing the current waveform which is drawn from the power supply. The presence and size of the L-C filter is determined by several system level constraints. In some low-power use cases that have no other circuits which are sensitive to EMI, a simple ferrite bead or a ferrite bead plus a capacitor can replace the tradition large inductor and capacitor that are commonly used. In other high-power applications, large toroid inductors are required for maximum power and film capacitors can be used due to audio characteristics. Refer to the application report Class-D LC Filter Design (SLOA119) for a detailed description on the proper component selection and design of an L-C filter based upon the desired load and response.

For EMI performance and EMI Design consideration, reference to application report: TAS5825M Design Considerations for EMC.



10.2 Typical Applications

10.2.1 2.0 (Stereo BTL) System

In the 2.0 system, two channels are presented to the amplifier via the digital input signal. These two channels are amplified and then sent to two separate speakers. In some cases, the amplified signal is further separated based upon frequency by a passive crossover network after the L-C filter. Even so, the application is considered 2.0.

Most commonly, the two channels are a pair of signals called a stereo pair, with one channel containing the audio for the left channel and the other channel containing the audio for the right channel. While certainly the two channels can contain any two audio channels, such as two surround channels of a multi-channel speaker system, the most popular occurrence in two channels systems is a stereo pair.

图 10-1 shows the 2.0 (Stereo BTL) system application.




图 10-1. 2.0 (Stereo BTL) System Application Schematic



10.2.2 Design Requirements

- · Power supplies:
 - 3.3-V supply
 - 5-V to 24-V supply
- Communication: host processor serving as I²C compliant controller
- External memory (such as EEPROM and FLASH) used for coefficients.

The requirements for the supporting components for the TAS5825M device in a Stereo 2.0 (BTL) system is provide in $\frac{1}{2}$ 10-2.

REFERENCE DESIGNATOR	VALUE	SIZE	DETAILED DESCRIPTION							
C1, C16	0.1 µF	0402	CAP, CERM, 0.1 µF, 50 V, ±10%, X7R, 0402							
C2, C17, C37, C38	22 µF	0805	CAP, CERM, 22 µF, 35 V, ±20%, JB, 0805							
C3	4.7 μF	0603	CAP, CERM, 4.7 µF, 10 V, ±10%, X5R, 0603							
C4	0.1 µF	0603	CAP, CERM, 0.1 µF, 16 V, ±10%, X7R, 0603							
C5, C14, C15	1 µF	0603	CAP, CERM, 1 µF, 16 V, ±10%, X5R, 0603							
C6, C9, C10, C13	0.47 µF	0603	CAP, CERM, 0.47 µF, 16 V, ±10%, X7R, 0603							
C41, C42, C43, C44	0.68 µF	0805	CAP, CERM, 0.68 µF, 50 V, ±10%, X7R, 0805							
L1, L2, L3, L4	10 µH		Inductor, Shielded, Ferrite, 10 μ H, 4.4 A, 0.0304 Ω , SMD 1274AS-H-100M=P3							
R1	ΟΩ	0402	RES, 0, 5%, 0.063 W, 0402							
R20, R21, R22, R23	10 k Ω	0402	RES, 10.0 k, 1%, 0.063 W, 0402							
	1									

表 10-2. Supporting Component Requirements for Stereo 2.0 (BTL) Systems

10.2.3 Detailed Design procedures

This Design procedures can be used for both Stereo 2.0, Advanced 2.1 and Mono Mode.

10.2.3.1 Step One: Hardware Integration

- Using the Typical Application Schematic as a guide, integrate the hardware into the system schematic.
- Following the recommended component placement, board layout, and routing given in the example layout above, integrate the device and the supporting components into the system PCB file.
 - The most critical sections of the circuit are the power supply inputs, the amplifier output signals, and the high-frequency signals, all of which go to the serial audio port. Constructing these signals to make sure the signals are given precedent as design trade-offs are made is recommended.
 - For questions and support go to the E2E forums (e2e.ti.com). If deviating from the recommended layout is necessary, go to the E2E forum to request a layout review.

10.2.3.2 Step Two: Hardware Integration


Using the TAS5825MEVM evaluation module and the PPC3 app to configure the desired device settings.

10.2.3.3 Step Three: Software Integration

- Using the End System Integration feature of the PPC3 app to generate a baseline configuration file.
- Generate additional configuration files based upon operating modes of the end-equipment and integrate static configuration information into initialization files.
- Integrate dynamic controls (such as volume controls, mute commands, and mode-based EQ curves) into the main system program.



10.2.4 Application Curves





10.2.5 MONO (PBTL) Systems

In MONO mode, TAS5825M can be used as PBTL mode to drive sub-woofer with more output power.




图 10-8. Sub-woofer (PBTL) Application Schematic



表 10-3. Supporting Component Requirements for Sub-woofer (PBTL) Systems

REFERENCE DESIGNATOR	VALUE	SIZE	DETAILED DESCRIPTION
C1, C2	390uF	10mmx10mm	CAP, AL, 390 µ F, 35 V, +/- 20%, 0.08 ohm, SMD
C4, C5	0.1 µF	0402	CAP, CERM, 0.1 µF, 50 V, ±10%, X7R, 0402
C3, C6	22 µF	0805	CAP, CERM, 22 µF, 35 V, ±20%, JB, 0805
C7	4.7 μF	0603	CAP, CERM, 4.7 µF, 10 V, ±10%, X5R, 0603
C8	0.1 µF	0603	CAP, CERM, 0.1 µF, 16 V, ±10%, X7R, 0603
C9,C10,C11	1 µF	0603	CAP, CERM, 1 µF, 16 V, ±10%, X5R, 0603
C12,C13,C16,C17	0.47 µF	0603	CAP, CERM, 0.47 µF, 16 V, ±10%, X7R, 0603
C14,C15	0.68 µF	0805	CAP, CERM, 0.68 µF, 50 V, ±10%, X7R, 0805
L1,L2	4.7 μH		Inductor, Shielded, 4.7 µH, 8.7 A
R2	1 kΩ	0402	RES, 0, 5%, 0.063 W, 0402
R3,R4,R5,R6	10 k Ω	0402	RES, 10.0 k, 1%, 0.063 W, 0402



10.2.6 Advanced 2.1 System (Two TAS5825M Devices)

In higher performance systems, the subwoofer output can be enhanced using digital audio processing as was done in the high-frequency channels. To accomplish this, two TAS5825M devices are used - one for the high frequency left and right speakers and one for the mono subwoofer speaker. In this system, the audio signal can be sent from the TAS5825M device through the SDOUT pin. Alternatively, the subwoofer amplifier can accept the same digital input as the stereo, which might come from a central systems processor. (10-9) shows the 2.1 (Stereo BTL with Two TAS5825M devices) system application.





图 10-9. 2.1 (2.1 CH with Two TAS5825M Devices) Application Schematic




10.2.7 Application Curves



10.3 Power Supply Recommendations

The TAS5825M device requires two power supplies for proper operation. A high-voltage supply calls PVDD is required to power the output stage of the speaker amplifier and the associated circuitry. Additionally, one low-voltage power supply which is calls DVDD is required to power the various low-power portions of the device. The allowable voltage range for both PVDD and DVDD supply are listed in the *Recommended Operating Conditions* table. The two power supplies do not have a required powerup sequence. The power supplies can be powered on in any order.







10.3.1 DVDD Supply

The DVDD supply that is required from the system is used to power several portions of the device. As shown in [m] 10-12, the DVDD supply provides power to the DVDD pin. Proper connection, routing and decoupling techniques are highlighted in # 10 and # 10.4.2 and must be followed as closely as possible for proper operation and performance.

Some portions of the device also require a separate power supply that is a lower voltage than the DVDD supply. To simplify the power supply requirements for the system, the TAS5825M device includes an integrated low dropout (LDO) linear regulator to create this supply. This linear regulator is internally connected to the DVDD supply and the output is presented on the DVDD_REG pin, providing a connection point for an external bypass capacitor. Note that the linear regulator integrated in the device has only been designed to support the current requirements of the internal circuitry, and must not be used to power any additional external circuity. Additional loading on this pin can cause the voltage to sag, negatively affecting the performance and operation of the device.

10.3.2 PVDD Supply

The output stage of the speaker amplifier drives the load using the PVDD supply. This is the power supply which provides the drive current to the load during playback. Proper connection, routing, and decoupling techniques are highlighted in the TAS5825MEVM and must be followed as closely as possible for proper operation and performance. Due to the high-voltage switching of the output stage, properly decoupling the output power stages in the manner described in the TAS5825M device # 10 is important. Lack of proper decoupling, like that shown in the # 10, results in voltage spikes which can damage the device.

A separate power supply is required to drive the gates of the MOSFETs used in the output stage of the speaker amplifier. This power supply is derived from the PVDD supply via an integrated linear regulator. A GVDD pin is provided for the attachment of decoupling capacitor for the gate drive voltage regulator. Note that the linear regulator integrated in the device has only been designed to support the current requirements of the internal circuitry, and must not be used to power any additional external circuitry. Additional loading on this pin can cause the voltage to sag, negatively affecting the performance and operation of the device.

Another separate power supply is derived from the PVDD supply via an integrated linear regulator is AVDD. AVDD pin is provided for the attachment of decoupling capacitor for the TAS5825M internal circuitry. Note that the linear regulator integrated in the device has only been designed to support the current requirements of the internal circuitry, and must not be used to power any additional external circuitry. Additional loading on this pin can cause the voltage to sag, negatively affecting the performance and operation of the device.

10.4 Layout

10.4.1 Layout Guidelines

10.4.1.1 General Guidelines for Audio Amplifiers

Audio amplifiers which incorporate switching output stages must have special attention paid to their layout and the layout of the supporting components used around them. The system level performance metrics, including thermal performance, electromagnetic compliance (EMC), device reliability, and audio performance are all affected by the device and supporting component layout.

The guidance provided in the applications section with regard to device and component selection can be followed by precise adherence to the layout guidance shown in # 10.4.2. These examples represent exemplary baseline balance of the engineering trade-offs involved with lying out the device. These designs can be modified slightly as needed to meet the needs of a given application. In some applications, for instance, solution size can be compromised to improve thermal performance through the use of additional contiguous copper neat the device. Conversely, EMI performance can be prioritized over thermal performance by routing on internal traces and incorporating a via picket-fence and additional filtering components. In all cases, TI recommends to start from the guidance shown in # 10.4.2 and work with TI field application engineers or through the E2E community to modify the example based upon the application specific goals.



10.4.1.2 Importance of PVDD Bypass Capacitor Placement on PVDD Network

Placing the bypassing and decoupling capacitors close to supply has long been understood in the industry. This applies to DVDD, AVDD, GVDD and PVDD. However, the capacitors on the PVDD net for the TAS5825M device deserve special attention.

The small bypass capacitors on the PVDD lines of the DUT must be placed as close to the PVDD pins as possible. Not only dose placing these device far away from the pins increase the electromagnetic interference in the system, but doing so can also negatively affect the reliability of the device. Placement of these components too far from the TAS5825M device can cause ringing on the output pins that can cause the voltage on the output pin to exceed the maximum allowable ratings shown in the *Absolute Maximum Ratings* table, damaging the deice . For that reason, the capacitors on the PVDD net must be no further away from their associated PVDD pins than what is shown in the example layouts in the # 10.4.2 section.

10.4.1.3 Optimizing Thermal Performance

Follow the layout example shown in the \mathbb{X} 10-13 to achieve the best balance of solution size, thermal, audio, and electromagnetic performance. In some cases, deviation from this guidance can be required due to design constraints which cannot be avoided. In these instances, the system designer must make sure that the heat can get out of the device and into the ambient air surrounding the device. Fortunately, the heat created in the device naturally travels away from the device and into the lower temperature structures around the device.

10.4.1.3.1 Device, Copper, and Component Layout

Primarily, the goal of the PCB design is to minimize the thermal impedance in the path to those cooler structures. These tips must be followed to achieve that goal:

- Avoid placing other heat producing components or structures near the amplifier (including above or below in the end equipment).
- If possible, use a higher layer count PCB to provide more heat sinking capability for the TAS5825M device and to prevent traces and copper signal and power planes from breaking up the contiguous copper on the top and bottom layer.
- Place the TAS5825M device away from the edge of the PCB when possible to make sure that the heat can travel away from the device on all four sides.
- Avoid cutting off the flow of heat from the TAS5825M device to the surrounding areas with traces or via strings. Instead, route traces perpendicular to the device and line up vias in columns which are perpendicular to the device.
- Unless the area between two pads of a passive component is large enough to allow copper to flow in between the two pads, orient the pads so that the narrow end of the passive component is facing the TAS5825M device.
- Because the ground pins are the best conductors of heat in the package, maintain a contiguous ground plane from the ground pins to the PCB area surrounding the device for as many of the ground pins as possible.

10.4.1.3.2 Stencil Pattern

The recommended drawings for the TAS5825M device PCB foot print and associated stencil pattern are shown at the end of this document in the package addendum. Additionally, baseline recommendations for the via arrangement under and around the device are given as a starting point for the PCB design. This guidance is provided to be an excellent choice for the majority of manufacturing capabilities in the industry and prioritizes manufacturability over all other performance criteria. In elevated ambient temperature or under high-power dissipation use-cases, this guidance can be too conservative and advanced PCB design techniques can be used to improve thermal performance of the system.

备注

The customer must verify that deviation from the guidance shown in the package addendum, including the deviation explained in this section, meets the customer's quality, reliability, and manufacturability goals.



10.4.1.3.2.1 PCB footprint and Via Arrangement

The PCB footprint (also known as a symbol or land pattern) communicates to the PCB fabrication vendor the shape and position of the copper patterns to which the TAS5825M device is soldered. This footprint can be followed directly from the guidance in the package addendum at the end of this data sheet. TI recommends to make sure that the thermal pad, which connects electrically and thermally to the PowerPAD[™] of the TAS5825M device, be made no smaller than what is specified in the package addendum. This method makes sure that the TAS5825M device has the largest interface possible to move heat from the device to the board.

The via pattern shown in the package addendum provides an improved interface to carry the heat from the device through to the layers of the PCB, because small diameter plated vias (with minimally-sized annular rings) present a low thermal-impedance path from the device into the PCB. Once into the PCB, the heat travels away from the device and into the surrounding structures and air. By increasing the number of vias, as shown in # 10.4.2, this interface can benefit from improved thermal performance.

备注

Vias can obstruct heat flow if the vias are not constructed properly.

More notes on the construction and placement of vias are as follows:

- Remove thermal reliefs on thermal vias, because the thermal reliefs impede the flow of heat through the via.
- Vias filled with thermally conductive material are best, but a simple plated via can be used to avoid the additional cost of filled vias.
- The diameter of the drill must be 8 mm or less. Also, the distance between the via barrel and the surrounding planes must be minimized to help heat flow from the via into the surrounding copper material. In all cases, minimum spacing must be determined by the voltages present on the planes surrounding the via and minimized wherever possible.
- Vias must be arranged in columns, which extend in a line radially from the heat source to the surrounding area. This arrangement is shown in #10.4.2.
- Make sure that vias do not cut off power current flow from the power supply through the planes on internal layers. If needed, remove some vias that are farthest from the TAS5825M device to open up the current path to and from the device.

10.4.1.3.2.2 Solder Stencil

During the PCB assembly process, a piece of metal called a stencil on top of the PCB and deposits solder paste on the PCB wherever there is an opening (called an aperture) in the stencil. The stencil determines the quantity and the location of solder paste that is applied to the PCB in the electronic manufacturing process. In most cases, the aperture for each of the component pads is almost the same size as the pad itself. However, the thermal pad on the PCB is large and depositing a large, single deposition of solder paste leads to manufacturing issues. Instead, the solder is applied to the board in multiple apertures, to allow the solder paste to outgas during the assembly process and reduce the risk of solder bridging under the device. This structure is called an aperture array, and is shown in the # 10.4.2 section. Make sure that the total area of the aperture array (the area of all of the small apertures combined) covers between 70% and 80% of the area of the thermal pad itself.



10.4.2 Layout Example




图 10-13. 2.0 (Stereo BTL) 3-D View






图 10-14. 2.0 (Stereo BTL) Top Copper View



11 Device and Documentation Support 11.1 Device Support

11.1.1 Device Nomenclature

The glossary listed in \ddagger 11 and is a general glossary with commonly used acronyms and words which are defined in accordance with a broad TI initiative to comply with industry standards such as JEDEC, IPC, IEEE, and others. The glossary provided in this section defines words, phrases, and acronyms that are unique to this product and documentation, collateral, or support tools and software used with this product. For any additional questions regarding definitions and terminology, please see the e2e Audio Amplifier Forum.

Bridge tied load (BTL) is an output configuration in which one terminal of the speaker is connected to one halfbridge and the other terminal is connected to another half-bridge.

DUT refers to a *device under test* to differentiate one device from another.

Closed-loop architecture describes a topology in which the amplifier monitors the output terminals, comparing the output signal to the input signal and attempts to correct for non-linearities in the output.

Dynamic controls are those which are changed during normal use by either the system or the end-user.

GPIO is a general purpose input/output pin and is a highly configurable, bi-directional digital pin, which can perform many functions as required by the system.

Host processor (also known as System Processor, Scalar, Host, or System Controller) refers to a device, which serves as a central system controller, providing control information to devices connected as well as gathering audio source data from devices upstream and distributing to other devices. This device often configures the controls of the audio processing devices (like the TAS5825M) in the audio path to optimize the audio output of a loudspeaker based on frequency response, time alignment, target sound pressure level, safe operating area of the system, and user preference.

Hybrid Flow uses components which are built in RAM and components which are built in ROM to make a configurable device that is easier to use than a fully-programmable device while remaining flexible enough to be used in several applications

Maximum continuous output power refers to the maximum output power that the amplifier can continuously deliver without shutting down when operated in a 25°C ambient temperature. Testing is performed for the period of time required that their temperatures reach thermal equilibrium and are no longer increasing

Parallel bridge tied load (PBTL) is an output configuration in which one terminal of the speaker is connected to two half-bridges which have been placed in parallel and the other terminal is connected to another pair of half bridges placed in parallel

R_{DS(on)} is a measure of the on-resistance of the MOSFETs used in the output stage of the amplifier.

Static controls/Static configurations are controls which do not change while the system is in normal use.

Vias are copper-plated through-hole in a PCB.

11.1.2 Development Support

For RDGUI software, please consult your local field support engineer.

11.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

11.3 支持资源

TI E2E[™] 支持论坛是工程师的重要参考资料,可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解 答或提出自己的问题可获得所需的快速设计帮助。



链接的内容由各个贡献者"按原样"提供。这些内容并不构成 TI 技术规范,并且不一定反映 TI 的观点;请参阅 TI 的《使用条款》。

11.4 Trademarks

PowerPAD[™] and TI E2E[™] are trademarks of Texas Instruments. 所有商标均为其各自所有者的财产。

11.5 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序,可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级,大至整个器件故障。精密的集成电路可能更容易受到损坏,这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

11.6 术语表

TI 术语表 本术语表列出并解释了术语、首字母缩略词和定义。

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TAS5825MRHBR	ACTIVE	VQFN	RHB	32	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-25 to 85	5825M	Samples
TAS5825MRHBT	ACTIVE	VQFN	RHB	32	250	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-25 to 85	5825M	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



www.ti.com

PACKAGE OPTION ADDENDUM

18-Jan-2023




Texas

www.ti.com

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	-	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TAS5825MRHBR	VQFN	RHB	32	3000	330.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2
TAS5825MRHBT	VQFN	RHB	32	250	180.0	12.4	5.3	5.3	1.1	8.0	12.0	Q2



www.ti.com

PACKAGE MATERIALS INFORMATION

17-Apr-2023



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TAS5825MRHBR	VQFN	RHB	32	3000	367.0	367.0	35.0
TAS5825MRHBT	VQFN	RHB	32	250	210.0	185.0	35.0

RHB 32

5 x 5, 0.5 mm pitch

GENERIC PACKAGE VIEW

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



RHB0032E



PACKAGE OUTLINE

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



RHB0032E

EXAMPLE BOARD LAYOUT

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

 Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




RHB0032E

EXAMPLE STENCIL DESIGN

VQFN - 1 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源, 不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担 保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验 证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。 您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成 本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023,德州仪器 (TI) 公司