

具有高级 Eco-mode™ 的 4.5V 至 18V 输入, 5A 同步降压转换器

查询样品: TPS56528

特性

- D-CAP2™ 模式支持快速瞬态响应
- 低输出纹波,支持陶瓷输出电容器
- 宽泛的 V_{IN}输入电压范围: 4.5V 至 18V
- 输出电压范围: 0.6V 至 7V
- 高效率集成型场效应晶体管 (FET) 针对更低占空比应用进行了优化 -68mΩ(高侧)与 37mΩ(低侧)
- 关断时的高效率,流耗不足 10μA
- 高初始带隙基准精度
- 预偏置软启动
- 650 kHz 开关频率 (f_{sw})
- 逐周期限流
- 高级自动跳跃 Eco-mode™ 为了在轻负载下实现高效率
- 电源正常输出
- 固定软启动时间: 1.0ms

应用范围


- 低电压系统的广泛应用
 - 数字电视电源
 - 高清 Blu-ray Disc™ 播放器
 - 网络家庭终端设备
 - 数字机顶盒 (STB)


说明

TPS56528 是一款自适应接通时间 D-CAP2™ 模式同步降压转换器。 TPS56528 可帮助系统设计人员通过一个成本有效、低组件数、低待机电流解决方案来完成各种终端设备的电源总线调节器集。 TPS56528 的主控制环路使用 D-CAP2™ 模式控制,此控制方式提供一个无需外部补偿组件的快速瞬态响应。 自适应接通时间控制支持更高负载情况下的脉宽调制 (PWM) 模式与轻负载下的高级 Eco-mode™ 运行之间的无缝转换。 高级 Eco-mode™ 使 TPS56528 能够在较轻负载条件下保持高效率。 TPS56528 的私有电路还使该器件能够使用诸如高分子有机半导体固体电容器(POSCAP)或 SP-CAP等低等效串联电阻 (ESR)输出电容器以及超低 ESR 陶瓷电容器。 该器件的工作输入电压介于 4.5V 至 18V VIN 之间。输出电压可在 0.6V 与 7V 之间进行设定。此外,该器件还特有一个固定值

TPS56528 采用 8 引脚 **DDA** 封装,并针对 -40℃ 到 85℃ 的工作温度范围内的运行而设计。

为 1.0ms 的软启动时间和电源正常输出功能。





M

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

D-CAP2, Eco-mode, advanced Eco-mode are trademarks of Texas Instruments. Blu-ray Disc is a trademark of Blu-ray Disc Association.





These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ORDERING INFORMATION(1)

T _A	PACKAGE ⁽²⁾ (3)	ORDERABLE PART NUMBER	PIN	TRANSPORT MEDIA
40°C to 95°C	DDA	TPS56528DDA	0	Tube
–40°C to 85°C	DDA	TPS56528DDAR	0	Tape and Reel

- (1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.
- (2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.
- (3) All package options have Cu NIPDAU lead/ball finish.

ABSOLUTE MAXIMUM RATINGS

over operating free-air temperature range (unless otherwise noted) (1)

		VA	VALUE			
		MIN				
	VIN, EN	-0.3	20			
	VBST	-0.3	26			
	VBST (10 ns transient)	-0.3	28			
Input voltage range	VBST (vs SW)	-0.3	6.5	V		
	VFB, PG	-0.3	6.5			
	SW	-2	20			
	SW (10 ns transient)	-3	22			
Output valtage as	VREG5	-0.3	6.5			
Output voltage range	GND	-0.3	0.3	V		
Voltage from GND to thermal pad	, V _{diff}	-0.2	0.2	V		
	Human Body Model (HBM)		2	kV		
Electrostatic discharge	Charged Device Model (CDM)		500	V		
Operating junction temperature, T _J		-40	150	°C		
Storage temperature, T _{stg}		-55	150			

⁽¹⁾ Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

THERMAL INFORMATION

	TUEDMAL METRIC(1)	TPS56528	LINUTO
	THERMAL METRIC ⁽¹⁾	DDA (8 PINS)	UNITS
θ_{JA}	Junction-to-ambient thermal resistance	44.4	
θ_{JCtop}	Junction-to-case (top) thermal resistance	51.6	
θ_{JB}	Junction-to-board thermal resistance	27.8	90044
ΨЈТ	Junction-to-top characterization parameter	8.7	°C/W
ΨЈВ	Junction-to-board characterization parameter	27.7	
θ_{JCbot}	Junction-to-case (bottom) thermal resistance	5.3	

(1) 有关传统和新的热 度量的更多信息,请参阅IC 封装热度量应用报告, SPRA953。



RECOMMENDED OPERATING CONDITIONS

over operating free-air temperature range, (unless otherwise noted)

			MIN	MAX	UNIT
V _{IN}	Supply input voltage range		4.5	18	V
		VBST	-0.1	24	
		VBST (10 ns transient)	-0.1	27	
		VBST(vs SW)	-0.1	6.0	
		PG	-0.1	5.7	
V _I	Input voltage range	EN	-0.1	18	V
		VFB	-0.1	5.5	
		SW	-1.8	18	
		SW (10 ns transient)	-3	21	
		GND	-0.1	0.1	
Vo	Output voltage range	VREG5	-0.1	5.7	V
Io	Output Current range	I _{VREG5}	0	5	mA
T _A	Operating free-air temperature		-40	85	°C
T _J	Operating junction temperature		-40	150	°C

ELECTRICAL CHARACTERISTICS

over operating free-air temperature range, V_{IN} = 12 V (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY	CURRENT				,	
I _{VIN}	Operating - non-switching supply current	V_{IN} current, $T_A = 25$ °C, $EN = 5$ V, $V_{FB} = 0.7$ V		170	350	μΑ
I _{VINSDN}	Shutdown supply current	V _{IN} current, T _A = 25°C, EN = 0 V		3.8	10	μA
LOGIC TH	HRESHOLD					
· · · · · · · · · · · · · · · · · · ·	EN high-level input voltage	EN	1.6			V
V_{EN}	EN low-level input voltage	EN			0.6	V
R _{EN}	EN pin resistance to GND	V _{EN} = 12 V	180	350	700	kΩ
V _{FB} VOLT	TAGE AND DISCHARGE RESISTANCE				,	
		$T_A = 25$ °C, $V_O = 1.05$ V, $I_O = 10$ mA, advanced Eco-mode TM operation		606		mV
V_{FBTH}	V _{FB} threshold voltage	$T_A = 25$ °C, $V_O = 1.05$ V, continuous mode operation	593	600	607	mV
		T_A = -40 to 85°C, V_O = 1.05 V, continuous mode operation ⁽¹⁾	588	600	612	mV
I _{VFB}	V _{FB} input current	V _{FB} = 0.7 V, T _A = 25°C		0	±0.15	μA
SW DISC	HARGE				,	
I _{DISCHG}	SW discharge current	EN = 0 V, SW = 1 V, T _A = 25°C	1.0	1.5		mA
V _{REG5} OU	ITPUT				,	
V_{VREG5}	V _{REG5} output voltage	T _A = 25°C, 6.0 V < V _{IN} < 18 V, 0 < I _{VREG5} < 5 mA	5.2	5.5	5.7	V
I _{VREG5}	Output current	V _{IN} = 6 V, V _{REG5} = 4.0 V, T _A = 25°C	20			mA
MOSFET						
D	High side switch resistance	25°C, V _{BST} - SW = 5.5 V		68		mΩ
R _{DS(on)}	Low side switch resistance	25°C		37		mΩ
CURREN'	T LIMIT					
I _{ocl}	Current limit	L out = 1.5 μ H ⁽¹⁾	5.5	6.2	7.8	Α
CURREN	T LIMIT		5.5		7.8	

⁽¹⁾ Not production tested.



ELECTRICAL CHARACTERISTICS (continued)

over operating free-air temperature range, V_{IN} = 12 V (unless otherwise noted)


	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT	
THERMAI	L SHUTDOWN	·					
_	The control of the state of the	Shutdown temperature (2)		165			
T _{SDN}	Thermal shutdown threshold	Hysteresis (2)		35		°C	
ON-TIME	TIMER CONTROL	·					
t _{ON}	On time	V _{IN} = 12 V, V _O = 1.05 V		150		ns	
t _{OFF(MIN)}	Minimum off time	T _A = 25°C, V _{FB} = 0.5 V		260	310	ns	
SOFT ST	ART	•	•		•		
t _{SS}	Soft-start time	Internal soft-start time	0.7	1.0	1.3	ms	
POWER 0	GOOD						
M	DC threehold	VFB rising(good)	85%	90%	95%		
V_{THPG}	PG threshold	VFB falling(Fault)		85%			
IPG	PG sink current	PG=0.5V	2	4		mA	
OUTPUT	UNDERVOLTAGE AND OVERVOLT	AGE PROTECTION					
V _{OVP}	Output OVP threshold	OVP Detect (L>H)		125%			
V_{UVP}	Output UVP threshold	UVP detect (H>L)		65%			
t _{UVPDEL}	Output UVP delay	to Hiccup state		7		μs	
t _{UVPEN}	Output UVP Enable delay	Relative to soft-start time		x1.7			
UVLO							
111/1/0	IN/I O there should	Wake up V _{REG5} voltage	3.45	3.75	4.05		
UVLO	UVLO threshold	Hysteresis V _{REG5} voltage	0.13	0.32	0.48	V	

⁽²⁾ Not production tested.



DEVICE INFORMATION

DDA PACKAGE (TOP VIEW)




PIN FUNCTIONS

FIII I ONCTIONS								
PIN		DESCRIPTION						
NAME NO.		DESCRIPTION						
EN	1	Enable input control. Active high and must be pulled up to enable the device.						
VFB	2	Converter feedback input. Connect to output voltage with feedback resistor divider.						
VREG5	3	$5.5~V$ power supply output. A capacitor (typical $0.47~\mu F$) should be connected to GND. VREG5 is not active when EN is low.						
PG	4	Open drain power good output.						
GND	5	Ground pin. Power ground return for switching circuit. Connect sensitive SS and VFB returns to GND at a single point.						
SW	6	Switch node connection between high-side NFET and low-side NFET.						
VBST	7	Supply input for the high-side FET gate drive circuit. Connect 0.1µF capacitor between VBST and SW pins. An internal diode is connected between VREG5 and VBST.						
VIN	8	Input voltage supply pin.						
Exposed Thermal Pad	Back side	Thermal pad of the package. Must be soldered to achieve appropriate dissipation. Must be connected to GND.						



FUNCTIONAL BLOCK DIAGRAM





OVERVIEW

The TPS56528 is a 5-A synchronous step-down (buck) converter with two integrated N-channel MOSFETs. It operates using D-CAP2™ mode control. The fast transient response of D-CAP2™ control reduces the output capacitance required to meet a specific level of performance. Proprietary internal circuitry allows the use of low ESR output capacitors including ceramic and special polymer types. And also PG output can be used for sequence operation.

DETAILED DESCRIPTION

PWM Operation

The main control loop of the TPS56528 is an adaptive on-time pulse width modulation (PWM) controller that supports a proprietary D-CAP2™ mode control. D-CAP2™ mode control combines constant on-time control with an internal compensation circuit for pseudo-fixed frequency and low external component count configuration with both low ESR and ceramic output capacitors. It is stable even with virtually no ripple at the output.

At the beginning of each cycle, the high-side MOSFET is turned on. This MOSFET is turned off after internal one shot timer expires. This one shot is set by the converter input voltage, VIN, and the output voltage, VO, to maintain a pseudo-fixed frequency over the input voltage range, hence it is called adaptive on-time control. The one-shot timer is reset and the high-side MOSFET is turned on again when the feedback voltage falls below the reference voltage. An internal ramp is added to reference voltage to simulate output ripple, eliminating the need for ESR induced output ripple from D-CAP2TM mode control.

PWM Frequency and Adaptive On-Time Control

TPS56528 uses an adaptive on-time control scheme and does not have a dedicated on board oscillator. The TPS56528 runs with a pseudo-constant frequency of 650 kHz by using the input voltage and output voltage to set the on-time one-shot timer. The on-time is inversely proportional to the input voltage and proportional to the output voltage; therefore, when the duty ratio is VOUT/VIN, the frequency is constant.

Advanced Auto-Skip Eco-Mode™ Control

The TPS56528 is designed with advanced auto-skip Eco-mode™ to increase higher light load efficiency. As the output current decreases from heavy load condition, the inductor current is also reduced. If the output current is reduced enough, the inductor current ripple valley reaches the zero level, which is the boundary between continuous conduction and discontinuous conduction modes. The rectifying low-side MOSFET is turned off when its zero inductor current is detected. As the load current further decreases the converter run into discontinuous conduction mode. The on-time is kept approximately the same as is in continuous conduction mode. The off-time increases as it takes more time to discharge the output capacitor to the level of the reference voltage with smaller load current. The transition point to the light load operation I_{OUT(LL)} current can be calculated in Equation 1

$$I_{OUT(LL)} = \frac{1}{2 \cdot L \cdot fsw} \cdot \frac{\left(V_{IN} - V_{OUT}\right) \cdot V_{OUT}}{V_{IN}} \tag{1}$$

Soft Start and Pre-Biased Soft Start

The TPS56528 has an internal 1.0ms soft-start. When the EN pin becomes high, internal soft-start function begins ramping up the reference voltage to the PWM comparator.

The TPS56528 contains a unique circuit to prevent current from being pulled from the output during startup if the output is pre-biased. When the soft-start commands a voltage higher than the pre-bias level (internal soft start becomes greater than feedback voltage V_{FB}), the controller slowly activates synchronous rectification by starting the first low side FET gate driver pulses with a narrow on-time. It then increments that on-time on a cycle-bycycle basis until it coincides with the time dictated by (1-D), where D is the duty cycle of the converter. This scheme prevents the initial sinking of the pre-bias output, and ensure that the out voltage (V_O) starts and ramps up smoothly into regulation and the control loop is given time to transition from pre-biased start-up to normal mode operation.



Power Good

The power-good function is activated after soft start has finished. The power good function becomes active after 1.7 times soft-start time. When the output voltage becomes within -10% of the target value, internal comparators detect power good state and the power good signal becomes high. The power good output, PG is an open drain output. If the feedback voltage goes under 15% of the target value, the power good signal becomes low.

Output Discharge Control

TPS56528 discharges the output via SW pin when EN is low, or the controller is turned off by the protection functions(UVP, UVLO and thermal shutdown). The internal regular low-side MOSFET is not turned on during the output discharge operation to avoid the possibility of causing negative voltage at the output.

Current Protection

The output overcurrent protection (OCP) is implemented using a cycle-by-cycle valley detect control circuit. The switch current is monitored by measuring the low-side FET switch voltage between the SW pin and GND. This voltage is proportional to the switch current. To improve accuracy, the voltage sensing is temperature compensated.

During the on time of the high-side FET switch, the switch current increases at a linear rate determined by V_{IN} , V_{OUT} , the on-time and the output inductor value. During the on time of the low-side FET switch, this current decreases linearly. The average value of the switch current is the load current lout. The TPS56528 constantly monitors the low-side FET switch voltage, which is proportional to the switch current, during the low-side on-time. If the measured voltage is above the voltage proportional to the current limit, an internal counter is incremented per each SW cycle and the converter maintains the low-side switch on until the measured voltage is below the voltage corresponding to the current limit at which time the switching cycle is terminated and a new switching cycle begins. In subsequent switching cycles, the on-time is set to a fixed value and the current is monitored in the same manner. If the over current condition exists for 7 consecutive switching cycles, the internal OCL threshold is set to a lower level, reducing the available output current. When a switching cycle occurs where the switch current is not above the lower OCL threshold, the counter is reset and the OCL limit is returned to the higher value.

There are some important considerations for this type of over-current protection. The peak current is the average load current plus one half of the peak-to-peak inductor current. The valley current is the average load current minus one half of the peak-to-peak inductor current. Since the valley current is used to detect the overcurrent threshold, the load current is higher than the over-current threshold. Also, when the current is being limited, the output voltage tends to fall as the demanded load current may be higher than the current available from the converter. This protection is non-latching. When the VFB voltage becomes lower than 65% of the target voltage, the UVP comparator detects it. After 7 µs detecting the UVP voltage, device will shut down and re-start after hiccup time.

When the over current condition is removed, the output voltage will return to the regulated value.

UVLO Protection

Undervoltage lock out protection (UVLO) monitors the voltage of the V_{REG5} pin. When the V_{REG5} voltage is lower than UVLO threshold voltage, the TPS56528 is shut off. This protection is non-latching.

Thermal Shutdown

TPS56528 monitors the temperature of itself. If the temperature exceeds the threshold value (typically 165°C), the device is shut off. This is non-latch protection.



TYPICAL CHARACTERISTICS

VIN = 12 V, (unless otherwise noted).





Figure 1. SUPPLY CURRENT vs JUNCTION TEMPERATURE






Figure 3. EN CURRENT vs EN VOLTAGE




Figure 4. 1.05-V OUTPUT VOLTAGE vs OUTPUT CURRENT




Figure 5. 1.05-V OUTPUT VOLTAGE vs INPUT VOLTAGE






Figure 6. 1.05-V, LOAD TRANSIENT RESPONSE

TEXAS INSTRUMENTS

TYPICAL CHARACTERISTICS (continued)

VIN = 12 V, (unless otherwise noted).





 $I_{OUT} \mbox{-} \mbox{-} \mbox{Output Current (A)} \\ \mbox{Figure 9. LIGHT LOAD EFFICIENCY vs OUTPUT CURRENT} \\$

0.01

0.001




Figure 11. SWITCHING FREQUENCY vs OUTPUT CURRENT




Figure 8. EFFICIENCY vs OUTPUT CURRENT




Figure 10. SWITCHING FREQUENCY vs INPUT VOLTAGE





Figure 12. VFB VOLTAGE vs JUNCTION TEMPERATURE



TYPICAL CHARACTERISTICS (continued)

VIN = 12 V, (unless otherwise noted).









Figure 14. VOLTAGE RIPPLE AT INPUT (I_O = 5 A)



Ambient Temperature (°C)
Figure 15. OUTPUT CURRENT vs
AMBIENT TEMPERATURE



DESIGN GUIDE

Step-By-Step Design Procedure

To begin the design process, the user must know a few application parameters:

- Input voltage range
- Output voltage
- Output current
- Output voltage ripple
- Input voltage ripple




Figure 16. Shows the schematic diagram for this design example.

Output Voltage Resistors Selection

The output voltage is set with a resistor divider from the output node to the VFB pin. It is recommended to use 1% tolerance or better divider resistors. Start by using Equation 2 to calculate V_{OUT} .

To improve efficiency at light loads consider using larger value resistors, high resistance is more susceptible to noise, and the voltage errors from the VFB input current are more noticeable.

$$V_{OUT} = 0.60 \times \left(1 + \frac{R1}{R2}\right) \tag{2}$$

Output Filter Selection

The output filter used with the TPS56528 is an LC circuit. This LC filter has double pole at:

$$\mathsf{F}_\mathsf{P} = \frac{1}{2\pi\sqrt{\mathsf{L}_\mathsf{OUT} \times \mathsf{C}_\mathsf{OUT}}} \tag{3}$$

At low frequencies, the overall loop gain is set by the output set-point resistor divider network and the internal gain of the TPS56528. The low frequency phase is 180 degrees. At the output filter pole frequency, the gain rolls off at a −40 dB per decade rate and the phase drops rapidly. D-CAP2™ introduces a high frequency zero that reduces the gain roll off to −20 dB per decade and increases the phase to 90 degrees one decade above the zero frequency. The inductor and capacitor selected for the output filter must be selected so that the double pole of Equation 3 is located below the high frequency zero but close enough that the phase boost provided be the high frequency zero provides adequate phase margin for a stable circuit. To meet this requirement use the values recommended in Table 1



Table 1. Recon	nmended Com	ponent Values
----------------	-------------	---------------

Output				C4 (pF) ⁽¹⁾			C7 + C8		
Voltage (V)	R1 (kΩ)	R2 (kΩ)	MIN	TYP	MAX	MIN	TYP	MAX	(μF)
1	33.2	49.9	5	33	100	1.0	1.5	4.7	20 - 68
1.05	37.4	49.9	5	33	100	1.0	1.5	4.7	20 - 68
1.2	49.9	49.9	5	22	47	1.0	1.5	4.7	20 - 68
1.5	75.0	49.9	5	15	33	1.0	1.5	4.7	20 - 68
1.8	100	49.9	5	10	22	1.0	1.5	4.7	20 - 68
2.5	158	49.9	5	10	22	1.5	2.2	4.7	20 - 68
3.3	226	49.9	2	5	15	1.5	2.2	4.7	20 - 68
5	365	49.9	2	5	10	2.2	3.3	4.7	20 - 68
6.5	487	49.9	2	2	10	2.2	3.3	4.7	20 - 68

(1) Optional

For higher output voltages at or above 1.8 V, additional phase boost can be achieved by adding a feed forward capacitor (C4) in parallel with R1

The inductor peak-to-peak ripple current, peak current and RMS current are calculated using Equation 4, Equation 5 and Equation 6. The inductor saturation current rating must be greater than the calculated peak current and the RMS or heating current rating must be greater than the calculated RMS current. Use 650 kHz for f_{SW} .

Use 650 kHz for f_{SW} . Make sure the chosen inductor is rated for the peak current of Equation 5 and the RMS current of Equation 6.

$$II_{P-P} = \frac{V_{OUT}}{V_{IN(MAX)}} \times \frac{V_{IN(MAX)} - V_{OUT}}{L_O \times f_{SW}}$$
(4)

$$II_{\mathsf{PEAK}} = I_{\mathsf{O}} + \frac{II_{\mathsf{P-P}}}{2} \tag{5}$$

$$I_{LO(RMS)} = \sqrt{I_0^2 + \frac{1}{12}II_{P-P}^2}$$
 (6)

For this design example, the calculated peak current is 5.51 A and the calculated RMS current is 5.01 A. The inductor used is a TDK SPM6530-1R5M100 with a peak current rating of 11.5 A and an RMS current rating of 11 A.

The capacitor value and ESR determines the amount of output voltage ripple. The TPS56528 is intended for use with ceramic or other low ESR capacitors. Recommended values range from 20µF to 68µF. Use Equation 7 to determine the required RMS current rating for the output capacitor.

$$I_{Co(RMS)} = \frac{V_{OUT} \times (V_{IN} - V_{OUT})}{\sqrt{12} \times V_{IN} \times L_O \times f_{SW}}$$
(7)

For this design two TDK C3216X5R0J226M 22 μ F output capacitors are used. The typical ESR is 2 m Ω each. The calculated RMS current is 0.284 A and each output capacitor is rated for 4A.

Input Capacitor Selection

The TPS56528 requires an input decoupling capacitor and a bulk capacitor is needed depending on the application. A ceramic capacitor over 10 μ F is recommended for the decoupling capacitor. An additional 0.1 μ F capacitor (C3) from pin 8 to ground is optional to provide additional high frequency filtering. The capacitor voltage rating needs to be greater than the maximum input voltage.

Bootstrap Capacitor Selection

A 0.1 μ F ceramic capacitor must be connected between the VBST to SW pin for proper operation. It is recommended to use a ceramic capacitor.



VREG5 Capacitor Selection

A 0.47-µF. ceramic capacitor must be connected between the VREG5 to GND pin for proper operation. It is recommended to use a ceramic capacitor.

THERMAL INFORMATION

This 8-pin DDA package incorporates an exposed thermal pad that is designed to be directly to an external heatsink. The thermal pad must be soldered directly to the printed board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the exposed thermal pad and how to use the advantage of its heat dissipating abilities, see the Technical Brief, PowerPAD™ Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD™ Made Easy, Texas Instruments Literature No. SLMA004.

The exposed thermal pad dimensions for this package are shown in the following illustration.





Figure 17. Thermal Pad Dimensions



LAYOUT CONSIDERATIONS

- 1. The TPS56528 can supply large load currents up to 5 A, so heat dissipation may be a concern. The top side area adjacent to the TPS56528 should be filled with ground as much as possible to dissipate heat.
- 2. The bottom side area directly below the IC should a dedicated ground area. It should be directed connected to the thermal pad of the using vias as shown. The ground area should be as large as practical. Additional internal layers can be dedicated as ground planes and connected to vias as well.
- 3. Keep the input switching current loop as small as possible.
- 4. Keep the SW node as physically small and short as possible to minimize parasitic capacitance and inductance and to minimize radiated emissions. Kelvin connections should be brought from the output to the feedback pin of the device.
- 5. Keep analog and non-switching components away from switching components.
- 6. Make a single point connection from the signal ground to power ground.
- 7. Do not allow switching current to flow under the device.
- 8. Keep the pattern lines for VIN and PGND broad.
- 9. Exposed pad of device must be connected to PGND with solder.
- 10. VREG5 capacitor should be placed near the device, and connected PGND.
- 11. Output capacitor should be connected to a broad pattern of the PGND.
- 12. Voltage feedback loop should be as short as possible, and preferably with ground shield.
- 13. Lower resistor of the voltage divider which is connected to the VFB pin should be tied to SGND.
- 14. Providing sufficient via is preferable for VIN, SW and PGND connection.
- 15. PCB pattern for VIN, SW, and PGND should be as broad as possible.
- 16. VIN Capacitor should be placed as near as possible to the device.



VIA to Ground Plane

Figure 18. PCB Layout



REVISION HISTORY

Cł	hanges from Revision April 2013 (*) to Revision A	Page
•	已将器件状态从:产品预览改为:生产	1



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

www.ti.com

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
TPS56528DDA	ACTIVE	SO PowerPAD	DDA	8	75	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	56528	Samples
TPS56528DDAR	ACTIVE	SO PowerPAD	DDA	8	2500	RoHS & Green	SN	Level-2-260C-1 YEAR	-40 to 125	56528	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.





10-Dec-2020

www.ti.com 5-Jan-2022

TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS56528DDAR	SO Power PAD	DDA	8	2500	330.0	12.8	6.4	5.2	2.1	8.0	12.0	Q1

www.ti.com 5-Jan-2022



*All dimensions are nominal

	Device Package Ty		Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
I	TPS56528DDAR	SO PowerPAD	DDA	8	2500	366.0	364.0	50.0	

PACKAGE MATERIALS INFORMATION

www.ti.com 5-Jan-2022

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)	
TPS56528DDA	DDA	HSOIC	8	75	517	7.87	635	4.25	



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4202561/G



DDA (R-PDSO-G8)

PowerPAD ™ PLASTIC SMALL-OUTLINE



NOTES: A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5-1994.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 for information regarding recommended board layout. This document is available at www.ti.com http://www.ti.com.
- E. See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.
- F. This package complies to JEDEC MS-012 variation BA

PowerPAD is a trademark of Texas Instruments.



DDA (R-PDSO-G8)

PowerPAD™ PLASTIC SMALL OUTLINE

THERMAL INFORMATION

This PowerPAD package incorporates an exposed thermal pad that is designed to be attached to a printed circuit board (PCB). The thermal pad must be soldered directly to the PCB. After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For additional information on the PowerPAD package and how to take advantage of its heat dissipating abilities, refer to Technical Brief, PowerPAD Thermally Enhanced Package, Texas Instruments Literature No. SLMA002 and Application Brief, PowerPAD Made Easy, Texas Instruments Literature No. SLMA004. Both documents are available at www.ti.com.

The exposed thermal pad dimensions for this package are shown in the following illustration.



Exposed Thermal Pad Dimensions

4206322-6/L 05/12

NOTE: A. All linear dimensions are in millimeters



DDA (R-PDSO-G8)

PowerPAD™ PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. This package is designed to be soldered to a thermal pad on the board. Refer to Technical Brief, PowerPad Thermally Enhanced Package, Texas Instruments Literature No. SLMA002, SLMA004, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at www.ti.com http://www.ti.com. Publication IPC-7351 is recommended for alternate designs.
- E. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Example stencil design based on a 50% volumetric metal load solder paste. Refer to IPC-7525 for other stencil recommendations.
- F. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

PowerPAD is a trademark of Texas Instruments.



重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022,德州仪器 (TI) 公司