

# UCC2541 72-W Synchronous Buck Converter



February 2006

System Power MAN

SLUU239

# UCC2541 72-W Synchronous Buck Converter

# **User's Guide**

Literature Number: SLUU239 February 2006





# UCC2541 72-W Synchronous Buck Converter

#### 1 Introduction

The UCC2541 is a voltage-mode synchronous-buck PWM controller for high current output converters of 30 A or higher. Higher efficiencies are achieved utilizing TI's proprietary Predictive Gate Drive<sup>™</sup> technology. The UCC2541 is based on the parent device UCC2540 which is a secondary side post-regulator for isolated applications. This controller provides a bootstrap circuit to allow the use of an N-channel MOSFET as the topside buck switch, reducing conduction losses and increasing silicon device utilization. By controlling the turn-off and turn-on of the main and the synchronous switch, Predictive Gate Drive<sup>™</sup> minimizes MOSFET body diode conduction and reverse recovery losses for higher efficiency, lower EMI and thermal improvements. This user's guide provides details on a single-phase synchronous-buck power converter with an input of nominal 12 V and an output of 1.8 V rated for 40-A continuous current output.

#### 2 Applications

High Current (>30 A) Point-of-Load Converters for:

- Servers
- Telecom Equipment
- Power Supply Modules

#### 3 Features

- V<sub>IN</sub> = 9.0 V to 15 V
- V<sub>OUT</sub> = 1.8 V +/-3%
- $I_{OUT} = 0 \text{ A to } 40 \text{ A}$
- Efficiency >80% at 40 A
- Output Voltage Ripple < 2%
- Power Semiconductor Devices
- Parallel MOSFETs for Higher Power
- External Synchronization Input
- Remote Shutdown Input



# 4 Electrical Performance Specification

	PARAMETER	TEST CONDITION	MIN	ТҮР	MAX	UNITS	
V <sub>IN</sub>	Input Voltage	Over lo range	9	12	15		
UVLO		V <sub>IN</sub> increasing	8.0	8.5	9.0	V	
	Under-voltage lockout (mode 1)	V <sub>IN</sub> decreasing	7.5	8.0	8.5		
		Hysteresis	0.3	0.5	0.8		
Ι <sub>Ο</sub>	Output current	60°C, 200 LFM airflow 25°C, natural convection	0		40	А	
f <sub>S</sub>	Switching frequency		270	300	330	kHz	
$\Delta \text{REG}_{\text{LINE}}$	Line regulation	Over V <sub>IN</sub> range			5	mV	
$\Delta \text{REG}_{\text{LOAD}}$	Load regulation	Over I <sub>O</sub> range			5	IIIV	
AREC	Total output variation	Includes set point, line, load			3	%	
$\Delta \text{REG}_{\text{TOT}}$			1.746	1.800	1.854	V	
~	Efficiency	Peak I <sub>OUT</sub> = 15A, $V_{IN}$ = 9 V		90%			
η		Full-load $I_{OUT}$ = 40 A, $V_{IN}$ = 12 V		83%			
V <sub>R</sub>	V <sub>OUT</sub> ripple (pk-pk)	20-MHz bandwidth limited		2		%/V <sub>O</sub>	
Ι <sub>Ο</sub>	Over-current threshold	trip Reset, followed by auto-recovery		52		А	
t <sub>TR</sub>		1 A/up 10 to 00%		30		μs	
$\Delta V_{TR}$	<ul> <li>Transient response</li> </ul>	1 A/µs 10 to 90% I <sub>O(max)</sub>		120		mV	

# Table 1. Electrical Performance Specification






Figure 1. EVM Schematic

SLUU239–February 2006 Submit Documentation Feedback



#### 6 Description

The HPA127 EVM module is a high-current single-phase 300-kHz synchronous buck power converter with a nominal 12-V input between 9 V and 15 V and an output of 1.8 V rated for 40-A continuous current output.

The converter can be divided into functional blocks:

- Device Bias: The converter is configured for mode 1 operation where the bias voltage is 8.5 V or higher and is compatible with a 12-V<sub>DC</sub> bias supply. Bias is supplied directly from the converter input voltage to VDD. The low-side drive bias, V<sub>DRV</sub> = 7.2 V, is generated through a linear regulator internal to the UCC2541. The high-side gate drive, BST, is derived from V<sub>DRV</sub> through two diode drops and is boosted by a flying capacitor and diode combination (D1/C1) using the synchronous rectifier drive, G2. V<sub>REF</sub> is derived through a linear regulator internal to the UCC2541 from V<sub>DRV</sub>.
- **Timing:** The timing section sets the oscillator capacitor charging current. Capacitors set the ramp timing and the synchronous rectifier gate cutoff time.
- **Power Train:** The power switches consists of two parallel high side control, Q1/Q2, and two parallel low-side synchronous rectifiers, Q3/Q4. The input filter is a capacitive filter with C6 as bulk capacitance and four ceramic capacitors to filter ripple current. The output filter consists of a low DCR, high current inductor and five low ESR specialty polymer (SP) aluminum electrolytic capacitors.
- **Control Loop Compensation:** A type III network compensates the voltage regulation loop. TP16/TP17 and R12 provide a point to inject a signal and make voltage control loop measurements. Overcurrent is detected by voltage across the DCR of the output inductor.
- Auxiliary Functions (Synchronization, Tracking, Shutdown): Synchronization and tracking inputs are pulled up to the reference voltage through R7 and R8 respectively. The Synchronization input signal is buffered by a single non-inverting gate and triggers on the falling edge. The converter can be shutdown by applying the reference voltage, V<sub>REF</sub>, to the shutdown pin, pulling the soft-start pin to ground.

#### CAUTION Synchronization frequency should be NO LESS than 360 kHz to avoid possible catastrophic failure of the converter.



## 7 Test Setup

The basic test setup recommended for evaluating the UCC2541EVM is shown below in Figure 2. The test setup consists of an input power supply, output loads, and meters to measure current and voltage on the input and output. Calibrated low-ohm resistors are recommended to measure the currents.




Figure 2. Recommended EVM test configuration.

# 7.2 Output Loads (LOAD)

For the output load,  $V_{OUT}$ , a programmable electronic load, LOAD, set to constant resistance mode and capable of sinking 60 A at 1.8 V is used. Constant resistance mode for the load requires that the output voltage is sensed at the output of the converter. Using a dc voltmeter, measure the output voltage,  $V_{OUT}$ , directly at the output test points  $V_{OUT+}$  (TP10) and  $V_{OUT-}$  (TP12). Measure the output current,  $I_{OUT}$ , with a shunt connected in series with return of the load. The LOAD shoud have leads of sufficient gauge to minimize voltage drop between device under test and LOAD. A cable length less than four feet at 4 gauge (8 gauge minimum) is recommended.

## 7.3 Input Power Supply (VIN)

The input voltage source shall be a variable dc source capable of supplying between 0  $V_{DC}$  and 15.5  $V_{DC}$ , at no less than 10  $A_{DC}$ . Using a dc voltmeter, measure the input voltage,  $V_{IN}$ , directly at the input test points  $V_{IN+}$  (TP3) and  $V_{IN-}$  (TP6). For fault protection to the EVM, limit the source current to not more than 10  $A_{DC}$ . Measure the input current,  $I_{IN}$ , with a shunt connected in series with the return of the source supply as shown. Use of the current shunt requires that the dc source remote sense lines be connected to the input test points for accurate voltage setting.



#### Test Setup

## 7.4 Network Analyzer (not shown)

To measure the closed loop response of the auxiliary output, a network analyzer can be connected directly across TP16 and TP17. The  $49.9-\Omega$  resistor (R12) between the output load and the voltage feedback allows for non-invasive measurement of the control to output loop response.

#### 7.5 Power Up/Down Sequence

The following procedure is recommended primarily for powering up and shutting down the UCC2541 EVM. Never walk away from a powered evaluation module for extended periods of time.

#### 7.6 Power Up Sequence

- Turn on the electronic load, LOAD. Set the electronic load to 4 A.
- Turn on the input power supply. Starting with the input dc power supply at the zero volt setting, slowly increase the voltage to the EVM operating range, 9.0 V to 15 V.
- The converter begins operating when the input voltage is at or before 9.0 V maximum, measured on the VIN DMM.

#### 7.7 Power Down Sequence

- Decrease the input power supply to 0 V and turn it off.
- Turn off electronic load.




Figure 3. Test Points for HPA127 Evaluation (TOP)

**Note:** Input/output test points input voltage test points, TP3/TP6, and output voltage test points, TP10/TP12 are mounted on the bottom side of the PCB.


# Table 2. EVM TESTPOINTS

TEST POINT	NAME	DESCRIPTION		
Bias				
TP1	VIN	Power supply input voltage to the converter.		
TP2	Boost	High-Side Control MOSFET driver supply pin.		
TP4	Reference	3.3-V reference.		
TP13	VDRV	7.2-V MOSFET driver regulated voltage		
Timing				
TP7	G2C	Low-side synchronous rectifier cutoff. Discharges with G1 risinedge in normal operation. Turns off the SR after a fixed intervof 3 times the ramp time during zero duty-cycle conditions.		
TP8	RAMP	Oscillator PWM ramp		
TP15	SOFTSTART	Voltage output soft start ramp. Shut down is active when this p is driven low by shutdown circuit.		
Power Train				
TP3	VIN (input)	Power supply voltage to the converter. Common point for input measurement and input power supply remote sense.		
TP5	G1	High-side control MOSFET gate drive.		
TP6	Power ground (input)	Return for power supply voltage to the converter. Common point for input measurement and input power supply remote sense.		
TP9	Switch node	Switching or phase node common between control and synchronous rectifier MOSFETs.		
TP10	V <sub>OUT</sub> (output)	Converter output voltage to the load. Common point for output voltage measurement and load remote sense.		
TP11	G2	Low-side synchronous rectifier gate drive.		
TP12	Power ground (output)	Return for converter output voltage to the load. Common poir for output voltage measurement and load remote sense.		
TP16	V <sub>OUT</sub> sense low (loop measurement)	Low-side connection point for network analyzer.		
TP17	V <sub>OUT</sub> sense high (loop measurement)	High-side connection point for network analyzer.		
TP18	Compensation	Voltage/current error amp compensation pin.		
External Controls				
TP14	Tracking	Tracking input to the voltage error amp.		
TP19	Shutdown	Shutdown input. 3.3 V applied to this point shuts the converte down.		
TP20	Synchronization	Synchronization input. Synchronizes oscillator to system clock.		
Grounds				
TP21, TP22, TP23, TP24	Signal ground			
TP25, TP26	Power ground			



# 8 Performance Data and Characteristic Curves

## 8.1 Characteristic Curves





# 8.2 Typical Waveforms






Figure 8.

Turn-On Trajectory







**Output Voltage Ripple** 











Predictive Gate Drive












#### **Overcurrent Protection**





# 9 EVM Assembly Drawing and PCB Layout.




Figure 15. Top Assembly

219T	TP6 <b>8</b> 97
<u>। (17</u> 18)	TP3 [297]

Figure 16. Bottom Assembly




Figure 17. Layer 1 (Top)




Figure 18. Layer 2 (Inner 1)




Figure 19. Layer 3 (Inner 2)




Figure 20. Layer 4 (Bottom)






Figure 21. Top Silk Layer




Figure 22. Bottom Silk Layer

# 

# 10 List of Material

REF	QTY	DESCRIPTION	PART NUMBER	MFR
C1	1	Capacitor, ceramic, 25 V, X7R, ±10%, 0.12 µF, 0805	Std.	Std.
C10	1	Capacitor, ceramic, 25 V, X7R, 10%, 1 µF, 0805	Std.	Std.
C11	1	Capacitor, ceramic, 50 V, C0G, ±5%, 10 nF, 0805	Std.	Std.
C13, C14, C15, C16, C17	5	Capacitor, aluminum, 4 V, 20% (SE series), 220 $\mu\text{F},$ 7343	EEF-SE0G221R	Panasonic
C18, C19	2	Capacitor, ceramic, 16 V, X7R, 10%, 0.47 µF, 0603	Std.	Std.
C2, C3, C4, C5, C12	5	Capacitor, ceramic, 16 V, X5R, 10%, 10 µF, 1210	Std.	Std.
C20	1	Capacitor, ceramic, 50 V, NPO, 5%, 1.8 nF, 0603	Std.	Std.
C21	1	Capacitor, ceramic, 50 V, C0G, 5%, 390 pF, 0603	Std.	Std.
C22	1	Capacitor, ceramic, 6.3 V, X5R, 10%, 1 µF, 0603	Std.	Std.
C23	1	Capacitor, ceramic, 50 V, NPO, 5%, 56 pF, 0603	Std.	Std.
C24	1	Capacitor, ceramic, 50 V, C0G, 5%, 2.7 nF, 0603	Std.	Std.
C25	1	Capacitor, ceramic, 16 V, X7R, 10%, 10 nF, 0603	Std.	Std.
C6	1	Capacitor, aluminum, SM, ±20%, 25 V, 470 $\mu\text{F},$ 0.406 x 0.457 inch	EEV-FK1E471P	Panasonic
C7	1	Capacitor, ceramic, 16 V, X7R, 10% , 0.1 µF, 0603	Std.	Std.
C8	1	Capacitor, ceramic, 50 V, NPO, 5%, 560 pF, 0603	Std.	Std.
C9	1	Capacitor, ceramic, 50 V, NPO, 5%, 220 pF, 0603	Std.	Std.
D1	1	Diode, schottky, 1 A, 40 V, SOD123	1N5819	Std.
HS1, HS2	2	Heatsink, DIP, 0.530 x 0.25 in.	619453B00250	Aavid
J1, J2, J3, J4	4	Copper, single barrel, one-hole, straight tongue (fixed) lug, #14 - #4 AWG wire, 1/4 stud hole, 1.55 x 0.50 in	CX70-14-C	Panduit
L1	1	Inductor, SMT, 62 A, 0.85 mΩ, 0.680 $\mu H,$ 0.790 x 0.770 in.	SER2010- 681MLB	Coilcraft
Q1, Q2	2	Transistor, MOSFET, 20 V, 59 A, 5.6mΩ, MP Can	IRF6633	IR
Q3, Q4	2	Transistor, MOSFET, 30 V, 180 A, 1.3 mΩ, MX Can	IRF6635	IR
Q5	1	Transistor, NPN, 40 V, 1 A, SOT-23	MMBT2222A	Std.
R1, R4	2	Resistor, chip, 1/16 W, 1%, 0 Ω, 0603	Std.	Std.
R11	1	Resistor, chip, 1/16 W, 1%, 2.55 kΩ, 0603	Std.	Std.
R12	1	Resistor, chip, 1/16 W, 1%, 49.9 Ω, 0603	Std.	Std.
	•			

# Table 3. List of Materials

REF	QTY	DESCRIPTION	PART NUMBER	MFR
R13, R14	2	Resistor, chip, 1/16 W, 1%, 61.9 kΩ, 0603	Std.	Std.
R15	1	Resistor, chip, 1/16 W, 1%, 316 kΩ, 0603	Std.	Std.
R17	1	Resistor, chip, 1/16 W, 1%, 3.48 kΩ, 0603	Std.	Std.
R18	1	Resistor, chip, 1/16 W, 1%, 10 Ω, 0603	Std.	Std.
R19	1	Resistor, chip, 1/16 W, 1%, 13.3 kΩ, 0603	Std.	Std.
R2, R6, R7, R8, R16, R22	6	Resistor, chip, 1/16 W, 1%, 10 kΩ, 0603	Std.	Std.
R20	1	Resistor, chip, 1/16 W, 1%, 287 kΩ, 0603	Std.	Std.
R21	0	Resistor, chip, 1/16 W, yy%, nopop, 0603	Std.	Std.
R3, R10	2	Resistor, chip, 1/16 W, 1%, 20 kΩ, 0603	Std.	Std.
R5	1	Resistor, chip, 1/8 W, 1%, 14.3 Ω, 1206	Std.	Std.
R9	1	Resistor, chip, 1/16 W, yy%, 787 Ω, 0603	Std.	Std.
TP1, TP2, TP3, TP4, TP5, TP6, TP7, TP8, TP9, TP10, TP11, TP12, TP13, TP14, TP15, TP16, TP17, TP18, TP19, TP20, TP21, TP22, TP23, TP24, TP25, TP26	26	Test point, SMT, 0.105 x 0.040	5015	
U1	1	IC, Digital Power Controller For Power Supply Applications, PWP20	UCC2541PWP	TI
U2	1	IC, single inverter, SC-70	SN74LVC1GU0 4DCKx	ТІ
	1	PCB, 3.6 x 2.5 x 0.062 in.	HPA127	Any
	2	Machine screw, hex head, 1/4-20, 3/8 in., steel		
	2	Nut, hex, 1/4-20, steel,		
	2	Washer, flat, 1/4-20, steel,		
	1	Epoxy, thermal adhesive	3880	Loctite

# Table 3. List of Materials (continued)

#### 11 Reference

• Data Sheet, UCC2541 High-Efficiency Secondary-Side Synchronous Buck PWM Controller, Texas Instruments Literature Number SLUS539

#### **EVALUATION BOARD/KIT IMPORTANT NOTICE**

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

TI currently deals with a variety of customers for products, and therefore our arrangement with the user is not exclusive.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit <u>www.ti.com/esh</u>.

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

#### **FCC Warning**

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

#### **EVM WARNINGS AND RESTRICTIONS**

It is important to operate this EVM within the input voltage range of 0 V to 15 V and the output voltage range of 0 V to 1.8 V.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 50° C. The EVM is designed to operate properly with certain components above 50° C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2006, Texas Instruments Incorporated

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Telephony	www.ti.com/telephony
Low Power Wireless	www.ti.com/lpw	Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2007, Texas Instruments Incorporated