


1 Photo

The photographs below show the PMP12082 Rev B assembly. This circuit was built on a PMP12082 Rev B PCB.

Top side




Bottom side





2 Flyback Efficiency

The efficiency data is shown in the tables below. J1 and J4 are opened during the test. Output current is drawn from J3.



V_{in}: 120V_{AC}/60Hz from Line1 to Line2

Vin(AC)	lin(A)	Pin(W)	PF	Vout(V)	lout(A)	Pout(W)	Eff (%)
120.08	0.2317	13.339	0.479	7.01	1.404	9.84	73.78%
120.11	0.2045	11.434	0.466	6.98	1.204	8.40	73.50%
120.15	0.1744	9.511	0.454	6.95	1.002	6.96	73.22%
120.19	0.1420	7.554	0.443	6.92	0.801	5.54	73.38%
120.21	0.1088	5.623	0.430	6.90	0.601	4.15	73.75%
120.23	0.0755	3.744	0.413	6.89	0.400	2.76	73.61%
120.24	0.0588	2.824	0.400	6.89	0.299	2.06	72.95%
120.26	0.0418	1.929	0.383	6.90	0.200	1.38	71.54%
120.28	0.0237	1.021	0.359	6.93	0.099	0.69	67.20%
120.30	0.0140	0.570	0.338	6.93	0.048	0.33	58.39%
120.31	0.0036	0.119	0.275	6.89	0.000	0.00	0.00%

PMP12082 Rev B Test Results



V_{in}: 240V_{AC}/50Hz from Line1 to Line2

Vin(AC)	lin(A)	Pin(W)	PF	Vout(V)	lout(A)	Pout(W)	Eff (%)
240.00	0.1433	13.593	0.395	6.99	1.403	9.81	72.15%
240.00	0.1248	11.646	0.389	6.96	1.204	8.38	71.95%
239.90	0.1060	9.699	0.381	6.93	1.004	6.96	71.74%
240.00	0.0868	7.756	0.372	6.92	0.803	5.56	71.64%
240.00	0.0678	5.875	0.361	6.90	0.603	4.16	70.82%
240.00	0.0479	3.989	0.347	6.89	0.400	2.76	69.09%
240.00	0.0379	3.059	0.336	6.88	0.300	2.06	67.47%
240.00	0.0273	2.115	0.323	6.87	0.200	1.37	64.96%
240.00	0.0161	1.172	0.303	6.85	0.100	0.69	58.45%
239.90	0.0103	0.706	0.287	6.84	0.051	0.35	49.40%
239.90	0.0033	0.161	0.205	6.83	0.000	0.00	0.00%




3 Thermal Images

The thermal images below show a top view and bottom view of the board under $120V_{AC}/60Hz$ and $692V_{DC}$ input conditions. The ambient temperature was 20° C with no forced air flow. The output was at full load (resistive): 7V/1A from J2, 3.3V/500mA from J5, 3.3V/300mA from J6

V_{in}: L-L 120V_{AC}/60Hz from Line1 to Line2






Spot analysis	Value
Amb Temperature	23.0°C
Area analysis	Value
D1Max	82.0°C
T1Max	50.7°C
Q1Max	59.5°C
U2Max	59.4°C
U4Max	54.0°C



 $V_{\text{in}}\text{: L-L }120V_{\text{AC}}\text{/}60\text{Hz}$ from Line1 to Line2 Bottom Side




Spot analysis	Value
Amb Temperature	23.6°C
Area analysis	Value
SnubberMax	80.2°C
Q2Max	52.7°C



Vin=340VDC from Line1 to Line2 (340VDC is generated by an AC source with a voltage doubler circuit)






Spot analysis	Value
Amb Temperature	23.4°C
Area analysis	Value
D1Max	85.7°C
T1Max	55.3°C
Q1Max	68.6°C
U2Max	62.0°C
U4Max	55.1°C



Vin=340VDC from Line1 to Line2 (340VDC is generated by an AC source with a voltage doubler circuit)

Bottom Side




Spot analysis	Value
Amb Temperature	24.2°C
Area analysis	Value
SnubberMax	79.1°C
Q2Max	60.3°C



Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit)

Top Side




Spot analysis	Value
Amb Temperature	23.4°C
Area analysis	Value
D1Max	86.8°C
T1Max	53.1°C
Q1Max	95.4°C
U2Max	63.6°C
U4Max	56.6°C
D16 Max	93.7°C



Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit)

Bottom Side




Spot analysis	Value
Amb Temperature	23.1°C
Area analysis	Value
SnubberMax	89.7°C
Q2Max	81.5°C




4 Startup Waveforms

The output voltages at startup are shown in the images below with resistive loads. CH1: Voltage after input rectifier, CH1: 3.3V(J6), CH2: 3.3V(J5), CH3: V(C18), CH4: 7V(J2)

4.1 Start Up @ 80VDC input from Line1 to Line2, 7V/1A(J2), 3.3V/500mA(J5) and 3.3V/300mA(J6) outputs.




4.2 Start Up @ 80VDC input from Line1 to Line2 and no loads.






4.3 Start Up @ Vin=340VDC from Line1 to Line2 (340VDC is generated by an AC source with a voltage doubler circuit), 7V/1A(J2), 3.3V/500mA(J5) and 3.3V/300mA(J6) outputs.




4.4 Start Up @ Vin=340VDC from Line1 to Line2 (340VDC is generated by an AC source with a voltage doubler circuit) input and no load.






4.5 Start Up @ Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit), 7V/1A(J2), 3.3V/500mA(J5) and 3.3V/300mA(J6) outputs.



4.6 Start Up @ Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit) input and no load.







5 Output Ripple Voltages


The output ripple voltages are shown in the plots below with resistive loads.

5.1 340VDC input from Line1 to Line2 with 7V/1A(J2), 3.3V/500mA(J5) and 3.3V/300mA(J6) outputs:











5.2 340VDC input from Line1 to Line2 with no loads:


7V ripple:



PMP12082 Rev B Test Results








50.0 mV/div 0 mV offset Timebase 0.0 ms Trigger C3 DC 5.00 ms/div Stop 83.0 mV 100 kS 2.00 MS/s Edge Positive

3.3V(J6) ripple:






Timebase 0.0 ms Trigger C3 DC 5.00 ms/div Stop 41.0 mV 100 kS 2.00 MS/s Edge Positive





5.3 692VDC input from Line1 to Line2 with 7V/1A(J2), 3.3V/500mA(J5) and 3.3V/300mA(J6) outputs:



PMP12082 Rev B Test Results









5.4 692VDC input from Line1 to Line2 with no loads:

7V ripple:



PMP12082 Rev B Test Results








6 Switching Waveforms

The images below show key switching waveforms of PMP12082RevB. The waveforms are measured with 7V/1.4A(J3) resistive load. Other outputs remain no load during the test. CH2: Q2 V_{DS} ; CH4: T1 pin 2 to GND; F1: CH4 - CH2.

6.1 Vin: 80VDC from Line1 to Line2: 7V/1.4A(J3), other outputs remain not loaded.




6.2 Vin: 80VDC from Line1 to Line2: no load for all outputs.






6.3 Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit): 7V/1.4A(J3), other outputs remain not loaded.





6.4 Vin=692VDC from Line1 to Line2 (692VDC is generated by an AC source with a voltage doubler circuit): no load for all outputs.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated