


Sample &

🖥 Buy





ZHCS597B-DECEMBER 2011-REVISED MAY 2015

DAC1282 面向抗震应用的低失真数模转换器

Technical

Documents

1 特性

- 单芯片测试信号生成器
- 缓冲电压输出
- 高性能:
 - 总谐波失真(THD): -125dB (G=1/1至1/8)
 - 信噪比(SNR): 120dB(413Hz BW, G=1/1)
- 模拟和数字增益控制
- 输出频率: 0.488Hz至250Hz
- 正弦,脉冲,和直流(DC)模式
- 数字数据输入模式
- 低导通电阻信号开关
- 同步输入
- 省电模式
- 模拟电源: 5V或者±2.5V
- 数字电源: 1.8V至3.3V
- 功率: 38mW
- 封装方式: 24引脚薄型小尺寸封装(TSSOP)
- 运行温度范围: -50°C至+125°C
- 2 应用
- 能量勘探
- 地震监测系统
- 高精度仪器

3 说明

Tools &

Software

DAC1282是一款全集成数模转换器(DAC),此转换器 可提供低失真,数字合成电压输出,适合于测震设备的 测试。DAC1282可在低功率小型封装内实现非常高的 性能。与高性能ADS1281和ADS1282模数转换器 (ADS)一起,这些器件可以创建一个满足地震数据采集 设备严格要求的测量系统。

Support &

Community

2.2


DAC1282集成了一个数字信号生成器,一个DAC,和 一个可生成正弦波,dc,和脉冲输出电压的输出放大器。

输出频率可编程范围为0.5Hz至250Hz之间并且震级由 模拟和数字控制进行计算。模拟增益和数字增益分别 可在6dB步长和0.5dB步长内调节。模拟增益设置与 ADS1282上那些用于高分辨率增益下测试的设置相匹 配。

DAC1282还提供脉冲输出。用户可对脉冲振幅进行编程,然后由引脚做出选择并进行精确计时。通过采用一个外部比特流样式可生成定制输出信号。

一个信号开关可将DAC输出连接至传感器,此传感器 用于THD和脉冲测试。开关计时受引脚和命令控制。

同步(SYNC)引脚使DAC输出与模数转换器(ADC)采样间隔同步。省电输入会将此器件关闭,从而将功耗减少到毫瓦(microwatt)级。



DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015

目录

1	特性1
2	应用1
3	说明1
4	修订历史记录 2
5	Device Comparison 3
6	Pin Configuration and Functions 3
7	Specifications 4
	7.1 Absolute Maximum Ratings 4
	7.2 ESD Ratings 4
	7.3 Thermal Information 4
	7.4 Electrical Characteristics 5
	7.5 Timing Requirements: Serial Peripheral Interface (SPI) Timing
	7.6 Typical Characteristics
8	Detailed Description 14

	82	Feature Description	16
	8.3	Device Functional Modes	30
	8.4	Programming	31
	8.5	Register Map	33
9	App	ication and Implementation	36
	9.1	Application Information	36
	9.2	Typical Applications	37
10	器件	和文档支持	39
	10.1	Community Resources	. 39
	10.2	商标	39
	10.3	静电放电警告	39
	10.4	术语表	. 39
11	机械	、封装和可订购信息	39

8.1 Overview 14

4 修订历史记录

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

C	hanges from Revision A (September 2012) to Revision B	Page
•	已添加 ADS1282A 器件至数据手册	1
C	hanges from Original (December 2011) to Revision A	Page
•	Updated Figure 16	10
•	Added last paragraph to Signal Output section	
•	Changed t _{CSHD} minimum specification in Table 11	25
•	Changed min, max, and unit columns in Table 12	




www.ti.com.cn



5 Device Comparison

DEVICE	DESCRIPTION
ADS1281	High-resolution ADC
ADS1282	High-resolution ADC with PGA
REF5050	Low-drift 5 V reference

6 Pin Configuration and Functions



Pin Functions

PIN		FUNCTION	DESCRIPTION
NAME	NO.	FUNCTION	DESCRIPTION
AVDD	13, 24	Analog supply	Analog positive power supply
AVSS	14	Analog supply	Analog negative power supply, reference ground
AVSS	23	Analog supply	Analog negative power supply
CAPN	15	Analog	External capacitor connected to VOUTN
CAPP	22	Analog	External capacitor connected to VOUTP
CS	1	Digital input	Serial port chip select
CLK	7	Digital input	Master clock 4.096 MHz
DGND	6	Ground	Key digital ground
DGND	11	Ground	Digital ground
DIN 3 Digital input Serial port data input		Serial port data input	
DOUT	4	Digital output	Serial port data output
DVDD	5	Digital supply	Digital power supply: 1.65 V to 3.6 V
RESET/PWDN	10	Digital input	Reset/power-down input
SCLK	2	Digital input	Serial port shift clock
SW/TD	8	Digital input	Switch control input or bitstream input
SWINN	17	Analog I/O	Switch negative input
SWINP	20	Analog I/O	Switch positive input
SWOUTN	18	Analog I/O	Switch negative output
SWOUTP	19	Analog I/O	Switch positive output
SYNC	9	Digital input	Synchronize input
VOUTN	16	Analog output	Negative voltage output
VOUTP	21	Analog output	Positive voltage output
VREF	12	Analog input	Reference voltage input

7 Specifications

7.1 Absolute Maximum Ratings⁽¹⁾

Over operating free-air temperature range, unless otherwise noted.

		MIN	MAX	UNIT
AVDD to AVSS		-0.3	+5.5	V
AVSS to DGND		-2.8	+0.3	V
DVDD to DGND		-0.3	+3.6	V
Input current continuous		-10	+10	mA
Analog input/output voltage	AV	/SS – 0.3	AVDD + 0.3	V
Switch current		-60	+60	mA
Digital input voltage to DGND		-0.3	DVDD + 0.3	V
Operating temperature range		-50	+125	°C
Storage temperature, T _{stg}		-60	+150	°C

(1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum conditions for extended periods may degrade device reliability. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those specified is not implied.

7.2 ESD Ratings

			VALUE	UNIT
V	Electrostatic	Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 ⁽¹⁾	±2000	M
V(ESD)	discharge	Charged-device model (CDM), per JEDEC specification JESD22-C101 ⁽²⁾	±500	v

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Thermal Information

	THERMAL METRIC ⁽¹⁾		
		24 PINS	UNIT
$R_{ extsf{ heta}JA}$	Junction-to-ambient thermal resistance	78.3	
R _{0JC(top)}	Junction-to-case (top) thermal resistance	12.1	
$R_{ extsf{ heta}JB}$	Junction-to-board thermal resistance	33.8	°C/W
Ψ _{JT}	Junction-to-top characterization parameter	0.3	°C/W
Ψ _{JB}	Junction-to-board characterization parameter	33.5	
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	N/A	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.

7.4 Electrical Characteristics

Minimum and maximum specifications are at $T_A = -40^{\circ}$ C to +85°C. Typical specifications are at $T_A = +25^{\circ}$ C, AVDD = +2.5 V, AVSS = -2.5 V, $f_{CLK} = 4.096$ MHz, $V_{REF} = 5$ V, and DVDD = 3.3 V (unless otherwise noted). Refer to Figure 50. DAC1282A supports gains = 1/1, 1/4, and 1/16 only.

	PARAMETER		TEST CONDITIONS	MIN 1	ΥP	MAX	UNIT
ANALO	G OUTPUT (VOUTP, VOUTN)		1			L	
	Full-scale output voltage ⁽¹⁾		Gain = 1/1 to 1/64	±V _{REF}	/2 × gain		V
	Output common-mode voltag	e ⁽²⁾			-0.1		V
	Differential output impedance)			1.6		Ω
CLOAD	Capacitive load					2	nF
R _{LOAD}	Resistive load			100			Ω
	Output current limit ⁽³⁾				±60		mA
			T _A = +25°C		2		
	High-Z output leakage		T _A = +85°C		50		nA
DC PER	FORMANCE (Excluding Pulse	Mode)					
	Gain error		Gain = 1/1		±0.1%	±0.75%	
	Gain match		Relative to gain = 1/1		±0.05%	±0.5%	
	Gain drift				2		ppm/°C
	Offset		Gain = 1/1 to 1/64	±(7/g	ain) + 50	±(75/gain) + 300	ppm FSR ⁽⁴⁾
	Offset drift				1.5		ppm FSR/°C
AC PER	FORMANCE						
-		DAC1282	Gain = 1/1		-125	-118	dB
			Gain = 1/2, 1/4, 1/8		-125		dB
			Gain = 1/16		-123		dB
THD	Total harmonic distortion ⁽⁵⁾		Gain = 1/32		-115		dB
			Gain = 1/64		-111		dB
		DAC1282A	Gain = 1/1		-118	-106	dB
		DAC1282A	Gain = 1/4, 1/16		-118		dB
			Gain = 1/1	116	120		dB
			Gain = 1/2		119		dB
			Gain = 1/4		117		dB
SNR	Signal-to-noise ratio ⁽⁶⁾		Gain = 1/8		114		dB
	Output frequency		Gain = 1/16		110		dB
			Gain = 1/32		106		dB
			Gain = 1/64		100		dB
				0.4883		250	Hz
	Digital gain		0.5-dB steps	Full mute		0	dB
DED	Dowor oupply rejection	AVDD, AVSS	60 Hz oo goin $-\frac{1}{9}$		85		dB
PSR	Power-supply rejection	DVDD	60-Hz ac, gain = 1/8		120		dB

(1) Full-scale differential output voltage: $V_{OUT} = (VOUTP - VOUTN) = \pm V_{REF}/2 \times Gain$. Gain is the DAC analog gain.

(2) Output common-mode voltage scales with analog supply voltage: $V_{COM} = 0.48 \times (AVDD - AVSS) + AVSS$.

(3) Sink or source current limit of VOUTP and VOUTN.

(4) FSR – full-scale range = $V_{REF} \times gain$.

(5) THD = total harmonic distortion. THD is measured by the ADS1282, and is the sum of first nine harmonics using complementing gain. f_{OUT} = 31.25 Hz, V_{OUT} – 0.5 dBFS, no load.

(6) SNR = signal-to-noise ratio. SNR is measured by the ADS1282 over a 413-Hz bandwidth using complementing gain. f_{OUT} = 31.25 Hz and V_{OUT} – 0.5 dBFS.

Electrical Characteristics (continued)

Minimum and maximum specifications are at $T_A = -40^{\circ}$ C to +85°C. Typical specifications are at $T_A = +25^{\circ}$ C, AVDD = +2.5 V, AVSS = -2.5 V, f_{CLK} = 4.096 MHz, V_{REF} = 5 V, and DVDD = 3.3 V (unless otherwise noted). Refer to Figure 50. DAC1282A supports gains = 1/1, 1/4, and 1/16 only.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
PULSE MODE					
Output levels	31 steps, approximate 3 dB per step	±0.0195		±2.5	V
Gain error			±0.1%	±0.75%	
Gain drift			3		ppm/°C
Offset			±0.5	±3	mV
Offset drift			3		µV/°C
Output noise ⁽⁷⁾			1.5		μV _{RMS}
Slew rate			5		V/µs
Settling time	0.1% final value		25		μs
DC MODE	- I	L		4	
Resolution			24		Bits
Step response			100		μs
	Gain = 1/1		1.3		μV _{RMS}
	Gain = 1/2		1.4		μV _{RMS}
	Gain = 1/4		1.8		μV _{RMS}
DC noise ⁽⁸⁾	Gain = 1/8		2.7		μV _{RMS}
	Gain = 1/16		4.7		μV _{RMS}
	Gain = 1/32		8.5		μV _{RMS}
	Gain = 1/64		16		μV _{RMS}
DIGITAL DATA MODE					I INIG
Data clock rate			f _{CLK} /16		Hz
Ones-density full-scale modulation	+FS and –FS, respectively	25%	OLK -	75%	
Signal bandwidth	-3 dB		8.2		kHz
REFERENCE VOLTAGE INPUT (V _{REF})			-		
Reference voltage, V _{REF} = VREF – AVSS		2.4	5	AVDD + 0.25	V
	Operating		220		kΩ
Reference input impedance	Power-down		10		MΩ
SIGNAL SWITCH					
Signal range		AVSS		AVDD	V
Current	Continuous	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		±50	mA
Differential on-resistance	V_{SWIN} , $V_{SWOUT} = 0 V$		2.8	200	Ω
Differential on-resistance flatness	V _{SWIN} , V _{SWOUT} = AVDD to AVSS		0.7		Ω
On-resistance match between outputs	V_{SWIN} , $V_{SWOUT} = 0 V$		0.04		Ω
•	$T_A = +25^{\circ}C$		±0.1		
Off-leakage current ⁽⁹⁾	$T_{A} = +85^{\circ}C$		±5		nA
Off-isolation ⁽¹⁰⁾			120		dB
DIGITAL INPUT/OUTPUT (DVDD = 1.65 V to 3.6 V)			120		üÐ
, ,	I _{OH} = 1 mA	0.8 × DVDD			V
V _{OH}		0.0 × 0 000		0.2 × DVDD	V
V _{OL}	I _{OL} = 1 mA				
ViH		0.8 × DVDD			V
V _{IL}		DGND		0.2 × DVDD	V
Input hysteresis			0.5		V
Input leakage				±10	μΑ
CLK CLK Input		1	4.096	4.225	MHz

(7)

 $V_{OUT} = 0$ V. Pulse mode output noise is measured by the ADS1282, over a 413-Hz bandwidth using ADC gain = 1. $V_{OUT} = 0$ V. DC noise is measured by the ADS1282, over a 413-Hz bandwidth using complementing gain. DC noise is referred to a (8) 1.77-V full-scale ADC output. Divide output-referred noise by the ADC gain to yield input-referred noise. Switch input or output voltage = AVDD - 0.5 V to AVSS + 0.5 V.

(9)

(10) f = 31.25 Hz, 1.77 V_{RMS}. Switch output loaded 2 x 10 k Ω to mid-supply range.



Electrical Characteristics (continued)

Minimum and maximum specifications are at $T_A = -40^{\circ}$ C to +85°C. Typical specifications are at $T_A = +25^{\circ}$ C, AVDD = +2.5 V, AVSS = -2.5 V, f_{CLK} = 4.096 MHz, V_{REF} = 5 V, and DVDD = 3.3 V (unless otherwise noted). Refer to Figure 50. DAC1282A supports gains = 1/1, 1/4, and 1/16 only.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
POWER SUPPLY					
AVSS		-2.6		0	V
AVDD		AVSS + 4.75		AVSS + 5.25	V
DVDD		1.65		3.6	V
	Gain = 1/1, V _{OUT} = 0 V		7.4	8.5	mA ⁽¹¹⁾
AVDD, AVSS current	Pulse mode, $V_{OUT} = 0 V$		7		mA
	Shutdown		1	10	μA
	Operating		180	300	μA
DVDD current	Shutdown ⁽¹²⁾		1	10	μA
Davida	Operating		38	44	mW
Power	Shutdown ⁽¹²⁾		10	85	μW
TEMPERATURE RANGE		· · ·			
Specified temperature range		-40		+85	°C
Operating temperature range		-50		+125	°C
Storage temperature range		-65		+150	°C

(11) Analog supply current scales with gain as follows:

 I_{AVDD} and $I_{AVSS} = 0.016 \times V_{REF} \times (44 \times Gain + 1) + 3.8 (mA).$ (12) Digital inputs stopped and maintained at V_{IH} or V_{IL} level.

DAC1282, DAC1282A

ZHCS597B-DECEMBER 2011-REVISED MAY 2015

www.ti.com.cn

NSTRUMENTS

EXAS

7.5 Timing Requirements: Serial Peripheral Interface (SPI) Timing

At $T_A = -40^{\circ}$ C to $+85^{\circ}$ C and DVDD = 1.65 V to 3.6 V, unless otherwise noted.

		MIN	MAX	UNIT
t _{CSSC}	CS low to first SCLK: setup time ⁽¹⁾	30		ns
t _{SCLK}	SCLK period	120		ns
t _{SPWH}	SCLK pulse width: high	50		ns
+	SCLK pulse width: low ⁽²⁾	50		ns
t _{SPWL}			2 ¹⁸	t _{CLK}
t _{DIST}	Valid DIN to SCLK high: setup time	40		ns
t _{DIHD}	Valid DIN to SCLK high: hold time	20		ns
t _{DOPD}	SCLK low to valid new DOUT: propagation delay ⁽³⁾		40	ns
t _{DOHD}	SCLK low to DOUT invalid: hold time		0	ns
t _{CSDOD}	CS low to DOUT driven: propagation delay ⁽³⁾		40	ns
t _{CSDOZ}	CS high to DOUT Hi-Z: propagation delay		20	ns
t _{CSH}	CS high pulse	50		ns
t _{SCCS}	Last SCLK falling edge to CS high	0		ns

(1)

 $\overline{\text{CS}}$ can be tied low. Holding SCLK low longer than 2¹⁸ f_{CLK} cycles resets the SPI interface. DOUT load = 20 pF || 100 k Ω to DGND. (2) (3)





Figure 1. Serial Interface Timing




7.6 Typical Characteristics



DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015


www.ti.com.cn

Typical Characteristics (continued)





Typical Characteristics (continued)




TEXAS INSTRUMENTS

DAC1282, DAC1282A

ZHCS597B-DECEMBER 2011-REVISED MAY 2015


www.ti.com.cn

Typical Characteristics (continued)





Typical Characteristics (continued)





8 Detailed Description

8.1 Overview

The DAC1282 is a single-chip, digital-to-analog converter (DAC) that self-generates low-distortion sine-wave and pulse-output signals for the demanding testing requirements of seismic recording equipment. Figure 32 shows the block diagram of the DAC1282.

The DAC1282A device is functionally equivalent to the DAC1282, except that the DAC1282A supports PGA gains of 1/1, 1/4, and 1/16 only. The DAC1282A also relaxes the THD specification of these gains. See the *Electrical Characteristics* section for more details.

The DAC1282 requires two supply voltages: analog and digital. The analog supply can be single 5 V or bipolar ± 2.5 V. The digital supply range is 1.65 V to 3.6V. The output signal common-mode voltage is regulated to 100 mV below the midpoint of the analog power-supply voltage. An internal power-on reset (POR) circuit resets the DAC on power-up.

An SPI[™]-compatible serial interface is used to access the DAC1282 registers for device configuration and control. The configuration registers can be read back by clocking the data out on the DOUT pin. The DAC1282 voltage output is fully differential and is taken out on the VOUTP/VOUTN pins. The CAPP/CAPN pins connect to external filter capacitors to reduce the output noise.

The reference input voltage sets the DAC1282 full-scale output. The DAC reference voltage is applied between the VREF and AVSS pins. The DAC is optimized to operate with a 5-V reference. The sine-wave generator is programmable by registers to set the sine frequency and amplitude. The frequency range is programmable from 0.4883 Hz to 250 Hz. The output level is controlled by both analog gain (in 6-dB steps), and digital gain (in 0.5-dB steps).




Figure 32. DAC1282 Block Diagram

The digital modulator takes the output from the sine-wave generator or the 24-bit dc register to generate the ones-density bitstream. The bitstream drives the main DAC. Optionally, ones-density data can be input to drive the DAC directly, bypasses the digital signal generator. The main DAC develops a differential output current that is converted to a differential output voltage by an internal current-to-voltage (I/V) amplifier. The output range is set by analog gain that scales the DAC current generator. The output amplifier provides current limit protection.

The dc mode is programmed by a 24-bit register and is used to provide a dc output. The dc mode also has programmable ranges controlled by the analog gain control.



DAC1282, DAC1282A ZHCS597B – DECEMBER 2011 – REVISED MAY 2015

Overview (continued)

In Pulse mode, a fast-response, 5-bit pulse DAC is used to provide 31 preset dc levels. The levels span over the available output ranges. The pulse DAC is optimized to provide fast response with short output rise times. The pulse DAC is triggered by the SYNC pin for precision control of the pulse time.

The DAC1282 includes a low distortion differential output switch. The output switch can connect the DAC1282 output to sensors for THD and impulse testing. The switch is controlled by either pin or command, thus allowing precise switch timing.

The SYNC input synchronizes the output signal to a known time reference. In sine mode, SYNC resets the sine wave to the zero crossing. In Pulse mode, SYNC selects one of two user-programmed dc levels.

The RESET/PWDN pin powers down the device when low. When RESET/PWDN is released high, the DAC1282 is reset.

The SW/TD input is dual function. In digital data mode, the pin is the ones-density data input. In the other modes, SW/TD controls the opening/closing of the switch.

Figure 33 shows the main details of the main DAC. The main DAC provides the digital-to-analog conversion by filtering the ones-density digital data. In operation, the current generator establishes the range current that is mirrored to a multi-tap, current-steering filter stage. The current generator is controlled by the analog gain control register that scales the weight of the tap currents to one of seven ranges (0 dB to -36 dB).

The current-steering stage switches the tap currents to the positive or negative current summing nodes, as the digital input is sampled. A higher ones-density directs an increasing average current to one node than the other, thus increasing the differential current. The differential current is converted to differential voltage by the internal I/V converter stage. The common-mode current sources balance the current at the amplifier summing node.




Figure 33. Main DAC Block Diagram

DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015




8.2 Feature Description

8.2.1 Signal Output (VOUTP, VOUTN)

As shown in Figure 34, the DAC provides a differential voltage ($V_{DIFF} = VOUTP - VOUTN$) on pins VOUTP and VOUTN. The output common-mode voltage (V_{COM}) is regulated to 100 mV below the midpoint of the analog supply (AVDD – AVSS).

Each signal output swings above and below the common-mode voltage. Best performance is realized when the DAC output is used differentially. In power-down mode, the outputs enter a high-impedance, 3-state mode.



NOTE: $V_{DIFF} = VOUTP - VOUTN = \pm 2.5 V \times Gain (V_{REF} = 5 V)$. $V_{COM} = -0.1 V (\pm 2.5 - V \text{ supplies}) \text{ or } 2.4 V (5 - V \text{ supply})$.

Figure 34. DAC Output Signal

The DAC output buffer is rated to drive up to a 2-nF capacitive load (maximum) and a 100- Ω resistive load (minimum). However, degradation of THD performance results in resistive loads less than 1 k Ω , as shown in Figure 26

The internal digital modulator generates the signal to drive the DAC. The modulator shapes the in-band noise to high frequency and the frequency-shaped noise is present on the DAC output. However, the high frequency DAC output noise is rejected by the digital filter of the ADC and does not affect system performance.

The DAC sampling update noise is also present on the signal output. The sampling noise does not affect the ADC performance, but when testing the ADC near full-scale input, the noise can cause false indication of the ADC modulator overrange detection. The ADS1282 overrange output signal indication should be ignored when testing at or below the ADC full-scale input.



Feature Description (continued)

8.2.2 DAC Modes

The DAC1282 has four operational modes of: sine, dc, pulse, and external digital data input. These modes are programmed by the MODE[1:0] bits in the GANMOD register, as shown in Table 1.

MODE[1:0] BITS	DAC MODE
00	Sine
01	DC
10	Digital data
11	Pulse

Table 1. DAC Modes

8.2.2.1 Sine Mode

In sine mode, the DAC1282 provides a sine-wave output. An internal signal generator develops the sine-wave signal. The M[3:0], N[7:0], and FREQ register bits program the output frequency. The frequency range is programmable from 0.4883 Hz to 250 Hz, as shown in Equation 1.

Output Frequency (Hz)⁽¹⁾ =
$$\frac{250}{2^{FREQ}} \times \frac{M[3:0] + 1}{N[7:0] + 1}$$

where:

 $\mathsf{M}[3:0] \leq \mathsf{N}[7:0]$

(1) f_{CLK} = 4.096 MHz. The signal frequency scales with f_{CLK} .

(1)

Table 2 lists values of registers M and N for selected output frequencies.

Table 2. Register Output Frequencies

SIGNAL FREQUENCY (Hz) ⁽¹⁾	M[3:0] REGISTER BITS	N[7:0] REGISTER BITS	FREQ BIT
0.48828125	0000	1111 1111	1
0.9765625	0000	1111 1111	0
1.953125	0000	0111 1111	0
3.90625	0000	0011 1111	0
7.8125	0000	0001 1111	0
15.625	0000	0000 1111	0
31.25	0000	0000 0111	0
50	0000	0000 0100	0
55	1010	0011 0001	0
60	0101	0001 1000	0
62.5	0000	0000 0011	0
100	1001	0001 1000	0
125	0000	0000 0001	0
250	0000	0000 0000	0

(1) $f_{CLK} = 4.096MHz$. The signal frequency scales with f_{CLK} .

ISTRUMENTS

XAS

When the M or N registers are updated, the sine wave resets to the zero-crossing point. The sine wave can also be reset to the zero-crossing point by taking the SYNC pin high; see the SYNC section.

The amplitude of the sine-wave output is determined by analog and digital gains. The analog gain increments are 6 dB, from 0 dB to -36 dB, and are programmed by the GAIN[2:0] register bits. Table 3 lists the analog gains.

ANALOG GAIN (V/V) ⁽¹⁾	ANALOG GAIN (dB) ⁽²⁾	DIFFERENTIAL RANGE (V) ⁽³⁾	GAIN[2:0] REGISTER BITS
1/1	0	±2.5	000
1/2	-6	±1.25	001
1/4	-12	±0.625	010
1/8	-18	±0.312	011
1/16	-24	±0.156	100
1/32	-30	±0.078	101
1/64	-36	±0.039	110

Table 3. Analog Gain

(1) The DAC1282A supports analog gains of 1/1, 1/4, and 1/16 only.

Relative to 1.77 V_{RMS} full-scale. $V_{REF} = 5 V$, digital gain = 0 dB. (2)

(3)

The digital gain resolution is in 0.5-dB increments, from 0 dB to full mute and is programmed by the SINEG[7:0] register bits. Table 4 lists the digital gain setting. Equation 2 is the amplitude setting in sine mode.

Sine Amplitude (dB) = Analog Gain (dB) + Digital Gain (dB)

(2)

Best SNR, for a given signal level, is achieved by reducing the analog gain while maximizing the digital gain.

SINEG[7:0] REGISTER BITS			
0000 0000			
0000 0001			
0000 0010			
—			
1110 1111			
1111 0000			
1111 xxxx			
1111 1111			

Table 4. Sine Mode Digital Gain



8.2.2.2 DC Mode

The DAC1282 provides a dc output mode with 24-bit available resolution. The output level is determined by the analog gain and the 24-bit dc registers.

The GAIN[2:0] register bits set the analog gain (see Table 3). The DCG[23:0] register bits set the 24-bit level over the selected analog range. Table 5 lists the digital gain settings in dc mode.

DCG[23:0] REGISTER BITS
7FFFFh
3FFFFh
0
C00000h
800001h

Table 5. DC Mode Digital Gain Settings

(1) $V_{REF} = 5$ V. Ideal output voltage excluding gain, offset, linearity and noise errors.

8.2.2.3 Pulse Mode

In pulse mode, a fast responding, 5-bit pulse DAC is used to generate the output. The pulse DAC is designed to approximate a linear-in-dB output function, allowing the generation of pulse test signals across all ranges. Two registers are used to preset the DAC output. The SYNC pin is used to select one of the two registers. When SYNC is low, the PULSA register value drives the DAC; when SYNC is high, the PULSB register value drives the DAC. The pulse registers can be programmed to yield differential outputs from -2.5 V to +2.5 V. Note that the pulse levels scale with V_{REF} and are independent of the analog gain settings. Table 6 lists the programmable range of the pulse A and pulse B registers.

OUTPUT (V) ⁽¹⁾	PULSA[4:0], PULSB[4:0]	OUTPUT (V) ⁽¹⁾	PULSA[4:0], PULSB[4:0]
+2.50	01111	-0.020	11111
+1.88	01110	-0.029	11110
+1.25	01101	-0.039	11101
+0.938	01100	-0.058	11100
+0.625	01011	-0.078	11011
+0.469	01010	-0.117	11010
+0.312	01001	-0.156	11001
+0.234	01000	-0.234	11000
+0.156	00111	-0.312	10111
+0.117	00110	-0.469	10110
+0.078	00101	-0.625	10101
+0.058	00100	-0.938	10100
+0.039	00011	-1.25	10011
+0.029	00010	-1.88	10010
+0.020	00001	-2.50	10001
0	00000		

Table 6. Pulse Register Values

(1) V_{REF} = 5 V. Ideal pulse mode differential output, values are rounded and exclude noise, offset, gain, and linearity errors.

Note that when pulse testing the ADC, the ADC digital filter time domain response has characteristic overshoot and ringing. As a result of the ADC filter overshoot, input levels close to ADC full scale may cause clipping of the ADC output code.

DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015



8.2.2.4 Digital Data Mode

In digital data mode, the DAC internal signal generator is bypassed and the DAC is driven instead by applying a bitstream input. Arbitrary DAC output waveforms can be generated by application of custom digital data patterns. The data format in this mode is ones-density modulated input at CLK/16 data rate (256 kHz). The input is applied to the SW/TD input pin. The DAC1282 output in digital data mode is defined in Equation 3.

Digital Data Mode Differential Output = VOUTP - VOUTN = V_{REF}/2 × Gain × (TD - 50%)/25%

where:

V_{REE} is 5-V nominal,

Gain is the analog gain (1/1 to 1/64),

TD is the bitstream ones-density from 25% to 75%.

(3)

The DAC1282 filters the digital data (bitstream) input providing a voltage output proportional to the bitstream ones-density. The GAIN[2:0] register sets the analog gain in 6-dB steps, from 0 dB to -36 dB (1/1 to 1/64); see the SYNC section for the external timing requirements. Table 7 lists several values of the external bitstream input.

VOUTP – VOUTN (V) ⁽¹⁾
–2.5 × Gain
–1.25 × Gain
0
+1.25 × Gain
+2.5 × Gain

Table 7. External Bitstream Input


(1) $V_{REF} = 5$ V. Gain is the analog gain, programmable from 1/1 to 1/64 (0 dB to -36 dB).



8.2.3 Reference Voltage (V_{REF})

The DAC1282 requires an external reference for operation. Although reference voltage as low as 2.5 V can be used, best SNR is achieved with a 5-V reference. The reference input is defined as the voltage difference between VREF and AVSS (that is, $V_{REF} = VREF - AVSS$). The DAC1282 output scales with V_{REF} ; consequently, reference noise or drift appears on the DAC output. Excessive reference noise may lead to degraded SNR. A low-drift and low-noise reference is recommended.

Connect the external reference ground pin directly to the AVSS pins using a star connector to AVSS pin 14. Star connection minimizes the possibility of power-supply crosstalk. Also, connect a 0.1-µF capacitor close to the VREF and AVSS terminals to reduce noise susceptibility. Figure 35 shows the reference connection. The reference input impedance is 220 k Ω . In power-down the switch is off, resulting in very high input impedance. For single-supply applications, connect AVSS to a clean analog ground point.



(1) Recommended bypass capacitor.

Figure 35. Reference Input Connection

8.2.4 Output Filter (CAPP, CAPN)

The CAPP and CAPN pins are the connections for two external capacitors, one capacitor connects to CAPP and VOUTP and the other capacitor connects to CAPN and VOUTN. The capacitors are required to filter the DAC sampling noise. The capacitor values are 1 nF; capacitors with low voltage coefficients should be used (COG ceramic or film).

As seen in Figure 36, the external capacitors form an analog low-pass filter with the internal feedback resistors. After step changes to the data in the sine, dc, and digital data modes, the settling of the DAC and the analog filter is 100-µs typical, as shown in Figure 46. In pulse mode, the filter is internally disabled, yielding shorter settling time.




Figure 36. Output Filter

8.2.5 Output Switch (SWINP, SWINN, SWOUTP, SWOUTN)

The DAC1282 has an integrated output switch. The switch can be used to route the DAC output signal to a sensor for pulse, THD, and common-mode testing. The switch has low on-resistance and matched elements to minimize signal distortion. The switch input voltage range extends to the analog power supply.

The switch is controlled by three register bits, SW[2:0], and is also controlled by the SW/TD input pin. The switch integrates break-before-make operation when the register or the SW/TD input control is changed. The SW/TD input can be used to force the switch open for precise timing control of sensor impulse testing; see the *Switch Control/DAC Data Input (SW/TD)* section. Figure 37 and Table 8 describe the switch operation.




Figure 37. DAC1282 Signal Switch

Note that when the DAC is in power-down mode, the switch is forced open.

As shown in Figure 29, the switch on-resistance varies with the switch signal level. When the switch is used to route the signal and a resistive load is connected to the switch output, the switch on-resistance variations interact with the load resistance and cause the THD to degrade. Figure 27 illustrates the dependence of THD versus switch load resistance. The dependence of THD data was taken with a full-scale signal.

DESCRIPTION	PIN CONNECTIONS	SWITCHES CLOSED	SW[2:0] REGISTER BITS
Open (default)	Open	None	000
Differential	SWINP to SWOUTP and SWINN to SWOUTN	S1, S3	001
Differential reverse	SWINP to SWOUTN and SWINN to SWOUTP	S2, S4	010
Common-mode positive	SWINP to SWOUTP and SWOUTN	S1, S2	011
Common-mode negative	SWINN to SWOUTP and SWOUTN	S3, S4	100
Single-ended positive	SWINP to SWOUTP	S1	101
Single-ended negative	SWINN to SWOUTN	S3	110
Output short	SWOUTP to SWOUTN	S5	111

Table 8. Switch Connections



8.2.6 Clock Input (CLK)

The CLK pin is the master clock input to the DAC1282, nominally 4.096 MHz. As with any high-performance data converter, a high-quality clock source is essential. A crystal oscillator or low-jitter PLL clock source is recommended. Make sure to avoid ringing on the input by keeping the trace short and source-terminating (typically 50 Ω). See the CLK specifications shown in Figure 38 and Table 9.



Figure 38. CLK Timing Requirements

Table 9. Requirements for Figure 38

SYMBOL	DESCRIPTION	MIN	MAX	UNIT
t _{CLK}	CLK period	235	1000	ns
t _{CPWH, L}	CLK pulse width high or low	95	900	ns

8.2.7 Switch Control/External Digital Input (SW/TD)

SW/TD is a multi-function digital input pin. The SW/TD function depends on the mode of operation.

8.2.7.1 SW Function

In sine, dc, and pulse mode, SW/TD controls the output switch. When SW/TD is low, all switches are forced open, overriding the switch register setting (SW[2:0]). When SW/TD is high, the switch is transparent to the value of register setting. In power-down mode, the switch is forced open.

8.2.7.2 TD Function

In digital input mode, SW/TD is the signal input used to drive the DAC. The data input are modulated by onesdensity and are clocked in by the master clock (CLK). When the ones-density is 75% (that is, on average, three out of four bits are '1'), the differential output voltage is at the positive maximum value. When the ones-density is 25% (that is, on average, three out of four bits are '0'), the differential output voltage is at the negative maximum value. When the ones-density is 50% (on average, an equal number of '0's and '1's), the differential output is zero.

SW/TD is sampled by the DAC1282 at the rate of CLK/16. Therefore, the sampling can have ±8 CLK periods of uncertainty. SYNC can be used to eliminate the uncertainty by synchronizing the phase of SW/TD to the desired CLK cycle. Synchronizing the digital input results in a consistent phase of the output signal; see the SYNC section.

The output range is set by the analog gain bits, GAIN[2:0]; see Table 3. Equation 3 describes the DAC output versus the bitstream input ones-density. Make sure to avoid ringing on the input by keeping the trace short. In some cases, source-terminating resistors may be necessary (20Ω to 50Ω).

TEXAS INSTRUMENTS

www.ti.com.cn

8.2.8 SYNC

SYNC is a digital input used to synchronize the DAC1282 output.

In the digital data mode, the DAC input is a ones-density bitstream. In this mode, the SYNC pin synchronizes the sampling of SW/TD digital data to the desired master clock cycle (CLK). When SYNC is low or high, the DAC operates normally. When SYNC is taken from low to high, the DAC output is reset to zero and the sample instant of SW/TD is reset to the eighth rising CLK edge that follows. The SW/TD is then regularly sampled on subsequent 16 CLK intervals. After synchronization, the DAC output is not settled and achieves full settling 400 CLK periods later, as shown in Figure 39.




Figure 39. Digital Data Mode Synchronization

SYMBOL	DESCRIPTION	MIN	TYP	UNIT
t _{SCSU}	SYNC high to CLK high setup time	30		ns
t _{TCSU}	SW/TD to CLK high setup time	30		ns
t _{CTHD}	CLK high to SW/TD hold time	10		ns
t _{SYLW}	SYNC low pulse width	2		t _{CLK}
t _{STDAT}	CLK high after SYNC high to SW/TD sample time		8	t _{CLK}
t _{TSOP}	SW/TD sample to output update		4	t _{CLK}
t _{SW/TD}	SW/TD period		16	t _{CLK}
t _{SETL}	SYNC high to fully-settled output		400	t _{CLK}

Table 10. Timing Characteristics	for	Figure	39 ⁽¹⁾
----------------------------------	-----	--------	--------------------------

(1) DVDD = 1.65 V to 3.6 V.



In sine mode, the SYNC rising edge resets the DAC output to differential 0 V (sine-wave zero-crossing point). When SYNC is high or low, the output is unaffected. When SYNC is taken from low to high, the output resets on the following CLK rising edge. SYNC must be pulsed low for a minimum of 2 CLK cycles. The SYNC input can be applied simultaneous to the DAC and the ADS1282 (ADC in pulse-sync mode).

To synchronize the DAC, observe SYNC to the CLK timing requirements shown in Figure 40. That is, the SYNC rising edge should be applied before the set-up time or after the hold time specifications. If the SYNC timing requirement is not met, the DAC may synchronize with one clock cycle timing error.




Figure 40. Sine Mode Synchronization

Table 11. Timing Characteristics for Figure 40	1)
--	----

SYMBOL	DESCRIPTION	MIN	UNIT
t _{SYLO}	SYNC pulse width low	2	t _{CLK}
t _{SCSU}	SYNC rising edge to CLK rising edge setup time	30	ns
t _{CSHD}	CLK rising edge to SYNC rising edge hold time	40	ns

(1) DVDD = 1.65 V to 3.6 V.

In pulse mode, the SYNC pin selects one of two pre-programmed pulse levels. The pulse levels are programmable from +2.5 V to -2.5 V in approximately 3-dB steps by pulse level registers PULSA and PULSB. When SYNC is low, the value of the PULSA register drives the DAC; when SYNC is high, the value of the PULSB register is the code of the DAC, as shown in Figure 41. When the SYNC pin is changed, the DAC output updates immediately to the new code.




Figure 41. Sync Operation in Pulse Mode

DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015

8.2.9 RESET/PWDN

The RESET/PWDN is a digital input used to power-down and reset the DAC1282. To power-down the DAC, take the pin low. In power-down mode, the power consumption is reduced to a device leakage level (see the Electrical Characteristics table). The signal output and digital pin DOUT enters 3-state and the output switch is driven off. Note that the digital inputs must remain defined as either logic low or logic high; do not float the inputs. Disable the CLK input to minimize leakage. To exit the power-down state, take the pin high. The DAC1282 is reset after power-down mode is exited.

The DAC1282 is reset by taking the $\overline{\text{RESET}/\text{PWDN}}$ pin low for a minimum of two f_{CLK} cycles and is then taken back high. The DAC1282 is held in reset for 2 f_{CLK} cycles; after this time, DAC communications may begin, as shown in Figure 42 and Table 12.




Figure 42. DAC RESET/PWDN

Table 12. Timing Characteristics for Figure 42

SYMBOL	DESCRIPTION	MIN	MAX	UNIT
t _{RSLO}	PWDN/RESET pulse width low for power-down	500		ns
t _{RSTM}	PWDN/RESET high to begin operation		500	ns

8.2.10 AVDD, AVSS, and DVDD Power Supplies

The DAC1282 has two power supplies: analog and digital. The analog supply (AVDD, AVSS) is 5 V and can either be single 5 V or dual (\pm 2.5 V). The analog supply should be clean and free from noise and ripple. The DAC1282 regulates the output common-mode voltage to 0.1 V below the mid-point of the analog supply. Because the analog supply pins draw signal-dependent current and AVSS (pin 14) is internally shared with the reference input low, trace resistance between AVSS (pin 14) and the AVSS power supply should be minimized or degraded performance may result. Therefore, connect the external reference ground terminal close to the device AVSS terminal using a star connection. This configuration helps to minimize power-supply coupling to the reference input.

DVDD is the digital supply used to power both the internal digital and the device I/O pins. The allowable range of DVDD is 1.65 V to 3.6 V.

The power supplies can be sequenced on or off in any order, but the analog or digital inputs should never exceed AVDD or AVSS, or DVDD, respectively. In such an event, the internal ESD protection diodes may begin to conduct. The input current must always be limited as specified in the Absolute Maximum Ratings table.



At power-on, when the latter of DVDD exceeds approximately 1.3 V, or the difference of AVDD – AVSS exceeds approximately 1.4 V, an internal power-on reset (POR) occurs. During POR, the device is held in a reset condition for a period of $2^{16} f_{CLK}$ periods as shown in Figure 43. During this time, the DAC1282 output is held at 0 V, differential. SPI communications are not possible during this time. After the reset time elapses, the default settings are loaded: 31.25 Hz, 28 mV_{RMS} amplitude, and output switch off. SPI communications can then be started.




Figure 43. Power-On Sequence

8.2.10.1 Power Consumption

The power consumed by the DAC1282 depends on the analog gain. Table 13 shows the DAC power consumption.

ANALOG GAIN	POWER (mW) ⁽¹⁾
1/1	38
1/2	28
1/4	23
1/8	21
1/16	20
1/32	20
1/64	20

Table 13. Power Consumption

(1) Typical power consumption with $V_{REF} = 5 V$ and $V_{OUT} = 0 V$. Excludes pulse mode.

8.2.10.2 Offset and Gain Error

The DAC1282 features a low offset error (\pm 7/Gain + 50 ppm FS typical) and low gain error (0.1 % typical). Offset and gain drift are also very low for the DAC1282. Drift is calculated using the box calculation method of Equation 4:

Drift Calculation = (Max – Min) / Temperature Range (ppm/°C)

Where:

Max and Min are, respectively, the maximum and minimum offset and gain errors (in ppm) recorded over the specified temperature range of -40° C to $+85^{\circ}$ C. (4)

Gain match is the gain error of Gain = 1/1 relative to all analog gains.

8.2.10.3 Signal-to-Noise Ratio (SNR)

The DAC1282 achieves excellent signal-to-noise ratio (SNR) performance. The SNR data are obtained using the DAC circuit of Figure 50 and data captured by the ADS1282.

SNR is measured with a signal level of -0.5 dBFS and a 31.25-Hz test frequency, then taking the fast fourier transform (FFT) of 4096 data points from the ADS1282, using complementing gains. The noise power is calculated over the bandwidth of 413 Hz (1-ms sample period). The dc, fundamental, and harmonic bins are removed to calculate the SNR. The SNR measurement represents the combination of the ADS1282 SNR and the SNR of the DAC1282.

DAC1282, DAC1282A ZHCS597B – DECEMBER 2011 – REVISED MAY 2015



8.2.10.4 DC Noise

DC noise data are obtained using the DAC circuit of Figure 50 with data captured by the ADS1282. The noise is measured in dc mode with the output voltage set to 0 V differential. The ADC gain is set to the complement of the DAC gain for each output range. The noise is the standard deviation of 4096-point ADC acquisition record (RMS noise, referred-to-output).

8.2.10.5 Total Harmonic Distortion (THD)

The DAC1282 achieves excellent THD performance. The THD data are obtained using the DAC circuit of Figure 50 and captured by the ADS1282. The ADC gain is set to the complement of the DAC gain for each output range.

THD is measured with a –0.5-dBFS output signal level and a 31.25-Hz test frequency, then taking the FFT of the 4096-point ADC acquisition record. The ADC data points are increased to 16,384 for gains of 1/16, 1/32, and 1/64 for improved rendition of harmonics as a result of the higher noise floor. The THD measurement represents the combination of the ADS1282 THD and the DAC1282 THD.

8.2.11 Step Response

The step response of the DAC depends on the mode. In pulse mode, the DAC disables the external analog filter formed by capacitors CAPP, CAPN. Disabling the analog filter in conjunction with the fast response pulse DAC results in noticeably faster rise time and shorter settling time. Note that additional filter components in the signal path may also affect the response time.

Figure 44 shows the pulse mode step response after the SYNC pin transition. Figure 45 shows the pulse mode detail settling to 0.1% of final value after the SYNC pin transition.






Figure 46 shows the step response time of the dc mode. The step response of sine and digital data mode have similar settling times. Note that additional filter components in the signal path may also affect the response time.




Figure 46. DC-Mode Step Response

8.2.12 Frequency Response

The DAC internal signal generator is capable of output signal frequencies from 0.489 Hz to 250 Hz. Frequencies outside of this range are also possible by driving the DAC directly with an external digital input (bitstream). However, the DAC low-pass filters the digital input and results in a sinx/x frequency response. The -3 dB signal bandwidth of the DAC filter is 8.2 kHz. Figure 47 illustrates the DAC1282 frequency response. Note that high-order noise-shaped digital inputs may limit the useable frequency range as a result of rising noise.




Figure 47. DAC Frequency Response



8.3 Device Functional Modes

8.3.1 Serial Interface

Configuration of the DAC is by an SPI-compatible serial interface consisting of four signals: \overline{CS} , SCLK, DIN, and DOUT; or the interface can consist of three signals in which case \overline{CS} may be tied low. Tying \overline{CS} low permanently selects the device and DOUT remains a driven output. The interface is used to read and write registers and also is used to send a DAC reset command.

8.3.1.1 Serial Communications

DAC1282 communication occurs by clocking register data into the device (on DIN) and reading back register data (on DOUT). The SCLK input is used to clock data into and out of the device. Data are input on the serial clock (SCLK) rising edge and output on the SCLK falling edge. The communication protocol is half-duplex (that is, data are transmitted to and from the device one direction at a time).

Communications to the device occur on 8-bit boundaries. If an unintentional SCLK transition should occur (such as is possible from a noise spike), the DAC1282 command decoder can be out-of-sync and the serial port may not respond properly. The serial port may reset in one of the following ways:

- 1. Take \overline{CS} high to reset the interface
- Hold SCLK inactive (low state) for 2¹⁸ f_{CLK} cycles to automatically reset the interface (see the SPI Timeout section)
- 3. Take RESET/PWDN low then back high to reset the device and the interface
- 4. Cycle the power supplies for a power-on reset (POR)

8.3.1.2 Chip Select (\overline{CS})

 \overline{CS} (chip select) selects the DAC1282 for communication. To select the device, pull \overline{CS} low. \overline{CS} must remain low for the duration of the command sequence. When \overline{CS} is taken high, the serial interface is reset, input commands are ignored, and DOUT enters a high-impedance state.

8.3.1.3 Serial Clock (SCLK)

The serial clock (SCLK) is a Schmitt-triggered input used to clock data into and out of the DAC1282. SCLK can be idled high or low. If SCLK is idled low, the SPI timeout feature is active. If SCLK is idled high, the SPI timeout feature is disabled.

Despite the built-in Schmitt-trigger, keep SCLK as clean as possible to prevent glitches from accidently shifting the data. Series-terminated printed circuit board (PCB) traces often help to reduce ringing and overshoot (series termination resistance is approximately 20Ω to 50Ω). If SCLK is held low for $2^{18} f_{CLK}$ periods, the serial interface is reset. The timeout feature can be used to automatically recover the SPI port in the event of a noise glitch. Avoid starting new commands after this time interval to prevent an unexpected serial port reset at the next command instant.

8.3.1.4 Data Input (DIN)

DIN is the data input pin used to send data to the DAC. The DAC1282 latches DIN input data on the rising edge of SCLK.

8.3.1.5 Data Output (DOUT)

DOUT is the data output pin used to read register data out of the DAC. The data are shifted out on the falling edge of SCLK. DOUT enters a 3-state when CS is high.

8.3.2 SPI Timeout

The DAC has an SPI timeout feature that can be used to recover the SPI port if a possible noise pulse should occur. The noise pulse may lead to a false SCLK detection that can render the DAC serial port unresponsive. The port is recovered by taking \overline{CS} high but, in applications where \overline{CS} is tied low, holding SCLK low for 2¹⁸ CLK cycles resets the SPI port automatically. When SCLK is low, the SPI port resets on every 2¹⁸ CLK cycle interval. Holding SCLK high disables the automatic SPI reset.



8.4 Programming

8.4.1 Commands

The commands summarized in Table 14 control and configure the DAC1282. The register read and register write commands are two-byte command arguments plus additional data bytes while the reset command is a one-byte command. The DAC1282 serial port chip select (CS) can be taken high or held low between commands but must remain low for the entire command operation.

COMMAND	TYPE	DESCRIPTION	FIRST OPCODE BYTE	SECOND OPCODE BYTE
RREG	Register	Read nnnn register(s) at address rrrr ⁽¹⁾	0010 rrrr	0000 nnnn
WREG	Register	Write nnnn register(s) at address rrrr	0100 rrrr	0000 nnnn
RESET	Control	Reset the device	0000 011x (06 or 07h)	—

Table 14. Command Definitions

(1) rrrr = Starting read or write register address, nnn= number of registers to read or write minus 1.


8.4.1.1 RREG: Read From Registers

Description: These two opcode bytes read register data. The register read operation is a two-byte opcode input followed by one or more bytes of register data as the output. The first byte of the command is the opcode and the register address combined. The second byte of the command specifies the number of registers to read (minus 1) in a block. Register data are output following the command input. Note that for multiple register read operations, the register address pointer does not wrap when the last register is exceeded.

First opcode byte: 0010 rrrr, where rrrr is the starting address register address to be read.

Second opcode byte: 0000 nnnn, where nnnn is the number of registers to read - 1.

Following bytes: Register data output in MSB-first format. The 16th SCLK falling edge of the opcode clocks out the MSB of the register data.



(1) $\overline{\text{CS}}$ may be tied low.

Figure 48. RREG Command Example: Read Two Registers Starting from Register 00h (Opcode 1 = 0010 0000, Opcode 2 = 0000 0001)

DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015

www.ti.com.cn


8.4.1.2 WREG: Write To Registers

Description: These two opcode bytes write register data. The register write operation is a two-byte opcode followed by one or more bytes of register data. The first byte of the command is the write opcode and the register address combined. The second byte of the command specifies the number of registers to write (minus 1) in a single sequence. The following bytes are the register data bytes. Note that for multiple register write operations, the register address pointer does not wrap when the last register is exceeded.

First opcode byte: 0010 *rrrr*, where *rrrr* is the starting address register address to be written.

Second opcode byte: 0000 nnnn, where nnnn is the number of registers to write - 1.

Following bytes: Register data input in MSB-first format.



(1) $\overline{\text{CS}}$ may be tied low.

Figure 49. WREG Command Example: Write Two Registers Starting from Register 00h (Opcode 1 = 0100 0000, Opcode 2 = 0000 0001)

8.4.1.3 RESET: Device Reset

Description: This command resets the DAC. The registers are set to power-on default the value; see the *RESET/PWDN* section.



8.5 Register Map

DAC1282 operation is controlled through a set of 8-bit registers. Collectively, the registers contain all the information needed to configure the DAC, such as output frequency and amplitude, output pulse levels, etc. Table 15 shows the register map.

The default state of the device at power-up, after the RESET pin is taken high or after a RESET command is as follows:

Sine mode, frequency = 31.25 Hz, -36-dB output range, 0-dB digital attenuation Switch state: open

ADDRESS	REGISTER	DEFAULT	BIT 7	BIT 6	BIT 5	BIT 4	BIT 3	BIT 2	BIT 1	BIT 0
0	GANMOD	xxx11000	ID2	ID1	ID0	GAIN2	GAIN1	GAIN0	MODE1	MODE0
1	SING	00000000	SINEG7	SINEG6	SINEG5	SINEG4	SINEG3	SINEG2	SINEG1	SINEG0
2	SWM	00000000	FREQ	SW2	SW1	SW0	M3	M2	M1	MO
3	Ν	00000111	N7	N6	N5	N4	N3	N2	N1	N0
4	DCG0	00000000	DCG7	DCG6	DCG5	DCG4	DCG3	DCG2	DCG1	DCG0
5	DCG1	00000000	DCG15	DCG14	DCG13	DCG12	DCG11	DCG10	DCG9	DCG8
6	DCG2	00000000	DCG23	DCG22	DCG21	DCG20	DCG19	DCG18	DCG17	DCG16
7	PULSA	00000000	0	0	0	PULSA4	PULSA3	PULSA2	PULSA1	PULSA0
8	PULSB	00000000	0	0	0	PULSB4	PULSB3	PULSB2	PULSB1	PULSB0

Table 15. Register Map

8.5.1 Register Descriptions

Table 16. GANMOD: Range and Mode Register 0 (address = 0h)

7	6	5	4	3	2	1	0
ID2	ID1	ID0	GAIN2	GAIN1	GAIN0	MODE1	MODE0
	•	•	•	•	•		

Bits[7:5]	ID[2:0]: Factory-programmed ide	ntification bit	s (read-only)				
	These bits may change at any time	without notific	cation.				
Bits[4:2]	GAIN[2:0]: Analog gain (output ra	ange)					
	the selected range and the digital g	ain. Sine mod Ind DCG2 reg	e digital gain isters. Pulse r	odes. The output amplitude is the combination of is programmed by the SINEG register; dc mode node levels are exclusively controlled by the PUL g gains of 1/1, 1/4, and 1/16 only.			
	GAIN[2:0]	DEVIC	E GAIN	OUTPUT RANGE (V) ⁽¹⁾			
	000	0 dB	1/1 V/V	±2.5			
	001 (DAC1282 only)	6 dB	1/2 V/V	±1.25			
	010	–12 dB	1/4 V/V	±0.625			
	011 (DAC1282 only)	–18 dB	1/8 V/V	±0.312			
	100	–24 dB	1/16 V/V	±0.156			
	101 (DAC1282 only)	–30 dB	1/32 V/V	±0.078			
	110 (DAC1282 only, default) ⁽²⁾	–36 dB	1/64 V/V	±0.039			
Bits[1:0]	MODE[1:0]: Mode control bits						
	The mode bits set the mode of operation. When the mode bits are changed, the internal signal generator block is reset.						
	00 = Sine mode (default) 01 = DC mode 10 = Digital data mode 11 = Pulse mode						

(1)

(Peak-to-peak) full-scale output range, $V_{REF} = 5$ V. Digital gain = 0 dB. Although both devices deafult to GAIN[2:0] = 110, the DAC1282A setting must be changed to one of the supported analog gains listed. (2)

DAC1282, DAC1282A ZHCS597B-DECEMBER 2011-REVISED MAY 2015

STRUMENTS

EXAS

	Table	17. SINEG: Si	ne Mode Digi	ital Gain Regi	ster (address	= 01h)	
7	6	5	4	3	2	1	0
SINEG7	SINEG6	SINEG5	SINEG4	SINEG3	SINEG2	SINEG1	SINEG0

Bits[7:0] SINEG[7:0]: Sine mode digital gain

This register byte sets the sine mode digital gain from 0 dB to -119.5 dB and to full mute, in 0.5-dB steps. The sine mode digital gain can be expressed as: -DGAIN[7:0]/2 (dB) and are listed in Table 18.

Table 18. Sine Mode Digital Gain

SINEG[7:0] REGISTER	SINE MODE DIGITAL GAIN (dB)
0000 0000 (default)	0.0
0000 0001	-0.5
0000 0010	-1.0
1110 1111	-119.5
1111 0000	Full mute
	Full mute
1111 1111	Full mute

Table 19. SWM: Switch, Output Frequency 'M', And Range Bit Register (address = 02h)

7	6	5	4	3	2	1	0
FREQ	SW2	SW1	SW0	M3	M2	M1	MO

Bit 7	FREQ: Frequency	,					
	This bit sets the sir	ne mode output frequency range; se	e Equation 1.				
Bits[6:4]	SW[2:0]: Switch c	SW[2:0]: Switch control bits					
		These bits control the switch settings when the SW/TD input is high. When SW/TD is low, the register ignored and the switch is forced open. In digital input mode, the switch is controlled only by the register					
	SW[2:0]	SWITCH DESCRIPTION	TERMINAL CONNECTIONS				
	000	Open (default)	All switches open				
	001	Differential	SWINP to SWOUTP and SWINN to SWOUTN				
	010	Differential reverse	SWINP to SWOUTN and SWINN to SWOUTP				
	011	Common-mode positive	SWINP to SWOUTP and SWINP to SWOUTN				
	100	Common-mode negative	SWINN to SWOUTP and SWINN to SWOUTN				
	101	Single-ended positive	SWINP to SWOUTP only				
	110	Single-ended negative	SWINN to SWOUTN only				
	111	Short	SWOUTP to SWOUTN				
Bits[3:0]	M[3:0]: Sine mode	e frequency, M bits					
	These bits control the sine-mode output frequency. The output frequency is given in Equation 1.						



DAC1282, DAC1282A

ZHCS597B – DECEMBER 2011 – REVISED MAY 2015
ENGOUND DECEMBER ZOTT REVICED MATT ZOTO

	т	able 20. N: S	ine Frequency	N Register (a	address = 03h	ı)	
7	6	5	4	3	2	1	0
N7	N6	N5	N4	N3	N2	N1	N0
Bits[7:0]	N[7:0]]: N register					
	These	e bits control the c	output frequency; s	ee Equation 1.			
Та	ble 21. DCG0	: DC Mode Di	igital Gain Byt	e 0, Least Sig	nificant Byte	(address = 04	4h)
7	6	5	4	3	2	1	0
DCG7	DCG6	DCG5	DCG4	DCG3	DCG2	DCG1	DCG0
	Table 22.	DCG1: DC M	lode Digital Ga	ain Byte 1, Mi	d Byte (addre	ss = 05h)	
7	6	5	4	3	2	1	0
DCG15	DCG14	DCG13	DCG12	DCG11	DCG10	DCG9	DCG8
		,					•
Та	ble 23. DCG2	: DC Mode D	igital Gain Byt	e 2, Most Sig	nificant Byte	(address = 06	ŝh)
_							
7	6	5	4	3	2	1	0
DCG23	DCG22	DCG21	DCG20	DCG19	2 DCG18	1 DCG17	0 DCG16
	DCG22 DCG[The D	DCG21 23:0]: DC mode 0CG0, DCG1, and	DCG20 digital gain settin	DCG19 g tes set the digital	DCG18 gain in dc mode; s	DCG17 see Table 5.	-
DCG23 Bits[7:0]	DCG22 DCG[The D	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le	DCG19 g tes set the digital t vel A Byte (a t	DCG18 gain in dc mode; s ddress = 07h)	DCG17 see Table 5.	DCG16
DCG23 Bits[7:0] 7	DCG22 DCG[The D	DCG21 23:0]: DC mode 0CG0, DCG1, and Table 24. PU 5	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4	DCG19 g tes set the digital vel A Byte (a d 3	DCG18 gain in dc mode; s ddress = 07h) 2	DCG17 see Table 5.	DCG16 0
DCG23	DCG22 DCG[The D	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le	DCG19 g tes set the digital t vel A Byte (a t	DCG18 gain in dc mode; s ddress = 07h)	DCG17 see Table 5.	DCG16 0
DCG23 Bits[7:0] 7 0	DCG22 DCG[The D	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU 5 0	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4	DCG19 g tes set the digital vel A Byte (a d 3	DCG18 gain in dc mode; s ddress = 07h) 2	DCG17 see Table 5.	DCG16
DCG23 Bits[7:0] 7 0	DCG22 DCG[The D 6 0 Rese	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU 5 0	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4	DCG19 g tes set the digital vel A Byte (a d 3	DCG18 gain in dc mode; s ddress = 07h) 2	DCG17 see Table 5.	DCG16 0
DCG23 Bits[7:0] 7 0 Bits[7:5]	DCG22 DCG[The D 6 0 Reset Alway	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU 5 0	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4 PULSA4	DCG19 g tes set the digital vel A Byte (a d 3	DCG18 gain in dc mode; s ddress = 07h) 2	DCG17 see Table 5.	DCG16 0
DCG23 Bits[7:0] 7 0 Bits[7:5]	DCG22 DCG[The D 6 0 Reset Alway PULS	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU 5 0 rved rved rs write '0'. sA[4:0]: Pulse lev	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4 PULSA4	DCG19 g tes set the digital t vel A Byte (a 3 PULSA3	DCG18 gain in dc mode; s ddress = 07h) 2 PULSA2	DCG17 see Table 5.	DCG16
DCG23 Bits[7:0] 7	DCG22 DCG[The D 6 0 Reset Alway PULS These The P SYNC progra	DCG21 23:0]: DC mode DCG0, DCG1, and Table 24. PU 5 0 rved rs write '0'. SA[4:0]: Pulse lev bits create pulse PULSA and PULS pin selects eithe	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4 PULSA4	DCG19 g tes set the digital vel A Byte (a 3 PULSA3 output when SYN independent leve	DCG18 gain in dc mode; s ddress = 07h) 2 PULSA2 IC is low.) Is that can be use a DAC output. The	DCG17 see Table 5. 1 PULSA1 d to provide pulse	0 PULSA0
DCG23 Bits[7:0] 7 0 Bits[7:5]	DCG22 DCG The D 6 0 Reset Alway PULS These The P SYNC progra RANC	DCG21 23:0]: DC mode CG0, DCG1, and Table 24. PU 5 0 rved rs write '0'. A[4:0]: Pulse lev bits create pulse PULSA and PULS pin selects eithe ammable in discre E[2:0] setting.	DCG20 digital gain settin I DCG2 register by LSA: Pulse Le 4 PULSA4 vel A bits e level A. (Selected B registers set two r level PULSA or le	DCG19 g tes set the digital evel A Byte (ac 3 PULSA3 output when SYN independent leve evel PULSB as the n in Table 6. Note	DCG18 gain in dc mode; s ddress = 07h) 2 PULSA2 IC is low.) Is that can be use b DAC output. The that the pulse leve	DCG17 see Table 5. 1 PULSA1 d to provide pulse pulse amplitude el value is indepe	0 PULSA0
DCG23 Bits[7:0] 7 0 Bits[7:5]	DCG22 DCG The D 6 0 Reset Alway PULS These The P SYNC progra RANC	DCG21 23:0]: DC mode CG0, DCG1, and Table 24. PU 5 0 rved rs write '0'. A[4:0]: Pulse lev bits create pulse PULSA and PULS pin selects eithe ammable in discre E[2:0] setting.	DCG20 digital gain settin DCG2 register by LSA: Pulse Le 4 PULSA4 vel A bits e level A. (Selected B registers set two r level PULSA or le ete steps, as shown	DCG19 g tes set the digital evel A Byte (ac 3 PULSA3 output when SYN independent leve evel PULSB as the n in Table 6. Note	DCG18 gain in dc mode; s ddress = 07h) 2 PULSA2 IC is low.) Is that can be use b DAC output. The that the pulse leve	DCG17 see Table 5. 1 PULSA1 d to provide pulse pulse amplitude el value is indepe	0 PULSA0

Bits[7:5]	Reserved			
	Always write '0'.			
Bits[4:0]	PULSB[4:0]: Pulse level B bits			
	These bits create pulse level B.			
	The PULSA and PULSB registers set two independent levels that can be used to provide pulse output. The SYNC pin selects either level PULSA or level PULSB as the DAC output. The pulse amplitude resolution is programmable in discrete steps; see Table 6. Note that the pulse level value is independent of the RANGE[2:0] setting.			



9 Application and Implementation

NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

9.1 Application Information

Figure 50 shows the basic DAC1282 connection. Bipolar analog supplies are shown (± 2.5 V). Single-supply operation is also possible with AVDD = 5 V and AVSS = GND. The digital supply range is 1.65 V to 3.6 V.

A low-noise, low-drift reference is recommended for best performance, such as the REF5050 (+5 V) and REF5045 (+4.5 V). Best signal-to-noise ratio is achieved with a 5-V reference, although a 4.5-V reference (REF5045) can be used with 1-dB loss in SNR. The 4.5-V reference can be operated from a 5-V supply. AVSS (pin 14) is the key reference ground point and should be connected to the reference ground terminal using a star connection. C_1 and C_2 are the required 1-nF output filter capacitors. The capacitors should be of the low volt-coefficient type (such as a COG ceramic or similar) and placed close to the device pins. Output resistors, R_1 and R_2 , decouple the DAC to ensure best performance when driving capacitive loads. The output is shown routed to the signal switch, providing a second, switched DAC output.




Figure 50. Basic Connection



www.ti.com.cn

9.2 Typical Applications

9.2.1 Single-Channel Seismic System

Figure 51 illustrates a single-channel data acquisition concept for seismic. The DAC1282 is used to test both the ADC and geophone. The DAC1282 connects directly to channel 1 of the ADC. Tests of the ADC include THD, pulse, input noise, common-mode, etc. The DAC output and ADC sample timing are controlled by the SYNC input pins.

The geophone connects to channel 2 of the ADC through input protection and optional filter networks. The DAC connects to the geophone using the integrated signal switch. Series resistors isolate the geophone from the DAC output. Geophone test capabilities include impulse, THD, leakage, and common-mode.




Figure 51. Single-Channel Seismic System



Typical Applications (continued)

9.2.2 Four-Channel Seismic System

Figure 52 illustrates a four-channel system. The switched DAC1282 output is routed to the ADC inputs. The signal from the DAC switch is used to perform sensor impulse testing by opening the switch while digitizing the response.




Figure 52. Four-Channel Seismic System



www.ti.com.cn

10 器件和文档支持

10.1 Community Resources

The following links connect to TI community resources. Linked contents are provided AS IS by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

TI E2E[™] Online Community *TI's Engineer-to-Engineer (E2E) Community.* Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

Design Support TI's Design Support Quickly find helpful E2E forums along with design support tools and contact information for technical support.

10.2 商标

E2E is a trademark of Texas Instruments. SPI is a trademark of Motorola. All other trademarks are the property of their respective owners.

10.3 静电放电警告



ESD 可能会损坏该集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理措施和安装程序,可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级,大至整个器件故障。精密的集成电路可能更容易受到损坏,这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

10.4 术语表

SLYZ022 — TI 术语表。

这份术语表列出并解释术语、首字母缩略词和定义。

11 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。 这些信息是针对指定器件可提供的最新数据。 这些数据会在无通知且不 对本文档进行修订的情况下发生改变。 欲获得该数据表的浏览器版本,请查阅左侧的导航栏。



PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
				_			(6)				
DAC1282AIPW	ACTIVE	TSSOP	PW	24	60	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC1282A	Samples
DAC1282AIPWR	ACTIVE	TSSOP	PW	24	2000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC1282A	Samples
DAC1282IPW	ACTIVE	TSSOP	PW	24	60	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC1282	Samples
DAC1282IPWR	ACTIVE	TSSOP	PW	24	2000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	DAC1282	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



www.ti.com

10-Dec-2020

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.




Texas

STRUMENTS

TAPE AND REEL INFORMATION





QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
DAC1282AIPWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1
DAC1282IPWR	TSSOP	PW	24	2000	330.0	16.4	6.95	8.3	1.6	8.0	16.0	Q1



www.ti.com

PACKAGE MATERIALS INFORMATION

5-Dec-2023



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	ength (mm) Width (mm)	
DAC1282AIPWR	TSSOP	PW	24	2000	350.0	350.0	43.0
DAC1282IPWR	TSSOP	PW	24	2000	350.0	350.0	43.0

TEXAS INSTRUMENTS

www.ti.com

5-Dec-2023

TUBE



- B - Alignment groove width

*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	Τ (μm)	B (mm)
DAC1282AIPW	PW	TSSOP	24	60	530	10.2	3600	3.5
DAC1282IPW	PW	TSSOP	24	60	530	10.2	3600	3.5

PW0024A



PACKAGE OUTLINE

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice. 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153.



PW0024A

EXAMPLE BOARD LAYOUT

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



PW0024A

EXAMPLE STENCIL DESIGN

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源, 不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担 保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验 证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。 您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成 本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址:Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023,德州仪器 (TI) 公司