

ISO7841x 高性能、8000V_{PK} 增强型四通道数字隔离器

1 特性

- 信令速率：最高 100Mbps
- 宽电源电压范围：2.25V 至 5.5V
- 2.25V 至 5.5V 电平转换
- 宽温度范围：-55°C 至 125°C
- 低功耗，1Mbps 时每通道的电流典型值为 1.7mA
- 低传播延迟：典型值为 11ns
(5V 电源)
- 出色的 CMTI (最小值)：±100kV/μs
- 优异的电磁兼容性 (EMC)
- 系统级 ESD、EFT 和浪涌抗扰性
- 低辐射
- 隔离栅寿命：> 40 年
- 宽体 SOIC-16 封装和超宽体 SOIC-16 封装选项
- 安全和监管批准：
 - 符合 DIN EN IEC 60747-17 (VDE 0884-17) 的 8000V_{PK} 增强型隔离
 - 符合 UL 1577 标准且长达 1 分钟的 5.7kV_{RMS} 隔离
 - CSA 组件验收通知 5A、IEC 60950-1 和 IEC 60601-1 终端设备标准
 - 符合 GB4943.1 标准的 CQC 认证
 - 符合 EN 61010-1 和 EN 62368-1 标准的 TUV 认证

2 应用

- 工业自动化
- 电机控制
- 电源
- 光伏逆变器
- 医疗设备
- 混合动力电动汽车

3 说明

ISO7841x 器件是一款高性能四通道数字隔离器，隔离电压为 8000V_{PK}。该器件已通过符合 VDE、CSA、CQC 和 TUV 标准的增强型隔离认证。在隔离 CMOS 或 LVCMOS 数字 I/O 时，该隔离器能够以低功耗提供高电磁抗扰度和低辐射。每个隔离通道都有由二氧化硅 (SiO₂) 绝缘栅隔开的逻辑输入和输出缓冲器。

该器件配有使能引脚，可用于将相应输出置于高阻态以适用于多控制器驱动应用，并降低功耗。ISO7841 器件具有三个正向通道和一个反向通道。如果出现输入功率或信号丢失，ISO7841 器件默认输出为高电平，ISO7841F 器件默认输出为低电平。请参阅 [器件功能模式](#) 部分，了解更多详细信息。


与隔离式电源结合使用时，该器件有助于防止数据总线或者其他电路中的噪声电流进入本地接地端，进而干扰或损坏敏感电路。凭借创新的芯片设计和布局技术，ISO7841 器件的电磁兼容性得到了显著增强，可轻松满足系统级 ESD、EFT、浪涌和辐射方面的要求。

ISO7841 器件采用 16 引脚 SOIC 宽体 (DW) 和超宽体 (DWW) 封装。

封装信息

器件型号	封装 ⁽¹⁾	封装尺寸 ⁽²⁾	本体尺寸 (标称值)
ISO7841 ISO7841F	DW (16)	10.30mm × 10.30mm	10.30mm × 7.50mm
	DWW (16)	10.30mm × 17.25mm	10.30mm × 14.0mm

- (1) 如需了解所有可用封装，请参阅数据末尾的可订购产品附录。
- (2) 封装尺寸 (长 × 宽) 为标称值，并包括引脚 (如适用)。



V_{CCI} 和 GNDI 分别是输入通道的电源和接地连接引脚。

V_{CCO} 和 GNDO 分别是输出通道的电源和接地连接引脚。

简化版原理图



Table of Contents

1 特性	1	5.19 Typical Characteristics	17
2 应用	1	6 Parameter Measurement Information	18
3 说明	1	7 Detailed Description	20
4 Pin Configuration and Functions	2	7.1 Overview.....	20
Pin Functions.....	2	7.2 Functional Block Diagram.....	20
5 Specifications	3	7.3 Feature Description.....	21
5.1 Absolute Maximum Ratings.....	3	7.4 Device Functional Modes.....	21
5.2 ESD Ratings.....	3	8 Application and Implementation	22
5.3 Recommended Operating Conditions.....	3	8.1 Application Information.....	22
5.4 Thermal Information.....	4	8.2 Typical Application.....	22
5.5 Power Ratings.....	4	8.3 Power Supply Recommendations.....	24
5.6 Insulation Specifications.....	5	8.4 Layout.....	25
5.7 Safety-Related Certifications.....	6	9 Device and Documentation Support	26
5.8 Safety Limiting Values.....	6	9.1 Documentation Support.....	26
5.9 Electrical Characteristics—5V Supply.....	7	9.2 Related Links.....	26
5.10 Supply Current Characteristics—5V Supply.....	8	9.3 Receiving Notification of Documentation Updates.....	26
5.11 Electrical Characteristics—3.3V Supply.....	9	9.4 支持资源.....	26
5.12 Supply Current Characteristics—3.3V Supply.....	10	9.5 Trademarks.....	26
5.13 Electrical Characteristics—2.5V Supply.....	11	9.6 静电放电警告.....	26
5.14 Supply Current Characteristics—2.5V Supply.....	12	9.7 术语表.....	26
5.15 Switching Characteristics—5V Supply.....	13	10 Revision History	26
5.16 Switching Characteristics—3.3V Supply.....	14	11 Mechanical, Packaging, and Orderable Information	27
5.17 Switching Characteristics—2.5V Supply.....	15		
5.18 Insulation Characteristics Curves.....	16		

4 Pin Configuration and Functions

Pin Functions

PIN		Type ⁽¹⁾	DESCRIPTION
NAME	NO.		
EN1	7	I	Output enable 1. Output pins on side 1 are enabled when EN1 is high or open and in high-impedance state when EN1 is low.
EN2	10	I	Output enable 2. Output pins on side 2 are enabled when EN2 is high or open and in high-impedance state when EN2 is low.
GND1	2	—	Ground connection for V _{CC1}
	8		
GND2	9	—	Ground connection for V _{CC2}
	15		
INA	3	I	Input, channel A
INB	4	I	Input, channel B
INC	5	I	Input, channel C
IND	11	I	Input, channel D
OUTA	14	O	Output, channel A
OUTB	13	O	Output, channel B
OUTC	12	O	Output, channel C
OUTD	6	O	Output, channel D
V _{CC1}	1	—	Power supply, V _{CC1}
V _{CC2}	16	—	Power supply, V _{CC2}

(1) I = Input, O = Output

5 Specifications

5.1 Absolute Maximum Ratings

See (1)

		MIN	MAX	UNIT
V_{CC1} , V_{CC2}	Supply voltage ⁽²⁾	- 0.5	6	V
Voltage	INx	- 0.5	$V_{CCX} + 0.5^{(3)}$	V
	OUTx	- 0.5	$V_{CCX} + 0.5^{(3)}$	
	ENx	- 0.5	$V_{CCX} + 0.5^{(3)}$	
I_O	Output current	- 15	15	mA
	Surge immunity		12.8	kV
T_{stg}	Storage temperature	- 65	150	°C

- (1) Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. *Absolute Maximum Ratings* do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If used outside the *Recommended Operating Conditions* but within the *Absolute Maximum Ratings*, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) All voltage values except differential I/O bus voltages are with respect to the local ground terminal (GND1 or GND2) and are peak voltage values.
- (3) Maximum voltage must not exceed 6V

5.2 ESD Ratings

			VALUE	UNIT
V _(ESD)	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±6000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±1500	

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

			MIN	NOM	MAX	UNIT
V_{CC1} , V_{CC2}	Supply voltage		2.25		5.5	V
I_{OH}	High-level output current	$V_{CCO}^{(2)} = 5V$	-4			mA
		$V_{CCO}^{(2)} = 3.3V$	-2			
		$V_{CCO}^{(2)} = 2.5V$	-1			
I_{OL}	Low-level output current	$V_{CCO}^{(2)} = 5V$		4		mA
		$V_{CCO}^{(2)} = 3.3V$		2		
		$V_{CCO}^{(2)} = 2.5V$		1		
V_{IH}	High-level input voltage		$0.7 \times V_{CCI}^{(2)}$		$V_{CCI}^{(2)}$	V
V_{IL}	Low-level input voltage		0		$0.3 \times V_{CCI}^{(2)}$	V
DR	Signaling Rate		0		100	Mbps
T_J	Junction temperature ⁽¹⁾		-55		150	°C
T_A	Ambient temperature		-55	25	125	°C

- (1) To maintain the recommended operating conditions for T_J , see § 5.4.
- (2) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.4 Thermal Information

THERMAL METRIC ⁽¹⁾		ISO7841		UNIT
		DW (SOIC)	DWW (SOIC)	
		16 Pins	16 Pins	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	78.9	78.9	°C/W
$R_{\theta JC(top)}$	Junction-to-case(top) thermal resistance	41.6	41.1	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	43.6	49.5	°C/W
ψ_{JT}	Junction-to-top characterization parameter	15.5	15.2	°C/W
ψ_{JB}	Junction-to-board characterization parameter	43.1	48.8	°C/W
$R_{\theta JC(bottom)}$	Junction-to-case(bottom) thermal resistance	N/A	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application note.

5.5 Power Ratings

$V_{CC1} = V_{CC2} = 5.5V$, $T_J = 150^{\circ}C$, $C_L = 15pF$, input a 50MHz 50% duty cycle square wave

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
P_D	Maximum power dissipation by ISO7841x				200	mW
P_{D1}	Maximum power dissipation by side-1 of ISO7841x				75	mW
P_{D2}	Maximum power dissipation by side-2 of ISO7841x				125	mW

5.6 Insulation Specifications

PARAMETER		TEST CONDITIONS	SPECIFICATION		UNIT
			DW	DWW	
GENERAL					
CLR	External clearance ⁽¹⁾	Shortest pin-to-pin distance through air	>8	>14.5	mm
		Shortest pin-to-pin distance through air (typical)		15.0	mm
CPG	External creepage ⁽¹⁾	Shortest pin-to-pin distance across the package surface	>8	>14.5	mm
		Shortest pin-to-pin distance across the package surface (typical)		15.0	mm
DTI	Distance through the insulation	Minimum internal gap (internal clearance)	>21	>21	μ m
CTI	Comparative tracking index	DIN EN 60112 (VDE 0303-11); IEC 60112; UL 746A	>600	>600	V
	Material group		I	I	
	Overvoltage category per IEC 60664-1	Rated mains voltage ≤ 600V _{RMS}	I – IV	I – IV	
		Rated mains voltage ≤ 1000V _{RMS}	I – III	I – IV	
DIN EN IEC 60747-17 (VDE 0884-17) ⁽²⁾					
V _{IORM}	Maximum repetitive peak isolation voltage		2121	2828	V _{PK}
V _{IOWM}	Maximum isolation working voltage	AC voltage (sine wave); Time dependent dielectric breakdown (TDDb) Test, see 图 5-1 and 图 5-2	1500	2000	V _{RMS}
		DC voltage	2121	2828	V _{DC}
V _{IOTM}	Maximum transient isolation voltage	V _{TEST} = 1.2 × V _{IOTM} t = 60s (qualification) t= 1s (100% production)	8000	8000	V _{PK}
V _{IMP}	Maximum impulse voltage ⁽³⁾	Tested in air, 1.2/50 μ s waveform per IEC 62368-1	9800	9800	V _{PK}
V _{IOSM}	Maximum surge isolation voltage ⁽⁴⁾	V _{IOSM} ≥ 1.3 x V _{IMP} ; Tested in oil (qualification test), 1.2/50- μ s waveform per IEC 62368-1	12800	12800	V _{PK}
q _{pd}	Apparent charge ⁽⁵⁾	Method a: After I/O safety test subgroup 2/3, V _{ini} = V _{IOTM} , t _{ini} = 60s; V _{pd(m)} = 1.2 × V _{IOTM} = 2545V _{PK} (DW) and 3394V _{PK} (DWW), t _m = 10s	≤5	≤5	pC
		Method a: After environmental tests subgroup 1, V _{ini} = V _{IOTM} , t _{ini} = 60s; V _{pd(m)} = 1.6 × V _{IORM} = 3394V _{PK} (DW) and 4525V _{PK} (DWW), t _m = 10s	≤5	≤5	
		Method b: At routine test (100% production); V _{ini} = 1.2 x V _{IOTM} , t _{ini} = 1s; V _{pd(m)} = 1.875 x V _{IORM} , t _m = 1s (method b1) or V _{pd(m)} = V _{ini} , t _m = t _{ini} (method b2)	≤5	≤5	
C _{IO}	Barrier capacitance, input to output ⁽⁶⁾	V _{IO} = 0.4 × sin (2 π ft), f = 1MHz	2	2	pF
R _{IO}	Isolation resistance, input to output ⁽⁶⁾	V _{IO} = 500V, T _A = 25°C	>10 ¹²	>10 ¹²	Ω
		V _{IO} = 500V, 100°C ≤ T _A ≤ 125°C	>10 ¹¹	>10 ¹¹	
		V _{IO} = 500V at T _S = 150°C	>10 ⁹	>10 ⁹	
	Pollution degree		2	2	
	Climatic category		55/125/21	55/125/21	
UL 1577					
V _{ISO}	Withstand isolation voltage	V _{TEST} = V _{ISO} = 5700V _{RMS} , t = 60s (qualification), V _{TEST} = 1.2 × V _{ISO} = 6840V _{RMS} , t = 1s (100% production)	5700	5700	V _{RMS}

(1) Creepage and clearance requirements should be applied according to the specific equipment isolation standards of an application. Care should be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the

isolator on the printed-circuit board do not reduce this distance. Creepage and clearance on a printed-circuit board become equal in certain cases. Techniques such as inserting grooves, ribs, or both on a printed circuit board are used to help increase these specifications.

- (2) This coupler is suitable for *safe electrical insulation* only within the safety ratings. Compliance with the safety ratings shall be ensured by means of suitable protective circuits.
- (3) Testing is carried out in air to determine the surge immunity of the package.
- (4) Testing is carried out in oil to determine the intrinsic surge immunity of the isolation barrier.
- (5) Apparent charge is electrical discharge caused by a partial discharge (pd).
- (6) All pins on each side of the barrier tied together creating a two-terminal device.

5.7 Safety-Related Certifications

VDE	CSA	UL	CQC	TUV
Certified according to DIN EN IEC 60747-17 (VDE 0884-17)	Approved under CSA Component Acceptance Notice 5A, IEC 60950-1 and IEC 60601-1	Certified according to UL 1577 Component Recognition Program	Certified according to GB 4943.1	Certified according to EN 61010-1 and EN 62368-1
Reinforced insulation Maximum transient isolation voltage, $8000V_{PK}$; Maximum repetitive peak isolation voltage, $2121V_{PK}$ (DW), $2828V_{PK}$ (DWW); Maximum surge isolation voltage, $12800V_{PK}$	Reinforced insulation per CSA 60950-1-07+A1+A2 and IEC 60950-1 2nd Ed., $800V_{RMS}$ (DW) and $1450V_{RMS}$ (DWW) max working voltage (pollution degree 2, material group I); 2 MOPP (Means of Patient Protection) per CSA 60601-1:14 and IEC 60601-1 Ed. 3.1, $250V_{RMS}$ (DW) and $400V_{RMS}$ (DWW) max working voltage	Single protection, $5700V_{RMS}$	Reinforced Insulation, Altitude $\leq 5000m$, Tropical Climate, $700V_{RMS}$ (DW) and $1450V_{RMS}$ (DWW) maximum working voltage	$5700V_{RMS}$ Reinforced insulation per EN 61010-1 up to working voltage of $600V_{RMS}$ (DW) and $1000V_{RMS}$ (DWW); $5700V_{RMS}$ Reinforced insulation per EN 62368-1 up to working voltage of $800V_{RMS}$ (DW) and $1450V_{RMS}$ (DWW)
Certificate number: 40040142	Master contract number: 220991	File number: E181974	Certificate number: CQC15001121716	Client ID number: 77311

5.8 Safety Limiting Values

Safety limiting intends to minimize potential damage to the isolation barrier upon failure of input or output circuitry. A failure of the I/O can allow low resistance to ground or the supply and, without current limiting, dissipate sufficient power to overheat the die and damage the isolation barrier potentially leading to secondary system failures.

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
I_S Safety input, output, or supply current	$R_{\theta JA} = 78.9^{\circ}C/W$, $V_I = 5.5V$, $T_J = 150^{\circ}C$, $T_A = 25^{\circ}C$			288	mA
	$R_{\theta JA} = 78.9^{\circ}C/W$, $V_I = 3.6V$, $T_J = 150^{\circ}C$, $T_A = 25^{\circ}C$			440	
	$R_{\theta JA} = 78.9^{\circ}C/W$, $V_I = 2.75V$, $T_J = 150^{\circ}C$, $T_A = 25^{\circ}C$			576	
P_S Safety input, output, or total power	$R_{\theta JA} = 78.9^{\circ}C/W$, $T_J = 150^{\circ}C$, $T_A = 25^{\circ}C$			1584	mW
T_S Maximum safety temperature				150	$^{\circ}C$

The maximum safety temperature is the maximum junction temperature specified for the device. The power dissipation and junction-to-air thermal impedance of the device installed in the application hardware determines the junction temperature. The assumed junction-to-air thermal resistance in the [节 5.4](#) is that of a device installed on a high-K test board for leaded surface-mount packages. The power is the recommended maximum input voltage times the current. The junction temperature is then the ambient temperature plus the power times the junction-to-air thermal resistance.

5.9 Electrical Characteristics—5V Supply

$V_{CC1} = V_{CC2} = 5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{OH}	High-level output voltage	$I_{OH} = -4mA$; see 图 6-1	$V_{CCO}^{(1)} - 0.4$	$V_{CCO}^{(1)} - 0.2$		V
V_{OL}	Low-level output voltage	$I_{OL} = 4mA$; see 图 6-1		0.2	0.4	V
$V_{I(HYS)}$	Input threshold voltage hysteresis		$0.1 \times V_{CCI}^{(1)}$			V
I_{IH}	High-level input current	$V_{IH} = V_{CCI}^{(1)}$ at INx or ENx			10	μA
I_{IL}	Low-level input current	$V_{IL} = 0V$ at INx or ENx	- 10			μA
CMTI	Common-mode transient immunity	$V_I = V_{CCI}^{(1)}$ or 0V, $V_{CM} = 1500V$; see 图 6-4	100			kV/ μs
C_I	Input capacitance	$V_I = V_{CC}/2 + 0.4 \times \sin(2\pi ft)$, $f = 1MHz$, $V_{CC} = 5V$		2		pF

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.10 Supply Current Characteristics—5V Supply

$V_{CC1} = V_{CC2} = 5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS		SUPPLY CURRENT	MIN	TYP	MAX	UNIT
ISO7841DW AND ISO7841FDW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.8	mA
			I _{CC2}		0.8	1.3	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.6	mA
			I _{CC2}		2	2.9	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.5	2.4	mA
			I _{CC2}		2.1	3.1	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5	7.3	mA
			I _{CC2}		3.4	4.9	
	All channels switching with square wave clock input; C _L = 15pF	1Mbps	I _{CC1}		3.3	4.9	mA
			I _{CC2}		2.9	4.2	
		10Mbps	I _{CC1}		3.9	5.5	mA
			I _{CC2}		4.4	5.7	
		100Mbps	I _{CC1}		9.2	11.6	mA
			I _{CC2}		19	21.9	
ISO7841DWW AND ISO7841FDWW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.8	mA
			I _{CC2}		0.8	1.3	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.6	mA
			I _{CC2}		2	2.9	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.5	2.4	mA
			I _{CC2}		2.1	3.3	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5	7.5	mA
			I _{CC2}		3.4	5.2	
	All channels switching with square wave clock input;C _L = 15pF	1Mbps	I _{CC1}		3.4	5	mA
			I _{CC2}		3	4.4	
		10Mbps	I _{CC1}		4	5.6	mA
			I _{CC2}		4.5	6.1	
		100Mbps	I _{CC1}		9.4	12.1	mA
			I _{CC2}		19.5	22.6	

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.11 Electrical Characteristics—3.3V Supply

$V_{CC1} = V_{CC2} = 3.3V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{OH}	High-level output voltage $I_{OH} = -2mA$; see 图 6-1	$V_{CCO}^{(1)} - 0.4$	$V_{CCO}^{(1)} - 0.2$		V
V_{OL}	Low-level output voltage $I_{OL} = 2mA$; see 图 6-1		0.2	0.4	V
$V_{I(HYS)}$	Input threshold voltage hysteresis	$0.1 \times V_{CCI}^{(1)}$			V
I_{IH}	High-level input current $V_{IH} = V_{CCI}^{(1)}$ at INx or ENx			10	μA
I_{IL}	Low-level input current $V_{IL} = 0V$ at INx or ENx	-10			μA
CMTI	Common-mode transient immunity $V_I = V_{CCI}^{(1)}$ or 0V, $V_{CM} = 1500V$; see 图 6-4	100			kV/ μs

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.12 Supply Current Characteristics—3.3V Supply

$V_{CC1} = V_{CC2} = 3.3V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS		SUPPLY CURRENT	MIN	TYP	MAX	UNIT
ISO7841DW AND ISO7841FDW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.8	mA
			I _{CC2}		0.8	1.3	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.6	mA
			I _{CC2}		1.9	2.9	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.5	2.4	mA
			I _{CC2}		2.1	3.1	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5	7.3	mA
			I _{CC2}		3.3	4.9	
	All channels switching with square wave clock input; C _L = 15pF	1Mbps	I _{CC1}		3.3	4.9	mA
			I _{CC2}		2.8	4.1	
		10Mbps	I _{CC1}		3.7	5.3	mA
			I _{CC2}		3.9	5.2	
		100Mbps	I _{CC1}		7.4	9.3	mA
			I _{CC2}		14.5	16.9	
ISO7841DWW AND ISO7841FDWW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.8	mA
			I _{CC2}		0.8	1.3	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.6	mA
			I _{CC2}		2	2.9	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.5	2.4	mA
			I _{CC2}		2.1	3.3	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5	7.5	mA
			I _{CC2}		3.4	5.2	
	All channels switching with square wave clock input; C _L = 15pF	1Mbps	I _{CC1}		3.4	5	mA
			I _{CC2}		2.9	4.4	
		10Mbps	I _{CC1}		3.8	5.4	mA
			I _{CC2}		4	5.5	
		100Mbps	I _{CC1}		7.5	9.9	mA
			I _{CC2}		14.8	17.2	

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.13 Electrical Characteristics—2.5V Supply

$V_{CC1} = V_{CC2} = 2.5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
V_{OH}	High-level output voltage	$I_{OH} = -1mA$; see 图 6-1	$V_{CCO}^{(1)} - 0.4$	$V_{CCO}^{(1)} - 0.2$		V
V_{OL}	Low-level output voltage	$I_{OL} = 1mA$; see 图 6-1		0.2	0.4	V
$V_{I(HYS)}$	Input threshold voltage hysteresis		$0.1 \times V_{CCI}^{(1)}$			V
I_{IH}	High-level input current	$V_{IH} = V_{CCI}^{(1)}$ at INx or ENx			10	μA
I_{IL}	Low-level input current	$V_{IL} = 0V$ at INx or ENx	– 10			μA
CMTI	Common-mode transient immunity	$V_I = V_{CCI}^{(1)}$ or 0V, $V_{CM} = 1500V$; see 图 6-4	100			kV/ μs

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.14 Supply Current Characteristics—2.5V Supply

$V_{CC1} = V_{CC2} = 2.5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS		SUPPLY CURRENT	MIN	TYP	MAX	UNIT
ISO7841DW AND ISO7841FDW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.7	mA
			I _{CC2}		0.8	1.2	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.5	mA
			I _{CC2}		1.9	2.8	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.6	2.3	mA
			I _{CC2}		2.2	3.1	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5.1	7.2	mA
			I _{CC2}		3.5	4.8	
	All channels switching with square wave clock input; C _L = 15pF	1Mbps	I _{CC1}		3.4	4.8	mA
			I _{CC2}		2.9	4	
		10Mbps	I _{CC1}		3.7	5.1	mA
			I _{CC2}		3.7	4.8	
		100Mbps	I _{CC1}		6.8	8.1	mA
			I _{CC2}		12	14.2	
ISO7841DWW AND ISO7841FDWW							
Supply current	Disable	EN1 = EN2 = 0V, V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.1	1.7	mA
			I _{CC2}		0.8	1.2	
		EN1 = EN2 = 0V, V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		4.5	6.5	mA
			I _{CC2}		1.9	2.8	
	DC signal	V _I = 0V (ISO7841F), V _I = V _{CCI} ⁽¹⁾ (ISO7841)	I _{CC1}		1.6	2.4	mA
			I _{CC2}		2.2	3.3	
		V _I = V _{CCI} ⁽¹⁾ (ISO7841F), V _I = 0V (ISO7841)	I _{CC1}		5.1	7.5	mA
			I _{CC2}		3.5	5.2	
	All channels switching with square wave clock input; C _L = 15pF	1Mbps	I _{CC1}		3.5	5	mA
			I _{CC2}		3	4.3	
		10Mbps	I _{CC1}		3.8	5.3	mA
			I _{CC2}		3.8	5.2	
		100Mbps	I _{CC1}		6.9	8.8	mA
			I _{CC2}		12.3	14.2	

(1) V_{CCI} = Input-side V_{CC} ; V_{CCO} = Output-side V_{CC} .

5.15 Switching Characteristics—5V Supply

$V_{CC1} = V_{CC2} = 5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH} , t_{PHL} Propagation delay time	See 图 6-1	6	11	16	ns
PWD Pulse width distortion ⁽¹⁾ $ t_{PHL} - t_{PLH} $			0.55	4.1	ns
$t_{sk(o)}$ Channel-to-channel output skew time ⁽²⁾	Same-direction channels			2.5	ns
$t_{sk(pp)}$ Part-to-part skew time ⁽³⁾				4.5	ns
t_r Output signal rise time	See 图 6-1		1.7	3.9	ns
t_f Output signal fall time			1.9	3.9	ns
t_{PHZ} Disable propagation delay, high-to-high impedance output	See 图 6-2		12	20	ns
t_{PLZ} Disable propagation delay, low-to-high impedance output			12	20	ns
t_{PZH} Enable propagation delay, high impedance-to-high output for ISO7841			10	20	ns
Enable propagation delay, high impedance-to-high output for ISO7841F			2	2.5	μs
t_{PZL} Enable propagation delay, high impedance-to-low output for ISO7841			2	2.5	μs
Enable propagation delay, high impedance-to-low output for ISO7841F			10	20	ns
t_{fs} Default output delay time from input power loss	Measured from the time V_{CC} goes below 1.7V. See 图 6-3		0.2	9	μs
t_{ie} Time interval error	$2^{16} - 1$ PRBS data at 100Mbps		0.90		ns

- (1) Also known as pulse skew.
- (2) $t_{sk(o)}$ is the skew between outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical loads.
- (3) $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any terminals of different devices switching in the same direction while operating at identical supply voltages, temperature, input signals and loads.

5.16 Switching Characteristics—3.3V Supply

$V_{CC1} = V_{CC2} = 3.3V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH} , t_{PHL} Propagation delay time	See 图 6-1	6	10.8	16	ns
PWD Pulse width distortion ⁽¹⁾ $ t_{PHL} - t_{PLH} $			0.7	4.2	ns
$t_{sk(o)}$ Channel-to-channel output skew time ⁽²⁾	Same-direction channels			2.2	ns
$t_{sk(pp)}$ Part-to-part skew time				4.5	ns
t_r Output signal rise time	See 图 6-1		0.8	3	ns
t_f Output signal fall time			0.8	3	ns
t_{PHZ} Disable propagation delay, high-to-high impedance output	See 图 6-2		17	32	ns
t_{PLZ} Disable propagation delay, low-to-high impedance output			17	32	ns
t_{PZH} Enable propagation delay, high impedance-to-high output for ISO7841			17	32	ns
Enable propagation delay, high impedance-to-high output for ISO7841F			2	2.5	μs
t_{PZL} Enable propagation delay, high impedance-to-low output for ISO7841			2	2.5	μs
Enable propagation delay, high impedance-to-low output for ISO7841F			17	32	ns
t_{fs} Default output delay time from input power loss	Measured from the time V_{CC} goes below 1.7V. See 图 6-3		0.2	9	μs
t_{ie} Time interval error	$2^{16} - 1$ PRBS data at 100Mbps		0.91		ns

(1) Also known as Pulse Skew.

(2) $t_{sk(o)}$ is the skew between outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical loads.

5.17 Switching Characteristics—2.5V Supply

 $V_{CC1} = V_{CC2} = 2.5V \pm 10\%$ (over recommended operating conditions unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
t _{PLH} , t _{PHL}	Propagation delay time	See 图 6-1	7.5	11.7	17.5	ns
PWD	Pulse width distortion ⁽¹⁾ t _{PHL} - t _{PLH}		0.66	4.2	ns	
t _{sk(o)}	Channel-to-channel output skew time ⁽²⁾	Same-direction Channels			2.2	ns
t _{sk(pp)}	Part-to-part skew time ⁽³⁾				4.5	ns
t _r	Output signal rise time	See 图 6-1		1	3.5	ns
t _f	Output signal fall time			1.2	3.5	ns
t _{PHZ}	Disable propagation delay, high-to-high impedance output	See 图 6-2		22	45	ns
t _{PLZ}	Disable propagation delay, low-to-high impedance output			22	45	ns
t _{PZH}	Enable propagation delay, high impedance-to-high output for ISO7841			18	45	ns
	Enable propagation delay, high impedance-to-high output for ISO7841F			2	2.5	μ s
t _{PZL}	Enable propagation delay, high impedance-to-low output for ISO7841			2	2.5	μ s
	Enable propagation delay, high impedance-to-low output for ISO7841F			18	45	ns
t _{fs}	Default output delay time from input power loss	Measured from the time V _{CC} goes below 1.7V. See 图 6-3		0.2	9	μ s
t _{ie}	Time interval error	2 ¹⁶ - 1 PRBS data at 100Mbps		0.91		ns

- (1) Also known as pulse skew.
- (2) $t_{sk(o)}$ is the skew between outputs of a single device with all driving inputs connected together and the outputs switching in the same direction while driving identical loads.
- (3) $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any terminals of different devices switching in the same direction while operating at identical supply voltages, temperature, input signals and loads.

5.18 Insulation Characteristics Curves




图 5-1. Reinforced Isolation Capacitor Life Time Projection for Devices in DW Package




图 5-2. Reinforced Isolation Capacitor Life Time Projection for Devices in DWW Package




图 5-3. Thermal Derating Curve for Limiting Current per VDE




图 5-4. Thermal Derating Curve for Limiting Power per VDE

5.19 Typical Characteristics




图 5-5. Supply Current vs Data Rate (With 15pF Load)




图 5-6. Supply Current vs Data Rate (With No Load)




图 5-7. High-Level Output Voltage vs High-level Output Current




图 5-8. Low-Level Output Voltage vs Low-Level Output Current




图 5-9. Power Supply Undervoltage Threshold vs Free-Air Temperature






图 5-10. Propagation Delay Time vs Free-Air Temperature

6 Parameter Measurement Information




- A. The input pulse is supplied by a generator having the following characteristics: $PRR \leq 50\text{kHz}$, 50% duty cycle, $t_r \leq 3\text{ns}$, $t_f \leq 3\text{ns}$, $Z_O = 50\Omega$. At the input, a 50Ω resistor is required to terminate Input Generator signal. The 50Ω resistor is not needed in actual application.
- B. $C_L = 15\text{pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

图 6-1. Switching Characteristics Test Circuit and Voltage Waveforms




- A. The input pulse is supplied by a generator having the following characteristics: $PRR \leq 10\text{kHz}$, 50% duty cycle, $t_r \leq 3\text{ns}$, $t_f \leq 3\text{ns}$, $Z_O = 5\Omega$.
- B. $C_L = 15\text{pF}$ and includes instrumentation and fixture capacitance within $\pm 20\%$.

图 6-2. Enable/Disable Propagation Delay Time Test Circuit and Waveform



A. C_L = 15pF and includes instrumentation and fixture capacitance within ±20%.

图 6-3. Default Output Delay Time Test Circuit and Voltage Waveforms



A. C_L = 15pF and includes instrumentation and fixture capacitance within ±20%.


图 6-4. Common-Mode Transient Immunity Test Circuit

7 Detailed Description

7.1 Overview

The ISO7841 device uses an ON-OFF keying (OOK) modulation scheme to transmit the digital data across a silicon-dioxide based isolation barrier. The transmitter sends a high-frequency carrier across the barrier to represent one digital state and sends no signal to represent the other digital state. The receiver demodulates the signal after advanced signal conditioning and produces the output through a buffer stage. If the EN pin is low then the output goes to high impedance. The ISO7841 device also incorporates advanced circuit techniques to maximize the CMTI performance and minimize the radiated emissions because of the high-frequency carrier and IO buffer switching. The conceptual block diagram of a digital capacitive isolator, 图 7-1, shows a functional block diagram of a typical channel.

7.2 Functional Block Diagram



Copyright © 2016, Texas Instruments Incorporated

图 7-1. Conceptual Block Diagram of a Digital Capacitive Isolator

图 7-2 shows a conceptual detail of how the ON-OFF keying scheme works.




图 7-2. On-Off Keying (OOK) Based Modulation Scheme

7.3 Feature Description

表 7-1 lists the device features.

表 7-1. Device Features

PART NUMBER	CHANNEL DIRECTION	RATED ISOLATION	MAXIMUM DATA RATE	DEFAULT OUTPUT
ISO7841	3 Forward,	5700V _{RMS} / 8000V _{PK} ⁽¹⁾	100Mbps	High
	1 Reverse			
ISO7841F	3 Forward,	5700V _{RMS} / 8000V _{PK} ⁽¹⁾	100Mbps	Low
	1 Reverse			

(1) See *Insulation Specifications* for detailed isolation ratings.

7.3.1 Electromagnetic Compatibility (EMC) Considerations

Many applications in harsh industrial environment are sensitive to disturbances such as electrostatic discharge (ESD), electrical fast transient (EFT), surge, and electromagnetic emissions. These electromagnetic disturbances are regulated by international standards such as IEC 61000-4-x and CISPR 22. Although system-level performance and reliability depends, to a large extent, on the application board design and layout, the ISO7841 device incorporates many chip-level design improvements for overall system robustness. Some of these improvements include

- Robust ESD protection cells for input and output signal pins and inter-chip bond pads.
- Low-resistance connectivity of ESD cells to supply and ground pins.
- Enhanced performance of high voltage isolation capacitor for better tolerance of ESD, EFT and surge events.
- Bigger on-chip decoupling capacitors to bypass undesirable high energy signals through a low impedance path.
- PMOS and NMOS devices isolated from each other by using guard rings to avoid triggering of parasitic SCRs.
- Reduced common mode currents across the isolation barrier by providing purely differential internal operation.

7.4 Device Functional Modes

表 7-2 lists the ISO7841 functional modes.

表 7-2. Function Table

V _{CCI}	V _{CCO}	INPUT (IN _x) ⁽²⁾	OUTPUT ENABLE (EN _x)	OUTPUT (OUT _x)	COMMENTS
PU	PU	H	H or open	H	Normal Operation: A channel output assumes the logic state of the input.
		L	H or open	L	
		Open	H or open	Default	Default mode: When IN _x is open, the corresponding channel output goes to the default logic state. Default= High for ISO7841 and Low for ISO7841F.
X	PU	X	L	Z	A low value of Output Enable causes the outputs to be high-impedance
PD	PU	X	H or open	Default	Default mode: When V _{CCI} is unpowered, a channel output assumes the logic state based on the selected default option. Default= High for IISO7841 and Low for ISO7841F. When V _{CCI} transitions from unpowered to powered-up, a channel output assumes the logic state of the input. When V _{CCI} transitions from powered-up to unpowered, channel output assumes the selected default state.
X	PD	X	X	Undetermined	When V _{CCO} is unpowered, a channel output is undetermined ⁽¹⁾ . When V _{CCO} transitions from unpowered to powered-up, a channel output assumes the logic state of the input

(1) The outputs are undetermined when 1.7V < V_{CCI}, V_{CCO} < 2.25V.

(2) A strongly driven input signal can weakly power the floating V_{CC} through an internal protection diode and cause undetermined output.

7.4.1 Device I/O Schematics




图 7-3. Device I/O Schematics

8 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

8.1 Application Information

The ISO7841 device is a high-performance, quad-channel digital isolator with a $5.7\text{kV}_{\text{RMS}}$ isolation voltage per UL 1577. The device comes with enable pins on each side that can be used to put the respective outputs in high impedance for multi-controller driving applications and reduce power consumption. The ISO7841 device uses single-ended CMOS-logic switching technology. The supply voltage range is from 2.25V to 5.5V for both supplies, V_{CC1} and V_{CC2} . When designing with digital isolators, keep in mind that because of the single-ended design structure, digital isolators do not conform to any specific interface standard and are only intended for isolating single-ended CMOS or TTL digital signal lines. The isolator is typically placed between the data controller (that is, μC or UART), and a data converter or a line transceiver, regardless of the interface type or standard.

8.2 Typical Application

图 8-1 shows the isolated SPI.




图 8-1. Isolated SPI for an Analog Input Module With 16 Input

8.2.1 Design Requirements


For this design example, use the parameters shown in 表 8-1.

表 8-1. Design Parameters

PARAMETER	VALUE
Supply voltage	2.25V to 5.5V
Decoupling capacitor between V _{CC1} and GND1	0.1µF
Decoupling capacitor from V _{CC2} and GND2	0.1µF

8.2.2 Detailed Design Procedure

Unlike optocouplers, which require external components to improve performance, provide bias, or limit current, the ISO7841 device only requires two external bypass capacitors to operate.



Copyright © 2016, Texas Instruments Incorporated

图 8-2. Typical ISO7841 Circuit Hook-Up

8.2.3 Application Curve

The typical eye diagram of the ISO7841 device indicates low jitter and wide open eye at the maximum data rate of 100Mbps.




图 8-3. Eye Diagram at 100Mbps PRBS, 5V and 25°C

8.3 Power Supply Recommendations

To help provide reliable operation at data rates and supply voltages, a 0.1 μF bypass capacitor is recommended at input and output supply pins (V_{CC1} and V_{CC2}). The capacitors must be placed as close to the supply pins as possible. If only a single primary-side power supply is available in an application, isolated power can be generated for the secondary-side with the help of a transformer driver such as Texas Instruments [SN6501](#). For such applications, detailed power supply design and transformer selection recommendations are available in [SN6501 Transformer Driver for Isolated Power Supplies](#).

8.4 Layout

8.4.1 Layout Guidelines

A minimum of four layers is required to accomplish a low EMI PCB design (see 图 8-4). Layer stacking must be in the following order (top-to-bottom): high-speed signal layer, ground plane, power plane and low-frequency signal layer.

- Routing the high-speed traces on the top layer avoids the use of vias (and the introduction of the inductances) and allows for clean interconnects between the isolator and the transmitter and receiver circuits of the data link.
- Placing a solid ground plane next to the high-speed signal layer establishes controlled impedance for transmission line interconnects and provides an excellent low-inductance path for the return current flow.
- Placing the power plane next to the ground plane creates additional high-frequency bypass capacitance of approximately 100pF/inch².
- Routing the slower speed control signals on the bottom layer allows for greater flexibility as these signal links typically have margin to tolerate discontinuities such as vias.

If an additional supply voltage plane or signal layer is needed, add a second power or ground plane system to the stack to keep the planes symmetrical. This makes the stack mechanically stable and prevents warping. Also the power and ground plane of each power system can be placed closer together, thus increasing the high-frequency bypass capacitance significantly.

For detailed layout recommendations, refer to [Digital Isolator Design Guide](#).

8.4.1.1 PCB Material

For digital circuit boards operating at less than 150Mbps, (or rise and fall times greater than 1ns), and trace lengths of up to 10 inches, use standard FR-4 UL94V-0 printed circuit board. This PCB is preferred over cheaper alternatives because of lower dielectric losses at high frequencies, less moisture absorption, greater strength and stiffness, and the self-extinguishing flammability-characteristics.

8.4.2 Layout Example




图 8-4. Layout Example Schematic

9 Device and Documentation Support

9.1 Documentation Support

9.1.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, [ADS79xx Pin Compatible, 12-, 10-, 8-Bit, 1-MSPS, 16-, 12-, 8-, 4-Channel, Single-Ended, Serial Interface ADCs](#), data sheet
- Texas Instruments, [Digital Isolator Design Guide](#), application note
- Texas Instruments, [Isolation Glossary](#), application note
- Texas Instruments, [MSP430G2x32, MSP430G2x02 Mixed Signal Microcontrollers](#), data sheet
- Texas Instruments, [REF50xx Low-Noise, Very Low Drift, Precision Voltage Reference](#), data sheet
- Texas Instruments, [Transformer Driver for Isolated Power Supplies](#), data sheet
- Texas Instruments, [TLV707, TLV707P 200-mA, Low-IQ, Low-Noise, Low-Dropout Regulator for Portable Devices](#), data sheet

9.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

表 9-1. Related Links

PARTS	PRODUCT FOLDER	ORDER NOW	TECHNICAL DOCUMENTS	TOOLS & SOFTWARE	SUPPORT & COMMUNITY
ISO7841	Click here	Click here	Click here	Click here	Click here
ISO7841F	Click here	Click here	Click here	Click here	Click here

9.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

9.4 支持资源

TI E2E™ 中文支持论坛是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的[使用条款](#)。

9.5 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

9.6 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

9.7 术语表

TI 术语表 本术语表列出并解释了术语、首字母缩略词和定义。

10 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision H (November 2014) to Revision I (November 2024)	Page
• 更新了整个文档中的表格、图和交叉参考的编号格式.....	1
• Added 15mm (typ) creepage/clearance to <i>Insulation Specifications</i> table.....	5


Changes from Revision G (March 2017) to Revision H (May 2024)	Page
• 更新了整个文档中的表格、图和交叉参考的编号格式.....	1
• 通篇将标准名称从 “DIN V VDE V 0884-10 (VDE V 0884-10):2006-12” 更新为 “DIN EN IEC 60747-17 (VDE 0884-17)”	1
• Added Maximum impulse voltage (V_{IMP}) specification to the <i>Insulation Specifications</i> section per DIN EN IEC 60747-17 (VDE 0884-17).....	5
• Changed test conditions and values of Maximum surge isolation voltage (V_{IOSM}) specification per DIN EN IEC 60747-17 (VDE 0884-17).....	5
• Added clarification to method b test conditions for Apparent charge (q_{PD}).....	5
• Changed the title of the <i>Electrical Characteristics—3.3V Supply</i> section to <i>Supply Current Characteristics—3.3V Supply</i>	10
• Changed <i>Reinforced Isolation Capacitor Life Time Projection</i> for DW and DWW packages per DIN EN IEC 60747-17 (VDE 0884-17).....	16

Changes from Revision F (April 2016) to Revision G (March 2017)	Page
• Changed part numbers in the <i>Power Ratings</i> table (previously <i>Power Dissipation Characteristics</i>)	4
• Changed the input-to-output test voltage parameter to apparent charge in the <i>Insulation Specifications</i>	5
• Added the <i>Receiving Notification of Documentation Updates</i> section.....	26


Changes from Revision E (March 2016) to Revision F (April 2016)	Page
• 更改了 <i>特性</i> 部分中的隔离栅寿命年数.....	1
• VDE 认证现已完成.....	1
• Changed V_{CCO} to V_{CCI} for the minimum value of the input threshold voltage hysteresis parameter in all electrical characteristics tables.....	7
• Added V_{CM} to the test condition of the common-mode transient immunity parameter in all electrical characteristics tables.....	7
• Added the lifetime projection graphs for DW and DWW packages to the <i>Safety Limiting Values</i> section	16

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**DW0016B**
PACKAGE OUTLINE
SOIC - 2.65 mm max height

SOIC

**NOTES:**

1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
5. Reference JEDEC registration MS-013.


www.ti.com

EXAMPLE BOARD LAYOUT

DW0016B

SOIC - 2.65 mm max height

SOIC




NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

www.ti.com

EXAMPLE STENCIL DESIGN**DW0016B****SOIC - 2.65 mm max height**

SOIC



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

www.ti.com




DWW0016A

PACKAGE OUTLINE

SOIC - 2.65 mm max height

PLASTIC SMALL OUTLINE




NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash.

www.ti.com

EXAMPLE BOARD LAYOUT**DWW0016A****SOIC - 2.65 mm max height**

PLASTIC SMALL OUTLINE



NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.


6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DWW0016A

SOIC - 2.65 mm max height

PLASTIC SMALL OUTLINE



NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

www.ti.com

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
ISO7841DW	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DW.A	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWW	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWW.A	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWWR	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841DWWR.A	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841
ISO7841FDW	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDW.A	Active	Production	SOIC (DW) 16	40 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWR	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWR.A	Active	Production	SOIC (DW) 16	2000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWW	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWW.A	Active	Production	SOIC (DWW) 16	45 TUBE	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWWR	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F
ISO7841FDWWR.A	Active	Production	SOIC (DWW) 16	1000 LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	ISO7841F

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) Part marking: There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ISO7841DWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7841DWWR	SOIC	DWW	16	1000	330.0	24.4	18.0	10.0	3.0	20.0	24.0	Q1
ISO7841FDWR	SOIC	DW	16	2000	330.0	16.4	10.75	10.7	2.7	12.0	16.0	Q1
ISO7841FDWWR	SOIC	DWW	16	1000	330.0	24.4	18.0	10.0	3.0	20.0	24.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ISO7841DWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7841DWWR	SOIC	DWW	16	1000	350.0	350.0	43.0
ISO7841FDWR	SOIC	DW	16	2000	350.0	350.0	43.0
ISO7841FDWWR	SOIC	DWW	16	1000	350.0	350.0	43.0

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
ISO7841DW	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7841DW.A	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7841DWW	DWW	SOIC	16	45	507	20	5000	9
ISO7841DWW.A	DWW	SOIC	16	45	507	20	5000	9
ISO7841FDW	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7841FDW.A	DW	SOIC	16	40	506.98	12.7	4826	6.6
ISO7841FDWW	DWW	SOIC	16	45	507	20	5000	9
ISO7841FDWW.A	DWW	SOIC	16	45	507	20	5000	9

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月