

# OPA137, OPA2137, OPA4137 Low Cost FET-Input Operational Amplifiers Micro Amplifier™ Series

## 1 Features

- FET Input:  $I_B = \pm 10\text{pA}$
- Low offset voltage:  $\pm 300\text{mV}$
- Wide supply range:  $\pm 2.25\text{ V}$  to  $\pm 18\text{ V}$
- Low quiescent current:  $120\mu\text{A}/\text{channel}$
- Excellent speed/power:  $1.1\text{MHz}$
- Input to positive supply
- Single, dual, and quad

## 2 Applications

- Strain gage amplifier
- Photodetector amplifier
- Precision integrator
- Battery-powered instruments
- Test equipment
- Active filters

## 3 Description

OPA137 series FET- input operational amplifiers are designed for low cost and miniature applications. In addition to small size (SOT-23-5 and MSOP-8 packages), amplifiers provide low input bias current ( $\pm 10\text{pA}$ ), low quiescent current ( $120\mu\text{A}/\text{channel}$ ), and high open-loop gain ( $145\text{dB}$ ).

Either single ( $+4.5\text{V}$  to  $+36\text{V}$ ) or dual ( $\pm 2.25\text{V}$  to  $\pm 18\text{V}$ ) supplies can be used. The input common-mode voltage range includes the positive supply an excellent choice for many single-supply applications. Single, dual, and quad versions have identical specifications for maximum design flexibility.

OPA137 op amps are easy to use and free from phase inversion and overload problems found in some

FET- input amplifiers. High performance, including linearity, is maintained as the amplifiers swing to the specified limits. In addition, the combination of high slew rate ( $4.5\text{V}/\mu\text{s}$ ) and wide bandwidth ( $1.1\text{MHz}$ ) provide fast settling time verifies good dynamic response. Dual and quad designs feature completely independent circuitry for lowest crosstalk and freedom from interaction.


The single (OPA137) packages are the tiny 5-lead SOT-23-5 surface mount, SO-8 surface mount, and 8-pin DIP. The dual (OPA2137) comes in the miniature MSOP-8 surface mount, and the SO-8 surface mount. The quad (OPA4137) packages are the SO-14 surface mount and the 14-pin DIP. All are specified from  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$  and operate from  $-55^\circ\text{C}$  to  $+125^\circ\text{C}$ . A SPICE macro-model is available for design analysis.

### Package Information

| PART NUMBER | PACKAGE <sup>(1)</sup> | PACKAGE SIZE <sup>(2)</sup> |
|-------------|------------------------|-----------------------------|
| OPA137      | SOIC (8)               | 4.90mm × 3.90mm             |
|             | SOT-23 (5)             | 2.90mm × 1.60mm             |
| OPA2137     | VSSOP (8)              | 3.00mm × 3.00mm             |
|             | SOIC (8)               | 4.90mm × 3.90mm             |
|             | PDIP (8)               | 6.35mm × 9.81mm             |
| OPA4137     | PDIP (14)              | 6.35mm × 19.30mm            |
|             | SOIC (14)              | 3.91mm × 8.65mm             |

(1) For more information, see [Section 9](#).

(2) The package size (length × width) is a nominal value and includes pins, where applicable.



Symbol (Each Amplifier)



## Table of Contents

|   |          |   |           |
|---|----------|---|-----------|
| <b>1 Features</b> .....                               | <b>1</b> | <b>6 Application and Implementation</b> .....               | <b>13</b> |
| <b>2 Applications</b> .....                           | <b>1</b> | 6.1 Application Information.....                            | 13        |
| <b>3 Description</b> .....                            | <b>1</b> | <b>7 Device and Documentation Support</b> .....             | <b>15</b> |
| <b>4 Pin Configuration and Functions</b> .....        | <b>3</b> | 7.1 Documentation Support.....                              | 15        |
| <b>5 Specifications</b> .....                         | <b>4</b> | 7.2 Receiving Notification of Documentation Updates....     | 15        |
| 5.1 Absolute Maximum Ratings.....                     | 4        | 7.3 Support Resources.....                                  | 15        |
| 5.2 ESD Ratings.....                                  | 4        | 7.4 Trademarks.....   | 15        |
| 5.3 Recommended Operating Conditions.....             | 5        | 7.5 Electrostatic Discharge Caution.....                    | 15        |
| 5.4 Electrical Characteristics, $V_S = \pm 15V$ ..... | 5        | 7.6 Glossary.....   | 15        |
| 5.5 Typical Characteristics.....                      | 6        | <b>8 Revision History</b> .....                             | <b>16</b> |
| 5.6 Old Die to New Die Transition.....                | 12       | <b>9 Mechanical, Packaging, and Orderable Information..</b> | <b>16</b> |

## 4 Pin Configuration and Functions




Figure 4-1. OPA137 SOT-23-5




Figure 4-2. OPA137, SO-8




Figure 4-3. OPA2137 8-Pin DIP, SO-8, MSOP-8




Figure 4-4. OPA4137 14-Pin DIP, SO-14

## 5 Specifications

### 5.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|          |                                     | MIN        | MAX  | UNIT |
|----------|-------------------------------------|------------|------|------|
| V+ to V– | Supply voltage                      |            | 36   | V    |
|          | Input voltage                       | -0.7       | +0.7 | V    |
|          | Input current                       |            | 2    | mA   |
|          | Output short-circuit <sup>(2)</sup> | Continuous |      |      |
|          | Operating temperature               | -55        | +125 | °C   |
|          | Storage temperature                 | -55        | +125 | °C   |
|          | Junction temperature                |            | +150 | °C   |
|          | Lead temperature (soldering, 10s)   |            | 300  | °C   |

- (1) Operation outside the *Absolute Maximum Ratings* may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under *Recommended Operating Conditions*. If used outside the *Recommended Operating Conditions* but within the *Absolute Maximum Ratings*, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
- (2) Short circuit to ground, one amplifier per package.

### 5.2 ESD Ratings

|                    |                         |  | VALUE | UNIT |
|--------------------|-------------------------|--|-------|------|
| V <sub>(ESD)</sub> | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V    |
|                    |                         | Charged device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±1000 |      |

- (1) JEDEC document JEP155 states that 500V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250V CDM allows safe manufacturing with a standard ESD control process.

### 5.3 Recommended Operating Conditions

over operating ambient temperature range (unless otherwise noted)

|                |                             | MIN   | MAX | UNIT |
|----------------|-----------------------------|-------|-----|------|
| V <sub>S</sub> | Supply voltage, (V+) – (V–) | ±2.25 | ±36 | V    |
| V <sub>I</sub> | Input voltage range         | V ±3  |     | V    |
| T <sub>A</sub> | Specified temperature       | –40   | +85 | °C   |

### 5.4 Electrical Characteristics, V<sub>S</sub> = ±15V

At T<sub>A</sub> = +25°C, R<sub>L</sub> = 10kΩ connected to ground, unless otherwise noted.<sup>(1)</sup>

Limits apply over the specified temperature range, T<sub>A</sub> = –40°C to +85°C.

| PARAMETER                  | CONDITION                                 | OPA137N, U, P<br>OPA2137E, U, P<br>OPA4137U, P |                                 |      | OPA137NA, UA, PA<br>OPA2137EA, UA, PA<br>OPA4137UA, PA |           |     | UNIT   |
|----------------------------|---|--|---------------------------------|------|--|-----------|-----|--------|
|                            |   | MIN  | TYP                             | MAX  | MIN  | TYP       | MAX |        |
| <b>OFFSET VOLTAGE</b>      |   |  |                                 |      |  |           |     |        |
| V <sub>OS</sub>            | Input offset voltage                      |  | ±0.3                            | ±3   |  | ±0.3      | ±10 | mV     |
|                            | T <sub>A</sub> = –40°C to +85°C           |  |                                 | ±7   |  |           | ±15 | mV     |
|                            | dV <sub>OS</sub> /dT vs Temperature       | T <sub>A</sub> = –40°C to +85°C                | 0.6                             |      |  |           |     | µV/°C  |
|                            | PSRR vs Power supply                      | V <sub>S</sub> = ±3V to ±18V                   | 0.1                             | ±250 |  |           |     | µV/V   |
|                            | T <sub>A</sub> = –40°C to +85°C           |  |                                 | ±250 |  |           |     | µV/V   |
|                            | Channel separation (dual, quad)           | dc   | 5                               |      |  |           |     | µV/V   |
| <b>INPUT BIAS CURRENT</b>  |   |  |                                 |      |  |           |     |        |
| I <sub>B</sub>             | Input bias current                        |  | ±10                             |      |  |           |     | pA     |
|                            | vs Temperature                            | V <sub>CM</sub> = 0V                           | See <a href="#">Section 5.5</a> |      |  |           |     |        |
| I <sub>OS</sub>            | Input offset current                      |  | ±5                              |      |  |           |     |        |
| <b>NOISE</b>               |   |  |                                 |      |  |           |     |        |
|                            | Input voltage noise,<br>f = 0.1Hz to 10Hz |  | 6                               |      |  |           |     | µVp-p  |
| e <sub>n</sub>             | Input voltage noise density,<br>f = 1kHz  |  | 30                              |      |  |           |     | nV/√Hz |
| i <sub>n</sub>             | Current noise density,<br>f = 1kHz        |  | 2                               |      |  |           |     | fA/√Hz |
| <b>INPUT VOLTAGE RANGE</b> |   |  |                                 |      |  |           |     |        |
| V <sub>CM</sub>            | Common-mode voltage range                 |  | (V–) + 3                        | (V+) |  |           |     | V      |
| CMRR                       | Common-mode rejection ratio               |  |                                 |      |  |           |     |        |
|                            | OPA137, OPA2137                           |  | 76                              | 84   |  | 70        |     | dB     |
|                            | OPA4137                                   |  | 74                              | 84   |  | 70        |     | dB     |
|                            | T <sub>A</sub> = –40°C to +85°C           |  |                                 |      |  |           |     |        |
|                            | OPA137, OPA2137                           | V <sub>CM</sub> = –12V to 13V                  | <b>72</b>                       |      |  | <b>70</b> |     | dB     |
|                            | OPA4137                                   |  | <b>70</b>                       |      |  | <b>70</b> |     | dB     |
| <b>INPUT IMPEDANCE</b>     |   |  |                                 |      |  |           |     |        |
|                            | Differential                              |  | 10 <sup>10</sup>   3            |      |  |           |     | Ω   pF |
|                            | Common-mode                               |  | 10 <sup>12</sup>   1            |      |  |           |     | Ω   pF |
| <b>OPEN-LOOP GAIN</b>      |   |  |                                 |      |  |           |     |        |
| A <sub>OL</sub>            | Open-loop voltage gain                    | V <sub>O</sub> = –13.8V to 13.9V               | 86                              | 94   |  |           |     | dB     |
|                            | T <sub>A</sub> = –40°C to +85°C           |  | <b>86</b>                       |      |  |           |     | dB     |
| <b>FREQUENCY RESPONSE</b>  |   |  |                                 |      |  |           |     |        |
| GBW                        | Gain-bandwidth product                    |  | 1.1                             |      |  |           |     | MHz    |

### 5.4 Electrical Characteristics, $V_S = \pm 15V$ (continued)

At  $T_A = +25^\circ C$ ,  $R_L = 10k\Omega$  connected to ground, unless otherwise noted.<sup>(1)</sup>



Limits apply over the specified temperature range,  $T_A = -40^\circ C$  to  $+85^\circ C$ .

| PARAMETER           |                                      | CONDITION                         | OPA137N, U, P<br>OPA2137E, U, P<br>OPA4137U, P |     |                                | OPA137NA, UA, PA<br>OPA2137EA, UA, PA<br>OPA4137UA, PA |     |     | UNIT       |
|---------------------|--------------------------------------|-----------------------------------|--|-----|--------------------------------|--|-----|-----|------------|
|                     |                                      |                                   | MIN  | TYP | MAX                            | MIN  | TYP | MAX |            |
| SR                  | Slew rate                            | G = 1, 10V Step,<br>$C_L = 100pF$ | 4.5  |     |                                |  |     |     | V/ $\mu s$ |
| Settling time       | 0.1%                                 |                                   | 4  |     |                                |  |     |     | $\mu s$    |
|                     | 0.01%                                |                                   | 5  |     |                                |  |     |     | $\mu s$    |
|                     | Overload recovery time               | $V_{IN} \cdot G = V_S$            | 1  |     |                                |  |     |     | $\mu s$    |
| THD+N               | Total harmonic distortion + noise    | G = 1, f = 1kHz,<br>3.5Vrms       | 0.02   |     |                                |  |     |     | %          |
| <b>OUTPUT</b>       |                                      |                                   |  |     |                                |  |     |     |            |
| $V_{OUT}$           | Voltage output                       |                                   | $(V-) + 1.2$                                   |     | $(V+) - 1.1$                   |  |     |     | V          |
|                     | $T_A = -40^\circ C$ to $+85^\circ C$ |                                   | <b><math>(V-) + 1.2</math></b>                 |     | <b><math>(V+) - 1.1</math></b> |  |     |     | V          |
| $I_{SC}$            | Short-circuit current                |                                   | -25/+60  |     |                                |  |     |     | mA         |
| $C_{LOAD}$          | Capacitive load drive                |                                   | 330  |     |                                |  |     |     | pF         |
| ZO                  | Open-loop output impedance           | f = 1MHz, IO = 0A                 | 575  |     |                                | 575  |     |     | $\Omega$   |
| <b>POWER SUPPLY</b> |                                      |                                   |  |     |                                |  |     |     |            |
| $V_S$               | Specified operating range            |                                   | $\pm 15$                                       |     |                                |  |     |     | V          |
|                     | Operating voltage range              |                                   |  |     |                                |  |     |     |            |
|                     | Dual supplies                        |                                   | $\pm 2.25^{(1)}$                               |     | $\pm 18$                       |  |     |     | V          |
|                     | Single supply                        |                                   | +4.5   |     | +36                            |  |     |     | V          |
| $I_Q$               | Quiescent current                    | $I_O = 0$                         | $\pm 120$                                      |     | $\pm 270$                      |  |     |     | $\mu A$    |
|                     | $T_A = -40^\circ C$ to $+85^\circ C$ |                                   |  |     | <b><math>\pm 375</math></b>    |  |     |     | $\mu A$    |

(1) At minimum power supply, voltage inputs must be biased above ground in accordance with common-mode voltage range restrictions.


### 5.5 Typical Characteristics

At  $T_A = +25^\circ C$ ,  $V_S = \pm 15V$ ,  $R_L = 10k\Omega$ , connected to ground, unless otherwise noted.




### 5.5 Typical Characteristics (continued)


At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




**Figure 5-3. Input Voltage and Current Noise Spectral Density vs Frequency (Old die)**




**Figure 5-4. Channel Separation vs Frequency (Old die)**




**Figure 5-5. Input Bias Current vs Temperature (Old die)**



**Figure 5-6. Input Bias Current vs Input Common-Mode Voltage (Old die)**



**Figure 5-7. Total Harmonic Distortion + Noise vs Frequency (Old die)**



**Figure 5-8.  $A_{OL}$ , CMRR, PSRR vs Temperature (Old die)**

### 5.5 Typical Characteristics (continued)

At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




Figure 5-9. Quiescent Current and Short-Circuit Current vs Temperature (Old die)




Figure 5-10. Quiescent Current and Short-Circuit Current vs Supply Voltage (Old die)




Figure 5-11. Maximum Output Voltage vs Frequency (Old die)




Figure 5-12. Output Voltage Swing vs Output Current (Old die)




Figure 5-13. Offset Voltage Production Distribution (Old die)






Figure 5-14. Offset Voltage Drift Production Distribution (Old die)

### 5.5 Typical Characteristics (continued)


At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




**Figure 5-15. Settling Time vs Closed-Loop Gain (Old die)**




**Figure 5-16. Small-Signal Overshoot vs Load Capacitance (Old die)**



**Figure 5-17. Small-Signal Step Response  $G = 1$ ,  $C_L = 50\text{pF}$  (Old die)**




**Figure 5-18. Large-Signal Step Response  $G = 1$ ,  $C_L = 50\text{pF}$  (Old die)**



Distribution from 15526 amplifiers,  $T_A = 25^\circ\text{C}$

**Figure 5-19. Offset Voltage Production Distribution (New Die)**




Distribution from 190 amplifiers


**Figure 5-20. Offset Voltage Drift Distribution (New Die)**

## 5.5 Typical Characteristics (continued)


At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




**Figure 5-21. Offset Voltage vs Temperature (New Die)**




**Figure 5-22. Offset Voltage vs Temperature (New Die)**




**Figure 5-23. Offset Voltage vs Common-Mode Voltage (New Die)**



**Figure 5-24. Offset Voltage vs Common-Mode Voltage (Transition Region) (New Die)**




**Figure 5-25. Offset Voltage vs Common-Mode Voltage (New Die)**




**Figure 5-26. Offset Voltage vs Common-Mode Voltage (New Die)**

### 5.5 Typical Characteristics (continued)


At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




**Figure 5-27. Offset Voltage vs Power Supply (New Die)**




**Figure 5-28. Open-Loop Gain and Phase vs Frequency (New Die)**




**Figure 5-29. Closed-Loop Gain vs Frequency (New Die)**



**Figure 5-30. Input Bias Current vs Common-Mode Voltage (New Die)**



**Figure 5-31. Input Bias Current vs Temperature (New Die)**



**Figure 5-32. Output Voltage Swing vs Output Current (Sourcing) (New Die)**

## 5.5 Typical Characteristics (continued)

At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.




Figure 5-33. Output Voltage Swing vs Output Current (Sinking) (New Die)




Figure 5-34. Output Voltage Swing vs Output Current (Sourcing) (New Die)




Figure 5-35. Output Voltage Swing vs Output Current (Sinking) (New Die)




Figure 5-36. CMRR and PSRR vs Frequency (New Die)

## 5.6 Old Die to New Die Transition

As of the publication of revision A of this data sheet, Texas Instruments has moved manufacturing of the die for OPAX137 to a modern fabrication site. The two different die are referred to in this document as “old” (previous fabrication site) and “new” die (current fabrication site). The die origin can be separated from the “Chip Source Origin” (CSO) parameter in the shipping information. The old die CSO is “SFAB”, for the new die the CSO is “RFB”. The old die information is maintained in this data sheet for comparison purposes, but all new manufacturing has moved to the new die.

## 6 Application and Implementation

### Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

### 6.1 Application Information

OPA137 series op amps are unity-gain stable and designed for a wide range of general-purpose applications. Power supply pins can be bypassed with 10nF ceramic capacitors or larger. All circuitry is completely independent in dual and quad versions, provides normal performance when one amplifier in a package is over-driven or short circuited. Many key parameters are maintained over the specified temperature range,  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .

#### 6.1.1 Operating Voltage


OPA137 op amps can be operated on power supplies as low as  $\pm 2.25\text{ V}$ . Performance remains excellent with power supplies ranging from  $\pm 2.25\text{ V}$  to  $\pm 18\text{ V}$  ( $+4.5\text{ V}$  to  $+36\text{ V}$  single supply). Most parameters vary only slightly throughout this supply voltage range. Quiescent current and short-circuit current vs supply voltage are shown in [Section 5.5](#).

Operation at very low supply voltage ( $V_S \leq \pm 3\text{ V}$ ) requires careful attention to ensure that the common-mode voltage remains within the linear range,  $V_{CM} = (V_-)+3\text{ V}$  to  $(V_+)$ . Inputs may need to be biased above ground in accordance with the common-mode voltage range restrictions for linear operation.

#### 6.1.2 Input Voltage

The input common-mode voltage range of OPA137 series op amps extends from  $(V_-)+3\text{ V}$  to the positive rail,  $V_+$ . For normal operation, inputs can be limited to this range. The inputs can go beyond the power supplies without output phase-reversal. Many FET-input op amps (such as TL061 types) exhibit phase-reversal of the output when the input common-mode range is exceeded. This can occur in voltage-follower circuits, causing serious problems in control loop applications.

Input terminals are diode-clamped to the power supply rails for ESD protection. If the input voltage can exceed the negative supply by 500mV, input current can be limited to 2mA (or less). If the input current is not adequately limited, you can see unpredictable behavior in the other amplifiers in the package. This is easily accomplished with an input resistor as shown in [Figure 6-1](#). Many input signals are inherently current-limited, therefore, a limiting resistor can not be neglected.



**Figure 6-1. Input Current Protection for Voltages Exceeding the Supply Voltage**

#### 6.1.3 High-Side Current Sensing

Many applications require the sensing of signals near the positive supply. The common-mode input range of OPA137 op amps includes the positive rail, enabling them to be used to sense power supply currents as shown in [Figure 6-2](#).




Figure 6-2. High-Side Current Monitor

#### 6.1.4 Input Bias Current

The input bias current is approximately 5pA at room temperature and increases with temperature as shown in the typical performance curve [Figure 5-5](#).

Input Bias current also varies with common-mode voltage and power supply voltage. This variation is dependent on the voltage between the negative power supply and the common-mode input voltage. The effect is shown in the typical performance curve [Figure 5-6](#).




Figure 6-3. Photo-detector Amplifier

## 7 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 7.1 Documentation Support

### 7.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on [ti.com](#). Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 7.3 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 7.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.  
All trademarks are the property of their respective owners.

### 7.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 7.6 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 8 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision * (August 1998) to Revision A (March 2026)   | Page |
|--|------|
| • Updated FET Input from $I_B = 5\text{pA}$ to $I_B = \pm 10\text{pA}$ .....   | 1    |
| • Updated Low offset voltage from 1.5mV to $\pm 300\text{mV}$ .....  | 1    |
| • Updated Low quiescent current from 220 $\mu\text{A}$ /channel to 120 $\mu\text{A}$ /channel.....                             | 1    |
| • Updated Excellent speed/power from 1MHz to 1.1MHz.....   | 1    |
| • Updated Low input bias current from 5pA to $\pm 10\text{pA}$ .....   | 1    |
| • Updated Low quiescent current from 220 $\mu\text{A}$ to 120 $\mu\text{A}$ .....  | 1    |
| • Updated High open-loop gain from 94dB to 145dB.....  | 1    |
| • Updated High slew rate from 3.5V/ms to (4.5V/ms).....  | 1    |
| • Added Block diagram and package information.....   | 1    |
| • Updated Input voltage noise from 2 $\mu\text{Vp-p}$ to 6 $\mu\text{Vp-p}$ .....  | 5    |
| • Updated Input offset voltage from $\pm 1.5\text{mV}$ and $\pm 2.5\text{mV}$ to $\pm 0.3\text{mV}$ .....                      | 5    |
| • Updated Input offset voltage vs Temperature from $\pm 15\text{mV}/^\circ\text{C}$ to $\pm 0.6\text{mV}/^\circ\text{C}$ ..... | 5    |
| • Updated PSRR from $\pm 90\mu\text{V/V}$ to $\pm 0.1\mu\text{V/V}$ .....  | 5    |
| • Updated Channel Separation (dual, quad) from 0.6 $\mu\text{V/V}$ to 5 $\mu\text{V/V}$ .....                                  | 5    |
| • Updated Input bias current from 5pA to 10pA.....   | 5    |
| • Updated Input offset current from 2pA to 5pA.....  | 5    |
| • Updated Input Voltage Noise from 2 $\mu\text{Vp-p}$ to 6 $\mu\text{Vp-p}$ .....  | 5    |
| • Updated Input Voltage Noise Density from 45nV/ $\sqrt{\text{Hz}}$ to 30nV/ $\sqrt{\text{Hz}}$ .....                          | 5    |
| • Updated Input offset current from 1.2fA/ $\sqrt{\text{Hz}}$ to 2fA/ $\sqrt{\text{Hz}}$ .....                                 | 5    |
| • Updated Gain-Bandwidth Product from 1MHz to 1.1MHz.....  | 5    |
| • Updated Slew Rate from 3.5V/ $\mu\text{s}$ to 4.5V/ $\mu\text{s}$ .....  | 5    |
| • Updated Settling Time at 0.1% from 8 $\mu\text{s}$ to 4 $\mu\text{s}$ .....  | 5    |
| • Updated Settling Time at 0.01% from 10 $\mu\text{s}$ to 5 $\mu\text{s}$ .....  | 5    |
| • Updated Total Harmonic Distortion + Noise from 0.05% to 0.02%.....   | 5    |
| • Updated Capacitive Load Drive from 1000pF to 330pF.....  | 5    |
| • Updated Quiescent Current from $\pm 220\mu\text{A}$ to $\pm 120\mu\text{A}$ Open-loop output impedance.....                  | 5    |
| • Added Open-loop output impedance value 575 $\Omega$ .....  | 5    |
| • Updated New die typical characteristics plots.....   | 6    |
| • Added New and old die to new die transition.....   | 12   |
| • Deleted Recommended SOT-23-5 and MSOP-8 Solder Footprints.....   | 14   |

## 9 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

**PACKAGING INFORMATION**

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)       |
|-------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------|
| <a href="#">OPA137N/250</a>   | Obsolete      | Production           | SOT-23 (DBV)   5 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA137N/3K</a>    | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-2-260C-1 YEAR               | -40 to 85    | E37                       |
| OPA137N/3K.A                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | E37                       |
| <a href="#">OPA137NA/250</a>  | Obsolete      | Production           | SOT-23 (DBV)   5 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA137NA/3K</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| OPA137NA/3K.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA137U</a>       | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U               |
| OPA137U.A                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U               |
| <a href="#">OPA137UA</a>      | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U<br>A          |
| OPA137UA.A                    | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U<br>A          |
| <a href="#">OPA137UA/2K5</a>  | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85    | (137UA, OPA)<br>137U<br>A |
| OPA137UA/2K5.A                | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | (137UA, OPA)<br>137U<br>A |
| OPA2137E/250                  | Obsolete      | Production           | VSSOP (DGK)   8  | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA2137E/2K5</a>  | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| OPA2137E/2K5.A                | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA2137EA/250</a> | Obsolete      | Production           | VSSOP (DGK)   8  | -                     | -           | Call TI                              | Call TI                           | -            | E37                       |
| <a href="#">OPA2137EA/2K5</a> | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -            | E37                       |
| OPA2137EA/2K5.A               | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA2137P</a>      | Active        | Production           | PDIP (P)   8     | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -            | OPA2137P                  |
| OPA2137P.A                    | Active        | Production           | PDIP (P)   8     | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | OPA2137P                  |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C)  | Part marking<br>(6)         |
|-------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|---------------|-----------------------------|
| <a href="#">OPA2137PA</a>     | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -             | (OPA2137P, OPA2137PA)<br>A  |
| OPA2137PA.A                   | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85     | (OPA2137P, OPA2137PA)<br>A  |
| <a href="#">OPA2137U</a>      | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | -             | OPA<br>2137U                |
| <a href="#">OPA2137U/2K5</a>  | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -             | (2137U, OPA)                |
| OPA2137U/2K5.A                | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | (2137U, OPA)                |
| <a href="#">OPA2137UA</a>     | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA<br>2137U<br>A           |
| <a href="#">OPA2137UA/2K5</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | (2137UA, OPA)<br>2137U<br>A |
| OPA2137UA/2K5.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | (2137UA, OPA)<br>2137U<br>A |
| <a href="#">OPA4137P</a>      | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -             | OPA4137P                    |
| OPA4137P.A                    | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -40 to 85     | OPA4137P                    |
| <a href="#">OPA4137PA</a>     | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -             | OPA4137P<br>A               |
| OPA4137PA.A                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -40 to 85     | OPA4137P<br>A               |
| OPA4137PAG4                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | See OPA4137PA | OPA4137P<br>A               |
| <a href="#">OPA4137U</a>      | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA4137U                    |
| <a href="#">OPA4137U/2K5</a>  | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | OPA4137U                    |
| OPA4137U/2K5.A                | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | OPA4137U                    |
| <a href="#">OPA4137UA</a>     | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA4137U<br>A               |
| <a href="#">OPA4137UA/2K5</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | (OPA4137U, OPA4137UA)<br>A  |

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)            |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------|
| OPA4137UA/2K5.A       | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | (OPA4137U, OPA4137<br>UA)<br>A |

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.


**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal


| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| OPA137N/3K    | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA137NA/3K   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA137UA/2K5  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA2137E/2K5  | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2137EA/2K5 | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2137U/2K5  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA2137UA/2K5 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA4137U/2K5  | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| OPA4137UA/2K5 | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| OPA137N/3K    | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| OPA137NA/3K   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| OPA137UA/2K5  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA2137E/2K5  | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA2137EA/2K5 | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA2137U/2K5  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA2137UA/2K5 | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA4137U/2K5  | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| OPA4137UA/2K5 | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |

**TUBE**


\*All dimensions are nominal

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| OPA137U     | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137U.A   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137UA    | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137UA.A  | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA2137P    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137P.A  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137PA   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137PA.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137P    | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137P.A  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PA   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PA.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PAG4 | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025