

## SN74AVC4T234 4 位双电源单向同相电压转换器

### 1 特性

- 0.9V 至 3.6V 的宽工作  $V_{CC}$  范围
- 3.6V 耐压 I/O 支持混合模式的信号操作
- 电压为 3.3V 时,  $t_{pd}$  最大值为 3.7ns
- 平衡传播延迟:  $t_{PLH} = t_{PHL}$
- 低静态功耗, 最大  $I_{CC}$  为 5 $\mu$ A
- 如果任一  $V_{CC}$  变为 0V, 则会禁用输出
- 电压为 1.8V 时, 输出驱动为  $\pm 3$ mA
- A 侧输出端有 26  $\Omega$  串联电阻
- $I_{off}$  支持局部断电模式运行
- 输入迟滞可在输入端实现缓慢的输入转换和更好的开关噪声抗扰度
- 最大数据速率
  - 380Mbps ( 1.8V 至 3.3V 转换 )
  - 200Mbps ( 小于 1.8V 至 3.3V 转换 )
  - 200Mbps ( 转换至 2.5V 或 1.8V )
  - 150Mbps ( 转换至 1.5V )
  - 100Mbps ( 转换至 1.2V )
- 闩锁性能超过 100mA, 符合 JESD 78 II 类规范的要求
- ESD 保护性能超过 JESD 22 规范要求
  - 2000V 人体放电模型 (A114-A)
  - 500V 充电器件模型 (C101)

### 2 应用

- 个人电子产品
- 工业
- 企业
- 电信

### 3 说明

这款 4 位同相总线收发器采用两个独立的可配置电源轨来实现 B 端口输入和 A 端口输出之间的异步通信。A 端口旨在跟踪  $V_{CCA}$ , 而 B 端口旨在跟踪  $V_{CCB}$ 。  $V_{CCA}$  和  $V_{CCB}$  均可配置为 0.9V 至 3.6V 范围内的值。

SN74AVC4T234 解决方案可确保在整个 0.9V 至 3.6V 的  $V_{CC}$  范围内实现极低的静态和动态功耗, 满足电池供电型便携式应用的低功耗需求, 从而延长电池的使用寿命。该产品还可以保持出色的信号完整性。


该器件完全符合使用  $I_{off}$  的部分断电应用的规范要求。  $I_{off}$  电路禁用输出, 从而可防止其断电时破坏性电流从该器件回流。

$V_{CC}$  隔离特性可确保只要有任何一个  $V_{CC}$  输入接地 (GND), 则 A 侧端口处于高阻抗状态。

#### 器件信息

| 器件型号            | 封装 <sup>(1)</sup> | 封装尺寸 (标称值)      |
|-----------------|-------------------|-----------------|
| SN74AVC4T234ZSU | uCSP (11)         | 2.00mm × 1.40mm |
| SN74AVC4T234ZWA | NFBGA (11)        | 2.00mm × 1.40mm |

(1) 如需了解所有可用封装, 请参阅数据表末尾的可订购产品附录。



逻辑图 (正逻辑)



## Table of Contents

|                                                                |          |                                                                  |           |
|----------------------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 特性</b> .....                                              | <b>1</b> | <b>8 Detailed Description</b> .....                              | <b>10</b> |
| <b>2 应用</b> .....                                              | <b>1</b> | 8.1 Overview.....                                                | 10        |
| <b>3 说明</b> .....                                              | <b>1</b> | 8.2 Functional Block Diagram.....                                | 10        |
| <b>4 Revision History</b> .....                                | <b>2</b> | 8.3 Feature Description.....                                     | 10        |
| <b>5 Pin Configuration and Functions</b> .....                 | <b>3</b> | 8.4 Device Functional Modes.....                                 | 10        |
| <b>6 Specifications</b> .....                                  | <b>4</b> | <b>9 Application and Implementation</b> .....                    | <b>11</b> |
| 6.1 Absolute Maximum Ratings.....                              | 4        | 9.1 Application Information.....                                 | 11        |
| 6.2 ESD Ratings.....                                           | 4        | 9.2 Typical Application.....                                     | 11        |
| 6.3 Recommended Operating Conditions.....                      | 5        | <b>10 Power Supply Recommendations</b> .....                     | <b>12</b> |
| 6.4 Thermal Information.....                                   | 6        | <b>11 Layout</b> .....                                           | <b>12</b> |
| 6.5 Electrical Characteristics.....                            | 6        | 11.1 Layout Guidelines.....                                      | 12        |
| 6.6 Switching Characteristics, $V_{CCB} = 1.1\text{ V}$ .....  | 7        | 11.2 Layout Example.....                                         | 12        |
| 6.7 Switching Characteristics, $V_{CCB} = 1.4\text{ V}$ .....  | 7        | <b>12 Device and Documentation Support</b> .....                 | <b>13</b> |
| 6.8 Switching Characteristics, $V_{CCB} = 1.65\text{ V}$ ..... | 7        | 12.1 Support Resources.....                                      | 13        |
| 6.9 Switching Characteristics, $V_{CCB} = 2.3\text{ V}$ .....  | 8        | 12.2 Trademarks.....                                             | 13        |
| 6.10 Switching Characteristics, $V_{CCB} = 3\text{ V}$ .....   | 8        | 12.3 Electrostatic Discharge Caution.....                        | 13        |
| 6.11 Operating Characteristics.....                            | 8        | 12.4 Glossary.....                                               | 13        |
| <b>7 Parameter Measurement Information</b> .....               | <b>9</b> | <b>13 Mechanical, Packaging, and Orderable Information</b> ..... | <b>13</b> |
| 7.1 Load Circuit and Voltage Waveforms.....                    | 9        |                                                                  |           |

## 4 Revision History

注：以前版本的页码可能与当前版本的页码不同

| <b>Changes from Revision A (June 2011) to Revision B (July 2020)</b>                                                        | <b>Page</b> |
|-----------------------------------------------------------------------------------------------------------------------------|-------------|
| • 通篇按照新的 TI 数据表标准进行格式调整并增加了信息.....                                                                                          | 1           |
| • 删除了“具有输入禁用特性，允许出现输入悬空的情况”特性.....                                                                                          | 1           |
| • 添加了“如果任一 $V_{CC}$ 变为 0V，则会禁用输出”特性.....                                                                                    | 1           |
| • 更新了整个文档中的表格、图和交叉参考的编号格式.....                                                                                              | 1           |
| • 删除了 订购信息 表.....                                                                                                           | 1           |
| • 添加了 ZWA 封装作为可订购产品.....                                                                                                    | 1           |
| • Added <i>ESD Ratings</i> table.....                                                                                       | 4           |
| • Added <i>Thermal Information</i> table.....                                                                               | 6           |
| • Added <i>Feature Description</i> section.....                                                                             | 10          |
| • Added <i>Device Functional Modes</i> section.....                                                                         | 10          |
| • Added <i>Application and Implementation</i> section.....                                                                  | 11          |
| • Added <i>Power Supply Recommendations</i> section.....                                                                    | 12          |
| • Added <i>Layout</i> section.....                                                                                          | 12          |
| • Added <i>Device and Documentation Support</i> , and <i>Mechanical, Packaging, and Orderable Information</i> sections..... | 13          |

## 5 Pin Configuration and Functions




图 5-1. ZSU/ZWA Package 11-Pin uCSP Transparent Top View

### Pin Functions

| PIN              | NO.      | TYPE | DESCRIPTION                                              |
|------------------|----------|------|----------------------------------------------------------|
| NAME             | ZSU, ZWA |      |                                                          |
| B1               | C7       | I    | Channel 1 Data input port                                |
| B2               | C5       | I    | Channel 2 Data input port                                |
| B3               | C3       | I    | Channel 3 Data input port                                |
| B4               | C1       | I    | Channel 4 Data input port                                |
| A1               | A7       | O    | Channel 1 Data output port                               |
| A2               | A5       | O    | Channel 2 Data output port                               |
| A3               | A3       | O    | Channel 3 Data output port                               |
| A4               | A1       | O    | Channel 4 Data output port                               |
| V <sub>CCA</sub> | B6       | —    | A-side output port power supply voltage (0.9 V to 3.6 V) |
| V <sub>CCB</sub> | B4       | —    | B-side input port power supply voltage (0.9 V to 3.6 V)  |
| GND              | B2       | —    | Ground                                                   |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                        |                                                                                       |                       | MIN   | MAX             | UNIT |
|------------------------|---------------------------------------------------------------------------------------|-----------------------|-------|-----------------|------|
| $V_{CCA}$<br>$V_{CCB}$ | Supply voltage                                                                        |                       | – 0.5 | 4.6             | V    |
| $V_I$                  | Input voltage <sup>(2)</sup>                                                          | Output ports (A port) | – 0.5 | 4.6             | V    |
|                        |                                                                                       | Input ports (B port)  | – 0.5 | 4.6             |      |
| $V_O$                  | Voltage applied to any output in the high-impedance or power-off state <sup>(2)</sup> | A port                | – 0.5 | 4.6             | V    |
| $V_O$                  | Voltage applied to any output in the high or low state <sup>(2) (3)</sup>             | A port                | – 0.5 | $V_{CCA} + 0.5$ | V    |
| $I_{IK}$               | Input clamp current                                                                   | $V_I < 0$             |       | – 50            | mA   |
| $I_{OK}$               | Output clamp current                                                                  | $V_O < 0$             |       | – 50            | mA   |
| $I_O$                  | Continuous output current                                                             |                       |       | ±20             | mA   |
|                        | Continuous current through $V_{CCA}$ , $V_{CCB}$ , or GND                             |                       |       | ±50             | mA   |
| $T_{stg}$              | Storage temperature                                                                   |                       | – 65  | 150             | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input voltage and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) The output positive-voltage rating may be exceeded up to 4.6 V maximum if the output current rating is observed.

### 6.2 ESD Ratings

|             |                         |                                                                                | VALUE | UNIT |
|-------------|-------------------------|--------------------------------------------------------------------------------|-------|------|
| $V_{(ESD)}$ | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V    |
|             |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±500  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

## 6.3 Recommended Operating Conditions

|                  |                                    |                            | V <sub>CCI</sub> <sup>(1) (3)</sup> | V <sub>CCO</sub> <sup>(2)</sup> | MIN                     | MAX                     | UNIT |
|------------------|------------------------------------|----------------------------|-------------------------------------|---------------------------------|-------------------------|-------------------------|------|
| V <sub>CCA</sub> | Supply voltage                     |                            |                                     |                                 | 0.9                     | 3.6                     | V    |
| V <sub>CCB</sub> | Supply voltage                     |                            |                                     |                                 | 0.9                     | 3.6                     | V    |
| V <sub>IH</sub>  | High-level input voltage           | Data inputs <sup>(4)</sup> | 0.9 V to 1.1 V                      |                                 | V <sub>CCI</sub> × 0.8  | 3.6                     | V    |
|                  |                                    |                            | 1.1 V to 1.4 V                      |                                 | V <sub>CCI</sub> × 0.8  | 3.6                     |      |
|                  |                                    |                            | 1.4 V to 1.95 V                     |                                 | V <sub>CCI</sub> × 0.65 | 3.6                     |      |
|                  |                                    |                            | 2.3 V to 2.7 V                      |                                 | V <sub>CCI</sub> × 0.65 | 3.6                     |      |
|                  |                                    |                            | 3 V to 3.6 V                        |                                 | V <sub>CCI</sub> × 0.65 | 3.6                     |      |
| V <sub>IL</sub>  | Low-level input voltage            | Data inputs <sup>(4)</sup> | 0.9 V to 1.1 V                      |                                 | 0                       | V <sub>CCI</sub> × 0.2  | V    |
|                  |                                    |                            | 1.1 V to 1.4 V                      |                                 | 0                       | V <sub>CCI</sub> × 0.2  |      |
|                  |                                    |                            | 1.1 V to 1.95 V                     |                                 | 0                       | V <sub>CCI</sub> × 0.35 |      |
|                  |                                    |                            | 2.3 V to 2.7 V                      |                                 | 0                       | V <sub>CCI</sub> × 0.35 |      |
|                  |                                    |                            | 3 V to 3.6 V                        |                                 | 0                       | V <sub>CCI</sub> × 0.35 |      |
| V <sub>I</sub>   | Input voltage                      |                            |                                     |                                 | 0                       | 3.6                     | V    |
| V <sub>O</sub>   | Output voltage                     | Active state               |                                     |                                 | 0                       | V <sub>CCO</sub>        | V    |
| I <sub>OH</sub>  | High-level output current          |                            |                                     | 0.9 V to 1.1 V                  |                         | – 0.1                   | mA   |
|                  |                                    |                            |                                     | 1.1 V to 1.3 V                  |                         | – 1                     |      |
|                  |                                    |                            |                                     | 1.4 V to 1.6 V                  |                         | – 2                     |      |
|                  |                                    |                            |                                     | 1.65 V to 1.95 V                |                         | – 3                     |      |
|                  |                                    |                            |                                     | 2.3 V to 2.7 V                  |                         | – 6                     |      |
|                  |                                    |                            |                                     | 3 V to 3.6 V                    |                         | – 12                    |      |
| I <sub>OL</sub>  | Low-level output current           |                            |                                     | 0.9 V to 1.1 V                  |                         | 0.1                     | mA   |
|                  |                                    |                            |                                     | 1.1 V to 1.3 V                  |                         | 1                       |      |
|                  |                                    |                            |                                     | 1.4 V to 1.6 V                  |                         | 2                       |      |
|                  |                                    |                            |                                     | 1.65 V to 1.95 V                |                         | 3                       |      |
|                  |                                    |                            |                                     | 2.3 V to 2.7 V                  |                         | 6                       |      |
|                  |                                    |                            |                                     | 3 V to 3.6 V                    |                         | 12                      |      |
| Δ t / Δ v        | Input transition rise or fall rate |                            |                                     | 3 V to 3.6 V                    |                         | 10                      | ns/V |
|                  |                                    |                            |                                     | 2.3 V to 2.7 V                  |                         | 20                      |      |
|                  |                                    |                            |                                     | 1.65 V to 1.95 V                |                         | 50                      |      |
|                  |                                    |                            |                                     | 1.4 V to 1.6 V                  |                         | 100                     |      |
|                  |                                    |                            |                                     | 1.1 V to 1.3 V                  |                         | 100                     |      |
| T <sub>A</sub>   | Operating free-air temperature     |                            |                                     |                                 | – 40                    | 85                      | °C   |

(1)  $V_{CCI}$  is the  $V_{CCB}$  input port.

(2)  $V_{CCO}$  is the  $V_{CCA}$  output port.

(3) All unused data inputs of the device must be held at  $V_{CCI}$  or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, [SCBA004](#).

(4) For  $V_{CCI}$  values not specified in the data sheet,  $V_{IH \min} = V_{CCI} \times 0.7$  V,  $V_{IL \max} = V_{CCI} \times 0.3$  V

## 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                                       | SN74AVC4T234 | SN74AVC4T234 | UNIT |
|-------------------------------|-------------------------------------------------------|--------------|--------------|------|
|                               |                                                       | ZSU (uCSP)   | ZWA (NFBGA)  |      |
|                               |                                                       | 11 PINS      | 11 PINS      |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance <sup>(2)</sup> | 165.9        | 181.4        | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance             | 123.8        | 136.7        | °C/W |
| $R_{\theta JB}$               | Junction-to-board thermal resistance                  | 123.2        | 137.7        | °C/W |
| $\psi_{JT}$                   | Junction-to-top characterization parameter            | 4.4          | 7.5          | °C/W |
| $\psi_{JB}$                   | Junction-to-board characterization parameter          | 122.9        | 137.4        | °C/W |

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

(2) The package thermal impedance is calculated in accordance with JEDEC 51-5.

## 6.5 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER <sup>(1) (2)</sup> |             | TEST CONDITIONS             | $V_{CCA}$      | $V_{CCB}$      | $T_A$                               | MIN             | TYP       | MAX     | UNIT    |
|------------------------------|-------------|-----------------------------|----------------|----------------|-------------------------------------|-----------------|-----------|---------|---------|
| $V_{OH}$                     |             | $I_{OH} = -100 \mu A$       | 0.9 V          | 0.9 V to 3.6 V | $T_A = -40^\circ C$ to $85^\circ C$ | $V_{CCA} - 0.1$ |           |         | V       |
|                              |             | $I_{OH} = -1 mA$            | 1.1 V          |                | $T_A = -40^\circ C$ to $85^\circ C$ | 0.88            |           |         |         |
|                              |             | $I_{OH} = -2 mA$            | 1.4 V          |                | $T_A = -40^\circ C$ to $85^\circ C$ | 1.05            |           |         |         |
|                              |             | $I_{OH} = -3 mA$            | 1.65 V         |                | $T_A = -40^\circ C$ to $85^\circ C$ | 1.2             |           |         |         |
|                              |             | $I_{OH} = -6 mA$            | 2.3V           |                | $T_A = -40^\circ C$ to $85^\circ C$ | 1.75            |           |         |         |
|                              |             | $I_{OH} = -12 mA$           | 3 V            |                | $T_A = -40^\circ C$ to $85^\circ C$ | 2.3             |           |         |         |
| $V_{OL}$                     |             | $I_{OL} = 100 \mu A$        | 0.9 V          | 0.9 V to 3.6 V | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.1     | V       |
|                              |             | $I_{OL} = 1 mA$             | 1.1 V          |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.2     |         |
|                              |             | $I_{OL} = 2 mA$             | 1.4 V          |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.2     |         |
|                              |             | $I_{OL} = 3 mA$             | 1.65 V         |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.25    |         |
|                              |             | $I_{OL} = 6 mA$             | 2.3V           |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.3     |         |
|                              |             | $I_{OL} = 12 mA$            | 3 V            |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 0.55    |         |
| $I_{off}$                    | A or B port | $V_I$ or $V_O = 0$ to 3.6 V | 0 V            | 0 V to 3.6 V   | $T_A = 25^\circ C$                  |                 | $\pm 0.1$ | $\pm 1$ | $\mu A$ |
|                              |             |                             | 0 V to 3.6 V   | 0 V            | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | $\pm 5$ |         |
|                              |             |                             |                |                | $T_A = 25^\circ C$                  |                 | $\pm 0.1$ | $\pm 1$ |         |
|                              |             |                             |                |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | $\pm 5$ |         |
| $I_{CCA}$                    |             | $V_{CCB}$ or GND, $I_O = 0$ | 0.8 V to 3.6 V | 0.8 V to 3.6 V | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       | $\mu A$ |
|                              |             |                             | 0 V            | 0 V to 3.6 V   | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       |         |
|                              |             |                             | 0 V to 3.6 V   | 0 V            | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       |         |
| $I_{CCB}$                    |             | $V_{CCB}$ or GND, $I_O = 0$ | 0.8 V to 3.6 V | 0.8 V to 3.6 V | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       | $\mu A$ |
|                              |             |                             | 0 V            | 0 V to 3.6 V   | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       |         |
|                              |             |                             | 0 V to 3.6 V   | 0 V            | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 8       |         |
| $I_{CCA} + I_{CCB}$          |             | $V_{CCB}$ or GND, $I_O = 0$ | 0.8 V to 3.6 V | 0.8 V to 3.6 V | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 16      | $\mu A$ |
| $C_i$                        | $V_{CCB}$   | $V_{CCB} = 3.3 V$ or GND    | 3.3 V          | 3.3 V          | $T_A = 25^\circ C$                  |                 | 22        |         | pF      |
| $C_{io}$                     | A or B port | $V_{CCA} = 3.3 V$ or GND    | 3.3 V          | 3.3 V          | $T_A = 25^\circ C$                  |                 | 5         |         | pF      |
|                              |             |                             |                |                | $T_A = -40^\circ C$ to $85^\circ C$ |                 |           | 7       |         |

(1)  $V_{CCI}$  is the  $V_{CCB}$  input port.

(2)  $V_{CCO}$  is the  $V_{CCA}$  output port.

## 6.6 Switching Characteristics, $V_{CCB} = 1.1\text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 1.1\text{ V}$  (unless otherwise noted) (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CCA}$                 | TYP | UNIT |
|-----------|-----------------|----------------|---------------------------|-----|------|
| $t_{PLH}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  | 5.5 | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 4.6 |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 4.2 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 3.7 |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 3.9 |      |
| $t_{PHL}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  | 4.7 | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 3.9 |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 3.4 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 3   |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 3.1 |      |

## 6.7 Switching Characteristics, $V_{CCB} = 1.4\text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 1.4\text{ V}$  (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CCA}$                 | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|---------------------------|-----|-----|-----|------|
| $t_{PLH}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  |     | 4.7 |     | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 5   |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.8 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 3.8 |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 1   |     | 3.8 |      |
| $t_{PHL}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  |     | 4.2 |     | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 5   |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.9 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 3   |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 1   |     | 3   |      |

## 6.8 Switching Characteristics, $V_{CCB} = 1.65\text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 1.65\text{ V}$  (see [Figure 7-1](#))

| PARAMETER | FROM<br>(INPUT) | TO<br>(OUTPUT) | $V_{CCA}$                 | MIN | TYP | MAX | UNIT |
|-----------|-----------------|----------------|---------------------------|-----|-----|-----|------|
| $t_{PLH}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  |     | 4.3 |     | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 4.2 |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 4.1 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 3.8 |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 1   |     | 3.7 |      |
| $t_{PHL}$ | B               | A              | $V_{CCA} = 1.1\text{ V}$  |     | 2.6 |     | ns   |
|           |                 |                | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 4.2 |      |
|           |                 |                | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 4.1 |      |
|           |                 |                | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 3.8 |      |
|           |                 |                | $V_{CCA} = 3\text{ V}$    | 1   |     | 3.7 |      |

## 6.9 Switching Characteristics, $V_{CCB} = 2.3\text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 2.3\text{ V}$  (see [Figure 7-1](#))

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | $V_{CCA}$                 | MIN | TYP | MAX | UNIT |
|-----------|--------------|-------------|---------------------------|-----|-----|-----|------|
| $t_{PLH}$ | B            | A           | $V_{CCA} = 1.1\text{ V}$  |     | 2.7 |     | ns   |
|           |              |             | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 3.5 |      |
|           |              |             | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.1 |      |
|           |              |             | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 2.8 |      |
|           |              |             | $V_{CCA} = 3\text{ V}$    | 0.2 |     | 4.1 |      |
| $t_{PHL}$ | B            | A           | $V_{CCA} = 1.1\text{ V}$  |     | 2.4 |     | ns   |
|           |              |             | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 3.7 |      |
|           |              |             | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.7 |      |
|           |              |             | $V_{CCA} = 2.3\text{ V}$  | 1.2 |     | 2.8 |      |
|           |              |             | $V_{CCA} = 3\text{ V}$    | 0.2 |     | 3.5 |      |

## 6.10 Switching Characteristics, $V_{CCB} = 3\text{ V}$

over recommended operating free-air temperature range,  $V_{CCB} = 3\text{ V}$  (see [Figure 7-1](#))

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | $V_{CCA}$                 | MIN | TYP | MAX | UNIT |
|-----------|--------------|-------------|---------------------------|-----|-----|-----|------|
| $t_{PLH}$ | B            | A           | $V_{CCA} = 1.1\text{ V}$  |     | 3.9 |     | ns   |
|           |              |             | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 3.8 |      |
|           |              |             | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.6 |      |
|           |              |             | $V_{CCA} = 2.3\text{ V}$  | 0.5 |     | 3.6 |      |
|           |              |             | $V_{CCA} = 3\text{ V}$    | 0.2 |     | 3.6 |      |
| $t_{PHL}$ | B            | A           | $V_{CCA} = 1.1\text{ V}$  |     | 3.9 |     | ns   |
|           |              |             | $V_{CCA} = 1.4\text{ V}$  | 2   |     | 3.7 |      |
|           |              |             | $V_{CCA} = 1.65\text{ V}$ | 1.5 |     | 3.1 |      |
|           |              |             | $V_{CCA} = 2.3\text{ V}$  | 0.5 |     | 3.5 |      |
|           |              |             | $V_{CCA} = 3\text{ V}$    | 0.2 |     | 3   |      |

## 6.11 Operating Characteristics

$T_A = 25^\circ\text{C}$


| PARAMETER                |        |                 | TEST CONDITIONS                                                   | $V_{CCA}, V_{CCB}$                  | TYP  | UNIT |
|--------------------------|--------|-----------------|-------------------------------------------------------------------|-------------------------------------|------|------|
| $C_{pdA}$ <sup>(1)</sup> | B to A | Outputs enabled | $C_L = 0$ ,<br>$f = 10\text{ MHz}$ ,<br>$t_r = t_f = 1\text{ ns}$ | $V_{CCA} = V_{CCB} = 1.1\text{ V}$  | 18.5 | pF   |
|                          |        |                 |                                                                   | $V_{CCA} = V_{CCB} = 1.4\text{ V}$  |      |      |
|                          |        |                 |                                                                   | $V_{CCA} = V_{CCB} = 1.65\text{ V}$ |      |      |
|                          |        |                 |                                                                   | $V_{CCA} = V_{CCB} = 2.3\text{ V}$  |      |      |
|                          |        |                 |                                                                   | $V_{CCA} = V_{CCB} = 3\text{ V}$    |      |      |

(1) Power dissipation capacitance per transceiver




## 7 Parameter Measurement Information

### 7.1 Load Circuit and Voltage Waveforms



| $V_{CCO}$          | $C_L$ | $R_L$          | $V_{TP}$ |
|--------------------|-------|----------------|----------|
| 1.2 V              | 30 pF | 0.5 k $\Omega$ | 0.1 V    |
| 1.5 V $\pm$ 0.1 V  | 30 pF | 0.5 k $\Omega$ | 0.1 V    |
| 1.8 V $\pm$ 0.15 V | 30 pF | 0.5 k $\Omega$ | 0.15 V   |
| 2.5 V $\pm$ 0.2 V  | 30 pF | 0.5 k $\Omega$ | 0.15 V   |
| 3.3 V $\pm$ 0.3 V  | 30 pF | 0.5 k $\Omega$ | 0.3 V    |



- NOTES:
- A.  $C_L$  includes probe and jig capacitance.
  - B. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10$  MHz,  $Z_O = 50 \Omega$ ,  $dv/dt \geq 1$  V/ns.
  - C. The outputs are measured one at a time, with one transition per measurement.
  - D.  $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - E.  $V_{CCI}$  is  $V_{CCB}$ .
  - F.  $V_{CCO}$  is  $V_{CCA}$ .

图 7-1. Load and Circuit and Voltage Waveforms

## 8 Detailed Description

### 8.1 Overview

The SN74AVC4T234 is a 4-bit, dual-supply noninverting voltage level translation device. The B input port pins are referenced to the  $V_{CCB}$  supply, and the A output port pins are referenced to the  $V_{CCA}$ . The B port is able to accept I/O voltages ranging from 0.9 V to 3.6 V.

### 8.2 Functional Block Diagram




图 8-1. Logic Diagram (Positive Logic)

### 8.3 Feature Description

#### 8.3.1 Fully Configurable Dual-Rail Design Allows Each Port to Operate Over the Full 0.9-V to 3.6-V Power-Supply Range

Both  $V_{CCA}$  and  $V_{CCB}$  can be supplied at any voltage between 0.9 V and 3.6 V; thus, making the device suitable for translating between any of the low voltage nodes (0.9, 1.05 V, 1.2 V, 1.8 V, 2.5 V, and 3.3 V).

#### 8.3.2 Supports High Speed Translation

The SN74AVC4T234 device can support high data rate applications. The translated signal data rate can be up to 380 Mbps when the signal is translated from 1.8 V to 3.3 V.

#### 8.3.3 $I_{off}$ Supports Partial-Power-Down Mode Operation

$I_{off}$  will prevent backflow current by disabling I/O output circuits when device is in partial-power-down mode.

### 8.4 Device Functional Modes

表 8-1. Function Table

| INPUTS                       | OUTPUTS                      |
|------------------------------|------------------------------|
| Bx                           | Ax                           |
| L                            | L                            |
| H (referenced to $V_{CCB}$ ) | H (referenced to $V_{CCA}$ ) |

## 9 Application and Implementation

### Note

以下应用部分的信息不属于 TI 组件规范，TI 不担保其准确性和完整性。客户应负责确定 TI 组件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

### 9.1 Application Information

The SN74AVC4T234 device can be used in level-translation applications for interfacing devices or systems operating at different interface voltages with one another. The SN74AVC4T234 device is ideal for use in applications where a push-pull driver is connected to the data I/Os. The max data rate can be up to 380 Mbps when device translates a signal from 1.8 V to 3.3 V.

### 9.2 Typical Application




图 9-1. Typical Application Diagram

#### 9.2.1 Design Requirements

For the design example shown in [Typical Application](#), use the parameters listed in [表 9-1](#).

表 9-1. Design Parameters

| DESIGN PARAMETER     | EXAMPLE VALUE  |
|----------------------|----------------|
| Input voltage range  | 0.9 V to 3.6 V |
| Output voltage range | 0.9 V to 3.6 V |

#### 9.2.2 Detailed Design Procedure

To begin the design process, determine the following:

- Input voltage range
  - Use the supply voltage of the device that is driving the SN74AVC4T234 device to determine the input voltage range. For a valid logic high, the value must exceed the  $V_{IH}$  of the input port. For a valid logic low, the value must be less than the  $V_{IL}$  of the input port.
- Output voltage range
  - Use the supply voltage of the device that the SN74AVC4T234 device is driving to determine the output voltage range.

### 9.2.3 Application Curves




图 9-2. Translation Up (1.2 V to 3.3 V) at 2.5 MHz

## 10 Power Supply Recommendations

The SN74AVC4T234 device uses two separate configurable power-supply rails,  $V_{CCA}$  and  $V_{CCB}$ .  $V_{CCA}$  accepts any supply voltage from 0.9 V to 3.6 V and  $V_{CCB}$  accepts any supply voltage from 0.9 V to 3.6 V. The A port and B port are designed to track  $V_{CCA}$  and  $V_{CCB}$  respectively allowing for low-voltage bidirectional translation between any of the 0.9-V, 1.05-V, 1.2-V, 1.5-V, 1.8-V, 2.5-V and 3.3-V voltage nodes.


## 11 Layout

### 11.1 Layout Guidelines

To ensure reliability of the device, following common printed-circuit board layout guidelines is recommended.

- Bypass capacitors should be used on power supplies.
- Short trace lengths should be used to avoid excessive loading.
- Place pads on the signal paths for loading capacitors or pullup resistors to help adjust rise and fall times of signals, depending on the system requirements.

### 11.2 Layout Example



## 12 Device and Documentation Support

### 12.1 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

### 12.2 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

### 12.3 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

### 12.4 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number            | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">SN74AVC4T234ZWAR</a> | Active        | Production           | NFBGA (ZWA)   11 | 2500   LARGE T&R      | Yes         | SN98.5/AG1/CU0.5                     | Level-2-260C-1 YEAR               | -40 to 85    | 1G2                 |
| SN74AVC4T234ZWAR.B               | Active        | Production           | NFBGA (ZWA)   11 | 2500   LARGE T&R      | Yes         | SN98.5/AG1/CU0.5                     | Level-2-260C-1 YEAR               | -40 to 85    | 1G2                 |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74AVC4T234ZWAR | NFBGA        | ZWA             | 11   | 2500 | 330.0              | 8.4                | 1.6     | 2.2     | 0.55    | 4.0     | 8.0    | Q2            |


## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74AVC4T234ZWAR | NFBGA        | ZWA             | 11   | 2500 | 338.1       | 338.1      | 20.6        |






4224717/A 12/2018


NOTES:

NanoFree is a trademark of Texas Instruments.

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.



LAND PATTERN EXAMPLE  
SCALE: 40X



4224717/A 12/2018

NOTES: (continued)

- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. Refer to Texas Instruments Literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).

## NFBGA - 0.45 mm max height

**SOLDER PASTE EXAMPLE**  
**BASED ON 0.1 mm THICK STENCIL**  
**SCALE: 40X**

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月