# 具有漏极开路输出的 SN74LVC1G07-Q1 单路缓冲器/驱动器

## 1 特性

- 符合汽车应用要求
- 具有符合 AEC-Q100 标准的下列特性：
  - 器件温度等级 1：–40°C 至 +125°C 环境工作温度范围
  - 2000V 器件的人体放电模型 (HBM) ESD 分类等级 2
  - 1000V 器件的充电设备模型 (CDM) ESD 分类等级 C5
- 支持 5V $V_{CC}$ 运行
- 输入与开漏输出支持最高 5.5V 的电压
- 3.3V 时 $t_{pd}$ 最大值为 5.7ns
- 低功耗，$I_{CC}$ 最大值为 10 µA
- 3.3V 时，输出驱动为 ±24mA
- $I_{off}$ 支持局部关断模式运行

## 2 应用

- 汽车信息娱乐系统
- 汽车 ADAS 摄像头和融合
- 汽车车身控制模块 AV 接收器
- 汽车 HEV/动力总成系统
- 蓝光播放器与家庭影院
- DVD 录像机和播放器
- 台式机或笔记本电脑
- 数字音频广播或互联网广播播放器
- 数码摄像机 (DVC)
- 嵌入式 PC
- GPS：个人导航设备
- 移动互联网设备
- 网络投影仪前端
- 便携式媒体播放器
- 专业音频混合器
- 烟雾探测器
- 固态硬盘 (SSD)：企业级
- 高清 (HDTV)
- 平板电脑：企业级
- 音频接口盒：便携式
- DLP 正投系统
- DVR 和 DVS
- 数码相框 (DPF)
- 数码相机

## 3 说明

SN74LVC1G07-Q1 是一款符合汽车应用要求的单通道漏极开路缓冲器/驱动器。该器件设计在 1.65V 至 5.5V $V_{CC}$ 下工作。


SN74LVC1G07-Q1 器件的输出为漏极开路，可连接其它开漏输出，从而实现低电平有效的连线 OR 或高电平有效的连线 AND 功能。最大灌电流为 32mA。

该器件完全适合使用 $I_{off}$ 的局部断电应用。当器件断电时，$I_{off}$ 电路将会禁用输出，以防在器件掉电时电流回流损坏器件。

**封装信息**

| 器件型号 | 封装(1) | 封装尺寸(2) | 封装尺寸（标称值）(3) |
|---|---|---|---|
| SN74LVC1G07-Q1 | DBV（SOT-23，5） | 2.90mm × 2.80mm | 2.90mm × 1.60mm |
| | DCK（SC70，5） | 2.00mm × 2.10mm | 2.00mm × 1.25mm |
| | DRY（USON，6） | 1.45mm × 1.00mm | 1.45mm × 1.00mm |

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。
(2) 封装尺寸（长 × 宽）为标称值，并包括引脚（如适用）。
(3) 封装尺寸（长 × 宽）为标称值，不包括引脚。




**逻辑图（正逻辑）**

本资源的原文使用英文撰写。 为方便起见，TI 提供了译文；由于翻译过程中可能使用了自动化工具，TI 不保证译文的准确性。 为确认准确性，请务必访问 ti.com 参考最新的英文版本（控制文档）。

# 内容

**1 特性** ..... 1
**2 应用** ..... 1
**3 说明** ..... 1
**4 引脚配置和功能** ..... 3
**5 规格** ..... 4
5.1 绝对最大额定值 ..... 4
5.2 ESD 等级 ..... 4
5.3 建议运行条件 ..... 4
5.4 热性能信息 ..... 5
5.5 电气特性 ..... 6
5.6 开关特性 ..... 6
5.7 工作特性 ..... 6
5.8 典型特性 ..... 7
**6 参数测量信息（漏极开路）** ..... 8
6.1 PMI ..... 8
**7 详细说明** ..... 9
7.1 概述 ..... 9
7.2 功能方框图 ..... 9
7.3 特性说明 ..... 9
7.4 器件功能模式 ..... 9
**8 应用和实施** ..... 10
8.1 应用信息 ..... 10
8.2 典型应用 ..... 10
8.3 电源相关建议 ..... 11
8.4 布局 ..... 11
**9 器件和文档支持** ..... 12
9.1 接收文档更新通知 ..... 12
9.2 支持资源 ..... 12
9.3 商标 ..... 12
9.4 静电放电警告 ..... 12
9.5 术语表 ..... 12
**10 修订历史记录** ..... 12
**11 机械、封装和可订购信息** ..... 13


Copyright © 2025 Texas Instruments Incorporated

# 4 引脚配置和功能






图 4-1. DBV 或 DCK 封装 5 引脚 SOT-23 或 SC70 顶视图




N.C. – 无内部连接
请参阅机械制图，了解尺寸。

图 4-2. DRY 封装 6 引脚 SON 透明俯视图

| 引脚 | | | 说明 |
|---|---|---|---|
| 名称 | DBV、DCK | DRY | |
| N.C. | 1 | 1、5 | 未连接 |
| A | 2 | 2 | 输入 |
| GND | 3 | 3 | 接地 |
| Y | 4 | 4 | 输出 |
| $V_{CC}$ | 5 | 6 | 电源引脚 |

Copyright © 2025 Texas Instruments Incorporated

# 5 规格

## 5.1 绝对最大额定值

在自然通风条件下的工作温度范围内测得（除非另有说明）(1)

| | | | 最小值 | 最大值 | 单位 |
|---|---|---|---|---|---|
| $V_{CC}$ | 电源电压 | | -0.5 | 6.5 | V |
| $V_I$ | 输入电压(2) | | -0.5 | 6.5 | V |
| $V_O$ | 在高阻抗或断电状态对任一输出施加的电压范围(2) | | -0.5 | 6.5 | V |
| $V_O$ | 应用到任一处于高电平或低电平状态输出的电压范围(2) (3) | | -0.5 | 6.5 | V |
| $I_{IK}$ | 输入钳位电流 | $V_I < 0$ | | -50 | mA |
| $I_{OK}$ | 输出钳位电流 | $V_O < 0$ | | -50 | mA |
| $I_O$ | 持续输出电流 | | | ±50 | mA |
| | 通过 $V_{CC}$ 或 GND 的持续电流 | | | ±100 | mA |
| $T_J$ | 工作结温 | | | 150 | °C |
| $T_{stg}$ | 贮存温度 | | -65 | 150 | °C |

(1) 超出“最大绝对额定值”下列出的值可能会对器件造成永久损坏。这些仅为在额定值下的工作情况，对于额定值下或者在超出“推荐的操作条件”下的任何其它情况下的器件功能性操作，在此并未说明。长时间处于绝对最大额定条件下可能会影响器件的可靠性。
(2) 如果遵守输入和输出电流额定值，则可能会超过输入和输出负电压额定值。
(3) $V_{CC}$ 的值在建议运行条件表中提供。

## 5.2 ESD 等级

| | | | 值 | 单位 |
|---|---|---|---|---|
| $V_{(ESD)}$ | 静电放电 | 人体放电模型 (HBM)，符合 AEC Q100-002 标准(1) | ±2000 | V |
| | | 充电器件模型 (CDM)，符合 AEC Q100-011 标准 | ±1000 | |

(1) AEC Q100-002 指示应当按照 ANSI/ESDA/JEDEC JS-001 规范执行 HBM 应力测试。

## 5.3 建议运行条件

在自然通风条件下的工作温度范围内测得（除非另有说明）(1)

| | | | 最小值 | 最大值 | 单位 |
|---|---|---|---|---|---|
| $V_{CC}$ | 电源电压 | 工作 | 1.65 | 5.5 | V |
| | | 仅数据保留 | 1.5 | | |
| $V_{IH}$ | 高电平输入电压 | $V_{CC}$ = 1.65V 至 1.95V | 0.65 × $V_{CC}$ | | V |
| | | $V_{CC}$ = 2.3V 至 2.7V | 1.7 | | |
| | | $V_{CC}$ = 3V 至 3.6V | 2 | | |
| | | $V_{CC}$ = 4.5V 至 5.5V | 0.7 × $V_{CC}$ | | |
| $V_{IL}$ | 低电平输入电压 | $V_{CC}$ = 1.65V 至 1.95V | | 0.35 × $V_{CC}$ | V |
| | | $V_{CC}$ = 2.3V 至 2.7V | | 0.7 | |
| | | $V_{CC}$ = 3V 至 3.6V | | 0.8 | |
| | | $V_{CC}$ = 4.5V 至 5.5V | | 0.3 × $V_{CC}$ | |
| $V_I$ | 输入电压 | | 0 | 5.5 | V |
| $V_O$ | 输出电压 | | 0 | 5.5 | V |
| $I_{OL}$ | 低电平输出电流 | $V_{CC}$ = 1.65V | | 4 | mA |
| | | $V_{CC}$ = 2.3V | | 8 | |
| | | $V_{CC}$ = 3V | | 16 | |
| | | | | 24 | |
| | | $V_{CC}$ = 4.5V | | 32 | |


Copyright © 2025 Texas Instruments Incorporated

在自然通风条件下的工作温度范围内测得（除非另有说明）(1)

| | | | 最小值 | 最大值 | 单位 |
|---|---|---|---|---|---|
| $\Delta t/\Delta v$ | 输入转换上升或下降速率 | $V_{CC}$ = 1.8V ± 0.15V，2.5V ± 0.2V | | 20 | ns/V |
| | | $V_{CC}$ = 3.3V ± 0.3V | | 10 | |
| | | $V_{CC}$ = 5V ± 0.5V | | 5 | |
| $T_A$ | 自然通风条件下的工作温度范围 | | -40 | 125 | °C |

(1) 器件的所有未使用输入必须保持在 $V_{CC}$ 或 GND，以确保器件正常运行。请参阅 TI 应用报告 *慢速或浮点 CMOS 输入的影响*，SCBA004。

## 5.4 热性能信息

| 热指标(1) | | SN74LVC1G07-Q1 | | | 单位 |
|---|---|---|---|---|---|
| | | DBV (SOT-23) | DCK (SC70) | DRY (SON) | |
| | | 5 引脚 | 5 引脚 | 6 引脚 | |
| $R_{\theta JA}$ | 结至环境热阻 | 357.1 | 371.0 | 439 | °C/W |
| $R_{\theta JC(top)}$ | 结至外壳（顶部）热阻 | 263.7 | 297.5 | 277 | °C/W |
| $R_{\theta JB}$ | 结至电路板热阻 | 264.4 | 258.6 | 271 | °C/W |
| $\psi_{JT}$ | 结至顶部特征参数 | 195.6 | 195.6 | 84 | °C/W |
| $\psi_{JB}$ | 结至电路板特征参数 | 262.2 | 256.2 | 271 | °C/W |
| $R_{\theta JC(bot)}$ | 结至外壳（底部）热阻 | – | – | – | °C/W |

(1) 有关新旧热指标的更多信息，请参阅 *半导体和 IC 封装热指标* 应用手册。

Copyright © 2025 Texas Instruments Incorporated

## 5.5 电气特性

在自然通风条件下的建议运行温度范围内测得（除非另有说明）

| 参数 | | 测试条件 | | $V_{CC}$ | 最小值 | 典型值 (1) | 最大值 | 单位 |
|---|---|---|---|---|---|---|---|---|
| $V_{OL}$ | | $I_{OL}$=100 μA | | 1.65V 至 5.5V | | | 0.1 | V |
| | | $I_{OL}$ = 4mA | | 1.65V | | | 0.45 | |
| | | $I_{OL}$ = 8mA | | 2.3V | | | 0.3 | |
| | | $I_{OL}$ = 16mA | | 3V | | | 0.4 | |
| | | $I_{OL}$ = 24mA | | | | | 0.55 | |
| | | $I_{OL}$ = 32mA | | 4.5V | | | 0.55 | |
| $I_I$ | A 输入 | $V_I$ = 5.5V 或 GND | | 0 至 5.5V | | | ±5 | μA |
| $I_{off}$ | | $V_I$ 或 $V_O$ = 5.5V | | 0 | | | ±10 | μA |
| $I_{CC}$ | | $V_I$ = 5.5V 或 GND， | $I_O$ = 0 | 1.65V 至 5.5V | | | 10 | μA |
| $\Delta I_{CC}$ | | 一个输入电压为 $V_{CC}$ – 0.6V， | 其他输入电压为 $V_{CC}$ 或 GND | 3V 至 5.5V | | | 500 | μA |
| $C_i$ | | $V_I$ = $V_{CC}$ 或 GND | | 3.3V | | 4 | | pF |
| $C_o$ | | $V_O$ = $V_{CC}$ 或 GND | | 3.3V | | 5 | | pF |

(1) 所有典型值均在 $V_{CC}$ = 3.3V、$T_A$ = 25°C 下测得。

## 5.6 开关特性

在自然通风条件下的建议工作温度范围内测得（除非另有说明）（请参阅 图 6-1）

| 参数 | 从（输入） | 至（输出） | $V_{CC}$ = 1.8V ± 0.15V | | $V_{CC}$ = 2.5V ± 0.2V | | $V_{CC}$ = 3.3V ± 0.3V | | $V_{CC}$ = 5V ± 0.5V | | 单位 |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | | | 最小值 | 最大值 | 最小值 | 最大值 | 最小值 | 最大值 | 最小值 | 最大值 | |
| $t_{pd}$ | A | Y | 2.4 | 9.8 | 1 | 7.0 | 1.5 | 5.7 | 1 | 4.9 | ns |

## 5.7 工作特性

$T_A$ = 25°C

| 参数 | | 测试条件 | $V_{CC}$ = 1.8V | $V_{CC}$ = 2.5V | $V_{CC}$ = 3.3V | $V_{CC}$ = 5V | 单位 |
|---|---|---|---|---|---|---|---|
| | | | 典型值 | 典型值 | 典型值 | 典型值 | |
| $C_{pd}$ | 功率耗散电容 | f = 10MHz | 3 | 3 | 4 | 6 | pF |


Copyright © 2025 Texas Instruments Incorporated

## 5.8 典型特性





图 5-1. 在 3.3V VCC 电压下的 TPD 随温度变化情况






图 5-2. 在 25°C 下 TPD 随温度的变化

# 6 参数测量信息（漏极开路）


## 6.1 PMI





LOAD CIRCUIT

| TEST | S1 |
|---|---|
| $t_{PZL}$ (see Notes E and F) | $V_{LOAD}$ |
| $t_{PLZ}$ (see Notes E and G) | $V_{LOAD}$ |
| $t_{PHZ}/t_{PZH}$ | $V_{LOAD}$ |


| $V_{CC}$ | INPUT | | $V_M$ | $V_{LOAD}$ | $C_L$ | $R_L$ | $V_\Delta$ |
|---|---|---|---|---|---|---|---|
| | $V_I$ | $t_r/t_f$ | | | | | |
| 1.8 V ± 0.15 V | $V_{CC}$ | ≤ 2 ns | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 1 kΩ | 0.15 V |
| 2.5 V ± 0.2 V | $V_{CC}$ | ≤ 2 ns | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 500 Ω | 0.15 V |
| 3.3 V ± 0.3 V | 3 V | ≤ 2.5 ns | 1.5 V | 6 V | 50 pF | 500 Ω | 0.3 V |
| 5 V ± 0.5 V | $V_{CC}$ | ≤ 2.5 ns | $V_{CC}/2$ | $2 \times V_{CC}$ | 50 pF | 500 Ω | 0.3 V |





VOLTAGE WAVEFORMS
PULSE DURATION




VOLTAGE WAVEFORMS
SETUP AND HOLD TIMES




VOLTAGE WAVEFORMS
PROPAGATION DELAY TIMES
INVERTING AND NONINVERTING OUTPUTS




VOLTAGE WAVEFORMS
ENABLE AND DISABLE TIMES
LOW- AND HIGH-LEVEL ENABLING

NOTES: A. $C_L$ includes probe and jig capacitance.
B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
C. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, $Z_O$ = 50 Ω.
D. The outputs are measured one at a time, with one transition per measurement.
E. Since this device has open-drain outputs, $t_{PLZ}$ and $t_{PZL}$ are the same as $t_{pd}$.
F. $t_{PZL}$ is measured at $V_M$.
G. $t_{PLZ}$ is measured at $V_{OL} + V_\Delta$.
H. All parameters and waveforms are not applicable to all devices.

**图 6-1. 负载电路和电压波形**


Copyright © 2025 Texas Instruments Incorporated

# 7 详细说明

## 7.1 概述

SN74LVC1G07-Q1 器件包含一个最大灌电流为 32mA 的开漏 缓冲器。该器件专用于使用 $I_{off}$ 的局部断电应用。$I_{off}$ 电路可禁用输出，以防在器件断电时电流回流对器件造成损坏。

## 7.2 功能方框图





**图 7-1. 逻辑图（正逻辑）**

## 7.3 特性说明

- 宽工作电压范围。
  - 可在 1.65V 至 5.5V 范围内工作。
- 支持降压转换。
- 输入和输出支持高达 5.5V 电压。
- $I_{off}$ 特性允许在 $V_{CC}$ 为 0V 时在输入和输出上产生电压。

## 7.4 器件功能模式

表 7-1 列出了 SN74LVC1G07-Q1 器件的功能模式。

**表 7-1. 功能表**

| 输入<br>A | 输出<br>Y |
|---|---|
| L | L |
| H | Z |

# 8 应用和实施

**备注**

以下应用部分中的信息不属于 TI 器件规格的范围，TI 不担保其准确性和完整性。TI 的客 户应负责确定器件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

## 8.1 应用信息

SN74LVC1G07-Q1 是一款高驱动 CMOS 器件，可用于实现高输出驱动缓冲器，例如 LED 应用。它可以在 4.5V 时灌入 32mA 电流，因此非常适合高驱动应用以及有线 OR/AND 功能。它非常适合高达 100MHz 的高速应用。输入可耐受 5.5V 电压，允许将其升压降压转换至 $V_{CC}$。

## 8.2 典型应用





**图 8-1. 典型应用-SN74LVC1G07-Q1**

### *8.2.1 设计要求*

此器件采用 CMOS 技术并具有高输出驱动。注意避免总线争用，因为它可以驱动超过最大限制的电流。高驱动也会在轻负载时产生快速边缘，因此应考虑布线和负载条件以防止响铃。

### *8.2.2 详细设计过程*

1. 建议的输入条件
   - 上升时间和下降时间规格。请参阅*建议运行条件*表中的 $\Delta t/\Delta V$。
   - 指定的高电平和低电平。请参阅*建议运行条件*表中的 $V_{IH}$ 和 $V_{IL}$。
   - 输入可耐受过压，允许它们在任何有效 $V_{CC}$ 下高达 *建议运行条件*表中的（$V_I$ 最大值）。
2. 建议的输出条件
   - 每路输出的负载电流不应超过（$I_O$ 最大值），且不能超过该器件的总电流（通过 $V_{CC}$ 或 GND 的持续电流）。这些限值位于*绝对最大额定值*表中。
   - 输出不应被拉至高于 5.5V。


Copyright © 2025 Texas Instruments Incorporated

### 8.2.3 应用曲线





**图 8-2. ICC 与频率间的关系**

## 8.3 电源相关建议

电源可以是 *建议运行条件* 表中最小和最大电源电压额定值之间的任何电压。

每个 $V_{CC}$ 引脚应具有一个良好的旁路电容器，以防止功率干扰。对于单电源器件，建议使用 0.1µF 电容器。如果有多个 $V_{CC}$ 引脚，则建议每个电源引脚使用 0.01 µ F 或 0.022 µ F 电容器。可以并联多个旁路电容器以抑制不同的噪声频率。0.1 µ F 和 1 µ F 电容器通常并联使用。为了获得更佳效果，旁路电容器应尽可能靠近电源引脚安装。

## 8.4 布局

### 8.4.1 布局指南

当使用多位逻辑器件时，输入决不能悬空。在许多情况下，未使用数字逻辑器件的全部或部分功能；例如，仅使用三输入与门的两个输入或仅使用 4 个缓冲门中的 3 个。此类输入引脚不应悬空，因为外部连接处的未定义电压会导致未定义的运行状态。以下指定了在所有情况下都必须遵守的规则。数字逻辑器件的所有未使用输入必须连接至高或低偏置以防悬空。应根据器件的功能为任何特定未使用的输入施加逻辑电平。通常，它们会连接到 GND 或 $V_{CC}$，具体取决于哪种更方便。

### 8.4.2 布局示例





**图 8-3. 布局示例**

# 9 器件和文档支持

## 9.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击*通知* 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

## 9.2 支持资源

TI E2E™ 中文支持论坛是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的使用条款。

## 9.3 商标

TI E2E™ is a trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

## 9.4 静电放电警告

静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

## 9.5 术语表

TI 术语表　　本术语表列出并解释了术语、首字母缩略词和定义。

# 10 修订历史记录

注：以前版本的页码可能与当前版本的页码不同

| Changes from Revision C (June 2025) to Revision D (October 2025) | Page |
|---|---|
| • 将 DCK 封装的结至环境热阻值从：301.2°C/W 更改为：371.0°C/W | 5 |
| • 将 DCK 封装的结至外壳（顶部）热阻值从：186.5°C/W 更改为：297.5°C/W | 5 |
| • 将 DCK 封装的结至电路板热阻值从：111.8°C/W 更改为：258.6°C/W | 5 |
| • 将 DCK 封装的结至顶部特征值从：78.3°C/W 更改为：195.6°C/W | 5 |
| • 将 DCK 封装的结至电路板特征值从：110.6°C/W 更改为：256.2°C/W | 5 |

| Changes from Revision B (May 2019) to Revision C (June 2025) | Page |
|---|---|
| • 更新了整个文档中的表格、图和交叉参考的编号格式 | 1 |
| • 将*器件信息* 表更改为*封装信息* | 1 |
| • 将 DBV 封装的结至环境热阻值从：269.3°C/W 更改为：357.1°C/W | 5 |
| • 将 DBV 封装的结至外壳（顶部）热阻值从：175.2°C/W 更改为：263.7°C/W | 5 |
| • 将 DBV 封装的结至电路板热阻值从：104.9°C/W 更改为：264.4°C/W | 5 |
| • 将 DBV 封装的结至顶部特征值从：73.4°C/W 更改为：195.6°C/W | 5 |
| • 将 DBV 封装的结至电路板特征值从：104.5°C/W 更改为：262.2°C/W | 5 |

| Changes from Revision A (February 2017) to Revision B (May 2019) | Page |
|---|---|
| • 向器件信息 表添加了 DRY 封装选项 | 1 |


Copyright © 2025 Texas Instruments Incorporated

- 向 节 4 添加了 DRY 封装作为产品预发布器件选项.....3
- 向节 5.4 表中添加了 DRY 封装.....5

## 11 机械、封装和可订购信息

以下页面包含机械、封装和可订购信息。这些信息是指定器件可用的最新数据。数据如有变更，恕不另行通知，且不会对此文档进行修订。有关此数据表的浏览器版本，请查阅左侧的导航栏。

Copyright © 2025 Texas Instruments Incorporated

## PACKAGING INFORMATION

| Orderable part number | Status (1) | Material type (2) | Package \| Pins | Package qty \| Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|---|---|---|---|---|---|---|---|---|---|
| 74LVC1G07QDBVRQ1G4 | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | (33I5, CCQO) |
| 74LVC1G07QDBVRQ1G4.A | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | (33I5, CCQO) |
| 74LVC1G07QDBVRQ1G4.B | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | (33I5, CCQO) |
| SN74LVC1G07QDBVRQ1 | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | NIPDAU \| SN | Level-1-260C-UNLIM | -40 to 125 | (33I5, 3NPH, 3VQF, CCQO) |
| SN74LVC1G07QDBVRQ1.A | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | (33I5, 3NPH, 3VQF, CCQO) |
| SN74LVC1G07QDBVRQ1.B | Active | Production | SOT-23 (DBV) \| 5 | 3000 \| LARGE T&R | Yes | SN | Level-1-260C-UNLIM | -40 to 125 | (33I5, 3NPH, 3VQF, CCQO) |
| SN74LVC1G07QDCKRQ1 | Active | Production | SC70 (DCK) \| 5 | 3000 \| LARGE T&R | Yes | SN | Level-2-260C-1 YEAR | -40 to 125 | 16J |
| SN74LVC1G07QDCKRQ1.A | Active | Production | SC70 (DCK) \| 5 | 3000 \| LARGE T&R | Yes | SN | Level-2-260C-1 YEAR | -40 to 125 | 16J |
| SN74LVC1G07QDCKRQ1.B | Active | Production | SC70 (DCK) \| 5 | 3000 \| LARGE T&R | Yes | SN | Level-2-260C-1 YEAR | -40 to 125 | 16J |
| SN74LVC1G07QDCKTQ1 | Active | Production | SC70 (DCK) \| 5 | 250 \| SMALL T&R | Yes | SN | Level-2-260C-1 YEAR | -40 to 125 | 16J |
| SN74LVC1G07QDCKTQ1.B | Active | Production | SC70 (DCK) \| 5 | 250 \| SMALL T&R | Yes | SN | Level-2-260C-1 YEAR | -40 to 125 | 16J |
| SN74LVC1G07QDRYRQ1 | Active | Production | SON (DRY) \| 6 | 5000 \| LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HL |
| SN74LVC1G07QDRYRQ1.B | Active | Production | SON (DRY) \| 6 | 5000 \| LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | HL |

(1) **Status:** For more details on status, see our product life cycle.

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the TI RoHS Statement for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF SN74LVC1G07-Q1 :**


- Catalog : SN74LVC1G07
- Enhanced Product : SN74LVC1G07-EP

NOTE: Qualified Version Definitions:


- Catalog - TI's standard catalog product
- Enhanced Product - Supports Defense, Aerospace and Medical Applications

## TAPE AND REEL INFORMATION

**REEL DIMENSIONS**





**TAPE DIMENSIONS**




| | |
|---|---|
| A0 | Dimension designed to accommodate the component width |
| B0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |


**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**




*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| 74LVC1G07QDBVRQ1G4 | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.3 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| 74LVC1G07QDBVRQ1G4 | SOT-23 | DBV | 5 | 3000 | 179.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 180.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.3 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 179.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 180.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 180.0 | 8.4 | 2.3 | 2.55 | 1.2 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDCKTQ1 | SC70 | DCK | 5 | 250 | 178.0 | 9.0 | 2.4 | 2.5 | 1.2 | 4.0 | 8.0 | Q3 |
| SN74LVC1G07QDRYRQ1 | SON | DRY | 6 | 5000 | 180.0 | 9.5 | 1.2 | 1.65 | 0.7 | 4.0 | 8.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal


| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|---|---|---|---|---|---|---|---|
| 74LVC1G07QDBVRQ1G4 | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| 74LVC1G07QDBVRQ1G4 | SOT-23 | DBV | 5 | 3000 | 200.0 | 183.0 | 25.0 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 210.0 | 185.0 | 35.0 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 200.0 | 183.0 | 25.0 |
| SN74LVC1G07QDBVRQ1 | SOT-23 | DBV | 5 | 3000 | 210.0 | 185.0 | 35.0 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 210.0 | 185.0 | 35.0 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| SN74LVC1G07QDCKRQ1 | SC70 | DCK | 5 | 3000 | 190.0 | 190.0 | 30.0 |
| SN74LVC1G07QDCKTQ1 | SC70 | DCK | 5 | 250 | 180.0 | 180.0 | 18.0 |
| SN74LVC1G07QDRYRQ1 | SON | DRY | 6 | 5000 | 189.0 | 185.0 | 36.0 |

# PACKAGE OUTLINE

## DBV0005A

## SOT-23 - 1.45 mm max height


SMALL OUTLINE TRANSISTOR





4214839/K 08/2024

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Refernce JEDEC MO-178.
4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
5. Support pin may differ or may not be present.




LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:15X





SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:15X

4214839/K 08/2024

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

# PACKAGE OUTLINE

## DCK0005A

## SOT - 1.1 max height


SMALL OUTLINE TRANSISTOR





4214834/G 11/2024

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Refernce JEDEC MO-203.
4. Support pin may differ or may not be present.
5. Lead width does not comply with JEDEC.
6. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25mm per side




LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:18X





SOLDER MASK DETAILS

4214834/G 11/2024

NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.
8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




SOLDER PASTE EXAMPLE
BASED ON 0.125 THICK STENCIL
SCALE:18X

4214834/G 11/2024

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
10. Board assembly site may have different recommendations for stencil design.

# DRY 6 USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD





Images above are just a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.

# PACKAGE OUTLINE

## DRY0006B


## USON - 0.55 mm max height

PLASTIC SMALL OUTLINE - NO LEAD





NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.




LAND PATTERN EXAMPLE
1:1 RATIO WITH PKG SOLDER PADS
SCALE:40X




SOLDER MASK DETAILS

4222207/B 02/2016

NOTES: (continued)


3. For more information, see QFN/SON PCB application report in literature No. SLUA271 (www.ti.com/lit/slua271).

# EXAMPLE STENCIL DESIGN

## DRY0006B

## USON - 0.55 mm max height

PLASTIC SMALL OUTLINE - NO LEAD




SOLDER PASTE EXAMPLE
BASED ON 0.075 - 0.1 mm THICK STENCIL
SCALE:40X

4222207/B 02/2016

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

# 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 TI 销售条款)、TI 通用质量指南 或 ti.com 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。 除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月