


TPS22997 具有可调上升时间的 5.5V、10A、4mΩ 导通电阻负载开关

1 特性

- 输入电压范围 (V_{IN}) : 0.1V-5.5V
- 偏置电压范围 : 1.5V 至 5.5V
- 最大持续电流 : 10A
- 导通电阻 (R_{ON}) : 4mΩ (典型值)
- 可调转换率控制
- 可调节快速输出放电 (QOD)
- 开漏电源正常 (PG) 信号
- 热关断
- 低功耗 :
 - 导通状态 (I_Q) : 10 μA (典型值)
 - 关闭状态 (I_{SD}) : 0.1 μA (典型值)
- 热关断
- ON 引脚智能下拉电阻 ($R_{PD,ON}$)
 - $ON \geq V_{IH}$ (I_{ON}) : 25nA (典型值)
 - $ON \leq V_{IL}$ ($R_{PD,ON}$) : 500kΩ (典型值)

2 应用

- 固态硬盘
- PC 和笔记本电脑
- 工业 PC
- 光学模块



TPS22997 方框图

3 说明

TPS22997 是一款单通道负载开关，具有可配置上升时间，从而可更大幅度地降低浪涌电流。此器件包含一个可在 0.1 V 至 5.5V 输入电压范围内运行的 N 沟道 MOSFET，并且支持 10 A 的最大持续电流。


该开关由使能引脚 (ON) 控制，该引脚能够直接连接低电压 GPIO 信号 ($V_{IH} = 0.8V$)。TPS22997 器件具有可选的 QOD 引脚，用于在开关关闭时快速输出放电，并且输出的下降时间 (t_{FALL}) 可以通过外部电阻进行调整。器件上有一个电源正常 (PG) 信号，指示主 MOSFET 何时完全导通，可用于启用下游负载。集成式热关断功能可确保在高温环境中提供保护。

TPS22997 采用 10 引脚 WQFN 封装 (RYZ) (1.5mm × 2.0mm，间距为 0.5mm) 并可在自然通风条件下的 -40°C 至 +125°C 温度范围运行。

器件信息

器件型号	封装 ⁽¹⁾	封装尺寸 (标称值)
TPS22997	WQFN (10)	1.5mm × 2.0mm

(1) 要了解所有可用封装，请参阅数据表末尾的可订购产品附录。



TPS22997 典型应用



Table of Contents

1 特性	1	8 Detailed Description	13
2 应用	1	8.1 Overview.....	13
3 说明	1	8.2 Functional Block Diagram.....	13
4 Revision History	2	8.3 Feature Description.....	13
5 Pin Configuration and Functions	3	8.4 Device Functional Modes.....	14
6 Specifications	4	9 Application and Implementation	16
6.1 Absolute Maximum Ratings.....	4	9.1 Application Information.....	16
6.2 ESD Ratings.....	4	9.2 Typical Application.....	16
6.3 Recommended Operating Conditions.....	4	9.3 Power Supply Recommendations.....	17
6.4 Thermal Information.....	4	9.4 Layout.....	18
6.5 Electrical Characteristics (VBIAS = 5 V).....	5	10 Device and Documentation Support	19
6.6 Electrical Characteristics (VBIAS = 3.3 V).....	5	10.1 接收文档更新通知.....	19
6.7 Electrical Characteristics (VBIAS = 1.5 V).....	6	10.2 支持资源.....	19
6.8 Switching Characteristics (VBIAS = 5 V).....	7	10.3 Trademarks.....	19
6.9 Switching Characteristics (VBIAS = 3.3 V).....	8	10.4 静电放电警告.....	19
6.10 Switching Characteristics (VBIAS = 1.5 V).....	9	10.5 术语表.....	19
6.11 Typical Characteristics.....	10	11 Mechanical, Packaging, and Orderable Information	20
7 Parameter Measurement Information	12		

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

DATE	REVISION	NOTES
December 2022	*	Initial Release

5 Pin Configuration and Functions




图 5-1. TPS22997 RYZ Package, 10-Pin WQFN (Top View)

表 5-1. Pin Functions

PIN		I/O ⁽¹⁾	DESCRIPTION
NAME	NO.		
VBIAS	1	I	Device bias supply
VIN	2, 3	I	Switch input
PG	4	O	Open drain power good signal, asserted high when the output is full load ready
GND	5	-	Device ground
QOD	6	-	Quick output discharge pin
VOUT	7, 8	O	Switch output
CT	9	I	Timing pin, can control the slew rate of the output through a capacitor to GND
ON	10	I	Enable pin

(1) I = Input, O = Output

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

		MIN	MAX	UNIT
V _{IN}	Input Voltage	– 0.3	6	V
V _{BIAS}	Bias Voltage	– 0.3	6	V
V _{ON} , V _{PG} , V _{QOD}	Control Pin Voltage	– 0.3	6	V
V _{CT}	CT Pin Voltage		15	V
I _{MAX}	Maximum Current		10	A
T _J	Junction temperature		Internally Limited	°C
T _{stg}	Storage temperature	– 65	150	°C

- (1) Stresses beyond those listed under *Absolute Maximum Rating* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Condition*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 ESD Ratings

			VALUE	UNIT
V _(ESD)	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000	V
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±1000	

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V _{IN}	Input Voltage	0.1		5.5	V
V _{BIAS}	Bias Voltage	1.5		5.5	V
V _{IH}	ON Pin High Voltage Range	0.8		5.5	V
V _{IL}	ON Pin Low Voltage Range	0		0.35	V
V _{PG} , V _{QOD}	Control Pin Voltage	0		5.5	V
T _A	Ambient Temperature	–40		125	°C

6.4 Thermal Information

THERMAL METRIC		TPS22997	UNIT
		RYZ (WQFN)	
		10 PINS	
R _{θJA}	Junction-to-ambient thermal resistance	83.7	°C/W
R _{θJC(top)}	Junction-to-case (top) thermal resistance	73.9	°C/W
R _{θJB}	Junction-to-board thermal resistance	18.2	°C/W
Ψ _{JT}	Junction-to-top characterization parameter	2.0	°C/W
Y _{JB}	Junction-to-board characterization parameter	18.1	°C/W

6.5 Electrical Characteristics (VBIAS = 5 V)

over operating free-air temperature range (unless otherwise noted). Typical values are specified at 25°C and VIN = 3.3V, VBIAS = 5.5V.

PARAMETER		TEST CONDITIONS	T _A	MIN	TYP	MAX	UNIT
Power Consumption							
I _{SD,VBIAS}	VBIAS Shutdown Current	ON = 0V	25°C	0.1			uA
			-40°C to 85°C	0.5			uA
			-40°C to 125°C	1			uA
I _{Q,VBIAS}	VBIAS Quiescent Current	ON > V _{IH}	25°C	10			uA
			-40°C to 85°C	15			uA
			-40°C to 125°C	15			uA
I _{SD,VIN}	VIN Shutdown Current	ON = 0V	25°C	0.1			uA
			-40°C to 85°C	1			uA
			-40°C to 125°C	7			uA
I _{ON}	ON pin leakage	ON = VBIAS	-40°C to 125°C	0.1			uA
Performance							
R _{ON}	On-Resistance	VIN = 5V	25°C	4			m Ω
			-40°C to 85°C	6			m Ω
			-40°C to 125°C	7			m Ω
R _{ON}	On-Resistance	VIN = 3.3V	25°C	4			m Ω
			-40°C to 85°C	6			m Ω
			-40°C to 125°C	7			m Ω
R _{ON}	On-Resistance	VIN = 1.8V	25°C	4			m Ω
			-40°C to 85°C	6			m Ω
			-40°C to 125°C	7			m Ω
R _{ON}	On-Resistance	VIN = 1.2V	25°C	4			m Ω
			-40°C to 85°C	6			m Ω
			-40°C to 125°C	7			m Ω
R _{ON}	On-Resistance	VIN = 0.8V	25°C	4			m Ω
			-40°C to 85°C	6			m Ω
			-40°C to 125°C	7			m Ω
V _{OL,PG}	Power Good VOL	I _{PG} = 1mA	-40°C to 125°C	0.2			V
R _{PD,ON}	Smart Pull Down Resistance		25°C	500			k Ω
			-40°C to 125°C	700			k Ω
R _{QOD}	QOD Resistance		25°C	50			Ω
			-40°C to 125°C	75			Ω
Protection							
TSD	Thermal Shutdown		-	150	170	190	°C
TSD _{HYS}	Thermal Shutdown Hysteresis		-	20			°C

6.6 Electrical Characteristics (VBIAS = 3.3 V)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	TA	MIN	TYP	MAX	UNIT
Power Consumption							

6.6 Electrical Characteristics (VBIAS = 3.3 V) (continued)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A	MIN	TYP	MAX	UNIT
I _{SD,VBIAS}	VBIAS Shutdown Current	ON = 0V	25°C	0.1			uA
			-40°C to 85°C	0.5		uA	
			-40°C to 125°C	1		uA	
I _{Q,VBIAS}	VBIAS Quiescent Current	ON > V _{IH}	25°C	10			uA
			-40°C to 85°C	15		uA	
			-40°C to 125°C	15		uA	
I _{SD,VIN}	VIN Shutdown Current	ON = 0V	25°C	0.1			uA
			-40°C to 85°C	1		uA	
			-40°C to 125°C	7		uA	
I _{ON}	ON pin leakage	ON = VBIAS	-40°C to 125°C	0.1			uA
Performance							
R _{ON}	On-Resistance	VIN = 3.3V	25°C	4			m Ω
			-40°C to 85°C	6		m Ω	
			-40°C to 125°C	7		m Ω	
R _{ON}	On-Resistance	VIN = 1.8V	25°C	4			m Ω
			-40°C to 85°C	6		m Ω	
			-40°C to 125°C	7		m Ω	
R _{ON}	On-Resistance	VIN = 1.2V	25°C	4			m Ω
			-40°C to 85°C	6		m Ω	
			-40°C to 125°C	7		m Ω	
R _{ON}	On-Resistance	VIN = 0.8V	25°C	4			m Ω
			-40°C to 85°C	6		m Ω	
			-40°C to 125°C	7		m Ω	
V _{OL,PG}	Power Good VOL	I _{PG} = 1mA	-40°C to 125°C	0.2			V
R _{PD,ON}	Smart Pull Down Resistance		25°C	500			k Ω
			-40°C to 125°C	700		k Ω	
R _{QOD}	QOD Resistance		25°C	50			Ω
			-40°C to 125°C	100		Ω	
Protection							
TSD	Thermal Shutdown		-	150	170	190	°C
TSD _{HYS}	Thermal Shutdown Hysteresis		-	20			°C

6.7 Electrical Characteristics (VBIAS = 1.5 V)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A	MIN	TYP	MAX	UNIT
Power Consumption							
I _{SD,VBIAS}	VBIAS Shutdown Current	ON = 0V	25°C		0.1		uA
			-40°C to 85°C			0.5	uA
			-40°C to 125°C			1	uA
I _{Q,VBIAS}	VBIAS Quiescent Current	ON > V _{IH}	25°C		10		uA
			-40°C to 85°C			15	uA
			-40°C to 125°C			15	uA

6.7 Electrical Characteristics (VBIAS = 1.5 V) (continued)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	T _A	MIN	TYP	MAX	UNIT
I _{SD,VIN}	VIN Shutdown Current	ON = 0V	25°C	0.1			uA
			-40°C to 85°C	1			uA
			-40°C to 125°C	7			uA
I _{ON}	ON pin leakage	ON = VBIAS	-40°C to 125°C	0.1			uA
Performance							
R _{ON}	On-Resistance	VIN = 1.5V	25°C	4.5			mΩ
			-40°C to 85°C	6			mΩ
			-40°C to 125°C	7			mΩ
R _{ON}	On-Resistance	VIN = 1.2V	25°C	4.5			mΩ
			-40°C to 85°C	6			mΩ
			-40°C to 125°C	7			mΩ
R _{ON}	On-Resistance	VIN = 0.8V	25°C	4.5			mΩ
			-40°C to 85°C	6			mΩ
			-40°C to 125°C	7			mΩ
V _{OL,PG}	Power Good VOL	I _{PG} = 1mA	-40°C to 125°C	0.2			V
R _{PD,ON}	Smart Pull Down Resistance		25°C	500			kΩ
			-40°C to 125°C	700			kΩ
R _{QOD}	QOD Resistance		25°C	55			Ω
			-40°C to 125°C	100			Ω
Protection							
TSD	Thermal Shutdown		-	150	170	190	°C
TSD _{HYS}	Thermal Shutdown Hysteresis		-	20			°C

6.8 Switching Characteristics (VBIAS = 5 V)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIN = 5V						
t _{ON}	Turn ON time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		1170		us
t _{RISE}	Rise time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		819		us
t _D	Delay time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		347		us
t _{FALL}	Fall time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		2090		us
t _{OFF}	Turn OFF time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		108		us
VIN = 3.3V						
t _{ON}	Turn ON time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		944		us
t _{RISE}	Rise time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		567		us
t _D	Delay time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		377		us
t _{FALL}	Fall time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		2110		us
t _{OFF}	Turn OFF time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		113		us
VIN = 1.8V						
t _{ON}	Turn ON time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		692		us
t _{RISE}	Rise time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		327		us
t _D	Delay time	R _L = 100 Ω, C _L = 10uF, CT = 1000pF		365		us

6.8 Switching Characteristics (VBIAS = 5 V) (continued)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2150		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		117		us
VIN = 1.2V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		591		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		227		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		364		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2180		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		120		us
VIN = 0.8V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		523		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		159		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		365		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2260		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		129		us

6.9 Switching Characteristics (VBIAS = 3.3 V)

over operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIN = 3.3V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		898		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		563		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		336		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2100		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		108		us
VIN = 1.8V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		708		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		331		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		377		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2145		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		113		us
VIN = 1.2V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		605		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		231		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		375		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2190		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		119		us
VIN = 0.8V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		536		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		162		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		373		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2260		us

6.9 Switching Characteristics (VBIAS = 3.3 V) (continued)

over operating free-air temperature range (unless otherwise noted)


PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		126		us

6.10 Switching Characteristics (VBIAS = 1.5 V)

over operating free-air temperature range (unless otherwise noted)


PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIN = 1.5V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		620		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		281		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		340		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2150		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		111		us
VIN = 1.2V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		642		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		237		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		404		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2170		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		114		us
VIN = 0.8V						
tON	Turn ON time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		535		us
tRISE	Rise time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		166		us
tD	Delay time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		368		us
tFALL	Fall time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		2245		us
tOFF	Turn OFF time	$R_L = 100\ \Omega$, $C_L = 10\ \mu\text{F}$, $C_T = 1000\text{pF}$		171		us

6.11 Typical Characteristics




VIN = VBIAS

图 6-1. On-Resistance vs Bias Voltage



VIN = VBIAS


图 6-2. QOD-Resistance vs Bias Voltage



VIN = VBIAS

VOUT = OPEN


图 6-3. Quiescent Current vs Bias Voltage



VIN = VBIAS

VOUT = GND

图 6-4. Shutdown Current vs Bias Voltage




VBIAS = 5 V

 $C_L = 10 \mu\text{F}$ $R_L = 100 \Omega$

CT = 1000 pF

图 6-5. Delay Time vs Input Voltage



VBIAS = 5 V

 $C_L = 10 \mu\text{F}$ $R_L = 100 \Omega$

CT = 1000 pF

图 6-6. Rise Time vs Input Voltage

6.11 Typical Characteristics (continued)




图 6-7. Turn-on Time vs Input Voltage




图 6-8. Turn-off Time vs Input Voltage




图 6-9. Fall Time vs Input Voltage




图 6-10. Rise Time vs CT Capacitor

7 Parameter Measurement Information




图 7-1. TPS22997 Timing Diagram


8 Detailed Description

8.1 Overview

The TPS22997 device is a single-channel load switch with a 4-mΩ power MOSFET designed to operate up to 10 A. The voltage range is 0.1 V to 5.5 V. A configurable rise time provides flexibility for power sequencing and minimizes inrush current for high capacitance loads.

The switch is controlled by an enable pin (ON), which is capable of interfacing directly with low voltage GPIO signals down to its V_{IH} level of 0.8 V. The TPS22997 device has an optional QOD pin for quick output discharge when switch is turned off, and the fall time (t_{FALL}) of the output can be adjusted through an external capacitor. There is a Power Good (PG) signal on the device that indicates when the main MOSFET is fully turned on and the on-resistance is at its final value.

8.2 Functional Block Diagram



8.3 Feature Description

8.3.1 ON and OFF Control

The ON pin controls the state of the switch. The ON pin is compatible with standard GPIO logic threshold so it can be used in a wide variety of applications. When the pin pull high, the device enables, and when it is low, the device disables.

8.3.2 Adjustable Slew Rate

A capacitor to GND on the CT pin sets the slew rate, and the higher the capacitance the lower the slew rate. The voltage on the CT pin can be as high as 15 V; therefore, the minimum voltage rating for the CT capacitor must be 30 V for optimal performance. Rise times for VBIAS = 5 V are shown below.

CT Capacitor	VIN = 5 V	VIN = 3.3 V	VIN = 1.8 V	VIN = 1.2 V	VIN = 0.8 V
0 pF	165 μ s	126 μ s	86 μ s	66 μ s	51 μ s
220 pF	309 μ s	221 μ s	137 μ s	99 μ s	74 μ s
1000 pF	819 μ s	554 μ s	319 μ s	222 μ s	160 μ s
4700 pF	3260 μ s	2170 μ s	1210 μ s	829 μ s	575 μ s

The following equation can be used to estimate the rise time for different VIN and CT capacitors at VBIAS = 5 V.

$$t_R = (0.1302 V_{IN} + 0.0063) \times CT + 27.797 V_{IN} + 30.54 \quad (1)$$

Where:

- t_R = Rise time in μ s
- V_{IN} = Input voltage in V
- CT = CT capacitance in pF

8.3.3 Adjustable Quick Output Discharge

The TPS22997 device includes a QOD feature that can be configured in one of three ways:

1. QOD pin shorted to VOUT pin. Using this method, the discharge rate after the switch becomes disabled is controlled with the value of the internal resistance RQOD. The value of this resistance is listed in the Electrical Characteristics table.
2. QOD pin connected to VOUT pin using an external resistor R_{EXT} . After the switch becomes disabled, the discharge rate is controlled by the value of the total resistance of the QOD.
3. QOD pin is unused and left floating. Using this method, there is no quick output discharge functionality, and the output remains floating after the switch is disabled.

Fall time is dependent on the strength of the configured pulldown resistance on the output.

8.3.4 Thermal Shutdown

When the device temperature reaches 150°C (typical), the device shuts itself off to prevent thermal damage. After it cools off by about 20°C, the device turns back on. If the device is kept in a thermally stressful environment, then the device oscillates between these two states until it can keep its temperature below the thermal shutdown point.

8.3.5 Power Good (PG) Signal

The TPS22997 device has a Power Good (PG) output signal to indicate the gate of the pass FET is driven high and the switch is on with the on-resistance close to its final value (full load ready). The signal is an active high and open drain output which can be connected to a voltage source through an external pullup resistor, R_{PU} . This voltage source can be VOUT from the TPS22997 device or another external voltage. VBIAS is required for PG to have a valid output.

8.4 Device Functional Modes

The below table summarizes the device functional modes:

ON	Fault Condition	VOUT State
L	N/A	Hi-Z
H	None	V_{IN} (through R_{ON})

ON	Fault Condition	VOUT State
X	Thermal shutdown	Hi-Z

9 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

9.1 Application Information

This section highlights some of the design considerations when implementing this device in various applications.

9.2 Typical Application

This typical application demonstrates how to use the TPS22997 device to limit startup inrush current.




图 9-1. TPS22997 Basic Application

表 9-1. Component Descriptions

PARAMETER	Purpose
C_{BIAS}	Stabilize the bias supply and filter out low frequency noise.
C_T	Adjustable rise time capacitor.
R_T	Optional C_T capacitor discharge resistor for cases when device is disabled before output has fully ramped up. Use a resistor $>10M\ \Omega$.
R_{DCHG}	Adjustable output discharge resistor.

9.2.1 Design Requirements

For this example, the values below are used as the design parameters.

表 9-2. Design Parameters

PARAMETER	VALUE
V_{BIAS}	5.0 V
V_{IN}	5.0 V
Load capacitance	220 μ F
Maximum inrush current	1.5 A

9.2.2 Detailed Design Procedure

When the switch enables, the charge up the output capacitance from 0 V to the set value (1.8 V in this example). This charge arrives in the form of inrush current. Calculate inrush current using [方程式 2](#).

$$\text{Inrush Current} = C_L \times dV_{OUT}/dt \quad (2)$$

Where:

- C_L is the output capacitance.
- dV_{OUT} is the change in V_{OUT} during the ramp up of the output voltage when device is enabled. Because rise time is 10% of V_{OUT} to 90% of V_{OUT} , this is 80% of the V_{IN} value.
- dt is the rise time in V_{OUT} during the ramp up of the output voltage when the device is enabled.

The TPS22997 offers an adjustable rise time for V_{OUT} , allowing the user to control the inrush current during turn on. Calculate the appropriate rise time using the design requirements and the inrush current equation as shown below.

$$1.5 \text{ A} = 220 \mu\text{F} \times (5.0 \text{ V} \times 80\%) / dt \quad (3)$$

$$dt = 586 \mu\text{s} \quad (4)$$

To ensure an inrush current of less than 1.5 A, a C_T setting that yields a rise time of more than 586 μs must be chosen. By using a 1000pF capacitance, a rise time of 819 μs is selected, limiting the inrush current to below 1.5 A.

9.2.3 Application Performance Plots




图 9-2. Inrush Current for $C_L = 220 \mu\text{F}$ with $C_T = 1000 \text{ pF}$




图 9-3. PG Pin Behavior with Inrush Current for $C_L = 220 \mu\text{F}$ with $C_T = 1000 \text{ pF}$

9.3 Power Supply Recommendations

The TPS22997 device is designed to operate with a V_{IN} range of 0.1 V to 5.5 V. Regulate the V_{IN} power supply well. The power supply must be able to withstand all transient load current steps. In most situations, using an input capacitance (C_{IN}) of 1 μF is sufficient to prevent the supply voltage from dipping when the switch is turned on. In cases where the power supply is slow to respond to a large transient current or large load current step, additional bulk capacitance can be required on the input.

A capacitor (C_{BIAS}) is recommended to be placed as close to the device as possible to stabilize the supply and filter out low frequency noise.

9.4 Layout

9.4.1 Layout Guidelines

For best performance, all traces must be as short as possible. To be most effective, place the input and output capacitors close to the device to minimize the effects that parasitic trace inductances can have on normal operation. Using wide traces for VIN, VOUT, and GND helps minimize the parasitic electrical effects.

9.4.2 Layout Example




图 9-4. TPS22997 Layout Example

10 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

10.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [订阅更新](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

10.2 支持资源

[TI E2E™ 支持论坛](#) 是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [《使用条款》](#)。

10.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

10.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

10.5 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPS22997RYZR	Active	Production	WQFN-HR (RYZ) 10	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	102
TPS22997RYZR.A	Active	Production	WQFN-HR (RYZ) 10	3000 LARGE T&R	Yes	SN	Level-1-260C-UNLIM	-40 to 125	102

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

RYZ0010A



PACKAGE OUTLINE
WQFN-HR - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



4226834/B 06/2021

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

EXAMPLE BOARD LAYOUT


RYZ0010A

WQFN-HR - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:30X



SOLDER MASK DETAILS
NOT TO SCALE

4226834/B 06/2021

NOTES: (continued)


3. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

EXAMPLE STENCIL DESIGN

RYZ0010A

WQFN-HR - 0.8 mm max height

PLASTIC QUAD FLATPACK - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.1 mm THICKNESS
SCALE: 30X

4226834/B 06/2021

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月