

TS5A3359 1Ω SP3T 双向模拟开关

5V/3.3V 单通道 3:1 多路复用器和多路解复用器

1 特性

- 断电模式隔离, $V_{CC} = 0$
- 指定的先断后合开关
- 低导通电阻 ($1\ \Omega$)
- 控制输入为 5.5V 耐压
- 低电荷注入 ($5\ \text{pC}$ $V_{CC} = 1.8\text{V}$)
- 出色的导通状态电阻匹配
- 低总谐波失真 (THD)
- 1.65V 至 5.5V 单电源运行
- 闩锁性能超过 100 mA, 符合 JESD 78 II 类规范
- ESD 性能经测试符合 JESD 22 规范
 - 2000V 人体放电模型 (A114-B, II 类)
 - 1000V 充电器件模型 (C101)

2 应用

- 手机
- PDA
- 便携式仪表
- 音频和视频信号路由
- 低电压数据采集系统
- 通信电路
- 调制解调器
- 硬盘
- 计算机外设
- 无线终端和外设


3 说明

TS5A3359 器件是一款工作电压范围为 1.65V 至 5.5V 的双向、单通道、单刀三掷 (SP3T) 模拟开关。TS5A3359 器件提供信号切换解决方案, 同时保持出色的信号完整性, 因此适用于各种市场中的广泛应用, 包括个人电子产品、测试和测量设备以及便携式仪器。该器件拥有低导通电阻、出色的导通状态电阻匹配以及最小总谐波失真 (THD) 性能, 可维持信号完整性。TS5A3359 器件还具有指定的先断后合特性, 可防止信号在跨通道传输时出现失真。该器件能耗超低, 可在 $V_{CC} = 0$ 时提供隔离。

器件信息⁽¹⁾

器件型号	封装	封装尺寸 (标称值)
TS5A3359	US8 (8)	2.30mm × 2.00mm
	DSBGA (8)	1.25mm × 2.25mm

(1) 如需了解所有可用封装, 请参阅数据表末尾的可订购产品附录。



简化版原理图



Table of Contents

1 特性	1	8.2 Functional Block Diagram	23
2 应用	1	8.3 Feature Description	23
3 说明	1	8.4 Device Functional Modes	23
4 Revision History	2	9 Application and Implementation	24
5 Pin Configuration and Functions	3	9.1 Application Information.....	24
6 Specifications	4	9.2 Typical Application.....	24
6.1 Absolute Maximum Ratings.....	4	10 Power Supply Recommendations	25
6.2 ESD Ratings.....	4	11 Layout	26
6.3 Recommended Operating Conditions.....	4	11.1 Layout Guidelines.....	26
6.4 Thermal Information.....	5	11.2 Layout Example.....	26
6.5 Electrical Characteristics for 5-V Supply.....	5	12 Device and Documentation Support	27
6.6 Electrical Characteristics for 3.3-V Supply.....	8	12.1 接收文档更新通知.....	27
6.7 Electrical Characteristics for 2.5-V Supply.....	10	12.2 支持资源.....	27
6.8 Electrical Characteristics for 1.8-V Supply.....	12	12.3 Trademarks.....	27
6.9 Typical Characteristics.....	14	12.4 Electrostatic Discharge Caution.....	27
7 Parameter Measurement Information	17	12.5 术语表.....	27
8 Detailed Description	23	13 Mechanical, Packaging, and Orderable Information	27
8.1 Overview.....	23		

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision E (January 2016) to Revision F (December 2021)	Page
• 更新了整个文档的表、图和交叉参考的编号格式.....	1
• 更新了器件信息表中 DSBGA (8) 封装的封装尺寸.....	1
Changes from Revision D (May 2015) to Revision E (January 2016)	Page
• Added T _J Junction Temperature to the <i>Absolute Maximum Ratings</i>	4
• Changed Input leakage current UNIT value From: μ A To: nA in <i>Electrical Characteristics for 5-V Supply</i>	5
Changes from Revision C (June 2008) to Revision D (May 2015)	Page
• 添加了 ESD 等级表、特性说明部分、器件功能模式、应用和实施部分、电源相关建议部分、布局部分、器件和文档支持部分以及机械、封装和可订购信息部分.....	1
• Changed YZP pinout numbering.....	3

5 Pin Configuration and Functions




图 5-1. YZP Package 8-Pin DSBGA Bottom View




图 5-2. DCU Package 8-Pin US8 Top View

表 5-1. Pin Functions

PIN			TYPE ⁽¹⁾	DESCRIPTION
NAME	DCU	YZP		
NO0	1	A1	I/O	Normally open
NO1	2	B1	I/O	Normally open
NO2	3	C1	I/O	Normally open
GND	4	D1	—	Ground
IN2	5	D2	I	Digital control to connect COM to NO
IN1	6	C2	I	Digital control to connect COM to NO
COM	7	B2	I/O	Common
VCC	8	A2	—	Power supply

(1) I = input, O = output.

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)^{(1) (2)}

			MIN	MAX	UNIT
V _{CC}	Supply voltage ⁽³⁾		- 0.5	6.5	V
V _{NO} V _{COM}	Analog voltage ^{(3) (4) (5)}		- 0.5	V _{CC} + 0.5	V
I _K	Analog port diode current	V _{NO} , V _{COM} < 0	- 50		mA
I _{NO} I _{COM}	On-state switch current	V _{NO} , V _{COM} = 0 to V _{CC}	- 200 - 400	200 400	mA
V _I	Digital input voltage ^{(3) (4)}		- 0.5	6.5	V
I _{IK}	Digital input clamp current	V _I < 0	- 50		mA
I _{CC}	Continuous current through V _{CC}		100		mA
I _{GND}	Continuous current through GND		- 100	100	mA
T _{stg}	Storage temperature		- 65	150	°C
T _J	Junction temperature		150		°C

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum
- (3) All voltages are with respect to ground, unless otherwise specified.
- (4) The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
- (5) This value is limited to 5.5-V maximum.

6.2 ESD Ratings

		VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾	±2000
		Charged device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾	±1000

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V_{CC}	Analog voltage	1.65	5.5	V
V_{NO} V_{COM}		0	V_{CC}	V
V_I	Digital input voltage	0	V_{CC}	V

6.4 Thermal Information

THERMAL METRIC ⁽¹⁾		TS5A3359		UNIT
		DCU (US8)	YZP (DSBGA)	
		8 PINS	8 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	204.2	105.8	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	76.2	1.6	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	82.9	10.8	°C/W
ψ_{JT}	Junction-to-top characterization parameter	7.6	3.1	°C/W
ψ_{JB}	Junction-to-board characterization parameter	82.5	10.8	°C/W

(1) For more information about traditional and new thermal metrics, see the *Semiconductor and IC Package Thermal Metrics* application report, [SPRA953](#).

6.5 Electrical Characteristics for 5-V Supply

$V_{CC} = 4.5\text{ V to }5.5\text{ V}$, $T_A = -40^{\circ}\text{C to }85^{\circ}\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER	TEST CONDITIONS	T_A	V_{CC}	MIN	TYP	MAX	UNIT
ANALOG SWITCH							
Analog signal range	V_{COM}, V_{NO}			0		V_{CC}	V
Peak ON resistance	r_{peak}	$0 \leq (V_{NO}) \leq V_{CC}$, $I_{COM} = -100\text{ mA}$, Switch ON, See 图 7-1	25°C Full	4.5 V	0.8	1.1 1.5	Ω
ON-state resistance	r_{on}	$V_{NO} = 2.5\text{ V}$, $I_{COM} = -100\text{ mA}$, Switch ON, See 图 7-1	25°C Full	4.5 V	0.7	0.9 1.1	Ω
ON-state resistance match between channels	Δr_{on}	$V_{NO} = 2.5\text{ V}$, $I_{COM} = -100\text{ mA}$, Switch ON, See 图 7-1	25°C Full	4.5 V	0.1	0.1 0.1	Ω
ON-state resistance flatness	$r_{on(flat)}$	$0 \leq (V_{NO}) \leq V_{CC}$, $I_{COM} = -100\text{ mA}$, $V_{NO} = 1\text{ V}, 1.5\text{ V}, 2.5\text{ V}$, $I_{COM} = -100\text{ mA}$, Switch ON, See 图 7-1	25°C Full	4.5 V	0.15	0.1 0.25 0.25	Ω
NO OFF leakage current	$I_{NO(OFF)}$	$V_{NO} = 1\text{ V or }4.5\text{ V}$, $V_{COM} = 1\text{ V to }4.5\text{ V}$, Switch OFF, See 图 7-2	25°C Full	5.5 V	-20	5 150	nA
	$I_{NO(PWROFF)}$	$V_{NO} = 0\text{ to }5.5\text{ V}$, $V_{COM} = 5.5\text{ V to }0$, Switch OFF, See 图 7-2	25°C Full	0 V	-1	0.8 25	$\mu\text{ A}$
NO ON leakage current	$I_{NO(ON)}$	$V_{NO} = 1\text{ V or }4.5\text{ V}$, $V_{COM} = \text{Open}$, Switch ON, See 图 7-2	25°C Full	5.5 V	-30	5 220	nA
COM OFF leakage current	$I_{COM(OFF)}$	$V_{NO} = 4.5\text{ V or }1\text{ V}$, $V_{COM} = 1\text{ V or }4.5\text{ V}$, Switch OFF, See 图 7-2	25°C Full	5.5 V	-25	8 250	nA
	$I_{COM(PWROFF)}$	$V_{COM} = 0\text{ to }5.5\text{ V}$, $V_{NO} = 5.5\text{ V to }0$, Switch OFF, See 图 7-2	25°C Full	0 V	-8	0.1 50	$\mu\text{ A}$
COM ON leakage current	$I_{COM(ON)}$	$V_{NO} = \text{Open}$, $V_{COM} = 1\text{ V or }4.5\text{ V}$, Switch ON, See 图 7-2	25°C Full	5.5 V	-30	5 220	nA
DIGITAL CONTROL INPUTS (IN1, IN2)⁽²⁾							
Input logic high	V_{IH}		Full		2.4	5.5	V
Input logic low	V_{IL}		Full		0	0.8	V

6.5 Electrical Characteristics for 5-V Supply (continued)

$V_{CC} = 4.5\text{ V to }5.5\text{ V}$, $T_A = -40^{\circ}\text{C to }85^{\circ}\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER	TEST CONDITIONS	T_A	V_{CC}	MIN	TYP	MAX	UNIT
Input leakage current I_{IH}, I_{IL}	$V_I = 5.5\text{ V or }0$	25°C	5.5 V	- 2		2	nA
		Full		- 20		20	

6.5 Electrical Characteristics for 5-V Supply (continued)

$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$, $T_A = -40^\circ\text{C to } 85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
DYNAMIC									
Turnon time	t _{ON}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	5 V	1	2.5	21	ns
				Full	4.5 V to 5.5 V	1		23.5	
Turnoff time	t _{OFF}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	5 V	1	6	10.5	ns
				Full	4.5 V to 5.5 V	1		12	
Break-before-make time	t _{BBM}	V _{NO} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-6	25°C	5 V	0.5	8.5	18	ns
				Full	4.5 V to 5.5 V	0.5		23	
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See 图 7-10	25°C	5 V		20		pC
NO OFF capacitance	C _{NO(OFF)}	V _{NO} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	5 V		18		pF
COM OFF capacitance	C _{COM(OFF)}	V _{COM} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	2.5 V		54		pF
NO ON capacitance	C _{NO(ON)}	V _{NO} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	5 V		78		pF
COM ON capacitance	C _{COM(ON)}	V _{COM} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	5 V		78		pF
Digital input capacitance	C _I	V _I = V _{CC} or GND,	See 图 7-4	25°C	5 V		2.5		pF
Bandwidth	BW	R _L = 50 Ω, Switch ON,	See 图 7-7	25°C	5 V		75		MHz
OFF isolation	O _{ISO}	R _L = 50 Ω, f = 1 MHz ,	Switch OFF, See 图 7-8	25°C	5 V		– 64		dB
Crosstalk	X _{TALK}	R _L = 50 Ω, f = 1 MHz ,	Switch ON, See 图 7-9	25°C	5 V		– 64		dB
Total harmonic distortion	THD	R _L = 600 Ω, C _L = 50 pF,	f = 20 Hz to 20 kHz, See 图 7-11	25°C	5 V		0.005%		
SUPPLY									
Positive supply current	I _{CC}	V _I = V _{CC} or GND,	Switch ON or OFF	25°C	5.5 V		16	50	nA
				Full				1200	

- (1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum
- (2) All unused digital inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs* ([SCBA004](#)).

6.6 Electrical Characteristics for 3.3-V Supply

$V_{CC} = 3\text{ V to }3.6\text{ V}$, $T_A = -40^\circ\text{C to }85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
ANALOG SWITCH									
Analog signal range	V _{COM} , V _{NO}					0		V _{CC}	V
Peak ON resistance	r _{peak}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = - 100 mA,	Switch ON, See 图 7-1	25°C	3 V	1.3		1.6	Ω
				Full		2			
ON-state resistance	r _{on}	V _{NO} = 2 V, I _{COM} = - 100 mA,	Switch ON, See 图 7-1	25°C	3 V	1.2		1.6	Ω
				Full		1.8			
ON-state resistance match between channels	Δ r _{on}	V _{NO} = 2 V, 0.8 V, I _{COM} = - 100 mA,	Switch ON, See 图 7-1	25°C	3 V	0.1		0.15	Ω
				Full		0.15			
ON-state resistance flatness	r _{on(flat)}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = - 100 mA,	Switch ON, See 图 7-1	25°C	3 V	0.2			Ω
		V _{NO} = 2 V, 0.8 V, I _{COM} = - 100 mA,	Switch ON, See 图 7-1	25°C		0.2		0.35	
				Full		0.35			
NO OFF leakage current	I _{NO(OFF)}	V _{NO} = 1 V or 3 V, V _{COM} = 1 V to 3 V,	Switch OFF, See 图 7-2	25°C	3.6 V	- 15	3	15	nA
				Full		- 30		30	
	I _{NO(PWROFF)}	V _{NO} = 0 to 3.6 V, V _{COM} = 3.6 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	- 1	0.2	1	μ A
				Full		- 10		10	
NO ON leakage current	I _{NO(ON)}	V _{NO} = 1 V or 3 V, V _{COM} = Open,	Switch ON, See 图 7-2	25°C	3.6 V	- 15	3	15	nA
				Full		- 40		40	
COM OFF leakage current	I _{COM(OFF)}	V _{NO} = 0 V to 3.6 V, V _{COM} = 1 V or V _{NO} = 3.6 V to 0, V _{COM} = 3 V,	Switch OFF, See 图 7-2	25°C	3.6 V	- 15	3	15	nA
				Full		- 75		75	
	I _{COM(PWROFF)}	V _{COM} = 0 to 3.6 V, V _{NO} = 3.6 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	- 1	0.2	1	μ A
				Full		- 20		20	
COM ON leakage current	I _{COM(ON)}	V _{NO} = Open, V _{COM} = 1 V or 3 V,	Switch ON, See 图 7-2	25°C	3.6 V	- 15	4	15	nA
				Full		- 40		40	
DIGITAL CONTROL INPUTS (IN1, IN2) ⁽²⁾									
Input logic high	V _{IH}			Full		2		5.5	V
Input logic low	V _{IL}			Full		0		0.8	V
Input leakage current	I _{IH} , I _{IL}	V _I = 5.5 V or 0		25°C	3.6 V	- 2		2	nA
				Full		- 20		20	

6.6 Electrical Characteristics for 3.3-V Supply (continued)

$V_{CC} = 3\text{ V to }3.6\text{ V}$, $T_A = -40^\circ\text{C to }85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
DYNAMIC									
Turnon time	t _{ON}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	3.3 V	1	16	30.5	ns
				Full	3 V to 3.6 V	1		34	
Turnoff time	t _{OFF}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	3.3 V	1	6	11.5	ns
				Full	3 V to 3.6 V	1		12.5	
Break-before-make time	t _{BBM}	V _{NO} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-6	25°C	3.3 V	0.5	13	26	ns
				Full	3 V to 3.6 V	0.5		30	
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See 图 7-10	25°C	3.3 V		12		pC
NO OFF capacitance	C _{NO(OFF)}	V _{NO} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	3.3 V		18		pF
COM OFF capacitance	C _{COM(OFF)}	V _{COM} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	3.3 V		55		pF
NO ON capacitance	C _{NO(ON)}	V _{NO} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	3.3 V		78		pF
COM ON capacitance	C _{COM(ON)}	V _{COM} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	3.3 V		78		pF
Digital input capacitance	C _I	V _I = V _{CC} or GND,	See 图 7-4	25°C	3.3 V		2.5		pF
Bandwidth	BW	R _L = 50 Ω, Switch ON,	See 图 7-7	25°C	3.3 V		73		MHz
OFF isolation	O _{ISO}	R _L = 50 Ω, f = 1 MHz,	Switch OFF, See 图 7-8	25°C	3.3 V		- 64		dB
Crosstalk	X _{TALK}	R _L = 50 Ω, f = 1 MHz,	Switch ON, See 图 7-9	25°C	3.3 V		- 64		dB
Total harmonic distortion	THD	R _L = 600 Ω, C _L = 50 pF,	f = 20 Hz to 20 kHz, See 图 7-11	25°C	3.3 V		0.01%		
SUPPLY									
Positive supply current	I _{CC}	V _I = V _{CC} or GND,	Switch ON or OFF	25°C	3.6 V		2	20	nA
				Full				350	

- (1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum
 (2) All unused digital inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs* ([SCBA004](#)).

6.7 Electrical Characteristics for 2.5-V Supply

$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$, $T_A = -40^\circ\text{C to } 85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
ANALOG SWITCH									
Analog signal range	V _{COM} , V _{NO}					0		V _{CC}	V
Peak ON resistance	r _{peak}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = − 8 mA,	Switch ON, See 图 7-1	25°C	2.3 V	1.8		2.5	Ω
				Full		2.7			
ON-state resistance	r _{on}	V _{NO} = 1.8 V, I _{COM} = − 8 mA,	Switch ON, See 图 7-1	25°C	2.3 V	1.5		2	Ω
				Full		2.4			
ON-state resistance match between channels	Δ r _{on}	V _{NO} = 1.8 V, I _{COM} = − 8 mA,	Switch ON, See 图 7-1	25°C	2.3 V			0.2	Ω
				Full				0.2	
ON-state resistance flatness	r _{on(flat)}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = − 8 mA,	Switch ON, See 图 7-1	25°C	2.3 V	0.6			Ω
				25°C		0.6		1	
				Full				1	
NO OFF leakage current	I _{NO(OFF)}	V _{NO} = 0.5 V or 2.3 V, V _{COM} = 0.5 V to 2.3 V,	Switch OFF, See 图 7-2	25°C	2.7 V	− 15	3	15	nA
				Full		− 30		30	
	I _{NO(PWROFF)}	V _{NO} = 0 to 2.7 V, V _{COM} = 2.7 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	− 1	0.1	1	μ A
				Full		− 10		10	
NO ON leakage current	I _{NO(ON)}	V _{NO} = 0.5 V or 2.3 V, V _{COM} = Open,	Switch ON, See 图 7-2	25°C	2.7 V	− 15	3	15	nA
				Full		− 35		35	
COM OFF leakage current	I _{COM(OFF)}	V _{NO} = 0.3 V to 2.3 V, V _{COM} = 0.5 V or 2.3 V,	Switch OFF, See 图 7-2	25°C	2.7 V	− 15	3	15	nA
				Full		− 60		60	
	I _{COM(PWROFF)}	V _{COM} = 0 to 2.7 V, V _{NO} = 2.7 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	− 1	0.1	1	μ A
				Full		− 10		10	
COM ON leakage current	I _{COM(ON)}	V _{NO} = Open, V _{COM} = 0.5 V or 2.2 V,	Switch ON, See 图 7-2	25°C	2.7 V	− 15	3.5	15	nA
				Full		− 40		40	
DIGITAL CONTROL INPUTS (IN1, IN2) ⁽²⁾									
Input logic high	V _{IH}			Full		1.8		5.5	V
Input logic low	V _{IL}			Full		0		0.6	V
Input leakage current	I _{IH} , I _{IL}	V _I = 5.5 V or 0		25°C	2.7 V	1		1	nA
				Full		10		10	

6.7 Electrical Characteristics for 2.5-V Supply (continued)

$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$, $T_A = -40^\circ\text{C to } 85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
DYNAMIC									
Turnon time	t _{ON}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	2.5 V	2	4.5	43	ns
				Full	2.3 V to 2.7 V	2		47.5	
Turnoff time	t _{OFF}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	2.5 V	2	8.5	11	ns
				Full	2.3 V to 2.7 V	2		12.5	
Break-before-make time	t _{BBM}	V _{NO} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-6	25°C	2.5 V	0.5	18.5	38.5	ns
				Full	2.3 V to 2.7 V	0.5		43	
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See 图 7-10	25°C	2.5 V		8		pC
NO OFF capacitance	C _{NO(OFF)}	V _{NO} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	2.5 V		18.5		pF
COM OFF capacitance	C _{COM(OFF)}	V _{COM} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	2.5 V		55		pF
NO ON capacitance	C _{NO(ON)}	V _{NO} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	2.5 V		78		pF
COM ON capacitance	C _{COM(ON)}	V _{COM} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	2.5 V		78		pF
Digital input capacitance	C _I	V _I = V _{CC} or GND,	See 图 7-4	25°C	2.5 V		3		pF
Bandwidth	BW	R _L = 50 Ω, Switch ON,	See 图 7-7	25°C	2.5 V		73		MHz
OFF isolation	O _{ISO}	R _L = 50 Ω, f = 1 MHz,	Switch OFF, See 图 7-8	25°C	2.5 V		- 64		dB
Crosstalk	X _{TALK}	R _L = 50 Ω, f = 1 MHz,	Switch ON, See 图 7-9	25°C	2.5 V		- 64		dB
Total harmonic distortion	THD	R _L = 600 Ω, C _L = 50 pF,	f = 20 Hz to 20 kHz, See 图 7-11	25°C	2.5 V		0.03%		
SUPPLY									
Positive supply current	I _{CC}	V _I = V _{CC} or GND,	Switch ON or OFF	25°C	2.7 V		1	10	nA
				Full				250	

- (1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum
 (2) All unused digital inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs* (SCBA004).

6.8 Electrical Characteristics for 1.8-V Supply

$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$, $T_A = -40^\circ\text{C to } 85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
ANALOG SWITCH									
Analog signal range	V _{COM} , V _{NO}					0		V _{CC}	V
Peak ON resistance	r _{peak}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = − 2 mA,	Switch ON, See 图 7-1	25°C	1.65 V	5		30	Ω
				Full					
ON-state resistance	r _{on}	V _{NO} = 1.5 V, I _{COM} = − 2 mA,	Switch ON, See 图 7-1	25°C	1.65 V	2		2.5	Ω
				Full		3.5			
ON-state resistance match between channels	Δ r _{on}	V _{NO} = 1.5 V, I _{COM} = − 2 mA,	Switch ON, See 图 7-1	25°C	1.65 V	0.15		0.4	Ω
				Full		0.4			
ON-state resistance flatness	r _{on(flat)}	0 ≤ (V _{NO}) ≤ V _{CC} , I _{COM} = − 2 mA,	Switch ON, See 图 7-1	25°C	1.65 V	5			Ω
				25°C		4.5			
				Full		5			
NO OFF leakage current	I _{NO(OFF)}	V _{NO} =0.3 V or 1.65 V, V _{COM} = 0.3 V to 1.65 V,	Switch OFF, See 图 7-2	25°C	1.95 V	− 15	3	15	nA
				Full		− 30		30	
	I _{NO(PWROFF)}	V _{NO} = 0 to 1.95 V, V _{COM} = 1.95 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	− 1	0.1	1	μ A
				Full		− 15		15	
NO ON leakage current	I _{NO(ON)}	V _{NO} =0.3 V or 1.65 V, V _{COM} = Open,	Switch ON, See 图 7-2	25°C	1.95 V	− 15	3	15	nA
				Full		− 30		30	
COM OFF leakage current	I _{COM(OFF)}	V _{NO} = 0.3 V to 1.65 V, V _{COM} =0.3 V or 1.65 V,	Switch OFF, See 图 7-2	25°C	1.95 V	− 15	3	15	nA
				Full		− 50		50	
	I _{COM(PWROFF)}	V _{COM} = 0 to 1.95 V, V _{NO} = 1.95 V to 0,	Switch OFF, See 图 7-2	25°C	0 V	− 1	0.1	1	μ A
				Full		− 10		10	
COM ON leakage current	I _{COM(ON)}	V _{NO} = Open, V _{COM} = 0.3 V or 1.65 V,	Switch ON, See 图 7-2	25°C	1.95 V	− 15	3	15	nA
				Full		− 30		30	
DIGITAL CONTROL INPUTS (IN1, IN2) ⁽²⁾									
Input logic high	V _{IH}			Full		1.5		5.5	V
Input logic low	V _{IL}			Full		0		0.6	V
Input leakage current	I _{IH} , I _{IL}	V _I = 5.5 V or 0		25°C	1.95 V	− 2		2	nA
				Full		− 20		20	







6.8 Electrical Characteristics for 1.8-V Supply (continued)

 $V_{CC} = 1.65\text{ V to }1.95\text{ V}$, $T_A = -40^\circ\text{C to }85^\circ\text{C}$ (unless otherwise noted)⁽¹⁾

PARAMETER		TEST CONDITIONS		T _A	V _{CC}	MIN	TYP	MAX	UNIT
DYNAMIC									
Turnon time	t _{ON}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	1.8 V	3	38.5	85	ns
				Full	1.65 V to 1.95 V	3		90	
Turnoff time	t _{OFF}	V _{COM} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-5	25°C	1.8 V	2	8.5	16	ns
				Full	1.65 V to 1.95 V	2		18	
Break-before-make time	t _{BBM}	V _{NO} = V _{CC} , R _L = 50 Ω,	C _L = 35 pF, See 图 7-6	25°C	1.8 V	1	33	75	ns
				Full	1.65 V to 1.95 V	1		80	
Charge injection	Q _C	V _{GEN} = 0, R _{GEN} = 0,	C _L = 1 nF, See 图 7-10	25°C	1.8 V		5		pC
NO OFF capacitance	C _{NO(OFF)}	V _{NO} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	1.8 V		18.5		pF
COM OFF capacitance	C _{COM(OFF)}	V _{COM} = V _{CC} or GND, Switch OFF,	See 图 7-4	25°C	1.8 V		55		pF
NO ON capacitance	C _{NO(ON)}	V _{NO} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	1.8 V		78		pF
COM ON capacitance	C _{COM(ON)}	V _{COM} = V _{CC} or GND, Switch ON,	See 图 7-4	25°C	1.8 V		78		pF
Digital input capacitance	C _I	V _I = V _{CC} or GND,	See 图 7-4	25°C	1.8 V		3		pF
Bandwidth	BW	R _L = 50 Ω, Switch ON,	See 图 7-7	25°C	1.8 V		73		MHz
OFF isolation	O _{ISO}	R _L = 50 Ω, f = 1 M Hz ,	Switch OFF, See 图 7-8	25°C	1.8 V		- 64		dB
Crosstalk	X _{TALK}	R _L = 50 Ω, f = 1 MHz,	Switch ON, See 图 7-9	25°C	1.8 V		- 64		dB
Total harmonic distortion	THD	R _L = 600 Ω, C _L = 50 pF,	f = 20 Hz to 20 kHz, See 图 7-11	25°C	1.8 V		0.08%		
SUPPLY									
Positive supply current	I _{CC}	V _I = V _{CC} or GND,	Switch ON or OFF	25°C	1.95 V		1		nA
				Full				200	

- (1) The algebraic convention, whereby the most negative value is a minimum and the most positive value is a maximum
- (2) All unused digital inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, [SCBA004](#).

6.9 Typical Characteristics

图 6-1. R_{on} vs V_{COM} 图 6-2. R_{on} vs V_{COM} Over Temperature ($V_{CC} = 3.3$ V)图 6-3. R_{on} vs V_{COM} Over Temperature ($V_{CC} = 5$ V)图 6-4. $I_{COM(OFF)}$ Leakage Current vs V_{COM} Over Temperature ($V_{CC} = 5$ V)图 6-5. $I_{NO(OFF)}$ Leakage Current vs V_{COM} Over Temperature ($V_{CC} = 5$ V)图 6-6. $I_{COM(ON)}$ Leakage Current vs V_{COM} Over Temperature ($V_{CC} = 5$ V)

6.9 Typical Characteristics (continued)




图 6-7. $I_{COM(PWROFF)}$ Leakage Current vs V_{COM} Over Temperature ($V_{CC} = 0$ V)




图 6-8. Charge Injection (Q_C) vs V_{COM}




图 6-9. t_{ON} and t_{OFF} vs Supply Voltage




图 6-10. T_{ON} and T_{OFF} vs Temperature




图 6-11. Logic-Level Threshold vs V_{CC}









图 6-12. Bandwidth ($V_{CC} = 5$ V)

6.9 Typical Characteristics (continued)

图 6-13. Off Isolation ($V_{CC} = 5\text{ V}$)图 6-14. Total Harmonic Distortion vs Frequency ($V_{CC} = 5\text{ V}$)图 6-15. Com Port to No2 PSRR, $In1 = V_{CC}$, $In2 = V_{CC}$ ($V_{CC} = 5\text{ V}$)图 6-16. Com Port to No0 PSRR, $In1 = V_{CC}$, $In2 = V_{CC}$ ($V_{CC} = 5\text{ V}$)图 6-17. Com Port Hi-Z PSRR, $In1 = 0\text{ V}$, $In2 = 0\text{ V}$ ($V_{CC} = 5\text{ V}$)

7 Parameter Measurement Information




图 7-1. ON-State Resistance (R_{on})




图 7-2. OFF-State Leakage Current ($I_{NC(OFF)}$, $I_{NO(OFF)}$, $I_{NO(PWROFF)}$, $I_{COM(OFF)}$, $I_{COM(PWROFF)}$)







图 7-3. ON-State Leakage Current ($I_{COM(ON)}$, $I_{NO(ON)}$)

图 7-4. Capacitance (C_I , $C_{COM(ON)}$, $C_{NO(OFF)}$, $C_{COM(OFF)}$, $C_{NO(ON)}$)

- A. All input pulses are supplied by generators having the following characteristics: $PRR \leq 10 \text{ MHz}$, $ZO = 50 \Omega$, $t_r < 5 \text{ ns}$, $t_f < 5 \text{ ns}$.
 B. C_L includes probe and jig capacitance.

图 7-5. Turnon (t_{ON}) and Turnoff Time (t_{OFF})

- A. All input pulses are supplied by generators having the following characteristics: $PRR \leq 10 \text{ MHz}$, $ZO = 50 \Omega$, $t_r < 5 \text{ ns}$, $t_f < 5 \text{ ns}$.
 B. C_L includes probe and jig capacitance.

图 7-6. Break-Before-Make Time (t_{BBM})




图 7-7. Bandwidth (BW)




图 7-8. Off Isolation (O_{ISO})






图 7-9. Crosstalk (X_{TALK})



- A. All input pulses are supplied by generators having the following characteristics: PRR $\leq 10 \text{ MHz}$, $Z_O = 50 \Omega$, $t_r < 5 \text{ ns}$, $t_f < 5 \text{ ns}$.
- B. C_L includes probe and jig capacitance.

图 7-10. Charge Injection (Q_C)

- A. C_L includes probe and jig capacitance.

图 7-11. Total Harmonic Distortion (THD)

表 7-1. Parameter Description

SYMBOL	DESCRIPTION
V_{COM}	Voltage at COM
V_{NO}	Voltage at NO
r_{on}	Resistance between COM and NC or COM and NO ports when the channel is ON
r_{peak}	Peak ON-state resistance over a specified voltage range
Δr_{on}	Difference of r_{on} between channels in a specific device
$r_{on(Flat)}$	Difference between the maximum and minimum value of r_{on} in a channel over the specified range of conditions
$I_{NO(OFF)}$	Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the OFF state
$I_{NO(PWROFF)}$	Leakage current measured at the NO port during the power-down condition, $V_{CC} = 0$.
$I_{NO(ON)}$	Leakage current measured at the NO port, with the corresponding channel (NO to COM) in the ON state and the output (COM) open
$I_{COM(ON)}$	Leakage current measured at the COM port, with the corresponding channel (COM to NO or COM to NC) in the ON state and the output (NC or NO) open
$I_{COM(OFF)}$	Leakage current measured at the COM port during the power-down condition, $V_{CC} = 0$
$I_{COM(PWROFF)}$	Leakage current measured at the COM port during the power-down condition, $V_{CC} = 0$.
V_{IH}	Minimum input voltage for logic high for the control input (IN)
V_{IL}	Maximum input voltage for logic low for the control input (IN)
V_I	Voltage at the control input (IN)
I_{IH}, I_{IL}	Leakage current measured at the control input (IN)
t_{ON}	Turnon time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning ON.
t_{OFF}	Turnoff time for the switch. This parameter is measured under the specified range of conditions and by the propagation delay between the digital control (IN) signal and analog output (COM or NO) signal when the switch is turning OFF.
t_{BBM}	Break-before-make time. This parameter is measured under the specified range of conditions and by the propagation delay between the output of two adjacent analog channels (NC and NO) when the control signal changes state.
Q_C	Charge injection is a measurement of unwanted signal coupling from the control (IN) input to the analog (NO or COM) output. This is measured in coulomb (C) and measured by the total charge induced due to switching of the control input. Charge injection, $Q_C = C_L \times \Delta V_{COM}$, C_L is the load capacitance and ΔV_{COM} is the change in analog output voltage.
$C_{NO(OFF)}$	Capacitance at the NO port when the corresponding channel (NO to COM) is OFF
$C_{NO(ON)}$	Capacitance at the NO port when the corresponding channel (NO to COM) is ON
$C_{COM(ON)}$	Capacitance at the COM port when the corresponding channel (COM to NO) is ON
$C_{COM(OFF)}$	Capacitance at the COM port when the corresponding channel (COM to NO) is OFF
C_I	Capacitance of control input (IN)
O_{ISO}	OFF isolation of the switch is a measurement of OFF-state switch impedance. This is measured in dB in a specific frequency, with the corresponding channel (NC to COM or NO to COM) in the OFF state.
X_{TALK}	Crosstalk is a measurement of unwanted signal coupling from an ON channel to an OFF channel (NC to NO or NO to NC). This is measured in a specific frequency and in dB.
BW	Bandwidth of the switch. This is the frequency in which the gain of an ON channel is - 3 dB less than the DC gain.
THD	Total harmonic distortion describes the signal distortion caused by the analog switch. This is defined as the ratio of root mean square (RMS) value of the second, third, and higher harmonic to the absolute magnitude of the fundamental harmonic.
I_{CC}	Static power-supply current with the control (IN) pin at V_{CC} or GND

表 7-2. Summary of Characteristics⁽¹⁾

PARAMETER	CHARACTERISTIC
Configuration	Triple 3:1 Multiplexer/ Demultiplexer (1 × SP3T)
Number of channels	1
ON-state resistance (r_{on})	1.1 Ω
ON-state resistance match (Δr_{on})	0.1 Ω
ON-state resistance flatness ($r_{on(flat)}$)	0.15 Ω
Turnon/turnoff time (t_{ON}/t_{OFF})	40 ns/35 ns
Break-before-make time (t_{BBM})	1 ns
Charge injection (Q_C)	40 pC
Bandwidth (BW)	100 MHz
OFF isolation (O_{ISO})	- 65 dB at 10 MHz
Crosstalk (X_{TALK})	- 66 dB at 10 MHz
Total harmonic distortion (THD)	0.01%
Leakage current ($I_{COM(OFF)}/I_{NO(OFF)}$)	$\pm 20 \mu A$
Power supply current (I_{CC})	0.1 μA
Package options	8-pin DCU or YZP


(1) $V_{CC} = 5 V$, $T_A = 25^\circ C$

8 Detailed Description

8.1 Overview

The TS5A3359 is a bidirectional, single-channel, single-pole triple-throw (SP3T) analog switch that is designed to operate from 1.65 V to 5.5 V. This device provides a signal switching solution while maintaining excellent signal integrity, which makes the TS5A3359 suitable for a wide range of applications in various markets including personal electronics, portable instrumentation, and test and measurement equipment. The device maintains the signal integrity by its low ON-state resistance, excellent ON-state resistance matching, and total harmonic distortion (THD) performance. To prevent signal distortion during the transferring of a signal from one channel to another, the TS5A3359 device also has a specified break-before-make feature. The device consumes very low power and provides isolation when $V_{CC} = 0$.

8.2 Functional Block Diagram



8.3 Feature Description

Isolation in Power-Down Mode, $V_{CC} = 0$

When power is not supplied to the VCC pin, $V_{CC} = 0$, the signal paths NO and COM are high impedance. This is specified in the electrical characteristics table under the COM and NO OFF leakage current when $V_{CC} = 0$. Because the device is high impedance when it is not powered, you may connect other signals to the signal chain without interference of the TS5A3359.

8.4 Device Functional Modes

表 8-1. Function Table

IN2	IN1	COM TO NO, NO TO COM
L	L	OFF
L	H	COM = NO0
H	L	COM = NO1
H	H	COM = NO2

9 Application and Implementation

备注

以下应用部分中的信息不属于 TI 器件规格的范围，TI 不担保其准确性和完整性。TI 的客户应负责确定器件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

9.1 Application Information

The TS5A3359 switch is bidirectional, so the NO and COM pins can be used as either inputs or outputs. This switch is typically used when there is only one signal path that needs to be able to communicate to 3 different signal paths.

9.2 Typical Application




图 9-1. Typical Application Schematic

9.2.1 Design Requirements

The TS5A3359 device can be properly operated without any external components. However, TI recommends connecting unused pins to ground through a 50-Ω resistor to prevent signal reflections back into the device. TI also recommends pulling up the digital control pins (IN1 and IN2) to VCC or pulling down to GND to avoid undesired switch positions that could result from the floating pin.

Select the appropriate supply voltage to cover the entire voltage swing of the signal passing through the switch because the TS5A3359 input and output signal swing through NO and COM are dependent on the supply voltage V_{CC} . For example, if the desired signal level to pass through the switch is 5 V, V_{CC} must be greater than or equal to 5 V. $V_{CC} = 3.3$ V would not be valid for passing a 5-V signal since the Analog signal voltage cannot exceed the supply.

9.2.2 Detailed Design Procedure

The TS5A3359 device can be properly operated without any external components. However, TI recommends connecting unused pins to ground through a 50- Ω resistor to prevent signal reflections back into the device. TI also recommends pulling up the digital control pins (IN1 and IN2) to VCC or pulling down to GND to avoid undesired switch positions that could result from the floating pin.

Select the appropriate supply voltage to cover the entire voltage swing of the signal passing through the switch because the TS5A3359 input/output signal swing through NO and COM are dependant of the supply voltage V_{CC} .

9.2.3 Application Curve




图 9-2. R_{on} vs V_{COM}

10 Power Supply Recommendations

TI recommends proper power-supply sequencing for all CMOS devices. Do not exceed the absolute maximum ratings, because stresses beyond the listed ratings can cause permanent damage to the device. Always sequence VCC on first, followed by NO or COM.

Although it is not required, power-supply bypassing improves noise margin and prevents switching noise propagation from the VCC supply to other components. A 0.1- μF capacitor, connected from VCC to GND, is adequate for most applications.

11 Layout

11.1 Layout Guidelines

TI recommends following common printed-circuit board layout guidelines to ensure reliability of the device.

- Bypass capacitors should be used on power supplies.
- Short trace lengths should be used to avoid excessive loading.

11.2 Layout Example




图 11-1. Recommended Layout

12 Device and Documentation Support

12.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [订阅更新](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

12.2 支持资源

[TI E2E™ 支持论坛](#) 是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《[使用条款](#)》。

12.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

12.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

12.5 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TS5A3359DCUR	Active	Production	VSSOP (DCU) 8	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	(AL, JALR) JZ
TS5A3359DCUR.B	Active	Production	VSSOP (DCU) 8	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	(AL, JALR) JZ
TS5A3359DCUR1G4	Active	Production	VSSOP (DCU) 8	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	JALR
TS5A3359DCUR1G4.B	Active	Production	VSSOP (DCU) 8	3000 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	JALR
TS5A3359DCUT	Obsolete	Production	VSSOP (DCU) 8	-	-	Call TI	Call TI	-40 to 85	(AL, JALR) JZ
TS5A3359YZPR	Active	Production	DSBGA (YZP) 8	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 85	J9
TS5A3359YZPR.B	Active	Production	DSBGA (YZP) 8	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-40 to 85	J9

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TS5A3359DCUR	VSSOP	DCU	8	3000	180.0	8.4	2.25	3.35	1.05	4.0	8.0	Q3
TS5A3359DCUR1G4	VSSOP	DCU	8	3000	180.0	8.4	2.25	3.35	1.05	4.0	8.0	Q3
TS5A3359YZPR	DSBGA	YZP	8	3000	180.0	8.4	1.02	2.02	0.63	4.0	8.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TS5A3359DCUR	VSSOP	DCU	8	3000	202.0	201.0	28.0
TS5A3359DCUR1G4	VSSOP	DCU	8	3000	202.0	201.0	28.0
TS5A3359YZPR	DSBGA	YZP	8	3000	210.0	185.0	35.0



4225266/A 09/2014

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-187 variation CA.

EXAMPLE BOARD LAYOUT


DCU0008A

VSSOP - 0.9 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 25X



4225266/A 09/2014

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.


6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DCU0008A

VSSOP - 0.9 mm max height

SMALL OUTLINE PACKAGE




SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE: 25X

4225266/A 09/2014

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.


YZP0008



PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



4223082/A 07/2016

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

EXAMPLE BOARD LAYOUT


YZP0008

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE
SCALE:40X



SOLDER MASK DETAILS
NOT TO SCALE

4223082/A 07/2016

NOTES: (continued)


- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 (www.ti.com/lit/snva009).

EXAMPLE STENCIL DESIGN

YZP0008

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE
BASED ON 0.1 mm THICK STENCIL
SCALE:40X

4223082/A 07/2016

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月