

## CDx4HC04 六路反相器

### 1 特性

- 缓冲输入
- 宽工作电压范围：2V 至 6V
- 宽工作温度范围：  
-55°C 至 +125°C
- 支持多达 10 个 LSTTL 负载的扇出
- 与 LSTTL 逻辑 IC 相比，可显著降低功耗

### 2 应用

- 同步反相时钟输入
- 对数字信号进行反相


### 3 说明

此器件包含六个独立的逆变器。每个逻辑门以正逻辑执行布尔函数  $Y = \overline{A}$ 。

#### 器件信息<sup>(1)</sup>

| 器件型号      | 封装        | 封装尺寸 (标称值)       |
|-----------|-----------|------------------|
| CD74HC04M | SOIC (14) | 8.70mm × 3.90mm  |
| CD74HC04E | PDIP (14) | 19.30mm × 6.40mm |
| CD54HC04F | CDIP (14) | 21.30mm × 7.60mm |

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。



功能引脚分配



## Table of Contents

|                                                  |          |                                                                  |           |
|--------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 特性</b> .....                                | <b>1</b> | 8.3 Feature Description.....                                     | <b>8</b>  |
| <b>2 应用</b> .....                                | <b>1</b> | 8.4 Device Functional Modes.....                                 | <b>9</b>  |
| <b>3 说明</b> .....                                | <b>1</b> | <b>9 Application and Implementation</b> .....                    | <b>10</b> |
| <b>4 Revision History</b> .....                  | <b>2</b> | 9.1 Application Information.....                                 | 10        |
| <b>5 Pin Configuration and Functions</b> .....   | <b>3</b> | 9.2 Typical Application.....                                     | 10        |
| Pin Functions.....                               | 3        | <b>10 Power Supply Recommendations</b> .....                     | <b>12</b> |
| <b>6 Specifications</b> .....                    | <b>4</b> | <b>11 Layout</b> .....                                           | <b>12</b> |
| 6.1 Absolute Maximum Ratings.....                | 4        | 11.1 Layout Guidelines.....                                      | 12        |
| 6.2 ESD Ratings.....                             | 4        | 11.2 Layout Example.....                                         | 12        |
| 6.3 Recommended Operating Conditions.....        | 4        | <b>12 Device and Documentation Support</b> .....                 | <b>13</b> |
| 6.4 Thermal Information.....                     | 5        | 12.1 Documentation Support.....                                  | 13        |
| 6.5 Electrical Characteristics.....              | 5        | 12.2 Related Links.....                                          | 13        |
| 6.6 Switching Characteristics.....               | 5        | 12.3 支持资源.....                                                   | 13        |
| 6.7 Operating Characteristics.....               | 6        | 12.4 Trademarks.....                                             | 13        |
| 6.8 Typical Characteristics.....                 | 6        | 12.5 静电放电警告.....                                                 | 13        |
| <b>7 Parameter Measurement Information</b> ..... | <b>7</b> | 12.6 术语表.....                                                    | 13        |
| <b>8 Detailed Description</b> .....              | <b>8</b> | <b>13 Mechanical, Packaging, and Orderable Information</b> ..... | <b>13</b> |
| 8.1 Overview.....                                | 8        |                                                                  |           |
| 8.2 Functional Block Diagram.....                | 8        |                                                                  |           |

## 4 Revision History

注：以前版本的页码可能与当前版本的页码不同

| <b>Changes from Revision E (June 2004) to Revision F (April 2021)</b>                      | <b>Page</b> |
|--------------------------------------------------------------------------------------------|-------------|
| • 更新了整个文档的表、图和交叉参考的编号格式.....                                                               | <b>1</b>    |
| • 更新至全新的数据表标准.....                                                                         | <b>1</b>    |
| • 将 HCT 器件移至单独的数据表 (SCHS401).....                                                          | <b>1</b>    |
| • $R_{\theta JA}$ increased for the D and PW packages and decreased for the N package..... | <b>5</b>    |

## 5 Pin Configuration and Functions




图 5-1. D, N, or J Package  
14-Pin SOIC, PDIP, or CDIP  
Top View

## Pin Functions

| PIN             |     | I/O    | DESCRIPTION         |
|-----------------|-----|--------|---------------------|
| NAME            | NO. |        |                     |
| 1A              | 1   | Input  | Channel 1, Input A  |
| 1Y              | 2   | Output | Channel 1, Output Y |
| 2A              | 3   | Input  | Channel 2, Input A  |
| 2Y              | 4   | Output | Channel 2, Output Y |
| 3A              | 5   | Input  | Channel 3, Input A  |
| 3Y              | 6   | Output | Channel 3, Output Y |
| GND             | 7   | —      | Ground              |
| 4Y              | 8   | Output | Channel 4, Output Y |
| 4A              | 9   | Input  | Channel 4, Input A  |
| 5Y              | 10  | Output | Channel 5, Output Y |
| 5A              | 11  | Input  | Channel 5, Input A  |
| 6Y              | 12  | Output | Channel 6, Output Y |
| 6A              | 13  | Input  | Channel 6, Input A  |
| V <sub>CC</sub> | 14  | —      | Positive Supply     |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                  |                                                   |                                                                      | MIN   | MAX | UNIT |
|------------------|---------------------------------------------------|----------------------------------------------------------------------|-------|-----|------|
| V <sub>CC</sub>  | Supply voltage                                    |                                                                      | - 0.5 | 7   | V    |
| I <sub>IK</sub>  | Input clamp current <sup>(2)</sup>                | V <sub>I</sub> < - 0.5 V or V <sub>I</sub> > V <sub>CC</sub> + 0.5 V |       | ±20 | mA   |
| I <sub>OK</sub>  | Output clamp current <sup>(2)</sup>               | V <sub>O</sub> < - 0.5 V or V <sub>O</sub> > V <sub>CC</sub> + 0.5 V |       | ±20 | mA   |
| I <sub>O</sub>   | Continuous output current                         | V <sub>O</sub> > - 0.5 V or V <sub>O</sub> < V <sub>CC</sub> + 0.5 V |       | ±25 | mA   |
|                  | Continuous current through V <sub>CC</sub> or GND |                                                                      |       | ±50 | mA   |
| T <sub>J</sub>   | Junction temperature <sup>(3)</sup>               | Plastic package                                                      |       | 150 | °C   |
|                  |                                                   | Hermetic package or die                                              |       | 175 |      |
|                  | Lead temperature (soldering 10s)                  | SOIC - lead tips only                                                |       | 300 | °C   |
| T <sub>stg</sub> | Storage temperature                               |                                                                      | - 65  | 150 | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Rating* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Condition*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) Guaranteed by design.

### 6.2 ESD Ratings

|                                                   |                         |                                                                                | VALUE | UNIT |
|---------------------------------------------------|-------------------------|--------------------------------------------------------------------------------|-------|------|
| <b>CD74HC04 IN D (SOIC) AND N (PDIP) PACKAGES</b> |                         |                                                                                |       |      |
| V <sub>(ESD)</sub>                                | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V    |
|                                                   |                         | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±500  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

|                 |                                |                         | MIN  | NOM | MAX             | UNIT |
|-----------------|--------------------------------|-------------------------|------|-----|-----------------|------|
| V <sub>CC</sub> | Supply voltage                 |                         | 2    | 5   | 6               | V    |
| V <sub>IH</sub> | High-level input voltage       | V <sub>CC</sub> = 2 V   | 1.5  |     |                 | V    |
|                 |                                | V <sub>CC</sub> = 4.5 V | 3.15 |     |                 |      |
|                 |                                | V <sub>CC</sub> = 6 V   | 4.2  |     |                 |      |
| V <sub>IL</sub> | Low-level input voltage        | V <sub>CC</sub> = 2 V   |      |     | 0.5             | V    |
|                 |                                | V <sub>CC</sub> = 4.5 V |      |     | 1.35            |      |
|                 |                                | V <sub>CC</sub> = 6 V   |      |     | 1.8             |      |
| V <sub>I</sub>  | Input voltage                  |                         | 0    |     | V <sub>CC</sub> | V    |
| V <sub>O</sub>  | Output voltage                 |                         | 0    |     | V <sub>CC</sub> | V    |
| t <sub>i</sub>  | Input transition time          | V <sub>CC</sub> = 2 V   |      |     | 1000            | ns   |
|                 |                                | V <sub>CC</sub> = 4.5 V |      |     | 500             |      |
|                 |                                | V <sub>CC</sub> = 6 V   |      |     | 400             |      |
| T <sub>A</sub>  | Operating free-air temperature |                         | - 55 |     | 125             | °C   |

## 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | CD74HC04   |          |          | UNIT |
|-------------------------------|----------------------------------------------|------------|----------|----------|------|
|                               |                                              | PW (TSSOP) | N (PDIP) | D (SOIC) |      |
|                               |                                              | 14 PINS    | 14 PINS  | 14 PINS  |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 151.7      | 69.3     | 133.6    | °C/W |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 79.4       | 57.4     | 89.0     | °C/W |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 94.7       | 49.0     | 89.5     | °C/W |
| $\Psi_{JT}$                   | Junction-to-top characterization parameter   | 25.2       | 37.4     | 45.5     | °C/W |
| $\Psi_{JB}$                   | Junction-to-board characterization parameter | 94.1       | 48.8     | 89.1     | °C/W |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | N/A        | N/A      | N/A      | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 6.5 Electrical Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| PARAMETER       |                           | TEST CONDITIONS                                     |                           | V <sub>CC</sub>            | Operating free-air temperature (T <sub>A</sub> ) |      |     |                |      |     |                 |      |     | UNIT |     |
|-----------------|---------------------------|-----------------------------------------------------|---------------------------|----------------------------|--------------------------------------------------|------|-----|----------------|------|-----|-----------------|------|-----|------|-----|
|                 |                           |                                                     |                           |                            | 25°C                                             |      |     | – 40°C to 85°C |      |     | – 55°C to 125°C |      |     |      |     |
|                 |                           |                                                     |                           |                            | MIN                                              | TYP  | MAX | MIN            | TYP  | MAX | MIN             | TYP  | MAX |      |     |
| V <sub>OH</sub> | High-level output voltage | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> | I <sub>OH</sub> = – 20 μA | 2 V                        | 1.9                                              |      |     | 1.9            |      |     | 1.9             |      |     | V    |     |
|                 |                           |                                                     |                           | 4.5 V                      | 4.4                                              |      |     | 4.4            |      |     | 4.4             |      |     |      |     |
|                 |                           |                                                     |                           | 6 V                        | 5.9                                              |      |     | 5.9            |      |     | 5.9             |      |     |      |     |
|                 |                           |                                                     | I <sub>OH</sub> = – 4 mA  | 4.5 V                      | 3.98                                             |      |     | 3.84           |      |     | 3.7             |      |     |      |     |
|                 |                           |                                                     |                           | I <sub>OH</sub> = – 5.2 mA | 6 V                                              | 5.48 |     |                | 5.34 |     |                 | 5.2  |     |      |     |
| V <sub>OL</sub> | Low-level output voltage  | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub> | I <sub>OL</sub> = 20 μA   | 2 V                        |                                                  |      |     | 0.1            |      |     | 0.1             |      |     | V    |     |
|                 |                           |                                                     |                           | 4.5 V                      |                                                  |      |     | 0.1            |      |     | 0.1             |      |     |      |     |
|                 |                           |                                                     |                           | 6 V                        |                                                  |      |     | 0.1            |      |     | 0.1             |      |     |      |     |
|                 |                           |                                                     | I <sub>OL</sub> = 4 mA    | 4.5 V                      |                                                  |      |     | 0.26           |      |     | 0.33            |      |     |      | 0.4 |
|                 |                           |                                                     |                           | I <sub>OL</sub> = 5.2 mA   | 6 V                                              |      |     |                | 0.26 |     |                 | 0.33 |     |      |     |
| I <sub>I</sub>  | Input leakage current     | V <sub>I</sub> = V <sub>CC</sub> or 0               |                           | 6 V                        |                                                  |      |     | ±0.1           |      |     | ±1              |      |     | μA   |     |
| I <sub>CC</sub> | Supply current            | V <sub>I</sub> = V <sub>CC</sub> or 0               | I <sub>O</sub> = 0        | 6 V                        |                                                  |      |     | 2              |      |     | 20              |      |     | μA   |     |
| C <sub>i</sub>  | Input capacitance         |                                                     |                           | 5 V                        |                                                  |      |     | 10             |      |     | 10              |      |     | pF   |     |

## 6.6 Switching Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| PARAMETER       |                   | FROM | TO                     | TEST<br>CONDITIO<br>NS | V <sub>CC</sub> | Operating free-air temperature (T <sub>A</sub> ) |     |     |                |     |     |                 |     |     | UNIT |
|-----------------|-------------------|------|------------------------|------------------------|-----------------|--------------------------------------------------|-----|-----|----------------|-----|-----|-----------------|-----|-----|------|
|                 |                   |      |                        |                        |                 | 25°C                                             |     |     | − 40°C to 85°C |     |     | − 55°C to 125°C |     |     |      |
|                 |                   |      |                        |                        |                 | MIN                                              | TYP | MAX | MIN            | TYP | MAX | MIN             | TYP | MAX |      |
| t <sub>pd</sub> | Propagation delay | A    | Y                      | C <sub>L</sub> = 50 pF | 2 V             | 85                                               |     |     | 105            |     |     | 130             |     |     | ns   |
|                 |                   |      |                        |                        | 4.5 V           | 17                                               |     |     | 21             |     |     | 26              |     |     |      |
|                 |                   |      |                        |                        | 6 V             | 14                                               |     |     | 18             |     |     | 22              |     |     |      |
|                 | A                 | Y    | C <sub>L</sub> = 15 pF | 5 V                    | 6               |                                                  |     |     |                |     |     |                 |     |     |      |

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| PARAMETER      |                 | FROM | TO | TEST<br>CONDITIO<br>NS | V <sub>CC</sub> | Operating free-air temperature (T <sub>A</sub> ) |     |     |                |     |     |                 |     |     | UNIT |
|----------------|-----------------|------|----|------------------------|-----------------|--------------------------------------------------|-----|-----|----------------|-----|-----|-----------------|-----|-----|------|
|                |                 |      |    |                        |                 | 25°C                                             |     |     | − 40°C to 85°C |     |     | − 55°C to 125°C |     |     |      |
|                |                 |      |    |                        |                 | MIN                                              | TYP | MAX | MIN            | TYP | MAX | MIN             | TYP | MAX |      |
| t <sub>t</sub> | Transition-time |      | Y  | C <sub>L</sub> = 50 pF | 2 V             | 75                                               |     |     | 95             |     |     | 110             |     |     | ns   |
|                |                 |      |    |                        | 4.5 V           | 15                                               |     |     | 19             |     |     | 22              |     |     |      |
|                |                 |      |    |                        | 6 V             | 13                                               |     |     | 16             |     |     | 19              |     |     |      |

## 6.7 Operating Characteristics

over operating free-air temperature range; typical values measured at  $T_A = 25^\circ\text{C}$  (unless otherwise noted).

| PARAMETER | TEST CONDITIONS                                   | $V_{CC}$ | MIN | TYP | MAX | UNIT |
|-----------|---------------------------------------------------|----------|-----|-----|-----|------|
| $C_{pd}$  | Power dissipation capacitance per gate<br>No load | 5V       |     | 21  |     | pF   |

## 6.8 Typical Characteristics

$T_A = 25^\circ\text{C}$




图 6-1. Typical output voltage in the high state ( $V_{OH}$ )





图 6-2. Typical output voltage in the low state ( $V_{OL}$ )


## 7 Parameter Measurement Information

- Phase relationships between waveforms were chosen arbitrarily. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_t < 6 \text{ ns}$ .
- The outputs are measured one at a time, with one input transition per measurement.




A.  $C_L = 50 \text{ pF}$  and includes probe and jig capacitance.

图 7-1. Load Circuit



A.  $t_t$  is the greater of  $t_r$  and  $t_f$ .

图 7-2. Voltage Waveforms Transition Times



A. The maximum between  $t_{PLH}$  and  $t_{PHL}$  is used for  $t_{pd}$ .


图 7-3. Voltage Waveforms Propagation Delays

## 8 Detailed Description

### 8.1 Overview

This device contains six independent inverters. Each gate performs the Boolean function  $Y = \bar{A}$  in positive logic.

### 8.2 Functional Block Diagram



### 8.3 Feature Description

#### 8.3.1 Balanced CMOS Push-Pull Outputs

A balanced output allows the device to sink and source similar currents. The drive capability of this device may create fast edges into light loads so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device are capable of driving larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to over-current. The electrical and thermal limits defined in the [Absolute Maximum Ratings](#) must be followed at all times.

The CD74HC04 can drive a load with a total capacitance less than or equal to the maximum load listed in the [Switching Characteristics](#) connected to a high-impedance CMOS input while still meeting all of the datasheet specifications. Larger capacitive loads can be applied, however it is not recommended to exceed the provided load value. If larger capacitive loads are required, it is recommended to add a series resistor between the output and the capacitor to limit output current to the values given in the [Absolute Maximum Ratings](#).

#### 8.3.2 Standard CMOS Inputs

Standard CMOS inputs are high impedance and are typically modeled as a resistor from the input to ground in parallel with the input capacitance given in the [Electrical Characteristics](#). The worst case resistance is calculated with the maximum input voltage, given in the [Absolute Maximum Ratings](#), and the maximum input leakage current, given in the [Electrical Characteristics](#), using ohm's law ( $R = V \div I$ ).

Signals applied to the inputs need to have fast edge rates, as defined by the input transition time in the [Recommended Operating Conditions](#) to avoid excessive current consumption and oscillations. If a slow or noisy input signal is required, a device with a Schmitt-trigger input should be used to condition the input signal prior to the standard CMOS input.



### 8.3.3 Clamp Diode Structure

The inputs and outputs to this device have both positive and negative clamping diodes as depicted in 图 8-1.

#### CAUTION

Voltages beyond the values specified in the [Absolute Maximum Ratings](#) table can cause damage to the device. The recommended input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




图 8-1. Electrical Placement of Clamping Diodes for Each Input and Output

### 8.4 Device Functional Modes

表 8-1. Function Table

| INPUT | OUTPUT |
|-------|--------|
| A     | Y      |
| L     | H      |
| H     | L      |

## 9 Application and Implementation

### 备注

以下应用部分中的信息不属于 TI 器件规格的范围，TI 不担保其准确性和完整性。TI 的客户应负责确定器件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

### 9.1 Application Information

This device can be used to add an additional stage to a counter with an external flip-flop. Because counters use a negative edge trigger, the flip-flop's clock input must be inverted to provide this function. This function only requires one of the six available inverters in the device, so the remaining channels can be used for other applications needing an inverted signal or improved signal integrity. Unused inputs must be terminated at  $V_{CC}$  or GND. Unused outputs can be left floating.

### 9.2 Typical Application




图 9-1. Typical application schematic

#### 9.2.1 Design Requirements

##### 9.2.1.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the [Recommended Operating Conditions](#). The supply voltage sets the device's electrical characteristics as described in the [Electrical Characteristics](#).

The supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the CD74HC04 plus the maximum supply current,  $I_{CC}$ , listed in the [Electrical Characteristics](#). The logic device can only source or sink as much current as it is provided at the supply and ground pins, respectively. Be sure not to exceed the maximum total current through GND or  $V_{CC}$  listed in the [Absolute Maximum Ratings](#).

Total power consumption can be calculated using the information provided in [CMOS Power Consumption and  \$C\_{pd}\$  Calculation](#).

Thermal increase can be calculated using the information provided in [Thermal Characteristics of Standard Linear and Logic \(SLL\) Packages and Devices](#).

#### CAUTION

The maximum junction temperature,  $T_J(\max)$  listed in the [Absolute Maximum Ratings](#), is an *additional limitation* to prevent damage to the device. Do not violate any values listed in the [Absolute Maximum Ratings](#). These limits are provided to prevent damage to the device.

##### 9.2.1.2 Input Considerations

Unused inputs must be terminated to either  $V_{CC}$  or ground. These can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input is to be used.

sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The resistor size is limited by drive current of the controller, leakage current into the CD74HC04, as specified in the [Electrical Characteristics](#), and the desired input transition rate. A 10-k $\Omega$  resistor value is often used due to these factors.

The CD74HC04 has standard CMOS inputs, so input signal edge rates cannot be slow. Slow input edge rates can cause oscillations and damaging shoot-through current. The recommended rates are defined in the [Recommended Operating Conditions](#).

Refer to the [§ 8.3](#) for additional information regarding the inputs for this device.

### 9.2.1.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the  $V_{OH}$  specification in the [Electrical Characteristics](#). Similarly, the ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the  $V_{OL}$  specification in the [Electrical Characteristics](#).

Unused outputs can be left floating. Do not connect outputs directly to  $V_{CC}$  or ground.

Refer to [§ 8.3](#) for additional information regarding the outputs for this device.

## 9.2.2 Detailed Design Procedure

1. Add a decoupling capacitor from  $V_{CC}$  to GND. The capacitor needs to be placed physically close to the device and electrically close to both the  $V_{CC}$  and GND pins. An example layout is shown in [§ 11](#).
2. Ensure the capacitive load at the output is  $\leq 70$  pF. This is not a hard limit, however it will ensure optimal performance. This can be accomplished by providing short, appropriately sized traces from the CD74HC04 to the receiving device.
3. Ensure the resistive load at the output is larger than  $(V_{CC} / I_{O(max)}) \Omega$ . This will ensure that the maximum output current from the [Absolute Maximum Ratings](#) is not violated. Most CMOS inputs have a resistive load measured in megaohms; much larger than the minimum calculated above.
4. Thermal issues are rarely a concern for logic gates, however the power consumption and thermal increase can be calculated using the steps provided in the application report, [CMOS Power Consumption and Cpd Calculation](#)

### 9.2.3 Application Curves




图 9-2. Typical application timing diagram

## 10 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the [Recommended Operating Conditions](#). Each  $V_{CC}$  terminal should have a bypass capacitor to prevent power disturbance. A 0.1- $\mu$ F capacitor is recommended for this device. It is acceptable to parallel multiple bypass caps to reject different frequencies of noise. The 0.1- $\mu$ F and 1- $\mu$ F capacitors are commonly used in parallel. The bypass capacitor should be installed as close to the power terminal as possible for best results, as shown in [Figure 11-1](#).

## 11 Layout

### 11.1 Layout Guidelines

When using multiple-input and multiple-channel logic devices inputs must not ever be left floating. In many cases, functions or parts of functions of digital logic devices are unused; for example, when only two inputs of a triple-input AND gate are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or  $V_{CC}$ , whichever makes more sense for the logic function or is more convenient.

### 11.2 Layout Example




图 11-1. Example layout for the CD74HC04

## 12 Device and Documentation Support

### 12.1 Documentation Support

#### 12.1.1 Related Documentation

For related documentation see the following:

- [HCMOS Design Considerations](#)
- [CMOS Power Consumption and CPD Calculation](#)
- [Designing with Logic](#)

#### 12.2 Related Links

The table below lists quick access links. Categories include technical documents, support and community resources, tools and software, and quick access to sample or buy.

### 12.3 支持资源

[TI E2E™ 支持论坛](#)是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

### 12.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

### 12.5 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

### 12.6 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number       | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)      |
|-----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------|
| <a href="#">CD54HC04F</a>   | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC04F                |
| CD54HC04F.A                 | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC04F                |
| <a href="#">CD54HC04F3A</a> | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8409801CA<br>CD54HC04F3A |
| CD54HC04F3A.A               | Active        | Production           | CDIP (J)   14  | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | 8409801CA<br>CD54HC04F3A |
| <a href="#">CD74HC04E</a>   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC04E                |
| CD74HC04E.A                 | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC04E                |
| <a href="#">CD74HC04M</a>   | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC04M                    |
| <a href="#">CD74HC04M96</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -55 to 125   | HC04M                    |
| CD74HC04M96.A               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC04M                    |
| CD74HC04M96G4               | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC04M                    |
| CD74HC04M96G4.A             | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC04M                    |
| <a href="#">CD74HC04MT</a>  | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC04M                    |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


**OTHER QUALIFIED VERSIONS OF CD54HC04, CD74HC04 :**

- Catalog : [CD74HC04](#)
- Military : [CD54HC04](#)

**NOTE: Qualified Version Definitions:**

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION




\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD74HC04M96 | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |




## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HC04M96 | SOIC         | D               | 14   | 2500 | 340.5       | 336.1      | 32.0        |

**TUBE**


\*All dimensions are nominal


| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HC04E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC04E   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC04E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC04E.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |

**J 14**

## GENERIC PACKAGE VIEW

**CDIP - 5.08 mm max height**


CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4040083-5/G


J0014A



## PACKAGE OUTLINE

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



4214771/A 05/2017

### NOTES:


1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package is hermetically sealed with a ceramic lid using glass frit.
4. Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
5. Falls within MIL-STD-1835 and GDIP1-T14.

# EXAMPLE BOARD LAYOUT



J0014A

CDIP - 5.08 mm max height

CERAMIC DUAL IN LINE PACKAGE



LAND PATTERN EXAMPLE  
NON-SOLDER MASK DEFINED  
SCALE: 5X




4214771/A 05/2017


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE




| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |




14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

**D0014A****PACKAGE OUTLINE****SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT




# EXAMPLE BOARD LAYOUT



D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
SCALE:8X



SOLDER MASK DETAILS

4220718/A 09/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.




## EXAMPLE STENCIL DESIGN

D0014A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:8X

4220718/A 09/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月