

ESD801 用于射频和 ADAS 信号保护的超低电容 ESD 二极管

1 特性

- IEC 61000-4-2 ESD 保护：
 - $\pm 15\text{kV}$ 接触放电
 - $\pm 15\text{kV}$ 空气间隙放电
- IEC 61000-4-5 浪涌保护：
 - 3A (8/20 μs)
- I/O 电容：0.3pF (典型值)
- 超低漏电流：1nA (典型值)
- 业界通用 0402 封装

2 应用

- 汽车天线 ESD 保护
- 射频信号 ESD 保护
- 近场通信 (NFC)
- 采用同轴电缆供电的汽车串行器/解串器
- USB Type-C (可耐受短接至 Vbus)

3 说明

ESD801 是一款双向 ESD 保护二极管。ESD801 采用业界通用 0402 (DFN-1006) 封装，并提供 15kV 的 IEC 61000-4-2 保护级别。根据 IEC 61000-4-5 标准，该器件可以钳制峰值脉冲电流高达 3A 的 8/20 μs 浪涌。

低电容和低漏电流有助于确保在各种系统和应用中免受瞬态事件的影响。这种保护对于许多应用（例如更小的外形尺寸和更快的数据速率）来说至关重要，这些应用随着时间的推移越来越普遍。

器件信息

器件型号	封装 ⁽¹⁾	封装尺寸 ⁽²⁾
ESD801	DPY (DFN1006, 2)	1mm × 0.6mm

(1) 有关更多信息，请参阅节 8。

(2) 封装尺寸 (长 × 宽) 为标称值，并包括引脚 (如适用)。




图 3-1. 功能方框图



内容

1 特性	1	5.6 电气特性	5
2 应用	1	5.7 典型特性	6
3 说明	1	6 器件和文档支持	7
4 引脚配置和功能	3	6.1 接收文档更新通知	7
5 规格	4	6.2 支持资源	7
5.1 绝对最大额定值.....	4	6.3 商标	7
5.2 ESD 等级 - JEDEC 规范.....	4	6.4 静电放电警告	7
5.3 ESD 等级 - IEC 规格.....	4	6.5 术语表	7
5.4 建议运行条件.....	4	7 修订历史记录	7
5.5 热性能信息.....	4	8 机械、封装和可订购信息	7

4 引脚配置和功能




图 4-1. DPY 封装，2 引脚 DFN1006（顶视图）

表 4-1. 引脚功能

引脚		类型 ⁽¹⁾	说明
名称	编号		
IO	1	I/O	ESD 保护通道。如果用作 ESD I/O，则将引脚 2 接地
IO	2	I/O	ESD 保护通道。如果用作 ESD I/O，则将引脚 1 接地

(1) I = 输入，O = 输出

5 规格

5.1 绝对最大额定值

在自然通风条件下的工作温度范围内测得 (除非另有说明) ⁽¹⁾

参数		最小值	最大值	单位
P _{PPM}	25°C 时的 IEC 61000-4-5 浪涌 (t _p = 8/20μs) 峰值脉冲功率 ⁽²⁾		183	W
I _{PPM}	25°C 时的 IEC 61000-4-5 浪涌 (t _p = 8/20μs) 峰值脉冲电流 ⁽²⁾		3	A
T _A	自然通风条件下的工作温度范围	-40	125	°C
T _{stg}	贮存温度	-65	155	°C

(1) 超出绝对最大额定值下列出的应力可能会对器件造成永久性损坏。这些仅为应力等级，并不意味着器件在这些条件下以及在建议运行条件以外的任何其他条件下能够正常运行。长时间处于绝对最大额定条件下可能会影响器件的可靠性。

(2) 除非另有说明，否则电压均以 GND 为基准。

5.2 ESD 等级 - JEDEC 规范

参数		测试条件	值	单位
V _(ESD)	静电放电	人体放电模型 (HBM), 符合 ANSI/ESDA/JEDEC JS-001 标准, 所有引脚 ⁽¹⁾	±2500	V
		充电器件模型 (CDM), 符合 JEDEC 规范 JS-002, 所有引脚 ⁽²⁾	±1000	

(1) JEDEC 文档 JEP155 指出: 500V HBM 时能够在标准 ESD 控制流程下安全生产。

(2) JEDEC 文档 JEP157 指出: 250V CDM 时能够在标准 ESD 控制流程下安全生产。

5.3 ESD 等级 - IEC 规格

参数		测试条件	值	单位
V _(ESD)	静电放电	IEC 61000-4-2 接触放电, 所有引脚	±15000	V
		IEC 61000-4-2 空气放电, 所有引脚	±15000	

5.4 建议运行条件

在自然通风条件下的工作温度范围内测得 (除非另有说明)

		最小值	标称值	最大值	单位
V _{IN}	输入电压	-36		36	V
T _A	自然通风条件下的工作温度范围	-40		125	°C

5.5 热性能信息

热指标 ⁽¹⁾		ESD801		单位
		DPY (DFN1006)		
		2 引脚		
R _{θJA}	结至环境热阻	262.6		°C/W
R _{θJC(top)}	结至外壳 (顶部) 热阻	132.3		°C/W
R _{θJB}	结至电路板热阻	78.5		°C/W
Ψ _{JT}	结至顶部特征参数	2.2		°C/W
Ψ _{JB}	结至电路板特征参数	78		°C/W
R _{θJC(bot)}	结至外壳 (底部) 热阻	不适用		°C/W

(1) 有关新旧热指标的更多信息, 请参阅[半导体和 IC 封装热指标应用报告](#)。

5.6 电气特性

在 $T_A = 25^\circ\text{C}$ 条件下 (除非另有说明)

参数		测试条件	最小值	典型值	最大值	单位
V_{RWM}	反向关断电压	$I_{IO} < 10\text{nA}$	-36		36	V
I_{LEAK}	V_{RWM} 下的漏电流	$V_{IO} = \pm 36\text{V}$, I/O 至 GND		1	10	nA
V_{BR}	击穿电压, I/O 至 GND ⁽¹⁾	$I_{IO} = \pm 10\text{mA}$	37.8		44.2	V
V_{CLAMP}	浪涌钳位电压, $t_p = 8/20\mu\text{s}$ ⁽²⁾	$I_{PP} = 3\text{A}$, I/O 至 GND		61		V
		$I_{PP} = 3\text{A}$, GND 至 I/O		61		V
	TLP 钳位电压, $t_p = 100\text{ns}$ ⁽³⁾	$I_{PP} = \pm 16\text{A}$ (100ns TLP), I/O 至 GND		67		V
R_{DYN}	动态电阻 ⁽⁴⁾	I/O 至 GND		1.05		Ω
		GND 至 I/O		1.05		
C_{LINE}	输入电容, IO 至 GND	$V_{IO} = 0\text{V}$, $f = 1\text{MHz}$		0.3	0.5	pF

- (1) V_{BR} 是指在器件进入快速复位状态之前, 在逐步升高电压期间, 在 1mA 时获得的电压
- (2) 根据 IEC 61000-4-5 器件承受 8/20 μs 指数衰减波形的应力
- (3) 非重复方波电流脉冲、传输线路脉冲 (TLP); ANSI/ESD STM5.5.1-2008
- (4) 在 $I = 10\text{A}$ 和 $I = 20\text{A}$ 之间使用 TLP 特性的最小二乘拟合来提取 R_{DYN}

5.7 典型特性




图 5-1. 偏置电压与电容间的关系




图 5-2. 直流 I-V 曲线




图 5-3. 正 TLP 曲线




图 5-4. 8/20 μs 浪涌响应

6 器件和文档支持

相关文档

相关文档如下：

- 德州仪器 (TI), [ESD 封装和布局指南](#)
- 德州仪器 (TI), [TI 的 IEC 61000-4-x 测试应用手册](#)
- 德州仪器 (TI), [ESD 布局指南用户指南](#)
- 德州仪器 (TI), [ESD 保护二极管 EVM 用户指南](#)
- 德州仪器 (TI), [通用 ESD 评估模块用户指南](#)
- 德州仪器 (TI), [阅读和理解 ESD 保护数据表用户指南](#)

6.1 接收文档更新通知

要接收文档更新通知，请导航至 [ti.com](#) 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

6.2 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

6.3 商标

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

6.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

6.5 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

7 修订历史记录

注：以前版本的页码可能与当前版本的页码不同

日期	修订版本	注释
December 2024	*	初始发行版

8 机械、封装和可订购信息

以下页面包含机械、封装和可订购信息。这些信息是指定器件可用的最新数据。数据如有变更，恕不另行通知，且不会对此文档进行修订。有关此数据表的浏览器版本，请查阅左侧的导航栏。

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
ESD801DPYR	Active	Production	X1SON (DPY) 2	10000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-	Q7

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF ESD801 :

- Automotive : [ESD801-Q1](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ESD801DPYR	X1SON	DPY	2	10000	178.0	8.4	0.7	1.15	0.47	2.0	8.0	Q1

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
ESD801DPYR	X1SON	DPY	2	10000	205.0	200.0	33.0

GENERIC PACKAGE VIEW

DPY 2

X1SON - 0.45 mm max height

1 x 0.6 mm

PLASTIC SMALL OUTLINE - NO LEAD

This image is a representation of the package family, actual package may vary.
Refer to the product data sheet for package details.



4231484/A


DPY0002A



PACKAGE OUTLINE

X1SON - 0.45 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



4224561/C 07/2024

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M
2. This drawing is subject to change without notice.

EXAMPLE BOARD LAYOUT


DPY0002A

X1SON - 0.45 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:60X



SOLDER MASK DETAILS

4224561/C 07/2024

NOTES: (continued)


3. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/sluea271).
4. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.

EXAMPLE STENCIL DESIGN

DPY0002A

X1SON - 0.45 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.1 mm THICK STENCIL
SCALE:60X

4224561/C 07/2024

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月