

## CDx4HCx4316 具有电平转换功能的高速 CMOS 逻辑四路模拟开关

### 1 特性

- 宽模拟输入电压范围：  
 $V_{CC} - V_{EE}$  : 0V 至 10V
- 低导通电阻：
  - 45Ω (典型值) :  $V_{CC} = 4.5V$
  - 35Ω (典型值) :  $V_{CC} = 6V$
  - 30Ω (典型值) :  $V_{CC} - V_{EE} = 9V$
- 快速开关和传播延迟时间
- 低关断漏电流
- 内置先断后合开关
- 逻辑电平转换，可启用 5V 逻辑以适应 ±5V 模拟信号
- 宽工作温度范围：-55°C 至 125°C
- HC 类型：
  - 工作电压为 2V 至 10V
  - 高抗噪性：当  $V_{CC} = 5V$  时， $N_{IL} = 30\%$ ， $N_{IH} = V_{CC}$  的 30%
- HCT 类型：
  - 直接 LSTTL 输入逻辑兼容性， $V_{IL} = 0.8V$  (最大值)， $V_{IH} = 2V$  (最小值)
  - CMOS 输入兼容性，在  $V_{OL}$ 、 $V_{OH}$  下  $I_I \leq 1\mu A$


### 2 说明

HC4316 和 CD74HCT4316 包含四个独立的数控模拟开关，这些开关采用硅栅 CMOS 技术并借助标准 CMOS 集成电路的低功耗特性来实现与 LSTTL 接近的运行速度。

此外，这些器件还包含逻辑电平转换电路，可通过 5V 逻辑电平实现 ±5V 电压之间的模拟信号切换。当公共使能 (E) 为低电平时，每个开关由其所选输入 (S) 上的高电平电压导通。E 为高电平时，将禁用所有开关。数字输入可以在  $V_{CC}$  和 GND 之间摆动；模拟输入/输出可以在  $V_{CC}$  (作为正限值) 和  $V_{EE}$  (作为负限值) 之间摆动。电压范围如图 13-1 和图 13-2 所示。

器件信息

| 输入 |   | 开关    |
|----|---|-------|
| E  | S | 导通/关断 |
| L  | L | 关断    |
| L  | H | 导通    |
| H  | H | 关断    |



一个开关



## Table of Contents

|                                                                            |           |                                                                  |           |
|----------------------------------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 特性</b> .....                                                          | <b>1</b>  | <b>14 Typical Performance Curves</b> .....                       | <b>17</b> |
| <b>2 说明</b> .....                                                          | <b>1</b>  | <b>15 Parameter Measurement Information</b> .....                | <b>18</b> |
| <b>3 Pin Configurations and Functions</b> .....                            | <b>3</b>  | <b>16 Detailed Description</b> .....                             | <b>20</b> |
| <b>4 Absolute Maximum Ratings</b> .....                                    | <b>4</b>  | 16.1 Functional Block Diagram.....                               | 20        |
| <b>5 Thermal Information</b> .....                                         | <b>5</b>  | 16.2 Device Functional Modes.....                                | 20        |
| <b>6 Recommended Operating Conditions</b> .....                            | <b>5</b>  | <b>17 Device and Documentation Support</b> .....                 | <b>21</b> |
| <b>7 Electrical Characteristics: HC Devices</b> .....                      | <b>6</b>  | 17.1 接收文档更新通知.....                                               | 21        |
| <b>8 Electrical Characteristics: HCT Devices</b> .....                     | <b>9</b>  | 17.2 支持资源.....                                                   | 21        |
| <b>9 Switching Characteristics HC</b> .....                                | <b>10</b> | 17.3 Trademarks.....                                             | 21        |
| <b>10 Switching Characteristics HCT</b> .....                              | <b>13</b> | 17.4 静电放电警告.....                                                 | 21        |
| <b>11 Analog Channel Specifications</b> .....                              | <b>15</b> | 17.5 术语表.....                                                    | 21        |
| <b>12 HCT Input Loading Table</b> .....                                    | <b>16</b> | <b>18 Revision History</b> .....                                 | <b>21</b> |
| <b>13 Recommended Operating Area as a Function of Supply Voltage</b> ..... | <b>16</b> | <b>19 Mechanical, Packaging, and Orderable Information</b> ..... | <b>21</b> |

## 3 Pin Configurations and Functions




图 3-1. CD74HC4316 (TSSOP)

表 3-1. Pin Functions

| PIN             |     | TYPE | DESCRIPTION               |
|-----------------|-----|------|---------------------------|
| NAME            | NO. |      |                           |
| 1Z              | 1   | I/O  | Input/Output for Switch 1 |
| 1Y              | 2   | I/O  | Input/Output for Switch 1 |
| 2Y              | 3   | I/O  | Input/Output for Switch 2 |
| 2Z              | 4   | I/O  | Input/Output for Switch 2 |
| 2S              | 5   | I    | Control pin for Switch 2  |
| 3S              | 6   | I    | Control pin for Switch 3  |
| E               | 7   | I    | Enable Pin                |
| GND             | 8   | -    | Ground Pin                |
| V <sub>EE</sub> | 9   | -    | Power Pin                 |
| 3Z              | 10  | I/O  | Input/Output for Switch 3 |
| 3Y              | 11  | I/O  | Input/Output for Switch 3 |
| 4Y              | 12  | I/O  | Input/Output for Switch 4 |
| 4Z              | 13  | I/O  | Input/Output for Switch 4 |
| 4S              | 14  | I    | Control pin for Switch 4  |
| 1S              | 15  | I    | Control pin for Switch 1  |
| V <sub>CC</sub> | 16  | -    | Power Pin                 |

## 4 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)</sup>

|                   |                                                 |                                                                | MIN   | MAX  | UNIT |
|-------------------|-------------------------------------------------|----------------------------------------------------------------|-------|------|------|
| $V_{CC} - V_{EE}$ | DC Supply voltage                               |                                                                | -0.5  | 10.5 | V    |
| $V_{CC}$          |                                                 |                                                                | - 0.5 | 7    | V    |
| $V_{EE}$          |                                                 |                                                                | 0.5   | -7   | V    |
| $I_{IK}$          | DC input diode current                          | $V_I < -0.5\text{ V}$ or $V_I > V_{CC} + 0.5\text{ V}$         | - 20  | 20   | mA   |
| $I_{OK}$          | DC switch diode current                         | $V_I < V_{EE} - 0.5\text{ V}$ or $V_I < V_{CC} + 0.5\text{ V}$ | - 25  | 25   | mA   |
| $I_{OK}$          | DC Output Diode Current                         | For $V_O < -0.5\text{ V}$ or $V_O > V_{CC} + 0.5\text{ V}$     | - 20  | 20   | mA   |
| $I_O$             | DC Output Source or Sink Current per Output Pin | For $V_O > -0.5\text{ V}$ or $V_O < V_{CC} + 0.5\text{ V}$     | - 25  | 25   | mA   |
| $I_{CC}$          | DC $V_{CC}$ or ground current                   |                                                                | - 50  | 50   | mA   |
| $T_{JMAX}$        | Maximum junction temperature                    |                                                                |       | 150  | °C   |
| $T_{LMAX}$        | Maximum lead temperature                        | Soldering 10 s                                                 |       | 300  | °C   |
| $T_{stg}$         | Storage temperature                             |                                                                | - 65  | 150  | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Rating* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Condition*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## 5 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                        | PW (TSSOP) | UNIT |
|-------------------------------|----------------------------------------|------------|------|
|                               |                                        | 16 PINS    |      |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance | 127.9      | °C/W |

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics](#) application report.

## 6 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

|                                  |                                                                   |                                           | MIN      | NOM | MAX      | UNIT |
|----------------------------------|-------------------------------------------------------------------|-------------------------------------------|----------|-----|----------|------|
| $V_{CC}$                         | Supply voltage range ( $T_A$ = full package temperature range)(2) | CD54 and 74HC types                       | 2        |     | 6        | V    |
|                                  |                                                                   | CD54 and 74HCT types                      | 4.5      |     | 5.5      |      |
| $V_{CC} - V_{EE}$ <sup>(1)</sup> | Supply voltage range ( $T_A$ = full package temperature range)(2) | CD54 and 74HC types, CD54 and 74HCT types | 2        |     | 10       | V    |
| $V_{EE}$                         | Supply voltage range ( $T_A$ = full package temperature range)(3) | CD54 and 74HC types, CD54 and 74HCT types | 0        |     | – 6      | V    |
| $V_I$                            | DC input control voltage                                          |                                           | GND      |     | $V_{CC}$ | V    |
| $V_{IS}$                         | Analog switch I/O voltage                                         |                                           | $V_{EE}$ |     | $V_{CC}$ | V    |
| $T_A$                            | Ambient temperature                                               |                                           | – 55     |     | 125      | °C   |
| $t_r, t_f$                       | Input rise and fall times                                         | 2 V                                       | 0        |     | 1000     | ns   |
|                                  |                                                                   | 4.5 V                                     | 0        |     | 500      |      |
|                                  |                                                                   | 6 V                                       | 0        |     | 400      |      |

(1)  $V_{DD}$  and  $V_{SS}$  can be any value as long as  $3\text{ V} \leq (V_{DD} - V_{SS}) \leq 24\text{ V}$ , and the minimum  $V_{DD}$  is met.

## 7 Electrical Characteristics: HC Devices

Over operating free-air temperature range,  $V_{\text{SUPPLY}} = \pm 5 \text{ V}$ , and  $R_L = 100 \ \Omega$ , (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                                                       | TEST CONDITIONS     |                    |                     |                     |                  | MIN | TYP | MAX  | UNIT |  |
|-----------------------------------------------------------------|---------------------|--------------------|---------------------|---------------------|------------------|-----|-----|------|------|--|
| SIGNAL INPUTS (V <sub>IS</sub> ) AND OUTPUTS (V <sub>OS</sub> ) |                     |                    |                     |                     |                  |     |     |      |      |  |
|                                                                 | V <sub>IS</sub> (V) | V <sub>I</sub> (V) | V <sub>EE</sub> (V) | V <sub>CC</sub> (V) | T <sub>A</sub>   |     |     |      |      |  |
| Input High Voltage, V <sub>IH</sub> , Min                       |                     |                    |                     | 2                   | 25°C             |     |     | 1.5  | V    |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 1.5  |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 1.5  |      |  |
|                                                                 |                     |                    |                     | 4.5                 | 25°C             |     |     | 3.15 |      |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 3.15 |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 3.15 |      |  |
|                                                                 |                     |                    |                     | 6                   | 25°C             |     |     | 4.2  |      |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 4.2  |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 4.2  |      |  |
| Input Low Voltage, V <sub>IL</sub> , Max                        |                     |                    |                     | 2                   | 25°C             |     |     | 0.5  | V    |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 0.5  |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 0.5  |      |  |
|                                                                 |                     |                    |                     | 4.5                 | 25°C             |     |     | 1.35 |      |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 1.35 |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 1.35 |      |  |
|                                                                 |                     |                    |                     | 6                   | 25°C             |     |     | 1.8  |      |  |
|                                                                 |                     |                    |                     |                     | – 40°C to +85°C  |     |     | 1.8  |      |  |
|                                                                 |                     |                    |                     |                     | – 55°C to +125°C |     |     | 1.8  |      |  |

Over operating free-air temperature range,  $V_{\text{SUPPLY}} = \pm 5 \text{ V}$ , and  $R_L = 100 \, \Omega$ , (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                                                                | TEST CONDITIONS                    |                                                           |      |     |                  | MIN | TYP | MAX       | UNIT          |
|--------------------------------------------------------------------------|------------------------------------|-----------------------------------------------------------|------|-----|------------------|-----|-----|-----------|---------------|
| $r_{\text{ON}}$<br>ON resistance<br>$I_O = 1 \text{ mA}$                 | $V_{\text{CC}}$ or $V_{\text{EE}}$ |                                                           | 0    | 4.5 | 25°C             |     | 30  | 180       | $\Omega$      |
|                                                                          |                                    |                                                           |      |     | – 40°C to +85°C  |     |     | 225       |               |
|                                                                          |                                    |                                                           |      |     | – 55°C to +125°C |     |     | 270       |               |
|                                                                          |                                    |                                                           | 0    | 6   | 25°C             |     | 35  | 160       |               |
|                                                                          |                                    |                                                           |      |     | – 40°C to +85°C  |     |     | 200       |               |
|                                                                          |                                    |                                                           |      |     | – 55°C to +125°C |     |     | 240       |               |
|                                                                          | $V_{\text{CC}}$ to $V_{\text{EE}}$ |                                                           | –4.5 | 4.5 | 25°C             |     | 30  | 135       | $\Omega$      |
|                                                                          |                                    |                                                           |      |     | – 40°C to +85°C  |     |     | 170       |               |
|                                                                          |                                    |                                                           |      |     | – 55°C to +125°C |     |     | 205       |               |
|                                                                          |                                    |                                                           | 0    | 4.5 | 25°C             |     | 40  | 320       |               |
|                                                                          |                                    |                                                           |      |     | – 40°C to +85°C  |     |     | 400       |               |
|                                                                          |                                    |                                                           |      |     | – 55°C to +125°C |     |     | 480       |               |
| $\Delta r_{\text{ON}}$<br>Maximum ON resistance between any two channels |                                    |                                                           | 0    | 4.5 | 25°C             |     | 10  |           | $\Omega$      |
|                                                                          |                                    |                                                           | 0    | 6   | 25°C             |     | 8.5 |           |               |
|                                                                          |                                    |                                                           | –4.5 | 4.5 | 25°C             |     | 5   |           |               |
| $I_{\text{IZ}}$<br>Switch OFF leakage current                            | $V_{\text{CC}} - V_{\text{EE}}$    | $V_{\text{IH}}$ or $V_{\text{IL}}$<br>$E = V_{\text{CC}}$ | 0    | 6   | 25°C             |     |     | $\pm 0.1$ | $\mu\text{A}$ |
|                                                                          |                                    |                                                           | 0    | 6   | – 55°C to 85°C   |     |     | $\pm 1$   |               |
|                                                                          |                                    |                                                           | 0    | 6   | – 55°C to 125°C  |     |     | $\pm 1$   |               |
|                                                                          |                                    |                                                           | –5   | 5   | 25°C             |     |     | $\pm 0.1$ |               |
|                                                                          |                                    |                                                           | –5   | 5   | – 55°C to 85°C   |     |     | $\pm 1$   |               |
|                                                                          |                                    |                                                           | –5   | 5   | – 55°C to 125°C  |     |     | $\pm 1$   |               |
| $I_{\text{IL}}$<br>Control input leakage current                         |                                    | $V_{\text{CC}}$ or GND                                    | 0    | 6   | 25°C             |     |     | $\pm 0.1$ | $\mu\text{A}$ |
|                                                                          |                                    |                                                           |      |     | – 55°C to 85°C   |     |     | $\pm 1$   |               |
|                                                                          |                                    |                                                           |      |     | – 55°C to 125°C  |     |     | $\pm 1$   |               |

Over operating free-air temperature range,  $V_{\text{SUPPLY}} = \pm 5 \text{ V}$ , and  $R_L = 100 \, \Omega$ , (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                                                             |                                                                                  | TEST CONDITIONS        |    |   |                    |  | MIN | TYP | MAX | UNIT |
|-----------------------------------------------------------------------|----------------------------------------------------------------------------------|------------------------|----|---|--------------------|--|-----|-----|-----|------|
| Quiescent Device Current, I <sub>DD</sub> Max<br>I <sub>O</sub> = 1mA | When V <sub>IS</sub> =<br>V <sub>EE</sub> , V <sub>OS</sub> =<br>V <sub>CC</sub> | V <sub>CC</sub> or GND | 0  | 6 | 25°C               |  |     |     | 14  | μA   |
|                                                                       |                                                                                  |                        |    |   | - 55°C to<br>85°C  |  |     |     | 80  |      |
|                                                                       |                                                                                  |                        |    |   | - 55°C to<br>125°C |  |     |     | 160 |      |
|                                                                       | When V <sub>IS</sub> =<br>V <sub>CC</sub> , V <sub>OS</sub> =<br>V <sub>EE</sub> | V <sub>CC</sub> or GND | -5 | 5 | 25°C               |  |     |     | 30  |      |
|                                                                       |                                                                                  |                        |    |   | - 55°C to<br>85°C  |  |     |     | 160 |      |
|                                                                       |                                                                                  |                        |    |   | - 55°C to<br>125°C |  |     |     | 320 |      |
| CONTROL (ADDRESS OR INHIBIT), V <sub>C</sub>                          |                                                                                  |                        |    |   |                    |  |     |     |     |      |

(1) For dual-supply systems theoretical worst case ( $V_I = 2.4 \text{ V}$ ,  $V_{CC} = 5.5 \text{ V}$ ) specification is 1.8mA

## 8 Electrical Characteristics: HCT Devices

Over operating free-air temperature range,  $V_{\text{SUPPLY}} = \pm 5 \text{ V}$ , and  $R_L = 100 \ \Omega$ , (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                                                       |                      | TEST CONDITIONS                    |                                    |                                    |                                    |                  | MIN    | TYP              | MAX | UNIT             |        |  |   |  |
|-----------------------------------------------------------------|----------------------|------------------------------------|------------------------------------|------------------------------------|------------------------------------|------------------|--------|------------------|-----|------------------|--------|--|---|--|
| SIGNAL INPUTS (V <sub>IS</sub> ) AND OUTPUTS (V <sub>OS</sub> ) |                      |                                    |                                    |                                    |                                    |                  |        |                  |     |                  |        |  |   |  |
|                                                                 |                      | V <sub>IS</sub> (V)                | V <sub>I</sub> (V)                 | V <sub>CC</sub> (V)                | V <sub>EE</sub> (V)                | T <sub>A</sub>   |        |                  |     |                  |        |  |   |  |
| High Level Input Voltage                                        | V <sub>IH</sub>      |                                    |                                    | 4.5 to 5.5                         |                                    | 25°C             | 2      |                  | V   |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 40°C to +85°C  | 2      |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to +125°C | 2      |                  |     |                  |        |  |   |  |
| Low Level Input Voltage                                         | V <sub>IL</sub>      |                                    |                                    |                                    |                                    | 4.5 to 5.5       |        | 25°C             | 0.8 |                  | V      |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    |                  |        | – 40°C to +85°C  | 0.8 |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    |                  |        | – 55°C to +125°C | 0.8 |                  |        |  |   |  |
| "ON" Resistance IO = 1mA                                        | R <sub>ON</sub>      |                                    |                                    | V <sub>CC</sub> or V <sub>EE</sub> | V <sub>IH</sub> or V <sub>IL</sub> |                  |        | 4.5              | 0   | 25°C             | 30 180 |  | Ω |  |
|                                                                 |                      |                                    |                                    |                                    |                                    |                  |        |                  |     | – 40°C to +85°C  | 45 225 |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    |                  |        |                  |     | – 55°C to +125°C | 270    |  |   |  |
|                                                                 |                      | V <sub>CC</sub> to V <sub>EE</sub> | 4.5                                | -4.5                               |                                    | 25°C             | 135    |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 40°C to +85°C  | 30 170 |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to +125°C | 205    |                  |     |                  |        |  |   |  |
|                                                                 |                      | V <sub>CC</sub> or V <sub>EE</sub> | 4.5                                | 0                                  |                                    | 25°C             | 320    |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 40°C to +85°C  | 85 400 |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to +125°C | 480    |                  |     |                  |        |  |   |  |
|                                                                 |                      | V <sub>CC</sub> to V <sub>EE</sub> | 4.5                                | -4.5                               |                                    | 25°C             | 35 170 |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 40°C to +85°C  | 215    |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to +125°C | 255    |                  |     |                  |        |  |   |  |
| "ON" Resistance Between Any Two Switches                        | ▲<br>R <sub>ON</sub> |                                    | VCC                                | 4.5                                | 0                                  | 25°C             | 10     |                  | Ω   |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    | 4.5                                | -4.5                               | 25°C             | 5      |                  | Ω   |                  |        |  |   |  |
| Off-Switch Leakage Current                                      | I <sub>IZ</sub>      | V <sub>CC</sub> - V <sub>EE</sub>  | V <sub>IH</sub> or V <sub>IL</sub> | 6                                  | 0                                  | 25°C             | ±0.1   |                  | μA  |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to 85°C   | ±1     |                  | μA  |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to 125°C  | ±1     |                  | μA  |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    | 5                                  | -5                                 | 25°C             | ±0.1   |                  | μA  |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to 85°C   | ±1     |                  |     |                  |        |  |   |  |
|                                                                 |                      |                                    |                                    |                                    |                                    | – 55°C to 125°C  | ±1     |                  |     |                  |        |  |   |  |

Over operating free-air temperature range,  $V_{\text{SUPPLY}} = \pm 5 \text{ V}$ , and  $R_L = 100 \, \Omega$ , (unless otherwise noted)<sup>(1)</sup>

| PARAMETER                                                      |                         | TEST CONDITIONS                                                                                                                                         |                                             |            |      |                 | MIN | TYP | MAX  | UNIT |
|----------------------------------------------------------------|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|------------|------|-----------------|-----|-----|------|------|
| Input Leakage Current (Any Control)                            | I <sub>IL</sub>         |                                                                                                                                                         | V <sub>CC</sub> or GND                      | 5.5        | 0    | 25°C            |     |     | ±0.1 | μA   |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 85°C  |     |     | ±1   |      |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 125°C |     |     | ±1   |      |
| Quiescent Device Current                                       | I <sub>CC</sub>         | When V <sub>IS</sub> = V <sub>EE</sub> , V <sub>OS</sub> = V <sub>CC</sub> , When V <sub>IS</sub> = V <sub>CC</sub> , V <sub>OS</sub> = V <sub>EE</sub> | Any voltage between V <sub>CC</sub> and GND | 5.5        | 0    | 25°C            |     |     | 8    | μA   |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 85°C  |     |     | 80   |      |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 125°C |     |     | 160  |      |
|                                                                |                         |                                                                                                                                                         |                                             | 5.5        | –4.5 | 25°C            |     |     | 16   |      |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 85°C  |     |     | 160  |      |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 125°C |     |     | 320  |      |
| Additional Quiescent Device Current Per Input Pin: 1 Unit Load | ▲I <sub>CC</sub><br>(1) | V <sub>CC</sub> - 2.1                                                                                                                                   |                                             | 4.5 to 5.5 |      | 25°C            |     | 100 | 360  | μA   |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 85°C  |     |     | 450  |      |
|                                                                |                         |                                                                                                                                                         |                                             |            |      | – 55°C to 125°C |     |     | 490  |      |
| CONTROL (ADDRESS OR INHIBIT), V <sub>C</sub>                   |                         |                                                                                                                                                         |                                             |            |      |                 |     |     |      |      |

(1) For dual-supply systems theoretical worst case ( $V_{\text{I}} = 2.4 \text{ V}$ ,  $V_{\text{CC}} = 5.5 \text{ V}$ ) specification is 1.8mA

## 9 Switching Characteristics HC

over operating free-air temperature range (unless otherwise noted)

| Parameter                           |                                     | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|-------------------------------------|-------------------------------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Propagation Delay, Switch In to Out | $t_{\text{PLH}}$ , $t_{\text{PHL}}$ | 0       | 2       | 50pF            | 25°C             |     |     | 60  | ns   |
|                                     |                                     | 0       | 2       |                 | - 40°C to +85°C  |     |     | 75  |      |
|                                     |                                     | 0       | 2       |                 | - 55°C to +125°C |     |     | 90  |      |
|                                     |                                     | 0       | 4.5     |                 | 25°C             |     |     | 12  |      |
|                                     |                                     | 0       | 4.5     |                 | - 40°C to +85°C  |     |     | 15  |      |
|                                     |                                     | 0       | 4.5     |                 | - 55°C to +125°C |     |     | 18  |      |
|                                     |                                     | 0       | 6       |                 | 25°C             |     |     | 10  |      |
|                                     |                                     | 0       | 6       |                 | - 40°C to +85°C  |     |     | 13  |      |
|                                     |                                     | 0       | 6       |                 | - 55°C to +125°C |     |     | 15  |      |
|                                     |                                     | -4.5    | 4.5     |                 | 25°C             |     |     | 8   |      |
|                                     |                                     | -4.5    | 4.5     |                 | - 40°C to +85°C  |     |     | 10  |      |
|                                     |                                     | -4.5    | 4.5     |                 | - 55°C to +125°C |     |     | 12  |      |

over operating free-air temperature range (unless otherwise noted)

| Parameter                         |                                     | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|-----------------------------------|-------------------------------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Turn<br>"ON"<br>Time !E<br>to Out | t <sub>PZH</sub> , t <sub>PZL</sub> | 0       | 2       | 50pF            | 25°C             |     |     | 205 | ns   |
|                                   |                                     | 0       | 2       |                 | - 40°C to +85°C  |     |     | 255 |      |
|                                   |                                     | 0       | 2       |                 | - 55°C to +125°C |     |     | 310 |      |
|                                   |                                     | 0       | 4.5     |                 | 25°C             |     |     | 41  |      |
|                                   |                                     | 0       | 4.5     |                 | - 40°C to +85°C  |     |     | 51  |      |
|                                   |                                     | 0       | 4.5     |                 | - 55°C to +125°C |     |     | 62  |      |
|                                   |                                     | 0       | 6       |                 | 25°C             |     |     | 35  |      |
|                                   |                                     | 0       | 6       |                 | - 40°C to +85°C  |     |     | 43  |      |
|                                   |                                     | 0       | 6       |                 | - 55°C to +125°C |     |     | 53  |      |
|                                   |                                     | -4.5    | 4.5     |                 | 25°C             |     |     | 37  |      |
|                                   |                                     | -4.5    | 4.5     |                 | - 40°C to +85°C  |     |     | 47  |      |
|                                   |                                     | -4.5    | 4.5     |                 | - 55°C to +125°C |     |     | 56  |      |
|                                   |                                     | -       | 5       | 15pF            | 25°C             |     |     | 8   |      |
| Turn<br>"ON"<br>Time nS<br>to Out | t <sub>PZH</sub> , t <sub>PZL</sub> | 0       | 2       | 50pF            | 25°C             |     |     | 175 | ns   |
|                                   |                                     | 0       | 2       |                 | - 40°C to +85°C  |     |     | 220 |      |
|                                   |                                     | 0       | 2       |                 | - 55°C to +125°C |     |     | 265 |      |
|                                   |                                     | 0       | 4.5     |                 | 25°C             |     |     | 35  |      |
|                                   |                                     | 0       | 4.5     |                 | - 40°C to +85°C  |     |     | 44  |      |
|                                   |                                     | 0       | 4.5     |                 | - 55°C to +125°C |     |     | 53  |      |
|                                   |                                     | 0       | 6       |                 | 25°C             |     |     | 30  |      |
|                                   |                                     | 0       | 6       |                 | - 40°C to +85°C  |     |     | 37  |      |
|                                   |                                     | 0       | 6       |                 | - 55°C to +125°C |     |     | 45  |      |
|                                   |                                     | -4.5    | 4.5     |                 | 25°C             |     |     | 34  |      |
|                                   |                                     | -4.5    | 4.5     |                 | - 40°C to +85°C  |     |     | 43  |      |
|                                   |                                     | -4.5    | 4.5     |                 | - 55°C to +125°C |     |     | 51  |      |
|                                   |                                     | -       | 5       | 15pF            | 25°C             |     |     | 14  |      |

over operating free-air temperature range (unless otherwise noted)

| Parameter                          |                       | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|------------------------------------|-----------------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Turn<br>"OFF"<br>Time !E<br>to Out | $t_{PLZ}$ , $t_{PHZ}$ | 0       | 2       | 50pF            | 25°C             |     |     | 205 | ns   |
|                                    |                       | 0       | 2       |                 | - 40°C to +85°C  |     |     | 255 | ns   |
|                                    |                       | 0       | 2       |                 | - 55°C to +125°C |     |     | 310 | ns   |
|                                    |                       | 0       | 4.5     |                 | 25°C             |     |     | 41  | ns   |
|                                    |                       | 0       | 4.5     |                 | - 40°C to +85°C  |     |     | 51  | ns   |
|                                    |                       | 0       | 4.5     |                 | - 55°C to +125°C |     |     | 62  | ns   |
|                                    |                       | 0       | 6       |                 | 25°C             |     |     | 35  | ns   |
|                                    |                       | 0       | 6       |                 | - 40°C to +85°C  |     |     | 43  | ns   |
|                                    |                       | 0       | 6       |                 | - 55°C to +125°C |     |     | 53  | ns   |
|                                    |                       | -4.5    | 4.5     |                 | 25°C             |     |     | 37  | ns   |
|                                    |                       | -4.5    | 4.5     |                 | - 40°C to +85°C  |     |     | 47  | ns   |
|                                    |                       | -4.5    | 4.5     |                 | - 55°C to +125°C |     |     | 56  | ns   |
|                                    |                       | -       | 5       | 15pF            | 25°C             |     |     | 8   | ns   |
| Turn<br>"OFF"<br>Time nS<br>to Out | $t_{PLZ}$ , $t_{PHZ}$ | 0       | 2       | 50pF            | 25°C             |     |     | 175 | ns   |
|                                    |                       | 0       | 2       |                 | - 40°C to +85°C  |     |     | 220 |      |
|                                    |                       | 0       | 2       |                 | - 55°C to +125°C |     |     | 265 |      |
|                                    |                       | 0       | 4.5     |                 | 25°C             |     |     | 35  |      |
|                                    |                       | 0       | 4.5     |                 | - 40°C to +85°C  |     |     | 44  |      |
|                                    |                       | 0       | 4.5     |                 | - 55°C to +125°C |     |     | 53  |      |
|                                    |                       | 0       | 6       |                 | 25°C             |     |     | 30  |      |
|                                    |                       | 0       | 6       |                 | - 40°C to +85°C  |     |     | 37  |      |
|                                    |                       | 0       | 6       |                 | - 55°C to +125°C |     |     | 45  |      |
|                                    |                       | -4.5    | 4.5     |                 | 25°C             |     |     | 34  |      |
|                                    |                       | -4.5    | 4.5     |                 | - 40°C to +85°C  |     |     | 43  |      |
|                                    |                       | -4.5    | 4.5     |                 | - 55°C to +125°C |     |     | 51  |      |
|                                    |                       | -       | 5       | 15pF            | 25°C             |     |     | 14  |      |

over operating free-air temperature range (unless otherwise noted)

| Parameter                        |                 | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|----------------------------------|-----------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Input (Control) Capacitance      | C <sub>I</sub>  | -       | -       | -               | 25°C             |     |     | 10  | pF   |
| Input (Control) Capacitance      |                 | -       | -       |                 | - 40°C to +85°C  |     |     | 10  |      |
| Input (Control) Capacitance      |                 | -       | -       |                 | - 55°C to +125°C |     |     | 10  |      |
| Power dissipation capacitance(1) | C <sub>PD</sub> | -       | 5       |                 | 25°C             |     | 42  |     |      |

## 10 Switching Characteristics HCT

over operating free-air temperature range (unless otherwise noted)

| Parameter                           |                                     | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |  |
|-------------------------------------|-------------------------------------|---------|---------|-----------------|------------------|-----|-----|-----|------|--|
| Propagation Delay, Switch In to Out | t <sub>PLH</sub> , t <sub>PHL</sub> | 0       | 4.5     | 50pF            | 25°C             |     |     | 12  | ns   |  |
|                                     |                                     |         |         |                 | – 40°C to +85°C  |     |     | 15  |      |  |
|                                     |                                     |         |         |                 | – 55°C to +125°C |     |     | 18  |      |  |
|                                     |                                     | -4.5    | 4.5     |                 | 25°C             |     |     | 8   |      |  |
|                                     |                                     |         |         |                 | – 40°C to +85°C  |     |     | 10  |      |  |
|                                     |                                     |         |         |                 | – 55°C to +125°C |     |     | 12  |      |  |

over operating free-air temperature range (unless otherwise noted)

| Parameter                |            | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|--------------------------|------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Turn "ON" Time !E to Out | tPZH, tPZL | 0       | 4.5     | 50pF            | 25°C             |     |     | 44  | ns   |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 55  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 66  |      |
|                          |            | -4.5    | 4.5     |                 | 25°C             |     |     | 42  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 53  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 63  |      |
|                          |            | -       | 5       | 15pF            | 25°C             |     | 18  |     |      |
|                          |            | 0       | 4.5     | 50pF            | 25°C             |     |     | 56  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 70  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 85  |      |
|                          |            | -4.5    | 4.5     |                 | 25°C             |     |     | 42  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 53  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 63  |      |
|                          |            | -       | 5       | 15pF            | 25°C             |     | 24  |     |      |
| Turn "ON" Time nS to Out | tPZH, tPZL | 0       | 4.5     | 50pF            | 25°C             |     |     | 40  | ns   |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 53  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 60  |      |
|                          |            | -4.5    | 4.5     |                 | 25°C             |     |     | 34  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 43  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 51  |      |
|                          |            | 0       | 5       | 15pF            | 25°C             |     | 17  |     |      |
|                          |            | 0       | 4.5     | 50pF            | 25°C             |     |     | 50  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 63  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 75  |      |
|                          |            | -4.5    | 4.5     |                 | 25°C             |     |     | 34  |      |
|                          |            |         |         |                 | - 40°C to +85°C  |     |     | 43  |      |
|                          |            |         |         |                 | - 55°C to +125°C |     |     | 51  |      |
|                          |            | -       | 5       | 15pF            | 25°C             |     | 18  |     |      |

over operating free-air temperature range (unless otherwise noted)

| Parameter                                       |                                     | VEE (V) | VCC (V) | Test Conditions |                  | MIN | NOM | MAX | UNIT |
|-------------------------------------------------|-------------------------------------|---------|---------|-----------------|------------------|-----|-----|-----|------|
| Turn<br>"OFF"<br>Time t <sub>IE</sub><br>to Out | t <sub>PLZ</sub> , t <sub>PHZ</sub> | 0       | 4.5     | 50pF            | 25°C             |     |     | 50  | ns   |
|                                                 |                                     |         |         |                 | – 40°C to +85°C  |     |     | 63  |      |
|                                                 |                                     |         |         |                 | – 55°C to +125°C |     |     | 75  |      |
|                                                 |                                     | –4.5    | 4.5     | 50pF            | 25°C             |     |     | 46  |      |
|                                                 |                                     |         |         |                 | – 40°C to +85°C  |     |     | 58  |      |
|                                                 |                                     |         |         |                 | – 55°C to +125°C |     |     | 69  |      |
|                                                 |                                     | –       | 5       | 15pF            | 25°C             |     |     | 21  |      |
| Turn<br>"OFF"<br>Time t <sub>NS</sub><br>to Out | t <sub>PLZ</sub> , t <sub>PHZ</sub> | 0       | 4.5     | 50pF            | 25°C             |     |     | 44  | ns   |
|                                                 |                                     |         |         |                 | – 40°C to +85°C  |     |     | 55  |      |
|                                                 |                                     |         |         |                 | – 55°C to +125°C |     |     | 66  |      |
|                                                 |                                     | –4.5    | 4.5     | 50pF            | 25°C             |     |     | 40  |      |
|                                                 |                                     |         |         |                 | – 40°C to +85°C  |     |     | 50  |      |
|                                                 |                                     |         |         |                 | – 55°C to +125°C |     |     | 60  |      |
|                                                 |                                     | –       | 5       | 15pF            | 25°C             |     |     | 18  |      |
| Input<br>(Control)<br>Capacitance               | C <sub>I</sub>                      | –       | –       | –               | 25°C             |     |     | 10  | pF   |
|                                                 |                                     | –       | –       | –               | – 40°C to +85°C  |     |     | 10  |      |
|                                                 |                                     | –       | –       | –               | – 55°C to +125°C |     |     | 10  |      |
| Power<br>dissipation<br>capacitance(1)          | C <sub>PD</sub>                     | –       | 5       | –               | 25°C             |     |     | 47  |      |

## 11 Analog Channel Specifications

over operating free-air temperature range (unless otherwise noted)

| Parameter                                                       | Test Conditions                           |  | HC, HCT TYPES | V <sub>CC</sub> (V) | MIN | NOM   | MAX | UNIT |
|-----------------------------------------------------------------|-------------------------------------------|--|---------------|---------------------|-----|-------|-----|------|
| f <sub>MAX</sub><br>Minimum switch frequency response at – 3 dB |                                           |  | HC            | 4.5                 |     | 200   |     | MHz  |
|                                                                 |                                           |  | HCT           | 4.5                 |     | 200   |     |      |
| THD<br>Sine-wave distortion                                     | 1kHz, V <sub>IS</sub> = 4V <sub>P-P</sub> |  | HC            | 4.5                 |     | 0.078 |     | %    |
|                                                                 | 1kHz, V <sub>IS</sub> = 8V <sub>P-P</sub> |  |               | 9                   |     | 0.018 |     |      |
|                                                                 | 1kHz, V <sub>IS</sub> = 4V <sub>P-P</sub> |  | HCT           | 4.5                 |     | 0.078 |     |      |
|                                                                 | 1kHz, V <sub>IS</sub> = 8V <sub>P-P</sub> |  |               | 9                   |     | 0.018 |     |      |
| Switch "OFF" Signal Feedthrough                                 |                                           |  | HC            | 4.5                 |     | –62   |     | dB   |
|                                                                 |                                           |  | HCT           | 4.5                 |     | –62   |     |      |

over operating free-air temperature range (unless otherwise noted)

| Parameter                                | Test Conditions |  | HC, HCT<br>TYPES | V <sub>CC</sub> (V) | MIN | NOM | MAX | UNIT |
|------------------------------------------|-----------------|--|------------------|---------------------|-----|-----|-----|------|
| Switch Input Capacitance, C <sub>S</sub> |                 |  | HC               | -                   |     | 5   |     | pF   |
|                                          |                 |  | HCT              | -                   |     | 5   |     |      |

12 HCT Input Loading Table

| INPUT | UNIT LOADS <sup>(1)</sup> |
|-------|---------------------------|
| All   | 0.5                       |

(1) Unit Load is  $\Delta I_{CC}$  limit specified in DC Electrical Table, e.g., 360  $\mu$ A max at 25°C

13 Recommended Operating Area as a Function of Supply Voltage




图 13-1.




图 13-2.

## 14 Typical Performance Curves




图 14-1. Typical On Resistance vs Input Signal Voltage




图 14-2. Typical On Resistance vs Input Signal Voltage




图 14-3. Switch Frequency Response




图 14-4. Switch-Off Signal Feedthrough and Crosstalk vs Frequency

## 15 Parameter Measurement Information




图 15-1. Crosstalk Between Two Switches Test Circuit




图 15-2. Frequency Response Test Circuit




图 15-3. Total Harmonic Distortion Test Circuit




图 15-4. Control-To-Switch Feedthrough Noise Test Circuit




图 15-5. Switch Off Signal Feedthrough




图 15-6. Switch Propagation Delay Times





图 15-7. Switch Turn-On and Turn-Off Propagation Delay Times Waveforms

# 16 Detailed Description

## 16.1 Functional Block Diagram



## 16.2 Device Functional Modes

表 16-1. Truth Table <sup>(1)</sup>

| INPUTS |   | SWITCH |
|--------|---|--------|
| E      | S |        |
| L      | L | OFF    |
| L      | H | ON     |
| H      | X | OFF    |

(1) H = High Level Voltage, L = Low Level Voltage, X = Do not Care

## 17 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

### 17.1 接收文档更新通知

要接收文档更新通知，请导航至 [ti.com](https://ti.com) 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

### 17.2 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

### 17.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

所有商标均为其各自所有者的财产。

### 17.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

### 17.5 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

## 18 Revision History

注：以前版本的页码可能与当前版本的页码不同

| Changes from Revision D (October 2003) to Revision E (July 2024) | Page               |
|------------------------------------------------------------------|--------------------|
| • 更新了整个文档中的表格、图和交叉参考的编号格式.....                                   | <a href="#">1</a>  |
| • Updated thermal information.....                               | <a href="#">5</a>  |
| • Updated electrical specifications.....                         | <a href="#">6</a>  |
| • Updated switching specifications.....                          | <a href="#">10</a> |
| • Updated analog channel specifications.....                     | <a href="#">15</a> |
| • Updated orderable information.....                             | <a href="#">21</a> |

## 19 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">CD54HC4316F3A</a>  | Active        | Production           | CDIP (J)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC4316F3A       |
| CD54HC4316F3A.A                | Active        | Production           | CDIP (J)   16   | 25   TUBE             | No          | SNPB                                 | N/A for Pkg Type                  | -55 to 125   | CD54HC4316F3A       |
| <a href="#">CD74HC4316E</a>    | NRND          | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC4316E         |
| CD74HC4316E.A                  | NRND          | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HC4316E         |
| <a href="#">CD74HC4316M</a>    | Obsolete      | Production           | SOIC (D)   16   | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HC4316M             |
| <a href="#">CD74HC4316M96</a>  | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC4316M             |
| CD74HC4316M96.A                | Active        | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC4316M             |
| <a href="#">CD74HC4316NSR</a>  | NRND          | Production           | SOP (NS)   16   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC4316M             |
| CD74HC4316NSR.A                | NRND          | Production           | SOP (NS)   16   | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HC4316M             |
| <a href="#">CD74HC4316PW</a>   | Obsolete      | Production           | TSSOP (PW)   16 | -                     | -           | Call TI                              | Call TI                           | -55 to 125   | HJ4316              |
| <a href="#">CD74HC4316PWR</a>  | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HJ4316              |
| CD74HC4316PWR.A                | Active        | Production           | TSSOP (PW)   16 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HJ4316              |
| <a href="#">CD74HCT4316E</a>   | NRND          | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT4316E        |
| CD74HCT4316E.A                 | NRND          | Production           | PDIP (N)   16   | 25   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -55 to 125   | CD74HCT4316E        |
| <a href="#">CD74HCT4316M</a>   | NRND          | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT4316M            |
| CD74HCT4316M.A                 | NRND          | Production           | SOIC (D)   16   | 40   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT4316M            |
| <a href="#">CD74HCT4316M96</a> | NRND          | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT4316M            |
| CD74HCT4316M96.A               | NRND          | Production           | SOIC (D)   16   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -55 to 125   | HCT4316M            |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF CD54HC4316, CD74HC4316 :**

- Catalog : [CD74HC4316](#)
- Military : [CD54HC4316](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Military - QML certified for Military and Defense Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD74HC4316M96  | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD74HC4316NSR  | SOP          | NS              | 16   | 2000 | 330.0              | 16.4               | 8.1     | 10.4    | 2.5     | 12.0    | 16.0   | Q1            |
| CD74HC4316PWR  | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |
| CD74HCT4316M96 | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device         | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD74HC4316M96  | SOIC         | D               | 16   | 2500 | 353.0       | 353.0      | 32.0        |
| CD74HC4316NSR  | SOP          | NS              | 16   | 2000 | 353.0       | 353.0      | 32.0        |
| CD74HC4316PWR  | TSSOP        | PW              | 16   | 2000 | 353.0       | 353.0      | 32.0        |
| CD74HCT4316M96 | SOIC         | D               | 16   | 2500 | 340.5       | 336.1      | 32.0        |

**TUBE**


\*All dimensions are nominal

| Device         | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| CD74HC4316E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4316E    | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4316E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HC4316E.A  | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT4316E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT4316E   | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT4316E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT4316E.A | N            | PDIP         | 16   | 25  | 506    | 13.97  | 11230  | 4.32   |
| CD74HCT4316M   | D            | SOIC         | 16   | 40  | 507    | 8      | 3940   | 4.32   |
| CD74HCT4316M.A | D            | SOIC         | 16   | 40  | 507    | 8      | 3940   | 4.32   |

D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- D. Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.

J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE




| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |



4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.



4220204/B 12/2023

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220204/B 12/2023

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

# EXAMPLE STENCIL DESIGN

PW0016A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220204/B 12/2023

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE




| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.




# PACKAGE OUTLINE

NS0016A

SOP - 2.00 mm max height

SOP



4220735/A 12/2021

## NOTES:



1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.

# EXAMPLE BOARD LAYOUT

NS0016A

SOP - 2.00 mm max height

SOP




SOLDER MASK DETAILS

4220735/A 12/2021

NOTES: (continued)

5. Publication IPC-7351 may have alternate designs.

6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE  
 BASED ON 0.125 mm THICK STENCIL  
 SCALE:7X

4220735/A 12/2021

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月