REF35 超低功耗高精度电压基准

1 特性

- 超低静态电流：
  - 650nA（典型值）
- 初始精度：±0.05%（最大值）
- 温度系数：
  - 12ppm/°C（−40°C 至 105°C 时的最大值）
- 输出 1/f 噪声（0.1Hz 至 10Hz）：3.3ppm$_{P-P}$
- NR 引脚可降低噪声
- EN 引脚可降低关断电流消耗
- 长期稳定性：1k 小时内为 40ppm
- 热迟滞：70ppm
- 额定温度范围：-40°C 至 +105°C
- 工作温度范围：-55°C 至 +125°C
- 输出电流：+10mA，−5mA
- 输入电压：V_{REF} + V_{DO} 至 6V
- 输出电压选项：
  - 1.024V、1.2V、1.25V、1.6V、1.8V、2.048V、2.5V、3.0V、3.3V、4.096V、5.0V
- 小型 6 引脚 SOT−23 封装
- 尺寸超小的 4 引脚 WCSP 封装

2 应用

- 流量变送器
- 血糖监控
- 伺服驱动器控制模块
- 电能质量分析仪
- 故障指示灯
- 示波器
- 过程分析
- 光学模块

3 说明

REF35 是毫微功耗、低漂移、高精度基准器件系列。REF35 系列具有 ±0.05% 初始精度，典型功耗为 650nA。该器件的温度系数 (12ppm/°C) 和长期稳定性（1000 小时内为 40ppm）有助于提高系统稳定性和可靠性。凭借低功耗以及高精度规格，此器件适用于多种便携式应用和低电流应用。

REF35 可提供高达 10mA 电流，噪声为 3.3ppm$_{p-p}$，负载调节为 20ppm/mA。借助这一功能集，REF35 可为精密传感器和 12 至 16 位数据转换器提供强大的低噪声高精度电源。


此系列的额定工作温度范围为 -40°C 至 105°C，并且在 -55°C 至 125°C 也可以正常运行。凭借宽温度范围，此系列适用于工业应用。

REF35 提供 1.024V 至 5.0V 的宽输出电压范围。该器件具有节省空间的 6 引脚 SOT-23 和 4 引脚 WCSP 封装选项。有关可用的电压和封装选项，请联系您当地的 TI 销售代表。

封装信息

器件型号	封装 (1)	封装尺寸（标称值）
REF35xxx	SOT-23 (6)	2.90mm × 1.60mm
	WCSP (4) (2)	1.05mm × 0.84mm

(1) 如需了解所有可用电压选项和封装，请参阅数据表末尾的可订购产品附录。
(2) 产品预发布。



REF35 用例

本文档旨在为方便起见，提供有关 TI 产品中文版本的信息，以确认产品的概要。有关适用的官方英文版本的最新信息，请访问 www.ti.com，其内容始终优先。TI 不保证翻译的准确性和有效性。在实际设计之前，请务必参考最新版本的英文版本。

Table of Contents

1 特性 1
2 应用 1
3 说明 1
4 Revision History 2
5 Device Comparison 3
6 Pin Configuration and Functions 3
7 Specifications 4
7.1 Absolute Maximum Ratings 4
7.2 ESD Ratings 4
7.3 Recommended Operating Conditions 4
7.4 Thermal Information 4
7.5 Electrical Characteristics 5
7.6 Typical Characteristics 7
8 Parameter Measurement Information 12
8.1 Solder Heat Shift 12
8.2 Temperature Coefficient 13
8.3 Long-Term Stability 13
8.4 Thermal Hysteresis 14
8.5 Noise Performance 15
8.6 Power Dissipation 18
9 Detailed Description 19
9.1 Overview 19
9.2 Functional Block Diagram 19
9.3 Feature Description 19
9.4 Device Functional Modes 20
10 Application and Implementation 22
10.1 Application Information 22
10.2 Typical Applications 22
10.3 Power Supply Recommendations 25
10.4 Layout 25
11 Device and Documentation Support 27
11.1 Documentation Support 27
11.2 接收文档更新通知 27
11.3 支持资源 27
11.4 Trademarks 27
11.5 Electrostatic Discharge Caution 27
11.6 术语表 27
12 Mechanical, Packaging, and Orderable Information 27

4 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision * (December 2021) to Revision A (August 2022)	Page
• 量产数据发布	1

Copyright © 2022 Texas Instruments Incorporated

5 Device Comparison

PRODUCT		V_{REF}
SOT-23 (6)	WCSP (4) (1)	
REF35102QDBVR	REF35102YBHR	1.024 V
REF35120QDBVR	REF35120YBHR	1.2 V
REF35125QDBVR	REF35125YBHR	1.25 V
REF35160QDBVR	REF35160YBHR	1.6 V
REF35180QDBVR	REF35180YBHR	1.8 V
REF35205QDBVR	REF35205YBHR	2.048 V
REF35250QDBVR	REF35250YBHR	2.5 V
REF35300QDBVR	REF35300YBHR	3.0 V
REF35330QDBVR	REF35330YBHR	3.3 V
REF35409QDBVR	REF35409YBHR	4.096 V
REF35500QDBVR	REF35500YBHR	5.0 V

(1) Product preview. Contact local TI support for samples.

6 Pin Configuration and Functions





图 6-1. DBV Package
6-Pin SOT-23
Top View



Preview only

图 6-2. YBH Package
4-Pin WCSP
Top View

表 6-1. Pin Functions

PIN			TYPE	DESCRIPTION
NAME	SOT-23	WCSP		
GND	1	B1	Ground	Device ground connection
GND	2	-	Ground	Device ground connection
EN	3	B2	Input	Enable connection. Enables or disables the device.
VIN	4	A2	Power	Input supply voltage connection
NR	5	-	Output	Noise reduction pin. Connect a capacitor to reduce noise.
VREF	6	A1	Output	Reference voltage output

Copyright © 2022 Texas Instruments Incorporated

7 Specifications

7.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) (1)

		MIN	MAX	UNIT
Input voltage	IN	–0.3	6.5	V
Enable voltage	EN	–0.3	IN + 0.3 (2)	V
Output voltage	V_{REF}	–0.3	IN + 0.3 (2)	V
Output short circuit current	I_{SC}		20	mA
Operating temperature range	T_A	–55	125	°C
Storage temperature range	T_{stg}	–65	170	°C

(1) Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.
(2) IN + 0.3 V or 6.5 V, whichever is lower

7.2 ESD Ratings

			VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins (1)	±2000	V
		Charged device model (CDM), per ANSI/ESDA/JEDEC JS-002, all pins (2)	±750	

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
IN	Input voltage (1)	V_{OUT} + V_{DO} (2)		6	V
EN	Enable voltage	0		IN	V
I_L	Output current	–5		10	mA
T_A	Operating temperature	–40	25	125	°C

(1) For V_{REF} = 1.024 V to 1.5 V, minimum V_{IN} = 1.7 V
(2) V_{DO} = Dropout voltage

7.4 Thermal Information

THERMAL METRIC(1)		REF35 DBV (SOT-23) 6 PINS	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance	164.4	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	102.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	59.6	°C/W
Ψ_{JT}	Junction-to-top characterization parameter	44.0	°C/W
Ψ_{JB}	Junction-to-board characterization parameter	59.4	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	N/A	°C/W

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application report.

Copyright © 2022 Texas Instruments Incorporated

7.5 Electrical Characteristics

At V_{IN} = V_{REF} + 0.5 V, V_{EN} = V_{IN}, C_L = 10 µF, C_{IN} = 0.1 µF, I_L = 0 mA, minimum and maximum specifications at T_A = –40℃ to 125℃, typical specifications T_A = 25℃; unless otherwise noted

PARAMETER		TEST CONDITION		MIN	TYP	MAX	UNIT
ACCURACY AND DRIFT							
	Output voltage accuracy	T_A = 25℃		–0.05		0.05	%
	Output voltage temperature coefficient	–40℃ ≤ T_A ≤ 105℃				12	ppm/℃
LINE AND LOAD REGULATION							
$\Delta V_{REF}/\Delta V_{IN}$	Line regulation	V_{REF} < 2.5 V; V_{IN} = V_{REF} + V_{DO} to V_{INMAX}; –40℃ ≤ T_A ≤ 105℃			40	160	ppm/V
		V_{REF} ≥ 2.5 V; V_{IN} = V_{REF} + V_{DO} to V_{INMAX}; –40℃ ≤ T_A ≤ 105℃			40	120	ppm/V
$\Delta V_{REF}/\Delta I_L$	Load regulation	I_L = 0 mA to 10 mA, V_{IN} = V_{REF} + V_{DO}	Source		20	60	ppm/mA
		I_L = 0 mA to 5 mA, V_{IN} = V_{REF} + V_{DO}	Sink		40	350	ppm/mA
POWER SUPPLY							
V_{IN}	Input voltage (1)			V_{REF} + V_{DO}		6	V
I_Q	Quiescent current	Active mode	T_A = 25℃		0.65	0.9	µA
			–40℃ ≤ T_A ≤ 85℃			1.3	
			–40℃ ≤ T_A ≤ 125℃			2.6	
		Shutdown mode	T_A = 25℃			0.1	
			–40℃ ≤ T_A ≤ 125℃			0.5	
V_{EN}	Enable pin voltage	Active mode (EN = 1 or Float)		0.7 x V_{IN}			V
		Shutdown mode (EN = 0)				0.3 x V_{IN}	
I_{EN}	Enable pin current	V_{EN} = V_{IN}			0.05	0.1	uA
V_{DO}	Dropout voltage	I_L = 5 mA				120	mV
		I_L = 10 mA				250	
I_{SC}	Short circuit current, Sourcing	V_{REF} = 0 V, T_A = 25℃			33		mA
I_{SC}	Short circuit current, Sinking	V_{REF} = V_{IN} V, T_A = 25℃			21		mA
TURN-ON TIME							
t_{ON}	Turn-on time (2)	0.1% settling, C_L = 1 µF, V_{REF} = 2.5 V			2		ms
NOISE							
e_n	Output voltage noise	f = 10 Hz to 1 kHz, C_L = 1 µF			0.7		ppm_{rms}
e_{np-p}	Low-frequency noise	f = 0.1 Hz to 10 Hz, V_{REF} ≥ 2.5 V			3.8		ppm_{p-p}
		f = 0.1 Hz to 10 Hz, V_{REF} < 2.5 V			3.3		ppm_{p-p}
HYSTERESIS AND LONG-TERM STABILITY							
	Long-term stability	0 to 1000h at 35°C			40		ppm
	Output voltage hysteresis	25°C, –40°C, 105°C, 25°C (cycle 1)			70		ppm
	Output voltage hysteresis	25°C, –40°C, 105°C, 25°C (cycle 2)			20		ppm
	Output voltage hysteresis	25°C, –40°C, 85°C, 25°C (cycle 1)			50		ppm
	Output voltage hysteresis	25°C, –40°C, 85°C, 25°C (cycle 2)			13		ppm
STABLE CAPACITANCE RANGE							

Copyright © 2022 Texas Instruments Incorporated

At V_{IN} = V_{REF} + 0.5 V, V_{EN} = V_{IN}, C_L = 10 µF, C_{IN} = 0.1 µF, I_L = 0 mA, minimum and maximum specifications at T_A = –40℃ to 125℃, typical specifications T_A = 25℃; unless otherwise noted

PARAMETER		TEST CONDITION	MIN	TYP	MAX	UNIT
	Input capacitor range		0.1			µF
	Output capacitor range (3)		0.1		10	µF

(1) For V_{REF} = 1.024 V to 1.5 V, minimum V_{IN} = 1.7 V
(2) Scales linearly with V_{REF}.
(3) ESR for the capacitor <= 400 mΩ

Copyright © 2022 Texas Instruments Incorporated

7.6 Typical Characteristics

at T_A = 25°C, V_{IN} = V_{EN} = V_{REF} + 0.3 V, I_L = 0 mA, C_L = 10 µF, C_{IN} = 0.1 µF (unless otherwise noted)




图 7-1. Output Voltage Drift vs Free-Air Temperature




图 7-2. Temperature Coefficient Distribution (V_{REF} = 1.25 V)




图 7-3. Temperature Coefficient Distribution (V_{REF} = 2.5 V)




图 7-4. Temperature Coefficient Distribution (V_{REF} = 5.0 V)




图 7-5. Initial Accuracy Distribution




图 7-6. 0.1 Hz to 10 Hz Noise Distribution (V_{REF} = 1.25 V, C_{NR} = Open, I_L = 0 mA)

Copyright © 2022 Texas Instruments Incorporated

7.6 Typical Characteristics (continued)

at T_A = 25°C, V_{IN} = V_{EN} = V_{REF} + 0.3 V, I_L = 0 mA, C_L = 10 µF, C_{IN} = 0.1 µF (unless otherwise noted)




图 7-7. 0.1 Hz to 10 Hz Noise Distribution (V_{REF} = 2.5 V, C_{NR} = Open, I_L = 0 mA)




图 7-8. 0.1 Hz to 10 Hz Noise Distribution (V_{REF} = 5 V, C_{NR} = Open, I_L = 0 mA)




图 7-9. 0.1 Hz to 10 Hz Noise Distribution (V_{REF} = 2.5 V, C_L = 1 µF, I_L = 0 mA)




图 7-10. 0.1 Hz to 10 Hz Noise Distribution (V_{REF} = 2.5 V, C_L = 1 µF, C_{NR} = Open)




图 7-11. Noise Density vs Frequency (V_{REF} = 1.25 V, I_L = 0 mA)




图 7-12. Noise Density vs Frequency (V_{REF} = 2.5 V, I_L = 0 mA)

Copyright © 2022 Texas Instruments Incorporated

7.6 Typical Characteristics (continued)

at T_A = 25°C, V_{IN} = V_{EN} = V_{REF} + 0.3 V, I_L = 0 mA, C_L = 10 µF, C_{IN} = 0.1 µF (unless otherwise noted)




图 7-13. Noise Density vs Frequency (V_{REF} = 5 V, I_L = 0 mA)




图 7-14. Load Regulation (Sourcing 10 mA) vs Free-Air Temperature




图 7-15. Load Regulation (Sinking 5 mA) vs Free-Air Temperature




图 7-16. Load Transient Response (V_{REF} = 2.5 V, C_L = 10 µF)




图 7-17. Load Transient Response (V_{REF} = 2.5 V, C_L = 10 µF)




图 7-18. Load Transient Response (V_{REF} = 2.5 V, C_L = 1 µF)

Copyright © 2022 Texas Instruments Incorporated

7.6 Typical Characteristics (continued)

at T_A = 25°C, V_{IN} = V_{EN} = V_{REF} + 0.3 V, I_L = 0 mA, C_L = 10 µF, C_{IN} = 0.1 µF (unless otherwise noted)




图 7-19. Load Transient Response (V_{REF} = 2.5 V, C_L = 1 µF)




图 7-20. Load Transient Response (V_{REF} = 1.25 V, C_L = 1 µF)




图 7-21. Load Transient Response (V_{REF} = 1.25 V, C_L = 1 µF)




图 7-22. Line Regulation vs Free-Air Temperature




图 7-23. Line Transient Response (V_{REF} = 1.25 V, C_L = 1 µF)




图 7-24. Line Transient Response (V_{REF} = 2.5 V, C_L = 1 µF)

Copyright © 2022 Texas Instruments Incorporated

7.6 Typical Characteristics (continued)

at T_A = 25°C, V_{IN} = V_{EN} = V_{REF} + 0.3 V, I_L = 0 mA, C_L = 10 µF, C_{IN} = 0.1 µF (unless otherwise noted)




图 7-25. Power Supply Rejection Ratio (V_{REF} = 2.5 V, I_L = 0 mA)




图 7-26. Output Impedance




图 7-27. Quiescent Current vs Free-Air Temperature




图 7-28. Dropout Voltage vs Free-Air Temperature




图 7-29. Solder Heat Shift Distribution




图 7-30. Long Term Stability - 2000 hours (V_{REF})

8 Parameter Measurement Information

8.1 Solder Heat Shift

The materials used in the manufacture of the REF35 have differing coefficients of thermal expansion, resulting in stress on the device die when the part is heated. Mechanical and thermal stress on the device die can cause the output voltages to shift, degrading the initial accuracy specifications of the product. Reflow soldering is a common cause of this error.

To illustrate this effect, a total of 32 devices were soldered on one printed circuit board using lead-free solder paste and the paste manufacturer suggested reflow profile. 图 8-1 shows the reflow profile. The printed circuit board is comprised of FR4 material. The board thickness is 1.66 mm and the area is 174 mm × 135 mm.




图 8-1. Reflow Profile

The reference output voltage is measured before and after the reflow process; 图 8-2 shows the typical shift. Although all tested units exhibit very low shifts (< 0.03%), higher shifts are also possible depending on the size, thickness, and material of the printed circuit board (PCB). An important note is that the histograms display the typical shift for exposure to a single reflow profile. Exposure to multiple reflows, as is common on PCBs with surface-mount components on both sides, causes additional shifts in the output bias voltage. If the PCB is exposed to multiple reflows, the device must be soldered in the last pass to minimize its exposure to thermal stress.




图 8-2. Solder Heat Shift Distribution, V_{REF} (%)

Copyright © 2022 Texas Instruments Incorporated

8.2 Temperature Coefficient

The REF35 is designed and tested for a low output voltage temperature coefficient. The temperature coefficient is defined as the change in output voltage over temperature. The temperature coefficient is calculated using the box method in which a box is formed by the minimum/maximum values for the nominal output voltage over the operating temperature range. REF35 has a low maximum temperature coefficient of 12 ppm/°C from –40°C to +105°C. The box method specifies limits for the temperature error but does not specify the exact shape and slope of the device under test. Due to temperature curvature correction to achieve low-temperature drift, the temperature drift is expected to be non-linear. See TI's Analog Design Journal, *Precision voltage references*, for more information on the box method. Use 方程式 1 for the box method.

$$\text{Drift} = \left(\frac{V_{REF(MAX)} - V_{REF(MIN)}}{V_{REF(25°C)} \times \text{Temperature Range}} \right) \times 10^6 \quad (1)$$

图 8-3 shows a typical voltage versus temperature curves for various reference voltages. 图 8-4 shows the distribution of temperature coefficients for REF35250 devices.




图 8-3. Output Voltage Drift Vs Free-Air Temperature




图 8-4. Temperature Coefficient Distribution

8.3 Long-Term Stability

One of the key performance parameters of the REF35 references is long-term stability also known as long-term drift. The long-term stability value is tested in a setup that reflects standard PCB board manufacturing practices. The boards are made of standard FR4 material and the board does not have special cuts or grooves around the devices to relieve the mechanical stress of the PCB. The devices and boards in this test do not undergo high temperature burn in post-soldering prior to testing. These conditions reflect a real world use case scenario and common manufacturing techniques.

During the long-term stability testing, precautions are taken to ensure that only the long-term stability drift is measured. The boards are maintained at 35°C in an oil bath. The oil bath ensures that the temperature is constant across the device over time compared to an air oven. The measurements are captured every 30 minutes with a calibrated 8.5 digit multimeter.

The typical long-term stability characteristic is expressed as a deviation of the reference voltage output over time.

图 8-5 shows that the typical drift value for the REF35 6-pin SOT-23 package is 40 ppm from 0 to 1000 hours and 55 ppm from 0 to 2000 hours. It is important to understand that long-term stability is not ensured by design and that the value is typical. The REF35 will experience the highest drift in the initial 1000 hr. Subsequent deviation is typically lower than first 1000 hr.

Copyright © 2022 Texas Instruments Incorporated




图 8-5. Long Term Stability - 2000 hours (V_{REF})

8.4 Thermal Hysteresis

Thermal hysteresis is measured with the REF35 soldered to a PCB, similar to a real-world application. Thermal hysteresis for the device is defined as the change in output voltage after operating the device at 25°C, cycling the device through the specified temperature range, and returning to 25°C. The PCB was baked at 150°C for 30 minutes before thermal hysteresis was measured. Use 方程式 2 to calculate the thermal hysteresis:

$$V_{HYST} = \left(\frac{| V_{PRE} - V_{POST} |}{V_{NOM}} \right) \times 10^6 \text{ (ppm)} \quad (2)$$

where

- V_{HYST} = thermal hysteresis (in units of ppm)
- V_{NOM} = the specified output voltage
- V_{PRE} = output voltage measured at 25°C pre-temperature cycling
- V_{POST} = output voltage measured after the device has cycled from 25°C through the specified temperature range of – 40°C to +85°C or – 40°C to +105°C and returns to 25°C.

The graphs below show the typical thermal hysteresis distribution across various temperature ranges in two cycles.

Copyright © 2022 Texas Instruments Incorporated




图 8-6. Thermal Hysteresis Distribution – 40ºC to 85ºC, Cycle 1




图 8-7. Thermal Hysteresis Distribution – 40ºC to 85ºC, Cycle 2




图 8-8. Thermal Hysteresis Distribution – 40ºC to 105ºC, Cycle 1




图 8-9. Thermal Hysteresis Distribution – 40ºC to 105ºC, Cycle 2

8.5 Noise Performance

The reference pin output noise is categorized as low frequency and broadband noise. The following sections describe these categories in detail.

8.5.1 Low-Frequency (1/f) Noise

Flicker noise, also known as 1/f noise, is a low-frequency noise that affects the device output voltage which can affect precision measurements in ADCs. This noise increases proportionally with output voltage and operating temperature. Noise is measured by filtering the output from 0.1 Hz to 10 Hz. The 1/f noise is an extremely low value, therefore the frequency of interest must be amplified and band-pass filtered. This is done by using a high-pass filter to block the DC voltage. The resulting noise is then amplified by a gain of 1000. The bandpass filter is created by a series of high-pass and low-pass filter that adds additional gain to make it more visible on a oscilloscope as shown in 图 8-10. 图 8-11 shows the effect of flicker noise over 10 second for REF35250. Flicker noise must be tested in a Faraday cage enclosure to block environmental noise.

Copyright © 2022 Texas Instruments Incorporated




图 8-10. Low-Frequency (1/f) Noise Test Setup




图 8-11. 0.1 Hz to 10 Hz Voltage Noise

图 8-12 shows the typical 1/f noise (0.1 Hz to 10 Hz) distribution across various load conditions. REF35 device also offers noise reduction functionality by adding an optional capacitor between NR (pin 5) and ground pins.

图 8-13 shows the typical 1/f noise (0.1 Hz to 10 Hz) distribution across REF35 devices with various capacitance between NR pin and GND.

Copyright © 2022 Texas Instruments Incorporated




图 8-12. 0.1 Hz to 10 Hz Noise Distribution vs Load Conditions




图 8-13. 0.1 Hz to 10 Hz Noise Distribution vs NR Capacitance

8.5.2 Broadband Noise

Broadband noise is a noise that appears at higher frequency compared to 1/f noise. The broadband noise is measured by high-pass filtering the output of the reference device, followed by a gain stage and measuring the result on a spectrum analyzer as shown in 图 8-14.




图 8-14. Broadband Noise Test Setup

For noise sensitive designs, a low-pass filter can be used to reduce broadband output noise. When designing a low-pass filter, take special care to ensure the output impedance of the filter does not degrade AC performance. This can occur in RC low-pass filters where a large series resistance can impact the load transients due to output current fluctuations. The REF35 device also offers noise reduction functionality by adding an optional capacitor between NR (pin 5) and ground pins. 图 8-15 and 图 8-16 show the noise spectrum for REF35250 and REF35500 devices respectively across various load capacitance.

Copyright © 2022 Texas Instruments Incorporated




图 8-15. Noise Spectrum 10 Hz to 100 kHz (V_{REF} = 2.5 V)




图 8-16. Noise Spectrum 10 Hz to 100 kHz (V_{REF} = 5 V)

8.6 Power Dissipation

The REF35 voltage references are capable of source up to 10 mA and sink up to 5 mA of load current across the rated input voltage range. However, when used in applications subject to high ambient temperatures, the input voltage and load current must be carefully monitored to ensure that the device does not exceeded its maximum power dissipation rating. The maximum power dissipation of the device can be calculated with 方程式 3:

$$T_J = T_A + P_D \times R_{\theta JA} \quad (3)$$

where

- P_D is the device power dissipation
- T_J is the device junction temperature
- T_A is the ambient temperature
- $R_{\theta JA}$ is the package (junction-to-air) thermal resistance

Because of this relationship, acceptable load current in high temperature conditions may be less than the maximum current-sourcing capability of the device. In no case should the device be operated outside of its maximum power rating because doing so can result in premature failure or permanent damage to the device.


Copyright © 2022 Texas Instruments Incorporated

9 Detailed Description

9.1 Overview

The REF35 is family of ultra-low current, low-noise, precision band-gap voltage references that are specifically designed for excellent initial voltage accuracy and drift. The *Functional Block Diagram* is a simplified block diagram of the REF35 showing basic band-gap topology.

9.2 Functional Block Diagram



9.3 Feature Description

9.3.1 Supply Voltage

The REF35 family of references features an extremely low dropout voltage. For 10 mA loaded conditions, a maximum dropout voltage is 250 mV. 图 7-28 shows a typical dropout voltage (V_{DO}) versus load current. The device supports operation with input voltage range from V_{REF} + V_{DO} to 6 V. The typical quiescent current is 650 nA and maximum quiescent current over temperature is only 2.6 μA. The low dropout voltage coupled with ultra-low current enable the operation across multiple battery powered applications.

9.3.2 EN Pin

The REF35 family supports device enable and disable functionality through logic level control on EN pin. The EN pin of REF35 does not use an internal pull-up resistor. Instead, the pin uses new 'clean EN' technology. This allows the EN pin to be in a no connect condition at start-up, and no extra current is drawn from the supply when the EN pin is pulled low in shutdown mode. When EN pin is pulled high or left unconnected at start-up, the device is in active mode. When EN pin is driven by an open-drain output, a pull-up resistor to VIN is required. The device must be in active mode for normal operation. The EN pin must not be pulled higher than VIN supply voltage.

The device can be placed in shutdown mode by pulling the EN pin low. When in shutdown mode, the output of the device becomes high impedance and the quiescent current of the device drops to 100 nA at room temperature. When changing the device state from shutdown to active state, ensure the EN pin is not left floating.

Also note that for applications where EN pin is no-connect, total parasitic capacitance on EN pin should be restricted within 30 pF.

See the *Electrical Characteristics* table for logic high and logic low voltage levels.

9.3.3 NR Pin

The REF35 pin allows access to the band-gap through the NR pin. Placing a capacitor from the NR pin to GND creates a low-pass filter in combination with the internal resistance of 60 kΩ. Leakage of the capacitance directly impacts the accuracy and temperature drift. If NR functionality is used, choose a low leakage capacitor. A capacitance of 1 μF creates a low-pass filter with corner frequency around 2.7 Hz. Such a filter decreases the overall noise on the VREF pin. Higher capacitance results in a lower filter cut off frequency, further reducing output noise. Please note, using the capacitor on NR pin also increases start-up time.

Copyright © 2022 Texas Instruments Incorporated

9.4 Device Functional Modes

9.4.1 Basic Connections

图 9-1 shows the typical connections for the REF35. TI recommends a supply bypass capacitor (C_{IN}) ranging from 0.1 µF to 10 µF. A 0.1 µF to 10 µF output capacitor (C_L) must be connected from REF to GND. The equivalent series resistance (ESR) value of C_L must be lower than 400 mΩ to ensure output stability.




图 9-1. Basic Connections

9.4.2 Start-Up

图 9-2 shows the start-up behavior of REF35250 device with 1 µF load capacitance. REF35 device ensures the output voltage settles to the expected output voltage within specified accuracy without oscillations. The start-up time is dependent on the output voltage variant, output capacitance and NR pin capacitance. Higher capacitance leads to longer start-up time.




图 9-2. REF35250 Start-Up Behavior, C_L = 1 µF

9.4.3 Output Transient Behavior

The REF35 output buffer is capable of sourcing 10 mA load current as well as sink 5 mA of load current. The output stage is designed using class AB architecture with ultra-low quiescent current. This architecture avoids the dead zone around the no load condition. The output buffer uses a fast start-up implementation to achieve 2ms typical turn-on time at C_L = 1 µF and no-load current condition.

图 9-3 and 图 9-4 show the output settling behavior for light load transient and high load transient respectively.

Copyright © 2022 Texas Instruments Incorporated




图 9-3. Load Transient Response 0 µA to 100 µA, C_L = 1 µF




图 9-4. Load Transient Response 1 mA to 10 mA, C_L = 1 µF

Copyright © 2022 Texas Instruments Incorporated

10 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI’s customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

10.1 Application Information

REF35 with low current consumption and class leading performance specifications is suitable reference for multiple applications. The device can also be used as a precision low noise power supply to sensor or data converter instead of traditional LDO or DC/DC based power supply. Basic applications includes positive/negative voltage reference and data acquisition systems. The table below shows the typical application of REF35 and its companion ADC/DAC.

表 10-1. Typical Applications and Companion ADC/DAC

APPLICATIONS	ADC/DAC
PLC - DCS	ADS7028, DAC8881, ADS1287, ADS7953
Rack Server	ADS7028, ADS7128, ADS7138
Field Transmitters - Pressure, Flow	ADS124S08
Optical Module, Optical Line Card	ADS7068, ADS7138
Medical Blood Glucose Meter	ADS1112
Power quality analyzer	ADC3662
Thermal imaging	ADC3541

10.2 Typical Applications

10.2.1 Negative Reference Voltage

For applications requiring a negative and positive reference voltage, the REF35 and OPA735 can be used to provide a dual-supply reference from a 5 V supply. 图 10-1 shows the REF35250 used to provide a 2.5 V supply reference voltage. The low drift performance of the REF35250 complements the low offset voltage and zero drift of the OPA735 to provide an accurate solution for split-supply applications. Take care to match the temperature coefficients of R1 and R2.




图 10-1. REF35 and OPA735 Create Positive and Negative Reference Voltages

Copyright © 2022 Texas Instruments Incorporated

10.2.2 Precision Power Supply and Reference

图 10-2 shows the basic configuration for the REF35 device as precision power supply to ADS7038 data converter which uses its power supply AVDD as reference. Connect bypass capacitors according to the guidelines in the *Input and Output Capacitors* section.




图 10-2. Basic Reference Connection

10.2.2.1 Design Requirements

A detailed design procedure is described based on a design example. For this design example, use the parameters listed in 表 10-2 as the input parameters.

表 10-2. Design Example Parameters

DESIGN PARAMETER	VALUE
Input voltage range V_{IN}	0 V - 5 V
Output resolution	12-bit
REF35 input capacitor	1 µF
REF35 output capacitor	10 µF

10.2.2.2 Detailed Design Procedure

10.2.2.2.1 Selection of Reference

The REF35500 reference is selected for this design. The REF35500 device operates of very low quiescent current while offering ±0.05% initial accuracy and very low noise. These parameters help improve system accuracy as compared to external LDO based power supply. The 5 V reference voltage supports the 0 V to 5 V input range specification.

10.2.2.2.2 Input and Output Capacitors

A 1 µF to 10 µF electrolytic or ceramic capacitor can be connected to the input to improve transient response in applications where the supply voltage may fluctuate.

A ceramic capacitor of at least a 0.1 µF must be connected to the output to improve stability and help filter out high frequency noise. Add an additional 10 µF capacitor in parallel to improve transient performance in

Copyright © 2022 Texas Instruments Incorporated

response to sudden changes in load current; however, keep in mind that doing so increases the start-up time of the device.

Best performance and stability is attained with low-ESR, low-inductance ceramic chip-type output capacitors (X5R, X7R, or similar). If using an electrolytic capacitor on the output, place a 0.1 μF ceramic capacitor in parallel to reduce overall ESR on the output. Place the input and output capacitors as close as possible to the device.

10.2.2.2.3 Selection of ADC

ADS7038 12-bit 8 channel multiplexed ADC is chosen for this application. The ADC offers low current operation with averaging mode to increase the resolution to 16-bit with internal averaging modes while operating with slow sampling speed.

10.2.2.3 Application Curves

表 10-3 and 图 10-3 show the captured measurement results for various DC inputs. The ADC output is captured and analyzed for output accuracy error and code spread with REF35500 as power supply versus LDO as power supply.

REF35 offers better accuracy and lower noise than the LDO device at lower quiescent current. This results in lower error in measurement as well as lower ADC output code variation across various OSR settings.

表 10-3. DC Input Performance Test Results

INPUT V	ADC OSR SETTING	REF35500		LDO	
		ERROR	CODE SPREAD	ERROR	CODE SPREAD
1.0 V	0	0.01 mV	32 LSB	8.9 mV	48 LSB
	8	0.3 mV	10 LSB	9.21 mV	16 LSB
	128	0.38 mV	6 LSB	9.26 mV	6 LSB
2.5 V	0	0.69 mV	32 LSB	22.89 mV	64 LSB
	8	1.44 mV	10 LSB	23.63 mV	18 LSB
	128	1.17 mV	3 LSB	23.41 mV	5 LSB
4 V	0	2.27 mV	32 LSB	37.84 mV	48 LSB
	8	3.01 mV	24 LSB	38.62 mV	24 LSB
	128	2.46 mV	3 LSB	38.09 mV	17 LSB

Copyright © 2022 Texas Instruments Incorporated




图 10-3. Error vs Input Voltage

10.3 Power Supply Recommendations

The REF35 family of references feature an extremely low-dropout voltage. These references can be operated with a supply of only 50 mV above the output voltage at no load. TI recommends a supply bypass capacitor ranging between 0.1 µF to 10 µF.

10.4 Layout

10.4.1 Layout Guidelines

图 10-4 shows an example of a PCB layout for a data acquisition system using the REF35. Some key considerations are:

- Connect low-ESR, 0.1 µF ceramic bypass capacitors at V_{IN}, V_{REF} of the REF35.
- Decouple other active devices in the system per the device specifications.
- Using a solid ground plane helps distribute heat and reduces electromagnetic interference (EMI) noise pickup.
- Place the external components as close to the device as possible.
- Do not run sensitive analog traces in parallel with digital traces. Avoid crossing digital and analog traces if possible, and only make perpendicular crossings when absolutely necessary.

图 10-5 shows the pin compatibility with TI REF30xx, REF31xx and REF33xx series references in the 3-pin SOT-23 package when using the REF35xxx family footprint. You must rotate the REF30xx, REF31xx and REF33xx reference devices by 180º before assembly.

Copyright © 2022 Texas Instruments Incorporated

10.4.2 Layout Examples




图 10-4. Layout Example




图 10-5. Pin Compatibility With REF30xx, REF31xx and REF33xx

Copyright © 2022 Texas Instruments Incorporated

11 Device and Documentation Support

11.1 Documentation Support

11.1.1 Related Documentation

For related documentation see the following:

- Texas Instruments, *INA21x Voltage Output, Low- or High-Side Measurement, Bidirectional, Zero-Drift Series, Current-Shunt Monitors* data sheet
- Texas Instruments, *Low-Drift Bidirectional Single-Supply Low-Side Current Sensing Reference Design*
- Texas Instruments, *Precision voltage references* Analog Design Journal

11.2 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 *订阅更新* 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

11.3 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料，可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

11.4 Trademarks

TI E2E™ is a trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

11.5 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

11.6 术语表

TI 术语表　　本术语表列出并解释了术语、首字母缩略词和定义。

12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Copyright © 2022 Texas Instruments Incorporated

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
PREF35125YBHR	ACTIVE	DSBGA	YBH	4	12000	RoHS & Green	SNAGCU	Level-1-260C-UNLIM	-40 to 125	P	Samples
PREF35180YBHR	ACTIVE	DSBGA	YBH	4	3000	TBD	Call TI	Call TI	-40 to 125		Samples
PREF35250YBHR	ACTIVE	DSBGA	YBH	4	3000	TBD	Call TI	Call TI	-40 to 125		Samples
REF35102QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2RTI	Samples
REF35120QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2RVI	Samples
REF35125QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2RUI	Samples
REF35160QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2UII	Samples
REF35170QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	31QI	Samples
REF35180QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2J2I	Samples
REF35205QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2UKI	Samples
REF35250QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2RSI	Samples
REF35300QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2SLI	Samples
REF35330QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2ULI	Samples
REF35360QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	31RI	Samples
REF35409QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2UMI	Samples
REF35500QDBVR	ACTIVE	SOT-23	DBV	6	3000	RoHS & Green	NIPDAUAG	Level-2-260C-1 YEAR	-40 to 125	2RWI	Samples

(1) The marketing status values are defined as follows:
ACTIVE: Product device recommended for new designs.
LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.
NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.
PREVIEW: Device has been announced but is not in production. Samples may or may not be available.
OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".
RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.
Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF REF35 :


- Automotive : REF35-Q1

NOTE: Qualified Version Definitions:


- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

TAPE AND REEL INFORMATION

REEL DIMENSIONS




TAPE DIMENSIONS



A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
REF35102QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35120QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35125QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35160QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35170QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35180QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35205QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35250QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35300QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35330QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35360QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35409QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3
REF35500QDBVR	SOT-23	DBV	6	3000	180.0	8.4	3.23	3.17	1.37	4.0	8.0	Q3

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal


Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
REF35102QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35120QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35125QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35160QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35170QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35180QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35205QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35250QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35300QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35330QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35360QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35409QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0
REF35500QDBVR	SOT-23	DBV	6	3000	213.0	191.0	35.0

PACKAGE OUTLINE

DBV0006A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR




ALTERNATIVE PACKAGE SINGULATION VIEW


4214840/E 02/2024

NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Body dimensions do not include mold flash or protrusion. Mold flash and protrusion shall not exceed 0.25 per side.
4. Leads 1,2,3 may be wider than leads 4,5,6 for package orientation.
5. Refernce JEDEC MO-178.



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:15X




SOLDER MASK DETAILS

4214840/E 02/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:15X

4214840/E 02/2024

NOTES: (continued)


8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

YBH0004

PACKAGE OUTLINE

DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



4224051/A 11/2017

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

EXAMPLE BOARD LAYOUT


YBH0004

DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 50X



SOLDER MASK DETAILS
NOT TO SCALE

4224051/A 11/2017

NOTES: (continued)


3. Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints.
   See Texas Instruments Literature No. SNVA009 (www.ti.com/lit/snva009).

EXAMPLE STENCIL DESIGN

YBH0004

DSBGA - 0.4 mm max height

DIE SIZE BALL GRID ARRAY



SOLDER PASTE EXAMPLE
BASED ON 0.075 mm THICK STENCIL
SCALE: 50X

4224051/A 11/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024，德州仪器 (TI) 公司