

# TPD6F002-Q1 面向 LCD 显示屏和 FPD-Link 的汽车类 ESD 保护和 EMI 滤波器

## 1 特性

- 符合 AEC-Q101 标准
- 针对数据端口的 6 通道电磁干扰 (EMI) 滤波
  - 100MHz 频率下的串扰衰减为  $-47\text{dB}$
  - 800MHz 频率下的插入损耗为  $-30\text{dB}$
  - 100MHz 频率下的的带宽为  $-3\text{dB}$
- Pi 型 (C-R-C) 滤波器配置  
( $R = 100\Omega$ ,  $C_{\text{TOTAL}} = 34\text{pF}$ )
- 优异的静电放电 (ESD) 保护, 超过了 IEC 61000-4-2 标准 (4 级)
  - $\pm 20\text{kV}$  IEC 61000-4-2 接触放电
  - $\pm 30\text{kV}$  IEC 61000-4-2 气隙放电
- 低泄漏电流  $20\text{nA}$  (最大值)
- 采用节省空间的小外形尺寸无引线 (SON) 封装 ( $3\text{mm} \times 1.35\text{mm}$ )

## 2 应用

- 液晶显示屏 (LCD) 显示接口
- 通用输入/输出 (GPIO)
- 存储器接口
- 采用柔性电缆的数据线
- FPD-Link

## 3 说明


TPD6F002-Q1 是一款高度集成的器件, 该器件提供有 6 通道 EMI 滤波器和基于瞬态电压抑制器 (TVS) 的 ESD 保护二极管阵列。低通滤波器阵列可为数据端口抑制 EMI/射频干扰 (RFI) 辐射, 防止其受到电磁干扰。TVS 二极管阵列的额定 ESD 冲击消散值高于 IEC 61000-4-2 国际标准中规定的最高水平。此器件高度集成, 并且采用易于布线的小型 DSV 封装, 可对 LCD 显示屏、存储器接口、GPIO 线和 FPD-Link 提供强力的电路保护。

### 器件信息<sup>(1)</sup>

器件型号	封装	封装尺寸 (标称值)
TPD6F002-Q1	SON (12)	3.00mm x 1.35mm

(1) 要了解所有可用封装, 请见数据表末尾的可订购产品附录。

## 4 简化电路原理图



PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

English Data Sheet: [SLLSEKO](#)


## 目 录

1	特性 .....	1
2	应用 .....	1
3	说明 .....	1
4	简化电路原理图 .....	1
5	修订历史记录 .....	2
6	Pin Configuration and Functions .....	3
7	Specifications .....	3
7.1	Absolute Maximum Ratings .....	3
7.2	ESD Ratings .....	3
7.3	Recommended Operating Conditions .....	3
7.4	Thermal Information .....	4
7.5	Electrical Characteristics .....	4
7.6	Typical Characteristics .....	5
8	Detailed Description .....	6
8.1	Overview .....	6
8.2	Functional Block Diagram .....	6
8.3	Feature Description .....	6
8.4	Device Functional Modes .....	7
9	Application and Implementation .....	7
9.1	Application Information .....	7
9.2	Typical Application .....	8
10	Power Supply Recommendations .....	10
11	Layout .....	10
11.1	Layout Guidelines .....	10
11.2	Layout Example .....	10
12	器件和文档支持 .....	11
12.1	商标 .....	11
12.2	静电放电警告 .....	11
12.3	术语表 .....	11
13	机械、封装和可订购信息 .....	11

## 5 修订历史记录

Changes from Original (December 2014) to Revision A	Page
• 最初发布的完整版数据表。 .....	1

## 6 Pin Configuration and Functions



### Pin Functions

PIN		I/O	DESCRIPTION
NAME	NO.		
ChX_In	1, 2, 3, 4, 5, 6	IO	ESD-protected channel, connected to corresponding ChX_Out
ChX_Out	7, 8, 9, 10, 11, 12	IO	ESD-protected channel, connected to corresponding ChX_In
GND	G	G	Ground

## 7 Specifications

### 7.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
$V_{IO}$	IO to GND		5.75	V
$T_J$	Junction temperature		125	°C
$T_{stg}$	Storage temperature range	-65	150	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rated conditions for extended periods may affect device reliability.

### 7.2 ESD Ratings

		VALUE	UNIT
$V_{(ESD)}$	Electrostatic discharge	Human body model (HBM), per AEC Q100-002, all pins <sup>(1)</sup>	kV
		Charged device model (CDM), per AEC Q101-005, all pins	
		IEC 61000-4-2 Contact Discharge	
		IEC 61000-4-2 Air-Gap Discharge	

(1) AEC Q100-002 indicates HBM stressing is done in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

### 7.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
$V_{IO}$	Input pin voltage	0	5.5	V	
$T_A$	Operating free-air temperature	-40	125	°C	

## 7.4 Thermal Information

THERMAL METRIC <sup>(1)</sup>		TPD6F002-Q1	UNIT
		DSV	
		12 PINS	
$R_{\theta JA}$	Junction-to-ambient thermal resistance	120.7	°C/W
$R_{\theta JC(\text{top})}$	Junction-to-case (top) thermal resistance	104.4	
$R_{\theta JB}$	Junction-to-board thermal resistance	78.5	
$\Psi_{JT}$	Junction-to-top characterization parameter	13.0	
$\Psi_{JB}$	Junction-to-board characterization parameter	77.7	
$R_{\theta JC(\text{bot})}$	Junction-to-case (bottom) thermal resistance	66.5	

(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](#).

## 7.5 Electrical Characteristics


$T_A = -40^\circ\text{C}$  to  $125^\circ\text{C}$  (Unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
$V_{BR}$	$I_{IO} = 10 \mu\text{A}$	6			V
R	$V_{IN} = 3.3 \text{ V}$ , $I_{In\text{-to}\text{-}out}} = 1\text{mA}$	85	100	115	$\Omega$
C	$V_{IO} = 2.5 \text{ V}$		17		pF
$I_{IO}$	$V_{IO} = 3.3 \text{ V}$		1	20	nA
$f_c$	$Z_{\text{SOURCE}} = 50 \Omega$ , $Z_{\text{LOAD}} = 50 \Omega$		100		MHz


(1) Typical values are at  $T_A = 25^\circ\text{C}$ .

## 7.6 Typical Characteristics


$T_A = 25^\circ\text{C}$  unless otherwise noted




**Figure 1. DC Voltage-Current Sweep across Input, Output Pins**




**Figure 2. Series Resistance vs Temperature**




**Figure 3. Typical Insertion-loss Characteristics (DC Bias = 0 V, 50 Ω Environment)**



**Figure 4. Capacitance (C1 or C2) vs. Bias Voltage**



**Figure 5. +8-kV IEC Waveform**




**Figure 6. -8-kV IEC Waveform**

## 8 Detailed Description

### 8.1 Overview

The TPD6F002-Q1 is a highly integrated device that provides a six channel EMI filter and a TVS based ESD protection diode array. The low-pass filter array suppresses EMI/RFI emissions for data ports subject to electromagnetic interference. The TPD6F002-Q1 is rated to dissipate ESD strikes above the maximum level specified in the IEC 61000-4-2 international standard. The high level of integration, combined with its small easy-to-route DSV package, makes this device ideal for protecting interfaces like LCD displays, memory interfaces, and FPD-Link.

### 8.2 Functional Block Diagram



### 8.3 Feature Description

The TPD6F002-Q1 is a highly integrated device that provides a six channel EMI filter and a TVS based ESD protection diode array. The low-pass filter array suppresses EMI/RFI emissions for data ports subject to electromagnetic interference. The TVS diode array is rated to dissipate ESD strikes above the maximum level specified in the IEC 61000-4-2 international standard. The high level of integration, combined with its small easy-to-route DSV package, allows this device to provide great circuit protection for LCD displays, memory interfaces, GPIO lines, and FPD-Link.

#### 8.3.1 AEC-Q101 Qualified

This device is qualified to AEC-Q101 standards. It passes HBM H3B ( $\pm 8$  kV) and CDM C5 ( $\pm 1$  kV) ESD ratings and is qualified to operate from  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

#### 8.3.2 Six-Channel EMI Filtering

This device provides six channels for EMI filtering of data lines with the following parameters:

- $-47$  dB Crosstalk Attenuation at 100 MHz
- $-30$  dB Insertion Loss at 800 MHz
- $-3$  dB Bandwidth: 100 MHz

#### 8.3.3 Pi-Style Filter Configuration

This device has a pi-style filtering configuration composed of a series resistor and two capacitors in parallel with the I/O pins. The typical resistor value is  $100\ \Omega$  and the typical capacitor values are  $17\ \text{pF}$  each.

#### 8.3.4 Robust ESD Protection

The ESD protection on all pins exceeds the IEC 61000-4-2 level 4 standard. Contact ESD is rated at  $\pm 20$  kV and Air-gap ESD is rated at  $\pm 30$  kV.

## Feature Description (continued)

### 8.3.5 Low Leakage Current

The I/O pins feature an ultra-low leakage current of 20-nA (max) with a bias of 3.3 V

### 8.3.6 Space-Saving SON Package

The layout of this device makes it easy to add protection to existing layouts. The packages offer flow-through routing which requires minimal changes to existing layout for addition of these devices. Additionally, the device offers a small space-saving package that takes a minimal footprint on the board.

## 8.4 Device Functional Modes

The TPD6F002-Q1 is a passive integrated circuit that passively filters EMI and triggers when voltages are above  $V_{BR}$  or below the lower diode voltage (-0.6 V). During ESD events, voltages as high as  $\pm 30$  kV (air) can be directed to ground via the internal diode network. Once the voltages on the protected line fall below the trigger levels, the device reverts to passive.

## 9 Application and Implementation


### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 9.1 Application Information

The TPD6F002-Q1 is a highly integrated device that provides a six channel EMI filter and a TVS based ESD protection diode array. The low-pass filter array suppresses EMI/RFI emissions for data ports subject to electromagnetic interference. The TVS diode array is rated to dissipate ESD strikes above the maximum level specified in the IEC 61000-4-2 international standard. The high level of integration, combined with its small easy-to-route DSV package, allows this device to provide great circuit protection for LCD displays, memory interfaces, GPIO lines, and FPD-Link.

## 9.2 Typical Application



**Figure 7. Display Panel Schematic**

## Typical Application (continued)

### 9.2.1 Design Requirements

For this design example, three TPD6F002-Q1 devices are being used in an 18-bit display panel application. This will provide a complete ESD and EMI protection solution for the display connector.

Given the display panel application, the following parameters are known.

DESIGN PARAMETER	VALUE
Signal range on all pins except GND	0 V to 5 V
Operating Frequency	50 MHz

### 9.2.2 Detailed Design Procedure

To begin the design process, some design parameters must be decided; the designer needs to know the following:

- Signal range of all the protected lines
- Operating frequency
- Crosstalk response

#### 9.2.2.1 Signal Range on All Protected Lines

The TPD6F002-Q1 has 6 identical protection channels for signal lines. All I/O pins will support a signal range from 0 to 5.5 V.


#### 9.2.2.2 Operating Frequency

The TPD6F002-Q1 has a 100 MHz –3 dB bandwidth, which supports the operating frequency for this display.

#### 9.2.2.3 Crosstalk Response

The TPD6F002-Q1 has a –47 dB near-side crosstalk attenuation at 100 MHz, sufficient for this display.

### 9.2.3 Application Curves



**Figure 8. Near-Side Crosstalk**

## 10 Power Supply Recommendations

This device is a passive EMI and ESD device so there is no need to power it. Care should be taken to not violate the recommended  $V_{IO}$  specification (5.5 V) to ensure the device functions properly.

## 11 Layout

### 11.1 Layout Guidelines

- The optimum placement is as close to the connector as possible.
  - EMI during an ESD event can couple from the trace being struck to other nearby unprotected traces, resulting in early system failures.
  - The PCB designer needs to minimize the possibility of EMI coupling by keeping any unprotected traces away from the protected traces which are between the TVS and the connector.
- Route the protected traces as straight as possible.
- Eliminate any sharp corners on the protected traces between the TVS and the connector by using rounded corners with the largest radii possible.
  - Electric fields tend to build up on corners, increasing EMI coupling.

### 11.2 Layout Example

This application is typical of an 18-bit RGB display panel layout.




Figure 9. TPD6F002-Q1 Layout

## 12 器件和文档支持

### 12.1 商标

All trademarks are the property of their respective owners.

### 12.2 静电放电警告



这些装置包含有限的内置 ESD 保护。存储或装卸时，应将导线一起截短或将装置放置于导电泡棉中，以防止 MOS 门极遭受静电损伤。

### 12.3 术语表

#### SLYZ022 — TI 术语表。

这份术语表列出并解释术语、首字母缩略词和定义。

## 13 机械、封装和可订购信息

以下页中包括机械、封装和可订购信息。这些信息是针对指定器件可提供的最新数据。这些数据会在无通知且不对本文档进行修订的情况下发生改变。欲获得该数据表的浏览器版本，请查阅左侧的导航栏。

**PACKAGING INFORMATION**

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
TPD6F002QDSVRQ1	Active	Production	SON (DSV)   12	3000   LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	UNS
TPD6F002QDSVRQ1.A	Active	Production	SON (DSV)   12	3000   LARGE T&R	Yes	NIPDAU	Level-2-260C-1 YEAR	-40 to 125	UNS

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



**OTHER QUALIFIED VERSIONS OF TPD6F002-Q1 :**

- Catalog : [TPD6F002](#)


---

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product

**TAPE AND REEL INFORMATION**
**REEL DIMENSIONS**

**TAPE DIMENSIONS**


A0	Dimension designed to accommodate the component width
B0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPD6F002QDSVRQ1	SON	DSV	12	3000	180.0	8.4	1.74	3.33	1.05	4.0	8.0	Q1


**TAPE AND REEL BOX DIMENSIONS**

\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPD6F002QDSVRQ1	SON	DSV	12	3000	213.0	191.0	35.0

DSV (R-PWSON-N12)

PLASTIC SMALL OUTLINE NO-LEAD



Bottom View

4209279/B 12/11

NOTES:

- All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
- This drawing is subject to change without notice.
- SON (Small Outline No-Lead) package configuration.
- The package thermal pad must be soldered to the board for thermal and mechanical performance.
- See the additional figure in the Product Data Sheet for details regarding the exposed thermal pad features and dimensions.

**Pin 1** identifiers are located on both top and bottom of the package and within the zone indicated.  
The Pin 1 identifiers are either a molded, marked, or metal feature.

# Thermal Pad Mechanical Data

DSV (R-PWSON-N12)


Plastic Small Outline No-Lead

## Thermal Information

This package incorporates an exposed thermal pad that is designed to be attached directly to an external heatsink. The thermal pad must be soldered directly to the printed circuit board (PCB). After soldering, the PCB can be used as a heatsink. In addition, through the use of thermal vias, the thermal pad can be attached directly to the appropriate copper plane shown in the electrical schematic for the device, or alternatively, can be attached to a special heatsink structure designed into the PCB. This design optimizes the heat transfer from the integrated circuit (IC).

For information on the Quad Flatpack No-Lead (QFN) package and its advantages, refer to Application Report, QFN/SON PCB Attachment, Texas Instruments Literature No. SLUA271. This document is available at [www.ti.com](http://www.ti.com).

The exposed thermal pad dimensions for this package are shown in the following illustration.



Bottom View

Exposed Thermal Pad Dimensions


4209318/B 12/11

NOTE: All linear dimensions are in millimeters

# LAND PATTERN DATA

DSV (R-PWSON-N12)

PLASTIC SMALL OUTLINE NO-LEAD



NOTES:

- All linear dimensions are in millimeters.
- This drawing is subject to change without notice.
- Publication IPC-7351 is recommended for alternate designs.
- This package is designed to be soldered to a thermal pad on the board. Refer to Application Note, Quad Flat-Pack Packages, Texas Instruments Literature No. SLUA271, and also the Product Data Sheets for specific thermal information, via requirements, and recommended board layout. These documents are available at [www.ti.com](http://www.ti.com) <<http://www.ti.com>>.
- Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
- Customers should contact their board fabrication site for minimum solder mask web tolerances between signal pads.

## 重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做出任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2026，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月