







SN74LV244A-Q1

ZHCSQW2B - AUGUST 2022 - REVISED JANUARY 2023

SN74LV244A-Q1 具有三态输出的汽车类八路缓冲器和驱动器

1 特性

- 符合面向汽车应用的 AEC-Q100 标准:
 - 器件温度等级 1:
 - 40°C 至 + 125°C , T_A
 - 器件 HBM ESD 分类等级 2
 - 器件 CDM ESD 分类等级 C6
- 采用 节 8.3.4QFN (WRKS) 封装
- 2 V 至 5.5 V V_{CC} 运行
- 5V 时 t_{od} 最大值为 6.5 ns
- 所有端口上均支持以混合模式电压运行
- I_{off} 支持局部断电模式运行
- 闩锁性能超过 250mA,符合 JESD 17 规范

2 应用

- 启用或禁用数字信号
- 消除缓慢或嘈杂输入信号
- 在控制器复位期间保持信号
- 对开关进行去抖

3 说明


SN74LV244A-Q1 八路缓冲器和线路驱动器在 2V 至 5.5V V_{CC} 电压下运行。


该器件配置为两组,每组四个驱动器,每组都由各自的 输出使能引脚进行控制。该器件专用于使用 Ioff 的局部 断电应用。Ioff 电路会禁用输出,从而在器件断电时防 止电流回流损坏器件。

封装信息(1)

器件型号	封装	封装尺寸 (标称值)
SN74LV244A-Q1	WRKS (WQFN, 20)	4.50mm × 2.50mm
31174LV244A-Q1	DGS (VSSOP , 20)	5.10mm × 3.00mm

如需了解所有可用封装,请参阅数据表末尾的可订购产品附





逻辑图(正逻辑)

English Data Sheet: SCLS906



Table of Contents

1 特性 1	8.1 Overview10
2 应用1	8.2 Functional Block Diagram10
3 说明1	8.3 Feature Description10
4 Revision History2	8.4 Device Functional Modes12
5 Pin Configuration and Functions3	9 Application and Implementation13
6 Specifications4	9.1 Application Information
6.1 Absolute Maximum Ratings4	9.2 Typical Application13
6.2 ESD Ratings4	9.3 Power Supply Recommendations15
6.3 Recommended Operating Conditions5	9.4 Layout15
6.4 Thermal Information5	10 Device and Documentation Support17
6.5 Electrical Characteristics6	10.1 Related Documentation17
6.6 Switching Characteristics, V _{CC} = 2.5 V ± 0.2 V6	10.2 Receiving Notification of Documentation Updates17
6.7 Switching Characteristics, V _{CC} = 3.3 V ± 0.3 V6	10.3 支持资源17
6.8 Switching Characteristics, V _{CC} = 5 V ± 0.5 V7	10.4 Trademarks17
6.9 Noise Characteristics7	10.5 静电放电警告17
6.10 Operating Characteristics7	10.6 术语表17
6.11 Typical Characteristics8	11 Mechanical, Packaging, and Orderable
7 Parameter Measurement Information9	Information17
8 Detailed Description10	

4 Revision History 注:以前版本的页码可能与当前版本的页码不同

Changes from Revision A (September 2022) to Revision B (January 2023)	Page
• 向数据表添加了 <i>DGS</i> 封装信息	1
Changes from Revision * (August 2022) to Revision A (September 2022)	Page
• 将数据表的状态从 <i>预告信息</i> 更改为 <i>"量产数据"</i>	1



5 Pin Configuration and Functions




图 5-1. SN74LV244A-Q1: WRKS Package, 20-Pin WQFN (Top View)




图 5-2. SN74LV244A-Q1: DGS Package, 20-Pin VSSOP (Top View)

表 5-1. Pin Functions

PIN TYPE(1)		TVD=(1)	DECODIDATION
NAME	NO.	IYPE(')	DESCRIPTION
1 OE	1	I	Bank 1, output enable, active low
1A1	2	I	Bank 1, channel 1 input
2Y4	3	0	Bank 2, channel 4 output
1A2	4	I	Bank 1, channel 2 input
2Y3	5	0	Bank 2, channel 3 output
1A3	6	I	Bank 1, channel 3 input
2Y2	7	0	Bank 2, channel 2 output
1A4	8	I	Bank 1, channel 4 input
2Y1	9	0	Bank 2, channel 1 output
GND	10	G	Ground
2A1	11	I	Bank 2, channel 1 input
1Y4	12	0	Bank 1, channel 4 output
2A2	13	I	Bank 2, channel 2 input
1Y3	14	0	Bank 1, channel 3 output
2A3	15	I	Bank 2, channel 3 input
1Y2	16	0	Bank 1, channel 2 output
2A4	17	1	Bank 2, channel 4 input
1Y1	18	0	Bank 1, channel 1 output
2 OE	19	I	Bank 2, output enable, active low
V _{CC}	20	Р	Positive supply

⁽¹⁾ I = Input, O = Output, I/O = Input or Output, G = Ground, P = Power.



6 Specifications

6.1 Absolute Maximum Ratings

Over operating free-air temperature range (unless otherwise noted)⁽¹⁾

			MIN	MAX	UNIT
V _{CC}	Supply voltage	-0.5	7	V	
VI	Input voltage ⁽²⁾	-0.5	7	V	
Vo	Voltage range applied to any output in the high-impedance or power-off sta	-0.5	7	V	
Vo	Output voltage (2) (3)	-0.5	V _{CC} + 0.5	V	
I _{IK}	Input clamp current	V _I < 0		-20	mA
I _{OK}	Output clamp current	V _O < 0		-50	mA
Io	Continuous output current		±25	mA	
	Continuous current through V _{CC} or GND		±50	mA	
T _{stg}	Storage temperature	-65	150	°C	

⁽¹⁾ Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute maximum ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If briefly operating outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not sustain damage, but it may not be fully functional. Operating the device in this manner may affect device reliability, functionality, performance, and shorten the device lifetime.

- (2) The input and output negative-voltage ratings may be exceeded if the input and output current ratings are observed.
- (3) This value is limited to 5.5 V maximum.

6.2 ESD Ratings

			VALUE	UNIT
	Electrostatic	Human body model (HBM), per AEC Q100-002 HBM ESD Classification Level 2 ⁽¹⁾	±4000	
V _(ESD)	discharge	Charged device model (CDM), per AEC Q100-011 CDM ESD Classification Level C4B	±2000	V

(1) AEC Q100-002 indicate that HBM stressing shall be in accordance with the ANSI/ESDA/JEDEC JS-001 specification.

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)(1)

			MIN	MAX	UNIT
V _{CC}	Supply voltage		2	5.5	V
\/	High level input voltage	V _{CC} = 2 V	1.5		V
V _{IH}	High-level input voltage	V _{CC} = 2.3 V to 5.5 V	V _{CC} × 0.7		V
\/	Low-level input voltage	V _{CC} = 2 V		0.5	V
V_{IL}	Low-level input voltage	V _{CC} = 2.3 V to 5.5 V	V	′ _{CC} × 0.3	V
V _I	Input voltage		0	5.5	V
\/	Output voltage	High or low state	0	V _{CC}	V
Vo	Output voltage	3-state	0	5.5	V
	High-level output current	V _{CC} = 2 V		-50	μΑ
		V _{CC} = 2.3 V to 2.7 V		-2	
I _{OH}		V _{CC} = 3 V to 3.6 V		-8	mA
		V _{CC} = 4.5 V to 5.5 V		-16	
		V _{CC} = 2 V		50	μΑ
		V _{CC} = 2.3 V to 2.7 V		2	
l _{OL}	Low-level output current	V _{CC} = 3 V to 3.6 V		8	mA
		V _{CC} = 4.5 V to 5.5 V		16	
		V _{CC} = 2.3 V to 2.7 V		200	
Δt/Δν	Input transition rise or fall rate	V _{CC} = 3 V to 3.6 V		100	ns/V
		V _{CC} = 4.5 V to 5.5 V		20	
T _A	Operating free-air temperature		-40	125	°C

⁽¹⁾ All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. See *Implications of Slow or Floating CMOS Inputs*.

6.4 Thermal Information

		SN74LV244	SN74LV244A-Q1				
	THERMAL METRIC ⁽¹⁾	WRKS (WQFN)	DGS (VSSOP)	UNIT			
		20 PINS	20 PINS				
$R_{\theta JA}$	Junction-to-ambient thermal resistance	75.8	125.5	°C/W			
R _{θJC(top)}	Junction-to-case (top) thermal resistance	80.3	80.0	°C/W			
R _{0JB}	Junction-to-board thermal resistance	50.5	63.8	°C/W			
Ψ_{JT}	Junction-to-top characterization parameter	16.0	8.4	°C/W			
ΨЈВ	Junction-to-board characterization parameter	50.4	79.9	°C/W			
R _{0JC(bot)}	Junction-to-case (bottom) thermal resistance	32.3	N/A	°C/W			

⁽¹⁾ For more information about traditional and new thermal metrics, see Semiconductor and IC Package Thermal Metrics.



6.5 Electrical Characteristics

over operating free-air temperature range (unless otherwise noted).

	PARAMETER	,	V _{cc}	MIN	TYP	MAX	UNIT
		I _{OH} = -50 mA	2 V to 5.5 V	V _{CC} - 0.1			
V _{OH}	High level output voltage	I _{OH} = -2 mA	2.3 V	2			V
		I _{OH} = -8 mA	3 V	2.48			
		I _{OH} = -16 mA	4.5 V	3.8			
		I _{OL} = 50 mA	2 V to 5.5 V			0.1	
V _{OL}	Low level output voltage	I _{OL} = 2 mA	2.3 V			0.4	V
		I _{OL} = 8mA	3 V			0.44	
		I _{OL} = 16 mA	4.5 V			0.55	
I	Input leakage current	V _I = 5.5 V or GND	0 V to 5.5 V			±1	μА
I _{OZ}	Off-State (High-Impedance State) Output Current (of a 3-State Output)	V _O = V _{CC} or GND	5.5 V			±5	μА
I _{CC}	Supply current	$V_I = V_{CC}$ or GND, $I_O = 0$	5.5 V			20	μA
I _{off}	Input/Output Power-Off Leakage Current	V_{I} or $V_{O} = 0$ to 5.5 V	0 V			5	μΑ
Ci	Input capacitance	V _I = V _{CC} or GND	3.3 V		2.3		pF

6.6 Switching Characteristics, V_{CC} = 2.5 V ± 0.2 V

over operating free-air temperature range (unless otherwise noted), (see 图 7-1)

PARAMETE	FROM	то	LOAD		25°C		-40	°C to 125	s°C	UNIT
R	(INPUT)	(OUTPUT)	CAP	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
t _{pd}	Α	Y	C _L = 15 pF		7.5	12.5	1		15	ns
t _{en}	ŌĒ	Y	C _L = 15 pF		8.9	14.6	1		17	ns
t _{dis}	ŌĒ	Y	C _L = 15 pF		9.1	14.1	1		16	ns
t _{pd}	Α	Y	C _L = 50 pF		9.5	15.3	1		18	ns
t _{en}	ŌĒ	Y	C _L = 50 pF		10.8	17.8	1		21	ns
t _{dis}	ŌĒ	Y	C _L = 50 pF		13.4	19.2	1		21	ns
t _{sk(o)}			C _L = 50 pF			2			2	ns

6.7 Switching Characteristics, V_{CC} = 3.3 V \pm 0.3 V

over operating free-air temperature range (unless otherwise noted), (see 图 7-1)

PARAMETE	FROM	то	LOAD		25°C		-40	°C to 125	5°C	UNIT
R	(INPUT)	(OUTPUT)	CAP	MIN	TYP	MAX	MIN	TYP	MAX	UNIT
t _{pd}	Α	Y	C _L = 15 pF		5.4	8.4	1		10	ns
t _{en}	ŌĒ	Y	C _L = 15 pF		6.3	10.6	1		12.5	ns
t _{dis}	ŌĒ	Y	C _L = 15 pF		7.6	11.7	1		13	ns
t _{pd}	Α	Υ	C _L = 50 pF		6.8	11.9	1		13.5	ns
t _{en}	ŌĒ	Υ	C _L = 50 pF		7.8	14.1	1		16	ns
t _{dis}	ŌĒ	Υ	C _L = 50 pF		11	16	1		18	ns
t _{sk(o)}			C _L = 50 pF			1.5			1.5	ns

Submit Document Feedback



6.8 Switching Characteristics, V_{CC} = 5 V ± 0.5 V

over recommended operating free-air temperature range (unless otherwise noted), (see 图 7-1)

PARAMETE	FROM	то	LOAD	25°C			-40	°C to 125°C		UNIT
R	(INPUT)	(OUTPUT)	CAP	MIN	TYP	MAX	MIN	TYP I	MAX	UNIT
t _{pd}	А	Y	C _L = 15 pF		3.9	5.5	1		6.5	ns
t _{en}	ŌĒ	Y	C _L = 15 pF		4.5	7.3	1		8.5	ns
t _{dis}	ŌĒ	Y	C _L = 15 pF		6.5	12.2	1		13.5	ns
t _{pd}	A	Y	C _L = 50 pF		4.9	7.5	1		8.5	ns
t _{en}	ŌĒ	Y	C _L = 50 pF		5.6	9.3	1		10.5	ns
t _{dis}	ŌĒ	Y	C _L = 50 pF		8.8	14.2	1		15.5	ns
t _{sk(o)}			C _L = 50 pF			1			1	ns

6.9 Noise Characteristics

 $V_{CC} = 3.3 \text{ V}, C_L = 50 \text{ pF}, T_A = 25^{\circ}\text{C}^{(1)}$

		MIN	TYP	MAX	UNIT
V _{OL(P)}	Quiet output, maximum dynamic		0.55		V
V _{OL(V)}	Quiet output, minimum dynamic		-0.5		V
V _{OH(V)}	Quiet output, minimum dynamic		2.9		V
V _{IH(D)}	High-level dynamic input voltage	2.31			V
V _{IL(D)}	Low-level dynamic input voltage			0.99	V

⁽¹⁾ Characteristics are for surface-mount packages only.


6.10 Operating Characteristics

 $T_A = 25^{\circ}C$

	PARAMETER	TEST CO	ONDITIONS	V _{CC}	TYP	UNIT
	Power dissipation capacitance	C _L = 50 pF	f 40 MH-	3.3 V	14	pF
C _{pd}			f = 10 MHz	5 V	16	



6.11 Typical Characteristics



S1

Open

Vcc

GND

 V_{CC}

TEST

t_{PLH}/t_{PHL}


t_{PLZ}/t_{PZL}


t_{PHZ}/t_{PZH}

Open Drain



7 Parameter Measurement Information





- A. C_L includes probe and jig capacitance.
- B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, $Z_O = 50 \Omega$, $t_r \leq 3$ ns. $t_f \leq 3$ ns.
- D. The outputs are measured one at a time, with one input transition per measurement.
- E. t_{PLZ} and t_{PHZ} are the same as t_{dis} .
- F. t_{PZL} and t_{PZH} are the same as t_{en} .
- G. t_{PHL} and t_{PLH} are the same as t_{pd}.
- H. All parameters and waveforms are not applicable to all devices.

图 7-1. Load Circuit and Voltage Waveforms

8 Detailed Description

8.1 Overview

The SN74LV244A-Q1 contains 8 individual high speed CMOS buffers with 3-state outputs.

Each buffer performs the boolean logic function xYn = xAn, with x being the bank number and n being the channel number. Each output enable $(x\overline{OE})$ controls four buffers. When the $x\overline{OE}$ pin is in the low state, the outputs of all buffers in the bank x are enabled. When the $x\overline{OE}$ pin is in the high state, the outputs of all buffers in the bank x are disabled outputs are placed into the high-impedance state.

To ensure the high-impedance state during power up or power down, both \overline{OE} pins should be tied to V_{CC} through a pull-up resistor; the minimum value of the resistor is determined by the current sinking capability of the driver and the leakage of the pin as defined in the *Electrical Characteristics* table.

8.2 Functional Block Diagram




图 8-1. Logic Diagram (Positive Logic)

8.3 Feature Description

8.3.1 Balanced CMOS 3-State Outputs

This device includes balanced CMOS 3-state outputs. Driving high, driving low, and high impedance are the three states that these outputs can be in. The term *balanced* indicates that the device can sink and source similar currents. The drive capability of this device may create fast edges into light loads, so routing and load conditions should be considered to prevent ringing. Additionally, the outputs of this device can drive larger currents than the device can sustain without being damaged. It is important for the output power of the device to be limited to avoid damage due to overcurrent. The electrical and thermal limits defined in the *Absolute Maximum Ratings* must be followed at all times.

When placed into the high-impedance mode, the output will neither source nor sink current, with the exception of minor leakage current as defined in the *Electrical Characteristics* table. In the high-impedance state, the output voltage is not controlled by the device and is dependent on external factors. If no other drivers are connected to the node, then this is known as a floating node and the voltage is unknown. A pull-up or pull-down resistor can be connected to the output to provide a known voltage at the output while it is in the high-impedance state. The value of the resistor will depend on multiple factors, including parasitic capacitance and power consumption limitations. Typically, a $10-k\Omega$ resistor can be used to meet these requirements.

Unused 3-state CMOS outputs should be left disconnected.

8.3.2 Latching Logic

This device includes latching logic circuitry. Latching circuits commonly include D-type latches and D-type flip-flops, but include all logic circuits that act as volatile memory.

When the device is powered on, the state of each latch is unknown. There is no default state for each latch at start-up.

The output state of each latching logic circuit only remains stable as long as power is applied to the device within the supply voltage range specified in the *Recommended Operating Conditions* table.

8.3.3 Partial Power Down (I_{off})

This device includes circuitry to disable all outputs when the supply pin is held at 0 V. When disabled, the outputs will neither source nor sink current, regardless of the input voltages applied. The amount of leakage current at each output is defined by the I_{off} specification in the *Electrical Characteristics* table.

8.3.4 Wettable Flanks

This device includes wettable flanks for at least one package. See the *Features* section on the front page of the data sheet for which packages include this feature.




图 8-2. Simplified Cutaway View of Wettable-Flank QFN Package and Standard QFN Package After Soldering

Wettable flanks help improve side wetting after soldering, which makes QFN packages easier to inspect with automatic optical inspection (AOI). As shown in $\ 8-2$, a wettable flank can be dimpled or step-cut to provide additional surface area for solder adhesion which assists in reliably creating a side fillet. See the mechanical drawing for additional details.



8.3.5 Clamp Diode Structure

图 8-3 shows the inputs and outputs to this device have negative clamping diodes only.

CAUTION

Voltages beyond the values specified in the *Absolute Maximum Ratings* table can cause damage to the device. The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.




图 8-3. Electrical Placement of Clamping Diodes for Each Input and Output

8.4 Device Functional Modes

The 表 8-1 list the functional modes of the SN74LV244A-Q1.

表 8-1. Function Table

INPU	OUTPUTS	
ŌĒ	A	Υ
L	L	L
L	Н	Н
Н	X	Z

(1) H = High Voltage Level, L = Low Voltage Level, X = Do Not Care, Z = High-Impedance State

Submit Document Feedback

Copyright © 2023 Texas Instruments Incorporated



9 Application and Implementation

备注

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

9.1 Application Information

The SN74LV244A-Q1 can be used to drive signals over relatively long traces or transmission lines. To reduce ringing caused by impedance mismatches between the driver, transmission line, and receiver, a series damping resistor placed in series with the transmitter's output can be used. The plot in the *Application Curve* section shows the received signal with three separate resistor values. Just a small amount of resistance can make a significant impact on signal integrity in this type of application.

9.2 Typical Application




图 9-1. Typical Application Block Diagram

9.2.1 Power Considerations

Ensure the desired supply voltage is within the range specified in the *Recommended Operating Conditions*. The supply voltage sets the device's electrical characteristics as described in the *Electrical Characteristics* section.

The positive voltage supply must be capable of sourcing current equal to the total current to be sourced by all outputs of the SN74LV244A-Q1 plus the maximum static supply current, I_{CC} , listed in the *Electrical Characteristics*, and any transient current required for switching. The logic device can only source as much current that is provided by the positive supply source. Be sure to not exceed the maximum total current through V_{CC} listed in the *Absolute Maximum Ratings*.

The ground must be capable of sinking current equal to the total current to be sunk by all outputs of the SN74LV244A-Q1 plus the maximum supply current, I_{CC}, listed in the *Electrical Characteristics*, and any transient current required for switching. The logic device can only sink as much current that can be sunk into its ground connection. Be sure to not exceed the maximum total current through GND listed in the *Absolute Maximum Ratings*.

The SN74LV244A-Q1 can drive a load with a total capacitance less than or equal to 50 pF while still meeting all of the data sheet specifications. Larger capacitive loads can be applied; however, it is not recommended to exceed 50 pF.

The SN74LV244A-Q1 can drive a load with total resistance described by $R_L \ge V_O / I_O$, with the output voltage and current defined in the *Electrical Characteristics* table with V_{OH} and V_{OL} . When outputting in the HIGH state, the output voltage in the equation is defined as the difference between the measured output voltage and the supply voltage at the V_{CC} pin.

Total power consumption can be calculated using the information provided in CMOS Power Consumption and Cpd Calculation.

Thermal increase can be calculated using the information provided in Thermal Characteristics of Standard Linear and Logic (SLL) Packages and Devices.



CAUTION

The maximum junction temperature, $T_{J(max)}$ listed in the *Absolute Maximum Ratings*, is an additional limitation to prevent damage to the device. Do not violate any values listed in the *Absolute Maximum Ratings*. These limits are provided to prevent damage to the device.

9.2.2 Input Considerations

Input signals must cross $V_{IL(max)}$ to be considered a logic LOW, and $V_{IH(min)}$ to be considered a logic HIGH. Do not exceed the maximum input voltage range found in the *Absolute Maximum Ratings*.

Unused inputs must be terminated to either V_{CC} or ground. The unused inputs can be directly terminated if the input is completely unused, or they can be connected with a pull-up or pull-down resistor if the input will be used sometimes, but not always. A pull-up resistor is used for a default state of HIGH, and a pull-down resistor is used for a default state of LOW. The drive current of the controller, leakage current into the SN74LV244A-Q1 (as specified in the *Electrical Characteristics*), and the desired input transition rate limits the resistor size. A 10-k Ω resistor value is often used due to these factors.

The SN74LV244A-Q1 has CMOS inputs and thus requires fast input transitions to operate correctly, as defined in the *Recommended Operating Conditions* table. Slow input transitions can cause oscillations, additional power consumption, and reduction in device reliability.

Refer to the Feature Description section for additional information regarding the inputs for this device.

9.2.3 Output Considerations

The positive supply voltage is used to produce the output HIGH voltage. Drawing current from the output will decrease the output voltage as specified by the V_{OH} specification in the *Electrical Characteristics*. The ground voltage is used to produce the output LOW voltage. Sinking current into the output will increase the output voltage as specified by the V_{OL} specification in the *Electrical Characteristics*.

Push-pull outputs that could be in opposite states, even for a very short time period, should never be connected directly together. This can cause excessive current and damage to the device.

Two channels within the same device with the same input signals can be connected in parallel for additional output drive strength.

Unused outputs can be left floating. Do not connect outputs directly to V_{CC} or ground.

Refer to the Feature Description section for additional information regarding the outputs for this device.

9.2.4 Detailed Design Procedure

- Add a decoupling capacitor from V_{CC} to GND. The capacitor needs to be placed physically close to the device and electrically close to both the V_{CC} and GND pins. An example layout is shown in the *Layout* section.
- 2. Ensure the capacitive load at the output is ≤ 50 pF. This is not a hard limit; it will, however, ensure optimal performance. This can be accomplished by providing short, appropriately sized traces from the SN74LV244A-Q1 to one or more of the receiving devices.
- 3. Ensure the resistive load at the output is larger than $(V_{CC} / I_{O(max)}) \Omega$. This will ensure that the maximum output current from the *Absolute Maximum Ratings* is not violated. Most CMOS inputs have a resistive load measured in M Ω ; much larger than the minimum calculated previously.
- 4. Thermal issues are rarely a concern for logic gates; the power consumption and thermal increase, however, can be calculated using the steps provided in the application report, CMOS Power Consumption and Cpd Calculation.



9.2.5 Application Curves




图 9-2. Simulated Signal Integrity at the Receiver With Different Damping Resistor (R_d) Values

9.3 Power Supply Recommendations

The power supply can be any voltage between the minimum and maximum supply voltage rating located in the *Absolute Maximum Ratings* section. Each V_{CC} terminal must have a good bypass capacitor to prevent power disturbance. For devices with a single supply, TI recommends a 0.1- μ F capacitor; if there are multiple V_{CC} terminals, then TI recommends a 0.01- μ F or 0.022- μ F capacitor for each power terminal. Multiple bypass capacitors can be paralleled to reject different frequencies of noise. Frequencies of 0.1 μ F and 1 μ F are commonly used in parallel. The bypass capacitor must be installed as close as possible to the power terminal for best results.

9.4 Layout

9.4.1 Layout Guidelines

When using multiple bit logic devices, inputs should not float. In many cases, functions or parts of functions of digital logic devices are unused. Some examples are when only two inputs of a triple-input AND gate are used, or when only 3 of the 4-buffer gates are used. Such unused input pins must not be left unconnected because the undefined voltages at the outside connections result in undefined operational states. All unused inputs of digital logic devices must be connected to a logic high or logic low voltage, as defined by the input voltage specifications, to prevent them from floating. The logic level that must be applied to any particular unused input depends on the function of the device. Generally, the inputs are tied to GND or V_{CC}, whichever makes more sense for the logic function or is more convenient.



9.4.2 Layout Example




图 9-3. Layout Example for the SN74LV244A-Q1 in the WRKS Package



10 Device and Documentation Support

10.1 Related Documentation

For related documentation, see the following:

- Texas Instruments, Power-Up Behavior of Clocked Devices
- Texas Instruments, Introduction to Logic

10.2 Receiving Notification of Documentation Updates

To receive notification of documentation updates—including silicon errata—go to the product folder for your device on ti.com. In the upper right-hand corner, click the *Alert me* button. This registers you to receive a weekly digest of product information that has changed (if any). For change details, check the revision history of any revised document.

10.3 支持资源

TI E2E™ 支持论坛是工程师的重要参考资料,可直接从专家获得快速、经过验证的解答和设计帮助。搜索现有解 答或提出自己的问题可获得所需的快速设计帮助。

链接的内容由各个贡献者"按原样"提供。这些内容并不构成 TI 技术规范,并且不一定反映 TI 的观点;请参阅 TI 的《使用条款》。

10.4 Trademarks

TI E2E[™] is a trademark of Texas Instruments. 所有商标均为其各自所有者的财产。

10.5 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理 和安装程序,可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级,大至整个器件故障。精密的集成电路可能更容易受到损坏,这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

10.6 术语表

TI 术语表 本术语表列出并解释了术语、首字母缩略词和定义。

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

www.ti.com 16-Apr-2023

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
SN74LV244AQDGSRQ1	ACTIVE	VSSOP	DGS	20	5000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	L244Q	Samples
SN74LV244AQWRKSRQ1	ACTIVE	VQFN	RKS	20	3000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 125	LV244AQ	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE OPTION ADDENDUM

www.ti.com 16-Apr-2023

OTHER QUALIFIED VERSIONS OF SN74LV244A-Q1:

Catalog : SN74LV244A

● Enhanced Product : SN74LV244A-EP

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product

• Enhanced Product - Supports Defense, Aerospace and Medical Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 17-Apr-2023

TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74LV244AQDGSRQ1	VSSOP	DGS	20	5000	330.0	16.4	5.4	5.4	1.45	8.0	16.0	Q1
SN74LV244AQWRKSRQ1	VQFN	RKS	20	3000	180.0	12.4	2.8	4.8	1.2	4.0	12.0	Q1

www.ti.com 17-Apr-2023




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74LV244AQDGSRQ1	VSSOP	DGS	20	5000	356.0	356.0	35.0
SN74LV244AQWRKSRQ1	VQFN	RKS	20	3000	210.0	185.0	35.0

2.5 x 4.5, 0.5 mm pitch


PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





PLASTIC QUAD FLATPACK - NO LEAD




NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- 5. Vias are optional depending on application, refer to device data sheet. If some or all are implemented, recommended via locations are shown.



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



重要声明和免责声明

TI"按原样"提供技术和可靠性数据(包括数据表)、设计资源(包括参考设计)、应用或其他设计建议、网络工具、安全信息和其他资源,不保证没有瑕疵且不做出任何明示或暗示的担保,包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任:(1) 针对您的应用选择合适的 TI 产品,(2) 设计、验证并测试您的应用,(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更,恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务,TI 对此概不负责。

TI 提供的产品受 TI 的销售条款或 ti.com 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023,德州仪器 (TI) 公司