


- Meet or Exceed the Requirements of TIA/EIA-232-F and ITU Recommendation V.28
- Very Low Power Consumption . . . 5 mW Typ
- Wide Driver Supply Voltage . . . ± 4.5 V to ± 15 V
- Driver Output Slew Rate Limited to 30 V/ μ s Max
- Receiver Input Hysteresis . . . 1000 mV Typ
- Push-Pull Receiver Outputs
- On-Chip Receiver 1- μ s Noise Filter

SN65C1154 . . . N PACKAGE
SN75C1154 . . . DW, N, OR NS PACKAGE
(TOP VIEW)



description/ordering information

The SN65C1164 and SN75C1154 are low-power BiMOS devices containing four independent drivers and receivers that are used to interface data terminal equipment (DTE) with data circuit-terminating equipment (DCE). These devices are designed to conform to TIA/EIA-232-F. The drivers and receivers of the SN65C1154 and SN75C1154 are similar to those of the SN75C188 quadruple driver and SN75C189A quadruple receiver, respectively. The drivers have a controlled output slew rate that is limited to a maximum of 30 V/ μ s and the receivers have filters that reject input noise pulses of shorter than 1 μ s. Both these features eliminate the need for external components.

The SN65C1154 and SN75C1154 have been designed using low-power techniques in a BiMOS technology. In most applications, the receivers contained in these devices interface to single inputs of peripheral devices such as ACEs, UARTs, or microprocessors. By using sampling, such peripheral devices usually are insensitive to the transition times of the input signals. If this is not the case, or for other uses, it is recommended that the SN65C1154 and SN75C1154 receiver outputs be buffered by single Schmitt input gates or single gates of the HCMOS, ALS, or 74F logic families.

ORDERING INFORMATION

| TA | PACKAGE [†] | | ORDERABLE PART NUMBER | TOP-SIDE MARKING |
|---------------|----------------------|--------------|-----------------------|------------------|
| –40°C to 85°C | PDIP (N) | Tube of 20 | SN65C1154N | SN65C1154N |
| 0°C to 70°C | PDIP (N) | Tube of 20 | SN75C1154N | SN75C1154N |
| | SOIC (DW) | Tube of 25 | SN75C1154DW | SN75C1154 |
| | | Reel of 2500 | SN75C1154DWR | |
| | SOP (NS) | Reel of 2000 | SN75C1154NSR | SN75C1154 |

[†] Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SN65C1154, SN75C1154 QUADRUPLE LOW-POWER DRIVERS/RECEIVERS


SLLS151D – DECEMBER 1988 – REVISED APRIL 2003

logic diagram (positive logic)


Typical of Each Receiver



Typical of Each Driver



schematics of inputs and outputs



Resistor values shown are nominal.

SN65C1154, SN75C1154 QUADRUPLE LOW-POWER DRIVERS/RECEIVERS

SLLS151D – DECEMBER 1988 – REVISED APRIL 2003

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)[†]

| | |
|--|--|
| Supply voltage: V_{DD} (see Note 1) | 15 V |
| V_{SS} | -15 V |
| V_{CC} | 7 V |
| Input voltage range, V_I : Driver | V_{SS} to V_{DD} |
| Receiver | -30 V to 30 V |
| Output voltage range, V_O : Driver | ($V_{SS} - 6$ V) to ($V_{DD} + 6$ V) |
| Receiver | -0.3 V to ($V_{CC} + 0.3$ V) |
| Package thermal impedance, θ_{JA} (see Notes 2 and 3): DW package | 58°C/W |
| N package | 69°C/W |
| NS package | 60°C/W |
| Operating virtual junction temperature, T_J | 150°C |
| Storage temperature range, T_{stg} | -65°C to 150°C |
| Lead temperature 1.6 mm (1/16 inch) from case for 10 seconds | 260°C |

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTES: 1. All voltage s are with respect to the network GND terminal.

2. Maximum power dissipation is a function of T_J (max), θ_{JA} , and T_A . The maximum allowable power dissipation at any allowable ambient temperature is $P_D = (T_J(\max) - T_A)/\theta_{JA}$. Operating at the absolute maximum T_J of 150°C can affect reliability.
3. The package thermal impedance is calculated in accordance with JEDEC 51-7.

recommended operating conditions

| | | MIN | NOM | MAX | UNIT |
|----------|--------------------------------|-----------|--------------|----------|------|
| V_{DD} | Supply voltage | 4.5 | 12 | 15 | V |
| V_{SS} | Supply voltage | -4.5 | -12 | -15 | V |
| V_{CC} | Supply voltage | 4.5 | 5 | 6 | V |
| V_I | Input voltage | Driver | $V_{SS} + 2$ | V_{DD} | V |
| | | Receiver | ± 25 | | |
| V_{IH} | High-level input voltage | Driver | 2 | | V |
| V_{IL} | Low-level input voltage | Driver | | 0.8 | V |
| I_{OH} | High-level output current | Receiver | | -1 | mA |
| I_{OL} | High-level output current | Receiver | | 3.2 | mA |
| TA | Operating free-air temperature | SN65C1154 | -40 | 85 | °C |
| | | SN75C1154 | 0 | 70 | |

DRIVER SECTION

electrical characteristics over operating free-air temperature range, $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$, $V_{CC} = 5 \text{ V} \pm 10\%$ (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | | | MIN | TYP† | MAX | UNIT |
|---|--|--|--|------|-------|-------|---------------|
| V_{OH} High-level output voltage | $V_{IL} = 0.8 \text{ V}$, See Figure 1 | $R_L = 3 \text{ k}\Omega$, | $V_{DD} = 5 \text{ V}$, $V_{SS} = -5 \text{ V}$ | 4 | 4.5 | | V |
| | | | $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$ | 10 | 10.8 | | |
| V_{OL} (see Note 4) | $V_{IH} = 2 \text{ V}$, See Figure 1 | $R_L = 3 \text{ k}\Omega$, | $V_{DD} = 5 \text{ V}$, $V_{SS} = -5 \text{ V}$ | | -4.4 | -4 | V |
| | | | $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$ | | -10.7 | -10 | |
| I_{IH} High-level input current | $V_I = 5 \text{ V}$, | See Figure 2 | | | 1 | | μA |
| I_{IL} Low-level input current | $V_I = 0$, | See Figure 2 | | | -1 | | μA |
| $I_{OS(H)}$ High-level short-circuit output current‡ | $V_I = 0.8 \text{ V}$, | $V_O = 0 \text{ or } V_{SS}$, | See Figure 1 | -7.5 | -12 | -19.5 | mA |
| $I_{OS(L)}$ Low-level short-circuit output current‡ | $V_I = 2 \text{ V}$, | $V_O = 0 \text{ or } V_{DD}$, | See Figure 1 | 7.5 | 12 | 19.5 | mA |
| I_{DD} Supply current from V_{DD} | No load, All inputs at 2 V or 0.8 V | $V_{DD} = 5 \text{ V}$, $V_{SS} = -5 \text{ V}$ | | 115 | 250 | | μA |
| | | $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$ | | 115 | 250 | | |
| I_{SS} Supply current from V_{SS} | No load, All inputs at 2 V or 0.8 V | $V_{DD} = 5 \text{ V}$, $V_{SS} = -5 \text{ V}$ | | -115 | -250 | | μA |
| | | $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$ | | -115 | -250 | | |
| r_o Output resistance | $V_{DD} = V_{SS} = V_{CC} = 0$, | $V_O = -2 \text{ V}$ to 2 V , | See Note 5 | 300 | 400 | | Ω |

† All typical values are at $T_A = 25^\circ\text{C}$.

‡ Not more than one output should be shorted at one time.

NOTES: 4. The algebraic convention, where the more positive (less negative) limit is designated as maximum, is used in this data sheet for logic levels only.

5. Test conditions are those specified by TIA/EIA-232-F.

switching characteristics, $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$, $V_{CC} = 5 \text{ V} \pm 10\%$, $T_A = 25^\circ\text{C}$ (see Figure 3)

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---|---|------|-----|-----|------------------------|
| t_{PLH} Propagation delay time, low- to high-level output§ | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 15 \text{ pF}$ | | 1.2 | 3 | μs |
| t_{PHL} Propagation delay time, high- to low-level output§ | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 15 \text{ pF}$ | | 2.5 | 3.5 | μs |
| t_{TLH} Transition time, low- to high-level output¶ | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 15 \text{ pF}$ | 0.53 | 2 | 3.2 | μs |
| t_{THL} Transition time, high- to low-level output¶ | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 15 \text{ pF}$ | 0.53 | 2 | 3.2 | μs |
| t_{TLH} Transition time, low- to high-level output# | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 2500 \text{ pF}$ | | 1 | 2 | μs |
| t_{THL} Transition time, high- to low-level output# | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 2500 \text{ pF}$ | | 1 | 2 | μs |
| SR Output slew rate | $R_L = 3 \text{ to } 7 \text{ k}\Omega$, $C_L = 15 \text{ pF}$ | 4 | 10 | 30 | $\text{V}/\mu\text{s}$ |

§ t_{PHL} and t_{PLH} include the additional time due to on-chip slew rate control and are measured at the 50% points.

¶ Measured between 10% and 90% points of output waveform

Measured between 3 V and -3 V points of output waveform (TIA/EIA-232-F conditions) with all unused inputs tied either high or low

SN65C1154, SN75C1154 QUADRUPLE LOW-POWER DRIVERS/RECEIVERS

SLLS151D – DECEMBER 1988 – REVISED APRIL 2003

RECEIVER SECTION

electrical characteristics over operating free-air temperature range, $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$, $V_{CC} = 5 \text{ V} \pm 10\%$ (unless otherwise noted)

| PARAMETER | TEST CONDITIONS | | | MIN | TYP† | MAX | UNIT | |
|-------------|--|---|--|------|-------|-------|---------------|----|
| V_{IT+} | Positive-going input threshold voltage | See Figure 5 | | 1.7 | 2.1 | 2.55 | V | |
| V_{IT-} | Negative-going input threshold voltage | See Figure 5 | | 0.65 | 1 | 1.25 | V | |
| V_{hys} | Input hysteresis voltage ($V_{IT+} - V_{IT-}$) | | | 600 | 1000 | | mV | |
| V_{OH} | High-level output voltage | $V_I = 0.75 \text{ V}$, $I_{OH} = -20 \mu\text{A}$, See Figure 5 and Note 6 | | | 3.5 | | V | |
| | | $V_I = 0.75 \text{ V}$, $I_{OH} = -1 \text{ mA}$, See Figure 5 | | | 2.8 | 4.4 | | |
| | | $V_{CC} = 4.5 \text{ V}$ | | | 3.8 | 4.9 | | |
| | | $V_{CC} = 5 \text{ V}$ | | | 4.3 | 5.4 | | |
| V_{OL} | Low-level output voltage | $V_I = 3 \text{ V}$, $I_{OL} = 3.2 \text{ mA}$, See Figure 5 | | 0.17 | 0.4 | | V | |
| I_{IH} | High-level input current | $V_I = 25 \text{ V}$ | | | 3.6 | 4.6 | 8.3 | mA |
| | | $V_I = 3 \text{ V}$ | | | 0.43 | 0.55 | 1 | |
| I_{IL} | Low-level input current | $V_I = -25 \text{ V}$ | | | -3.6 | -5 | -8.3 | mA |
| | | $V_I = -3 \text{ V}$ | | | -0.43 | -0.55 | -1 | |
| $I_{OS(H)}$ | Short-circuit output at high level | $V_I = 0.75 \text{ V}$, $V_O = 0$, See Figure 4 | | | -8 | -15 | mA | |
| $I_{OS(L)}$ | Short-circuit output at low level | $V_I = V_{CC}$, $V_O = V_{CC}$, See Figure 4 | | | 13 | 25 | mA | |
| I_{CC} | Supply current from V_{CC} | No load, All inputs at 0 or 5 V | $V_{DD} = 5 \text{ V}$, $V_{SS} = -5 \text{ V}$ | | 400 | 600 | μA | |
| | | | $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$ | | 400 | 600 | | |

† All typical values are at $T_A = 25^\circ\text{C}$.

NOTE 6: If the inputs are left unconnected, the receiver interprets this as an input low and the receiver outputs will remain in the high state.

switching characteristics, $V_{DD} = 12 \text{ V}$, $V_{SS} = -12 \text{ V}$, $V_{CC} = 5 \text{ V} \pm 10\%$, $T_A = 25^\circ\text{C}$

| PARAMETER | TEST CONDITIONS | | | MIN | TYP | MAX | UNIT |
|------------|---|--|--|-----|-----|-----|---------------|
| t_{PLH} | Propagation delay time, low- to high-level output | $C_L = 50 \text{ pF}$, $R_L = 5 \text{ k}\Omega$, See Figure 6 | | 3 | 4 | | μs |
| t_{PHL} | Propagation delay time, high- to low-level output | $C_L = 50 \text{ pF}$, $R_L = 5 \text{ k}\Omega$, See Figure 6 | | 3 | 4 | | μs |
| t_{TLH} | Transition time, low- to high-level output | $C_L = 50 \text{ pF}$, $R_L = 5 \text{ k}\Omega$, See Figure 6 | | 300 | 450 | | ns |
| t_{THL} | Transition time, high- to low-level output | $C_L = 50 \text{ pF}$, $R_L = 5 \text{ k}\Omega$, See Figure 6 | | 100 | 300 | | ns |
| $t_{w(N)}$ | Duration of longest pulse rejected as noise† | $C_L = 50 \text{ pF}$, $R_L = 5 \text{ k}\Omega$ | | 1 | | 4 | μs |

† The receiver ignores any positive- or negative-going pulse that is less than the minimum value of $t_{w(N)}$ and accepts any positive- or negative-going pulse greater than the maximum of $t_{w(N)}$.

PARAMETER MEASUREMENT INFORMATION




Figure 1. Driver Test Circuit
(V_{OH} , V_{OL} , I_{OSL} , I_{OSH})





Figure 2. Driver Test Circuit (I_{IL} , I_{IH})



TEST CIRCUIT




Figure 3. Driver Test Circuit and Voltage Waveforms




Figure 4. Receiver Test Circuit (I_{OSH} , I_{OSL})





Figure 5. Receiver Test Circuit (V_{IT} , V_{OL} , V_{OH})

SN65C1154, SN75C1154 QUADRUPLE LOW-POWER DRIVERS/RECEIVERS

SLLS151D – DECEMBER 1988 – REVISED APRIL 2003

PARAMETER MEASUREMENT INFORMATION



NOTES: A. The pulse generator has the following characteristics: $t_W = 25 \mu s$, PRR = 20 kHz, $Z_O = 50 \Omega$, $t_f = t_f < 50 \text{ ns}$.
B. C_L includes probe and jig capacitance.

Figure 6. Receiver Test Circuit and Voltage Waveforms

PACKAGING INFORMATION

| Orderable part number | Status (1) | Material type (2) | Package Pins | Package qty Carrier | RoHS (3) | Lead finish/ Ball material (4) | MSL rating/ Peak reflow (5) | Op temp (°C) | Part marking (6) |
|------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| SN65C1154N | Active | Production | PDIP (N) 20 | 20 TUBE | Yes | NIPDAU | N/A for Pkg Type | -40 to 85 | SN65C1154N |
| SN65C1154N.A | Active | Production | PDIP (N) 20 | 20 TUBE | Yes | NIPDAU | N/A for Pkg Type | -40 to 85 | SN65C1154N |
| SN75C1154DW | Active | Production | SOIC (DW) 20 | 25 TUBE | Yes | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | SN75C1154 |
| SN75C1154DW.A | Active | Production | SOIC (DW) 20 | 25 TUBE | Yes | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | SN75C1154 |
| SN75C1154DWR | Active | Production | SOIC (DW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | SN75C1154 |
| SN75C1154DWR.A | Active | Production | SOIC (DW) 20 | 2000 LARGE T&R | Yes | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | SN75C1154 |
| SN75C1154N | Active | Production | PDIP (N) 20 | 20 TUBE | Yes | NIPDAU | N/A for Pkg Type | 0 to 70 | SN75C1154N |
| SN75C1154N.A | Active | Production | PDIP (N) 20 | 20 TUBE | Yes | NIPDAU | N/A for Pkg Type | 0 to 70 | SN75C1154N |

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.



⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.


Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION
REEL DIMENSIONS

TAPE DIMENSIONS


| | |
|----|---|
| A0 | Dimension designed to accommodate the component width |
| B0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN75C1154DWR | SOIC | DW | 20 | 2000 | 330.0 | 24.4 | 10.8 | 13.3 | 2.7 | 12.0 | 24.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN75C1154DWR | SOIC | DW | 20 | 2000 | 350.0 | 350.0 | 43.0 |

TUBE



*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μ m) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------------|--------|
| SN65C1154N | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |
| SN65C1154N.A | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |
| SN75C1154DW | DW | SOIC | 20 | 25 | 506.98 | 12.7 | 4826 | 6.6 |
| SN75C1154DW.A | DW | SOIC | 20 | 25 | 506.98 | 12.7 | 4826 | 6.6 |
| SN75C1154N | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |
| SN75C1154N.A | N | PDIP | 20 | 20 | 506 | 13.97 | 11230 | 4.32 |

N (R-PDIP-T**)

16 PINS SHOWN

PLASTIC DUAL-IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).
B. This drawing is subject to change without notice.

△ Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).

△ The 20 pin end lead shoulder width is a vendor option, either half or full width.


PACKAGE OUTLINE

DW0020A



SOIC - 2.65 mm max height

SOIC



NOTES:


1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
5. Reference JEDEC registration MS-013.

EXAMPLE BOARD LAYOUT


DW0020A

SOIC - 2.65 mm max height

SOIC



LAND PATTERN EXAMPLE
SCALE:6X



SOLDER MASK DETAILS

4220724/A 05/2016

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DW0020A

SOIC - 2.65 mm max height

SOIC



SOLDER PASTE EXAMPLE
BASED ON 0.125 mm THICK STENCIL
SCALE:6X

4220724/A 05/2016

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025