



## TLC59213x 8-Bit Parallel In and Out Darlington Source Driver With Latch

### 1 Features

- Output Current on Each Channel ( $I_{OUT}$  Max = –500 mA)
- $V_{CE(sus)} = 13.2$  V
- Input Compatible With TTL/5-V CMOS
- Clear ( $\overline{CLR}$ ) and Clock (CLK) TTL/CMOS Control Inputs
- CLR Control Input to Off the Output
- Darlington Source Driver
- Clock Input Up to 1 MHz
- Enhanced Hold Time ( $t_h$ ) on TLC59213A
- Temperature Range: –40°C to 85°C

### 2 Applications

- Lamp and Display (LED)
- Hammer
- Relay

### 3 Description

The TLC59213 and TLC59213A are 8-bit source drivers with input latch with CLK input and  $\overline{CLR}$  to set the output OFF. The TLC59213 and TLC59213A have large output source currents up to 500 mA with Darlington transistor and collectors tied to  $V_{CC}$ . These feature make the device optimum level of driving the matrix of ink jet printer head, LEDs, and the scan-side of resistor's matrix. The TLC59213 and TLC59213A differ only in the Data Hold Time Specification ( $t_h$ ).

The clamp diode is between output and ground for switching inductive load.


All inputs are TTL/CMOS, which enable to any logic-level inputs such as MCU, CPU or SN74LV594 (serial to parallel) and the output enable LED matrix display. It can also be used with another device sink driver such as TLC59210, TLC59211 and TLC59212.

#### Device Information<sup>(1)</sup>

| PART NUMBER | PACKAGE    | BODY SIZE (NOM)    |
|-------------|------------|--------------------|
| TLC59213    | PDIP (20)  | 24.33 mm × 6.35 mm |
| TLC59213A   | TSSOP (20) | 6.50 mm × 4.40 mm  |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### Typical Application Diagram



## Table of Contents

|                                                  |          |                                                                  |           |
|--------------------------------------------------|----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                          | <b>1</b> | 8.2 Functional Block Diagram .....                               | 7         |
| <b>2 Applications</b> .....                      | <b>1</b> | 8.3 Feature Description .....                                    | 7         |
| <b>3 Description</b> .....                       | <b>1</b> | 8.4 Device Functional Modes .....                                | 7         |
| <b>4 Revision History</b> .....                  | <b>2</b> | <b>9 Application and Implementation</b> .....                    | <b>8</b>  |
| <b>5 Pin Configuration and Functions</b> .....   | <b>3</b> | 9.1 Application Information .....                                | 8         |
| <b>6 Specifications</b> .....                    | <b>4</b> | 9.2 Typical Application .....                                    | 8         |
| 6.1 Absolute Maximum Ratings .....               | 4        | <b>10 Power Supply Recommendations</b> .....                     | <b>9</b>  |
| 6.2 ESD Ratings .....                            | 4        | <b>11 Layout</b> .....                                           | <b>10</b> |
| 6.3 Recommended Operating Conditions .....       | 4        | 11.1 Layout Guidelines .....                                     | 10        |
| 6.4 Electrical Characteristics .....             | 4        | 11.2 Layout Example .....                                        | 10        |
| 6.5 Timing Requirements .....                    | 5        | <b>12 Device and Documentation Support</b> .....                 | <b>11</b> |
| 6.6 Switching Characteristics .....              | 5        | 12.1 Community Resources .....                                   | 11        |
| 6.7 Typical Characteristics .....                | 5        | 12.2 Trademarks .....                                            | 11        |
| <b>7 Parameter Measurement Information</b> ..... | <b>6</b> | 12.3 Electrostatic Discharge Caution .....                       | 11        |
| <b>8 Detailed Description</b> .....              | <b>7</b> | 12.4 Glossary .....                                              | 11        |
| 8.1 Overview .....                               | 7        | <b>13 Mechanical, Packaging, and Orderable Information</b> ..... | <b>11</b> |


## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision A (March 2010) to Revision B                                                                                                                                                                                                                                                                                                                                                                                                  | Page     |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|
| <ul style="list-style-type: none"> <li>Added <i>Pin Configuration and Functions</i> section, <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i>, <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section .....</li> </ul> | <b>1</b> |

## 5 Pin Configuration and Functions

**N or PW Package  
20-Pin PDIP or TSSOP  
Top View**



**Pin Functions**

| PIN             |     | I/O | DESCRIPTION                                  |
|-----------------|-----|-----|----------------------------------------------|
| NAME            | NO. |     |                                              |
| CLR             | 1   | I   | Direct clear of output                       |
| D1              | 2   | I   | Input control to the current source driver   |
| D2              | 3   | I   | Input control to the current source driver   |
| D3              | 4   | I   | Input control to the current source driver   |
| D4              | 5   | I   | Input control to the current source driver   |
| D5              | 6   | I   | Input control to the current source driver   |
| D6              | 7   | I   | Input control to the current source driver   |
| D7              | 8   | I   | Input control to the current source driver   |
| D8              | 9   | I   | Input control to the current source driver   |
| CLK             | 10  | I   | Clock to positive edge triggered D flipflops |
| GND             | 11  | —   | Ground                                       |
| Y8              | 12  | O   | Output to load                               |
| Y7              | 13  | O   | Output to load                               |
| Y6              | 14  | O   | Output to load                               |
| Y5              | 15  | O   | Output to load                               |
| Y4              | 16  | O   | Output to load                               |
| Y3              | 17  | O   | Output to load                               |
| Y2              | 18  | O   | Output to load                               |
| Y1              | 19  | O   | Output to load                               |
| V <sub>cc</sub> | 20  | I   | Supply voltage                               |

## 6 Specifications

### 6.1 Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

|                  |                           | MIN                  | MAX                   | UNIT |
|------------------|---------------------------|----------------------|-----------------------|------|
| V <sub>DD</sub>  | Supply voltage            | –0.5                 | 15                    | V    |
| V <sub>I</sub>   | Input voltage             | –0.5                 | V <sub>CC</sub> + 0.5 | V    |
|                  | Collector-emitter voltage | –0.5                 | 15                    | V    |
| I <sub>O</sub>   | Peak output current       |                      | –500                  | mA   |
| I <sub>IK</sub>  | Input clamp current       | V <sub>I</sub> < 0 V | –20                   | mA   |
| I <sub>OK</sub>  | Output clamp current      | V <sub>O</sub> < 0 V | –500                  | mA   |
| T <sub>stg</sub> | Storage temperature       | –65                  | 150                   | °C   |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 6.2 ESD Ratings

|                    |                                                                                | VALUE | UNIT |
|--------------------|--------------------------------------------------------------------------------|-------|------|
| V <sub>(ESD)</sub> | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001 <sup>(1)</sup>              | ±2000 | V    |
|                    | Charged-device model (CDM), per JEDEC specification JESD22-C101 <sup>(2)</sup> | ±1000 |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

|                 |                                |            | MIN              | MAX  | UNIT |
|-----------------|--------------------------------|------------|------------------|------|------|
| V <sub>CC</sub> | Supply voltage                 |            | 4.5              | 13.2 | V    |
| V <sub>IH</sub> | High-level input voltage       |            | 2                |      | V    |
| V <sub>IL</sub> | Low-level input voltage        |            |                  | 0.8  | V    |
| I <sub>O</sub>  | Output current (8 channel)     | N package  | Duty cycle < 10% | 400  | mA   |
|                 |                                |            | Duty cycle < 50% | 200  |      |
|                 |                                | PW package | Duty cycle < 10% | 350  |      |
|                 |                                |            | Duty cycle < 50% | 170  |      |
| T <sub>A</sub>  | Operating free-air temperature |            | –40              | 85   | °C   |

### 6.4 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER            | TEST CONDITIONS           | MIN                                                       | TYP             | MAX  | UNIT |
|----------------------|---------------------------|-----------------------------------------------------------|-----------------|------|------|
| I <sub>CEX</sub>     | Output leakage current    | V <sub>CC</sub> = 13.2 V, Outputs off                     |                 | 2    | μA   |
| V <sub>CE(sus)</sub> | Output saturation voltage | I <sub>OUT</sub> = –350 mA                                |                 | 2.35 | V    |
|                      |                           | I <sub>OUT</sub> = –225 mA                                |                 | 2.15 |      |
|                      |                           | I <sub>OUT</sub> = –100 mA                                |                 | 1.96 |      |
| I <sub>I</sub>       | Input current             | V <sub>CC</sub> = 13.2 V, V <sub>I</sub> = 0 or 13.2 V    |                 | 1    | μA   |
| V <sub>f</sub>       | Clamp forward voltage     | I <sub>f</sub> = –350 mA                                  |                 | –2   | V    |
| I <sub>CC</sub>      | Supply current            | V <sub>CC</sub> = 13.2 V,<br>V <sub>I</sub> = 0 or 13.2 V | All outputs OFF | 4.6  | mA   |
|                      |                           |                                                           | All outputs ON  | 4.8  |      |
| C <sub>I</sub>       | Input capacitance         |                                                           |                 | 10   | pF   |

## 6.5 Timing Requirements

over recommended operating free-air temperature range (unless otherwise noted), see [Figure 3](#)


|          |             |                                             |                        | MIN                                                                                         | MAX | UNIT |
|----------|-------------|---------------------------------------------|------------------------|---------------------------------------------------------------------------------------------|-----|------|
| $t_{su}$ | Setup time  | D before CLK $\uparrow$                     |                        | 50                                                                                          |     | ns   |
|          |             | $\overline{CLR}$ high before CLK $\uparrow$ |                        | 50                                                                                          |     | ns   |
| $t_h$    | Hold time   | D after CLK $\uparrow$                      | TLC59213,<br>TLC59213A | $T_A = -40^\circ\text{C}$ to $85^\circ\text{C}$                                             | 50  | ns   |
|          |             |                                             | TLC59213               | $T_A = 0^\circ\text{C}$ to $70^\circ\text{C}$                                               | 25  |      |
|          |             |                                             | TLC59213A              | $T_A = 0^\circ\text{C}$ to $70^\circ\text{C}$ , $V_{CC} = 4.5\text{ V}$ to $5.5\text{ V}$   | 15  |      |
|          |             |                                             |                        | $T_A = 0^\circ\text{C}$ to $70^\circ\text{C}$ , $V_{CC} = 10.8\text{ V}$ to $13.2\text{ V}$ | 19  |      |
| $t_w$    | Pulse width | CLK, $\overline{CLR}$                       |                        | 100                                                                                         |     | ns   |

## 6.6 Switching Characteristics


over operating free-air temperature range (unless otherwise noted), see [Figure 3](#)

| PARAMETER  | FROM<br>(INPUT)                                     | TO<br>(OUTPUT)   | TEST<br>CONDITIONS | $T_A = 25^\circ\text{C}$         |     |     | $T_A = -40^\circ\text{C}$ to $85^\circ\text{C}$ |     | UNIT |
|------------|-----------------------------------------------------|------------------|--------------------|----------------------------------|-----|-----|-------------------------------------------------|-----|------|
|            |                                                     |                  |                    | MIN                              | TYP | MAX | MIN                                             | MAX |      |
| $t_{PLH}$  | Propagation delay time,<br>low-to-high level output | CLK              | Y                  | RL = 25 $\Omega$ ,<br>CL = 15 pF | 107 | 200 |                                                 | 250 | ns   |
| $t_{PHL}$  | Propagation delay time,<br>high-to-low level output | CLK              | Y                  | RL = 25 $\Omega$ ,<br>CL = 15 pF | 111 | 200 |                                                 | 250 | ns   |
| $t_{PHLR}$ | Propagation delay time,<br>high-to-low level output | $\overline{CLR}$ | Y                  | RL = 25 $\Omega$ ,<br>CL = 15 pF | 104 | 200 |                                                 | 250 | ns   |

## 6.7 Typical Characteristics





**Figure 1. Maximum Output Current vs Duty Cycle (TSSOP (PW) Package)**



**Figure 2. Maximum Output Current vs Duty Cycle (DIP (N) Package)**

## 7 Parameter Measurement Information


**TEST CIRCUIT**

**VOLTAGE WAVEFORMS**

- $C_L$  includes probe and jig capacitance.
- All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1\text{ MHz}$ ,  $Z_O = 50\ \Omega$ ,  $t_r \leq 3\text{ ns}$ , and  $t_f \leq 3\text{ ns}$ .
- The outputs are measured one at a time with one transition per measurement.


**Figure 3. Test Circuit and Voltage Waveforms**

## 8 Detailed Description

### 8.1 Overview

The TLC59213 device is an 8-bit Darlington source driver with latch for large-output source currents up to 500 mA.

### 8.2 Functional Block Diagram



(1) This symbol is in accordance with ANSI/IEEE Standard 91-1984 and IEC Publication 617-12.

### 8.3 Feature Description

Each of the 8 channels is controlled by its input ( $D_n$ ), a direct clear ( $\overline{CLR}$ ), and clock (CLK) through a positive-edge-triggered D-type flip-flops. Information at the data (D) input meeting the setup time requirements is transferred to the output (Y) on the positive-going edge of the clock (CLK) pulse. When CLK is at either the high or low level, the D-input has no effect at the output. When  $\overline{CLR}$  is at low level, the D-input has no effect at the output.

### 8.4 Device Functional Modes

Table 1 lists the functional modes of the TLC59213.

**Table 1. Function Table (Each Latch)<sup>(1)</sup>**

| INPUTS           |     |   | OUTPUT<br>Y |
|------------------|-----|---|-------------|
| $\overline{CLR}$ | CLK | D |             |
| L                | X   | X | Z (OFF)     |
| H                | ↑   | L | Z (OFF)     |
| H                | ↑   | H | H (ON)      |
| H                | L   | X | $Y_0$       |
| H                | ↓   | X | $Y_0$       |

(1) L: Low-level  
H: High-level  
X: Irrelevant  
↑: Rising edge  
↓: Falling edge  
Z: High-impedance (OFF)

## 9 Application and Implementation


### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 9.1 Application Information

In LED display application, TLC59213 is used to drive the current source for 8 LEDs in parallel. LED display pattern can be created by providing different bit pattern. At every positive clock edge, new bit pattern will be transferred to LED display.

### 9.2 Typical Application



**Figure 4. Typical Application Diagram**

#### 9.2.1 Design Requirements

For LED display application, LED is selected based on the application. The current level is determined by the required brightness. Given the available supply, the resistor value could be determined. The maximum output current is constrained by the duty cycle. See [Figure 1](#) and [Figure 2](#).

#### 9.2.2 Detailed Design Procedure

The selection of supply voltage (VCC), LED, and resistor sets the current of the LED.


$$V_R + V_L + V_{CE} = V_{CC} \quad (1)$$

$$I = (V_{CC} - V_L - V_{CE}) / R \quad (2)$$

$V_R$  is the voltage drop across the resistor,  $V_L$  is the voltage drop across the LED when LED is on,  $V_{CE}$  is the collector-to-emitter voltage of the Darlington current source driver, when the driver is enabled. For example, when  $V_{CC} = 12\text{ V}$ ,  $V_L = 2.9\text{ V}$ , and  $V_{CE} = 1.6\text{ V}$ , a 75-Ω resistor is used to obtain output current 100 mA.

## Typical Application (continued)

### 9.2.3 Application Curve



**Figure 5. Output Voltage and Current Response**

## 10 Power Supply Recommendations


The supply voltage to TLC59213 is from 4.5 V to 13.2 V.

## 11 Layout

### 11.1 Layout Guidelines

The traces that carry current from the output pins must be wide enough to support the current.

### 11.2 Layout Example



**Figure 6. Layout Recommendation**

## 12 Device and Documentation Support

### 12.1 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

**TI E2E™ Online Community** *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At [e2e.ti.com](http://e2e.ti.com), you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

### 12.2 Trademarks

E2E is a trademark of Texas Instruments.  
All other trademarks are the property of their respective owners.

### 12.3 Electrostatic Discharge Caution



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 12.4 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 13 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins  | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|-----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TLC59213AIN</a>   | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC59213AIN         |
| TLC59213AIN.A                 | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC59213AIN         |
| <a href="#">TLC59213AIPW</a>  | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -            | Y59213A             |
| <a href="#">TLC59213AIPWR</a> | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | Y59213A             |
| TLC59213AIPWR.A               | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | Y59213A             |
| <a href="#">TLC59213AIPWT</a> | Obsolete      | Production           | TSSOP (PW)   20 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | Y59213A             |
| <a href="#">TLC59213IN</a>    | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC59213IN          |
| TLC59213IN.A                  | Active        | Production           | PDIP (N)   20   | 20   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | TLC59213IN          |
| <a href="#">TLC59213IPWR</a>  | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | Y59213              |
| TLC59213IPWR.A                | Active        | Production           | TSSOP (PW)   20 | 2000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | Y59213              |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLC59213AIPWR | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |
| TLC59213IPWR  | TSSOP        | PW              | 20   | 2000 | 330.0              | 16.4               | 6.95    | 7.0     | 1.4     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal



| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLC59213AIPWR | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |
| TLC59213IPWR  | TSSOP        | PW              | 20   | 2000 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal

| Device        | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|---------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TLC59213AIN   | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| TLC59213AIN.A | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| TLC59213IN    | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |
| TLC59213IN.A  | N            | PDIP         | 20   | 20  | 506    | 13.97  | 11230  | 4.32   |



4220206/A 02/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-153.

# EXAMPLE BOARD LAYOUT


PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE: 10X



4220206/A 02/2017

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

PW0020A

TSSOP - 1.2 mm max height

SMALL OUTLINE PACKAGE



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE: 10X

4220206/A 02/2017


NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.


N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **<br>DIM      | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



4040049/E 12/2002

NOTES:

- A. All linear dimensions are in inches (millimeters).  
B. This drawing is subject to change without notice.
-  Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).  
 The 20 pin end lead shoulder width is a vendor option, either half or full width.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025