TI Designs

Display DevPack Design Guide



TI Designs

TI Designs provide the foundation that you need including methodology, testing and design files to quickly evaluate and customize the system. TI Designs help *you* accelerate your time to market.

Design Resources

TIDC-DEVPACK- DISPLAY	Tool Folder Containing Design Files
CC2650	Product Folder
CC2640	Product Folder
CC2630	Product Folder
CC2620	Product Folder
SensorTag	Product Folder
Debug DevPack	Product Folder




ASK Our E2E Experts
WEBENCH® Calculator Tools

Design Features

- · Add a Display to Your SensorTag
- Offers a Low Power Graphical Display
- Enables Wearable and Display Applications
- Works With the SensorTag Application

Featured Applications

- Wearables
- Refrigerator Display
- · Remote Display
- Debugging
- Weather Stations
- Sensor Nodes







SimpleLink is a trademark of Texas Instruments. Bluetooth® Smart is a trademark of Bluetooth SIG. Bluetooth is a registered trademark of Bluetooth SIG. Sharp is a registered trademark of Sharp Corporation. ZigBee is a trademark of ZigBee Alliance. All other trademarks are the property of their respective owners.





An IMPORTANT NOTICE at the end of this TI reference design addresses authorized use, intellectual property matters and other important disclaimers and information.

1 Key System Specifications

- 1.28" Graphical Display
- 96 x 96 Pixel Resolution
- Ultra-Low Power, Sharp® LS013B4DN04 Memory LC
- SPI Interface

2 System Description

Add a display to your SensorTag with the Display DevPack. Plug it into the SensorTag DevPack expansion header and expand your design with a 96×96 pixel graphical display. TI designed the display for wearable applications, weather stations, or any portable display application displaying information from the web.

The SensorTag battery powers DevPack based on ultra-low power, display technology with a typical current draw of 2 µA.

2.1 CC2650

The Display Devpack demonstrates a low-power graphical display that interfaces with a CC2650 device. The CC2650 is a wireless MCU targeting *Bluetooth*[®] Smart[™], ZigBee[™] and 6LoWPAN, and ZigBee RF4CE remote control applications.



www.ti.com Block Diagram

The device is a member of the CC26xx family of cost effective, ultra-low power, 2.4-GHz RF devices. Very low active RF and MCU current and low-power mode current consumption provide excellent battery life. This device operates on small coin-cell batteries and can be used with energy-harvesting applications.




Figure 1. CC2650 Functional Block Diagram

3 Block Diagram




Figure 2. CC2650 and Display Block Diagram



System Design Theory www.ti.com

4 System Design Theory

4.1 CC2650 SensorTag with Display DevPack

The SensorTag and Display DevPack is a complete development kit that requires no embedded software knowledge to start testing.

To get started, do the following:

- 1. Plug the Display DevPack into the SensorTag DevPack connector.
- 2. Connect the SensorTag to your smart phone using Bluetooth Smart.
- 3. Download the Display DevPack software from the application.
- 4. Control the display directly from your phone.

4.2 Embedded Software Development

The SensorTag includes open hardware and a software reference design for low cost and low-power IoT nodes. Use the SensorTag with the Debug DevPack for the lowest cost hardware development platform. You can easily port the SensorTag application between radio standards to quickly evaluate which wireless technology is best for your application.

4.3 Hardware Development

Use the SensorTag hardware as the development platform for your IoT project. The open hardware platform includes ten low-power sensors and the Display DevPack to develop and test your own sensors and display applications.



5 Getting Started Hardware

5.1 Plug the Display DevPack into the SensorTag



Figure 3. Plugging the Display DevPack into the SensorTag



5.2 Download the Display DevPack Firmware




Figure 4. Downloading the Display DevPack Firmware



5.3 Enter Text into the SensorTag Application to display it on the LCD Screen




Figure 5. Writing Text to Send it to the Display



5.4 Cut the Rubber Sleeve to Fit Your Application

To cut the rubber sleeve to fit the display, use a sharp knife to cut carefully around the edge of the display.

NOTE: Cut only around display and not the entire PCB.



Figure 6. Cutting the Rubber Sleeve to Fit the Display

6 Getting Started Firmware

The *Bluetooth* Smart firmware for the SensorTag Display DevPack is included in the *Bluetooth* low energy Stack examples (BLE-STACK-2).

7 Test Setup

See Section 5.





www.ti.com Design Files

8 Design Files

8.1 Schematics

To download the schematics for each board, see the design files at http://www.ti.com/tool/TIDC-DEVPACK-DISPLAY.








Figure 7. : Display DevPack Schematic



Design Files www.ti.com

8.2 Bill of Materials

To download the bill of materials (BOM), see the design files at <u>TIDC-DEVPACK-DISPLAY</u>.

Table 1. BOM

Designator	Quantity	Value	Description	Part Number	Manufacturer
C1	1	100 nF	CAPACITOR, CERAMIC X7R, 100 nF, 25 V, -10%/10%, -55°C/125°C, 0603, SMD	GRM188R71E104KA01D	MURATA
C2 C3	2	1 μF	CAPACITOR, CERAMIC X5R, 1 µF, 25 V, -10%/10%, -55°C/85°C, 0603, SMD	GRM188R61E105KA12D	MURATA
CR1	1	LS013B4DN04	OPTO, DISPLAY, LCD, 2.7 V TO 3.3 V, NOT APPLY	LS013B4DN04	SHARP
FIDU1 FIDU2 FIDU3 FIDU4 FIDU5 FIDU6	6	FIDU_1.27 mm	FIDUCIAL MARK, ROUND 1.27 mm		
J2	1	LSS-110-01-F- DV-A-TR	CONNECTOR, HEADER, HI-SPEED SOCKET, FEMALE, STRAIGHT,2 ROWS ,20 PINS, PITCH 0.635 mm, SMD	LSS-110-01-F-DV-A-TR	SAMTEC
J3	1	AYF531035	CONNECTOR, FLEXI, FEMALE, RIGHT ANGLE, TOP AND BOTTOM DOUBLE CONTACTS, 1 ROW, 10 PINS, PITCH 0.5 mm, SMD	AYF531035	PANASONIC INDUSTRIAL
R1	1	820 k	RESISTOR, THICK FILM, 820 k, -1%/1%, 0.1 W, 75 V, -55°C/155°C, 0603, SMD	CRCW0603820KFKEA	VISHAY

8.3 PCB Layout Recommendations

The layout of this DevPack only uses digital signals at a relatively low data rate. The layout requires no special considerations.



www.ti.com Design Files

8.3.1 Layout Prints

To download the layout prints for each board, see the design files at TIDC-DEVPACK-DISPLAY.




Figure 8. Top Silkscreen



Figure 9. Top Solder Mask




Figure 10. Top Layer



Design Files www.ti.com




Figure 11. Bottom Layer




Figure 12. Bottom Solder Mask




Figure 13. Bottom Silkscreen



www.ti.com Design Files




Figure 14. Mechanical Dimensions



Design Files www.ti.com

8.4 Cadence Project

To download the Cadence project files, see the design files at TIDC-DEVPACK-DISPLAY.

8.5 Layout Guidelines

To download the layout guidelines, see the design files at TIDC-DEVPACK-DISPLAY.

8.6 Gerber Files

To download the Gerber files, see the design files at TIDC-DEVPACK-DISPLAY.

8.7 Assembly Drawings

To download the Assembly Drawings for each board, see the design files at TIDC-DEVPACK-DISPLAY.




Figure 15. Assembly Top

Figure 16. Assembly Bottom

8.8 Software Files

Associate this BLE stack to this TI Design: http://www.ti.com/tool/ble-stack.

9 References

- 1. CC26xx SimpleLink Wireless MCU Technical Reference Manual, (SWCU117)
- 2. CC2650 SimpleLink™ Multistandard Wireless MCU, (SWRS158)
- 3. CC2640 SimpleLink Bluetooth Smart Wireless MCU, (SWRS176)
- 4. CC2630 SimpleLink 6LoWPAN / ZigBee Wireless MCU, (SWRS177)
- 5. CC2620 SimpleLink ZigBee RF4CE Wireless MCU, (SWRS156)



www.ti.com About the Author

10 About the Author

JARLE BOE is a system applications manager at TI. He manages application specific designs like the SensorTag for *Bluetooth* Smart, ZigBee, and 6LoWPAN wireless applications. Jarle brings 18 years of experience from software engineering, hardware engineering, applications, and marketing projects.

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.