



## TLV713 Capacitor-Free, 150-mA, Low-Dropout Regulator With Foldback Current Limit for Portable Devices

### 1 Features

- Stable Operation With or Without Capacitors
- Foldback Overcurrent Protection
- Packages:
  - 1-mm × 1-mm 4-Pin X2SON
  - 5-Pin SOT-23
- Very Low Dropout: 230 mV at 150 mA
- Accuracy: 1%
- Low  $I_Q$ : 50  $\mu$ A
- Input Voltage Range: 1.4 V to 5.5 V
- Available in Fixed-Output Voltages: 1 V to 3.3 V
- High PSRR: 65 dB at 1 kHz
- Active Output Discharge (P Version Only)

### 2 Applications

- PDAs and Battery-Powered Portable Devices
- MP3 Players and Other Hand-Held Products
- WLAN and Other PC Add-On Cards

### 3 Description

The TLV713 series of low-dropout (LDO) linear regulators are low quiescent current LDOs with excellent line and load transient performance and are designed for power-sensitive applications. These devices provide a typical accuracy of 1%.

The TLV713 series of devices is designed to be stable without an output capacitor. The removal of the output capacitor allows for a very small solution size. However, the TLV713 series is also stable with any output capacitor if an output capacitor is used.

The TLV713 also provides inrush current control during device power up and enabling. The TLV713 limits the input current to the defined current limit to avoid large currents from flowing from the input power source. This functionality is especially important in battery-operated devices.


The TLV713 series is available in standard DQN and DBV packages. The TLV713P provides an active pulldown circuit to quickly discharge output loads.

#### Device Information<sup>(1)</sup>


| DEVICE NAME | PACKAGE    | BODY SIZE         |
|-------------|------------|-------------------|
| TLV713      | X2SON (4)  | 1.00 mm × 1.00 mm |
|             | SOT-23 (5) | 2.90 mm × 1.60 mm |

(1) For all available packages, see the orderable addendum at the end of the data sheet.

#### Typical Application Circuit



#### Dropout Voltage vs Output Current



## Table of Contents

|                                                 |           |                                                                  |           |
|-------------------------------------------------|-----------|------------------------------------------------------------------|-----------|
| <b>1 Features</b> .....                         | <b>1</b>  | <b>8 Application and Implementation</b> .....                    | <b>16</b> |
| <b>2 Applications</b> .....                     | <b>1</b>  | 8.1 Application Information.....                                 | 16        |
| <b>3 Description</b> .....                      | <b>1</b>  | 8.2 Typical Application .....                                    | 17        |
| <b>4 Revision History</b> .....                 | <b>2</b>  | 8.3 What to Do and What Not to Do .....                          | 18        |
| <b>5 Pin Configurations and Functions</b> ..... | <b>5</b>  | <b>9 Power Supply Recommendations</b> .....                      | <b>18</b> |
| <b>6 Specifications</b> .....                   | <b>6</b>  | <b>10 Layout</b> .....                                           | <b>19</b> |
| 6.1 Absolute Maximum Ratings .....              | 6         | 10.1 Layout Guidelines .....                                     | 19        |
| 6.2 ESD Ratings.....                            | 6         | 10.2 Layout Examples.....                                        | 20        |
| 6.3 Recommended Operating Conditions.....       | 6         | <b>11 Device and Documentation Support</b> .....                 | <b>21</b> |
| 6.4 Thermal Information .....                   | 6         | 11.1 Device Support.....                                         | 21        |
| 6.5 Electrical Characteristics.....             | 7         | 11.2 Documentation Support .....                                 | 21        |
| 6.6 Typical Characteristics .....               | 8         | 11.3 Receiving Notification of Documentation Updates .....       | 21        |
| <b>7 Detailed Description</b> .....             | <b>12</b> | 11.4 Community Resources.....                                    | 21        |
| 7.1 Overview .....                              | 12        | 11.5 Trademarks .....                                            | 22        |
| 7.2 Functional Block Diagrams .....             | 12        | 11.6 Electrostatic Discharge Caution.....                        | 22        |
| 7.3 Feature Description.....                    | 13        | 11.7 Glossary .....                                              | 22        |
| 7.4 Device Functional Modes.....                | 15        | <b>12 Mechanical, Packaging, and Orderable Information</b> ..... | <b>22</b> |

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| <b>Changes from Revision E (March 2015) to Revision F</b>                 | <b>Page</b> |
|---------------------------------------------------------------------------|-------------|
| • Added last sentence to <i>Undervoltage Lockout (UVLO)</i> section ..... | 13          |
| • Added <i>UVLO Circuit Limitation</i> section .....                      | 16          |

| <b>Changes from Revision D (July 2013) to Revision E</b>                                                                                                                                                                                                                                                                                             | <b>Page</b> |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| • Changed format to meet latest data sheet standards; added new sections, and moved existing sections.....                                                                                                                                                                                                                                           | 1           |
| • Changed Features bullet about device package options .....                                                                                                                                                                                                                                                                                         | 1           |
| • Changed front-page figure .....                                                                                                                                                                                                                                                                                                                    | 1           |
| • Changed Pin Configuration and Functions section; updated table format.....                                                                                                                                                                                                                                                                         | 5           |
| • Changed Absolute Maximum Ratings table conditions .....                                                                                                                                                                                                                                                                                            | 6           |
| • Changed <i>Output voltage range</i> and <i>Junction temperature range</i> parameter maximum specifications in Absolute Maximum Ratings table .....                                                                                                                                                                                                 | 6           |
| • Added <i>ESD Ratings</i> table, <i>Feature Description</i> section, <i>Device Functional Modes</i> , <i>Application and Implementation</i> section, <i>Power Supply Recommendations</i> section, <i>Layout</i> section, <i>Device and Documentation Support</i> section, and <i>Mechanical, Packaging, and Orderable Information</i> section ..... | 6           |
| • Corrected DBV data in Thermal Information table .....                                                                                                                                                                                                                                                                                              | 6           |
| • Changed conditions of Electrical Characteristics table: changed $V_{IN}$ to $V_{IN(nom)}$ ; changed $T_A$ to $T_J$ ; corrected operating temperature range .....                                                                                                                                                                                   | 7           |
| • Changed $T_A$ to $T_J$ and 85°C to 125°C throughout Electrical Characteristics table .....                                                                                                                                                                                                                                                         | 7           |
| • Added test conditions for line regulation parameter .....                                                                                                                                                                                                                                                                                          | 7           |
| • Changed $V_{DO}$ parameter in Electrical Characteristics table: all rows changed .....                                                                                                                                                                                                                                                             | 7           |
| • Changed $V_n$ parameter typical specification in Electrical Characteristics table .....                                                                                                                                                                                                                                                            | 7           |
| • Deleted $T_J$ parameter from Electrical Characteristics table .....                                                                                                                                                                                                                                                                                | 7           |
| • Added $T_J$ condition to $I_{LIM}$ parameter in Electrical Characteristics table for clarification .....                                                                                                                                                                                                                                           | 7           |
| • Changed Typical Characteristics conditions.....                                                                                                                                                                                                                                                                                                    | 8           |
| • Changed <a href="#">Figure 1</a> through <a href="#">Figure 11</a> in Typical Characteristics to show improved performance definition .....                                                                                                                                                                                                        | 8           |

|                                                                                                                            |    |
|----------------------------------------------------------------------------------------------------------------------------|----|
| • Added new <a href="#">Figure 3</a> .....                                                                                 | 8  |
| • Changed <a href="#">Figure 4</a> .....                                                                                   | 8  |
| • Changed <a href="#">Figure 5</a> .....                                                                                   | 8  |
| • Changed <a href="#">Figure 9</a> graph and figure title .....                                                            | 8  |
| • Added new <a href="#">Figure 10</a> .....                                                                                | 8  |
| • Changed <a href="#">Figure 12</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 8  |
| • Changed <a href="#">Figure 13</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 9  |
| • Changed <a href="#">Figure 14</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 9  |
| • Changed <a href="#">Figure 15</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 9  |
| • Changed <a href="#">Figure 17</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 9  |
| • Changed <a href="#">Figure 19</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 10 |
| • Changed <a href="#">Figure 21</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 10 |
| • Changed <a href="#">Figure 22</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 10 |
| • Changed <a href="#">Figure 23</a> ; corrected notation on axis titles to show units per graph division (units/div) ..... | 10 |
| • Changed <a href="#">Shutdown</a> section: clarified description .....                                                    | 13 |
| • Changed <a href="#">Foldback Current Limit</a> section: adjusted flow and clarified description .....                    | 14 |
| • Changed paragraph 1 of <a href="#">Thermal Protection</a> .....                                                          | 14 |
| • Changed <a href="#">Table 2</a> .....                                                                                    | 17 |
| • Moved <a href="#">Ordering Information</a> to <a href="#">Device Nomenclature</a> section .....                          | 21 |

| <b>Changes from Revision C (July 2013) to Revision D</b>                                           | <b>Page</b> |
|----------------------------------------------------------------------------------------------------|-------------|
| • Changed document status from Mixed Status to Production Data .....                               | 1           |
| • Deleted DPW package from document .....                                                          | 1           |
| • Deleted reference to DPW package from last sentence of <a href="#">Description</a> section ..... | 1           |
| • Deleted DPW pin out drawing from front-page graphic .....                                        | 1           |
| • Deleted footnote for page 1 graphic .....                                                        | 1           |
| • Deleted DPW pinout drawing from Pin Configurations section .....                                 | 5           |
| • Deleted reference to DPW package from Pin Descriptions table .....                               | 5           |
| • Deleted DPW data from Thermal Information table .....                                            | 6           |
| • Deleted footnote 3 of Ordering Information table .....                                           | 21          |


| <b>Changes from Revision B (December 2012) to Revision C</b>                                    | <b>Page</b> |
|-------------------------------------------------------------------------------------------------|-------------|
| • Changed last Features bullet .....                                                            | 1           |
| • Added Typical Application Circuit .....                                                       | 1           |
| • Changed last two rows of the $V_{DO}$ parameter in the Electrical Characteristics table ..... | 7           |

| <b>Changes from Revision A (October 2012) to Revision B</b> | <b>Page</b> |
|-------------------------------------------------------------|-------------|
| • Changed footnote for page 1 graphic .....                 | 1           |
| • Added DBV data to Thermal Information table .....         | 6           |
| • Changed footnote 3 of Ordering Information table .....    | 21          |


| Changes from Original (September 2012) to Revision A                                         | Page |
|----------------------------------------------------------------------------------------------|------|
| • Reordered Features bullets .....                                                           | 1    |
| • Changed dropout range in fourth Features bullet.....                                       | 1    |
| • Changed <i>Package</i> and <i>Fixed-Output Voltage</i> Features bullets .....              | 1    |
| • Added second and third paragraphs to <i>Description</i> section.....                       | 1    |
| • Updated DQN pin out drawing.....                                                           | 1    |
| • Changed DQN pinout caption in Pin Configurations section.....                              | 5    |
| • Changed 1.2 V to 0.9 V in description of EN pin in Pin Descriptions table .....            | 5    |
| • Changed DQN header row in Thermal Information table .....                                  | 6    |
| • Changed $V_{OUT}$ maximum specification in Electrical Characteristics table .....          | 7    |
| • Combined all $V_{DO}$ rows together in Electrical Characteristics table .....              | 7    |
| • Changed $V_{DO}$ specifications in Electrical Characteristics table .....                  | 7    |
| • Changed $I_{SHDN}$ test conditions in Electrical Characteristics table .....               | 7    |
| • Changed Typical Characteristics conditions.....                                            | 8    |
| • Added curves.....                                                                          | 8    |
| • Changed junction temperature range in second paragraph of <i>Overview</i> section .....    | 12   |
| • Updated <a href="#">Figure 24</a> .....                                                    | 12   |
| • Deleted third paragraph from <i>Thermal Information</i> section.....                       | 14   |
| • Changed second paragraph of <i>Input and Output Capacitor Considerations</i> section ..... | 16   |
| • Deleted curve reference from <i>Dropout Voltage</i> section .....                          | 16   |

## 5 Pin Configurations and Functions

**DQN Package**  
**4-Pin X2SON**  
**Top View**



**DBV Package**  
**5-Pin SOT-23**  
**Top View**



### Pin Functions

| PIN         |       |        | I/O | DESCRIPTION                                                                                                                                                                                                                                                              |
|-------------|-------|--------|-----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| NAME        | NO.   |        |     |                                                                                                                                                                                                                                                                          |
|             | X2SON | SOT-23 |     |                                                                                                                                                                                                                                                                          |
| EN          | 3     | 3      | I   | Enable pin. Driving EN over 0.9 V turns on the regulator. Driving EN below 0.4 V puts the regulator into shutdown mode.                                                                                                                                                  |
| GND         | 2     | 2      | —   | Ground pin                                                                                                                                                                                                                                                               |
| IN          | 4     | 1      | I   | Input pin. A small capacitor is recommended from this pin to ground. See the <a href="#">Input and Output Capacitor Considerations</a> section in the <a href="#">Feature Description</a> for more details.                                                              |
| NC          | —     | 4      | —   | No internal connection                                                                                                                                                                                                                                                   |
| OUT         | 1     | 5      | O   | Regulated output voltage pin. For best transient response, a small 1-μF ceramic capacitor is recommended from this pin to ground. See the <a href="#">Input and Output Capacitor Considerations</a> section in the <a href="#">Feature Description</a> for more details. |
| Thermal pad |       | —      | —   | The thermal pad is electrically connected to the GND node. Connect to the GND plane for improved thermal performance.                                                                                                                                                    |

## 6 Specifications

### 6.1 Absolute Maximum Ratings

Over operating junction temperature range ( $T_J = 25^{\circ}\text{C}$ ), unless otherwise noted. All voltages are with respect to GND.<sup>(1)</sup>

|                               |                                | MIN                                     | MAX            | UNIT               |
|-------------------------------|--------------------------------|-----------------------------------------|----------------|--------------------|
| Voltage                       | Input, $V_{IN}$                | −0.3                                    | 6              | V                  |
|                               | Enable, $V_{EN}$               | −0.3                                    | $V_{IN} + 0.3$ |                    |
|                               | Output, $V_{OUT}$              | −0.3                                    | 3.6            |                    |
| Current                       | Maximum output, $I_{OUT(max)}$ | Internally limited                      |                |                    |
| Output short-circuit duration |                                | Indefinite                              |                |                    |
| Total power dissipation       | Continuous, $P_{D(tot)}$       | See <a href="#">Thermal Information</a> |                |                    |
| Temperature                   | Storage, $T_{stg}$             | −55                                     | 150            | $^{\circ}\text{C}$ |
|                               | Junction, $T_J$                | −55                                     | 125            | $^{\circ}\text{C}$ |

- (1) Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions*. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### 6.2 ESD Ratings

|             |                         |                                                                                          | VALUE | UNIT |
|-------------|-------------------------|------------------------------------------------------------------------------------------|-------|------|
| $V_{(ESD)}$ | Electrostatic discharge | Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>              | ±2000 | V    |
|             |                         | Charged device model (CDM), per JEDEC specification JESD22-C101, all pins <sup>(2)</sup> | ±500  |      |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

### 6.3 Recommended Operating Conditions

over operating junction temperature range (unless otherwise noted).

|           |                                      | MIN | NOM | MAX      | UNIT               |
|-----------|--------------------------------------|-----|-----|----------|--------------------|
| $V_{IN}$  | Input voltage                        | 1.4 |     | 5.5      | V                  |
| $V_{EN}$  | Enable range                         | 0   |     | $V_{IN}$ | V                  |
| $I_{OUT}$ | Output current                       | 0   |     | 150      | mA                 |
| $C_{IN}$  | Input capacitor                      | 0   | 1   |          | $\mu\text{F}$      |
| $C_{OUT}$ | Output capacitor                     | 0   | 0.1 | 100      | $\mu\text{F}$      |
| $T_J$     | Operating junction temperature range | −40 |     | 125      | $^{\circ}\text{C}$ |

### 6.4 Thermal Information

| THERMAL METRIC <sup>(1)</sup> |                                              | TLV713, TLV713P |             | UNIT                        |
|-------------------------------|----------------------------------------------|-----------------|-------------|-----------------------------|
|                               |                                              | DQN (X2SON)     | DBV (SOT23) |                             |
|                               |                                              | 4 PINS          | 5 PINS      |                             |
| $R_{\theta JA}$               | Junction-to-ambient thermal resistance       | 255.8           | 249         | $^{\circ}\text{C}/\text{W}$ |
| $R_{\theta JC(top)}$          | Junction-to-case (top) thermal resistance    | 159.3           | 172.7       | $^{\circ}\text{C}/\text{W}$ |
| $R_{\theta JB}$               | Junction-to-board thermal resistance         | 208.2           | 76.7        | $^{\circ}\text{C}/\text{W}$ |
| $\psi_{JT}$                   | Junction-to-top characterization parameter   | 16.2            | 49.7        | $^{\circ}\text{C}/\text{W}$ |
| $\psi_{JB}$                   | Junction-to-board characterization parameter | 208.1           | 75.8        | $^{\circ}\text{C}/\text{W}$ |
| $R_{\theta JC(bot)}$          | Junction-to-case (bottom) thermal resistance | 148.6           | n/a         | $^{\circ}\text{C}/\text{W}$ |

- (1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC Package Thermal Metrics application report](#).

## 6.5 Electrical Characteristics


Over operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ),  $V_{IN(nom)} = V_{OUT(nom)} + 0.5\text{ V}$  or  $V_{IN(nom)} = 2\text{ V}$  (whichever is greater),  $I_{OUT} = 1\text{ mA}$ ,  $V_{EN} = V_{IN}$ , and  $C_{OUT} = 0.47\text{ }\mu\text{F}$ , unless otherwise noted. Typical values are at  $T_J = 25^{\circ}\text{C}$ .

| PARAMETER                        |                                  | TEST CONDITIONS                                                                                        |                                                                        | MIN   | TYP  | MAX      | UNIT                |
|----------------------------------|----------------------------------|--------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------|-------|------|----------|---------------------|
| $V_{IN}$                         | Input voltage range              |                                                                                                        |                                                                        | 1.4   |      | 5.5      | V                   |
| $V_{OUT}$                        | Output voltage range             |                                                                                                        |                                                                        | 1     |      | 3.3      | V                   |
|                                  | DC output accuracy               | $V_{OUT} \geq 1.8\text{ V}$ , $T_J = 25^{\circ}\text{C}$                                               |                                                                        | -1%   |      | 1%       |                     |
|                                  |                                  | $V_{OUT} < 1.8\text{ V}$ , $T_J = 25^{\circ}\text{C}$                                                  |                                                                        | -20   |      | 20       | mV                  |
|                                  |                                  | $V_{OUT} \geq 1.2\text{ V}$ , $-40^{\circ}\text{C} \leq T_J \leq 125^{\circ}\text{C}$                  |                                                                        | -1.5% |      | 1.5%     |                     |
|                                  |                                  | $V_{OUT} < 1.2\text{ V}$ , $-40^{\circ}\text{C} \leq T_J \leq 125^{\circ}\text{C}$                     |                                                                        | -50   |      | 50       | mV                  |
| $\Delta V_{OUT(\Delta V_{IN})}$  | Line regulation                  | Max $\{V_{OUT(nom)} + 0.5\text{ V}, V_{IN} = 2.0\text{ V}\} \leq V_{IN} \leq 5.5\text{ V}$             |                                                                        |       | 1    | 5        | mV                  |
| $\Delta V_{OUT(\Delta I_{OUT})}$ | Load regulation                  | $0\text{ mA} \leq I_{OUT} \leq 150\text{ mA}$                                                          |                                                                        |       | 10   | 30       | mV                  |
| $V_{DO}$                         | Dropout voltage                  | $V_{OUT} = 0.98 \times V_{OUT(nom)}$ ,<br>$T_J = -40^{\circ}\text{C}$ to $85^{\circ}\text{C}$          | $1\text{ V} \leq V_{OUT} < 1.8\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 600  | 900      | mV                  |
|                                  |                                  |                                                                                                        | $V_{OUT} = 1.1\text{ V}$ , $I_{OUT} = 100\text{ mA}$                   |       | 470  | 600      |                     |
|                                  |                                  |                                                                                                        | $1.8\text{ V} \leq V_{OUT} < 2.1\text{ V}$ , $I_{OUT} = 30\text{ mA}$  |       | 70   |          |                     |
|                                  |                                  |                                                                                                        | $1.8\text{ V} \leq V_{OUT} < 2.1\text{ V}$ , $I_{OUT} = 150\text{ mA}$ |       | 350  | 575      |                     |
|                                  |                                  |                                                                                                        | $2.1\text{ V} \leq V_{OUT} < 2.5\text{ V}$ , $I_{OUT} = 30\text{ mA}$  |       | 90   |          |                     |
|                                  |                                  |                                                                                                        | $2.1\text{ V} \leq V_{OUT} < 2.5\text{ V}$ , $I_{OUT} = 150\text{ mA}$ |       | 290  | 481      |                     |
|                                  |                                  |                                                                                                        | $2.5\text{ V} \leq V_{OUT} < 3\text{ V}$ , $I_{OUT} = 30\text{ mA}$    |       | 50   |          |                     |
|                                  |                                  |                                                                                                        | $2.5\text{ V} \leq V_{OUT} < 3\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 246  | 445      |                     |
|                                  |                                  | $V_{OUT} = 0.98 \times V_{OUT(nom)}$ ,<br>$T_J = -40^{\circ}\text{C}$ to $125^{\circ}\text{C}$         | $3\text{ V} \leq V_{OUT} < 3.6\text{ V}$ , $I_{OUT} = 30\text{ mA}$    |       | 46   |          |                     |
|                                  |                                  |                                                                                                        | $3\text{ V} \leq V_{OUT} < 3.6\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 230  | 420      |                     |
|                                  |                                  |                                                                                                        | $1\text{ V} \leq V_{OUT} < 1.8\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 600  | 1020     |                     |
|                                  |                                  |                                                                                                        | $V_{OUT} = 1.1\text{ V}$ , $I_{OUT} = 100\text{ mA}$                   |       | 470  | 720      |                     |
|                                  |                                  |                                                                                                        | $1.8\text{ V} \leq V_{OUT} < 2.1\text{ V}$ , $I_{OUT} = 150\text{ mA}$ |       | 350  | 695      |                     |
|                                  |                                  |                                                                                                        | $2.1\text{ V} \leq V_{OUT} < 2.5\text{ V}$ , $I_{OUT} = 150\text{ mA}$ |       | 290  | 601      |                     |
|                                  |                                  |                                                                                                        | $2.5\text{ V} \leq V_{OUT} < 3\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 246  | 565      |                     |
|                                  |                                  |                                                                                                        | $3\text{ V} \leq V_{OUT} < 3.6\text{ V}$ , $I_{OUT} = 150\text{ mA}$   |       | 230  | 540      |                     |
| $I_{GND}$                        | Ground pin current               | $I_{OUT} = 0\text{ mA}$                                                                                |                                                                        |       | 50   | 75       | $\mu\text{A}$       |
| $I_{SHUTDOWN}$                   | Shutdown current                 | $V_{EN} \leq 0.4\text{ V}$ , $2.0\text{ V} \leq V_{IN} \leq 5.5\text{ V}$ , $T_J = 25^{\circ}\text{C}$ |                                                                        |       | 0.1  | 1        | $\mu\text{A}$       |
| PSRR                             | Power-supply rejection ratio     | $V_{IN} = 3.3\text{ V}$ ,<br>$V_{OUT} = 2.8\text{ V}$ ,<br>$I_{OUT} = 30\text{ mA}$                    | $f = 100\text{ Hz}$                                                    |       | 70   |          | dB                  |
|                                  |                                  |                                                                                                        | $f = 10\text{ kHz}$                                                    |       | 55   |          |                     |
|                                  |                                  |                                                                                                        | $f = 1\text{ MHz}$                                                     |       | 55   |          |                     |
| $V_n$                            | Output noise voltage             | BW = 100 Hz to 100 kHz, $V_{IN} = 2.3\text{ V}$ , $V_{OUT} = 1.8\text{ V}$ , $I_{OUT} = 10\text{ mA}$  |                                                                        |       | 73   |          | $\mu\text{V}_{RMS}$ |
| $t_{STR}$                        | Start-up time <sup>(1)</sup>     | $C_{OUT} = 1.0\text{ }\mu\text{F}$ , $I_{OUT} = 150\text{ mA}$                                         |                                                                        |       | 100  |          | $\mu\text{s}$       |
| $V_{HI}$                         | Enable high (enabled)            |                                                                                                        |                                                                        | 0.9   |      | $V_{IN}$ | V                   |
| $V_{LO}$                         | Enable low (disabled)            |                                                                                                        |                                                                        | 0     |      | 0.4      | V                   |
| $I_{EN}$                         | EN pin current                   | EN = 5.5 V                                                                                             |                                                                        |       | 0.01 |          | $\mu\text{A}$       |
| $R_{PULLDOWN}$                   | Pulldown resistor (TLV713P only) | $V_{IN} = 4\text{ V}$                                                                                  |                                                                        |       | 120  |          | $\Omega$            |
| $I_{LIM}$                        | Output current limit             | $V_{IN} = 3.8\text{ V}$ , $V_{OUT} = 3.3\text{ V}$ , $T_J = -40$ to $85^{\circ}\text{C}$               |                                                                        | 180   |      |          | mA                  |
|                                  |                                  | $V_{IN} = 2.25\text{ V}$ , $V_{OUT} = 1.8\text{ V}$ , $T_J = -40$ to $85^{\circ}\text{C}$              |                                                                        | 180   |      |          |                     |
|                                  |                                  | $V_{IN} = 2.0\text{ V}$ , $V_{OUT} = 1.2\text{ V}$ , $T_J = -40$ to $85^{\circ}\text{C}$               |                                                                        | 180   |      |          |                     |
| $I_{SC}$                         | Short-circuit current            | $V_{OUT} = 0\text{ V}$                                                                                 |                                                                        |       | 40   |          | mA                  |
| $T_{SD}$                         | Thermal shutdown                 | Shutdown, temperature increasing                                                                       |                                                                        |       | 158  |          | $^{\circ}\text{C}$  |
|                                  |                                  | Reset, temperature decreasing                                                                          |                                                                        |       | 140  |          |                     |


(1) Start-up time is the time from EN assertion to  $(0.98 \times V_{OUT(nom)})$ .

## 6.6 Typical Characteristics


Over operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(nom)} + 0.5\text{ V}$  or  $2.0\text{ V}$  (whichever is greater),  $I_{OUT} = 10\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $V_{OUT(nom)} = 1.8\text{ V}$ , unless otherwise noted. Typical values are at  $T_J = 25^{\circ}\text{C}$ .




**Figure 1. 1.8-V Line Regulation vs  $V_{IN}$  and Temperature**




**Figure 2. 1.8-V Load Regulation vs  $I_{OUT}$  and Temperature**




**Figure 3. 1.8-V Output Voltage Over Temperature**



**Figure 4. 1.8-V Dropout Voltage vs  $I_{OUT}$  and Temperature**



**Figure 5. 3.3-V Dropout Voltage vs  $I_{OUT}$  and Temperature**



**Figure 6. Ground Pin Current vs  $V_{IN}$  and Temperature**



## Typical Characteristics (continued)

Over operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(nom)} + 0.5\text{ V}$  or  $2.0\text{ V}$  (whichever is greater),  $I_{OUT} = 10\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $V_{OUT(nom)} = 1.8\text{ V}$ , unless otherwise noted. Typical values are at  $T_J = 25^{\circ}\text{C}$ .




Figure 7. Ground Pin Current vs  $I_{OUT}$  and Temperature




Figure 8. Shutdown Current vs  $V_{IN}$  and Temperature




Figure 9. Power-Supply Rejection Ratio Over  $C_{OUT}$




Figure 10. Power-Supply Rejection Ratio Over  $I_{OUT}$




Figure 11. Output Spectral Noise Density










Figure 12. Line Transient

## Typical Characteristics (continued)

Over operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(nom)} + 0.5\text{ V}$  or  $2.0\text{ V}$  (whichever is greater),  $I_{OUT} = 10\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $V_{OUT(nom)} = 1.8\text{ V}$ , unless otherwise noted. Typical values are at  $T_J = 25^{\circ}\text{C}$ .


**Figure 13. Line Transient**

**Figure 14. 0-mA to 20-mA Load Transient**

**Figure 15. 0-mA to 20-mA Load Transient**

**Figure 16. 3.3-V Output Voltage vs Output Current (Foldback Current Limit)**

**Figure 17. 0-mA to 100-mA Load Transient**

**Figure 18. 1.8-V Output Voltage vs Output Current (Foldback Current Limit)**

## Typical Characteristics (continued)

Over operating temperature range ( $T_J = -40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ ),  $V_{IN} = V_{OUT(nom)} + 0.5\text{ V}$  or  $2.0\text{ V}$  (whichever is greater),  $I_{OUT} = 10\text{ mA}$ ,  $V_{EN} = V_{IN}$ ,  $C_{OUT} = 1\text{ }\mu\text{F}$ , and  $V_{OUT(nom)} = 1.8\text{ V}$ , unless otherwise noted. Typical values are at  $T_J = 25^{\circ}\text{C}$ .




Figure 19. 10-mA to 150-mA Load Transient

Figure 20.  $V_{IN}$  Power-Up and Power-Down




Figure 21. Start-up With EN

Figure 22. Start-up With EN




Figure 23. Shutdown Response With Enable


## 7 Detailed Description

### 7.1 Overview

These devices belong to a new family of next-generation value low-dropout (LDO) regulators. These devices consume low quiescent current and deliver excellent line and load transient performance. These characteristics, combined with low noise, very good PSRR with little ( $V_{IN} - V_{OUT}$ ) headroom, make this family of devices ideal for RF portable applications.

This family of regulators offers current limit and thermal protection. Device operating junction temperature is  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

### 7.2 Functional Block Diagrams



**Figure 24. TLV713 Block Diagram**

## Functional Block Diagrams (continued)




Figure 25. TLV713P Block Diagram

## 7.3 Feature Description

### 7.3.1 Undervoltage Lockout (UVLO)

The TLV713 uses a UVLO circuit that disables the output until the input voltage is greater than the rising UVLO voltage. This circuit ensures that the device does not exhibit any unpredictable behavior when the supply voltage is lower than the operational range of the internal circuitry,  $V_{IN(min)}$ . During UVLO disable, the output of the TLV713P version is connected to ground with a 120-Ω pulldown resistor. Fast rising and falling voltage changes near UVLO levels require at least a 1-ms delay before the rising and falling edges; see the [UVLO Circuit Limitation](#) section.

### 7.3.2 Shutdown

The enable pin (EN) is active high. Enable the device by forcing the EN pin to exceed  $V_{EN(high)}$  (0.9 V, minimum). Turn off the device by forcing the EN pin to drop below 0.4 V. If shutdown capability is not required, connect EN to IN.

The TLV713P has an internal pulldown MOSFET that connects a 120-Ω resistor to ground when the device is disabled. The discharge time after disabling depends on the output capacitance ( $C_{OUT}$ ) and the load resistance ( $R_L$ ) in parallel with the 120-Ω pulldown resistor. The time constant is calculated in [Equation 1](#).

$$\tau = \frac{120 \cdot R_L}{120 + R_L} \cdot C_{OUT} \quad (1)$$

## Feature Description (continued)

### 7.3.3 Foldback Current Limit

The TLV713 has an internal foldback current limit that helps protect the regulator during fault conditions. The current supplied by the device is gradually reduced while the output voltage decreases. When the output is shorted, the LDO supplies a typical current of 40 mA. Output voltage is not regulated when the device is in current limit, and is calculated by [Equation 2](#):

$$V_{OUT} = I_{LIMIT} \times R_{LOAD} \quad (2)$$

The PMOS pass transistor dissipates  $[(V_{IN} - V_{OUT}) \times I_{LIMIT}]$  until thermal shutdown is triggered and the device turns off. The device is turned on by the internal thermal shutdown circuit during cool down. If the fault condition continues, the device cycles between current limit and thermal shutdown. See the [Thermal Information](#) section for more details.

The TLV713 PMOS pass element has a built-in body diode that conducts current when the voltage at OUT exceeds the voltage at IN. This current is not limited, so if extended reverse voltage operation is anticipated, external limiting to 5% of the rated output current is recommended.

### 7.3.4 Thermal Protection

Thermal protection disables the output when the junction temperature rises to approximately 158°C, allowing the device to cool. When the junction temperature cools to approximately 140°C, the output circuitry is again enabled. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit may cycle on and off. This cycling limits regulator dissipation, protecting the device from damage as a result of overheating.

Any tendency to activate the thermal protection circuit indicates excessive power dissipation or an inadequate heatsink. For reliable operation, junction temperature must be limited to 125°C maximum. To estimate the margin of safety in a complete design (including heatsink), increase the ambient temperature until the thermal protection is triggered; use worst-case loads and signal conditions.

The TLV713 internal protection circuitry is designed to protect against overload conditions. This circuitry is not intended to replace proper heatsinking. Continuously running the TLV713 into thermal shutdown degrades device reliability.

## 7.4 Device Functional Modes

### 7.4.1 Normal Operation

The device regulates to the nominal output voltage under the following conditions:

- The input voltage is at least as high as  $V_{IN(min)}$ .
- The input voltage is greater than the nominal output voltage added to the dropout voltage.
- The enable voltage has previously exceeded the enable rising threshold voltage and has not decreased below the enable falling threshold.
- The output current is less than the current limit.
- The device junction temperature is less than the maximum specified junction temperature.

### 7.4.2 Dropout Operation

If the input voltage is lower than the nominal output voltage plus the specified dropout voltage, but all other conditions are met for normal operation, the device operates in dropout mode. In this mode of operation, the output voltage is the same as the input voltage minus the dropout voltage. The transient performance of the device is significantly degraded because the pass device is in the linear region and no longer controls the current through the LDO. Line or load transients in dropout can result in large output voltage deviations.

### 7.4.3 Disabled

The device is disabled under the following conditions:

- The enable voltage is less than the enable falling threshold voltage or has not yet exceeded the enable rising threshold.
- The device junction temperature is greater than the thermal shutdown temperature.

Table 1 shows the conditions that lead to the different modes of operation.

**Table 1. Device Functional Mode Comparison**

| OPERATING MODE                                            | PARAMETER                                                      |                         |                     |                      |
|-----------------------------------------------------------|----------------------------------------------------------------|-------------------------|---------------------|----------------------|
|                                                           | $V_{IN}$                                                       | $V_{EN}$                | $I_{OUT}$           | $T_J$                |
| Normal mode                                               | $V_{IN} > V_{OUT(nom)} + V_{DO}$ and<br>$V_{IN} > V_{IN(min)}$ | $V_{EN} > V_{EN(high)}$ | $I_{OUT} < I_{LIM}$ | $T_J < 125^{\circ}C$ |
| Dropout mode                                              | $V_{IN(min)} < V_{IN} < V_{OUT(nom)} + V_{DO}$                 | $V_{EN} > V_{EN(high)}$ | —                   | $T_J < 125^{\circ}C$ |
| Disabled mode<br>(any true condition disables the device) | —                                                              | $V_{EN} < V_{EN(low)}$  | —                   | $T_J > 158^{\circ}C$ |

## 8 Application and Implementation

### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### 8.1 Application Information

#### 8.1.1 Input and Output Capacitor Considerations

The TLV713 uses an advanced internal control loop to obtain stable operation both with and without the use of input or output capacitors. The TLV713 dynamic performance is improved with the use of an output capacitor. An output capacitance of 0.1  $\mu\text{F}$  or larger generally provides good dynamic response. X5R- and X7R-type ceramic capacitors are recommended because these capacitors have minimal variation in value and equivalent series resistance (ESR) over temperature.

Although an input capacitor is not required for stability, it is good analog design practice to connect a 0.1- $\mu\text{F}$  to 1- $\mu\text{F}$  capacitor from IN to GND. This capacitor counteracts reactive input sources and improves transient response, input ripple, and PSRR. An input capacitor is recommended if the source impedance is more than 0.5  $\Omega$ . A higher-value capacitor may be necessary if large, fast, rise-time load transients are anticipated or if the device is located several inches from the input power source.

#### 8.1.2 Dropout Voltage

The TLV713 uses a PMOS pass transistor to achieve low dropout. When  $(V_{\text{IN}} - V_{\text{OUT}})$  is less than the dropout voltage ( $V_{\text{DO}}$ ), the PMOS pass device is in the linear region of operation and the input-to-output resistance is the  $R_{\text{DS(on)}}$  of the PMOS pass element.  $V_{\text{DO}}$  scales approximately with output current because the PMOS device behaves like a resistor in dropout. As with any linear regulator, PSRR and transient response are degraded as  $(V_{\text{IN}} - V_{\text{OUT}})$  approaches dropout.

#### 8.1.3 Transient Response

As with any regulator, increasing the size of the output capacitor reduces over- and undershoot magnitude but increases the duration of the transient response.

#### 8.1.4 UVLO Circuit Limitation


The TLV713 UVLO circuit is sensitive to fast rising and falling input voltage changes that result in the device turning on and off. When the input voltage drops below the minimum  $V_{\text{IN}}$  and the device is turned off, provide a minimum 1-ms delay before turning on the device again. This minimum 1-ms delay allows the internal circuit to reset to the correct state. If the TLV713 is turned on again before the delay elapses, an EN toggle is required for the internal circuit to reset to the correct state.



## 8.2 Typical Application

Several versions of the TPS713 are ideal for powering the [MSP430 microcontroller](#).

[Figure 26](#) shows a diagram of the TLV713 powering an MSP430 microcontroller. [Table 2](#) shows potential applications of some voltage versions.



**Figure 26. TLV713 Powering a Microcontroller**

**Table 2. Typical MSP430 Applications**

| DEVICE    | V <sub>OUT</sub> (Typ) | APPLICATION                                                             |
|-----------|------------------------|-------------------------------------------------------------------------|
| TLV71318P | 1.8 V                  | Allows for lowest power consumption with many MSP430s                   |
| TLV71325P | 2.5 V                  | 2.2-V supply required by many MSP430s for flash programming and erasing |

### 8.2.1 Design Requirements

[Table 3](#) lists the design requirements.

**Table 3. Design Parameters**

| PARAMETER                   | DESIGN REQUIREMENT                 |
|-----------------------------|------------------------------------|
| Input voltage               | 4.2 V to 3 V (Lithium Ion battery) |
| Output voltage              | 1.8 V, ±1%                         |
| DC output current           | 10 mA                              |
| Peak output current         | 75 mA                              |
| Maximum ambient temperature | 65°C                               |


### 8.2.2 Detailed Design Procedure

An input capacitor is not required for this design because of the low impedance connection directly to the battery.


No output capacitor allows for the minimal possible inrush current during start-up, ensuring the 180-mA maximum input current limit is not exceeded.

Verify that the maximum junction temperature is not exceeded by referring to [Figure 30](#).


### 8.2.3 Application Curves



**Figure 27. Power-Supply Rejection Ratio vs Frequency**



**Figure 28. Output Spectral Noise Density**



**Figure 29. VIN Power Up and Power Down**

### 8.3 What to Do and What Not to Do

Place at least one 0.1-μF ceramic capacitor as close as possible to the OUT pin of the regulator for best transient performance.

Place at least one 1-μF capacitor as close as possible to the IN pin for best transient performance.

Do not place the output capacitor more than 10 mm away from the regulator.

Do not exceed the absolute maximum ratings.

Do not continuously operate the device in current limit or near thermal shutdown.

## 9 Power Supply Recommendations

These devices are designed to operate from an input voltage supply range from 1.4 V to 5.5 V. The input voltage range must provide adequate headroom for the device to have a regulated output. This input supply must be well-regulated and stable. If the input supply is noisy, additional input capacitors with low ESR can help improve the output noise performance.

## 10 Layout

### 10.1 Layout Guidelines

#### 10.1.1 Board Layout Recommendations to Improve PSRR and Noise Performance

Input and output capacitors must be placed as close to the device pins as possible. To improve AC performance (such as PSRR, output noise, and transient response), TI recommends that the board be designed with separate ground planes for  $V_{IN}$  and  $V_{OUT}$ , with the ground plane connected only at the device GND pin. In addition, the output capacitor ground connection must be connected directly to the device GND pin. High-ESR capacitors may degrade PSRR performance.


#### 10.1.2 Power Dissipation

The ability to remove heat from the die is different for each package type, presenting different considerations in the printed-circuit-board (PCB) layout. The PCB area around the device that is free of other components moves the heat from the device to the ambient air. Performance data for JEDEC low- and high-K boards are given in [Thermal Information](#). Using heavier copper increases the effectiveness in removing heat from the device. The addition of plated through-holes to heat-dissipating layers also improves the heatsink effectiveness.

Power dissipation depends on input voltage and load conditions. Power dissipation ( $P_D$ ) can be approximated by the product of the output current times the voltage drop across the output pass element ( $V_{IN}$  to  $V_{OUT}$ ), as shown in [Equation 3](#).

$$P_D = (V_{IN} - V_{OUT}) \times I_{OUT} \quad (3)$$

[Figure 30](#) shows the maximum ambient temperature versus the power dissipation of the TLV713. This figure assumes the device is soldered on a JEDEC standard, high-K layout with no airflow over the board. Actual board thermal impedances vary widely. If the application requires high power dissipation, having a thorough understanding of the board temperature and thermal impedances is helpful to ensure the TLV713 does not operate above a junction temperature of 125°C.



**Figure 30. Maximum Ambient Temperature vs Device Power Dissipation**

Estimating the junction temperature can be done by using the thermal metrics  $\Psi_{JT}$  and  $\Psi_{JB}$ , shown in the [Thermal Information](#) table. These metrics are a more accurate representation of the heat transfer characteristics of the die and the package than  $R_{\theta JA}$ . The junction temperature can be estimated with [Equation 4](#).

## Layout Guidelines (continued)

$$\Psi_{JT}: T_J = T_T + \Psi_{JT} \cdot P_D$$

$$\Psi_{JB}: T_J = T_B + \Psi_{JB} \cdot P_D$$

where

- $P_D$  is the power dissipation shown by [Equation 3](#),
- $T_T$  is the temperature at the center-top of the IC package,
- $T_B$  is the PCB temperature measured 1 mm away from the IC package *on the PCB surface*.


(4)

### NOTE

Both  $T_T$  and  $T_B$  can be measured on actual application boards using a thermo-gun (an infrared thermometer).


For more information about measuring  $T_T$  and  $T_B$ , see the [Using New Thermal Metrics application note](#), available for download at [www.ti.com](http://www.ti.com).

## 10.2 Layout Examples



(1) Not required.

**Figure 31. X2SON Layout Example**



(1) Not required.

**Figure 32. SOT-23 Layout Example**

## 11 Device and Documentation Support

### 11.1 Device Support

#### 11.1.1 Development Support

##### 11.1.1.1 Evaluation Modules

Three evaluation modules (EVMs) are available to assist in the initial circuit performance evaluation using the TLV713:

- [TLV71312PEVM-171](#)
- [TLV71318PEVM-171](#)
- [TLV71333PEVM-171](#)

These EVMs can be requested at the Texas Instruments website through the device product folders or purchased directly from [the TI eStore](#).

##### 11.1.1.2 Spice Models

Computer simulation of circuit performance using SPICE is often useful when analyzing the performance of analog circuits and systems. A SPICE model for the TLV713 is available through the product folders under *Tools & Software*.

#### 11.1.2 Device Nomenclature

**Table 4. Ordering Information<sup>(1)(2)</sup>**

| PRODUCT          | V <sub>O</sub>                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TLV713xx(x)PyyyZ | <p><b>XX(X)</b> is the nominal output voltage. For output voltages with a resolution of 100 mV, two digits are used in the ordering number; otherwise, three digits are used (for example, 28 = 2.8 V; 475 = 4.75 V).</p> <p><b>P</b> is optional; devices with P have an LDO regulator with an active output discharge.</p> <p><b>YYY</b> is the package designator.</p> <p><b>Z</b> is the package quantity. R is for reel (3000 pieces), T is for tape (250 pieces).</p> |

(1) For the most current package and ordering information see the Package Option Addendum at the end of this document, or visit the device product folder on [www.ti.com](#).

(2) Output voltages from 1.0 V to 3.3 V in 50-mV increments are available. Contact the factory for details and availability.

## 11.2 Documentation Support

### 11.2.1 Related Documentation

For related documentation see the following:

- Texas Instruments, [Using New Thermal Metrics application report](#)
- Texas Instruments, [TLV713xxEVM-171 User's Guide user's guide](#)

### 11.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. In the upper right corner, click on *Alert me* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

### 11.4 Community Resources

The following links connect to TI community resources. Linked contents are provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

**TI E2E™ Online Community** *TI's Engineer-to-Engineer (E2E) Community*. Created to foster collaboration among engineers. At e2e.ti.com, you can ask questions, share knowledge, explore ideas and help solve problems with fellow engineers.

**Design Support** *TI's Design Support* Quickly find helpful E2E forums along with design support tools and contact information for technical support.

## 11.5 Trademarks

E2E is a trademark of Texas Instruments.  
All other trademarks are the property of their respective owners.

## 11.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## 11.7 Glossary

[SLYZ022](#) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

## PACKAGING INFORMATION

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TLV71310PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUQI                |
| TLV71310PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUQI                |
| <a href="#">TLV71310PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUQI                |
| TLV71310PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUQI                |
| <a href="#">TLV71310PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | ET                  |
| TLV71310PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | ET                  |
| <a href="#">TLV71310PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | ET                  |
| TLV71310PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | ET                  |
| <a href="#">TLV71311PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUPI                |
| TLV71311PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUPI                |
| <a href="#">TLV71311PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUPI                |
| TLV71311PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUPI                |
| <a href="#">TLV71312PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| TLV71312PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| <a href="#">TLV71312PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| TLV71312PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| TLV71312PDBVTG4               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| TLV71312PDBVTG4.A             | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUEI                |
| <a href="#">TLV71312PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AF                  |
| TLV71312PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AF                  |
| <a href="#">TLV71312PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AF                  |
| TLV71312PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AF                  |
| <a href="#">TLV71315PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUGI                |
| TLV71315PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUGI                |
| <a href="#">TLV71315PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUGI                |
| TLV71315PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUGI                |
| <a href="#">TLV71315PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AY                  |
| TLV71315PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AY                  |
| <a href="#">TLV71315PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AY                  |

| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TLV71315PDQNT.A                | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AY                  |
| <a href="#">TLV713185PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUII                |
| TLV713185PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | VUII                |
| <a href="#">TLV713185PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUII                |
| TLV713185PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUII                |
| <a href="#">TLV713185PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A1                  |
| TLV713185PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A1                  |
| <a href="#">TLV713185PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A1                  |
| TLV713185PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A1                  |
| <a href="#">TLV71318PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| TLV71318PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| TLV71318PDBVRG4                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| TLV71318PDBVRG4.A              | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| <a href="#">TLV71318PDBVT</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| TLV71318PDBVT.A                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUDI                |
| <a href="#">TLV71318PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AW                  |
| TLV71318PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AW                  |
| <a href="#">TLV71318PDQNT</a>  | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AW                  |
| TLV71318PDQNT.A                | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AW                  |
| <a href="#">TLV71320DQNR</a>   | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | B2                  |
| TLV71320DQNR.A                 | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | B2                  |
| <a href="#">TLV71320DQNT</a>   | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | B2                  |
| TLV71320DQNT.A                 | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 85    | B2                  |
| <a href="#">TLV71325PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| TLV71325PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| TLV71325PDBVRG4                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| TLV71325PDBVRG4.A              | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| <a href="#">TLV71325PDBVT</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| TLV71325PDBVT.A                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUJI                |
| <a href="#">TLV71325PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AZ                  |
| TLV71325PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AZ                  |



| Orderable part number          | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|--------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TLV71325PDQNT</a>  | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AZ                  |
| TLV71325PDQNT.A                | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AZ                  |
| <a href="#">TLV713285PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| TLV713285PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| TLV713285PDBVRG4               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| TLV713285PDBVRG4.A             | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| <a href="#">TLV713285PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| TLV713285PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VULI                |
| <a href="#">TLV713285PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| TLV713285PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| TLV713285PDQNRG4               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| TLV713285PDQNRG4.A             | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| <a href="#">TLV713285PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| TLV713285PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | A2                  |
| <a href="#">TLV71328PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUKI                |
| TLV71328PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUKI                |
| <a href="#">TLV71328PDBVT</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUKI                |
| TLV71328PDBVT.A                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUKI                |
| <a href="#">TLV71328PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| TLV71328PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| TLV71328PDQNRG4                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| TLV71328PDQNRG4.A              | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| <a href="#">TLV71328PDQNT</a>  | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| TLV71328PDQNT.A                | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AK                  |
| <a href="#">TLV71330PDBVR</a>  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUMI                |
| TLV71330PDBVR.A                | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | VUMI                |
| <a href="#">TLV71330PDBVT</a>  | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUMI                |
| TLV71330PDBVT.A                | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUMI                |
| <a href="#">TLV71330PDQNR</a>  | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AL                  |
| TLV71330PDQNR.A                | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AL                  |
| <a href="#">TLV71330PDQNT</a>  | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AL                  |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|-------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| TLV71330PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AL                  |
| <a href="#">TLV71333PDBVR</a> | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| TLV71333PDBVR.A               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| TLV71333PDBVRG4               | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| TLV71333PDBVRG4.A             | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| <a href="#">TLV71333PDBVT</a> | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| TLV71333PDBVT.A               | Active        | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | VUFI                |
| <a href="#">TLV71333PDQNR</a> | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AH                  |
| TLV71333PDQNR.A               | Active        | Production           | X2SON (DQN)   4  | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AH                  |
| <a href="#">TLV71333PDQNT</a> | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AH                  |
| TLV71333PDQNT.A               | Active        | Production           | X2SON (DQN)   4  | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | AH                  |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative

and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF TLV713P :**

- Automotive : [TLV713P-Q1](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

## TAPE AND REEL INFORMATION




\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLV71310PDBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71310PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71310PDQNR   | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71310PDQNT   | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71311PDBVR   | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71311PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71312PDBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71312PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71312PDBVTG4 | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71312PDQNR   | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71312PDQNT   | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71315PDBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71315PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71315PDQNR   | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71315PDQNT   | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV713185PDBVR  | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |

| Device           | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TLV713185PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV713185PDQNR   | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV713185PDQNT   | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71318PDBVR    | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71318PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71318PDBVT    | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71318PDQNR    | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71318PDQNT    | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71320DQNR     | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71320DQNT     | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71325PDBVR    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71325PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71325PDBVT    | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71325PDQNR    | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71325PDQNT    | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV713285PDBVR   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV713285PDBVRG4 | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV713285PDBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV713285PDQNR   | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV713285PDQNRG4 | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV713285PDQNT   | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71328PDBVR    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71328PDBVT    | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71328PDQNR    | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71328PDQNRG4  | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71328PDQNT    | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71330PDBVR    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71330PDBVR    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71330PDBVT    | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71330PDQNR    | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71330PDQNT    | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71333PDBVR    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71333PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71333PDBVT    | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| TLV71333PDQNR    | X2SON        | DQN             | 4    | 3000 | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| TLV71333PDQNT    | X2SON        | DQN             | 4    | 250  | 180.0              | 8.4                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device          | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLV71310PDBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71310PDBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71310PDQNR   | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71310PDQNT   | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71311PDBVR   | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| TLV71311PDBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71312PDBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71312PDBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71312PDBVTG4 | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71312PDQNR   | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71312PDQNT   | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71315PDBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71315PDBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71315PDQNR   | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71315PDQNT   | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV713185PDBVR  | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV713185PDBVT  | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV713185PDQNR  | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |

| Device           | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TLV713185PDQNT   | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71318PDBVR    | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| TLV71318PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71318PDBVT    | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71318PDQNR    | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71318PDQNT    | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71320DQNR     | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71320DQNT     | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71325PDBVR    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71325PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71325PDBVT    | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71325PDQNR    | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71325PDQNT    | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV713285PDBVR   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV713285PDBVRG4 | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV713285PDBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV713285PDQNR   | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV713285PDQNRG4 | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV713285PDQNT   | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71328PDBVR    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71328PDBVT    | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71328PDQNR    | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71328PDQNRG4  | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71328PDQNT    | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71330PDBVR    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71330PDBVR    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71330PDBVT    | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71330PDQNR    | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71330PDQNT    | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71333PDBVR    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71333PDBVRG4  | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71333PDBVT    | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| TLV71333PDQNR    | X2SON        | DQN             | 4    | 3000 | 210.0       | 185.0      | 35.0        |
| TLV71333PDQNT    | X2SON        | DQN             | 4    | 250  | 210.0       | 185.0      | 35.0        |

**DQN 4**

## GENERIC PACKAGE VIEW

**X2SON - 0.4 mm max height**


PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4210367/F







4215302/E 12/2016

## NOTES:

1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. The package thermal pad must be soldered to the printed circuit board for optimal thermal and mechanical performance.
4. Features may not exist. Recommend use of pin 1 marking on top of package for orientation purposes.
5. Shape of exposed side leads may differ.
6. Number and location of exposed tie bars may vary.



LAND PATTERN EXAMPLE  
SCALE: 40X




SOLDER MASK DETAIL

4215302/E 12/2016

NOTES: (continued)

7. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).
8. If any vias are implemented, it is recommended that vias under paste be filled, plugged or tented.



SOLDER PASTE EXAMPLE  
 BASED ON 0.075 - 0.1mm THICK STENCIL

EXPOSED PAD  
 88% PRINTED SOLDER COVERAGE BY AREA  
 SCALE: 60X

4215302/E 12/2016

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.




# EXAMPLE BOARD LAYOUT


DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)


6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025