





TMDSSK3358 Board

- See the Hardware Implementation Document for design details
- See the Hardware User Guide for board details
- See the PCB Build Specification for PCB Details







AM3358
ZCZ Package




ID Memory




User Reset/Interrupt Switches



User LEDs





Mechanical




Boot Configuration

AM335X_LCD_DATA[15:0]	01000000000011011b	MMC0, SPI0, UART0, USB0
-----------------------	--------------------	-------------------------







Terminations




VTT Regulator





DDR3 DECAPS



VTT REG. DECAPS







<Variant Name>

LCD


CAPACITIVE TOUCH OPTION




LCD Module




BackLight Driver




1.8V LDO




3.3V LDO




SD/MMC Connector




USB1 Port




USB1 Power




[illegible]



Reset





```
PHYADDRESS = 00000
```






Mode "0000" = 1000 BASE-T, RGMII






Audio Codec







USB HUB




USB - UART (Optional)




FILTERS



EEPROM



FT2232 DECAPS



JTAG

