

## SN74LVC1G04 シングル インバータ ゲート

### 1 特長

- 0.64mm<sup>2</sup>、0.5mm ピッチの超小型パッケージ (DPW) で供給
- 5V  $V_{CC}$  動作をサポート
- 入力 は 5.5V までの電圧に対応し、 $V_{CC}$  への降圧変換が可能
- 3.3ns の最大  $t_{pd}$  (3.3V 時)
- 低い消費電力、最大  $I_{CC}$ : 10 $\mu$ A
- 3.3V で  $\pm 24$ mA の出力駆動能力
- $I_{off}$  により活線挿抜、部分的パワーダウン モード、バックドライブ保護をサポート
- JESD 78、Class II 準拠で 100mA 超のラッチアップ性能
- JESD 22 を上回る ESD 保護
  - 2000V、人体モデル (A114-A)
  - 200V、マシン モデル (A115-A)
  - 1000V、デバイス帯電モデル (C101)

### 2 アプリケーション

- AV レシーバ
- オーディオ ドック:ポータブル
- ブルーレイ プレーヤおよびホームシアター
- 内蔵 PC
- MP3 プレーヤ / レコーダ (ポータブル オーディオ)
- パーソナル デジタル アシスタント (PDA)
- 電源:テレコム / サーバーの AC/DC 電源:シングルコントローラ:アナログおよびデジタル
- ソリッド ステートドライブ (SSD):クライアントおよびエンタープライズ
- テレビ:LCD / デジタル、高品位(HDTV)
- タブレット:エンタープライズ
- ビデオ アナリティクス:サーバー
- ワイヤレス ヘッドセット、キーボード、マウス

### 3 説明

このシングル インバータ ゲートは、1.65V ~ 5.5V  $V_{CC}$  動作に設計されています。

SN74LVC1G04 デバイスは、ブール関数  $Y = \bar{A}$  を実行します。


この CMOS デバイスは出力駆動能力が大きく、広い  $V_{CC}$  動作範囲にわたって静止電力消費が低く保たれます。

SN74LVC1G04 デバイスは、ボディ サイズ 0.8mm × 0.8mm の超小型 DPW パッケージなど、各種のパッケージで供給されます。

#### パッケージ情報

| 型番          | パッケージ (1)        | パッケージ サイズ (2)   | 本体サイズ (公称) (3)  |
|-------------|------------------|-----------------|-----------------|
| SN74LVC1G04 | DBV (SOT-23, 5)  | 2.9mm × 2.8mm   | 2.9mm × 1.6mm   |
|             | DCK (SC70, 5)    | 2.0mm × 2.1mm   | 2.0mm × 1.25mm  |
|             | DPW (X2SON, 5)   | 0.8mm × 0.8mm   | 0.8mm × 0.8mm   |
|             | DRL (SOT-5X3, 5) | 1.6mm × 1.6mm   | 1.6mm × 1.2mm   |
|             | DRY (USON, 6)    | 1.45mm × 1.0mm  | 1.45mm × 1.0mm  |
|             | DSF (X2SON, 6)   | 1.0mm × 1.0mm   | 1.0mm × 1.0mm   |
|             | YZP (DSBGA, 5)   | 1.75mm × 1.75mm | 1.75mm × 1.25mm |
|             | YZV (DSBGA, 4)   | 1.25mm × 1.25mm | 1.25mm × 1.25mm |

- (1) 利用可能なすべてのパッケージについては、データシートの末尾にある注文情報を参照してください。
- (2) パッケージ サイズ (長さ × 幅) は公称値であり、該当する場合はピンも含まれます。
- (3) 本体サイズ (長さ×幅) は公称値であり、ピンは含まれません。




概略回路図



## 目次

|                                                                                                             |          |                                     |           |
|-------------------------------------------------------------------------------------------------------------|----------|-------------------------------------|-----------|
| <b>1 特長</b> .....                                                                                           | <b>1</b> | <b>7 詳細説明</b> .....                 | <b>10</b> |
| <b>2 アプリケーション</b> .....                                                                                     | <b>1</b> | 7.1 概要.....                         | 10        |
| <b>3 説明</b> .....                                                                                           | <b>1</b> | 7.2 機能ブロック図.....                    | 10        |
| <b>4 ピン構成および機能</b> .....                                                                                    | <b>3</b> | 7.3 機能説明.....                       | 10        |
| <b>5 仕様</b> .....                                                                                           | <b>4</b> | 7.4 デバイスの機能モード.....                 | 10        |
| 5.1 絶対最大定格.....                                                                                             | 4        | <b>8 アプリケーションと実装</b> .....          | <b>11</b> |
| 5.2 ESD 定格.....                                                                                             | 4        | 8.1 アプリケーション情報に関する免責事項.....         | 11        |
| 5.3 推奨動作条件.....                                                                                             | 5        | 8.2 アプリケーション情報.....                 | 11        |
| 5.4 熱に関する情報.....                                                                                            | 5        | 8.3 代表的なアプリケーション.....               | 11        |
| 5.5 電気的特性.....                                                                                              | 6        | 8.4 電源に関する推奨事項.....                 | 12        |
| 5.6 スイッチング特性、 $C_L = 15\text{pF}$ .....                                                                     | 6        | 8.5 レイアウト.....                      | 12        |
| 5.7 スイッチング特性、 $C_L = 30\text{pF}$ または $50\text{pF}$ 、 $-40^\circ\text{C}$<br>$\sim 85^\circ\text{C}$ .....  | 6        | <b>9 デバイスおよびドキュメントのサポート</b> .....   | <b>13</b> |
| 5.8 スイッチング特性、 $C_L = 15\text{pF}$ 、 $-40^\circ\text{C} \sim 125^\circ\text{C}$ .....                        | 7        | 9.1 ドキュメントの更新通知を受け取る方法.....         | 13        |
| 5.9 スイッチング特性、 $C_L = 30\text{pF}$ または $50\text{pF}$ 、 $-40^\circ\text{C}$<br>$\sim 125^\circ\text{C}$ ..... | 7        | 9.2 サポート・リソース.....                  | 13        |
| 5.10 動作特性.....                                                                                              | 7        | 9.3 商標.....                         | 13        |
| 5.11 代表的特性.....                                                                                             | 7        | 9.4 静電気放電に関する注意事項.....              | 13        |
| <b>6 パラメータ測定情報</b> .....                                                                                    | <b>8</b> | 9.5 用語集.....                        | 13        |
|                                                                                                             |          | <b>10 改訂履歴</b> .....                | <b>13</b> |
|                                                                                                             |          | <b>11 メカニカル、パッケージ、および注文情報</b> ..... | <b>14</b> |

## 4 ピン構成および機能



### ピンの機能

| ピン              |               |          |        |     |     | 説明    |
|-----------------|---------------|----------|--------|-----|-----|-------|
| 名称              | DBV, DCK, DRL | DSF, DRY | YZP    | YZV | DPW |       |
| NC              | 1             | 1, 5     | A1, B2 | -   | 1   | 無接続   |
| A               | 2             | 2        | B1     | A1  | 2   | 入力    |
| GND             | 3             | 3        | C1     | B1  | 3   | グラウンド |
| Y               | 4             | 4        | C2     | B2  | 4   | 出力    |
| V <sub>CC</sub> | 5             | 6        | A2     | A2  | 5   | 電源端子  |

## 5 仕様

### 5.1 絶対最大定格

自由気流での動作温度範囲内 (特に記述のない限り) <sup>(1)</sup>

|           |                                                      | 最小値       | 最大値            | 単位      |
|-----------|------------------------------------------------------|-----------|----------------|---------|
| $V_{CC}$  | 電源電圧範囲                                               | -0.5      | 6.5            | V       |
| $V_I$     | 入力電圧範囲                                               | -0.5      | 6.5            | V       |
| $V_O$     | 高インピーダンスまたは電源オフ状態で出力に印加される電圧範囲 <sup>(2)</sup>        | -0.5      | 6.5            | V       |
| $V_O$     | High または Low 状態にある任意の出力に印加される電圧範囲 <sup>(2) (3)</sup> | -0.5      | $V_{CC} + 0.5$ | V       |
| $I_{IK}$  | 入力クランプ電流                                             | $V_I < 0$ |                | -50 mA  |
| $I_{OK}$  | 出力クランプ電流                                             | $V_O < 0$ |                | -50 mA  |
| $I_O$     | 連続出力電流                                               |           |                | ±50 mA  |
|           | $V_{CC}$ または GND を通過する連続電流                           |           |                | ±100 mA |
| $T_{stg}$ | 保存温度                                                 | -65       | 150            | °C      |

- (1) 絶対最大定格を上回るストレスが加わった場合、デバイスに永続的な損傷が発生する可能性があります。これらは、ストレス定格のみを示すものであり、これらの条件や「推奨動作条件」に示されたその他の条件と等しい、またはそれを超える条件で本デバイスが正しく動作することを意味するものではありません。絶対最大定格の状態が長時間続くと、デバイスの信頼性に影響を与える可能性があります。
- (2) 入力電流と出力電流の定格を遵守していても、入力と出力の負電圧の定格を超える可能性があります。
- (3)  $V_{CC}$  の値は、「推奨動作条件」の表に記載されています。

### 5.2 ESD 定格

|             |                                                                | 値     | 単位 |
|-------------|----------------------------------------------------------------|-------|----|
| $V_{(ESD)}$ | 人体モデル (HBM)、ANSI/ESDA/JEDEC JS-001 に準拠、すべてのピン <sup>(1)</sup>   | ±2000 | V  |
|             | デバイス帯電モデル (CDM)、JEDEC 仕様 JESD22-C101 に準拠、すべてのピン <sup>(2)</sup> | ±1000 |    |

- (1) JEDEC のドキュメント JEP155 に、500V HBM では標準の ESD 管理プロセスで安全な製造が可能であると規定されています。
- (2) JEDEC のドキュメント JEP157 に、250V CDM では標準の ESD 管理プロセスで安全な製造が可能であると規定されています。

## 5.3 推奨動作条件

| (1)             |                       | 最小値                                         | 最大値                    | 単位   |
|-----------------|-----------------------|---------------------------------------------|------------------------|------|
| V <sub>CC</sub> | 電源電圧                  | 動作                                          | 1.65                   | V    |
|                 |                       | データ保持のみ                                     | 1.5                    |      |
| V <sub>IH</sub> | High レベル入力電圧          | V <sub>CC</sub> = 1.65V~1.95V               | 0.65 × V <sub>CC</sub> | V    |
|                 |                       | V <sub>CC</sub> = 2.3V~2.7V                 | 1.7                    |      |
|                 |                       | V <sub>CC</sub> = 3V~3.6V                   | 2                      |      |
|                 |                       | V <sub>CC</sub> = 4.5V~5.5V                 | 0.7 × V <sub>CC</sub>  |      |
| V <sub>IL</sub> | Low レベル入力電圧           | V <sub>CC</sub> = 1.65V~1.95V               | 0.35 × V <sub>CC</sub> | V    |
|                 |                       | V <sub>CC</sub> = 2.3V~2.7V                 | 0.7                    |      |
|                 |                       | V <sub>CC</sub> = 3V~3.6V                   | 0.8                    |      |
|                 |                       | V <sub>CC</sub> = 4.5V~5.5V                 | 0.3 × V <sub>CC</sub>  |      |
| V <sub>I</sub>  | 入力電圧                  | 0                                           | 5.5                    | V    |
| V <sub>O</sub>  | 出力電圧                  | 0                                           | V <sub>CC</sub>        | V    |
| I <sub>OH</sub> | High レベル出力電流          | V <sub>CC</sub> = 1.65V                     | -4                     | mA   |
|                 |                       | V <sub>CC</sub> = 2.3V                      | -8                     |      |
|                 |                       | V <sub>CC</sub> = 3V                        | -16                    |      |
|                 |                       |                                             | -24                    |      |
|                 |                       | V <sub>CC</sub> = 4.5V                      | -32                    |      |
| I <sub>OL</sub> | Low レベル出力電流           | V <sub>CC</sub> = 1.65V                     | 4                      | mA   |
|                 |                       | V <sub>CC</sub> = 2.3V                      | 8                      |      |
|                 |                       | V <sub>CC</sub> = 3V                        | 16                     |      |
|                 |                       |                                             | 24                     |      |
|                 |                       | V <sub>CC</sub> = 4.5V                      | 32                     |      |
| Δt/Δv           | 入力遷移の立ち上がりまたは立ち下がりレート | V <sub>CC</sub> = 1.8V ± 0.15V, 2.5V ± 0.2V | 20                     | ns/V |
|                 |                       | V <sub>CC</sub> = 3.3V ± 0.3V               | 10                     |      |
|                 |                       | V <sub>CC</sub> = 5V ± 0.5V                 | 5                      |      |
| T <sub>A</sub>  | 外気温度での動作時             | -40                                         | 125                    | °C   |

(1) デバイスが適切に動作するように、デバイスの未使用の入力はすべて、V<sub>CC</sub> または GND に固定する必要があります。テキサス インストルメンツのアプリケーション レポート『低速またはフローティング CMOS 入力の影響』(文献番号 SCBA004) を参照してください。

## 5.4 熱に関する情報

| 熱評価基準 <sup>(1)</sup> |                     | SN74LVC1G04 |       |      |      |      |      | 単位   |
|----------------------|---------------------|-------------|-------|------|------|------|------|------|
|                      |                     | DBV         | DCK   | DRL  | DRY  | YZP  | DPW  |      |
|                      |                     | 5 ピン        | 5 ピン  | 5 ピン | 6 ピン | 5 ピン | 4 ピン |      |
| R <sub>θJA</sub>     | 接合部から周囲への熱抵抗        | 357.1       | 371.0 | 243  | 439  | 130  | 340  | °C/W |
| R <sub>θJCTop</sub>  | 接合部からケース (上面) への熱抵抗 | 263.7       | 297.5 | 78   | 277  | 54   | 215  |      |
| R <sub>θJB</sub>     | 接合部から基板への熱抵抗        | 264.4       | 258.6 | 78   | 271  | 51   | 294  |      |
| ψ <sub>JT</sub>      | 接合部から上面への特性パラメータ    | 195.6       | 195.6 | 10   | 84   | 1    | 41   |      |
| ψ <sub>JB</sub>      | 接合部から基板への特性パラメータ    | 262.2       | 256.2 | 77   | 271  | 50   | 294  |      |
| R <sub>θJBot</sub>   | 接合部からケース (底面) への熱抵抗 | —           | —     | —    | —    | —    | 250  |      |

(1) 従来および最新の熱評価基準の詳細については、『半導体および IC パッケージの熱評価基準』アプリケーション ノートを参照してください。

## 5.5 電気的特性

自由空気での推奨動作温度範囲内 (特に記述のない限り)

| パラメータ            |      | テスト条件                                                              | V <sub>CC</sub> | -40℃ ～ 85℃            | 推奨値<br>-40℃ ～ 125℃ |                       |     | 単位 |
|------------------|------|--------------------------------------------------------------------|-----------------|-----------------------|--------------------|-----------------------|-----|----|
|                  |      |                                                                    |                 | 最小値                   | 標準値 <sup>(1)</sup> | 最大値                   | 最小値 |    |
| V <sub>OH</sub>  |      | I <sub>OH</sub> = -100μA                                           | 1.65V ～ 5.5V    | V <sub>CC</sub> - 0.1 |                    | V <sub>CC</sub> - 0.1 |     | V  |
|                  |      | I <sub>OH</sub> = -4mA                                             | 1.65V           | 1.2                   |                    | 1.2                   |     |    |
|                  |      | I <sub>OH</sub> = -8mA                                             | 2.3V            | 1.9                   |                    | 1.9                   |     |    |
|                  |      | I <sub>OH</sub> = -16mA                                            | 3V              | 2.4                   |                    | 2.4                   |     |    |
|                  |      | I <sub>OH</sub> = -24mA                                            |                 | 2.3                   |                    | 2.3                   |     |    |
|                  |      | I <sub>OH</sub> = -32mA                                            | 4.5V            | 3.8                   |                    | 3.8                   |     |    |
| V <sub>OL</sub>  |      | I <sub>OL</sub> = 100μA                                            | 1.65V ～ 5.5V    | 0.1                   |                    | 0.1                   |     | V  |
|                  |      | I <sub>OL</sub> = 4mA                                              | 1.65V           | 0.45                  |                    | 0.45                  |     |    |
|                  |      | I <sub>OL</sub> = 8mA                                              | 2.3V            | 0.3                   |                    | 0.3                   |     |    |
|                  |      | I <sub>OL</sub> = 16mA                                             | 3V              | 0.4                   |                    | 0.4                   |     |    |
|                  |      | I <sub>OL</sub> = 24mA                                             |                 | 0.55                  |                    | 0.55                  |     |    |
|                  |      | I <sub>OL</sub> = 32mA                                             | 4.5V            | 0.55                  |                    | 0.55                  |     |    |
| I <sub>I</sub>   | A 入力 | V <sub>I</sub> = 5.5 V または GND                                     | 0～5.5V          | ±5                    |                    | ±5                    |     | μA |
| I <sub>off</sub> |      | V <sub>I</sub> または V <sub>O</sub> = 5.5V                           | 0               | ±10                   |                    | ±10                   |     | μA |
| I <sub>CC</sub>  |      | V <sub>I</sub> = 5.5 V または GND    I <sub>O</sub> = 0               | 1.65V ～ 5.5V    | 10                    |                    | 10                    |     | μA |
| ΔI <sub>CC</sub> |      | 1 つの入力は V <sub>CC</sub> - 0.6V、<br>その他の入力は V <sub>CC</sub> または GND | 3V ～ 5.5V       | 500                   |                    | 500                   |     | μA |
| C <sub>i</sub>   |      | V <sub>I</sub> = V <sub>CC</sub> または GND                           | 3.3V            | 3.5                   |                    | 3.50                  |     | pF |

(1) 代表値はすべて、V<sub>CC</sub> = 3.3V、T<sub>A</sub> = 25°Cにおける値です。

## 5.6 スイッチング特性、C<sub>L</sub> = 15pF

自由気流での推奨動作温度範囲内、C<sub>L</sub> = 15pF (特に記述のない限り)

(図 6-1 を参照)

| パラメータ           | 始点<br>(入力) | 終点<br>(出力) | -40°C ~ 85°C                      |     |                                  |     |                                  |     |                                |     | 単位 |
|-----------------|------------|------------|-----------------------------------|-----|----------------------------------|-----|----------------------------------|-----|--------------------------------|-----|----|
|                 |            |            | V <sub>CC</sub> = 1.8V<br>± 0.15V |     | V <sub>CC</sub> = 2.5V<br>± 0.2V |     | V <sub>CC</sub> = 3.3V<br>± 0.3V |     | V <sub>CC</sub> = 5V<br>± 0.5V |     |    |
|                 |            |            | 最小値                               | 最大値 | 最小値                              | 最大値 | 最小値                              | 最大値 | 最小値                            | 最大値 |    |
| t <sub>pd</sub> | A          | Y          | 2                                 | 6.4 | 1                                | 4.2 | 0.7                              | 3.3 | 0.7                            | 3.1 | ns |

## 5.7 スイッチング特性、C<sub>L</sub> = 30pF または 50pF、-40°C ~ 85°C

自由気流での推奨動作温度範囲内、C<sub>L</sub> = 30pF または 50pF (特に記述のない限り)

(図 6-2 を参照)

| パラメータ           | 始点<br>(入力) | 終点<br>(出力) | -40°C ~ 85°C                      |     |                                  |     |                                  |     |                                |     | 単位 |
|-----------------|------------|------------|-----------------------------------|-----|----------------------------------|-----|----------------------------------|-----|--------------------------------|-----|----|
|                 |            |            | V <sub>CC</sub> = 1.8V<br>± 0.15V |     | V <sub>CC</sub> = 2.5V<br>± 0.2V |     | V <sub>CC</sub> = 3.3V<br>± 0.3V |     | V <sub>CC</sub> = 5V<br>± 0.5V |     |    |
|                 |            |            | 最小値                               | 最大値 | 最小値                              | 最大値 | 最小値                              | 最大値 | 最小値                            | 最大値 |    |
| t <sub>pd</sub> | A          | Y          | 3                                 | 7.5 | 1.4                              | 5.2 | 1                                | 4.2 | 1                              | 3.7 | ns |

## 5.8 スイッチング特性、 $C_L = 15\text{pF}$ 、 $-40^\circ\text{C} \sim 125^\circ\text{C}$

自由気流での推奨動作温度範囲内、 $C_L = 15\text{pF}$  (特に記述のない限り)  
(図 6-1 を参照)

| パラメータ           | 始点<br>(入力) | 終点<br>(出力) | -40°C ~ 125°C                     |     |                                  |     |                                  |     |                                |     | 単位 |
|-----------------|------------|------------|-----------------------------------|-----|----------------------------------|-----|----------------------------------|-----|--------------------------------|-----|----|
|                 |            |            | V <sub>CC</sub> = 1.8V<br>± 0.15V |     | V <sub>CC</sub> = 2.5V<br>± 0.2V |     | V <sub>CC</sub> = 3.3V<br>± 0.3V |     | V <sub>CC</sub> = 5V<br>± 0.5V |     |    |
|                 |            |            | 最小値                               | 最大値 | 最小値                              | 最大値 | 最小値                              | 最大値 | 最小値                            | 最大値 |    |
| t <sub>pd</sub> | A          | Y          | 2                                 | 6.4 | 1                                | 4.2 | 0.7                              | 3.3 | 0.7                            | 3.1 | ns |

## 5.9 スイッチング特性、 $C_L = 30\text{pF}$ または $50\text{pF}$ 、 $-40^\circ\text{C} \sim 125^\circ\text{C}$

自由気流での推奨動作温度範囲内、 $C_L = 30\text{pF}$  または  $50\text{pF}$  (特に記述のない限り)  
(図 6-2 を参照)

| パラメータ           | 始点<br>(入力) | 終点<br>(出力) | -40°C ~ 125°C                     |     |                                  |     |                                  |     |                                |     | 単位 |
|-----------------|------------|------------|-----------------------------------|-----|----------------------------------|-----|----------------------------------|-----|--------------------------------|-----|----|
|                 |            |            | V <sub>CC</sub> = 1.8V<br>± 0.15V |     | V <sub>CC</sub> = 2.5V<br>± 0.2V |     | V <sub>CC</sub> = 3.3V<br>± 0.3V |     | V <sub>CC</sub> = 5V<br>± 0.5V |     |    |
|                 |            |            | 最小値                               | 最大値 | 最小値                              | 最大値 | 最小値                              | 最大値 | 最小値                            | 最大値 |    |
| t <sub>pd</sub> | A          | Y          | 3                                 | 7.5 | 1.4                              | 5.2 | 1                                | 4.2 | 1                              | 3.7 | ns |

## 5.10 動作特性

自由気流での動作温度範囲内 (特に記述のない限り)

| パラメータ           | テスト条件              | $V_{CC} = 1.8\text{V}$ | $V_{CC} = 2.5\text{V}$ | $V_{CC} = 3.3\text{V}$ | $V_{CC} = 5.0\text{V}$ | 単位 |
|-----------------|--------------------|------------------------|------------------------|------------------------|------------------------|----|
|                 |                    | 標準値                    | 標準値                    | 標準値                    | 標準値                    |    |
| $C_{pd}$ 電力散逸容量 | $f = 10\text{MHz}$ | 16                     | 18                     | 18                     | 20                     | pF |

## 5.11 代表的特性




図 5-1.  $3.3\text{V } V_{CC}$  での温度範囲における昇温脱離法





図 5-2.  $25^\circ\text{C}$  での  $V_{CC}$  における昇温脱離





## 6 パラメータ測定情報



LOAD CIRCUIT


| TEST              | S1         |
|-------------------|------------|
| $t_{PLH}/t_{PHL}$ | Open       |
| $t_{PLZ}/t_{PZL}$ | $V_{LOAD}$ |
| $t_{PHZ}/t_{PZH}$ | GND        |

| $V_{CC}$                         | INPUTS   |                      | $V_M$      | $V_{LOAD}$        | $C_L$ | $R_L$        | $V_{\Delta}$ |
|----------------------------------|----------|----------------------|------------|-------------------|-------|--------------|--------------|
|                                  | $V_I$    | $t_r/t_f$            |            |                   |       |              |              |
| $1.8\text{ V} \pm 0.15\text{ V}$ | $V_{CC}$ | $\leq 2\text{ ns}$   | $V_{CC}/2$ | $2 \times V_{CC}$ | 15 pF | 1 M $\Omega$ | 0.15 V       |
| $2.5\text{ V} \pm 0.2\text{ V}$  | $V_{CC}$ | $\leq 2\text{ ns}$   | $V_{CC}/2$ | $2 \times V_{CC}$ | 15 pF | 1 M $\Omega$ | 0.15 V       |
| $3.3\text{ V} \pm 0.3\text{ V}$  | 3 V      | $\leq 2.5\text{ ns}$ | 1.5 V      | 6 V               | 15 pF | 1 M $\Omega$ | 0.3 V        |
| $5\text{ V} \pm 0.5\text{ V}$    | $V_{CC}$ | $\leq 2.5\text{ ns}$ | $V_{CC}/2$ | $2 \times V_{CC}$ | 15 pF | 1 M $\Omega$ | 0.3 V        |

VOLTAGE WAVEFORMS  
PULSE DURATIONVOLTAGE WAVEFORMS  
SETUP AND HOLD TIMESVOLTAGE WAVEFORMS  
PROPAGATION DELAY TIMES  
INVERTING AND NONINVERTING OUTPUTSVOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES  
LOW- AND HIGH-LEVEL ENABLING

- NOTES:
- $C_L$  includes probe and jig capacitance.
  - Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10\text{ MHz}$ ,  $Z_O = 50\ \Omega$ .
  - The outputs are measured one at a time, with one transition per measurement.
  - $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - All parameters and waveforms are not applicable to all devices.


図 6-1. 負荷回路および電圧波形




LOAD CIRCUIT

| TEST              | S1         |
|-------------------|------------|
| $t_{PLH}/t_{PHL}$ | Open       |
| $t_{PLZ}/t_{PZL}$ | $V_{LOAD}$ |
| $t_{PHZ}/t_{PZH}$ | GND        |


| $V_{CC}$                         | INPUTS   |                      | $V_M$      | $V_{LOAD}$        | $C_L$ | $R_L$        | $V_{\Delta}$ |
|----------------------------------|----------|----------------------|------------|-------------------|-------|--------------|--------------|
|                                  | $V_I$    | $t_r/t_f$            |            |                   |       |              |              |
| $1.8\text{ V} \pm 0.15\text{ V}$ | $V_{CC}$ | $\leq 2\text{ ns}$   | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 1 k $\Omega$ | 0.15 V       |
| $2.5\text{ V} \pm 0.2\text{ V}$  | $V_{CC}$ | $\leq 2\text{ ns}$   | $V_{CC}/2$ | $2 \times V_{CC}$ | 30 pF | 500 $\Omega$ | 0.15 V       |
| $3.3\text{ V} \pm 0.3\text{ V}$  | 3 V      | $\leq 2.5\text{ ns}$ | 1.5 V      | 6 V               | 50 pF | 500 $\Omega$ | 0.3 V        |
| $5\text{ V} \pm 0.5\text{ V}$    | $V_{CC}$ | $\leq 2.5\text{ ns}$ | $V_{CC}/2$ | $2 \times V_{CC}$ | 50 pF | 500 $\Omega$ | 0.3 V        |




VOLTAGE WAVEFORMS  
PULSE DURATION



VOLTAGE WAVEFORMS  
SETUP AND HOLD TIMES



VOLTAGE WAVEFORMS  
PROPAGATION DELAY TIMES  
INVERTING AND NONINVERTING OUTPUTS



VOLTAGE WAVEFORMS  
ENABLE AND DISABLE TIMES  
LOW- AND HIGH-LEVEL ENABLING

- NOTES:
- $C_L$  includes probe and jig capacitance.
  - Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10\text{ MHz}$ ,  $Z_O = 50\ \Omega$ .
  - The outputs are measured one at a time, with one transition per measurement.
  - $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - $t_{PZL}$  and  $t_{PZH}$  are the same as  $t_{en}$ .
  - $t_{PLH}$  and  $t_{PHL}$  are the same as  $t_{pd}$ .
  - All parameters and waveforms are not applicable to all devices.

図 6-2. 負荷回路および電圧波形

## 7 詳細説明

### 7.1 概要

SN74LVC1G04 デバイスにはインバータ ゲートが内蔵されており、ブール関数  $Y = \bar{A}$  を実行します。このデバイスは  $I_{off}$  を使用することで、部分的パワーダウン アプリケーションに完全対応しています。 $I_{off}$  回路が出力をディセーブルにするため、電源切断時にデバイスに電流が逆流して損傷に至ることを回避できます。

DPW パッケージ テクノロジーは、IC パッケージングにおける大きなブレークスルーです。フットプリントが 0.64 平方 mm と超小型であり、従来の製造に適した 0.5mm のリード ピッチを保持しながら、その他のパッケージ オプションに比べて基板面積を大幅に節約できます。

### 7.2 機能ブロック図



### 7.3 機能説明

- 広い動作電圧範囲。
  - 1.65V ~ 5.5V で動作。
- 降圧変換に対応。
- 5.5V までの入力電圧に対応。
- $I_{off}$  機能により、 $V_{CC}$  が 0V のときに入力と出力に電圧をかけることが可能。

### 7.4 デバイスの機能モード

機能表

| 入力<br>A | 出力<br>Y |
|---------|---------|
| H       | L       |
| L       | H       |

## 8 アプリケーションと実装

### 8.1 アプリケーション情報に関する免責事項

#### 注


以下のアプリケーション情報は、TI の製品仕様に含まれるものではなく、TI ではその正確性または完全性を保証いたしません。個々の目的に対する製品の適合性については、お客様の責任で判断していただくことになります。お客様は自身の設計実装を検証しテストすることで、システムの機能を確認する必要があります。

### 8.2 アプリケーション情報


SN74LVC1G04 は、LED アプリケーションなどの高出力駆動による反転ロジックの実装に使用できる、高駆動 CMOS デバイスです。3.3V で 24mA の駆動電流を生成できるため、複数の出力の駆動に理想的であり、最大 100MHz の高速アプリケーションに適しています。入力 は 5.5V 耐圧であり、 $V_{CC}$  に降圧変換できます。

### 8.3 代表的なアプリケーション

Inverter Logic Function



Basic LED Driver



#### 8.3.1 設計要件

このデバイスは CMOS 技術を採用しており、平衡型出力ドライバを備えています。上限値を超える電流が流れる可能性があるため、バスが競合しないように注意が必要です。また、大きな駆動能力で軽負荷を駆動することでも高速なエッジが生じるため、配線と負荷の条件を検討してリンギングを防止してください。

#### 8.3.2 詳細な設計手順

##### 1. 推奨入力条件

- 立ち上がり時間と立ち下がり時間の仕様:「[推奨動作条件](#)」表の ( $\Delta t/\Delta V$ ) を参照してください。
- High レベルと Low レベルを規定:「[推奨動作条件](#)」表の ( $V_{IH}$  および  $V_{IL}$ ) を参照してください。
- 入力は過電圧許容で、「[推奨動作条件](#)」表で記載された任意の有効な  $V_{CC}$  において (最大  $V_I$ ) に対応できます。

##### 2. 推奨出力条件

- 負荷電流は、出力ごとに  $I_O$  の最大値を超えないようにする必要があります。また、本製品の総電流 ( $V_{CC}$  または GND に流れる連続電流) を超えないようにする必要があります。これらの限界値は、「[絶対最大定格](#)」表に記載されています。
- 出力は、 $V_{CC}$  を超えてプルされないようにしてください。

### 8.3.3 アプリケーション曲線




図 8-1. I<sub>cc</sub> と周波数との関係

## 8.4 電源に関する推奨事項

電源には、「[推奨動作条件](#)」表に記載されている最小電源電圧定格と最大電源電圧定格の間の任意の電圧を使用できます。

電源の障害を防止するため、各 VCC ピンに適切なバイパス コンデンサを配置する必要があります。単一電源のデバイスの場合は、0.1μF を推奨します。複数の VCC ピンがある場合は、各電源ピンに対して 0.01μF または 0.022μF を推奨します。複数のバイパス コンデンサを並列に配置して、異なる周波数のノイズを除去することもできます。一般的に、0.1μF と 1μF のコンデンサは並列に使用されます。最良の結果を得るため、バイパス コンデンサは電源ピンのできるだけ近くに配置してください。

## 8.5 レイアウト


### 8.5.1 レイアウトのガイドライン

多ビット ロジック デバイスを使用する場合、入力をフローティングにしないでください。

多くの場合、デジタル論理デバイスの機能または機能の一部は使用されません (たとえば、トリプル入力 AND ゲートの 2 つの入力のみを使用する場合や 4 つのバッファ ゲートのうちの 3 つのみを使用する場合)。このような入力ピンを未接続のままにしないでください。外部接続の電圧が未確定の場合、動作状態が不定になるためです。あらゆる状況で遵守しなければならない規則は次の段落で規定されています。

デジタル ロジック デバイスの未使用の入力はすべて、フローティングにならないように、High または Low バイアスに接続する必要があります。特定の未使用の入力に対して適用が必要となるロジック レベルは、デバイスの機能により異なります。一般に、GND または VCC のうち、より適切であるかより利便性の高い方に接続されます。

### 8.5.2 レイアウト例



## 9 デバイスおよびドキュメントのサポート

### 9.1 ドキュメントの更新通知を受け取る方法

ドキュメントの更新についての通知を受け取るには、[www.tij.co.jp](http://www.tij.co.jp) のデバイス製品フォルダを開いてください。[通知] をクリックして登録すると、変更されたすべての製品情報に関するダイジェストを毎週受け取ることができます。変更の詳細については、改訂されたドキュメントに含まれている改訂履歴をご覧ください。

### 9.2 サポート・リソース

テキサス・インスツルメンツ E2E™ サポート・フォーラムは、エンジニアが検証済みの回答と設計に関するヒントをエキスパートから迅速かつ直接得ることができる場所です。既存の回答を検索したり、独自の質問をしたりすることで、設計に必要な支援を迅速に得ることができます。

リンクされているコンテンツは、各寄稿者により「現状のまま」提供されるものです。これらはテキサス・インスツルメンツの仕様を構成するものではなく、必ずしもテキサス・インスツルメンツの見解を反映したものではありません。テキサス・インスツルメンツの使用条件を参照してください。

### 9.3 商標

テキサス・インスツルメンツ E2E™ is a trademark of Texas Instruments.  
すべての商標は、それぞれの所有者に帰属します。

### 9.4 静電気放電に関する注意事項



この IC は、ESD によって破損する可能性があります。テキサス・インスツルメンツは、IC を取り扱う際には常に適切な注意を払うことを推奨します。正しい取り扱いおよび設置手順に従わない場合、デバイスを破損するおそれがあります。

ESD による破損は、わずかな性能低下からデバイスの完全な故障まで多岐にわたります。精密な IC の場合、パラメータがわずかに変化するだけで公表されている仕様から外れる可能性があるため、破損が発生しやすくなっています。

### 9.5 用語集

[テキサス・インスツルメンツ用語集](#) この用語集には、用語や略語の一覧および定義が記載されています。

## 10 改訂履歴

資料番号末尾の英字は改訂を表しています。その改訂履歴は英語版に準じています。

| Changes from Revision AE (June 2025) to Revision AF (October 2025) | Page |
|--------------------------------------------------------------------|------|
| • DCK パッケージの接合部と周囲の間の熱抵抗値を次のように変更: 229°C/W >> 371.0°C/W.....       | 5    |
| • DCK パッケージの接合部とケース (上面) の間の熱抵抗値を次のように変更: 93°C/W >> 297.5°C/W..... | 5    |
| • DCK パッケージの接合部と基板の間の熱抵抗値を次のように変更: 65°C/W >> 258.6°C/W.....        | 5    |
| • DCK パッケージの接合部と上面の間の特性値を次のように変更: 2°C/W >> 195.6°C/W.....          | 5    |
| • DCK パッケージの接合部と基板の間の特性値を次のように変更: 64°C/W >> 256.2°C/W.....         | 5    |

| Changes from Revision AD (April 2014) to Revision AE (June 2025)    | Page |
|---------------------------------------------------------------------|------|
| • ドキュメント全体にわたって表、図、相互参照の採番方法を更新.....                                | 1    |
| • 「製品情報」表を「パッケージ情報」に変更.....                                         | 1    |
| • T <sub>stg</sub> を「絶対最大定格」表に移動.....                               | 4    |
| • 「取り扱い定格」を「ESD 定格」に変更.....                                         | 4    |
| • DBV パッケージの接合部と周囲の間の熱抵抗値を次のように変更: 278°C/W >> 357.1°C/W.....        | 5    |
| • DBV パッケージの接合部とケース (上面) の間の熱抵抗値を次のように変更: 164°C/W >> 263.7°C/W..... | 5    |
| • DBV パッケージの接合部と基板の間の熱抵抗値を次のように変更: 62°C/W >> 264.4°C/W.....         | 5    |
| • DBV パッケージの接合部と上面の間の特性値を次のように変更: 44°C/W >> 195.6°C/W.....          | 5    |

- DBV パッケージの接合部と基板の間の特性値を次のように変更: 62°C/W >> 262.2°C/W ..... [5](#)
- 

## 11 メカニカル、パッケージ、および注文情報

以降のページには、メカニカル、パッケージ、および注文に関する情報が記載されています。この情報は、指定のデバイスに使用できる最新のデータです。このデータは、予告なく、このドキュメントを改訂せずに変更される場合があります。本データシートのブラウザ版を使用されている場合は、画面左側の説明をご覧ください。

## PACKAGING INFORMATION

| Orderable part number             | Status<br>(1)    | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                                     |
|-----------------------------------|------------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------------------------------------|
| <a href="#">SN74LVC1G04DBVR</a>   | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | (C045, C04F, C04J,<br>C04K, C04R)<br>(C04H, C04P, C04S) |
| SN74LVC1G04DBVR.A                 | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | (C045, C04F, C04J,<br>C04K, C04R)<br>(C04H, C04P, C04S) |
| SN74LVC1G04DBVR.B                 | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 125   | (C045, C04F, C04J,<br>C04K, C04R)<br>(C04H, C04P, C04S) |
| SN74LVC1G04DBVRE4                 | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| SN74LVC1G04DBVRG4.A               | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| SN74LVC1G04DBVRG4.B               | Active           | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| <a href="#">SN74LVC1G04DBVT</a>   | Active           | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | (C045, C04F, C04J,<br>C04K, C04R)<br>(C04H, C04P, C04S) |
| SN74LVC1G04DBVT.B                 | Active           | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (C045, C04F, C04J,<br>C04K, C04R)<br>(C04H, C04P, C04S) |
| SN74LVC1G04DBVTE4                 | Active           | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| <a href="#">SN74LVC1G04DBVTG4</a> | Active           | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| SN74LVC1G04DBVTG4.B               | Active           | Production           | SOT-23 (DBV)   5 | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | C04<br>C04P                                             |
| <a href="#">SN74LVC1G04DCK3</a>   | Last<br>Time Buy | Production           | SC70 (DCK)   5   | 3000   LARGE T&R      | Yes         | SNBI                                 | Level-1-260C-UNLIM                | -40 to 125   | (CCF, CCZ)                                              |

| Orderable part number             | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)                              |
|-----------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------------------------|
| SN74LVC1G04DCK3.B                 | Last Time Buy | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | SNBI                                 | Level-1-260C-UNLIM                | -40 to 125   | (CCF, CCZ)                                       |
| <a href="#">SN74LVC1G04DCKR</a>   | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCJ, CC<br>K, CCR)<br>(CCH, CCP, CCS) |
| SN74LVC1G04DCKR.A                 | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCJ, CC<br>K, CCR)<br>(CCH, CCP, CCS) |
| SN74LVC1G04DCKR.B                 | Active        | Production           | SC70 (DCK)   5    | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCJ, CC<br>K, CCR)<br>(CCH, CCP, CCS) |
| SN74LVC1G04DCKRE4                 | Active        | Production           | SC70 (DCK)   5    | 3000   null           | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCK, CC<br>R)<br>(CCH, CCP, CCS)      |
| SN74LVC1G04DCKRE4.B               | Active        | Production           | SC70 (DCK)   5    | 3000   null           | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCK, CC<br>R)<br>(CCH, CCP, CCS)      |
| SN74LVC1G04DCKRG4                 | Active        | Production           | SC70 (DCK)   5    | 3000   null           | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC5                                              |
| SN74LVC1G04DCKRG4.B               | Active        | Production           | SC70 (DCK)   5    | 3000   null           | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC5                                              |
| <a href="#">SN74LVC1G04DCKT</a>   | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU   SN                          | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCJ, CC<br>R)<br>(CCH, CCP)           |
| SN74LVC1G04DCKT.B                 | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCJ, CC<br>R)<br>(CCH, CCP)           |
| SN74LVC1G04DCKTE4                 | Active        | Production           | SC70 (DCK)   5    | 250   null            | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCR)<br>(CCH, CCP)                    |
| SN74LVC1G04DCKTE4.B               | Active        | Production           | SC70 (DCK)   5    | 250   null            | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCR)<br>(CCH, CCP)                    |
| <a href="#">SN74LVC1G04DCKTG4</a> | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCR)<br>(CCH, CCP)                    |
| SN74LVC1G04DCKTG4.B               | Active        | Production           | SC70 (DCK)   5    | 250   SMALL T&R       | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | (CC5, CCF, CCR)<br>(CCH, CCP)                    |
| <a href="#">SN74LVC1G04DPWR</a>   | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | K4                                               |
| SN74LVC1G04DPWR.B                 | Active        | Production           | X2SON (DPW)   5   | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | K4                                               |
| <a href="#">SN74LVC1G04DRLR</a>   | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 125   | (CC7, CCR)                                       |

| Orderable part number           | Status<br>(1) | Material type<br>(2) | Package   Pins    | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|---------------------------------|---------------|----------------------|-------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| SN74LVC1G04DRLR.B               | Active        | Production           | SOT-5X3 (DRL)   5 | 4000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 125   | (CC7, CCR)          |
| <a href="#">SN74LVC1G04DRY2</a> | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DRY2.B               | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| <a href="#">SN74LVC1G04DRYR</a> | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DRYR.B               | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DRYRG4               | Active        | Production           | SON (DRY)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| <a href="#">SN74LVC1G04DSF2</a> | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DSF2.B               | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DSF2G4               | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DSF2G4.B             | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| <a href="#">SN74LVC1G04DSFR</a> | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAU   NIPDAUAG                    | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| SN74LVC1G04DSFR.B               | Active        | Production           | SON (DSF)   6     | 5000   LARGE T&R      | Yes         | NIPDAUAG                             | Level-1-260C-UNLIM                | -40 to 125   | CC                  |
| <a href="#">SN74LVC1G04YZPR</a> | Active        | Production           | DSBGA (YZP)   5   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | (CC7, CCN)          |
| SN74LVC1G04YZPR.B               | Active        | Production           | DSBGA (YZP)   5   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | (CC7, CCN)          |
| <a href="#">SN74LVC1G04YZVR</a> | Active        | Production           | DSBGA (YZV)   4   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | CC<br>7             |
| SN74LVC1G04YZVR.B               | Active        | Production           | DSBGA (YZV)   4   | 3000   LARGE T&R      | Yes         | SNAGCU                               | Level-1-260C-UNLIM                | -40 to 85    | CC<br>7             |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

**(6) Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF SN74LVC1G04 :**

- Automotive : [SN74LVC1G04-Q1](#)
- Enhanced Product : [SN74LVC1G04-EP](#)

NOTE: Qualified Version Definitions:

- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects
- Enhanced Product - Supports Defense, Aerospace and Medical Applications

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LVC1G04DBVR   | SOT-23       | DBV             | 5    | 3000 | 178.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DBVT   | SOT-23       | DBV             | 5    | 250  | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DBVTG4 | SOT-23       | DBV             | 5    | 250  | 178.0              | 9.0                | 3.23    | 3.17    | 1.37    | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DCKR   | SC70         | DCK             | 5    | 3000 | 178.0              | 9.0                | 2.4     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DCKT   | SC70         | DCK             | 5    | 250  | 178.0              | 9.0                | 2.4     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DCKTG4 | SC70         | DCK             | 5    | 250  | 178.0              | 9.2                | 2.4     | 2.4     | 1.22    | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DCKTG4 | SC70         | DCK             | 5    | 250  | 178.0              | 9.0                | 2.4     | 2.5     | 1.2     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DPWR   | X2SON        | DPW             | 5    | 3000 | 178.0              | 8.4                | 0.91    | 0.91    | 0.5     | 2.0     | 8.0    | Q3            |
| SN74LVC1G04DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 180.0              | 8.4                | 1.98    | 1.78    | 0.69    | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DRY2   | SON          | DRY             | 6    | 5000 | 180.0              | 9.5                | 1.6     | 1.15    | 0.75    | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DRYR   | SON          | DRY             | 6    | 5000 | 180.0              | 9.5                | 1.15    | 1.6     | 0.75    | 4.0     | 8.0    | Q1            |
| SN74LVC1G04DSF2   | SON          | DSF             | 6    | 5000 | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DSF2G4 | SON          | DSF             | 6    | 5000 | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q3            |
| SN74LVC1G04DSFR   | SON          | DSF             | 6    | 5000 | 180.0              | 9.5                | 1.16    | 1.16    | 0.5     | 4.0     | 8.0    | Q2            |
| SN74LVC1G04YZPR   | DSBGA        | YZP             | 5    | 3000 | 178.0              | 9.2                | 1.02    | 1.52    | 0.63    | 4.0     | 8.0    | Q1            |

---

| Device          | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| SN74LVC1G04YZVR | DSBGA        | YZV             | 4    | 3000 | 180.0              | 8.4                | 1.0     | 1.0     | 0.63    | 2.0     | 8.0    | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74LVC1G04DBVR   | SOT-23       | DBV             | 5    | 3000 | 208.0       | 191.0      | 35.0        |
| SN74LVC1G04DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74LVC1G04DBVT   | SOT-23       | DBV             | 5    | 250  | 210.0       | 185.0      | 35.0        |
| SN74LVC1G04DBVTG4 | SOT-23       | DBV             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74LVC1G04DCKR   | SC70         | DCK             | 5    | 3000 | 180.0       | 180.0      | 18.0        |
| SN74LVC1G04DCKT   | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74LVC1G04DCKTG4 | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74LVC1G04DCKTG4 | SC70         | DCK             | 5    | 250  | 180.0       | 180.0      | 18.0        |
| SN74LVC1G04DPWR   | X2SON        | DPW             | 5    | 3000 | 205.0       | 200.0      | 33.0        |
| SN74LVC1G04DRLR   | SOT-5X3      | DRL             | 5    | 4000 | 202.0       | 201.0      | 28.0        |
| SN74LVC1G04DRY2   | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G04DRYR   | SON          | DRY             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G04DSF2   | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G04DSF2G4 | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G04DSFR   | SON          | DSF             | 6    | 5000 | 184.0       | 184.0      | 19.0        |
| SN74LVC1G04YZPR   | DSBGA        | YZP             | 5    | 3000 | 220.0       | 220.0      | 35.0        |
| SN74LVC1G04YZVR   | DSBGA        | YZV             | 4    | 3000 | 182.0       | 182.0      | 20.0        |



# EXAMPLE BOARD LAYOUT

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:15X



SOLDER MASK DETAILS

4214839/K 08/2024

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.
7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DBV0005A

SOT-23 - 1.45 mm max height

SMALL OUTLINE TRANSISTOR



SOLDER PASTE EXAMPLE  
BASED ON 0.125 mm THICK STENCIL  
SCALE:15X

4214839/K 08/2024

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**DRY 6**

**USON - 0.6 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4207181/G


DRY0006A



## PACKAGE OUTLINE

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



4222894/A 01/2018

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



**LAND PATTERN EXAMPLE**  
1:1 RATIO WITH PKG SOLDER PADS  
EXPOSED METAL SHOWN  
SCALE:40X



**SOLDER MASK DETAILS**

4222894/A 01/2018

NOTES: (continued)

3. For more information, see QFN/SON PCB application report in literature No. SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

## EXAMPLE STENCIL DESIGN

DRY0006A

USON - 0.6 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.075 - 0.1 mm THICK STENCIL  
SCALE:40X

4222894/A 01/2018

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.




DSF0006A

## PACKAGE OUTLINE

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



4220597/B 06/2022

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC registration MO-287, variation X2AAF.

# EXAMPLE BOARD LAYOUT


DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:40X



SOLDER MASK DETAILS

4220597/B 06/2022

NOTES: (continued)


4. For more information, see Texas Instruments literature number SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

## EXAMPLE STENCIL DESIGN

DSF0006A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD




SOLDER PASTE EXAMPLE  
BASED ON 0.09 mm THICK STENCIL

PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:40X

4220597/B 06/2022

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.


DRL0005A



## PACKAGE OUTLINE

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



4220753/E 11/2024

### NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. Reference JEDEC registration MO-293 Variation UAAD-1

# EXAMPLE BOARD LAYOUT


DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



LAND PATTERN EXAMPLE  
SCALE:30X



SOLDERMASK DETAILS

4220753/E 11/2024

NOTES: (continued)


5. Publication IPC-7351 may have alternate designs.
6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

DRL0005A

SOT - 0.6 mm max height

PLASTIC SMALL OUTLINE



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL  
SCALE:30X

4220753/E 11/2024

NOTES: (continued)

7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
8. Board assembly site may have different recommendations for stencil design.

## GENERIC PACKAGE VIEW

**DPW 5**

**X2SON - 0.4 mm max height**

PLASTIC SMALL OUTLINE - NO LEAD



Images above are just a representation of the package family, actual package may vary.  
Refer to the product data sheet for package details.

4211218-3/D




# EXAMPLE BOARD LAYOUT

DPW0005A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE  
SOLDER MASK DEFINED  
SCALE:60X

4223102/D 03/2022

NOTES: (continued)


4. This package is designed to be soldered to a thermal pad on the board. For more information, refer to QFN/SON PCB application note in literature No. SLUA271 ([www.ti.com/lit/sluea271](http://www.ti.com/lit/sluea271)).

# EXAMPLE STENCIL DESIGN

DPW0005A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE  
BASED ON 0.1 mm THICK STENCIL

EXPOSED PAD 3  
92% PRINTED SOLDER COVERAGE BY AREA UNDER PACKAGE  
SCALE:100X

4223102/D 03/2022

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



YZP0005



# PACKAGE OUTLINE

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



D: Max = 1.418 mm, Min = 1.358 mm

E: Max = 0.918 mm, Min = 0.858 mm

4219492/A 05/2017

## NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.

# EXAMPLE BOARD LAYOUT


YZP0005

DSBGA - 0.5 mm max height

DIE SIZE BALL GRID ARRAY



LAND PATTERN EXAMPLE  
SCALE:40X




SOLDER MASK DETAILS  
NOT TO SCALE

4219492/A 05/2017

NOTES: (continued)

- Final dimensions may vary due to manufacturing tolerance considerations and also routing constraints. For more information, see Texas Instruments literature number SNVA009 ([www.ti.com/lit/snva009](http://www.ti.com/lit/snva009)).



SOLDER PASTE EXAMPLE  
 BASED ON 0.1 mm THICK STENCIL  
 SCALE:40X


4219492/A 05/2017

NOTES: (continued)

4. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release.

YZV (S-XBGA-N4)

DIE-SIZE BALL GRID ARRAY



D: Max = 0.918 mm, Min = 0.858 mm


E: Max = 0.918 mm, Min = 0.858 mm

4206083/C 07/13


- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. NanoFree™ package configuration.

NanoFree is a trademark of Texas Instruments.





LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:18X



SOLDER MASK DETAILS

4214834/G 11/2024

NOTES: (continued)

7. Publication IPC-7351 may have alternate designs.
8. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOLDER PASTE EXAMPLE  
BASED ON 0.125 THICK STENCIL  
SCALE:18X

4214834/G 11/2024

NOTES: (continued)

9. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
10. Board assembly site may have different recommendations for stencil design.

## 重要なお知らせと免責事項

TI は、技術データと信頼性データ (データシートを含みます)、設計リソース (リファレンス デザインを含みます)、アプリケーションや設計に関する各種アドバイス、Web ツール、安全性情報、その他のリソースを、欠陥が存在する可能性のある「現状のまま」提供しており、商品性および特定目的に対する適合性の黙示保証、第三者の知的財産権の非侵害保証を含みいかなる保証も、明示的または黙示的にかかわらず拒否します。

これらのリソースは、TI 製品を使用する設計の経験を積んだ開発者への提供を意図したものです。(1) お客様のアプリケーションに適した TI 製品の選定、(2) お客様のアプリケーションの設計、検証、試験、(3) お客様のアプリケーションに該当する各種規格や、その他のあらゆる安全性、セキュリティ、規制、または他の要件への確実な適合に関する責任を、お客様のみが単独で負うものとし、TI は一切の責任を拒否します。

上記の各種リソースは、予告なく変更される可能性があります。これらのリソースは、リソースで説明されている TI 製品を使用するアプリケーションの開発の目的でのみ、TI はその使用をお客様に許諾します。これらのリソースに関して、他の目的で複製することや掲載することは禁止されています。TI や第三者の知的財産権のライセンスが付与されている訳ではありません。お客様は、これらのリソースを自身で使用した結果発生するあらゆる申し立て、損害、費用、損失、責任について、TI およびその代理人を完全に補償するものとし、TI は一切の責任を拒否します。

TI の製品は、[TI の販売条件](#)、[TI の総合的な品質ガイドライン](#)、[ti.com](#) または TI 製品などに関連して提供される他の適用条件に従い提供されます。TI がこれらのリソースを提供することは、適用される TI の保証または他の保証の放棄の拡大や変更を意味するものではありません。TI がカスタム、またはカスタマー仕様として明示的に指定していない限り、TI の製品は標準的なカタログに掲載される汎用機器です。

お客様がいかなる追加条項または代替条項を提案する場合も、TI はそれらに異議を唱え、拒否します。

Copyright © 2026, Texas Instruments Incorporated

最終更新日：2025 年 10 月