



Solar Dice

CC430F5147 & TPS62740



Agenda

- Solar Dice demo:
 - Description
 - Setup and getting started
- Implementation: powering a low power wireless sensor
 - Requirements of powering low power wireless sensors based on the example of the “Solar Dice”
 - Solar cell characteristics
 - Selecting the storage capacitor
 - Requirements for the DC-DC converter
 - System bench data and scope plots
- CC430 energy optimized software tuning
- Conclusion and Summary

Energy Harvesting: Solar dice

Demo description

The demo demonstrates a wireless communication (CC430) between a dice and a computer powered by solar cells and step-down DC-DC converter (TPS62740)


– without any batteries!

The dice transmits wirelessly its position to a computer. Energy is harvested from 6 solar panels and the position is determined by an acceleration sensor.

- Transmission of dice position to the computer
- For voltage control, ADC10 application is running
- CC430 is running in low power mode
- Lowest current consumption is 2.36uA
- Transmission minimum cycle time is ~ 1s
- RF protocol is ~ 50 bytes
- PV voltage is ~ 4V
- Working with PV low leakage 330uF capacitor
- Optimized firmware for low current application

Energy Harvesting: Solar Dice

TPS62740 + CC430F5147



- **DC-DC TPS62740 spec digest:**

- Super low quiescent current: 360nA
- Slew Rate Controlled Load Switch
- 16 Pin-selectable output voltages between 1.8V – 3.3V
- Up to 90% Efficiency
- Up to 300mA Output Current

- **MCU CC430F5147 + RF core features digest:**


- RF frequency 868MHz/915MHz
- Data rate 250 kBaud, Deviation 127kHz
- Filter BW 541kHz, 36bit data, 16bit CRC
- RF Protocol length 50Byte total, RF Power level -1dBm
- Software optimized protocol to reduce current consumption

- **Accelerometer and Solar Cell digest:**

- Thin film Solar Panel Type Sanyo AM-5610 4.7V
- Digital, triaxial acceleration sensor BMA250 for cube side location


Solar powered dice

Simplified system block diagram



CC430F5147

TPS62740




Implementation: Powering a low power wireless sensor

Requirements for powering low power wireless sensors

- Reduce RF Peak Power consumption
- Minimize RF transmission time
- Minimize time of CC430 active mode
- Energy optimized MCU startup

Solar dice with CC430 and TPS62740



Energy source:


Amorphous solar panel
(Sanyo)

Effective size 18.6 x 17.6 mm
(3.27cm²); 4.7V no load


High efficiency step down converter:

- Ensures proper start up of CC430
- Provides regulated and optimized operating point for CC430
- Handles peak currents

Solar Panel characteristic




Panel **can** deliver average power, but **can't** handle peak power during TX!



Energy Storage Capacitor

Principle

Capacitor C1



Energy in storage cap $\sim V^2$

$V_{min} = 2.1V$ (system supply voltage)

$V_{max} \sim 3.6 - 4.5V$ panel voltage
(maximum output power)

Energy Storage Capacitor

Calculating available energy

$$dQ := C_1 \cdot dV$$

$$dE := dQ \cdot V$$

$$E := \int_{V_1}^{V_2} C_1 \cdot V dV$$

$$E_{C1_total} := \frac{1}{2} C_1 \cdot V_{max}^2$$

$$E_{C1_usable} := \frac{1}{2} \cdot C_1 \cdot \left(V_{max_C1}^2 - V_{min_C1}^2 \right)$$

Example:

Usuable energy in buffer capacitor:

300uF @ 4V → 1900uWs

Energy in storage cap ~ V²

V_{min} = 2.1V (system supply voltage)

V_{max} ~ 3.6 – 4.5V panel voltage

(maximum output power)

Requirements for the DC/DC Converter TPS62740

- Proper system start up:
 - system start up only if sufficient energy is stored in storage capacitor
 - Provide fast and monotonic supply voltage ramp up
- High efficiency at light loads
- Provides a stable and optimum operating voltage for the system
- RF friendly behavior (frequency, V_{OUT} ripple)





Figure 8. Efficiency V_{OUT} = 2.1V

Check out for more:

➤ www.ti.com/product/tps62740

➤ www.ti.com/dcs-control

Analysis: TX load profile




Peak Power consumption
@ 3.6V:

$$17\text{mA} * 3.6\text{V} = 51\text{mW}$$

Energy E(TX @ 3.6V VCC):

$$29\mu\text{As} * 3.6\text{V} = 104\mu\text{Ws}$$



Optimization @ 2.1V VCC:

Peak Power :


$$2.1\text{V} * 17\text{mA} = 36\text{mW}$$

Energy E (TX @ 2.1V

VCC): 61uWs


η (DC/DC) ~ 90%: 68uWs

Getting the system started



Proper system start up:


- “Energy Optimized” SW coding
- SW optimized for available energy in buffer cap
- Fast + monotonic voltage ramp (DC/DC)
- Stable supply voltage for the system



Failing start up:

- Start up sequence too energy hungry
- Supply voltage breakdown
- Panel can not support energy
- Bigger buffer cap necessary → cost


Adaption to changing light conditions



Normal operation with sufficient light:
TX every 2 sec.

Panel provides more energy than needed

Less light → reduced energy from panel



SW controlled TX cycle adaption:

- TX cycles are reduced at lower light conditions
- TX only if Voltage @ buffer cap reached 3.8V
- Operating solar panel @ maximum power area

CC430

Energy optimized software tuning

Standard firmware is most of the time not optimized for energy harvesting applications. For solar applications follow special programming rules!


1. On startup go immediately to LPM3 mode (Low power mode)
2. Optimize the startup. Partition the tasks. This allows enough charge storage in the buffer capacitor.
3. Time your cycle for RX or TX (1 s in this example)
4. Control the usable energy with ADC module
5. Make extensive use of low power modes
6. Start your tasks only if you have enough energy
7. Power down peripherals immediately after use
8. Optimize the RF protocol (Demo ~ 50bytes)

Check out for more:

➤ www.ti.com/cc430

Solar Dice

CC430 energy optimized software tuning



Conclusions

- 👍 Know the system requirements and possible trade offs
- 👍 Analyze the load profile and detect energy peaks
- 👍 Optimize system operating points to reduce peak energy consumption by Software and Hardware
- 👍 Select the right Harvester
- 👍 DC/DC converter provides proper system start up and operating voltage
- 👍 The less components the lower your power consumption
- 👍 ... and read datasheets carefully 😊

Summary

- In combination with Solar module and TPS62740, the CC430 works without batteries
- CC430 firmware optimized protocol to reduce current consumption is important

Check out for more:

- www.ti.com/product/tps62740
- www.ti.com/cc430
- www.ti.com/dcs-control

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated