

EVM User's Guide: LMK6BEVM

LMK6B Evaluation Module




1 Description

The LMK6BEVM provides a complete evaluation platform to evaluate the clock performance and flexibility of the Texas Instruments LMK6B Ultra Low Jitter, High-performance BAW Oscillator family. This EVM can be used as a flexible clock source for compliance testing, performance evaluation, and initial system prototyping. The onboard edge-launch SMA ports provide access to the configurable clock output of the LMK6B, which allows the device to interface with test equipment and reference boards using commercially available coaxial cables, adapters, or baluns (not included).

2 Features

- Contains footprints for three standard 6-pin oscillator packages: DLE (3.2mm × 2.5mm), DLF (2.5mm × 2.0mm), and DLR (2.0mm × 1.6mm)
- Onboard voltage regulator to generate standard supply voltages (2.5V, 3.3V)
- Can be powered using USB only, option for external power supply



LMK6BEVM Evaluation Board

3 Evaluation Module Overview

3.1 Introduction

The LMK6B is an ultra-high-performance clock oscillator using TI's BAW technology. The LMK6B is available in three package sizes: DLE (3.2mm × 2.5mm), DLF (2.5mm × 2.0mm), and DLR (2.0mm × 1.6mm). All three footprints are included on the EVM with independent termination networks. By default, the LMK6BEVM is populated with a 625MHz AC-LVPECL variant of LMK6B with a DLF package size (Y1). The DLE and DLR footprints are left unpopulated so the user can solder the desired frequency variant for evaluation.

The LMK6B is powered entirely using USB and the onboard voltage regulator. An external power supply can also be used for evaluation.

To begin evaluating the LMK6B BAW oscillator, use a matched pair of SMA coaxial cables to connect the clock output to test equipment such as an oscilloscope or phase noise analyzer, or use the output directly as a clock source for another reference board.

3.2 Kit Contents

The box contains:

- One LMK6BEVM board (DC407A)

3.3 Specifications

- Supports standard frequencies from 50MHz to 2.5GHz
- ±20ppm total frequency stability inclusive of all factors, including 10 years aging
- Ultra-Low jitter: 35fs max RMS jitter for Fout = 625MHz
- Operating temperature range of -40°C to +85°C

4 Implementation Results

4.1 Evaluation Setup Requirement

The evaluation requires the following hardware:

- DC power supply or USB power supply
- Oscilloscope
- Signal analyzer (optional)

4.2 Setup

4.2.1 Connection Diagram

Figure 4-1 shows the LMK6BEVM connection diagram. The top region of the board contains 3 zones for each package size. Each zone contains a footprint to populate a LMK6B oscillator (Y1, Y2, Y3), a jumper to pull the oscillator pin 1 and 2 high or low (J2, J4, J9), and an output termination network with an SMA connector (P1-P4, P6, P7).

The bottom-left region of the board contains jumpers for configuring the power supply network. Provide input power using the included USB cable, or an external supply connected to the EXTIN SMA connector (P5).




Figure 4-1. Connection Diagram

4.2.2 Power Supply

Set the jumpers according to the table below.

Table 4-1. Power Supply Jumper Configuration

Input Source	Voltage Regulator	Pins to Short on J7	Pins to Short on J8
5V USB	LDO	3-4	1-2
EXTIN	LDO	1-2	1-2
	Bypass	open	3-4

To use the onboard voltage regulators, apply between 3.6V and 5V to the EXTIN SMA connector (P5), or supply 5V using the mini USB connector. The voltage regulator provides 2.5V or 3.3V to the LMK6B device based on the jumper selection of J10.

To bypass the onboard voltage regulators and use an external supply directly, remove the jumper from J7 and short pins 3-4 on J8.

4.2.3 Clock Output

To test the clock output of Y1, connect the P1 and P2 SMA connectors to an oscilloscope or phase noise analyzer. Similarly, to test the clock output of Y2 or Y3, connect P3-P4 or P6-P7 respectively to an oscilloscope or phase noise analyzer.

4.2.4 EVM Header Configuration

[Table 4-2](#) summarizes the EVM header configurations to connect and route power to the VDD domains of the individual devices, in addition to the individual output enable (OE), standby (ST), or frequency select (FSEL) pins depending on the device populated.

Table 4-2. EVM Header Configurations

Component	Name	Description
J7, J8	VDD	VDD Supply Voltage Source J7: Tie pins 3-4 (default) J8: Tie pins 1-2 (default) By default, VDD is sourced from USB power supply and onboard LDO. See Table 4-1 for more details
J10	VDD_Reg	VDD_Reg Voltage Level Tie pins 3-4 (default): Selects VDD = 3.3V Tie pins 1-2: Selects VDD = 2.5V
J2, J4, J9	Oscillator pin 1 and 2 (OE and FSEL)	Oscillator Pin 1 (OE) Tie pins 1-3 (default): Pull LMK6B OE to VDD, clock output is enabled Tie pins 3-5: Pull LMK6B OE to GND, clock output is disabled Oscillator Pin 2 (FSEL) Tie pins 2-4 (default): Pull LMK6B FSEL to VDD, output frequency = 312.5MHz Tie pins 4-6: Pull LMK6B FSEL to GND, output frequency = 156.25MHz Jumper removed: LMK6B FSEL is internally biased to mid-level, output frequency = 625MHz

4.2.5 Configuring the Output Clock Termination

The LMK6BEVM comes pre-populated with an AC-coupled termination designed for LP-HCSL, LVDS, AC-LVPECL, and custom swing output formats. For the LVDS, AC-LVPECL, and custom swing output types, terminate the output with a 100Ω differential termination. If the output is AC-coupled, terminate the P and N channels with 50Ω tied to a bias voltage to set the desired common mode voltage.

For LP-HCSL, the output can interface with a high-impedance load to provide the full signal swing. Unlike conventional HCSL drivers, no external termination resistors are required.




Figure 4-2. AC-LVPECL, LVDS, and Custom Swing Output Terminations




Figure 4-3. LP-HCSL Output Termination

4.3 Performance Data and Results

4.3.1 Typical Measurement




Figure 4-4. Phase Noise Plot of 312.5MHz LMK6B Variant

5 Hardware Design Files

5.1 Schematics




Figure 5-1. Schematic - LMK6B Oscillators




Figure 5-2. Schematic - Power Supply

5.2 PCB Layout and Layer Stack-Up

5.2.1 PCB Layer Stack-Up

#	Name	Material	Type	Weight	Thickness	Dk
	Top Overlay		Overlay			
	Top Solder	Solder Resist	Solder Mask		0.4mil	4
1	Top Layer		Signal	1oz	1.4mil	
	Dielectric 1	MT40	Prepreg		10mil	3.45
2	Int1 (GND)		Signal	1oz	1.4mil	
	Dielectric 2	FR4	Core		32.87mil	4.8
3	Int2 (PWR)		Signal	1oz	1.4mil	
	Dielectric 3	MT40	Prepreg		10mil	3.45
4	Bottom Layer		Signal	1oz	1.4mil	
	Bottom Solder	Solder Resist	Solder Mask		0.4mil	4
	Bottom Overlay		Overlay			

Figure 5-3. PCB Layer Stack-Up

5.2.2 PCB Layout




Figure 5-4. Top View Composite




Figure 5-5. GND Layer




Figure 5-6. PWR Layer




Figure 5-7. Bottom View Composite

5.3 Bill of Materials (BOM)

Bill of Materials

Designator	Description	Manufacturer	PartNumber	Quantity
C1, C4, C5, C8, C19, C20	0.1 μ F \pm 10% 10V Ceramic Capacitor X7R 0402 (1005 Metric)	Würth Electronics	8.85012E+11	6
C2, C7, C18	CAP, CERM, 1 μ F, 16V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	TDK	CGA3E1X7R1C105K080A C	3
C3, C6, C17	0.1 μ F \pm 10% 16V Ceramic Capacitor 0201 (0603 Metric)	Passive Plus	0201BB104KW160	3
C9, C16	CAP, CERM, 10 μ F, 16V, +/- 20%, X7R, 0805	Taiyo Yuden	EMK212BB7106MG-T	2
C10	10 μ F \pm 20% 25V Ceramic Capacitor X5R 0603 (1608 Metric)	Murata Electronics	ZRB18AR61E106ME01L	1
C11	1 μ F \pm 10% 16V Ceramic Capacitor X7S 0603 (1608 Metric)	Murata	GRM188C71C105KA12D	1
C12	0.1 μ F \pm 10% 16V Ceramic Capacitor X7R 0603 (1608 Metric)	Murata Electronics North America	GCJ188R71C104KA01D	1
C13	CAP, CERM, 0.01 μ F, 25V, +/- 1%, C0G/NP0, 0603	Kemet	C0603C103F3GACTU	1
C14	CAP, CERM, 0.1 μ F, 16V, +/- 5%, X7R, 0603	Kemet	C0603C104J4RACTU	1
C15	Chip Multilayer Ceramic Capacitors for General Purpose, 0402, 22 μ F, X5R, 15%, 20%, 10V	Murata	GRM158R61A226ME15D	1
D1, D2, D3	LED, Green, SMD	Lite-On	LTST-C190GKT	3
H1, H2, H3, H4	Machine Screw, Round, #4-40 \times 1/4, Nylon, Philips panhead	B&F Fastener Supply	NY PMS 440 0025 PH	4
H5, H6, H7, H8	Standoff, Hex, 0.5"L #4-40 Nylon	Keystone	1902C	4
J1, J3, J6	Header, 100mil, 2x1, Gold, TH	Samtec	TSW-102-07-G-S	3
J2, J4, J9	Header, 2.54mm, 3x2, Gold, Black, SMT	Sullins Connector Solutions	GBC03DABN-M30	3
J5	Connector, Receptacle, Mini-USB Type B, R/A, Top Mount SMT	TE Connectivity	1734035-2	1
J7, J8, J10	Header, 2.54mm, 2x2, Gold, SMT	Würth Elektronik	61030421121	3
P1, P2, P3, P4, P5, P6, P7	Connector, End launch SMA, 50 Ω , SMT	Cinch Connectivity	142-0701-851	7
R1, R5, R10, R16, R39, R47	RES Thick Film, 0 Ω , 0.2W, 0402	Vishay Dale	CRCW04020000Z0EDHP	6
R6, R7, R13, R14, R35, R36	RES, 220, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	Vishay-Dale	CRCW0603220RJNEA	6
R19, R20, R30	RES, 120, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	Vishay-Dale	CRCW0603120RJNEA	3
R22	RES, 2.43k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	Vishay-Dale	CRCW06032K43FKEA	1
R23	RES, 3.57k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	Vishay-Dale	CRCW06033K57FKEA	1
R25, R26	RES, 1.15k, 1%, 0.1W, AEC-Q200 Grade 0, 0603	Vishay-Dale	CRCW06031K15FKEA	2
R27	33k Ω \pm 0.1% 0.1W, 1/10W Chip Resistor 0603 (1608 Metric) Automotive AEC-Q200 Thin Film	Panasonic	ERA-3AEB333V	1
SH-J1, SH-J2, SH-J3, SH-J4, SH-J5, SH-J6, SH-J7, SH-J8, SH-J9, SH-J10, SH-J11, SH-J12	Shunt, 100mil, Gold plated, Black	Samtec	SNT-100-BK-G	12
TP1, TP2, TP4, TP6	Test Point, Miniature, SMT	Keystone	5019	4

Designator	Description	Manufacturer	PartNumber	Quantity
U1	500mA High-Accuracy Low-Noise Low-Dropout (LDO) Voltage Regulator, DSK0010A (WSON-10)	Texas Instruments	TPS7A9001DSKR	1
U2	Single-Channel ESD Protection in 0402 Package With 10pF Capacitance and 9V Breakdown, DPY0002A (X1SON-2)	Texas Instruments	TPD1E10B09DPYR	1
Y1	LMK6B_DLF	Texas Instruments	LMK6BPK625000FDLFR	1
C21, C22, C23, C24, C25, C26	Cap Ceramic 2pF 50V C0G ±0.1pF SMD 0402 +125°C Paper T/R	Samsung	CL05C020BB5NNNC	0
FID1, FID2, FID3	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	0
R2, R4, R11, R15, R40, R46	RES, 210, 1%, 0.063W, AEC-Q200 Grade 0, 0402	Vishay-Dale	CRCW0402210RFKED	0
R3, R8, R9	RES, 100, 1%, 0.125W, AEC-Q200 Grade 1, 0402	AT Ceramics	ATC504L1000FTNCFT	0
R21, R24, R28, R29, R31, R32, R33, R34, R37, R38, R44, R45	RES, 10.0k, 1%, 0.1 W, 0603	Yageo	RC0603FR-0710KL	0
Y2	LMK6B_DLE	Texas Instruments	LMK6B_DLE	0
Y3	LMK6B_DLR6A	Texas Instruments	LMK6B_DLR6A	0

6 Additional Information

Trademarks

All trademarks are the property of their respective owners.

7 Related Documentation

See the [LMK6Bx Ultra Low Jitter, High-performance BAW Oscillator Datasheet](#) for more information about the LMK6B devices.

STANDARD TERMS FOR EVALUATION MODULES

1. *Delivery:* TI delivers TI evaluation boards, kits, or modules, including any accompanying demonstration software, components, and/or documentation which may be provided together or separately (collectively, an "EVM" or "EVMs") to the User ("User") in accordance with the terms set forth herein. User's acceptance of the EVM is expressly subject to the following terms.
 - 1.1 EVMs are intended solely for product or software developers for use in a research and development setting to facilitate feasibility evaluation, experimentation, or scientific analysis of TI semiconductors products. EVMs have no direct function and are not finished products. EVMs shall not be directly or indirectly assembled as a part or subassembly in any finished product. For clarification, any software or software tools provided with the EVM ("Software") shall not be subject to the terms and conditions set forth herein but rather shall be subject to the applicable terms that accompany such Software
 - 1.2 EVMs are not intended for consumer or household use. EVMs may not be sold, sublicensed, leased, rented, loaned, assigned, or otherwise distributed for commercial purposes by Users, in whole or in part, or used in any finished product or production system.
2. *Limited Warranty and Related Remedies/Disclaimers:*
 - 2.1 These terms do not apply to Software. The warranty, if any, for Software is covered in the applicable Software License Agreement.
 - 2.2 TI warrants that the TI EVM will conform to TI's published specifications for ninety (90) days after the date TI delivers such EVM to User. Notwithstanding the foregoing, TI shall not be liable for a nonconforming EVM if (a) the nonconformity was caused by neglect, misuse or mistreatment by an entity other than TI, including improper installation or testing, or for any EVMs that have been altered or modified in any way by an entity other than TI, (b) the nonconformity resulted from User's design, specifications or instructions for such EVMs or improper system design, or (c) User has not paid on time. Testing and other quality control techniques are used to the extent TI deems necessary. TI does not test all parameters of each EVM. User's claims against TI under this Section 2 are void if User fails to notify TI of any apparent defects in the EVMs within ten (10) business days after delivery, or of any hidden defects with ten (10) business days after the defect has been detected.
 - 2.3 TI's sole liability shall be at its option to repair or replace EVMs that fail to conform to the warranty set forth above, or credit User's account for such EVM. TI's liability under this warranty shall be limited to EVMs that are returned during the warranty period to the address designated by TI and that are determined by TI not to conform to such warranty. If TI elects to repair or replace such EVM, TI shall have a reasonable time to repair such EVM or provide replacements. Repaired EVMs shall be warranted for the remainder of the original warranty period. Replaced EVMs shall be warranted for a new full ninety (90) day warranty period.

WARNING

Evaluation Kits are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems.

User shall operate the Evaluation Kit within TI's recommended guidelines and any applicable legal or environmental requirements as well as reasonable and customary safeguards. Failure to set up and/or operate the Evaluation Kit within TI's recommended guidelines may result in personal injury or death or property damage. Proper set up entails following TI's instructions for electrical ratings of interface circuits such as input, output and electrical loads.

NOTE:

EXPOSURE TO ELECTROSTATIC DISCHARGE (ESD) MAY CAUSE DEGRADATION OR FAILURE OF THE EVALUATION KIT; TI RECOMMENDS STORAGE OF THE EVALUATION KIT IN A PROTECTIVE ESD BAG.

3 Regulatory Notices:

3.1 United States

3.1.1 Notice applicable to EVMs not FCC-Approved:

FCC NOTICE: This kit is designed to allow product developers to evaluate electronic components, circuitry, or software associated with the kit to determine whether to incorporate such items in a finished product and software developers to write software applications for use with the end product. This kit is not a finished product and when assembled may not be resold or otherwise marketed unless all required FCC equipment authorizations are first obtained. Operation is subject to the condition that this product not cause harmful interference to licensed radio stations and that this product accept harmful interference. Unless the assembled kit is designed to operate under part 15, part 18 or part 95 of this chapter, the operator of the kit must operate under the authority of an FCC license holder or must secure an experimental authorization under part 5 of this chapter.

3.1.2 For EVMs annotated as FCC – FEDERAL COMMUNICATIONS COMMISSION Part 15 Compliant:

CAUTION

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC Interference Statement for Class A EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

FCC Interference Statement for Class B EVM devices

NOTE: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

3.2 Canada

3.2.1 For EVMs issued with an Industry Canada Certificate of Conformance to RSS-210 or RSS-247

Concerning EVMs Including Radio Transmitters:

This device complies with Industry Canada license-exempt RSSs. Operation is subject to the following two conditions:

(1) this device may not cause interference, and (2) this device must accept any interference, including interference that may cause undesired operation of the device.

Concernant les EVMs avec appareils radio:

Le présent appareil est conforme aux CNR d'Industrie Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes: (1) l'appareil ne doit pas produire de brouillage, et (2) l'utilisateur de l'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

Concerning EVMs Including Detachable Antennas:

Under Industry Canada regulations, this radio transmitter may only operate using an antenna of a type and maximum (or lesser) gain approved for the transmitter by Industry Canada. To reduce potential radio interference to other users, the antenna type and its gain should be so chosen that the equivalent isotropically radiated power (e.i.r.p.) is not more than that necessary for successful communication. This radio transmitter has been approved by Industry Canada to operate with the antenna types listed in the user guide with the maximum permissible gain and required antenna impedance for each antenna type indicated. Antenna types not included in this list, having a gain greater than the maximum gain indicated for that type, are strictly prohibited for use with this device.

Concernant les EVMs avec antennes détachables

Conformément à la réglementation d'Industrie Canada, le présent émetteur radio peut fonctionner avec une antenne d'un type et d'un gain maximal (ou inférieur) approuvé pour l'émetteur par Industrie Canada. Dans le but de réduire les risques de brouillage radioélectrique à l'intention des autres utilisateurs, il faut choisir le type d'antenne et son gain de sorte que la puissance isotrope rayonnée équivalente (p.i.r.e.) ne dépasse pas l'intensité nécessaire à l'établissement d'une communication satisfaisante. Le présent émetteur radio a été approuvé par Industrie Canada pour fonctionner avec les types d'antenne énumérés dans le manuel d'usage et ayant un gain admissible maximal et l'impédance requise pour chaque type d'antenne. Les types d'antenne non inclus dans cette liste, ou dont le gain est supérieur au gain maximal indiqué, sont strictement interdits pour l'exploitation de l'émetteur.

3.3 Japan

3.3.1 *Notice for EVMs delivered in Japan:* Please see http://www.tij.co.jp/lstds/ti_ja/general/eStore/notice_01.page 日本国内に輸入される評価用キット、ボードについては、次のところをご覧ください。

<https://www.ti.com/ja-jp/legal/notice-for-evaluation-kits-delivered-in-japan.html>

3.3.2 *Notice for Users of EVMs Considered "Radio Frequency Products" in Japan:* EVMs entering Japan may not be certified by TI as conforming to Technical Regulations of Radio Law of Japan.

If User uses EVMs in Japan, not certified to Technical Regulations of Radio Law of Japan, User is required to follow the instructions set forth by Radio Law of Japan, which includes, but is not limited to, the instructions below with respect to EVMs (which for the avoidance of doubt are stated strictly for convenience and should be verified by User):

1. Use EVMs in a shielded room or any other test facility as defined in the notification #173 issued by Ministry of Internal Affairs and Communications on March 28, 2006, based on Sub-section 1.1 of Article 6 of the Ministry's Rule for Enforcement of Radio Law of Japan,
2. Use EVMs only after User obtains the license of Test Radio Station as provided in Radio Law of Japan with respect to EVMs, or
3. Use of EVMs only after User obtains the Technical Regulations Conformity Certification as provided in Radio Law of Japan with respect to EVMs. Also, do not transfer EVMs, unless User gives the same notice above to the transferee. Please note that if User does not follow the instructions above, User will be subject to penalties of Radio Law of Japan.

【無線電波を送信する製品の開発キットをお使いになる際の注意事項】 開発キットの中には技術基準適合証明を受けていないものがあります。技術適合証明を受けていないものご使用に際しては、電波法遵守のため、以下のいずれかの措置を取っていただく必要がありますのでご注意ください。

1. 電波法施行規則第6条第1項第1号に基づく平成18年3月28日総務省告示第173号で定められた電波暗室等の試験設備でご使用いただく。
2. 実験局の免許を取得後ご使用いただく。
3. 技術基準適合証明を取得後ご使用いただく。

なお、本製品は、上記の「ご使用にあたっての注意」を譲渡先、移転先に通知しない限り、譲渡、移転できないものとします。

上記を遵守頂けない場合は、電波法の罰則が適用される可能性があることをご留意ください。日本テキサス・イ

ンスツルメンツ株式会社

東京都新宿区西新宿 6 丁目 2 4 番 1 号

西新宿三井ビル

3.3.3 *Notice for EVMs for Power Line Communication:* Please see http://www.tij.co.jp/lstds/ti_ja/general/eStore/notice_02.page

電力線搬送波通信についての開発キットをお使いになる際の注意事項については、次のところをご覧ください。 <https://www.ti.com/ja-jp/legal/notice-for-evaluation-kits-for-power-line-communication.html>

3.4 European Union

3.4.1 *For EVMs subject to EU Directive 2014/30/EU (Electromagnetic Compatibility Directive):*

This is a class A product intended for use in environments other than domestic environments that are connected to a low-voltage power-supply network that supplies buildings used for domestic purposes. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

-
- 4 *EVM Use Restrictions and Warnings:*
 - 4.1 EVMS ARE NOT FOR USE IN FUNCTIONAL SAFETY AND/OR SAFETY CRITICAL EVALUATIONS, INCLUDING BUT NOT LIMITED TO EVALUATIONS OF LIFE SUPPORT APPLICATIONS.
 - 4.2 User must read and apply the user guide and other available documentation provided by TI regarding the EVM prior to handling or using the EVM, including without limitation any warning or restriction notices. The notices contain important safety information related to, for example, temperatures and voltages.
 - 4.3 *Safety-Related Warnings and Restrictions:*
 - 4.3.1 User shall operate the EVM within TI's recommended specifications and environmental considerations stated in the user guide, other available documentation provided by TI, and any other applicable requirements and employ reasonable and customary safeguards. Exceeding the specified performance ratings and specifications (including but not limited to input and output voltage, current, power, and environmental ranges) for the EVM may cause personal injury or death, or property damage. If there are questions concerning performance ratings and specifications, User should contact a TI field representative prior to connecting interface electronics including input power and intended loads. Any loads applied outside of the specified output range may also result in unintended and/or inaccurate operation and/or possible permanent damage to the EVM and/or interface electronics. Please consult the EVM user guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative. During normal operation, even with the inputs and outputs kept within the specified allowable ranges, some circuit components may have elevated case temperatures. These components include but are not limited to linear regulators, switching transistors, pass transistors, current sense resistors, and heat sinks, which can be identified using the information in the associated documentation. When working with the EVM, please be aware that the EVM may become very warm.
 - 4.3.2 EVMs are intended solely for use by technically qualified, professional electronics experts who are familiar with the dangers and application risks associated with handling electrical mechanical components, systems, and subsystems. User assumes all responsibility and liability for proper and safe handling and use of the EVM by User or its employees, affiliates, contractors or designees. User assumes all responsibility and liability to ensure that any interfaces (electronic and/or mechanical) between the EVM and any human body are designed with suitable isolation and means to safely limit accessible leakage currents to minimize the risk of electrical shock hazard. User assumes all responsibility and liability for any improper or unsafe handling or use of the EVM by User or its employees, affiliates, contractors or designees.
 - 4.4 User assumes all responsibility and liability to determine whether the EVM is subject to any applicable international, federal, state, or local laws and regulations related to User's handling and use of the EVM and, if applicable, User assumes all responsibility and liability for compliance in all respects with such laws and regulations. User assumes all responsibility and liability for proper disposal and recycling of the EVM consistent with all applicable international, federal, state, and local requirements.
 5. *Accuracy of Information:* To the extent TI provides information on the availability and function of EVMs, TI attempts to be as accurate as possible. However, TI does not warrant the accuracy of EVM descriptions, EVM availability or other information on its websites as accurate, complete, reliable, current, or error-free.
 6. *Disclaimers:*
 - 6.1 EXCEPT AS SET FORTH ABOVE, EVMS AND ANY MATERIALS PROVIDED WITH THE EVM (INCLUDING, BUT NOT LIMITED TO, REFERENCE DESIGNS AND THE DESIGN OF THE EVM ITSELF) ARE PROVIDED "AS IS" AND "WITH ALL FAULTS." TI DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, REGARDING SUCH ITEMS, INCLUDING BUT NOT LIMITED TO ANY EPIDEMIC FAILURE WARRANTY OR IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF ANY THIRD PARTY PATENTS, COPYRIGHTS, TRADE SECRETS OR OTHER INTELLECTUAL PROPERTY RIGHTS.
 - 6.2 EXCEPT FOR THE LIMITED RIGHT TO USE THE EVM SET FORTH HEREIN, NOTHING IN THESE TERMS SHALL BE CONSTRUED AS GRANTING OR CONFERRING ANY RIGHTS BY LICENSE, PATENT, OR ANY OTHER INDUSTRIAL OR INTELLECTUAL PROPERTY RIGHT OF TI, ITS SUPPLIERS/LICENSORS OR ANY OTHER THIRD PARTY, TO USE THE EVM IN ANY FINISHED END-USER OR READY-TO-USE FINAL PRODUCT, OR FOR ANY INVENTION, DISCOVERY OR IMPROVEMENT, REGARDLESS OF WHEN MADE, CONCEIVED OR ACQUIRED.
 7. *USER'S INDEMNITY OBLIGATIONS AND REPRESENTATIONS.* USER WILL DEFEND, INDEMNIFY AND HOLD TI, ITS LICENSORS AND THEIR REPRESENTATIVES HARMLESS FROM AND AGAINST ANY AND ALL CLAIMS, DAMAGES, LOSSES, EXPENSES, COSTS AND LIABILITIES (COLLECTIVELY, "CLAIMS") ARISING OUT OF OR IN CONNECTION WITH ANY HANDLING OR USE OF THE EVM THAT IS NOT IN ACCORDANCE WITH THESE TERMS. THIS OBLIGATION SHALL APPLY WHETHER CLAIMS ARISE UNDER STATUTE, REGULATION, OR THE LAW OF TORT, CONTRACT OR ANY OTHER LEGAL THEORY, AND EVEN IF THE EVM FAILS TO PERFORM AS DESCRIBED OR EXPECTED.

8. *Limitations on Damages and Liability:*

8.1 *General Limitations.* IN NO EVENT SHALL TI BE LIABLE FOR ANY SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL, OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THESE TERMS OR THE USE OF THE EVMS , REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. EXCLUDED DAMAGES INCLUDE, BUT ARE NOT LIMITED TO, COST OF REMOVAL OR REINSTALLATION, ANCILLARY COSTS TO THE PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES, RETESTING, OUTSIDE COMPUTER TIME, LABOR COSTS, LOSS OF GOODWILL, LOSS OF PROFITS, LOSS OF SAVINGS, LOSS OF USE, LOSS OF DATA, OR BUSINESS INTERRUPTION. NO CLAIM, SUIT OR ACTION SHALL BE BROUGHT AGAINST TI MORE THAN TWELVE (12) MONTHS AFTER THE EVENT THAT GAVE RISE TO THE CAUSE OF ACTION HAS OCCURRED.

8.2 *Specific Limitations.* IN NO EVENT SHALL TI'S AGGREGATE LIABILITY FROM ANY USE OF AN EVM PROVIDED HEREUNDER, INCLUDING FROM ANY WARRANTY, INDEMNITY OR OTHER OBLIGATION ARISING OUT OF OR IN CONNECTION WITH THESE TERMS, , EXCEED THE TOTAL AMOUNT PAID TO TI BY USER FOR THE PARTICULAR EVM(S) AT ISSUE DURING THE PRIOR TWELVE (12) MONTHS WITH RESPECT TO WHICH LOSSES OR DAMAGES ARE CLAIMED. THE EXISTENCE OF MORE THAN ONE CLAIM SHALL NOT ENLARGE OR EXTEND THIS LIMIT.

9. *Return Policy.* Except as otherwise provided, TI does not offer any refunds, returns, or exchanges. Furthermore, no return of EVM(s) will be accepted if the package has been opened and no return of the EVM(s) will be accepted if they are damaged or otherwise not in a resalable condition. If User feels it has been incorrectly charged for the EVM(s) it ordered or that delivery violates the applicable order, User should contact TI. All refunds will be made in full within thirty (30) working days from the return of the components(s), excluding any postage or packaging costs.

10. *Governing Law:* These terms and conditions shall be governed by and interpreted in accordance with the laws of the State of Texas, without reference to conflict-of-laws principles. User agrees that non-exclusive jurisdiction for any dispute arising out of or relating to these terms and conditions lies within courts located in the State of Texas and consents to venue in Dallas County, Texas. Notwithstanding the foregoing, any judgment may be enforced in any United States or foreign court, and TI may seek injunctive relief in any United States or foreign court.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025