

SN74AVC2T244 2-Bit Unidirectional Voltage-level Translator

1 Features


- Wide Operating V_{CC} Range of 0.9 V to 3.6 V
- Low Static-Power Consumption, 6- μ A Max I_{CC}
- Output Enable Feature Allows User to Disable Outputs to Reduce Power Consumption
- ± 24 -mA Output Drive at 3.0 V
- I_{off} Supports Partial Power-Down-Mode Operation
- Input Hysteresis Allows Slow Input Transition and Better Switching Noise Immunity at Input
- Maximum Data Rates
 - 380 Mbps (1.8-V to 3.3-V Translation)
 - 200 Mbps (<1.8-V to 3.3-V Translation)
 - 200 Mbps (Translate to 2.5 V or 1.8 V)
 - 150 Mbps (Translate to 1.5 V)
 - 100 Mbps (Translate to 1.2 V)
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
 - 5000-V Human-Body Model (A114-A)

2 Applications

- Handset, Smartphone, Tablet, Server

3 Description

This 2-bit unidirectional translator uses two separate configurable power-supply rails. The A port is designed to track V_{CCA} . V_{CCA} accepts any supply voltage from 0.9 V to 3.6 V. The B port is designed to track V_{CCB} . V_{CCB} accepts any supply voltage from 0.9 V to 3.6 V. This allows for low-voltage translation between 0.9-V, 1.2-V, 1.5-V, 1.8-V, 2.5-V and 3.6-V voltage nodes. For the SN74AVC2T244, when the output-enable ($\overline{OE}$) input is high, all outputs are placed in the high-impedance state. The SN74AVC2T244 is designed so that the $\overline{OE}$ input circuit is referenced to V_{CCA} . This device is fully specified for partial-power-down applications using I_{off} . The I_{off} circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.



DQE and DQM Packages 8 Pin X2SON (Top View)



Table of Contents

1 Features	1	6.4 AC Electrical Characteristics.....	6
2 Applications	1	7 Device and Documentation Support	7
3 Description	1	7.1 Receiving Notification of Documentation Updates.....	7
4 Revision History	2	7.2 Support Resources.....	7
5 Pin Configuration and Functions	3	7.3 Trademarks.....	7
6 Specifications	4	7.4 Electrostatic Discharge Caution.....	7
6.1 Absolute Maximum Ratings.....	4	7.5 Glossary.....	7
6.2 Recommended Operating Conditions.....	4	8 Mechanical, Packaging, and Orderable Information	7
6.3 Electrical Characteristics.....	5		

4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision B (September 2011) to Revision C (March 2021)	Page
• Updated the numbering format for tables, figures, and cross-references throughout the document.....	1
• Updated the title of the data sheet.....	1
• Deleted <i>Ordering Information</i> table, see POA at the end of the datasheet.	1

5 Pin Configuration and Functions




Figure 5-1. DQE and DQM Packages 8 Pin X2SON (Top View)

Table 5-1. Pin Functions

PIN	FUNCTION
VCCA	Input Port DC Power Supply
VCCB	Output Port DC Power Supply
GND	Ground
An	Input Port
Bn	Output Port
OE	Output Enable

6 Specifications

6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted) ⁽¹⁾

			MIN	MAX	UNIT
Voltage	DC Supply voltage, V_{CCA} V_{CCB}		−0.5	4.6	V
	DC Input voltage, V_I	A_n	−0.5	4.6	V
	Control Input, V_C	$\overline{OE}$	−0.5	4.6	V
	DC Output voltage, V_O , $V_{CCA} = V_{CCB} = 0$	(Power Down) B_n	−0.5	4.6	V
		(Active Mode) B_n	−0.5	4.6	
		3-State Mode B_n	−0.5	4.6	
	DC Input Diode current, I_{IK}	$V_I < GND$		−20	mA
	DC Output Diode current, I_{OK}	$V_O < GND$		−50	mA
	DC Output Source/Sink current, I_O			±50	mA
	DC Supply current per supply pin, I_{CCA} , I_{CCB}			±100	mA
I_{GND}	DC Ground current per ground pin			±100	mA
T_{stg}	Storage temperature range		−65	150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

6.2 Recommended Operating Conditions

			MIN	MAX	UNIT
V_{CCA} , V_{CCB}	Positive DC Supply voltage		0.9	3.6	V
V_I	Bus input voltage		GND	3.6	V
V_I	Input voltage		GND	3.6	V
V_C	Control input	$\overline{OE}$	GND	3.6	V
V_O	Bus output voltage	(Power Down Mode) B_n	GND	3.6	V
		(Active Mode) B_n	GND	V_{CCB}	V
		3-State Mode B_n	GND	3.6	V
T_A	Operating free-air temperature		−40	85	°C
$\Delta t/\Delta v$	Input transition rise or fall rate V_I from 30% to 70% of V_{CC} ; $V_{CC} = 3.3\text{ V} \pm 0.3\text{ V}$		0	10	nS

6.3 Electrical Characteristics

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER ^{(1) (2)}		TEST CONDITIONS	V _{CCA} (V)	V _{CCB} (V)	–40°C to 85°C		UNIT
					MIN	MAX	
V _{IH}	Input HIGH Voltage (An, $\overline{OE}$)		2.7 – 3.6	0.9 – 3.6	2.0	–	V
			2.3 – 2.7		1.6	–	
			1.4 – 2.3		0.65 × V _{CCA}	–	
			0.9 – 1.4		0.9 × V _{CCA}	–	
V _{IL}	Input LOW voltage (An, $\overline{OE}$)		2.7 – 3.6	0.9 – 3.6	–	0.8	V
			2.3 – 2.7		–	0.7	
			1.4 – 2.3		–	0.35 × V _{CCA}	
			0.9 – 1.5		–	0.1 × V _{CCA}	
V _{OH}	Output HIGH voltage	I _{OH} = –100 µA; V _I = V _H	0.9 – 3.6	0.9 – 3.6	V _{CCB} – 0.2	–	V
		I _{OH} = –0.5 mA; V _I = V _H	0.9	0.9	0.75 × V _{CCB}	–	
		I _{OH} = –2 mA; V _I = V _H	1.4	1.4	1.05	–	
		I _{OH} = –6 mA; V _I = V _H	1.65	1.65	1.25	–	
			2.3	2.3	2.0	–	
		I _{OH} = –12 mA; V _I = V _H	2.3	2.3	1.8	–	
			2.7	2.7	2.2	–	
		I _{OH} = –18 mA; V _I = V _H	2.3	2.3	1.7	–	
			3.0	3.0	2.4	–	
		I _{OH} = –24 mA; V _I = V _H	3.0	3.0	2.2	–	
V _{OL}	Output LOW voltage	I _{OH} = 100 µA; V _I = V _H	0.9 – 3.6	0.9 – 3.6	–	0.2	V
		I _{OH} = 0.5 mA; V _I = V _H	1.1	1.1	–	0.3	
		I _{OH} = 2 mA; V _I = V _H	1.4	1.4	–	0.35	
		I _{OH} = 6 mA; V _I = V _H	1.65	1.65	–	0.3	
			2.3	2.3	–	0.4	
		I _{OH} = 12 mA; V _I = V _H	2.7	2.7	–	0.4	
			2.3	2.3	–	0.6	
		I _{OH} = 18 mA; V _I = V _H	3.0	3.0	–	0.4	
			3.0	3.0	–	0.55	
I _I	Input Leakage Current	V _I = V _{CCA} or GND	0.9 – 3.6	0.9 – 3.6	–1.0	1.5	µA
I _{OFF}	Power-Off Leakage Current	$\overline{OE}$ = 0V	0	0.9 – 3.6	–1.0	1.3	µA
			0.9 – 3.6	0	–1.0	1.5	
I _{CCA}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 – 3.6	0.9 – 3.6	–	3.0	µA
I _{CCB}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 – 3.6	0.9 – 3.6	–	3.0	µA
I _{CCA} + I _{CCB}	Quiescent Supply Current	V _I = V _{CCA} or GND; I _O = 0	0.9 – 3.6	0.9 – 3.6	–	6.0	µA
ΔI _{CCA}	Increase in I _{CC} per Input Voltage, Other inputs at V _{CCA} or GND	V _I = V _{CCA} – 0.3 V; V _I = V _{CCA} or GND	3.6	3.6	–	5.0	µA

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER ^{(1) (2)}		TEST CONDITIONS	V _{CCA} (V)	V _{CCB} (V)	–40°C to 85°C		UNIT
					MIN	MAX	
ΔI_{CCB}	Increase in I_{CC} per Input Voltage, Other inputs at V_{CCA} or GND	$V_I = V_{CCA} - 0.3 \text{ V}$; $V_I = V_{CCA}$ or GND	3.6	3.6	–	5.0	μA
I_{OZ}	I/O Tri-State Output Leakage Current	$T_A = 25^\circ\text{C}$, $\overline{OE} = 0 \text{ V}$	0.9 – 3.6	0.9 – 3.6	–1.0	1.0	μA

(1) V_{CCO} is the V_{CC} associated with the output port.

(2) V_{CCI} is the V_{CC} associated with the input port.

6.4 AC Electrical Characteristics

over operating free-air temperature range (unless otherwise noted)

	PARAMETER	V _{CCA} (V)	V _{CCB} (V)	MIN	MAX	UNIT
t_{PLH} , t_{PHL}	Propagation Delay, A_n to B_n	0.9 – 3.6	0.9 – 3.6		20	nS
		1.2 – 3.6	1.2 – 3.6		7	
		1.8 – 3.6	1.8 – 3.6		3.5	
t_{PZH} , t_{PZL}	Output Enable, $\overline{OE}$ to B_n	0.9 – 3.6	0.9 – 3.6		23	nS
		1.2 – 3.6	1.2 – 3.6		6.5	
		1.8 – 3.6	1.8 – 3.6		4.1	
t_{PHZ} , t_{PLZ}	Output Disable, $\overline{OE}$ to B_n	0.9 – 3.6	0.9 – 3.6		17	nS
		1.2 – 3.6	1.2 – 3.6		7	
		1.8 – 3.6	1.8 – 3.6		4.3	
t_{OSHL} , t_{OSLH}	Output to Output Skew, Time	0.9 – 3.6	0.9 – 3.6		0.15	nS
		1.2 – 3.6	1.2 – 3.6		0.15	
		1.8 – 3.6	1.8 – 3.6		0.15	

Table 6-1. Capacitance

(2)	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT
C_{IN}	Control Pin Input Capacitance	$V_{CCA} = V_{CCB} = 3.3 \text{ V}$, $V_I = 0 \text{ V}$ or $V_{CCA/B}$	3.5	pF
$C_{I/O}$	I/O Pin Input capacitance	$V_{CCA} = V_{CCB} = 3.3 \text{ V}$, $V_I = 0 \text{ V}$ or $V_{CCA/B}$	5.0	pF
C_{PD}	Power Dissipation Capacitance	$V_{CCA} = V_{CCB} = 3.3 \text{ V}$, $V_I = 0 \text{ V}$ or $V_{CCA/B}$, $f = 10 \text{ MHz}$	33	pF

(1) Typical values are at $T_A = +25^\circ\text{C}$.

(2) C_{PD} is defined as the value of the IC's equivalent capacitance from which the operating current can be calculated from: $I_{CC(\text{operating})} \approx C_{PD} \times V_{CC} \times f_{IN} \times N_{SW}$ where $I_{CC} = I_{CCA} + I_{CCB}$ and N_{SW} = total number of outputs switching.

7 Device and Documentation Support

7.1 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Subscribe to updates* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

7.2 Support Resources

[TI E2E™ support forums](#) are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's [Terms of Use](#).

7.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

7.4 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

7.5 Glossary

[TI Glossary](#) This glossary lists and explains terms, acronyms, and definitions.

8 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
SN74AVC2T244DQER	Active	Production	X2SON (DQE) 8	5000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA
SN74AVC2T244DQER.B	Active	Production	X2SON (DQE) 8	5000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA
SN74AVC2T244DQMR	Active	Production	X2SON (DQM) 8	3000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA
SN74AVC2T244DQMR.B	Active	Production	X2SON (DQM) 8	3000 LARGE T&R	Yes	NIPDAUAG	Level-1-260C-UNLIM	-40 to 85	VA

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
SN74AVC2T244DQER	X2SON	DQE	8	5000	180.0	8.4	1.2	1.6	0.55	4.0	8.0	Q1
SN74AVC2T244DQMR	X2SON	DQM	8	3000	180.0	8.4	1.57	2.21	0.59	4.0	8.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74AVC2T244DQER	X2SON	DQE	8	5000	202.0	201.0	28.0
SN74AVC2T244DQMR	X2SON	DQM	8	3000	202.0	201.0	28.0

DQM (R-PX2SON-N8)

PLASTIC SMALL OUTLINE NO-LEAD




4210302/A 06/2009

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. SON (Small Outline No-Lead) package configuration.




DQM (R-PX2SON-N8)

PLASTIC SMALL OUTLINE NO-LEAD

Example Board Layout





Example Stencil Design
0.1mm Thick Stencil
(Note C)



Solder Mask Details

4218746/A 07/13

- NOTES:
- A. All linear dimensions are in millimeters.
 - B. This drawing is subject to change without notice.
 - C. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC 7525 for stencil design considerations.
 - D. Customers should contact their board fabrication site for recommended solder mask tolerances.



4225204/A 08/2019

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This package complies to JEDEC MO-287 variation X2EAF.

EXAMPLE BOARD LAYOUT


DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 40X



4225204/A 08/2019

NOTES: (continued)


- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).

EXAMPLE STENCIL DESIGN

DQE0008A

X2SON - 0.4 mm max height

PLASTIC SMALL OUTLINE - NO LEAD



SOLDER PASTE EXAMPLE
BASED ON 0.075 MM THICK STENCIL
SCALE: 40X

4225204/A 08/2019

NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025