


## FEATURES

- **Controlled Baseline**
  - One Assembly/Test Site, One Fabrication Site
- **Enhanced Diminishing Manufacturing Sources (DMS) Support**
- **Enhanced Product-Change Notification**
- **Qualification Pedigree <sup>(1)</sup>**
- **Complete Pulse-Width Modulation (PWM) Power-Control Circuitry**
- **Completely Synchronized Operation**
- **Internal Undervoltage Lockout Protection**
- **Wide Supply-Voltage Range**
- **Internal Short-Circuit Protection**
- **Oscillator Frequency . . . 500 kHz Max**
- **Variable Dead Time Provides Control Over Total Range**
- **Internal Regulator Provides a Stable 2.5-V Reference Supply**

(1) Component qualification in accordance with JEDEC and industry standards to ensure reliable operation over an extended temperature range. This includes, but is not limited to, Highly Accelerated Stress Test (HAST) or biased 85/85, temperature cycle, autoclave or unbiased HAST, electromigration, bond intermetallic life, and mold compound life. Such qualification testing should not be viewed as justifying use of this component beyond specified performance and environmental limits.



## DESCRIPTION/ORDERING INFORMATION

The TL1451A-EP incorporates on a single monolithic chip all the functions required in the construction of two pulse-width modulation (PWM) control circuits. Designed primarily for power-supply control, the TL1451A-EP contains an on-chip 2.5-V regulator, two error amplifiers, an adjustable oscillator, two dead-time comparators, undervoltage lockout circuitry, and dual common-emitter output transistor circuits.

The uncommitted output transistors provide common-emitter output capability for each controller. The internal amplifiers exhibit a common-mode voltage range from 1.04 V to 1.45 V. The dead-time control (DTC) comparator has no offset unless externally altered and can provide 0% to 100% dead time. The on-chip oscillator can be operated by terminating RT and CT. During low  $V_{CC}$  conditions, the undervoltage lockout control circuit feature locks the outputs off until the internal circuitry is operational.

The TL1451A-EP is characterized for operation from  $-55^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

### ORDERING INFORMATION


$T_A$	PACKAGE <sup>(1)</sup>		ORDERABLE PART NUMBER	TOP-SIDE MARKING
$-55^{\circ}\text{C}$ to $125^{\circ}\text{C}$	SOIC – D	Tape and reel	TL1451AMDREP	TL1451EPG4

(1) Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

FUNCTIONAL BLOCK DIAGRAM



COMPONENT COUNT

Resistors	65
Capacitors	8
Transistors	105
JFETs	18

**Absolute Maximum Ratings<sup>(1)</sup>**

over operating free-air temperature range

			MIN	MAX	UNIT
$V_{CC}$	Supply voltage			51	V
$V_I$	Amplifier input voltage			20	V
$V_O$	Collector output voltage			51	V
$I_O$	Collector output current			21	mA
	Continuous power total dissipation		See Dissipation Rating Table		
$T_A$	Operating free-air temperature range	M suffix	-55	125	°C
$T_{stg}$	Storage temperature range		-65	150	°C
	Lead temperature	1,6 mm (1/16 in) from case for 10 s		260	°C

(1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

### Dissipation Ratings

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR ABOVE $T_A = 25^\circ\text{C}$	$T_A = 70^\circ\text{C}$ POWER RATING	$T_A = 85^\circ\text{C}$ POWER RATING	$T_A = 125^\circ\text{C}$ POWER RATING
D	1088 mW	8.7 mW/°C	696 mW	566 mW	218 mW

### Recommended Operating Conditions

		MIN	MAX	UNIT
$V_{CC}$	Supply voltage	3.6	50	V
$V_I$	Amplifier input voltage	1.05	1.45	V
$V_O$	Collector output voltage		50	V
$I_O$	Collector output current		20	mA
	Current into feedback terminal		45	μA
$R_F$	Feedback resistor	100		kΩ
$C_T$	Timing capacitor	150	15000	pF
$R_T$	Timing resistor	5.1	100	kΩ
	Oscillator frequency	1	500	kHz
$T_A$	Operating free-air temperature	-55	125	°C
		M suffix		

### Reference Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS		MIN	TYP <sup>(1)</sup>	MAX	UNIT
Output voltage (pin 16)	$I_O = 1\text{ mA}$	$T_A = 25^\circ\text{C}$	2.4	2.5	2.6	V
		$T_A = \text{MIN and } 125^\circ\text{C}$	2.35	2.46	2.65	
Output voltage change with temperature				-0.63%	$\pm 4\%$ <sup>(2)</sup>	
Input voltage regulation	$V_{CC} = 3.6\text{ V to } 40\text{ V}$	$T_A = 25^\circ\text{C}$		2	12.5	mV
		$T_A = 125^\circ\text{C}$		0.7	15	
		$T_A = \text{MIN}$		0.3	30	
Output voltage regulation	$I_O = 0.1\text{ mA to } 1\text{ mA}$	$T_A = 25^\circ\text{C}$		1	7.5	mV
		$T_A = 125^\circ\text{C}$		0.3	14	
		$T_A = \text{MIN}$		0.3	20	
Short-circuit output current	$V_O = 0$		3	10	30	mA

- (1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.  
 (2) These parameters are not production tested.

### Undervoltage Lockout Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Upper threshold voltage ( $V_{CC}$ )	$T_A = 25^\circ\text{C}$		2.72		V
	$T_A = 125^\circ\text{C}$		1.7		
	$T_A = \text{MIN}$		3.15		
Lower threshold voltage ( $V_{CC}$ )	$T_A = 25^\circ\text{C}$		2.6		V
	$T_A = 125^\circ\text{C}$		1.65		
	$T_A = \text{MIN}$		3.09		
Hysteresis ( $V_{CC}$ )	$T_A = 25^\circ\text{C}$	80	120		mV
	$T_A = 125^\circ\text{C}$	10	50		
	$T_A = \text{MIN}$	10	60		
Reset threshold voltage ( $V_{CC}$ )	$T_A = 25^\circ\text{C}$	1.5			V
	$T_A = 125^\circ\text{C}$	0.95			
	$T_A = \text{MIN}$	1.5			

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

### Short-Circuit Protection Control Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Input threshold voltage (SCP)	$T_A = 25^\circ\text{C}$	650	700	750	mV
	$T_A = 125^\circ\text{C}$	400	478	650	
	$T_A = \text{MIN}$	800	880	950	
Standby voltage (SCP)		140	185	230	mV
Latched input voltage (SCP)	$T_A = 25^\circ\text{C}$		60	120	mV
	$T_A = 125^\circ\text{C}$		70	120	
	$T_A = \text{MIN}$		60	120	
Equivalent timing resistance			170		k $\Omega$
Comparator threshold voltage (FEEDBACK)			1.18		V

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

### Oscillator Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Frequency	$C_T = 330\text{ pF}$ , $R_T = 10\text{ k}\Omega$	$T_A = 25^\circ\text{C}$	200		kHz
		$T_A = 125^\circ\text{C}$	195		
		$T_A = \text{MIN}$	193		
Standard deviation of frequency	$C_T = 330\text{ pF}$ , $R_T = 10\text{ k}\Omega$		2%		
Frequency change with voltage	$V_{CC} = 3.6\text{ V to }40\text{ V}$	$T_A = 25^\circ\text{C}$	1%		
		$T_A = 125^\circ\text{C}$	1%		
		$T_A = \text{MIN}$	3%		
Frequency change with temperature			1.37%	$\pm 10\%$ <sup>(2)</sup>	

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

(2) These parameters are not production tested.

**Dead-Time Control Section Electrical Characteristics**

 over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Input bias current (DTC)	$T_A = 25^\circ\text{C}$			1	$\mu\text{A}$
	$T_A = \text{MIN}$ and $125^\circ\text{C}$			3	
Latch mode (source) current (DTC)		-80	-145		$\mu\text{A}$
Latched input voltage (DTC)	$T_A = 25^\circ\text{C}$	2.3			V
	$T_A = 125^\circ\text{C}$	2.22	2.32		
	$T_A = \text{MIN}$	2.28	2.4		
Input threshold voltage at $f = 10\text{ kHz}$ (DTC)	Zero duty cycle		2.05	2.25 <sup>(2)</sup>	V
	Maximum duty cycle	1.2 <sup>(2)</sup>	1.45		

 (1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

(2) These parameters are not production tested.

**Error-Amplifier Section Electrical Characteristics**

 over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Input offset voltage	$V_O (\text{FEEDBACK}) = 1.25\text{ V}$	$T_A = 25^\circ\text{C}$		$\pm 7$	mV
		$T_A = 125^\circ\text{C}$		$\pm 10$	
		$T_A = \text{MIN}$		$\pm 12$	
Input offset current	$V_O (\text{FEEDBACK}) = 1.25\text{ V}$	$T_A = 25^\circ\text{C}$		$\pm 100$	nA
		$T_A = 125^\circ\text{C}$		$\pm 100$	
		$T_A = \text{MIN}$		$\pm 200$	
Input bias current	$V_O (\text{FEEDBACK}) = 1.25\text{ V}$	$T_A = 25^\circ\text{C}$	160	500	nA
		$T_A = 125^\circ\text{C}$	100	500	
		$T_A = \text{MIN}$	142	700	
Common-mode input voltage range	$V_{CC} = 3.6\text{ V}$ to $40\text{ V}$	1.05 to 1.45			V
Open-loop voltage amplification	$R_F = 200\text{ k}\Omega$	$T_A = 25^\circ\text{C}$	70	80	dB
		$T_A = 125^\circ\text{C}$	70	80	
		$T_A = \text{MIN}$	64	80	
Unity-gain bandwidth			1.5		MHz
Common-mode rejection ratio		60	80		dB
Positive output voltage swing		2			V
Negative output voltage swing				1	V
Output (sink) current (FEEDBACK)	$V_{ID} = -0.1\text{ V}$ , $V_O = 1.25\text{ V}$	$T_A = 25^\circ\text{C}$	0.5	1.6	mA
		$T_A = 125^\circ\text{C}$	0.4	1.8	
		$T_A = \text{MIN}$	0.3	1.7	
Output (source) current (FEEDBACK)	$V_{ID} = 0.1\text{ V}$ , $V_O = 1.25\text{ V}$	$T_A = 25^\circ\text{C}$	-45	-70	$\mu\text{A}$
		$T_A = 125^\circ\text{C}$	-25	-50	
		$T_A = \text{MIN}$	-15	-70	

 (1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

### Output Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Collector off-state current	$V_O = 50\text{ V}$			10	$\mu\text{A}$
Output saturation voltage	$T_A = 25^\circ\text{C}$		1.2	2	V
	$T_A = 125^\circ\text{C}$		1.6	2.4	
	$T_A = \text{MIN}$		1.36	2.2	
Short-circuit output current	$V_O = 6\text{ V}$		90		mA

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

### PWM Comparator Section Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Input threshold voltage at $f = 10\text{ kHz}$ (FEEDBACK)	Zero duty cycle		2.05	2.25 <sup>(2)</sup>	V
	Maximum duty cycle	1.2 <sup>(2)</sup>	1.45		

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

(2) These parameters are not production tested.


### Total Device Electrical Characteristics

over recommended operating free-air temperature range,  $V_{CC} = 6\text{ V}$ ,  $f = 200\text{ kHz}$  (unless otherwise noted)


PARAMETER	TEST CONDITIONS	MIN	TYP <sup>(1)</sup>	MAX	UNIT
Standby supply current	Off-state		1.3	1.8	mA
Average supply current	$R_T = 10\text{ k}\Omega$		1.7	2.4	mA

(1) All typical values are at  $T_A = 25^\circ\text{C}$ , unless otherwise indicated.

**PARAMETER MEASUREMENT INFORMATION**



**Figure 1. Test Circuit**



(1) Protection enable time,  $t_{pe} = (0.051 \times 10^6 \times C_{pe})$  in seconds

**Figure 2. TL1451A-EP Timing**

TYPICAL CHARACTERISTICS




Figure 3. Estimated Devised Life at Elevated Temperatures for Wirebond Voiding Fail Mode




Figure 4. Triangle Oscillator Frequency vs Timing Resistance




Figure 5. Oscillator Frequency Variation vs Free-Air Temperature



TYPICAL CHARACTERISTICS (continued)




Figure 6. Triangle Waveform Swing Voltage vs Timing Capacitance




Figure 7. Triangle Waveform Period vs Timing Capacitance




Figure 8. Reference Output Voltage Variation vs Free-Air Temperature




Figure 9. Reference Output Voltage Variation vs Free-Air Temperature

TYPICAL CHARACTERISTICS (continued)




Figure 10. Reference Output Voltage vs Supply Voltage




Figure 11. Dropout Voltage Variation vs Free-air Temperature




Figure 12. Undervoltage Lockout Hysteresis Characteristics




Figure 13. Undervoltage Lockout Characteristics

TYPICAL CHARACTERISTICS (continued)




Figure 14. Short-Circuit Protection Characteristics





Figure 15. Protection Enable Time vs Protection Enable Capacitance

TYPICAL CHARACTERISTICS (continued)




Figure 16. Error Amplifier Maximum Output Voltage Swing vs Frequency




Figure 17. Open-Loop Voltage Amplification vs Frequency







Figure 18. Gain (Amplifier in Unity-Gain Configuration vs Frequency)

**TYPICAL CHARACTERISTICS (continued)**



**Figure 19. Closed-Loop Gain and Phase Shift vs Frequency**



TYPICAL CHARACTERISTICS (continued)



Test Circuit

Figure 20. Closed-Loop Gain and Phase Shift vs Frequency



**TYPICAL CHARACTERISTICS (continued)**



Test Circuit

Figure 21. Closed-Loop Gain and Phase Shift vs Frequency

TYPICAL CHARACTERISTICS (continued)



Test Circuit

Figure 22. Closed-Loop Gain and Phase Shift vs Frequency




Figure 23. Output Sink Current vs Collector Output Saturation Voltage



TYPICAL CHARACTERISTICS (continued)




Figure 24. Maximum Output Voltage Swing vs Free-Air Temperature




Figure 25. Output Transistor On Duty Cycle vs Dead-Time Input Voltage




Figure 26. Standby Current vs Supply Voltage

TYPICAL CHARACTERISTICS (continued)




Figure 27. Standby Current vs Free-Air Temperature





Figure 28. Maximum Continuous Power Dissipation vs Free-Air Temperature

**APPLICATION INFORMATION**



**Figure 29. High-Speed Dual Switching Regulator**

**PACKAGING INFORMATION**

Orderable part number	Status (1)	Material type (2)	Package   Pins	Package qty   Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
<a href="#">TL1451AMDREP</a>	Active	Production	SOIC (D)   16	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-55 to 125	TL1451EP
TL1451AMDREP.A	Active	Production	SOIC (D)   16	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-55 to 125	TL1451EP
<a href="#">V62/06611-01XE</a>	Active	Production	SOIC (D)   16	2500   LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-55 to 125	TL1451EP

(1) **Status:** For more details on status, see our [product life cycle](#).

(2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

(3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

(4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

(5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

(6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**OTHER QUALIFIED VERSIONS OF TL1451A-EP :**

- Catalog : [TL1451A](#)

- Automotive : [TL1451A-Q1](#)

NOTE: Qualified Version Definitions:

- Catalog - TI's standard catalog product
- Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TL1451AMDREP	SOIC	D	16	2500	330.0	16.4	6.5	10.3	2.1	8.0	16.0	Q1


**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal



Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TL1451AMDREP	SOIC	D	16	2500	350.0	350.0	43.0

D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



4040047-6/M 06/11

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  -  C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
  -  D. Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
  - E. Reference JEDEC MS-012 variation AC.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2025, Texas Instruments Incorporated

Last updated 10/2025